



LOW NOISE, HIGH GAIN & IP3


Monolithic Amplifier PMA4-33GLN+

Mini-Circuits

50Ω 0.7 to 3.0 GHz

THE BIG DEAL

- Low noise figure, 0.47 dB typ. at 900 MHz
- High gain, 39 dB typ. at 900 MHz
- High OIP3, +40 dBm typ. at 900 MHz
- High Pout, P1dB 22.6 dBm typ. at 900 MHz



Generic photo used for illustration purposes only

CASE STYLE: DG1886

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

APPLICATIONS

- Base station infrastructure
- Portable Wireless
- LTE
- GPS
- GSM
- Airborne radar

PRODUCT OVERVIEW

Mini-Circuits PMA4-33GLN+ is an E-PHEMT* based, low noise, dual chip, MMIC amplifier with a unique combination of low noise, high gain and high IP3, making this amplifier ideal for sensitive, high-dynamic-range receiver applications. This design operates on a single 5V supply, is well matched for 50Ω systems, and comes in a 4mm x 4mm, low-profile package accommodating dense circuit board layouts.

KEY FEATURES

| Feature | Advantages |
|---|---|
| Low noise, 0.47 dB at 0.9 GHz | Enables lower system noise figure performance |
| High Gain <ul style="list-style-type: none"> • 38.9 dB at 900 MHz • 26.9 dB at 2000 MHz | High gain with low noise minimizes the effect of noise figure reduction resulting from cascading of multiple stages and simplifies circuit design. |
| High IP3 <ul style="list-style-type: none"> • +40.4 dBm at 0.9 GHz • +40.2 dBm at 2 GHz | Combination of low noise and high IP3 makes this MMIC amplifier ideal for use in low noise receiver front end (RFE) as it gives the user advantages of sensitivity & two-tone IM performance at both ends of the dynamic range. |
| High max input power <ul style="list-style-type: none"> • +24 dBm | Ruggedized design provides high power handling for input powers common at receiver inputs, eliminating the need for an external limiter in most cases. |
| 4 x 4mm 16-lead MCLP package | Provides low inductance, repeatable transitions, and excellent thermal contact to PCB |
| High reliability | Low signal operating current of 154 mA nominal maintains junction temperatures typically below 103°C at 85°C ground lead temperature. |

*Enhancement mode Pseudomorphic High Electron Mobility Transistor

REV B
ECO-010881
PMA4-33GLN+
TH/RS/CP
211130





LOW NOISE, HIGH GAIN & IP3

Monolithic Amplifier PMA4-33GLN+

Mini-Circuits

ELECTRICAL SPECIFICATIONS¹ AT 25°C AND 5V, UNLESS NOTED OTHERWISE

| Parameter | Condition (GHz) | Min. | Typ. | Max. | Units |
|---|--------------------|------|------------------|------|-------|
| Frequency Range | | 0.7 | | 3.0 | GHz |
| Noise Figure | 0.7 | | 0.53 | — | dB |
| | 0.9 | | 0.47 | 0.85 | |
| | 1.5 | | 0.66 | — | |
| | 2.0 | | 0.91 | — | |
| | 3.0 | | 1.79 | — | |
| Gain | 0.7 | 35.0 | 41.3 | — | dB |
| | 0.9 | | 38.9 | | |
| | 1.5 | | 31.8 | | |
| | 2.0 | | 26.9 | | |
| | 3.0 | | 18.0 | | |
| Input Return Loss | 0.7 | | 9.1 | | dB |
| | 0.9 | | 12.3 | | |
| | 1.5 | | 13.0 | | |
| | 2.0 | | 11.6 | | |
| | 3.0 | | 9.4 | | |
| Output Return Loss | 0.7 | | 5.5 | | dB |
| | 0.9 | | 10.0 | | |
| | 1.5 | | 12.8 | | |
| | 2.0 | | 6.7 | | |
| | 3.0 | | 7.0 | | |
| Output Power @1 dB compression ² | 0.7 | | 22.5 | | dBm |
| | 0.9 | | 22.6 | | |
| | 1.5 | | 22.6 | | |
| | 2.0 | | 22.9 | | |
| | 3.0 | | 20.6 | | |
| Output IP3 | 0.7 | | 35.8 | | dBm |
| | 0.9 | | 40.4 | | |
| | 1.5 | | 41.0 | | |
| | 2.0 | | 40.2 | | |
| | 3.0 | | 35.7 | | |
| Device Operating Voltage | | | 5.0 | | V |
| Device Operating Current | Q1 ² | | 55 | | mA |
| | Q2 ² | | 97 | | |
| | Total ² | | 152 | 186 | |
| Device Current Variation vs. Temperature at 5V ³ | | | -135 | | µA/°C |
| Device Current Variation vs. Voltage at 25°C | | | 0.027 | | mA/mV |
| Thermal Resistance, junction-to-ground lead | | | 53 (Q1), 36 (Q2) | | °C/W |

1. Measured on Mini-Circuits Characterization test board TB-754+. See Characterization Test Circuit (Fig. 1)

2. Current increases at P1dB

3. (Current at 85°C - Current at -45°C)/130





Monolithic Amplifier PMA4-33GLN+

MAXIMUM RATINGS⁴


| Parameter | Ratings (Q1) | Ratings (Q2) |
|-------------------------------------|--|--|
| Operating Temperature (ground lead) | -40°C to 85°C | -40°C to 85°C |
| Storage Temperature | -65°C to 150°C | -65°C to 150°C |
| Total Power Dissipation | 0.55W | 1W |
| Input Power (CW) | +24dBm (5 minutes max) ^(Note 5) | +21 dBm (50-2000 MHz) +26 dBm (2000-3000 MHz) ^(Note 6) |
| Q1 & Q2 cascade on TB-754+ | +24 dBm | |
| DC Voltage | 5.5 V | 6V |

4. Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.


5. Measured on Mini-Circuits test board, TB-615+

6. Measured on Mini-Circuits test board, TB-313

SIMPLIFIED SCHEMATIC & PAD DESCRIPTION



TOP VIEW




| Function | Pad Number | Description (See Figure 1) |
|-------------------|---------------------|--|
| RF IN Q1 | 2 | Connects to RF input via C1 and Pad 3 via L1 |
| RF-OUT Q1 & DC IN | 5 | Connects to RF IN Q2 via C2 and V_s via L2 |
| V Bias Q1 | 4 | Connects to Supply voltage V_s via R1 |
| RF-GND Q1 | 3 | Connects to ground via C4/C5 |
| RF-IN Q2 | 8 | Connects to RF OUT Q1 via C2 |
| RF-OUT Q2 & DC IN | 11 | Connects to RF OUT via C3 and V_s via L3 |
| Ground | Paddle | Connects to ground |
| No Connection | 1,6,7,9,10,12 to 16 | Not used internally. Connected to ground on test board |



LOW NOISE, HIGH GAIN & IP3

Monolithic Amplifier PMA4-33GLN+

RECOMMENDED APPLICATION AND CHARACTERIZATION TEST CIRCUIT



BOM OF TEST BOARD TB-754+

| SEQ | Size | Description |
|----------|--------|-----------------------|
| DUT | 4x4 mm | PMA4-33GLN+ Amplifier |
| L1 | 0402 | Inductor 15nH |
| L2 | 0402 | Inductor 5.6nH |
| L3 | 0402 | Inductor 82nH |
| C1 | 0402 | Capacitor 56pF |
| C2 | 0402 | Capacitor 82pF |
| C3 | 0402 | Capacitor 68pF |
| C4 | 0402 | Capacitor 1000pF |
| C5 to C8 | 0402 | Capacitor 0.1μF |
| R1 | 0402 | Resistor, 1kΩ |

Fig 1. Application and Characterization circuit


Note: This block diagram is used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-754+)

Gain, Return loss, Output power at 1dB compression (P1 dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -40 dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 5 dBm/tone at output.

PRODUCT MARKING



Marking may contain other features or characters for internal lot control



LOW NOISE, HIGH GAIN & IP3

Monolithic Amplifier **PMA4-33GLN+**

Mini-Circuits

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

| | |
|--|---|
| Performance Data | Data Table |
| | Swept Graphs |
| | S-Parameter (S2P Files) Data Set (.zip file) |
| Case Style | DG1886 Plastic package, exposed paddle, lead finish: tin-silver over nickel |
| Tape & Reel Standard quantities available on reel | F68 7" reels with 20, 50, 100, 200, 500 or 1K devices |
| Suggested Layout for PCB Design | PL-407 |
| Evaluation Board | TB-754+ |
| Environmental Ratings | ENV08T1 |

ESD RATING


Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (pass 25V) in accordance with ANSI/ESD STM5.2-1999

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL TEST FLOW CHART



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 152.54mA @ Temperature = +25°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|--------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 150.0 | 25.82 | 79.98 | 1.25 | 5.04 | 44.31 | 1.20 | 32.55 | 18.80 | 3.66 |
| 200.0 | 30.26 | 99.36 | 0.62 | 4.78 | 126.67 | 1.25 | 33.49 | 19.82 | 1.61 |
| 250.0 | 34.02 | 78.20 | 1.06 | 4.37 | 11.60 | 1.13 | 34.68 | 20.48 | 1.16 |
| 300.0 | 37.22 | 83.22 | 1.21 | 3.99 | 14.93 | 1.05 | 34.67 | 21.15 | 0.91 |
| 350.0 | 39.27 | 76.82 | 1.71 | 3.70 | 7.56 | 0.95 | 36.11 | 21.38 | 0.72 |
| 400.0 | 40.86 | 78.24 | 2.52 | 3.55 | 9.56 | 0.86 | 36.18 | 21.59 | 0.55 |
| 450.0 | 41.86 | 74.55 | 3.48 | 3.54 | 7.06 | 0.79 | 35.53 | 21.90 | 0.52 |
| 500.0 | 42.44 | 71.11 | 4.47 | 3.70 | 5.39 | 0.75 | 36.48 | 22.04 | 0.64 |
| 600.0 | 42.54 | 65.82 | 6.87 | 4.61 | 4.07 | 0.75 | 38.00 | 22.66 | 0.45 |
| 700.0 | 41.87 | 62.36 | 9.35 | 6.24 | 3.76 | 0.81 | 38.94 | 22.68 | 0.55 |
| 800.0 | 40.66 | 60.28 | 11.56 | 8.41 | 3.94 | 0.89 | 40.13 | 22.76 | 0.44 |
| 900.0 | 39.30 | 58.38 | 13.01 | 11.11 | 4.04 | 0.95 | 41.80 | 22.59 | 0.53 |
| 1000.0 | 37.96 | 57.16 | 14.04 | 14.38 | 4.29 | 0.99 | 43.85 | 22.73 | 0.42 |
| 1100.0 | 36.65 | 56.03 | 14.64 | 17.62 | 4.47 | 1.01 | 43.79 | 22.81 | 0.49 |
| 1200.0 | 35.39 | 54.97 | 14.75 | 19.18 | 4.58 | 1.01 | 42.94 | 22.83 | 0.54 |
| 1300.0 | 34.25 | 54.13 | 14.81 | 17.73 | 4.72 | 1.01 | 42.18 | 22.82 | 0.63 |
| 1400.0 | 33.12 | 53.20 | 14.61 | 15.37 | 4.76 | 1.00 | 41.94 | 22.91 | 0.65 |
| 1500.0 | 32.10 | 52.30 | 14.08 | 13.54 | 4.72 | 0.99 | 42.38 | 22.94 | 0.69 |
| 1600.0 | 31.14 | 51.50 | 13.94 | 11.99 | 4.71 | 0.97 | 42.13 | 22.71 | 0.73 |
| 1700.0 | 30.18 | 50.75 | 13.59 | 10.85 | 4.71 | 0.95 | 41.22 | 23.15 | 0.81 |
| 1800.0 | 29.30 | 49.97 | 12.97 | 9.92 | 4.64 | 0.94 | 41.52 | 23.13 | 0.87 |
| 1900.0 | 28.41 | 49.07 | 12.64 | 9.15 | 4.52 | 0.92 | 41.51 | 23.04 | 0.85 |
| 2000.0 | 27.52 | 48.45 | 12.28 | 8.54 | 4.56 | 0.90 | 41.12 | 22.84 | 0.95 |
| 2200.0 | 25.70 | 47.02 | 11.73 | 7.68 | 4.59 | 0.87 | 41.01 | 22.99 | 1.04 |
| 2400.0 | 23.87 | 45.74 | 11.25 | 7.19 | 4.76 | 0.85 | 40.18 | 23.68 | 1.16 |
| 2600.0 | 22.08 | 44.60 | 10.91 | 7.03 | 5.06 | 0.85 | 39.33 | 23.37 | 1.26 |
| 2800.0 | 20.25 | 43.49 | 10.59 | 7.05 | 5.47 | 0.85 | 37.34 | 22.39 | 1.35 |
| 3000.0 | 18.57 | 42.31 | 10.27 | 7.20 | 5.80 | 0.86 | 36.05 | 21.41 | 1.55 |
| 3200.0 | 16.92 | 41.25 | 9.84 | 7.48 | 6.23 | 0.89 | 34.72 | 20.16 | 1.64 |
| 3400.0 | 15.43 | 40.15 | 9.65 | 7.63 | 6.50 | 0.90 | 32.71 | 18.96 | 1.84 |
| 3600.0 | 14.04 | 38.99 | 9.38 | 7.76 | 6.65 | 0.91 | 31.28 | 17.67 | 1.96 |
| 3800.0 | 12.69 | 37.96 | 9.08 | 7.79 | 6.81 | 0.92 | 30.67 | 16.63 | 2.23 |
| 4000.0 | 11.51 | 36.78 | 9.00 | 7.66 | 6.72 | 0.92 | 29.06 | 15.73 | 2.50 |
| 4200.0 | 10.39 | 35.58 | 8.73 | 7.65 | 6.56 | 0.93 | 27.21 | 14.70 | 2.75 |
| 4400.0 | 9.21 | 34.48 | 8.61 | 7.43 | 6.48 | 0.93 | 25.28 | 13.55 | 3.14 |
| 4600.0 | 8.50 | 32.89 | 8.57 | 7.30 | 5.76 | 0.93 | 24.06 | 12.71 | 3.30 |
| 4800.0 | 8.04 | 31.06 | 8.08 | 7.05 | 4.72 | 0.94 | 22.46 | 11.63 | 3.62 |
| 5000.0 | 7.55 | 29.30 | 7.88 | 6.75 | 3.93 | 0.93 | 20.70 | 9.76 | 3.87 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 145.71mA @ Temperature = +25°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|--------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 150.0 | 25.48 | 80.37 | 1.12 | 5.06 | 43.72 | 1.22 | 32.06 | 18.35 | 3.78 |
| 200.0 | 29.95 | 88.55 | 0.59 | 4.79 | 36.07 | 1.25 | 33.08 | 19.42 | 1.67 |
| 250.0 | 33.73 | 77.83 | 1.11 | 4.38 | 11.97 | 1.12 | 34.18 | 20.14 | 1.15 |
| 300.0 | 36.96 | 87.73 | 1.23 | 3.98 | 25.40 | 1.05 | 34.38 | 20.87 | 0.94 |
| 350.0 | 39.05 | 83.33 | 1.68 | 3.69 | 15.44 | 0.96 | 35.83 | 21.13 | 0.76 |
| 400.0 | 40.67 | 78.64 | 2.41 | 3.52 | 9.85 | 0.86 | 35.46 | 21.36 | 0.53 |
| 450.0 | 41.69 | 71.68 | 3.37 | 3.51 | 5.14 | 0.78 | 36.56 | 21.66 | 0.55 |
| 500.0 | 42.31 | 70.84 | 4.40 | 3.64 | 5.23 | 0.74 | 36.54 | 21.79 | 0.60 |
| 600.0 | 42.43 | 65.33 | 6.85 | 4.56 | 3.88 | 0.74 | 37.54 | 22.39 | 0.43 |
| 700.0 | 41.76 | 61.96 | 9.35 | 6.18 | 3.62 | 0.81 | 39.19 | 22.35 | 0.57 |
| 800.0 | 40.55 | 60.03 | 11.40 | 8.34 | 3.86 | 0.89 | 40.18 | 22.44 | 0.49 |
| 900.0 | 39.19 | 58.45 | 12.94 | 11.03 | 4.11 | 0.95 | 42.11 | 22.29 | 0.54 |
| 1000.0 | 37.82 | 56.84 | 13.85 | 14.35 | 4.20 | 0.99 | 43.58 | 22.45 | 0.44 |
| 1100.0 | 36.51 | 55.81 | 14.32 | 17.65 | 4.41 | 1.01 | 42.82 | 22.52 | 0.52 |
| 1200.0 | 35.24 | 54.77 | 14.45 | 19.34 | 4.55 | 1.02 | 42.63 | 22.49 | 0.55 |
| 1300.0 | 34.09 | 53.76 | 14.54 | 17.93 | 4.60 | 1.01 | 41.58 | 22.50 | 0.63 |
| 1400.0 | 32.96 | 53.01 | 14.39 | 15.51 | 4.73 | 1.00 | 42.52 | 22.60 | 0.66 |
| 1500.0 | 31.94 | 52.12 | 13.90 | 13.67 | 4.70 | 0.99 | 41.85 | 22.63 | 0.69 |
| 1600.0 | 30.97 | 51.33 | 13.69 | 12.07 | 4.70 | 0.97 | 41.26 | 22.41 | 0.77 |
| 1700.0 | 30.02 | 50.50 | 13.28 | 10.89 | 4.65 | 0.96 | 41.01 | 22.90 | 0.83 |
| 1800.0 | 29.14 | 49.80 | 12.79 | 9.97 | 4.63 | 0.94 | 41.07 | 22.84 | 0.85 |
| 1900.0 | 28.26 | 48.95 | 12.55 | 9.19 | 4.54 | 0.92 | 40.81 | 22.72 | 0.88 |
| 2000.0 | 27.36 | 48.22 | 12.21 | 8.55 | 4.52 | 0.90 | 40.76 | 22.52 | 0.95 |
| 2200.0 | 25.55 | 46.92 | 11.61 | 7.70 | 4.62 | 0.87 | 40.65 | 22.69 | 1.06 |
| 2400.0 | 23.71 | 45.69 | 11.21 | 7.19 | 4.81 | 0.85 | 40.12 | 23.40 | 1.18 |
| 2600.0 | 21.91 | 44.52 | 10.78 | 7.01 | 5.10 | 0.85 | 39.35 | 23.01 | 1.27 |
| 2800.0 | 20.08 | 43.49 | 10.53 | 7.05 | 5.57 | 0.85 | 37.70 | 21.99 | 1.39 |
| 3000.0 | 18.38 | 42.41 | 10.18 | 7.19 | 5.98 | 0.87 | 36.30 | 21.01 | 1.62 |
| 3200.0 | 16.74 | 41.36 | 9.79 | 7.46 | 6.41 | 0.89 | 34.69 | 19.74 | 1.65 |
| 3400.0 | 15.25 | 40.14 | 9.53 | 7.61 | 6.60 | 0.90 | 32.39 | 18.55 | 1.82 |
| 3600.0 | 13.85 | 39.09 | 9.30 | 7.73 | 6.84 | 0.91 | 30.85 | 17.25 | 1.99 |
| 3800.0 | 12.50 | 37.97 | 9.06 | 7.75 | 6.94 | 0.92 | 30.09 | 16.17 | 2.20 |
| 4000.0 | 11.33 | 36.82 | 8.90 | 7.65 | 6.86 | 0.93 | 28.40 | 15.24 | 2.45 |
| 4200.0 | 10.20 | 35.60 | 8.67 | 7.62 | 6.70 | 0.93 | 26.48 | 14.23 | 2.72 |
| 4400.0 | 9.03 | 34.52 | 8.51 | 7.42 | 6.61 | 0.93 | 24.55 | 13.07 | 3.17 |
| 4600.0 | 8.33 | 32.93 | 8.45 | 7.30 | 5.88 | 0.94 | 23.38 | 12.23 | 3.36 |
| 4800.0 | 7.86 | 31.07 | 7.96 | 7.05 | 4.80 | 0.94 | 21.92 | 11.20 | 3.50 |
| 5000.0 | 7.38 | 29.38 | 7.76 | 6.77 | 4.03 | 0.94 | 20.34 | 9.40 | 3.63 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 160.98mA @ Temperature = +25°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|--------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 150.0 | 26.08 | 76.07 | 1.23 | 5.03 | 26.70 | 1.20 | 32.88 | 19.20 | 3.66 |
| 200.0 | 30.50 | 90.28 | 0.61 | 4.76 | 42.76 | 1.24 | 34.02 | 20.23 | 1.53 |
| 250.0 | 34.24 | 76.16 | 1.16 | 4.36 | 9.79 | 1.11 | 34.81 | 20.89 | 1.15 |
| 300.0 | 37.41 | 91.13 | 1.25 | 3.98 | 36.10 | 1.05 | 35.17 | 21.47 | 0.83 |
| 350.0 | 39.43 | 87.18 | 1.72 | 3.70 | 23.30 | 0.96 | 35.91 | 21.70 | 0.71 |
| 400.0 | 40.99 | 75.02 | 2.56 | 3.55 | 6.76 | 0.85 | 36.41 | 21.90 | 0.54 |
| 450.0 | 41.96 | 73.77 | 3.51 | 3.56 | 6.50 | 0.78 | 36.92 | 22.19 | 0.53 |
| 500.0 | 42.54 | 71.23 | 4.54 | 3.69 | 5.45 | 0.74 | 36.64 | 22.34 | 0.61 |
| 600.0 | 42.61 | 66.46 | 6.94 | 4.61 | 4.35 | 0.75 | 37.49 | 22.98 | 0.47 |
| 700.0 | 41.94 | 63.07 | 9.52 | 6.21 | 4.04 | 0.81 | 39.68 | 23.04 | 0.55 |
| 800.0 | 40.74 | 60.46 | 11.60 | 8.34 | 3.98 | 0.88 | 41.83 | 23.12 | 0.49 |
| 900.0 | 39.40 | 59.02 | 13.12 | 10.96 | 4.28 | 0.94 | 41.25 | 22.92 | 0.50 |
| 1000.0 | 38.06 | 57.55 | 14.13 | 14.24 | 4.43 | 0.98 | 43.34 | 23.05 | 0.45 |
| 1100.0 | 36.76 | 56.43 | 14.84 | 17.43 | 4.62 | 1.00 | 43.18 | 23.15 | 0.52 |
| 1200.0 | 35.51 | 55.34 | 14.98 | 18.98 | 4.73 | 1.01 | 44.95 | 23.17 | 0.52 |
| 1300.0 | 34.36 | 54.40 | 15.15 | 17.63 | 4.81 | 1.01 | 43.78 | 23.15 | 0.60 |
| 1400.0 | 33.24 | 53.55 | 14.80 | 15.30 | 4.88 | 1.00 | 42.52 | 23.22 | 0.64 |
| 1500.0 | 32.23 | 52.62 | 14.33 | 13.51 | 4.83 | 0.99 | 43.88 | 23.27 | 0.67 |
| 1600.0 | 31.26 | 51.88 | 14.16 | 11.97 | 4.86 | 0.97 | 42.65 | 23.04 | 0.69 |
| 1700.0 | 30.31 | 50.99 | 13.72 | 10.81 | 4.77 | 0.95 | 42.73 | 23.44 | 0.82 |
| 1800.0 | 29.44 | 50.13 | 13.22 | 9.90 | 4.66 | 0.93 | 42.38 | 23.44 | 0.83 |
| 1900.0 | 28.56 | 49.37 | 12.84 | 9.14 | 4.60 | 0.92 | 41.16 | 23.36 | 0.87 |
| 2000.0 | 27.66 | 48.70 | 12.56 | 8.53 | 4.63 | 0.90 | 41.44 | 23.16 | 0.93 |
| 2200.0 | 25.87 | 47.12 | 11.93 | 7.68 | 4.56 | 0.87 | 40.80 | 23.31 | 1.04 |
| 2400.0 | 24.04 | 45.86 | 11.45 | 7.19 | 4.74 | 0.85 | 40.56 | 24.00 | 1.15 |
| 2600.0 | 22.27 | 44.58 | 11.02 | 7.02 | 4.96 | 0.84 | 38.96 | 23.76 | 1.25 |
| 2800.0 | 20.45 | 43.53 | 10.78 | 7.08 | 5.41 | 0.85 | 37.35 | 22.83 | 1.33 |
| 3000.0 | 18.77 | 42.36 | 10.39 | 7.23 | 5.73 | 0.86 | 36.40 | 21.86 | 1.58 |
| 3200.0 | 17.13 | 41.23 | 9.93 | 7.51 | 6.09 | 0.89 | 34.99 | 20.63 | 1.64 |
| 3400.0 | 15.64 | 40.10 | 9.72 | 7.69 | 6.35 | 0.90 | 33.19 | 19.48 | 1.86 |
| 3600.0 | 14.25 | 39.06 | 9.53 | 7.82 | 6.59 | 0.91 | 31.84 | 18.21 | 2.09 |
| 3800.0 | 12.91 | 37.95 | 9.29 | 7.84 | 6.70 | 0.92 | 31.26 | 17.17 | 2.20 |
| 4000.0 | 11.73 | 36.78 | 9.13 | 7.74 | 6.60 | 0.92 | 29.78 | 16.24 | 2.55 |
| 4200.0 | 10.59 | 35.59 | 8.93 | 7.70 | 6.48 | 0.93 | 27.94 | 15.29 | 2.89 |
| 4400.0 | 9.44 | 34.54 | 8.75 | 7.50 | 6.41 | 0.93 | 26.03 | 14.17 | 3.16 |
| 4600.0 | 8.73 | 32.92 | 8.74 | 7.36 | 5.69 | 0.93 | 24.70 | 13.36 | 3.42 |
| 4800.0 | 8.28 | 31.13 | 8.23 | 7.10 | 4.68 | 0.94 | 22.98 | 12.28 | 3.56 |
| 5000.0 | 7.79 | 29.41 | 8.09 | 6.80 | 3.92 | 0.93 | 21.02 | 10.46 | 3.82 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 163.26mA @ Temperature = -45°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|--------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 150.0 | 26.80 | 83.34 | 1.08 | 5.07 | 51.53 | 1.22 | 33.69 | 19.15 | 3.03 |
| 200.0 | 31.02 | 102.13 | 0.58 | 4.87 | 151.83 | 1.26 | 34.86 | 20.44 | 1.24 |
| 250.0 | 34.71 | 80.84 | 1.13 | 4.53 | 15.51 | 1.14 | 37.36 | 21.31 | 0.85 |
| 300.0 | 37.81 | 77.91 | 1.24 | 4.24 | 8.28 | 1.08 | 36.30 | 22.21 | 0.69 |
| 350.0 | 39.76 | 76.94 | 1.66 | 4.04 | 7.48 | 1.00 | 37.25 | 22.48 | 0.54 |
| 400.0 | 41.23 | 77.12 | 2.37 | 3.96 | 8.32 | 0.93 | 37.52 | 22.73 | 0.39 |
| 450.0 | 42.13 | 74.90 | 3.27 | 4.00 | 7.37 | 0.87 | 39.32 | 22.97 | 0.41 |
| 500.0 | 42.63 | 71.41 | 4.28 | 4.21 | 5.73 | 0.82 | 38.86 | 23.01 | 0.45 |
| 600.0 | 42.72 | 66.66 | 6.52 | 5.15 | 4.53 | 0.81 | 38.80 | 23.48 | 0.36 |
| 700.0 | 42.11 | 63.19 | 8.88 | 6.63 | 4.06 | 0.85 | 40.13 | 23.27 | 0.40 |
| 800.0 | 41.02 | 60.71 | 10.86 | 8.56 | 3.95 | 0.90 | 40.86 | 23.34 | 0.32 |
| 900.0 | 39.79 | 59.08 | 12.38 | 10.99 | 4.10 | 0.95 | 40.72 | 23.18 | 0.37 |
| 1000.0 | 38.54 | 57.79 | 13.72 | 13.48 | 4.27 | 0.98 | 42.32 | 23.45 | 0.30 |
| 1100.0 | 37.30 | 56.42 | 14.48 | 15.69 | 4.29 | 1.00 | 43.58 | 23.55 | 0.34 |
| 1200.0 | 36.10 | 55.34 | 14.94 | 16.58 | 4.38 | 1.00 | 45.27 | 23.49 | 0.39 |
| 1300.0 | 34.98 | 54.39 | 15.28 | 15.80 | 4.44 | 1.00 | 45.60 | 23.54 | 0.46 |
| 1400.0 | 33.88 | 53.53 | 15.08 | 14.45 | 4.51 | 0.99 | 48.65 | 23.67 | 0.46 |
| 1500.0 | 32.88 | 52.73 | 14.64 | 13.13 | 4.53 | 0.98 | 47.02 | 23.67 | 0.49 |
| 1600.0 | 31.93 | 51.85 | 14.49 | 11.92 | 4.48 | 0.97 | 46.76 | 23.46 | 0.55 |
| 1700.0 | 30.97 | 51.11 | 14.09 | 11.02 | 4.51 | 0.95 | 44.18 | 24.09 | 0.62 |
| 1800.0 | 30.10 | 50.32 | 13.49 | 10.19 | 4.45 | 0.94 | 43.88 | 23.90 | 0.59 |
| 1900.0 | 29.23 | 49.61 | 13.22 | 9.52 | 4.44 | 0.93 | 43.28 | 23.66 | 0.60 |
| 2000.0 | 28.34 | 48.94 | 12.81 | 8.94 | 4.47 | 0.91 | 43.34 | 23.45 | 0.66 |
| 2200.0 | 26.56 | 47.56 | 12.04 | 8.07 | 4.51 | 0.89 | 40.61 | 23.74 | 0.74 |
| 2400.0 | 24.74 | 46.35 | 11.49 | 7.42 | 4.67 | 0.86 | 39.81 | 24.50 | 0.82 |
| 2600.0 | 23.00 | 45.13 | 11.02 | 7.13 | 4.88 | 0.85 | 38.34 | 23.97 | 0.87 |
| 2800.0 | 21.24 | 44.08 | 10.63 | 7.06 | 5.24 | 0.85 | 36.68 | 23.21 | 0.93 |
| 3000.0 | 19.58 | 42.89 | 10.15 | 7.01 | 5.46 | 0.86 | 35.46 | 22.53 | 1.14 |
| 3200.0 | 17.99 | 41.86 | 9.76 | 7.21 | 5.83 | 0.87 | 33.89 | 21.47 | 1.14 |
| 3400.0 | 16.57 | 40.58 | 9.37 | 7.34 | 5.89 | 0.89 | 31.89 | 20.47 | 1.35 |
| 3600.0 | 15.19 | 39.52 | 9.03 | 7.34 | 6.03 | 0.90 | 30.38 | 19.05 | 1.50 |
| 3800.0 | 13.87 | 38.38 | 8.86 | 7.30 | 6.08 | 0.90 | 29.89 | 17.94 | 1.64 |
| 4000.0 | 12.70 | 37.17 | 8.57 | 7.22 | 5.93 | 0.91 | 28.39 | 16.96 | 1.89 |
| 4200.0 | 11.58 | 36.06 | 8.44 | 7.09 | 5.84 | 0.91 | 26.74 | 15.93 | 2.02 |
| 4400.0 | 10.43 | 34.95 | 8.35 | 6.89 | 5.73 | 0.91 | 25.09 | 14.77 | 2.36 |
| 4600.0 | 9.69 | 33.43 | 8.27 | 6.83 | 5.15 | 0.92 | 24.22 | 14.02 | 2.48 |
| 4800.0 | 9.25 | 31.63 | 7.83 | 6.48 | 4.18 | 0.92 | 23.18 | 13.38 | 2.70 |
| 5000.0 | 8.84 | 29.76 | 7.60 | 6.21 | 3.38 | 0.91 | 21.22 | 11.88 | 2.96 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 150.87mA @ Temperature = -45°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|--------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | | | (dBm) | (dBm) | (dB) |
| 150.0 | 26.23 | 78.30 | 1.04 | 5.09 | 29.66 | 1.23 | 33.26 | 18.89 | 2.86 |
| 200.0 | 30.50 | 83.70 | 0.58 | 4.88 | 19.65 | 1.26 | 34.07 | 20.15 | 1.22 |
| 250.0 | 34.22 | 80.87 | 1.06 | 4.54 | 14.66 | 1.16 | 35.82 | 20.97 | 0.79 |
| 300.0 | 37.37 | 91.04 | 1.19 | 4.24 | 36.27 | 1.10 | 36.36 | 21.90 | 0.66 |
| 350.0 | 39.36 | 76.34 | 1.66 | 4.04 | 7.32 | 1.00 | 36.64 | 22.14 | 0.55 |
| 400.0 | 40.88 | 76.39 | 2.35 | 3.95 | 7.92 | 0.93 | 37.25 | 22.36 | 0.37 |
| 450.0 | 41.82 | 75.31 | 3.20 | 3.99 | 7.85 | 0.87 | 36.94 | 22.60 | 0.41 |
| 500.0 | 42.36 | 69.76 | 4.20 | 4.20 | 4.89 | 0.82 | 37.54 | 22.63 | 0.46 |
| 600.0 | 42.47 | 66.02 | 6.50 | 5.13 | 4.33 | 0.81 | 37.24 | 23.10 | 0.33 |
| 700.0 | 41.88 | 62.88 | 8.86 | 6.62 | 4.02 | 0.85 | 38.58 | 22.88 | 0.41 |
| 800.0 | 40.78 | 60.60 | 10.88 | 8.57 | 4.01 | 0.90 | 39.76 | 22.96 | 0.33 |
| 900.0 | 39.54 | 58.63 | 12.46 | 11.01 | 4.01 | 0.95 | 40.41 | 22.81 | 0.35 |
| 1000.0 | 38.28 | 57.36 | 13.67 | 13.51 | 4.18 | 0.98 | 41.58 | 23.09 | 0.28 |
| 1100.0 | 37.04 | 56.20 | 14.49 | 15.76 | 4.31 | 1.00 | 41.68 | 23.18 | 0.32 |
| 1200.0 | 35.83 | 55.04 | 14.69 | 16.68 | 4.35 | 1.00 | 44.11 | 23.11 | 0.37 |
| 1300.0 | 34.71 | 54.04 | 15.03 | 15.91 | 4.40 | 1.00 | 45.51 | 23.17 | 0.43 |
| 1400.0 | 33.60 | 53.25 | 14.87 | 14.55 | 4.50 | 0.99 | 46.00 | 23.30 | 0.45 |
| 1500.0 | 32.60 | 52.53 | 14.45 | 13.21 | 4.57 | 0.98 | 46.85 | 23.31 | 0.46 |
| 1600.0 | 31.65 | 51.63 | 14.32 | 12.00 | 4.51 | 0.97 | 46.89 | 23.11 | 0.48 |
| 1700.0 | 30.69 | 50.98 | 13.79 | 11.08 | 4.58 | 0.96 | 44.28 | 23.74 | 0.58 |
| 1800.0 | 29.82 | 50.18 | 13.40 | 10.25 | 4.52 | 0.94 | 43.33 | 23.55 | 0.56 |
| 1900.0 | 28.95 | 49.48 | 13.09 | 9.57 | 4.52 | 0.93 | 44.07 | 23.30 | 0.59 |
| 2000.0 | 28.05 | 48.74 | 12.77 | 8.98 | 4.52 | 0.91 | 43.24 | 23.09 | 0.65 |
| 2200.0 | 26.28 | 47.44 | 11.94 | 8.10 | 4.59 | 0.89 | 40.66 | 23.38 | 0.70 |
| 2400.0 | 24.46 | 46.20 | 11.41 | 7.44 | 4.75 | 0.86 | 39.61 | 24.14 | 0.84 |
| 2600.0 | 22.71 | 45.05 | 11.10 | 7.15 | 5.01 | 0.85 | 38.05 | 23.54 | 0.86 |
| 2800.0 | 20.96 | 44.02 | 10.65 | 7.08 | 5.38 | 0.85 | 36.34 | 22.77 | 0.93 |
| 3000.0 | 19.30 | 42.85 | 10.17 | 7.02 | 5.62 | 0.86 | 35.06 | 22.10 | 1.15 |
| 3200.0 | 17.71 | 41.85 | 9.86 | 7.22 | 6.02 | 0.87 | 33.31 | 21.02 | 1.15 |
| 3400.0 | 16.29 | 40.61 | 9.44 | 7.35 | 6.12 | 0.89 | 31.31 | 19.97 | 1.28 |
| 3600.0 | 14.91 | 39.57 | 9.14 | 7.36 | 6.28 | 0.90 | 29.57 | 18.48 | 1.47 |
| 3800.0 | 13.59 | 38.47 | 9.02 | 7.31 | 6.37 | 0.90 | 28.90 | 17.35 | 1.62 |
| 4000.0 | 12.43 | 37.28 | 8.68 | 7.23 | 6.21 | 0.91 | 27.35 | 16.38 | 1.82 |
| 4200.0 | 11.30 | 36.15 | 8.50 | 7.10 | 6.09 | 0.91 | 25.68 | 15.33 | 2.09 |
| 4400.0 | 10.15 | 35.07 | 8.49 | 6.91 | 6.03 | 0.91 | 23.97 | 14.19 | 2.35 |
| 4600.0 | 9.42 | 33.56 | 8.33 | 6.85 | 5.41 | 0.92 | 23.25 | 13.46 | 2.33 |
| 4800.0 | 8.99 | 31.78 | 7.91 | 6.50 | 4.40 | 0.91 | 22.39 | 12.89 | 2.61 |
| 5000.0 | 8.58 | 29.93 | 7.53 | 6.24 | 3.54 | 0.92 | 20.64 | 11.61 | 2.87 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 169.63mA @ Temperature = -45°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|--------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 150.0 | 26.92 | 77.24 | 1.13 | 5.06 | 26.26 | 1.22 | 34.20 | 19.57 | 3.02 |
| 200.0 | 31.15 | 81.50 | 0.58 | 4.86 | 14.02 | 1.26 | 35.19 | 20.88 | 1.28 |
| 250.0 | 34.82 | 83.53 | 1.02 | 4.53 | 18.82 | 1.16 | 37.23 | 21.74 | 0.83 |
| 300.0 | 37.91 | 81.12 | 1.18 | 4.24 | 11.26 | 1.09 | 37.33 | 22.59 | 0.71 |
| 350.0 | 39.83 | 80.05 | 1.66 | 4.04 | 10.31 | 1.01 | 37.84 | 22.86 | 0.58 |
| 400.0 | 41.28 | 77.23 | 2.47 | 3.97 | 8.63 | 0.92 | 38.19 | 23.08 | 0.40 |
| 450.0 | 42.16 | 74.78 | 3.39 | 4.01 | 7.40 | 0.86 | 37.75 | 23.34 | 0.40 |
| 500.0 | 42.65 | 71.93 | 4.30 | 4.23 | 6.07 | 0.83 | 39.16 | 23.38 | 0.49 |
| 600.0 | 42.70 | 66.88 | 6.59 | 5.15 | 4.67 | 0.81 | 39.08 | 23.85 | 0.36 |
| 700.0 | 42.10 | 63.74 | 8.97 | 6.62 | 4.32 | 0.85 | 40.58 | 23.64 | 0.43 |
| 800.0 | 41.00 | 61.28 | 10.97 | 8.53 | 4.22 | 0.90 | 40.45 | 23.70 | 0.32 |
| 900.0 | 39.78 | 59.30 | 12.50 | 10.92 | 4.21 | 0.95 | 41.76 | 23.50 | 0.38 |
| 1000.0 | 38.53 | 58.01 | 13.79 | 13.36 | 4.38 | 0.98 | 42.46 | 23.78 | 0.29 |
| 1100.0 | 37.31 | 56.71 | 14.58 | 15.52 | 4.43 | 0.99 | 46.72 | 23.91 | 0.38 |
| 1200.0 | 36.10 | 55.66 | 15.07 | 16.40 | 4.54 | 1.00 | 45.02 | 23.88 | 0.40 |
| 1300.0 | 34.99 | 54.68 | 15.40 | 15.66 | 4.58 | 1.00 | 47.10 | 23.92 | 0.46 |
| 1400.0 | 33.89 | 53.92 | 15.25 | 14.36 | 4.70 | 0.99 | 52.21 | 24.05 | 0.47 |
| 1500.0 | 32.90 | 53.03 | 14.87 | 13.05 | 4.68 | 0.98 | 48.50 | 24.05 | 0.50 |
| 1600.0 | 31.94 | 52.15 | 14.70 | 11.87 | 4.64 | 0.96 | 46.39 | 23.84 | 0.54 |
| 1700.0 | 30.99 | 51.42 | 14.28 | 10.98 | 4.66 | 0.95 | 45.28 | 24.44 | 0.58 |
| 1800.0 | 30.12 | 50.61 | 13.71 | 10.16 | 4.59 | 0.94 | 45.64 | 24.26 | 0.59 |
| 1900.0 | 29.26 | 49.80 | 13.40 | 9.50 | 4.53 | 0.92 | 45.31 | 24.02 | 0.62 |
| 2000.0 | 28.37 | 49.09 | 13.04 | 8.92 | 4.54 | 0.91 | 43.69 | 23.80 | 0.67 |
| 2200.0 | 26.60 | 47.67 | 12.27 | 8.07 | 4.56 | 0.88 | 42.00 | 24.06 | 0.75 |
| 2400.0 | 24.79 | 46.36 | 11.70 | 7.43 | 4.67 | 0.86 | 40.92 | 24.80 | 0.82 |
| 2600.0 | 23.06 | 45.12 | 11.23 | 7.15 | 4.86 | 0.85 | 39.27 | 24.24 | 0.84 |
| 2800.0 | 21.31 | 44.04 | 10.83 | 7.08 | 5.20 | 0.85 | 37.48 | 23.45 | 0.94 |
| 3000.0 | 19.66 | 42.79 | 10.35 | 7.03 | 5.39 | 0.85 | 36.37 | 22.67 | 1.12 |
| 3200.0 | 18.07 | 41.73 | 9.95 | 7.23 | 5.73 | 0.87 | 34.83 | 21.48 | 1.14 |
| 3400.0 | 16.65 | 40.51 | 9.59 | 7.39 | 5.84 | 0.89 | 33.01 | 20.35 | 1.31 |
| 3600.0 | 15.28 | 39.45 | 9.29 | 7.40 | 5.99 | 0.90 | 31.53 | 18.97 | 1.48 |
| 3800.0 | 13.96 | 38.34 | 9.18 | 7.35 | 6.06 | 0.90 | 31.00 | 17.90 | 1.65 |
| 4000.0 | 12.80 | 37.13 | 8.85 | 7.26 | 5.91 | 0.91 | 29.64 | 16.94 | 1.80 |
| 4200.0 | 11.67 | 36.03 | 8.69 | 7.13 | 5.82 | 0.91 | 27.99 | 15.94 | 2.03 |
| 4400.0 | 10.53 | 34.95 | 8.66 | 6.93 | 5.75 | 0.90 | 26.30 | 14.87 | 2.37 |
| 4600.0 | 9.79 | 33.46 | 8.53 | 6.87 | 5.17 | 0.91 | 25.35 | 14.16 | 2.36 |
| 4800.0 | 9.36 | 31.69 | 8.11 | 6.52 | 4.22 | 0.91 | 24.08 | 13.58 | 2.59 |
| 5000.0 | 8.95 | 29.84 | 7.80 | 6.25 | 3.41 | 0.91 | 21.80 | 12.12 | 2.83 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 145.08mA @ Temperature = +85°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|--------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 150.0 | 24.58 | 78.82 | 1.29 | 4.93 | 45.13 | 1.18 | 30.78 | 18.11 | 4.41 |
| 200.0 | 29.28 | 89.92 | 0.67 | 4.63 | 50.64 | 1.22 | 31.81 | 18.87 | 1.98 |
| 250.0 | 33.13 | 78.86 | 1.25 | 4.17 | 15.00 | 1.08 | 32.67 | 19.31 | 1.33 |
| 300.0 | 36.43 | 88.23 | 1.37 | 3.72 | 30.44 | 0.99 | 33.11 | 19.74 | 1.11 |
| 350.0 | 38.59 | 84.37 | 1.82 | 3.35 | 18.17 | 0.89 | 33.79 | 19.96 | 0.89 |
| 400.0 | 40.29 | 75.81 | 2.56 | 3.11 | 7.31 | 0.78 | 33.96 | 20.15 | 0.69 |
| 450.0 | 41.40 | 72.46 | 3.50 | 3.03 | 5.38 | 0.70 | 34.39 | 20.44 | 0.70 |
| 500.0 | 42.10 | 70.45 | 4.65 | 3.11 | 4.81 | 0.65 | 35.27 | 20.61 | 0.72 |
| 600.0 | 42.29 | 65.45 | 7.13 | 3.92 | 3.73 | 0.67 | 36.14 | 21.35 | 0.59 |
| 700.0 | 41.60 | 62.19 | 9.59 | 5.53 | 3.63 | 0.76 | 37.57 | 21.81 | 0.66 |
| 800.0 | 40.34 | 60.35 | 11.81 | 7.80 | 4.03 | 0.86 | 39.32 | 22.03 | 0.60 |
| 900.0 | 38.90 | 58.47 | 13.10 | 10.52 | 4.22 | 0.94 | 40.25 | 21.80 | 0.65 |
| 1000.0 | 37.47 | 57.13 | 14.00 | 14.22 | 4.51 | 0.99 | 39.99 | 21.78 | 0.58 |
| 1100.0 | 36.12 | 56.19 | 14.43 | 18.35 | 4.83 | 1.01 | 39.65 | 21.75 | 0.64 |
| 1200.0 | 34.83 | 55.20 | 14.41 | 21.25 | 5.02 | 1.02 | 39.34 | 21.75 | 0.69 |
| 1300.0 | 33.65 | 54.45 | 14.39 | 19.46 | 5.25 | 1.02 | 38.63 | 21.58 | 0.77 |
| 1400.0 | 32.52 | 53.51 | 14.22 | 16.02 | 5.28 | 1.01 | 38.70 | 21.60 | 0.81 |
| 1500.0 | 31.51 | 52.58 | 13.72 | 13.99 | 5.22 | 1.00 | 38.73 | 21.70 | 0.88 |
| 1600.0 | 30.55 | 51.79 | 13.30 | 12.11 | 5.18 | 0.98 | 38.70 | 21.51 | 0.92 |
| 1700.0 | 29.61 | 50.94 | 13.06 | 10.74 | 5.10 | 0.96 | 38.59 | 21.76 | 1.05 |
| 1800.0 | 28.75 | 50.11 | 12.64 | 9.84 | 5.00 | 0.94 | 38.77 | 21.96 | 1.09 |
| 1900.0 | 27.87 | 49.22 | 12.39 | 8.96 | 4.86 | 0.91 | 38.85 | 22.06 | 1.12 |
| 2000.0 | 27.00 | 48.40 | 12.16 | 8.28 | 4.77 | 0.89 | 38.97 | 21.99 | 1.19 |
| 2200.0 | 25.20 | 46.93 | 11.49 | 7.50 | 4.76 | 0.86 | 38.71 | 22.13 | 1.33 |
| 2400.0 | 23.39 | 45.51 | 11.26 | 7.08 | 4.88 | 0.84 | 38.58 | 22.75 | 1.49 |
| 2600.0 | 21.57 | 44.28 | 10.90 | 7.01 | 5.17 | 0.84 | 38.01 | 22.65 | 1.61 |
| 2800.0 | 19.72 | 43.08 | 10.70 | 7.15 | 5.59 | 0.85 | 36.60 | 21.67 | 1.72 |
| 3000.0 | 17.99 | 42.00 | 10.60 | 7.39 | 6.08 | 0.87 | 35.69 | 20.69 | 2.02 |
| 3200.0 | 16.30 | 41.05 | 10.06 | 7.69 | 6.62 | 0.89 | 34.46 | 19.62 | 2.15 |
| 3400.0 | 14.76 | 39.88 | 10.09 | 7.87 | 6.94 | 0.90 | 32.33 | 18.48 | 2.44 |
| 3600.0 | 13.36 | 38.92 | 9.86 | 8.16 | 7.33 | 0.92 | 31.09 | 17.35 | 2.65 |
| 3800.0 | 11.99 | 37.79 | 9.58 | 8.18 | 7.45 | 0.93 | 30.31 | 16.29 | 2.91 |
| 4000.0 | 10.82 | 36.59 | 9.76 | 8.11 | 7.41 | 0.93 | 28.64 | 15.45 | 3.18 |
| 4200.0 | 9.67 | 35.36 | 9.24 | 8.23 | 7.24 | 0.95 | 26.72 | 14.46 | 3.56 |
| 4400.0 | 8.47 | 34.29 | 9.03 | 7.94 | 7.17 | 0.94 | 24.77 | 13.34 | 3.92 |
| 4600.0 | 7.79 | 32.62 | 9.28 | 7.86 | 6.39 | 0.94 | 23.47 | 12.38 | 4.10 |
| 4800.0 | 7.29 | 30.81 | 8.61 | 7.77 | 5.32 | 0.96 | 21.95 | 11.04 | 4.46 |
| 5000.0 | 6.76 | 29.13 | 8.74 | 7.44 | 4.58 | 0.94 | 20.81 | 9.91 | 4.91 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 137.78mA @ Temperature = +85°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|--------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 150.0 | 24.24 | 81.22 | 1.24 | 4.95 | 59.58 | 1.19 | 30.52 | 17.71 | 4.50 |
| 200.0 | 28.98 | 89.70 | 0.67 | 4.65 | 50.84 | 1.22 | 31.56 | 18.46 | 2.05 |
| 250.0 | 32.84 | 77.50 | 1.05 | 4.18 | 11.89 | 1.10 | 32.59 | 18.94 | 1.37 |
| 300.0 | 36.17 | 79.00 | 1.26 | 3.73 | 10.59 | 1.00 | 32.59 | 19.44 | 1.13 |
| 350.0 | 38.36 | 76.39 | 1.76 | 3.35 | 7.70 | 0.88 | 33.34 | 19.63 | 0.89 |
| 400.0 | 40.09 | 77.32 | 2.50 | 3.10 | 8.60 | 0.78 | 33.74 | 19.84 | 0.70 |
| 450.0 | 41.23 | 71.91 | 3.53 | 3.00 | 5.20 | 0.69 | 34.53 | 20.14 | 0.63 |
| 500.0 | 41.96 | 70.96 | 4.51 | 3.07 | 5.03 | 0.66 | 34.03 | 20.32 | 0.74 |
| 600.0 | 42.17 | 65.42 | 7.06 | 3.87 | 3.73 | 0.67 | 36.06 | 21.06 | 0.56 |
| 700.0 | 41.49 | 62.11 | 9.53 | 5.48 | 3.62 | 0.76 | 38.12 | 21.48 | 0.66 |
| 800.0 | 40.23 | 59.96 | 11.68 | 7.75 | 3.89 | 0.86 | 39.12 | 21.68 | 0.59 |
| 900.0 | 38.78 | 58.16 | 12.94 | 10.45 | 4.11 | 0.94 | 39.61 | 21.46 | 0.65 |
| 1000.0 | 37.35 | 57.05 | 13.65 | 14.13 | 4.51 | 0.99 | 39.21 | 21.47 | 0.59 |
| 1100.0 | 35.99 | 56.02 | 14.21 | 18.23 | 4.80 | 1.01 | 39.19 | 21.45 | 0.63 |
| 1200.0 | 34.69 | 55.03 | 14.08 | 21.24 | 4.99 | 1.02 | 39.36 | 21.44 | 0.70 |
| 1300.0 | 33.52 | 54.12 | 14.06 | 19.62 | 5.12 | 1.02 | 38.42 | 21.30 | 0.79 |
| 1400.0 | 32.38 | 53.31 | 14.00 | 16.16 | 5.24 | 1.01 | 38.49 | 21.32 | 0.84 |
| 1500.0 | 31.37 | 52.53 | 13.34 | 14.12 | 5.26 | 1.00 | 38.42 | 21.40 | 0.89 |
| 1600.0 | 30.41 | 51.65 | 12.97 | 12.21 | 5.17 | 0.98 | 38.09 | 21.23 | 0.93 |
| 1700.0 | 29.47 | 50.88 | 12.77 | 10.83 | 5.14 | 0.96 | 38.27 | 21.49 | 1.07 |
| 1800.0 | 28.61 | 50.02 | 12.49 | 9.92 | 5.03 | 0.94 | 38.37 | 21.67 | 1.09 |
| 1900.0 | 27.74 | 49.16 | 12.15 | 9.02 | 4.89 | 0.92 | 38.33 | 21.75 | 1.12 |
| 2000.0 | 26.87 | 48.36 | 11.95 | 8.34 | 4.81 | 0.90 | 38.73 | 21.67 | 1.22 |
| 2200.0 | 25.07 | 46.88 | 11.30 | 7.53 | 4.80 | 0.87 | 38.25 | 21.81 | 1.34 |
| 2400.0 | 23.26 | 45.47 | 11.14 | 7.10 | 4.93 | 0.85 | 38.32 | 22.47 | 1.53 |
| 2600.0 | 21.44 | 44.27 | 10.73 | 7.01 | 5.23 | 0.85 | 37.83 | 22.34 | 1.62 |
| 2800.0 | 19.58 | 43.14 | 10.68 | 7.14 | 5.71 | 0.86 | 36.76 | 21.36 | 1.76 |
| 3000.0 | 17.85 | 42.03 | 10.50 | 7.37 | 6.18 | 0.87 | 35.84 | 20.34 | 2.00 |
| 3200.0 | 16.16 | 41.04 | 10.01 | 7.66 | 6.70 | 0.89 | 34.47 | 19.20 | 2.12 |
| 3400.0 | 14.62 | 39.94 | 9.94 | 7.83 | 7.06 | 0.91 | 32.20 | 18.05 | 2.31 |
| 3600.0 | 13.21 | 38.94 | 9.71 | 8.12 | 7.42 | 0.92 | 30.73 | 16.85 | 2.68 |
| 3800.0 | 11.84 | 37.81 | 9.42 | 8.14 | 7.54 | 0.93 | 29.76 | 15.80 | 2.87 |
| 4000.0 | 10.68 | 36.64 | 9.72 | 8.06 | 7.55 | 0.93 | 28.08 | 14.90 | 3.23 |
| 4200.0 | 9.53 | 35.40 | 9.16 | 8.20 | 7.36 | 0.95 | 26.07 | 13.93 | 3.51 |
| 4400.0 | 8.34 | 34.34 | 8.95 | 7.91 | 7.29 | 0.95 | 24.13 | 12.83 | 4.04 |
| 4600.0 | 7.66 | 32.67 | 9.10 | 7.84 | 6.48 | 0.94 | 22.89 | 11.88 | 4.10 |
| 4800.0 | 7.16 | 30.85 | 8.47 | 7.77 | 5.40 | 0.96 | 21.47 | 10.58 | 4.52 |
| 5000.0 | 6.62 | 29.15 | 8.55 | 7.44 | 4.63 | 0.95 | 20.47 | 9.40 | 4.73 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)








TEST CONDITIONS: Vd = 5.25V, Id = 150.50mA @ Temperature = +85°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
|--------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | | | | | K | Measure | | | |
| (MHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 150.0 | 24.76 | 77.45 | 1.32 | 4.89 | 38.54 | 1.17 | 30.88 | 18.36 | 4.46 |
| 200.0 | 29.46 | 87.88 | 0.65 | 4.59 | 38.03 | 1.21 | 32.00 | 19.02 | 1.98 |
| 250.0 | 33.28 | 82.83 | 1.09 | 4.13 | 20.85 | 1.09 | 32.96 | 19.45 | 1.30 |
| 300.0 | 36.57 | 85.92 | 1.34 | 3.69 | 22.25 | 0.99 | 32.99 | 19.83 | 1.10 |
| 350.0 | 38.71 | 84.34 | 1.92 | 3.33 | 18.73 | 0.87 | 34.09 | 20.02 | 0.92 |
| 400.0 | 40.39 | 76.62 | 2.62 | 3.09 | 7.99 | 0.77 | 34.29 | 20.21 | 0.68 |
| 450.0 | 41.48 | 73.93 | 3.61 | 3.01 | 6.34 | 0.70 | 34.83 | 20.49 | 0.68 |
| 500.0 | 42.17 | 70.34 | 4.69 | 3.10 | 4.70 | 0.65 | 35.18 | 20.67 | 0.73 |
| 600.0 | 42.34 | 66.36 | 7.25 | 3.90 | 4.11 | 0.67 | 36.10 | 21.40 | 0.56 |
| 700.0 | 41.65 | 62.68 | 9.76 | 5.51 | 3.81 | 0.76 | 38.33 | 21.95 | 0.67 |
| 800.0 | 40.40 | 60.74 | 12.01 | 7.78 | 4.19 | 0.86 | 39.04 | 22.23 | 0.59 |
| 900.0 | 38.97 | 58.83 | 13.41 | 10.50 | 4.37 | 0.93 | 39.86 | 21.99 | 0.63 |
| 1000.0 | 37.55 | 57.78 | 14.19 | 14.25 | 4.82 | 0.99 | 39.58 | 21.93 | 0.59 |
| 1100.0 | 36.19 | 56.56 | 14.70 | 18.46 | 5.02 | 1.01 | 39.18 | 21.87 | 0.64 |
| 1200.0 | 34.90 | 55.77 | 14.64 | 21.41 | 5.33 | 1.02 | 39.64 | 21.85 | 0.71 |
| 1300.0 | 33.73 | 54.74 | 14.62 | 19.46 | 5.38 | 1.02 | 38.67 | 21.66 | 0.79 |
| 1400.0 | 32.60 | 53.90 | 14.52 | 15.94 | 5.48 | 1.01 | 38.78 | 21.63 | 0.83 |
| 1500.0 | 31.60 | 52.99 | 13.95 | 13.90 | 5.42 | 0.99 | 38.82 | 21.76 | 0.88 |
| 1600.0 | 30.63 | 52.07 | 13.47 | 12.02 | 5.31 | 0.98 | 38.70 | 21.58 | 0.94 |
| 1700.0 | 29.69 | 51.27 | 13.37 | 10.65 | 5.26 | 0.95 | 38.75 | 21.77 | 1.04 |
| 1800.0 | 28.84 | 50.38 | 12.93 | 9.76 | 5.11 | 0.93 | 38.88 | 22.02 | 1.09 |
| 1900.0 | 27.96 | 49.48 | 12.57 | 8.88 | 4.95 | 0.91 | 39.36 | 22.16 | 1.13 |
| 2000.0 | 27.10 | 48.59 | 12.35 | 8.21 | 4.82 | 0.89 | 39.14 | 22.14 | 1.21 |
| 2200.0 | 25.31 | 47.04 | 11.67 | 7.45 | 4.77 | 0.86 | 38.93 | 22.25 | 1.35 |
| 2400.0 | 23.51 | 45.59 | 11.44 | 7.05 | 4.86 | 0.84 | 38.33 | 22.85 | 1.47 |
| 2600.0 | 21.70 | 44.23 | 10.97 | 7.00 | 5.07 | 0.84 | 37.76 | 22.81 | 1.59 |
| 2800.0 | 19.86 | 43.05 | 10.98 | 7.17 | 5.52 | 0.85 | 36.49 | 21.93 | 1.74 |
| 3000.0 | 18.13 | 41.95 | 10.79 | 7.45 | 5.99 | 0.87 | 35.61 | 20.96 | 2.01 |
| 3200.0 | 16.44 | 40.95 | 10.24 | 7.77 | 6.50 | 0.89 | 34.64 | 19.99 | 2.11 |
| 3400.0 | 14.91 | 39.84 | 10.37 | 7.98 | 6.87 | 0.90 | 32.67 | 18.92 | 2.35 |
| 3600.0 | 13.50 | 38.88 | 10.01 | 8.31 | 7.25 | 0.92 | 31.41 | 17.79 | 2.61 |
| 3800.0 | 12.13 | 37.72 | 9.73 | 8.33 | 7.35 | 0.93 | 30.69 | 16.81 | 2.85 |
| 4000.0 | 10.96 | 36.55 | 10.02 | 8.25 | 7.35 | 0.93 | 29.18 | 15.90 | 3.25 |
| 4200.0 | 9.80 | 35.31 | 9.49 | 8.37 | 7.18 | 0.95 | 27.31 | 14.97 | 3.46 |
| 4400.0 | 8.62 | 34.26 | 9.29 | 8.06 | 7.13 | 0.94 | 25.37 | 13.86 | 3.94 |
| 4600.0 | 7.94 | 32.62 | 9.59 | 7.97 | 6.38 | 0.94 | 24.00 | 12.87 | 4.19 |
| 4800.0 | 7.42 | 30.84 | 8.92 | 7.88 | 5.34 | 0.95 | 22.39 | 11.43 | 4.40 |
| 5000.0 | 6.89 | 29.17 | 9.10 | 7.52 | 4.61 | 0.94 | 21.16 | 10.67 | 4.73 |


Typical Performance Curves




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.002


| CASE # | A | B | C | D | E | F | G | H | J | K |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|----------------|----------------|
| DG1886 | .157 (4.00) | .157 (4.00) | .035 (0.90) | .009 (0.24) | .098 (2.50) | .098 (2.50) | .012 (0.30) | -- -- | .018 (0.45) | .026 (0.65) |

| CASE # | L | M | N | P | Q | R | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|---------------|----------|
| DG1886 | .185 (4.70) | .185 (4.70) | .085 (2.16) | .014 (0.36) | .035 (0.89) | .85 (2.16) | .04 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$


Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



| REVISIONS | | | | | |
|-----------|---------|-------------|----------|----|------|
| REV OR | ECN No. | DESCRIPTION | DATE | DR | AUTH |
| | M144560 | NEW RELEASE | 01/22/14 | AV | RS |
| | | | | | |
| | | | | | |


**SUGGESTED MOUNTING CONFIGURATION FOR
DG1886 CASE STYLE, "16AM03" PIN CODE**



| COMPONENT | SIZE |
|----------------|------|
| C1-8, L1-3, R1 | 0402 |

NOTES:

1. TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010"±.001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-754+.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|----------------------------|-------------|----------|
| DIMENSIONS ARE IN INCHES | DRAWN AV | 01/13/14 |
| TOLERANCES ON: | CHECKED IL | 01/22/14 |
| 2 PL DECIMALS ± | APPROVED RS | 01/22/14 |
| 3 PL DECIMALS ± .005 | | |
| ANGLES ± | | |
| FRACTIONS ± | | |



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235



PL, 16AM03, DG1886, TB-754+

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

| SIZE | CODE IDENT | DRAWING NO: | REV: |
|-------|------------|-------------|---------------|
| A | 15542 | 98-PL-407 | OR |
| FILE: | 98PL407 | SCALE: 8:1 | SHEET: 1 OF 1 |

Evaluation Board and Circuit




Schematic Diagram

| COMPONENT | VALUE | SIZE |
|-------------|----------|------|
| DUT | EA3 | 0402 |
| C1 | 56 pF | |
| C2 | 82 pF | |
| C3 | 68 pF | |
| C4 | 1000 pF | |
| C5,C6,C7,C8 | 1.0 uF | |
| R1 | 1.0 kOhm | |
| L1 | 15 nH | |
| L2 | 5.6 nH | |
| L3 | 82 nH | |

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|--|---|
| Operating Temperature | -40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C or -65° to 150° Ambient Environment | Individual Model Data Sheet |
| HTOL | 1000 hours at 125°C | MIL-STD-883, Method 1005, Condition B |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Mechanical Shock | 1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only | MIL-STD-883, Method 2002, Condition B, except Y1 direction only |
| Vibration (Variable Frequency) | 50g peak | MIL-STD-883, Method 2007, Condition B |
| Autoclave | 15 psig, 100% RH, 121°C, 96 hours | JESD22-A102, Condition C |
| HAST | 130°C, 85% RH, 96 hours | JESD22-A110 |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1 |
| Moisture Sensitivity: Level 1 | Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak | J-STD-020 |

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|-------------------------|
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |