

STRIPLINE SURFACE MOUNT

Power Splitter/Combiner

QCH-272+

50Ω 700 to 2700 MHz

2-Way 90°

200W

KEY FEATURES

- · High power handling, up to 200W
- Wide bandwidth
- Excellent amplitude unbalance, ±0.1 dB


The state of the s

Generic photo used for illustration purposes only

APPLICATIONS

- Balanced amplifiers
- I&O modulators
- Defense and military

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' QCH-272+ is a 2-way 90° power splitter, capable of handling up to 200W with amplitude unbalance of ± 0.1 dB typ and phase unbalance of ± 0.9 deg. typ. Operating over a frequency range of 700 to 2700 MHz, the outstanding phase and amplitude unbalance make this component a versatile building block for use in a variety of systems and sub-system designs from balanced amplifiers and antenna feeds to military applications and more. The splitter is fabricated using laminated PCB process (1.80 x 0.40 x 0.19") and includes wrap-around terminations for good solderability and easy visual inspection.

ELECTRICAL SPECIFICATIONS 1, 2 AT +25°C

Parameter	Conditions (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range	-	700	_	2700	MHz	
Insertion Loss ³	700 - 2700	-	0.3	0.5	dB	
Isolation	700 - 2700	17	22	-	dB	
Phase Unbalance	700 - 2700	-	±0.9	±5.0	deg	
Association de Libertaine	700 - 2700	00 - 2700 – ±0.1		±1.0	ı.	
Amplitude Unbalance	800 - 2700	-	±0.1	±0.6	dB	
Return Loss	700 - 2700	16.5	23	-	dB	
Thermal Resistance ⁴	700 - 2700	-	0.3	-	°C/W	

- 1. Tested in Evaluation Board TB-884+. De-embbeded to the device reference plane.
- 2. Model is symmetrical and all ports are interchangeable, see Port Function Description/Configuration table for details and S-Parameters for actual performance.
- 3. Does not include theoretical loss due to coupling. Nominal theoretical loss is 3 dB.
- 4. Thermal Resistance is defined as Θ jc= (Hot Spot Temperature on DUT Base Plate Temperature)/Input Power.

ABSOLUTE MAXIMUM RATINGS 5

Operating Case Tempo	erature ⁶	-55°C to +105°C		
Storage Temperature		-55°C to +105°C		
	+85°C case	200 W		
Power Input	+95°C case	170 W		
	+105°C case	140 W		

- 5. Permanent damage may occur if any of these limits are exceeded.
- 6. Case temperature is defined as temperature on base plate.



STRIPLINE SURFACE MOUNT

Power Splitter/Combiner


QCH-272+

 50Ω 700 to 2700 MHz

2-Way 90°

200W

TYPICAL PERFORMANCE GRAPHS*



 $^{^{\}star}$ Data corresponds to Configuration A at +25 $^{\circ}\text{C}$ unless otherwise specified.



STRIPLINE SURFACE MOUNT

ower Splitter/Combiner

QCH-272+


50Ω

700 to 2700 MHz

2-Way 90°

200W

FUNCTIONAL DIAGRAM




PAD DESCRIPTION/CONFIGURATION 7

Function	Pad	Description
Sum	1	Sum port
Isolation	2	Isolation port
Port 1 (0°)	3	0° port
Port 2 (90°)	4	90° port
Ground	5	Ground

Configuration	Sum	Isolation	Port 1 (0°)	Port 2 (90°)
Α	1	2	3	4
В	2	1	4	3
С	3	4	1	2
D	4	3	2	1

^{7.} Model is symmetrical and all ports are interchangeable, see Port Function Configurations table and s-parameters for actual performance.

SUGGESTED PCB LAYOUT (PL-480)



- NOTES:


 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4003C WITH DIELECTRIC THICKNESS 0.032"±.003". COPPER: 1 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

CASE STYLE DRAWING (PQ2181)



NOTES:

- Base material: Printed wiring laminate.
- Termination finish: 2-5 µinch (.05-.13 microns) Immersion Gold.
- 3. Dimensions: Inches [mm]. Tolerances 2 Pl. ±.03 inch; 3 Pl. ±.010 inch.
- Weight: 1.0 grams
- Marking may contain other features or characters for internal lot control.

PRODUCT MARKING*: QCH-272+

* Marking may contain other features or characters for internal lot control.

/////// Metallization

Solder Resist



Power Splitter/Combiner

QCH-272+

50Ω

700 to 2700 MHz

2-Way 90°

200W

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD

CLICK HERE

Performance Data & Graphs	Data Graphs S-Parameter (S4P files) data set (.zip file) de-embedded to device pads
Case Style	PQ2181 Lead finish: 2-5 μ inch (0.05-0.13 microns) immersion gold
RoHS Status	Compliant
Tape and Reel	F118
Suggested Layout for PCB Design	PL-480
Evaluation Board	TB-884+ Gerber file
Environmental Rating	ENV02T8

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at https://www.minicircuits.com/terms/viewterm.html



QCH-272+

Typical Performance Data

Test Conditions: Input Power =+5 dBm @Temperature = -55°C, Configuration A

Freq.		Total Loss ¹		Amp. Unbal.	Phase Unbal.	Isolation		Returi	ı Loss	
(MHz)		(dB)		(±dB)	(deg)	(dB)		(d	В)	
	Sum-Port 1	Sum-Port 2	Avg	(half P-P)	(Rel. to 90°)	Port 1 - Port 2	Sum	Port 1	Port 2	Iso
700	2.51	3.82	3.12	0.66	-0.48	30.01	-30.99	-31.17	-28.62	-29.65
740	2.65	3.66	3.13	0.51	-0.47	30.38	-32.54	-32.42	-29.46	-30.65
780	2.76	3.52	3.12	0.38	-0.53	30.90	-33.04	-33.41	-29.66	-31.66
820 860	2.87 2.97	3.40 3.29	3.13 3.13	0.27 0.17	-0.59 -0.57	31.18 31.48	-33.38 -33.51	-34.45 -35.46	-29.85 -30.12	-32.45 -33.43
900	3.05	3.21	3.13	0.17	-0.66	31.57	-33.41	-36.08	-30.12	-34.54
940	3.13	3.14	3.13	0.03	-0.65	31.91	-33.97	-36.55	-30.64	-35.51
980	3.19	3.08	3.13	0.06	-0.67	32.22	-34.09	-35.81	-30.81	-36.10
1020	3.26	3.04	3.15	0.11	-0.72	32.66	-34.07	-34.80	-30.84	-36.27
1060	3.30	3.00	3.15	0.15	-0.71	32.62	-34.02	-33.60	-30.95	-35.69
1100	3.34	2.97	3.15	0.18	-0.74	32.84	-33.81	-32.03	-30.77	-34.98
1140	3.38	2.95	3.16	0.21	-0.71	33.12	-33.96	-30.98	-30.42	-34.70
1180	3.40 3.42	2.94 2.93	3.16	0.23	-0.70	33.19 33.68	-33.31	-30.00	-30.23	-34.06
1220 1260	3.42 3.43	2.93 2.93	3.17 3.17	0.24 0.25	-0.76 -0.70	33.91	-32.57 -32.15	-28.98 -28.13	-30.07 -29.96	-33.67 -33.50
1300	3.44	2.93	3.17	0.25	-0.70	34.23	-32.13	-27.48	-30.08	-32.98
1340	3.44	2.95	3.19	0.24	-0.74	34.29	-32.55	-26.89	-29.88	-32.77
1380	3.43	2.96	3.19	0.23	-0.73	34.49	-31.99	-26.25	-29.32	-32.89
1420	3.42	2.98	3.19	0.22	-0.76	34.66	-31.53	-25.88	-28.96	-32.65
1460	3.41	2.99	3.19	0.20	-0.77	34.52	-30.92	-25.49	-28.18	-32.32
1500	3.40	3.01	3.20	0.19	-0.81	34.17	-30.28	-25.06	-27.33	-32.23
1540	3.38	3.04	3.21	0.17	-0.88	33.33	-29.81	-24.82	-26.38	-31.36
1580	3.38	3.06	3.22	0.16	-0.92	32.88	-29.37	-24.57	-25.70	-30.78
1620	3.36	3.08	3.22	0.13	-0.97	31.98	-28.61	-24.57	-24.71	-30.37
1660 1700	3.35 3.34	3.11 3.12	3.23 3.23	0.11 0.11	-1.04 -1.16	31.14 30.16	-28.10 -27.59	-24.71 -24.64	-23.86 -23.16	-29.36 -28.85
1740	3.33	3.14	3.23	0.10	-1.16	29.15	-27.25	-24.53	-22.62	-28.27
1780	3.34	3.17	3.25	0.08	-1.31	28.22	-26.94	-24.42	-22.30	-27.27
1820	3.33	3.18	3.25	0.07	-1.39	27.23	-26.72	-23.88	-21.82	-26.71
1860	3.34	3.17	3.25	0.09	-1.36	27.12	-26.80	-23.84	-21.68	-26.36
1900	3.33	3.17	3.25	0.08	-1.23	26.49	-26.47	-23.38	-21.39	-25.54
1940	3.34	3.18	3.26	0.08	-1.21	25.82	-26.01	-22.94	-21.24	-25.03
1980	3.34	3.19	3.26	80.0	-1.14	25.27	-25.21	-22.70	-20.97	-24.87
2020 2060	3.36 3.39	3.20 3.23	3.28 3.31	0.08 0.08	-1.22 -1.41	24.48 23.78	-24.46 -24.14	-22.40 -21.82	-20.72 -20.59	-24.52 -24.30
2100	3.39 3.41	3.23 3.17	3.29	0.08	-0.90	23.62	-24.14	-21.62	-20.59	-24.30 -24.26
2140	3.41	3.19	3.30	0.11	-0.80	23.09	-22.63	-21.10	-20.49	-24.05
2180	3.43	3.21	3.32	0.11	-0.64	22.52	-22.20	-20.77	-20.61	-23.88
2220	3.43	3.19	3.31	0.12	-0.36	22.42	-21.77	-20.21	-20.69	-24.03
2260	3.42	3.21	3.31	0.11	-0.10	22.16	-21.66	-19.88	-20.77	-23.93
2300	3.40	3.23	3.31	0.09	0.08	21.92	-21.75	-19.86	-20.88	-23.96
2340	3.38	3.25	3.31	0.07	0.05	21.78	-21.49	-19.87	-20.89	-24.20
2380	3.38	3.28	3.33	0.05	0.10	21.54	-21.24	-19.81	-20.93	-24.03
2420	3.35 3.34	3.32 3.34	3.33 3.34	0.02 0.00	0.11 -0.06	21.30 21.15	-21.06 -21.01	-19.76 -19.85	-20.93 -20.97	-23.65 -23.93
2460 2500	3.34	3.34	3.34 3.35	0.00	-0.06 -0.31	20.69	-21.01	-19.85 -19.54	-20.97 -20.88	-23.93 -23.08
2540	3.29	3.42	3.35	0.02	-0.31 -0.41	20.65	-20.39		-20.66	-23.06
2580	3.27	3.47	3.37	0.11	-0.41	20.54	-20.39		-20.46	-22.23
2620	3.29	3.54	3.41	0.13	-1.32	19.98	-20.20	-18.99	-20.14	-21.52
2660	3.24	3.54	3.39	0.16	-1.51	20.11	-19.87		-19.46	-21.37
2700	3.21	3.59	3.40	0.20	-1.44	20.21	-19.95		-19.13	-21.22
2740	3.14	3.66	3.39	0.27	-1.95	20.21	-19.72		-18.66	-20.87
2780	3.13	3.71	3.41	0.31	-2.24	20.15	-19.83		-18.47	-21.02
2820	3.08	3.77	3.41	0.36	-2.40	20.17	-19.59	-18.84	-17.77	-20.87

QCH-272+

Typical Performance Data

Test Conditions: Input Power =+5 dBm @Temperature = -55°C, Configuration B

Freq.		Total Loss ¹		Amp. Unbal.	Phase Unbal.	Isolation		Retur	n Loss	
(MHz)		(dB)		(±dB)	(deg)	(dB)		(d	В)	
	Sum-Port 1	Sum-Port 2	Avg	(half P-P)	(Rel. to 90°)	Port 1 - Port 2	Sum	Port 1	Port 2	Iso
700	2.51	3.83	3.12	0.66	0.26	30.18	29.65	28.62	31.17	30.99
740	2.64	3.66	3.12	0.51	0.32	30.48	30.65	29.46	32.42	32.54
780	2.75	3.52	3.12	0.38	0.29	30.97	31.66	29.66	33.41	33.04
820 860	2.86 2.96	3.40 3.30	3.12 3.13	0.27 0.17	0.29 0.35	31.19 31.44	32.45 33.43	29.85 30.12	34.45 35.46	33.38 33.51
900	3.04	3.22	3.13	0.17	0.33	31.62	34.54	30.12	36.08	33.41
940	3.12	3.14	3.13	0.00	0.37	31.79	35.51	30.64	36.55	33.97
980	3.18	3.08	3.13	0.06	0.41	32.07	36.10	30.81	35.81	34.09
1020	3.24	3.04	3.14	0.11	0.40	32.49	36.27	30.84	34.80	34.07
1060	3.29	3.00	3.14	0.15	0.45	32.51	35.69	30.95	33.60	34.02
1100	3.33	2.97	3.15	0.19	0.42	32.73	34.98	30.77	32.03	33.81
1140	3.37	2.95	3.15	0.22	0.49	32.99	34.70	30.42	30.98	33.96
1180	3.39	2.94	3.16	0.23	0.54	33.10	34.06	30.23	30.00	33.31
1220 1260	3.41 3.42	2.94 2.94	3.17 3.17	0.24 0.25	0.52 0.60	33.51 33.88	33.67 33.50	30.07 29.96	28.98 28.13	32.57 32.15
1300	3.42	2.95	3.17	0.25	0.58	34.17	32.98	30.08	27.48	32.12
1340	3.42	2.95	3.18	0.24	0.56	34.37	32.77	29.88	26.89	32.55
1380	3.41	2.97	3.18	0.23	0.59	34.62	32.89	29.32	26.25	31.99
1420	3.40	2.99	3.19	0.22	0.52	34.84	32.65	28.96	25.88	31.53
1460	3.39	3.00	3.19	0.20	0.48	34.85	32.32	28.18	25.49	30.92
1500	3.37	3.02	3.19	0.18	0.44	34.53	32.23	27.33	25.06	30.28
1540	3.37	3.05	3.21	0.17	0.33	33.89	31.36	26.38	24.82	29.81
1580	3.36	3.06	3.21	0.16	0.33	33.37	30.78	25.70	24.57	29.37
1620 1660	3.34 3.33	3.09 3.10	3.21 3.21	0.14 0.12	0.25 0.18	32.44 31.47	30.37 29.36	24.71 23.86	24.57 24.71	28.61 28.10
1700	3.34	3.12	3.23	0.12	0.05	30.50	28.85	23.16	24.71	27.59
1740	3.32	3.13	3.22	0.12	0.07	29.55	28.27	22.62	24.53	27.25
1780	3.33	3.15	3.24	0.10	0.01	28.48	27.27	22.30	24.42	26.94
1820	3.34	3.16	3.25	0.09	-0.01	27.52	26.71	21.82	23.88	26.72
1860	3.34	3.16	3.25	0.10	0.02	27.24	26.36	21.68	23.84	26.80
1900	3.33	3.16	3.24	0.09	0.11	26.63	25.54	21.39	23.38	26.47
1940	3.34	3.16	3.25	0.09	0.12	25.89	25.03	21.24	22.94	26.01
1980 2020	3.35 3.36	3.17 3.19	3.26 3.27	0.10 0.09	0.25 0.14	25.28 24.51	24.87 24.52	20.97 20.72	22.70 22.40	25.21 24.46
2060	3.39	3.21	3.30	0.09	0.09	23.77	24.30	20.72	21.82	24.14
2100	3.40	3.16	3.28	0.13	0.54	23.63	24.26	20.63	21.50	23.31
2140	3.40	3.17	3.28	0.12	0.75	23.04	24.05	20.49	21.10	22.63
2180	3.41	3.20	3.30	0.12	0.80	22.48	23.88	20.61	20.77	22.20
2220	3.39	3.18	3.28	0.11	1.19	22.40	24.03	20.69	20.21	21.77
2260	3.38	3.20	3.29	0.10	1.30	22.13	23.93	20.77	19.88	21.66
2300	3.37	3.23	3.30	0.08	1.40	21.91	23.96	20.88	19.86	21.75
2340 2380	3.35 3.35	3.24 3.28	3.29 3.31	0.06 0.04	1.30	21.76 21.54	24.20 24.03	20.89 20.93	19.87 19.81	21.49
2380	3.35 3.32	3.28 3.31	3.31	0.04	1.32 1.22	21.54	23.65	20.93	19.81	21.24 21.06
2460	3.31	3.37	3.34	0.01	1.17	21.16	23.93	20.97	19.76	21.00
2500	3.31	3.37	3.34	0.03	0.96	20.72	23.08	20.88	19.54	20.84
2540	3.25	3.42	3.33	0.09	0.73	20.67	22.71	20.66	19.46	20.39
2580	3.23	3.46	3.34	0.11	0.31	20.59	22.23	20.46	19.17	20.16
2620	3.25	3.49	3.37	0.12	-0.34	19.99	21.52	20.14	18.99	20.20
2660	3.20	3.54	3.37	0.16	-0.39	20.15	21.37	19.46	18.99	19.87
2700	3.19	3.59	3.39	0.20	-0.55	20.24	21.22	19.13	18.93	19.95
2740	3.12	3.64 3.70	3.37	0.26	-1.02 -1.32	20.25 20.18	20.87 21.02	18.66	18.92 18.93	19.72 19.83
2780 2820	3.12 3.07	3.70 3.74	3.40 3.39	0.28 0.33	-1.32 -1.51	20.18	20.87	18.47 17.77	18.93	19.83
2020	5.07	J. / 4	5.55	0.00	-1.01	20.20	20.01	17.77	10.04	10.00

QCH-272+

Typical Performance Data

Test Conditions: Input Power =+5 dBm @Temperature = -55°C, Configuration C

Freq.		Total Loss ¹		Amp. Unbal.	Phase Unbal.	Isolation		Returi	n Loss	
(MHz)		(dB)		(±dB)	(deg)	(dB)		(d	В)	
	Sum-Port 1	Sum-Port 2	Avg	(half P-P)	(Rel. to 90°)	Port 1 - Port 2	Sum	Port 1	Port 2	Iso
700	2.51	3.82	3.12	0.66	0.38	29.41	31.17	30.99	29.65	28.62
740	2.64	3.66	3.12	0.51	0.42	29.68	32.42	32.54	30.65	29.46
780	2.76	3.52 3.40	3.12	0.38	0.38 0.38	29.93 30.03	33.41	33.04	31.66	29.66 29.85
820 860	2.87 2.96	3.40	3.13 3.13	0.27 0.17	0.38	30.03 30.22	34.45 35.46	33.38 33.51	32.45 33.43	30.12
900	3.05	3.21	3.13	0.08	0.43	30.34	36.08	33.41	34.54	30.30
940	3.13	3.14	3.13	0.01	0.48	30.48	36.55	33.97	35.51	30.64
980	3.19	3.08	3.13	0.06	0.52	30.61	35.81	34.09	36.10	30.81
1020	3.25	3.04	3.14	0.11	0.52	30.62	34.80	34.07	36.27	30.84
1060	3.30	3.00	3.15	0.15	0.59	30.43	33.60	34.02	35.69	30.95
1100	3.34	2.97	3.15	0.19	0.58	30.24	32.03	33.81	34.98	30.77
1140 1180	3.38 3.39	2.95 2.94	3.16 3.16	0.22 0.23	0.63 0.70	30.03 30.02	30.98 30.00	33.96 33.31	34.70 34.06	30.42 30.23
1220	3.42	2.94	3.17	0.24	0.67	29.99	28.98	32.57	33.67	30.23
1260	3.42	2.93	3.17	0.25	0.75	29.80	28.13	32.15	33.50	29.96
1300	3.43	2.94	3.18	0.25	0.76	29.83	27.48	32.12	32.98	30.08
1340	3.43	2.95	3.18	0.24	0.74	29.66	26.89	32.55	32.77	29.88
1380	3.42	2.96	3.18	0.23	0.79	29.40	26.25	31.99	32.89	29.32
1420	3.41	2.98	3.19	0.22	0.74	29.22	25.88	31.53	32.65	28.96
1460	3.40	3.00	3.20	0.21	0.72	28.69	25.49	30.92	32.32	28.18
1500 1540	3.39 3.38	3.02 3.04	3.20 3.21	0.19 0.17	0.70 0.62	28.08 27.56	25.06 24.82	30.28 29.81	32.23 31.36	27.33 26.38
1580	3.37	3.05	3.21	0.17	0.62	27.06	24.57	29.37	30.78	25.70
1620	3.36	3.08	3.22	0.14	0.55	26.40	24.57	28.61	30.37	24.71
1660	3.34	3.10	3.22	0.12	0.50	25.89	24.71	28.10	29.36	23.86
1700	3.34	3.11	3.22	0.12	0.34	25.23	24.64	27.59	28.85	23.16
1740	3.33	3.12	3.22	0.11	0.38	24.58	24.53	27.25	28.27	22.62
1780	3.33	3.14	3.23	0.10	0.33	23.89	24.42	26.94	27.27	22.30
1820	3.33	3.16	3.24	0.09	0.22	23.42	23.88	26.72	26.71	21.82
1860 1900	3.34 3.33	3.16 3.16	3.25 3.24	0.09 0.09	0.27 0.38	23.03 22.49	23.84 23.38	26.80 26.47	26.36 25.54	21.68 21.39
1940	3.34	3.16	3.25	0.09	0.38	22.05	22.94	26.01	25.03	21.24
1980	3.34	3.17	3.25	0.09	0.49	21.61	22.70	25.21	24.87	20.97
2020	3.36	3.19	3.27	0.09	0.34	21.16	22.40	24.46	24.52	20.72
2060	3.39	3.21	3.30	0.09	0.30	20.76	21.82	24.14	24.30	20.59
2100	3.41	3.16	3.28	0.13	0.70	20.61	21.50	23.31	24.26	20.63
2140	3.41	3.17	3.29	0.12	0.89	20.27	21.10	22.63	24.05	20.49
2180 2220	3.43 3.43	3.20 3.18	3.31 3.30	0.12 0.13	0.94 1.29	19.91 19.91	20.77 20.21	22.20 21.77	23.88 24.03	20.61 20.69
2260	3.42	3.20	3.31	0.13	1.53	19.77	19.88	21.66	23.93	20.77
2300	3.41	3.23	3.32	0.09	1.69	19.64	19.86	21.75	23.96	20.88
2340	3.39	3.25	3.32	0.07	1.61	19.65	19.87	21.49	24.20	20.89
2380	3.38	3.28	3.33	0.05	1.70	19.64	19.81	21.24	24.03	20.93
2420	3.36	3.31	3.33	0.02	1.55	19.55	19.76	21.06	23.65	20.93
2460	3.35	3.37	3.36	0.01	1.59	19.67	19.85	21.01	23.93	20.97
2500	3.35	3.36	3.35	0.01	1.39	19.50	19.54	20.84	23.08	20.88
2540 2580	3.29 3.26	3.43 3.45	3.36 3.35	0.07 0.10	1.13 0.80	19.61 19.73	19.46 19.17	20.39 20.16	22.71 22.23	20.66 20.46
2620	3.29	3.49	3.39	0.10	0.80	19.73	18.99	20.10	21.52	20.40
2660	3.24	3.54	3.39	0.15	0.14	19.34	18.99	19.87	21.37	19.46
2700	3.20	3.58	3.39	0.19	0.09	19.35	18.93	19.95	21.22	19.13
2740	3.14	3.64	3.38	0.25	-0.51	19.19	18.92	19.72	20.87	18.66
2780	3.12	3.70	3.40	0.29	-0.74	19.13	18.93	19.83	21.02	18.47
2820	3.07	3.73	3.39	0.33	-0.89	18.82	18.84	19.59	20.87	17.77

Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document are based on Mini-Circuits applicable established test performance otteria and measurement instructions.
 The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled

QCH-272+

Typical Performance Data

Test Conditions: Input Power =+5 dBm @Temperature = -55°C, Configuration D

700 2.51 3.83 3.12 0.66 -0.58 29.29 28.62 29.65 3.740 3.66 3.12 0.51 -0.57 29.65 29.46 30.65 3.780 2.76 3.52 3.12 0.38 -0.64 29.90 29.66 31.66	Port 2 Iso 30.99 31.1 32.54 32.4 33.04 33.4 33.38 34.4
Sum-Port 1 Sum-Port 2 Avg (half P-P) (Rel. to 90°) Port 1 - Port 2 Sum Port 1 - Fort 3 700 2.51 3.83 3.12 0.66 -0.58 29.29 28.62 29.65 7.05 29.65 29.46 30.65	30.99 31.1 32.54 32.4 33.04 33.4 33.38 34.4
740 2.64 3.66 3.12 0.51 -0.57 29.65 29.46 30.65 3 780 2.76 3.52 3.12 0.38 -0.64 29.90 29.66 31.66 3	32.54 32.4 33.04 33.4 33.38 34.4
780 2.76 3.52 3.12 0.38 -0.64 29.90 29.66 31.66 3	33.04 33.4 33.38 34.4
	33.38 34.4
900 297 341 343 027 074 2004 2006 2246	
	33.41 36.0
	33.97 36.5 34.09 35.8
	34.09 35.6
	34.02 33.6
	33.81 32.0
	33.96 30.9
	33.31 30.0
	32.57 28.9
	32.15 28.1
	32.12 27.4
	32.55 26.8
	31.99 26.2
	31.53 25.8
	30.92 25.4 30.28 25.0
	29.81 24.8
	29.37 24.5
	28.61 24.5
	28.10 24.7
	27.59 24.6
	27.25 24.5
	26.94 24.4
	26.72 23.8
	26.80 23.8
	26.47 23.3
	26.01 22.9
	25.21 22.7 24.46 22.4
	24.46 22.4
	23.31 21.5
	22.63 21.1
	22.20 20.7
	21.77 20.2
	21.66 19.8
	21.75 19.8
	21.49 19.8
	21.24 19.8
	21.06 19.7
	21.01 19.8
	20.84 19.5 20.39 19.4
	20.39 19.4 20.16 19.1
	20.16 19.1
	19.87 18.9
	19.95 18.9
	19.72 18.9
	19.83 18.9
	19.59 18.8

QCH-272+

Typical Performance Data

Test Conditions: Input Power =+5 dBm @Temperature = +25°C, Configuration A

Freq.		Total Loss ¹		Amp. Unbal.	Phase Unbal.	Isolation		Retur	n Loss	
(MHz)		(dB)		(±dB)	(deg)	(dB)		(d	В)	
	Sum-Port 1	Sum-Port 2	Avg	(half P-P)	(Rel. to 90°)	Port 1 - Port 2	Sum	Port 1	Port 2	Iso
700	2.51	3.84	3.12	0.67	-0.27	31.20	-32.51	-31.85	-29.76	-30.93
740	2.64	3.68	3.13	0.52	-0.28	31.23	-33.71	-32.74	-30.19	-31.50
780	2.75	3.54	3.13	0.39	-0.32	31.50	-34.27	-33.78	-30.36	-32.16
820 860	2.86 2.96	3.43 3.32	3.14 3.14	0.28 0.18	-0.35 -0.34	31.66 31.87	-34.68 -35.27	-34.86 -35.85	-30.32 -30.57	-32.58 -33.23
900	3.05	3.32	3.14	0.10	-0.34 -0.44	32.00	-35.58	-36.15	-30.57	-33.23
940	3.12	3.17	3.14	0.10	-0.44	32.25	-35.93	-36.13	-30.72	-34.44
980	3.19	3.11	3.15	0.04	-0.42	32.65	-35.80	-35.28	-30.75	-34.95
1020	3.25	3.07	3.16	0.09	-0.47	33.06	-34.96	-34.45	-30.69	-35.32
1060	3.29	3.03	3.16	0.13	-0.44	33.03	-34.25	-33.35	-30.96	-35.35
1100	3.33	3.00	3.16	0.17	-0.46	33.46	-33.85	-32.13	-31.05	-35.40
1140	3.37	2.98	3.17	0.20	-0.44	33.97	-34.02	-31.28	-31.17	-35.95
1180	3.39	2.97	3.17	0.21	-0.42	34.16 34.94	-33.63	-30.33	-31.42	-35.57
1220 1260	3.41 3.42	2.96 2.96	3.18 3.18	0.22 0.23	-0.47 -0.41	34.94 35.21	-33.02 -32.66	-29.36 -28.56	-31.49 -31.63	-35.21 -35.05
1300	3.42	2.97	3.19	0.23	-0.41	35.77	-32.73	-28.05	-31.52	-34.71
1340	3.42	2.98	3.19	0.22	-0.43	35.87	-32.86	-27.58	-30.91	-34.32
1380	3.42	2.99	3.20	0.21	-0.43	36.08	-32.61	-27.12	-30.20	-34.17
1420	3.41	3.02	3.21	0.20	-0.43	35.91	-32.17	-26.79	-29.50	-33.61
1460	3.40	3.03	3.21	0.18	-0.45	35.65	-31.57	-26.53	-28.63	-32.95
1500	3.39	3.06	3.22	0.17	-0.50	35.07	-31.02	-26.18	-27.70	-32.43
1540	3.38	3.08	3.23	0.15	-0.56	33.92	-30.53	-25.87	-26.84	-31.76
1580	3.36 3.36	3.10 3.13	3.23 3.24	0.13 0.11	-0.61 -0.65	33.16 32.05	-29.96 -29.28	-25.62 -25.41	-26.05 -25.21	-30.84 -30.21
1620 1660	3.35	3.13	3.24	0.11	-0.65 -0.69	31.28	-29.26	-25.41	-23.21 -24.44	-30.21 -29.45
1700	3.34	3.16	3.25	0.09	-0.73	30.17	-28.35	-25.37	-23.75	-28.76
1740	3.33	3.18	3.25	0.08	-0.76	29.20	-27.71	-25.21	-23.10	-28.32
1780	3.33	3.20	3.26	0.07	-0.80	28.38	-27.20	-25.16	-22.61	-27.71
1820	3.33	3.21	3.27	0.06	-0.80	27.46	-26.67	-24.93	-22.18	-27.10
1860	3.34	3.22	3.28	0.06	-0.77	26.87	-26.13	-24.72	-21.80	-26.85
1900	3.33	3.23	3.28	0.06	-0.77	26.15	-25.64	-24.31	-21.47	-26.22
1940 1980	3.34 3.34	3.23 3.24	3.28 3.29	0.06 0.06	-0.74 -0.68	25.49 25.03	-25.06 -24.49	-23.82 -23.50	-21.30 -21.14	-25.80 -25.77
2020	3.36	3.24	3.29	0.06	-0.66 -0.67	25.03 24.57	-24.49	-23.06	-21.14	-25.77 -25.46
2060	3.37	3.25	3.31	0.07	-0.56	24.14	-23.73	-22.55	-20.94	-25.24
2100	3.39	3.24	3.31	0.08	-0.40	23.74	-23.52	-22.29	-20.97	-25.51
2140	3.40	3.25	3.32	0.08	-0.30	23.46	-23.07	-22.00	-21.09	-25.29
2180	3.40	3.24	3.32	0.09	-0.08	23.12	-22.69	-21.60	-21.23	-25.10
2220	3.40	3.25	3.32	0.08	0.12	22.84	-22.42	-21.13	-21.34	-24.99
2260	3.40	3.26	3.33	0.07	0.27	22.54	-22.32	-20.72	-21.60	-24.70
2300 2340	3.39 3.38	3.27 3.30	3.33 3.34	0.07 0.05	0.44 0.48	22.26 22.07	-22.31 -22.13	-20.56 -20.35	-21.83 -21.91	-24.50 -24.42
2340	3.37	3.32	3.34	0.03	0.46	21.86	-22.13 -21.95	-20.33	-21.91	-24.42 -24.18
2420	3.36	3.35	3.35	0.03	0.54	21.64	-21.90	-20.21	-22.04	-23.92
2460	3.34	3.39	3.36	0.02	0.43	21.57	-22.00	-20.09	-21.95	-23.91
2500	3.32	3.42	3.37	0.05	0.36	21.38	-21.91	-20.12		-23.56
2540	3.29	3.46	3.37	0.09	0.10	21.16	-21.61	-20.10	-21.24	-23.15
2580	3.28	3.50	3.39	0.11	-0.12	21.04		-19.97	-20.85	-22.79
2620	3.24	3.54	3.39	0.15	-0.33	20.89		-19.88	-20.37	-22.19
2660	3.22	3.59	3.40	0.19	-0.66	20.68		-19.69	-19.88	-21.69
2700 2740	3.19 3.14	3.63 3.70	3.40 3.41	0.23 0.28	-0.89 -1.31	20.70 20.48	-20.94 -20.65	-19.66 -19.61	-19.43 -18.99	-21.52 -21.09
2780	3.14	3.75	3.42	0.28	-1.64	20.36	-20.05	-19.01	-18.53	-21.09
2820	3.08	3.82	3.43	0.38	-1.79	20.25	-20.43	-19.24		-20.67
		-	-		-	-				

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification and operformance afterial and measurement instructions.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits applicable established test performance afterial and measurement instructions.

The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"), Purchasers of this part are entitled.

QCH-272+

Typical Performance Data

Test Conditions: Input Power =+5 dBm @Temperature = +25°C, Configuration B

Freq.		Total Loss ¹		Amp. Unbal.	Phase Unbal.	Isolation		Return	ı Loss	
(MHz)		(dB)		(±dB)	(deg)	(dB)		(d	В)	
	Sum-Port 1	Sum-Port 2	Avg	(half P-P)	(Rel. to 90°)	Port 1 - Port 2	Sum	Port 1	Port 2	Iso
700	2.54	3.84	3.14	0.66	0.11	31.37	30.93	29.76	31.85	32.51
740	2.67	3.68	3.15	0.51	0.14	31.33	31.50	30.19	32.74	33.71
780	2.78 2.89	3.54 3.43	3.14	0.38	0.10 0.10	31.57	32.16 32.58	30.36	33.78	34.27 34.68
820 860	2.89	3.43	3.15 3.15	0.27 0.17	0.10	31.67 31.83	33.23	30.32 30.57	34.86 35.85	35.27
900	3.07	3.24	3.15	0.08	0.10	32.04	33.93	30.72	36.15	35.58
940	3.15	3.17	3.16	0.01	0.12	32.12	34.44	30.85	36.13	35.93
980	3.22	3.11	3.16	0.06	0.16	32.49	34.95	30.75	35.28	35.80
1020	3.28	3.07	3.17	0.11	0.13	32.87	35.32	30.69	34.45	34.96
1060	3.32	3.03	3.17	0.15	0.18	32.93	35.35	30.96	33.35	34.25
1100	3.36	3.00	3.18	0.19	0.15	33.36	35.40	31.05	32.13	33.85
1140 1180	3.40 3.42	2.98 2.97	3.18 3.19	0.21 0.23	0.19 0.21	33.85 34.09	35.95 35.57	31.17 31.42	31.28 30.33	34.02 33.63
1220	3.44	2.97	3.19	0.23	0.19	34.81	35.21	31.42	29.36	33.02
1260	3.45	2.97	3.20	0.24	0.23	35.24	35.05	31.63	28.56	32.66
1300	3.45	2.98	3.21	0.24	0.19	35.77	34.71	31.52	28.05	32.73
1340	3.45	2.99	3.21	0.24	0.16	36.08	34.32	30.91	27.58	32.86
1380	3.45	3.00	3.22	0.23	0.17	36.34	34.17	30.20	27.12	32.61
1420	3.44	3.02	3.22	0.21	0.12	36.26	33.61	29.50	26.79	32.17
1460	3.43	3.04	3.23	0.20	0.06	36.16	32.95	28.63	26.53	31.57
1500 1540	3.41 3.41	3.06 3.08	3.23 3.24	0.18 0.17	0.00 -0.08	35.59 34.55	32.43 31.76	27.70 26.84	26.18 25.87	31.02 30.53
1580	3.39	3.10	3.24	0.17	-0.06 -0.15	33.59	30.84	26.05	25.62	29.96
1620	3.39	3.13	3.26	0.14	-0.23	32.47	30.21	25.21	25.41	29.28
1660	3.38	3.14	3.26	0.13	-0.29	31.55	29.45	24.44	25.41	28.86
1700	3.37	3.15	3.26	0.11	-0.32	30.46	28.76	23.75	25.37	28.35
1740	3.37	3.17	3.27	0.10	-0.38	29.51	28.32	23.10	25.21	27.71
1780	3.37	3.18	3.27	0.10	-0.40	28.55	27.71	22.61	25.16	27.20
1820	3.37	3.19	3.28	0.09	-0.39	27.67	27.10	22.18	24.93	26.67
1860 1900	3.38 3.38	3.20 3.20	3.29 3.29	0.09 0.09	-0.39 -0.35	26.91 26.22	26.85 26.22	21.80 21.47	24.72 24.31	26.13 25.64
1940	3.38	3.21	3.29	0.09	-0.33	25.50	25.80	21.30	23.82	25.04
1980	3.39	3.22	3.30	0.09	-0.24	24.98	25.77	21.14	23.50	24.49
2020	3.40	3.22	3.31	0.09	-0.17	24.53	25.46	21.00	23.06	24.05
2060	3.42	3.23	3.32	0.10	-0.15	24.08	25.24	20.94	22.55	23.73
2100	3.43	3.22	3.32	0.11	0.00	23.71	25.51	20.97	22.29	23.52
2140	3.43	3.22	3.32	0.11	0.12	23.36	25.29	21.09	22.00	23.07
2180 2220	3.43 3.42	3.22 3.24	3.32 3.33	0.11 0.09	0.38 0.53	23.06 22.79	25.10 24.99	21.23 21.34	21.60 21.13	22.69 22.42
2260	3.42	3.25	3.33	0.08	0.53	22.49	24.99	21.60	20.72	22.42
2300	3.41	3.27	3.34	0.07	0.68	22.23	24.50	21.83	20.56	22.31
2340	3.39	3.29	3.34	0.05	0.66	22.04	24.42	21.91	20.35	22.13
2380	3.39	3.33	3.36	0.03	0.59	21.85	24.18	22.06	20.21	21.95
2420	3.37	3.36	3.36	0.01	0.55	21.62	23.92	22.04	20.13	21.90
2460	3.35	3.40	3.37	0.03	0.37	21.58	23.91	21.95	20.09	22.00
2500	3.34	3.43	3.38	0.05	0.12	21.39	23.56	21.65		21.91
2540 2580	3.31 3.30	3.46 3.50	3.38 3.40	0.08 0.10	-0.13 -0.41	21.17 21.06	23.15 22.79	21.24 20.85	20.10 19.97	21.61 21.33
2620	3.30 3.27	3.50 3.54	3.40	0.10	-0.41	20.88	22.79	20.85	19.97	21.33
2660	3.25	3.57	3.41	0.16	-1.02	20.69	21.69	19.88	19.69	21.12
2700	3.22	3.63	3.42	0.20	-1.23	20.72	21.52	19.43	19.66	20.94
2740	3.19	3.69	3.43	0.25	-1.55	20.51	21.09	18.99	19.61	20.65
2780	3.16	3.74	3.44	0.29	-2.00	20.36	20.74	18.53	19.37	20.46
2820	3.13	3.80	3.45	0.33	-2.16	20.25	20.67	18.23	19.24	20.43

QCH-272+

Typical Performance Data

Test Conditions: Input Power =+5 dBm @Temperature = +25°C, Configuration C

Freq.		Total Loss ¹		Amp. Unbal.	Phase Unbal.	Isolation		Returi	n Loss	
(MHz)		(dB)		(±dB)	(deg)	(dB)		(d	В)	
	Sum-Port 1	Sum-Port 2	Avg	(half P-P)	(Rel. to 90°)	Port 1 - Port 2	Sum	Port 1	Port 2	Iso
700	2.51	3.84	3.12	0.67	0.50	30.21	31.85	32.51	30.93	29.76
740	2.64	3.68	3.13	0.52	0.52	30.23	32.74	33.71	31.50	30.19
780	2.75	3.54	3.13	0.40	0.50	30.39	33.78	34.27	32.16	30.36
820 860	2.86 2.96	3.43 3.32	3.14 3.14	0.29 0.18	0.51 0.58	30.44 30.40	34.86 35.85	34.68 35.27	32.58 33.23	30.32 30.57
900	3.04	3.24	3.14	0.10	0.54	30.52	36.15	35.58	33.93	30.72
940	3.12	3.17	3.14	0.02	0.59	30.52	36.13	35.93	34.44	30.85
980	3.19	3.11	3.15	0.04	0.64	30.59	35.28	35.80	34.95	30.75
1020	3.25	3.07	3.16	0.09	0.63	30.77	34.45	34.96	35.32	30.69
1060	3.29	3.03	3.16	0.14	0.70	30.78	33.35	34.25	35.35	30.96
1100	3.33	3.00	3.16	0.17	0.70	30.91	32.13	33.85	35.40	31.05
1140 1180	3.37 3.38	2.98 2.97	3.17 3.17	0.20 0.21	0.75 0.82	30.99 31.20	31.28 30.33	34.02 33.63	35.95 35.57	31.17 31.42
1220	3.41	2.97	3.17	0.21	0.82	31.35	29.36	33.02	35.21	31.42
1260	3.41	2.97	3.18	0.23	0.87	31.23	28.56	32.66	35.05	31.63
1300	3.42	2.98	3.19	0.22	0.88	31.26	28.05	32.73	34.71	31.52
1340	3.42	2.99	3.20	0.22	0.86	31.04	27.58	32.86	34.32	30.91
1380	3.41	3.00	3.20	0.21	0.91	30.73	27.12	32.61	34.17	30.20
1420	3.40	3.02	3.21	0.20	0.89	30.39	26.79	32.17	33.61	29.50
1460 1500	3.39 3.38	3.04 3.05	3.21 3.21	0.18 0.17	0.86 0.83	29.85 29.09	26.53 26.18	31.57 31.02	32.95 32.43	28.63 27.70
1540	3.37	3.08	3.21	0.17	0.83	28.38	25.87	30.53	31.76	26.84
1580	3.35	3.10	3.22	0.14	0.73	27.71	25.62	29.96	30.84	26.05
1620	3.35	3.12	3.23	0.12	0.68	26.91	25.41	29.28	30.21	25.21
1660	3.34	3.14	3.24	0.11	0.63	26.37	25.41	28.86	29.45	24.44
1700	3.33	3.15	3.24	0.10	0.61	25.58	25.37	28.35	28.76	23.75
1740	3.33	3.17	3.25	0.08	0.58	24.95	25.21	27.71	28.32	23.10
1780 1820	3.32 3.33	3.18 3.19	3.25 3.26	0.08 0.07	0.56 0.54	24.37 23.82	25.16 24.93	27.20 26.67	27.71 27.10	22.61 22.18
1860	3.33	3.19	3.26	0.07	0.60	23.30	24.93	26.13	26.85	21.80
1900	3.33	3.20	3.26	0.07	0.62	22.70	24.31	25.64	26.22	21.47
1940	3.34	3.21	3.27	0.07	0.67	22.27	23.82	25.06	25.80	21.30
1980	3.34	3.22	3.28	0.07	0.73	21.84	23.50	24.49	25.77	21.14
2020	3.36	3.22	3.29	0.07	0.77	21.50	23.06	24.05	25.46	21.00
2060	3.38	3.23	3.30	0.08	0.88	21.21	22.55	23.73	25.24	20.94
2100 2140	3.39 3.40	3.22 3.22	3.30 3.31	0.08 0.09	0.98 1.12	20.84 20.72	22.29 22.00	23.52 23.07	25.51 25.29	20.97 21.09
2180	3.41	3.22	3.31	0.09	1.41	20.55	21.60	22.69	25.10	21.23
2220	3.40	3.24	3.32	0.08	1.54	20.39	21.13	22.42	24.99	21.34
2260	3.40	3.25	3.32	0.08	1.70	20.28	20.72	22.32	24.70	21.60
2300	3.40	3.27	3.33	0.06	1.85	20.14	20.56	22.31	24.50	21.83
2340	3.38	3.30	3.34	0.05	1.88	20.09	20.35	22.13	24.42	21.91
2380	3.38	3.33	3.35	0.03	1.89	20.06	20.21 20.13	21.95	24.18	22.06
2420 2460	3.36 3.34	3.36 3.40	3.36 3.37	0.00 0.03	1.86 1.77	19.92 19.96	20.13	21.90 22.00	23.92 23.91	22.04 21.95
2500	3.32	3.43	3.37	0.06	1.59	19.95	20.03		23.56	21.65
2540	3.29	3.47	3.38	0.09	1.31	19.87	20.10	21.61	23.15	21.24
2580	3.28	3.50	3.39	0.11	1.13	19.94	19.97	21.33	22.79	20.85
2620	3.24	3.53	3.38	0.15	0.79	19.81	19.88	21.12	22.19	20.37
2660	3.22	3.57	3.39	0.18	0.57	19.69	19.69	21.10	21.69	19.88
2700	3.18	3.62	3.39	0.22	0.40	19.68	19.66	20.94	21.52	19.43
2740 2780	3.14 3.11	3.69 3.74	3.41 3.41	0.28 0.31	0.03 -0.39	19.46 19.34	19.61 19.37	20.65 20.46	21.09 20.74	18.99 18.53
2820	3.07	3.80	3.42	0.31	-0.59	19.16	19.37	20.40	20.74	18.23
_525	5.01	0.00	J. 12	5.00	0.00			00	_0.07	

QCH-272+

Typical Performance Data

Test Conditions: Input Power =+5 dBm @Temperature = +25°C, Configuration D

MHz Cab Cab	Freq.		Total Loss ¹		Amp. Unbal.	Phase Unbal.	Isolation		Retur	n Loss	
Tool	(MHz)		(dB)		(±dB)	(deg)	(dB)		(d	В)	
740		Sum-Port 1	Sum-Port 2	Avg	(half P-P)		Port 1 - Port 2	Sum	Port 1	Port 2	Iso
780											
820 2.89 3.43 3.15 0.27 -0.78 30.42 30.32 32.58 34.68 34.69 900 3.08 3.24 3.16 0.09 -0.88 30.62 30.72 33.93 35.57 35.58 36.15 940 3.16 3.17 3.16 0.01 -0.91 30.62 30.72 33.93 35.58 36.15 980 3.22 3.11 3.16 0.05 -0.92 30.69 30.75 34.95 35.80 35.28 1020 3.28 3.07 3.17 0.11 -0.99 30.98 30.69 35.35 34.25 35.80 1100 3.37 3.00 3.18 0.15 -0.98 30.98 35.35 34.25 33.48 11100 3.37 3.00 3.18 0.21 -1.02 30.98 33.16 35.40 33.85 32.13 11100 3.45 2.96 3.16 3.16 3.11 31.61 3											
860 2.99 3.32 3.15 0.17 -0.78 30.46 30.57 33.23 35.57 35.85 940 3.16 3.17 3.16 0.01 -0.91 30.62 30.85 34.44 35.93 36.13 980 3.22 3.11 3.16 0.01 -0.91 30.62 30.85 34.44 35.93 36.13 1020 3.28 3.07 3.17 0.11 -0.99 30.98 30.75 34.95 35.80 35.22 1100 3.33 3.03 3.18 0.15 -0.96 30.95 30.96 35.35 34.25 33.35 1140 3.40 2.98 3.18 0.21 -1.02 30.91 31.17 35.50 34.25 33.35 34.25 33.35 1220 34.4 2.96 3.19 0.24 -1.07 31.26 31.17 33.02 22.1 -1.02 30.91 31.17 33.02 22.1 -1.03 30.82 31.43											
900											
940											
980 3.22 3.11 3.16 0.05 -0.92 30.089 30.75 34.95 35.80 35.28 1000 3.28 3.37 3.49 3.45 3.45 3.45 1000 3.33 3.33 3.03 3.18 0.15 -0.96 30.95 30.96 35.35 34.25 33.35 1100 3.37 3.00 3.18 0.15 -0.96 30.95 30.96 35.35 34.25 33.35 1100 3.42 2.98 3.18 0.21 -1.02 30.91 31.17 35.95 34.02 31.28 1180 3.42 2.98 3.18 0.22 -1.01 31.26 31.42 35.57 33.63 30.33 31.220 3.44 2.96 3.19 0.24 -1.07 31.25 31.49 35.21 33.02 29.36 1260 3.45 2.96 3.20 0.25 -1.05 30.82 31.63 35.05 35.20 35.05 35.20 3.45 2.98 3.21 0.24 -1.14 30.75 30.91 34.32 32.86 27.58 1380 3.45 2.99 3.21 0.24 -1.14 30.75 30.91 34.32 32.86 27.58 1380 3.45 2.99 3.21 0.23 -1.13 30.35 30.03 34.51 30.33 32.33 30.33 3.33 3.33 3.33 3.33 3.34 3.46 2.98 3.21 0.23 -1.13 30.35 30.20 34.77 32.61 27.12 1420 3.44 3.02 3.22 0.21 -1.19 29.61 29.50 33.61 32.17 26.79 1460 3.43 3.03 3.23 0.20 -1.24 29.61 29.50 33.61 32.17 26.79 1460 3.43 3.03 3.23 0.18 -1.33 28.62 27.70 32.43 31.02 26.18 3.39 3.13 3.26 0.13 -1.54 26.51 25.21 30.21 29.28 25.51 1570 26.18 3.39 3.13 3.26 0.13 -1.54 26.51 25.21 30.21 29.28 25.51 1700 3.37 3.16 3.26 0.11 -1.66 25.51 23.75 28.76 28.85 25.37 1740 3.37 3.18 3.22 3.30 0.08 -1.75 24.06 22.61 27.71 27.20 25.16 25.21 30.21 29.28 25.41 1700 3.37 3.16 3.26 0.11 -1.66 25.51 23.75 28.76 28.85 25.37 1740 3.37 3.18 3.27 3.30 0.08 -1.75 24.06 22.61 27.71 27.20 25.16 25.21 30.21 29.28 25.41 1700 3.37 3.18 3.22 3.30 0.08 -1.75 23.25 21.80 26.85 26.13 24.72 25.66 22.60 24.41 25.77 24.49 25.50 25.60 25.60 3.42 3.33 0.09 -1.76 22.66 21.47 26.22 25.											
1020											
1100	1020		3.07	3.17	0.11	-0.99	30.98	30.69	35.32	34.96	34.45
1140											
1180											
1220											31.28
1260											
1300 3.45 2.97 3.20 0.24 -1.08 30.88 31.52 34.71 32.73 28.05 1340 3.46 2.98 3.21 0.24 -1.14 30.75 30.91 34.32 32.86 27.58 1380 3.45 2.99 3.21 0.23 -1.13 30.35 30.20 34.17 32.61 27.12 1460 3.44 3.02 3.22 0.21 -1.19 29.61 29.50 33.61 32.17 26.79 1460 3.43 3.03 3.23 0.20 -1.24 29.03 28.63 32.95 31.57 26.51 1500 3.42 3.05 3.23 0.18 -1.33 28.62 27.70 32.43 31.02 26.18 1500 3.39 3.10 3.24 0.15 -1.46 27.18 26.05 30.84 29.96 28.61 1620 3.39 3.13 3.26 0.13 -1.54 26.51 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
1340 3.46 2.98 3.21 0.24 -1.14 30.75 30.91 34.32 32.66 27.58 1380 3.45 2.99 3.21 0.23 -1.13 30.35 30.20 34.17 32.61 27.12 1420 3.44 3.02 3.22 0.21 -1.19 29.61 29.50 33.61 32.17 26.79 1460 3.43 3.03 3.23 0.20 -1.24 29.03 28.63 32.95 31.57 26.53 1500 3.42 3.05 3.23 0.18 -1.33 28.62 27.70 32.43 31.02 26.18 1500 3.41 3.08 3.24 0.17 -1.40 27.98 26.84 31.76 30.53 25.87 1500 3.39 3.13 3.26 0.13 -1.54 26.51 25.21 30.21 29.28 25.41 1700 3.37 3.18 3.26 0.11 -1.66 25.51 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
1420 3.44 3.02 3.22 0.21 -1.19 29.61 29.50 33.61 32.17 26.53 1500 3.42 3.05 3.23 0.20 -1.24 29.03 28.63 32.95 31.57 26.53 1540 3.41 3.08 3.24 0.17 -1.40 27.98 26.84 31.76 30.53 25.67 1580 3.39 3.10 3.24 0.15 -1.46 27.18 26.05 30.84 29.96 25.62 1620 3.39 3.13 3.26 0.13 -1.54 26.51 25.21 30.21 29.28 25.41 1700 3.37 3.16 3.26 0.11 -1.66 25.51 23.75 28.76 28.35 25.37 1740 3.37 3.18 3.27 0.10 -1.71 24.67 23.10 28.32 27.71 25.21 1780 3.37 3.21 3.29 0.08 -1.75 24.06 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
1460 3.43 3.03 3.23 0.20 -1.24 29.03 28.63 32.95 31.57 26.53 1500 3.42 3.05 3.23 0.18 -1.33 28.62 27.70 32.43 31.02 26.18 1540 3.41 3.08 3.24 0.15 -1.46 27.18 26.05 30.84 29.96 25.62 1620 3.39 3.13 3.26 0.13 -1.54 26.51 25.21 30.21 29.28 25.41 1660 3.38 3.14 3.26 0.12 -1.62 26.09 24.44 29.45 28.86 25.41 1700 3.37 3.16 3.26 0.11 -1.66 25.51 23.75 28.76 28.35 25.37 1740 3.37 3.18 3.27 0.10 -1.75 24.06 22.61 27.71 27.20 25.16 1820 3.37 3.21 3.29 0.08 -1.73 23.65 <t< td=""><td></td><td>3.45</td><td>2.99</td><td></td><td></td><td></td><td>30.35</td><td>30.20</td><td>34.17</td><td>32.61</td><td></td></t<>		3.45	2.99				30.35	30.20	34.17	32.61	
1500											
1540											
1580											
1620											
1660											
1700											
1740 3.37 3.18 3.27 0.10 -1.71 24.67 23.10 28.32 27.71 25.21 1780 3.37 3.19 3.28 0.09 -1.75 24.06 22.61 27.71 27.20 25.16 1820 3.37 3.21 3.29 0.08 -1.73 23.65 22.18 27.10 26.67 24.93 1860 3.38 3.22 3.30 0.08 -1.75 23.25 21.80 26.85 26.13 24.72 1900 3.38 3.22 3.30 0.08 -1.76 22.66 21.47 26.22 25.64 24.31 1940 3.38 3.23 3.30 0.08 -1.76 22.66 21.47 26.22 25.64 24.31 1980 3.40 3.23 3.31 0.08 -1.66 21.86 21.14 25.77 24.49 23.50 2060 3.42 3.24 3.33 0.09 -1.56 21.30 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
1820 3.37 3.21 3.29 0.08 -1.73 23.65 22.18 27.10 26.67 24.93 1860 3.38 3.22 3.30 0.08 -1.75 23.25 21.80 26.85 26.13 24.72 1900 3.38 3.22 3.30 0.08 -1.76 22.66 21.47 26.22 25.64 24.31 1940 3.38 3.23 3.30 0.08 -1.76 22.66 21.47 26.22 25.64 22.56 1980 3.40 3.23 3.31 0.08 -1.66 21.86 21.14 25.77 24.49 23.50 2020 3.40 3.24 3.32 0.08 -1.61 21.63 21.00 25.46 24.05 23.06 2060 3.42 3.24 3.33 0.09 -1.56 21.30 20.94 25.24 23.73 22.55 2100 3.43 3.24 3.33 0.09 -1.27 20.78 <t< td=""><td>1740</td><td>3.37</td><td>3.18</td><td></td><td>0.10</td><td></td><td>24.67</td><td></td><td>28.32</td><td>27.71</td><td>25.21</td></t<>	1740	3.37	3.18		0.10		24.67		28.32	27.71	25.21
1860 3.38 3.22 3.30 0.08 -1.75 23.25 21.80 26.85 26.13 24.72 1900 3.38 3.22 3.30 0.08 -1.76 22.66 21.47 26.22 25.64 24.31 1940 3.38 3.23 3.30 0.08 -1.72 22.18 21.30 25.80 25.06 23.82 1980 3.40 3.23 3.31 0.08 -1.66 21.86 21.14 25.77 24.49 23.50 2020 3.40 3.24 3.32 0.08 -1.61 21.63 21.00 25.46 24.05 23.06 2060 3.42 3.24 3.33 0.09 -1.56 21.30 20.94 25.24 23.73 22.55 2100 3.43 3.24 3.33 0.09 -1.27 20.78 21.09 25.29 23.07 22.00 2180 3.44 3.24 3.34 0.10 -1.05 20.68 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
1900 3.38 3.22 3.30 0.08 -1.76 22.66 21.47 26.22 25.64 24.31 1940 3.38 3.23 3.30 0.08 -1.72 22.18 21.30 25.80 25.06 23.82 1980 3.40 3.23 3.31 0.08 -1.66 21.86 21.14 25.77 24.49 23.50 2020 3.40 3.24 3.32 0.08 -1.61 21.63 21.00 25.46 24.05 23.06 2060 3.42 3.24 3.33 0.09 -1.56 21.30 20.94 25.24 23.73 22.55 2100 3.43 3.24 3.33 0.09 -1.40 20.88 20.97 25.51 23.52 22.29 2140 3.43 3.24 3.33 0.09 -1.27 20.78 21.09 25.29 23.07 22.00 2180 3.44 3.24 3.34 0.10 -1.05 20.68 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
1940 3.38 3.23 3.30 0.08 -1.72 22.18 21.30 25.80 25.06 23.82 1980 3.40 3.23 3.31 0.08 -1.66 21.86 21.14 25.77 24.49 23.50 2020 3.40 3.24 3.32 0.08 -1.61 21.63 21.00 25.46 24.05 23.06 2060 3.42 3.24 3.33 0.09 -1.56 21.30 20.94 25.24 23.73 22.55 2100 3.43 3.24 3.33 0.09 -1.40 20.88 20.97 25.51 23.52 22.29 2140 3.43 3.24 3.33 0.09 -1.27 20.78 21.09 25.29 23.07 22.00 2180 3.44 3.24 3.34 0.10 -1.05 20.68 21.23 25.10 22.69 21.60 2220 3.42 3.25 3.33 0.09 -0.87 20.50 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
1980 3.40 3.23 3.31 0.08 -1.66 21.86 21.14 25.77 24.49 23.50 2020 3.40 3.24 3.32 0.08 -1.61 21.63 21.00 25.46 24.05 23.06 2060 3.42 3.24 3.33 0.09 -1.56 21.30 20.94 25.24 23.73 22.55 2100 3.43 3.24 3.33 0.09 -1.40 20.88 20.97 25.51 23.52 22.29 2140 3.43 3.24 3.33 0.09 -1.27 20.78 21.09 25.29 23.07 22.00 2180 3.44 3.24 3.34 0.10 -1.05 20.68 21.23 25.10 22.69 21.60 2220 3.42 3.25 3.33 0.09 -0.87 20.50 21.34 24.99 22.42 21.13 2260 3.41 3.27 3.34 0.08 -0.81 20.32 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
2020 3.40 3.24 3.32 0.08 -1.61 21.63 21.00 25.46 24.05 23.06 2060 3.42 3.24 3.33 0.09 -1.56 21.30 20.94 25.24 23.73 22.55 2100 3.43 3.24 3.33 0.09 -1.40 20.88 20.97 25.51 23.52 22.29 2140 3.43 3.24 3.33 0.09 -1.27 20.78 21.09 25.29 23.07 22.00 2180 3.44 3.24 3.34 0.10 -1.05 20.68 21.23 25.10 22.69 21.60 2220 3.42 3.25 3.33 0.09 -0.87 20.50 21.34 24.99 22.42 21.13 2260 3.42 3.26 3.34 0.08 -0.81 20.32 21.60 24.70 22.32 20.72 2300 3.41 3.27 3.34 0.07 -0.70 20.16 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
2060 3.42 3.24 3.33 0.09 -1.56 21.30 20.94 25.24 23.73 22.55 2100 3.43 3.24 3.33 0.09 -1.40 20.88 20.97 25.51 23.52 22.29 2140 3.43 3.24 3.33 0.09 -1.27 20.78 21.09 25.29 23.07 22.00 2180 3.44 3.24 3.34 0.10 -1.05 20.68 21.23 25.10 22.69 21.60 2220 3.42 3.25 3.33 0.09 -0.87 20.50 21.34 24.99 22.42 21.13 2260 3.42 3.26 3.34 0.08 -0.81 20.32 21.60 24.70 22.32 20.72 2300 3.41 3.27 3.34 0.07 -0.70 20.16 21.83 24.50 22.31 20.56 2340 3.39 3.29 3.34 0.05 -0.71 20.11 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
2140 3.43 3.24 3.33 0.09 -1.27 20.78 21.09 25.29 23.07 22.00 2180 3.44 3.24 3.34 0.10 -1.05 20.68 21.23 25.10 22.69 21.60 2220 3.42 3.25 3.33 0.09 -0.87 20.50 21.34 24.99 22.42 21.13 2260 3.42 3.26 3.34 0.08 -0.81 20.32 21.60 24.70 22.32 20.72 2300 3.41 3.27 3.34 0.07 -0.70 20.16 21.83 24.50 22.31 20.56 2340 3.39 3.29 3.34 0.05 -0.71 20.11 21.91 24.42 22.13 20.35 2380 3.39 3.32 3.35 0.03 -0.75 20.08 22.06 24.18 21.95 20.21 2420 3.37 3.35 3.36 0.01 -0.74 19.93 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
2180 3.44 3.24 3.34 0.10 -1.05 20.68 21.23 25.10 22.69 21.60 2220 3.42 3.25 3.33 0.09 -0.87 20.50 21.34 24.99 22.42 21.13 2260 3.42 3.26 3.34 0.08 -0.81 20.32 21.60 24.70 22.32 20.72 2300 3.41 3.27 3.34 0.07 -0.70 20.16 21.83 24.50 22.31 20.56 2340 3.39 3.29 3.34 0.05 -0.71 20.11 21.91 24.42 22.13 20.56 2380 3.39 3.32 3.35 0.03 -0.75 20.08 22.06 24.18 21.95 20.21 2420 3.37 3.35 3.36 0.01 -0.74 19.93 22.04 23.92 21.90 20.13 2460 3.34 3.41 3.37 0.04 -1.10 19.94 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
2220 3.42 3.25 3.33 0.09 -0.87 20.50 21.34 24.99 22.42 21.13 2260 3.42 3.26 3.34 0.08 -0.81 20.32 21.60 24.70 22.32 20.72 2300 3.41 3.27 3.34 0.07 -0.70 20.16 21.83 24.50 22.31 20.56 2340 3.39 3.29 3.34 0.05 -0.71 20.11 21.91 24.42 22.13 20.35 2380 3.39 3.32 3.35 0.03 -0.75 20.08 22.06 24.18 21.95 20.21 2420 3.37 3.35 3.36 0.01 -0.74 19.93 22.04 23.92 21.90 20.13 2460 3.35 3.38 3.36 0.01 -0.74 19.93 22.04 23.92 21.90 20.19 2500 3.34 3.41 3.37 0.04 -1.10 19.94 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>22.00</td></t<>											22.00
2260 3.42 3.26 3.34 0.08 -0.81 20.32 21.60 24.70 22.32 20.72 2300 3.41 3.27 3.34 0.07 -0.70 20.16 21.83 24.50 22.31 20.56 2340 3.39 3.29 3.34 0.05 -0.71 20.11 21.91 24.42 22.13 20.35 2380 3.39 3.32 3.35 0.03 -0.75 20.08 22.06 24.18 21.95 20.21 2420 3.37 3.35 3.36 0.01 -0.74 19.93 22.04 23.92 21.90 20.13 2460 3.35 3.38 3.36 0.02 -0.94 19.94 21.95 23.91 22.00 20.09 2500 3.34 3.41 3.37 0.04 -1.10 19.94 21.95 23.91 22.00 20.09 2540 3.31 3.46 3.38 0.08 -1.34 19.84 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>21.60</td></t<>											21.60
2300 3.41 3.27 3.34 0.07 -0.70 20.16 21.83 24.50 22.31 20.56 2340 3.39 3.29 3.34 0.05 -0.71 20.11 21.91 24.42 22.13 20.35 2380 3.39 3.32 3.35 0.03 -0.75 20.08 22.06 24.18 21.95 20.21 2420 3.37 3.35 3.36 0.01 -0.74 19.93 22.04 23.92 21.90 20.13 2460 3.35 3.38 3.36 0.02 -0.94 19.94 21.95 23.91 22.00 20.09 2500 3.34 3.41 3.37 0.04 -1.10 19.94 21.65 23.56 21.91 20.12 2540 3.31 3.46 3.38 0.08 -1.34 19.84 21.24 23.15 21.61 20.10 2580 3.30 3.50 3.40 0.10 -1.64 19.86 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
2340 3.39 3.29 3.34 0.05 -0.71 20.11 21.91 24.42 22.13 20.35 2380 3.39 3.32 3.35 0.03 -0.75 20.08 22.06 24.18 21.95 20.21 2420 3.37 3.35 3.36 0.01 -0.74 19.93 22.04 23.92 21.90 20.13 2460 3.35 3.38 3.36 0.02 -0.94 19.94 21.95 23.91 22.00 20.09 2500 3.34 3.41 3.37 0.04 -1.10 19.94 21.65 23.56 21.91 20.12 2540 3.31 3.46 3.38 0.08 -1.34 19.84 21.24 23.15 21.61 20.10 2580 3.30 3.50 3.40 0.10 -1.64 19.86 20.85 22.79 21.33 19.97 2620 3.27 3.54 3.40 0.14 -1.85 19.81 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>-</td><td></td><td></td></t<>									-		
2380 3.39 3.32 3.35 0.03 -0.75 20.08 22.06 24.18 21.95 20.21 2420 3.37 3.35 3.36 0.01 -0.74 19.93 22.04 23.92 21.90 20.13 2460 3.35 3.38 3.36 0.02 -0.94 19.94 21.95 23.91 22.00 20.09 2500 3.34 3.41 3.37 0.04 -1.10 19.94 21.65 23.56 21.91 20.12 2540 3.31 3.46 3.38 0.08 -1.34 19.84 21.24 23.15 21.61 20.10 2580 3.30 3.50 3.40 0.10 -1.64 19.86 20.85 22.79 21.33 19.97 2620 3.27 3.54 3.40 0.14 -1.85 19.81 20.37 22.19 21.12 19.88 2660 3.25 3.59 3.42 0.17 -2.26 19.70 <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></t<>											
2420 3.37 3.35 3.36 0.01 -0.74 19.93 22.04 23.92 21.90 20.13 2460 3.35 3.38 3.36 0.02 -0.94 19.94 21.95 23.91 22.00 20.09 2500 3.34 3.41 3.37 0.04 -1.10 19.94 21.65 23.56 21.91 20.12 2540 3.31 3.46 3.38 0.08 -1.34 19.84 21.24 23.15 21.61 20.10 2580 3.30 3.50 3.40 0.10 -1.64 19.86 20.85 22.79 21.33 19.97 2620 3.27 3.54 3.40 0.14 -1.85 19.81 20.37 22.19 21.12 19.88 2660 3.25 3.59 3.42 0.17 -2.26 19.70 19.88 21.69 21.10 19.69											
2460 3.35 3.38 3.36 0.02 -0.94 19.94 21.95 23.91 22.00 20.09 2500 3.34 3.41 3.37 0.04 -1.10 19.94 21.65 23.56 21.91 20.12 2540 3.31 3.46 3.38 0.08 -1.34 19.84 21.24 23.15 21.61 20.10 2580 3.30 3.50 3.40 0.10 -1.64 19.86 20.85 22.79 21.33 19.97 2620 3.27 3.54 3.40 0.14 -1.85 19.81 20.37 22.19 21.12 19.88 2660 3.25 3.59 3.42 0.17 -2.26 19.70 19.88 21.69 21.10 19.69											20.13
2540 3.31 3.46 3.38 0.08 -1.34 19.84 21.24 23.15 21.61 20.10 2580 3.30 3.50 3.40 0.10 -1.64 19.86 20.85 22.79 21.33 19.97 2620 3.27 3.54 3.40 0.14 -1.85 19.81 20.37 22.19 21.12 19.88 2660 3.25 3.59 3.42 0.17 -2.26 19.70 19.88 21.69 21.10 19.69								21.95		22.00	
2580 3.30 3.50 3.40 0.10 -1.64 19.86 20.85 22.79 21.33 19.97 2620 3.27 3.54 3.40 0.14 -1.85 19.81 20.37 22.19 21.12 19.88 2660 3.25 3.59 3.42 0.17 -2.26 19.70 19.88 21.69 21.10 19.69											
2620 3.27 3.54 3.40 0.14 -1.85 19.81 20.37 22.19 21.12 19.88 2660 3.25 3.59 3.42 0.17 -2.26 19.70 19.88 21.69 21.10 19.69											
2660 3.25 3.59 3.42 0.17 -2.26 19.70 19.88 21.69 21.10 19.69											
2.00 0.20 0.00 0.70 0.21 72.01 18.00 18.40 21.02 20.84 18.00											
2740 3.19 3.70 3.44 0.26 -2.83 19.50 18.99 21.09 20.65 19.61											
2780 3.17 3.76 3.45 0.30 -3.24 19.42 18.53 20.74 20.46 19.37											
2820 3.14 3.82 3.47 0.34 -3.42 19.27 18.23 20.67 20.43 19.24											

QCH-272+

Typical Performance Data

Test Conditions: Input Power =+5 dBm @Temperature = +105°C, Configuration A

Freq.		Total Loss ¹		Amp. Unbal.	Phase Unbal.	Isolation		Returi	n Loss	
(MHz)		(dB)		(±dB)	(deg)	(dB)		(d	В)	
	Sum-Port 1	Sum-Port 2	Avg	(half P-P)	(Rel. to 90°)	Port 1 - Port 2	Sum	Port 1	Port 2	Iso
700	2.54	3.87	3.15	0.67	-0.21	33.15	-34.38	-34.97	-32.07	-34.06
740	2.67	3.71	3.16	0.53	-0.20	33.61	-36.21	-36.88	-33.17	-35.38
780	2.78	3.57	3.16	0.40	-0.23	34.10	-36.68	-38.71	-33.26	-36.61
820	2.89	3.46	3.17	0.29	-0.26	34.53	-37.16	-40.98	-33.34	-37.69
860	2.99	3.36	3.17	0.19	-0.23	35.17	-37.70	-43.29	-33.90	-38.75
900 940	3.07 3.15	3.28 3.21	3.17 3.18	0.11 0.04	-0.31 -0.29	35.51 36.31	-37.65 -38.21	-42.54 -41.77	-33.89 -34.18	-40.42 -41.72
980	3.15	3.21 3.16	3.18	0.04	-0.29	37.03	-38.22	-39.97	-34.16	-41.72 -42.75
1020	3.28	3.12	3.20	0.08	-0.33	37.88	-37.38	-37.76	-33.98	-43.82
1060	3.32	3.08	3.20	0.12	-0.31	38.30	-36.48	-36.18	-34.39	-44.54
1100	3.36	3.05	3.20	0.15	-0.33	39.24	-36.03	-34.79	-34.55	-45.13
1140	3.40	3.04	3.22	0.18	-0.31	40.48	-36.51	-33.69	-35.00	-47.00
1180	3.41	3.03	3.22	0.19	-0.30	41.32	-36.34	-32.65	-35.63	-46.77
1220	3.43	3.02	3.22	0.20	-0.36	42.83	-35.98	-31.66	-35.82	-45.08
1260	3.45	3.02	3.23	0.21	-0.33	44.15	-35.38	-30.63	-35.87	-45.24
1300	3.45	3.03	3.23	0.21	-0.27	46.11	-35.06	-29.98	-35.73	-44.08
1340 1380	3.45 3.45	3.04 3.05	3.24 3.25	0.20 0.20	-0.36 -0.34	46.30 47.97	-35.52 -35.15	-29.33 -28.65	-34.94 -33.80	-43.13 -42.66
1420	3.44	3.05	3.25	0.20	-0.34	46.02	-34.48	-28.36	-32.76	-42.86 -40.81
1460	3.43	3.09	3.26	0.17	-0.36	44.04	-33.92	-28.02	-31.23	-38.17
1500	3.42	3.11	3.26	0.15	-0.37	41.90	-33.23	-27.67	-29.84	-37.00
1540	3.41	3.14	3.27	0.13	-0.41	38.97	-32.83	-27.45	-28.40	-35.19
1580	3.41	3.15	3.28	0.12	-0.41	37.81	-32.56	-27.10	-27.67	-33.92
1620	3.39	3.18	3.28	0.10	-0.43	36.08	-31.88	-27.00	-26.59	-33.34
1660	3.38	3.21	3.29	0.08	-0.44	34.67	-31.35	-26.91	-25.60	-32.16
1700	3.37	3.22	3.29	0.07	-0.49	33.24	-30.72	-26.70	-24.75	-31.24
1740	3.36	3.24	3.30	0.06	-0.46	32.15	-30.16	-26.56	-23.97	-30.58
1780	3.36	3.28	3.32	0.04	-0.57	30.85	-29.26	-26.46	-23.42	-29.41
1820 1860	3.36 3.37	3.30 3.29	3.33 3.33	0.02 0.03	-0.65 -0.60	29.42 28.91	-28.50 -28.08	-26.02 -26.00	-22.80 -22.35	-28.91 -28.51
1900	3.36	3.30	3.33	0.03	-0.51	27.98	-27.30	-25.45	-21.99	-20.31
1940	3.36	3.31	3.33	0.02	-0.53	27.02	-26.51	-24.89	-21.74	-27.76
1980	3.36	3.32	3.34	0.03	-0.45	26.30	-25.73	-24.43	-21.45	-27.10
2020	3.40	3.35	3.37	0.02	-0.78	25.30	-25.34	-24.08	-21.33	-26.54
2060	3.42	3.36	3.39	0.03	-0.77	24.76	-25.18	-23.42	-21.24	-26.40
2100	3.42	3.31	3.36	0.06	-0.25	24.68	-24.44	-22.89	-21.35	-26.10
2140	3.42	3.32	3.37	0.05	-0.20	24.21	-23.91	-22.52	-21.36	-25.93
2180	3.46	3.34	3.40	0.06	-0.09	23.51	-23.58	-22.15	-21.59	-25.33
2220 2260	3.45 3.45	3.31 3.32	3.38 3.38	0.07 0.07	0.17 0.42	23.38 23.02	-23.14 -23.02	-21.58 -21.16	-21.72 -21.88	-25.35 -24.99
2300	3.44	3.35	3.39	0.07	0.42	22.62	-23.02	-21.16	-21.00	-24.99 -24.53
2340	3.43	3.37	3.40	0.03	0.61	22.43	-22.90	-20.95	-22.07 -22.25	-24.53 -24.71
2380	3.43	3.39	3.41	0.02	0.78	22.17	-22.45	-20.66	-22.42	-24.48
2420	3.41	3.42	3.41	0.01	0.89	21.86	-22.37	-20.43	-22.43	-23.93
2460	3.39	3.46	3.42	0.04	0.65	21.73	-22.56	-20.52	-22.68	-24.39
2500	3.40	3.48	3.44	0.05	0.60	21.41	-22.44	-20.36	-22.38	-23.78
2540	3.34	3.53	3.43	0.10	0.57	21.35	-21.97	-20.44	-21.78	-23.51
2580	3.31	3.59	3.45	0.14	0.47	21.17	-21.83		-21.50	-23.24
2620	3.33	3.62	3.47	0.15	-0.10	20.63	-21.50		-20.61	-22.25
2660	3.27	3.66	3.46	0.20	-0.36	20.57	-21.44		-20.06	-22.08
2700	3.24	3.72	3.47	0.25	-0.32	20.51	-21.36		-19.66	-21.68
2740 2780	3.18 3.16	3.80 3.86	3.48 3.50	0.32 0.37	-0.85 -1.32	20.33 20.03	-20.99 -21.05		-19.15 -19.02	-20.99 -20.87
2820	3.10	3.86	3.50 3.50	0.37	-1.32 -1.55	20.03 19.94	-21.05		-19.02	
2020	0.12	0.02	0.00	0.71	1.00	10.07	20.14	10.13	10.73	20.00

Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document are based on Mini-Circuits applicable established test performance otteria and measurement instructions.
 The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled

QCH-272+

Typical Performance Data

Test Conditions: Input Power =+5 dBm @Temperature = +105°C, Configuration B

Freq.		Total Loss ¹		Amp.	Phase	Isolation		Retur	n Loss	
				Unbal.	Unbal.					
(MHz)	Sum-Port 1	(dB) Sum-Port 2	Avg	(±dB)	(deg)	(dB) Port 1 - Port 2	Sum	(a Port 1	B)	loo
700				(half P-P)	(Rel. to 90°)				Port 2	Iso
700 740	2.56 2.69	3.86 3.70	3.16 3.17	0.65 0.50	0.03 0.06	33.40 33.75	34.06 35.38	32.07 33.17	34.97 36.88	34.38 36.21
780	2.80	3.56	3.16	0.38	0.03	34.20	36.61	33.26	38.71	36.68
820	2.92	3.45	3.18	0.26	0.03	34.54	37.69	33.34	40.98	37.16
860	3.01	3.35	3.18	0.17	0.07	35.12	38.75	33.90	43.29	37.70
900	3.10	3.27	3.18	0.08	0.03	35.56	40.42	33.89	42.54	37.65
940	3.18	3.20	3.19	0.01	0.04	36.11	41.72	34.18	41.77	38.21
980	3.24	3.14	3.19	0.06	0.06	36.77	42.75	34.16	39.97	38.22
1020	3.30	3.10	3.20	0.11	0.03	37.59	43.82	33.98	37.76	37.38
1060 1100	3.34 3.38	3.06 3.04	3.20 3.21	0.15 0.18	0.06 0.01	38.13 39.06	44.54 45.13	34.39 34.55	36.18 34.79	36.48 36.03
1140	3.42	3.04	3.21	0.16	0.01	40.23	45.13	35.00	33.69	36.51
1180	3.44	3.01	3.22	0.22	0.04	41.12	46.77	35.63	32.65	36.34
1220	3.46	3.01	3.23	0.23	0.02	42.42	45.08	35.82	31.66	35.98
1260	3.47	3.01	3.23	0.24	0.04	44.15	45.24	35.87	30.63	35.38
1300	3.48	3.02	3.24	0.24	0.02	45.97	44.08	35.73	29.98	35.06
1340	3.48	3.03	3.25	0.23	-0.05	47.17	43.13	34.94	29.33	35.52
1380	3.47	3.04	3.25	0.23	-0.05	49.29	42.66	33.80	28.65	35.15
1420	3.46	3.06	3.26	0.21	-0.12	47.58	40.81	32.76	28.36	34.48
1460 1500	3.46 3.45	3.08 3.10	3.27 3.27	0.20 0.18	-0.18 -0.22	45.61 43.20	38.17 37.00	31.23 29.84	28.02	33.92 33.23
1540	3.44	3.10	3.28	0.16	-0.22 -0.32	39.97	35.19	28.40	27.67 27.45	32.83
1580	3.44	3.13	3.28	0.17	-0.35	38.33	33.92	27.67	27.43	32.56
1620	3.42	3.16	3.29	0.14	-0.37	36.64	33.34	26.59	27.00	31.88
1660	3.41	3.18	3.29	0.12	-0.41	34.99	32.16	25.60	26.91	31.35
1700	3.41	3.21	3.31	0.11	-0.55	33.59	31.24	24.75	26.70	30.72
1740	3.40	3.22	3.31	0.10	-0.54	32.49	30.58	23.97	26.56	30.16
1780	3.40	3.24	3.32	0.09	-0.60	31.04	29.41	23.42	26.46	29.26
1820	3.41 3.41	3.26	3.33	0.08	-0.64	29.63 28.93	28.91	22.80	26.02	28.50
1860 1900	3.41	3.26 3.26	3.33 3.33	0.08 0.08	-0.65 -0.58	28.93 28.04	28.51 27.73	22.35 21.99	26.00 25.45	28.08 27.30
1940	3.41	3.27	3.34	0.08	-0.60	27.01	27.73	21.74	24.89	26.51
1980	3.42	3.28	3.35	0.08	-0.53	26.23	27.10	21.45	24.43	25.73
2020	3.45	3.33	3.39	0.07	-0.78	25.25	26.54	21.33	24.08	25.34
2060	3.47	3.32	3.39	0.08	-0.76	24.69	26.40	21.24	23.42	25.18
2100	3.47	3.27	3.37	0.11	-0.35	24.65	26.10	21.35	22.89	24.44
2140	3.47	3.28	3.37	0.10	-0.20	24.11	25.93	21.36	22.52	23.91
2180	3.49	3.31	3.40	0.10	-0.22	23.45	25.33	21.59	22.15	23.58 23.14
2220 2260	3.48 3.47	3.29 3.30	3.38 3.38	0.10 0.09	0.17 0.23	23.35 22.99	25.35 24.99	21.72 21.88	21.58 21.16	23.14 23.02
2300	3.47	3.33	3.40	0.09	0.23	22.61	24.53	22.07	20.95	22.96
2340	3.45	3.34	3.39	0.06	0.29	22.42	24.71	22.25	20.84	22.61
2380	3.45	3.38	3.41	0.04	0.29	22.17	24.48	22.42	20.66	22.45
2420	3.43	3.41	3.42	0.02	0.24	21.85	23.93	22.43	20.43	22.37
2460	3.42	3.47	3.44	0.03	0.14	21.74	24.39	22.68	20.52	22.56
2500	3.42	3.47	3.44	0.02	-0.05	21.42	23.78	22.38	20.36	22.44
2540	3.37	3.53	3.45	0.08	-0.18	21.37	23.51	21.78	20.44	21.97
2580	3.35	3.55	3.45	0.10	-0.68	21.20	23.24	21.50	20.40	21.83
2620	3.36	3.58	3.47	0.11	-0.84 1.16	20.64	22.25	20.61 20.06	20.21	21.50
2660 2700	3.32 3.30	3.66 3.72	3.49 3.50	0.17 0.20	-1.16 -1.36	20.59 20.53	22.08 21.68	19.66	20.49 20.34	21.44 21.36
2740	3.24	3.72	3.50	0.20	-1.88	20.36	20.99	19.00	20.34	20.99
2780	3.23	3.84	3.52	0.30	-2.23	20.03	20.87	19.02	20.09	21.05
2820	3.19	3.90	3.53	0.35	-2.58	19.95	20.50	18.49	19.79	20.74
	I							<u> </u>		

Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document are based on Mini-Circuits applicable established test performance otteria and measurement instructions.
 The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled

QCH-272+

Typical Performance Data

Test Conditions: Input Power =+5 dBm @Temperature = +105°C, Configuration C

Freq.		Total Loss ¹		Amp. Unbal.	Phase Unbal.	Isolation		Retur	n Loss	
(MHz)		(dB)		(±dB)	(deg)	(dB)		(d	В)	
	Sum-Port 1	Sum-Port 2	Avg	(half P-P)	(Rel. to 90°)	Port 1 - Port 2	Sum	Port 1	Port 2	Iso
700	2.54	3.86	3.15	0.67	0.34	32.12	34.97	34.38	34.06	32.07
740	2.67	3.70	3.15	0.52	0.37	32.58	36.88	36.21	35.38	33.17
780	2.78	3.56	3.15	0.39	0.36	32.93	38.71	36.68	36.61	33.26
820 860	2.90 2.99	3.45 3.35	3.17 3.17	0.28 0.18	0.36 0.44	33.19 33.57	40.98 43.29	37.16 37.70	37.69 38.75	33.34 33.90
900	3.08	3.27	3.17	0.10	0.44	33.53	42.54	37.70	40.42	33.89
940	3.15	3.20	3.17	0.02	0.44	33.77	41.77	38.21	41.72	34.18
980	3.22	3.14	3.18	0.04	0.48	33.95	39.97	38.22	42.75	34.16
1020	3.28	3.10	3.19	0.09	0.48	34.12	37.76	37.38	43.82	33.98
1060	3.32	3.06	3.19	0.13	0.53	34.30	36.18	36.48	44.54	34.39
1100	3.36	3.04	3.20	0.16	0.50	34.51	34.79	36.03	45.13	34.55
1140 1180	3.40 3.41	3.02 3.01	3.21 3.21	0.19 0.20	0.55 0.60	34.66 35.28	33.69 32.65	36.51 36.34	47.00 46.77	35.00 35.63
1220	3.43	3.01	3.21	0.20	0.56	35.42	31.66	35.98	45.08	35.82
1260	3.44	3.01	3.22	0.22	0.60	35.28	30.63	35.38	45.24	35.87
1300	3.45	3.01	3.22	0.22	0.63	35.28	29.98	35.06	44.08	35.73
1340	3.46	3.03	3.24	0.22	0.58	34.84	29.33	35.52	43.13	34.94
1380	3.45	3.04	3.24	0.21	0.63	34.39	28.65	35.15	42.66	33.80
1420	3.44	3.06	3.25	0.19	0.59	33.84	28.36	34.48	40.81	32.76
1460	3.43 3.42	3.07 3.09	3.25	0.18	0.57 0.56	32.83 31.71	28.02 27.67	33.92 33.23	38.17	31.23 29.84
1500 1540	3.42 3.41	3.12	3.25 3.26	0.16 0.14	0.50	30.59	27.45	32.83	37.00 35.19	28.40
1580	3.40	3.12	3.26	0.14	0.48	29.76	27.43	32.56	33.92	27.67
1620	3.39	3.16	3.27	0.12	0.48	28.74	27.00	31.88	33.34	26.59
1660	3.38	3.18	3.28	0.10	0.47	27.85	26.91	31.35	32.16	25.60
1700	3.37	3.20	3.28	0.09	0.33	26.94	26.70	30.72	31.24	24.75
1740	3.36	3.21	3.28	0.07	0.37	26.09	26.56	30.16	30.58	23.97
1780 1820	3.36 3.36	3.24 3.26	3.30 3.31	0.06 0.05	0.34 0.18	25.24 24.62	26.46 26.02	29.26 28.50	29.41 28.91	23.42 22.80
1860	3.36	3.26	3.31	0.05	0.16	24.04	26.02	28.08	28.51	22.35
1900	3.36	3.26	3.31	0.05	0.33	23.38	25.45	27.30	27.73	21.99
1940	3.37	3.27	3.32	0.05	0.30	22.82	24.89	26.51	27.26	21.74
1980	3.37	3.28	3.32	0.04	0.39	22.28	24.43	25.73	27.10	21.45
2020	3.40	3.33	3.36	0.04	0.05	21.65	24.08	25.34	26.54	21.33
2060	3.43	3.32	3.37	0.05	0.10	21.41	23.42	25.18	26.40	21.24
2100 2140	3.44 3.43	3.27 3.28	3.35 3.35	0.08 0.07	0.53 0.66	21.22 20.95	22.89 22.52	24.44 23.91	26.10 25.93	21.35 21.36
2180	3.47	3.31	3.39	0.08	0.67	20.61	22.15	23.58	25.33	21.59
2220	3.46	3.29	3.37	0.08	1.04	20.61	21.58	23.14	25.35	21.72
2260	3.46	3.30	3.38	0.08	1.22	20.46	21.16	23.02	24.99	21.88
2300	3.46	3.33	3.39	0.06	1.40	20.27	20.95	22.96	24.53	22.07
2340	3.44	3.35	3.39	0.04	1.38	20.24	20.84	22.61	24.71	22.25
2380 2420	3.44 3.43	3.38 3.41	3.41 3.42	0.03 0.00	1.46 1.39	20.16 20.00	20.66 20.43	22.45 22.37	24.48 23.93	22.42 22.43
2420	3.43 3.40	3.41	3.42	0.00	1.39	20.00	20.43	22.56	23.93	22.43
2500	3.41	3.47	3.44	0.04	1.26	19.93	20.32	22.44	23.78	22.38
2540	3.35	3.53	3.44	0.09	1.08	20.02	20.44	21.97	23.51	21.78
2580	3.32	3.56	3.44	0.12	0.70	20.12	20.40	21.83	23.24	21.50
2620	3.34	3.58	3.46	0.13	0.59	19.68	20.21	21.50	22.25	20.61
2660	3.28	3.66	3.47	0.20	0.28	19.77	20.49	21.44	22.08	20.06
2700	3.25	3.71	3.47	0.24	0.14 -0.47	19.71 19.55	20.34	21.36 20.99	21.68 20.99	19.66 19.15
2740 2780	3.18 3.16	3.78 3.84	3.47 3.49	0.31 0.35	-0.47 -0.83	19.55	20.20 20.09	20.99	20.99	19.15
2820	3.10	3.90	3.49	0.39	-0.65 -1.15	19.21	19.79	20.74	20.50	18.49
	-	00					1 0			

QCH-272+


Typical Performance Data


Test Conditions: Input Power =+5 dBm @Temperature = +105°C, Configuration D

Freq.		Total Loss ¹		Amp.	Phase	Isolation		Returi	n Loss	
				Unbal.	Unbal.					
(MHz)	Sum-Port 1	(dB) Sum-Port 2	Avg	(±dB) (half P-P)	(deg) (Rel. to 90°)	(dB) Port 1 - Port 2	Sum	Port 1	B) Port 2	Iso
700	2.56	3.88	3.17	0.66	-0.51	31.95	32.07	34.06	34.38	34.97
700 740	2.50	3.72	3.17	0.66	-0.51 -0.51	32.51	33.17	35.38	36.21	36.88
780	2.81	3.58	3.18	0.39	-0.57	32.86	33.26	36.61	36.68	38.71
820	2.92	3.47	3.19	0.27	-0.63	33.15	33.34	37.69	37.16	40.98
860	3.02	3.37	3.19	0.18	-0.60	33.62	33.90	38.75	37.70	43.29
900	3.10	3.29	3.19	0.10	-0.68	33.63	33.89	40.42	37.65	42.54
940	3.18	3.22	3.20	0.02	-0.71	33.88	34.18	41.72	38.21	41.77
980	3.25	3.16	3.20	0.04	-0.72	34.07	34.16	42.75	38.22	39.97
1020 1060	3.31 3.35	3.13 3.09	3.22 3.22	0.09 0.14	-0.80 -0.76	34.39 34.50	33.98 34.39	43.82 44.54	37.38 36.48	37.76 36.18
1100	3.39	3.09	3.22	0.14	-0.76 -0.82	34.50 34.42	34.55	44.54	36.48	36.18
1140	3.43	3.04	3.23	0.17	-0.84	34.50	35.00	47.00	36.51	33.69
1180	3.45	3.03	3.23	0.21	-0.83	35.32	35.63	46.77	36.34	32.65
1220	3.47	3.03	3.24	0.22	-0.90	35.16	35.82	45.08	35.98	31.66
1260	3.48	3.03	3.25	0.23	-0.89	34.52	35.87	45.24	35.38	30.63
1300	3.49	3.04	3.26	0.23	-0.90	34.32	35.73	44.08	35.06	29.98
1340	3.49	3.06	3.27	0.22	-1.00	34.36	34.94	43.13	35.52	29.33
1380	3.48	3.06	3.26	0.21	-0.99	33.72	33.80	42.66	35.15	28.65
1420	3.47	3.09	3.28	0.20	-1.05	32.68	32.76	40.81	34.48	28.36
1460 1500	3.47 3.45	3.10 3.12	3.28 3.28	0.19 0.17	-1.10 -1.16	31.73 31.16	31.23 29.84	38.17 37.00	33.92 33.23	28.02 27.67
1540	3.45	3.12	3.20	0.17	-1.10	30.11	28.40	35.19	32.83	27.67
1580	3.44	3.17	3.30	0.13	-1.23	29.14	27.67	33.92	32.56	27.43
1620	3.43	3.20	3.31	0.12	-1.26	28.31	26.59	33.34	31.88	27.00
1660	3.42	3.22	3.32	0.10	-1.34	27.56	25.60	32.16	31.35	26.91
1700	3.42	3.24	3.33	0.10	-1.37	26.89	24.75	31.24	30.72	26.70
1740	3.40	3.26	3.33	0.08	-1.36	25.79	23.97	30.58	30.16	26.56
1780	3.41	3.29	3.35	0.07	-1.50	24.93	23.42	29.41	29.26	26.46
1820	3.42	3.32	3.37	0.06	-1.48	24.49	22.80	28.91	28.50	26.02
1860	3.42	3.31	3.36	0.06	-1.49	24.03	22.35 21.99	28.51	28.08	26.00
1900 1940	3.42 3.42	3.31 3.32	3.36 3.37	0.06 0.05	-1.43 -1.41	23.37 22.74	21.99	27.73 27.26	27.30 26.51	25.45 24.89
1940	3.44	3.32	3.38	0.05	-1.41	22.74	21.74	27.20	25.73	24.43
2020	3.46	3.37	3.41	0.05	-1.60	21.80	21.33	26.54	25.34	24.08
2060	3.48	3.37	3.42	0.06	-1.59	21.52	21.24	26.40	25.18	23.42
2100	3.48	3.32	3.40	0.09	-1.13	21.29	21.35	26.10	24.44	22.89
2140	3.48	3.33	3.40	0.08	-1.03	21.02	21.36	25.93	23.91	22.52
2180	3.50	3.35	3.42	0.08	-0.91	20.75	21.59	25.33	23.58	22.15
2220	3.49	3.33	3.41	0.09	-0.67	20.74	21.72	25.35	23.14	21.58
2260	3.48	3.33	3.40	0.08	-0.51	20.51	21.88	24.99	23.02	21.16
2300 2340	3.48 3.46	3.36 3.38	3.42 3.42	0.06 0.05	-0.40 -0.37	20.30 20.27	22.07 22.25	24.53 24.71	22.96 22.61	20.95 20.84
2340	3.46 3.46	3.40	3.42	0.05	-0.37 -0.34	20.27	22.25	24.71	22.61	20.84
2420	3.44	3.44	3.44	0.03	-0.34	20.19	22.42	23.93	22.43	20.43
2460	3.43	3.47	3.45	0.02	-0.58	20.04	22.43	24.39	22.56	20.52
2500	3.43	3.50	3.46	0.03	-0.68	19.93	22.38	23.78	22.44	20.36
2540	3.38	3.54	3.46	0.08	-0.70	20.02	21.78	23.51	21.97	20.44
2580	3.36	3.61	3.48	0.12	-0.89	20.06	21.50	23.24	21.83	20.40
2620	3.37	3.64	3.50	0.13	-1.52	19.71	20.61	22.25	21.50	20.21
2660	3.33	3.68	3.50	0.18	-1.83	19.79	20.06	22.08	21.44	20.49
2700	3.31	3.74	3.52	0.21	-1.81	19.72	19.66	21.68	21.36	20.34
2740	3.25	3.82	3.53	0.28	-2.20	19.62	19.15	20.99	20.99	20.20
2780 2820	3.24 3.20	3.89 3.94	3.55 3.55	0.32 0.37	-2.72 -2.98	19.61 19.34	19.02 18.49	20.87 20.50	21.05	20.09 19.79
2020	3.20	3.94	ა.ეე	0.37	-2.90	19.34	10.49	20.50	20.74	19.79


Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document are based on Mini-Circuits applicable established test performance otteria and measurement instructions.
 The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled


Typical Performance Graphs (Configuration A)







Typical Performance Curves (Configuration B)







Typical Performance Curves (Configuration C)







Typical Performance Curves (Configuration D)







Typical Performance Curves (VSWR at Configuration A)










Case Style

PQ

Outline Dimensions

PQ2181



CASE#	A	В	С	D	Е	F	G	Н	J	K	L	M	N	P	WT. GRAMS
PQ2181	1.800 (45.72)		.190 (4.83)	.080 (2.03)	.140 (3.56)	.013 (0.33)	.040 (1.02)		1.810 (45.97)	.085 (2.16)	.040 (1.02)	.015 (0.38)	1.560 (39.62)	.410 (10.41)	1.0

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .010

Notes:

- 1. Base material: Printed wiring laminate.
- 2. Termination finish:

For RoHS Cases, all models (+) suffix: 2-5 $\mu inch$ (.05-.13 microns) Immersion Gold.

-G TYP

For RoHS-5 Cases, all models no (+) suffix: Tin-Lead plate.



INTERNET http://www.minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F120

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices p	er Reel
			Small	20
			quantity	50
72	16	13	standards	100
			(see note)	200
			Standard	500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET http://www.minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION

		REVISIONS			
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M155012	NEW RELEASE (FROM RAVON)	09/16	GF	YB
A	M163158	ADD TRACE CUTOUTS	07/17	HH	YB
A	R92310	ADD TRACE CUTOUTS	07/17	HH	YB

SUGGESTED MOUNTING CONFIGURATION FOR PQ2181 CASE STYLE 08DC08 PIN CONNECTION, 50 OHM



NOTES:

- 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4003C WITH DIELECTRIC THICKNESS. .032"±.003". COPPER: 1 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- 3. CUTOUTS IN RF LINES ARE REQUIRED TO ACHIEVE SPECIFIED ISOLATION.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE	l ——			• 4 ®		
DIMENSIONS ARE IN INCHES	DRAWN	GF (RAVON)	14 SEP 16		Min	i-Circu	its.	13 Neptur	ne Avenue NY 11235
TOLERANCES ON: 2 PL DECIMALS ±	CHECKED	HH (RAVON)	14 SEP 16		Т			Brooklyn	NI 11235
3 PL DECIMALS ± .005	APPROVED	YB (RAVON)	14 SEP 16		PΙ.	08DC08,	P021	81	
FRACTIONS ±					т 11,	oobcoo,	I &~I	O I	
1111	Mini-Circuits ® This document and its contents are the property of mini-circuits.					TB - 884 +			
EXCEPT FOR USE EXPRESSLY GRANTED AND THE UNITED STATES GOVERNMENT	, IN WRITING, T	TO ITS VENDORS, VE	NDEE	SIZE	CODE IDENT	DRAWING NO:			REV:
DESIGN, USE , MANUFACTURING AND I THESE CONTENTS SHALL NOT BE USEI	REPRODUCTION F D, DUPLICATED (RIGHTS THERETO. OR DISCLOSED TO AI	NY OUTSIDE	A	15542	98-PL	-480		A
PARTY, IN WHOLE OR IN PART, WITHO				FILE: O	8PL480(A)	SCALE: 2.5:1	SHEET:	1	OF 1
	ASHEETA1.D	WG REV:A DA	TE:01/12/95	<u> </u>	OF L4OU(A)	2.5:1		T	Or I







All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105° C Case Environment	Individual Model Data Sheet
Storage Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (high Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

ENV02T8 Rev: OR

06/14/16

M155459 File: ENV02T8.pdf

This document and its contents are the property of Mini-Circuits.