



STRIPLINE SURFACE MOUNT

2 Way 90° Power Splitter

QCH-451+

50Ω 2 Way-90° 225 to 450 MHz 250W

KEY FEATURES

- High power handling, up to 250W
- Wide bandwidth
- Excellent Amplitude Unbalance, $\pm 0.25\text{dB}$


APPLICATIONS

- Balanced Amplifiers
- I & Q Modulators
- Defense and Military



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits new 2-way 90° power splitter, QCH-451+ capable of handling up to 250W with amplitude unbalance of $\pm 0.25\text{ dB}$ typ and phase unbalance of $\pm 1.4\text{ deg. typ}$. Operating over a frequency range of 225 to 450 MHz, the outstanding phase and amplitude unbalance make this component a versatile building block for use in a variety of systems and sub-system designs from balanced amplifiers and antenna feeds to military applications and more. The splitter is fabricated using laminated PCB process (1.26 x 0.5 x 0.088") and includes wrap-around terminations for good solderability and easy visual inspection.

ELECTRICAL SPECIFICATIONS^{1,2} AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Frequency Range		225		450	MHz
Mainline Loss ³	225-450	-	0.2	0.3	dB
Isolation	225-450	21	27	-	dB
Phase Unbalance	225-450	-	± 1.4	± 5	dB
Amplitude Unbalance	225-450	-	± 0.25	± 0.5	dB
Return Loss	225-450	21	26	-	dB
Thermal Resistance ⁴	225-450	-	0.5	-	°C/W

1. Tested on Evaluation Board TB-914+. De-embedded to the device reference plane.
2. Symmetrical all ports are interchangeable. See Pad Configuration Table and S-Parameters for actual performance.
3. Does not include theoretical loss due to coupling. Nominal theoretical loss is 3 dB.
4. Thermal Resistance is defined as, example $(\theta_{jc}) = (\text{Hot Spot Temperature on DUT} - \text{Base Plate Temperature}) / \text{Input Power}$

ABSOLUTE MAXIMUM RATINGS⁵

Operating Case Temperature ⁶		-55 °C to +105 °C
Storage Temperature		-55 °C to +105 °C
Power Input	+85 °C case	250 W
	+95 °C case	230 W
	+105 °C case	200 W

5. Permanent damage may occur if any of these limits are exceeded.
6. Case temperature is defined as temperature on base plate.





STRIPLINE SURFACE MOUNT

2 Way 90° Power Splitter


QCH-451+

50Ω 2 Way-90° 225 to 450 MHz 250W


TYPICAL PERFORMANCE GRAPHS

Data corresponds to Configuration A at +25°C unless specified otherwise.


QCH-451+
Total Loss (dB)




QCH-451+
Isolation (dB)



QCH-451+
Amplitude & Phase Unbalance



QCH-451+
Return Loss (dB)





STRIPLINE SURFACE MOUNT

2 Way 90° Power Splitter

QCH-451+

50Ω 2 Way-90° 225 to 450 MHz 250W

FUNCTIONAL DIAGRAM




Figure 1. QCH-451+ Functional Diagram

PAD DESCRIPTION/CONFIGURATION⁷

Function	Pad Number	Description
Input	1	Connects to RF Input Port
Output	2	Connects to RF Output Port
Coupled Forward	4	Connects to Coupled Forward Port
Coupled Reverse	3	Connects to Coupled Reverse Port
Ground	5	Connects to Ground

Configuration	Sum	Isolation	Port 1 (0°)	Port 2 (90°)
A	1	2	3	4
B	2	1	4	3
C	3	4	1	2
D	4	3	2	1

7. Model is symmetrical and all ports are interchangeable, see Port Function Description/Configuration table for details and S-Parameters for actual performance.

SUGGESTED PCB LAYOUT (PL-529)





Figure 2. Suggested PCB Layout PL-529

CASE STYLE DRAWING (PQ2185-1)



NOTES:

1. Base material: Printed wiring laminate.
2. Termination finish: 2-5 μinch (.05-.13 microns) Immersion Gold.
3. Weight: 4.5 grams
4. Marking may contain other features or characters for internal lot control.

PRODUCT MARKING*: QCH-451+

*Marking may contain other features or characters for internal lot control.



STRIPLINE SURFACE MOUNT

2 Way 90° Power Splitter

QCH-451+

50Ω 2 Way-90° 225 to 450 MHz 250W

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD.

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs S-Parameter (S4P Files) Data Set (.zip file) De-embedded to device pads
Case Style	PQ2185-1 Lead Finish: 2-5 inch (0.05-0.13 microns) Immersion Gold.
RoHS Status	Compliant
Tape and Reel	F118
Suggested Layout for PCB Design	PL-529
Evaluation Board	TB-914+
	Gerber File
Environmental Rating	ENV02T8

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



2-Way 90° Power Splitter/Combiner

QCH-451+

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = -55°C, Configuration A.

Freq. (MHz)	Total Loss*			Amp. Unb. (±dB) Half P-P	Ph. Unb. (deg) Rel. to 90°	Isolation (dB) Port1-Port2	Return Loss (dB)			
	Sum-Port 1	Sum-Port 2	Average				Sum	Port 1	Port 2	Iso
150	-1.83	-4.91	-3.64	1.54	-0.23	-27.48	-29.06	-29.01	-28.46	-28.47
160	-1.99	-4.61	-3.49	1.31	-0.21	-27.31	-29.13	-29.22	-28.69	-28.52
170	-2.14	-4.35	-3.38	1.10	-0.19	-27.09	-29.08	-29.31	-28.82	-28.47
180	-2.28	-4.12	-3.30	0.91	-0.18	-26.88	-29.05	-29.43	-28.97	-28.38
190	-2.42	-3.92	-3.23	0.74	-0.16	-26.70	-28.96	-29.44	-29.01	-28.24
200	-2.55	-3.75	-3.19	0.59	-0.13	-26.53	-28.74	-29.35	-28.96	-28.08
210	-2.67	-3.59	-3.15	0.45	-0.12	-26.35	-28.58	-29.29	-28.94	-27.97
220	-2.79	-3.45	-3.13	0.32	-0.10	-26.33	-28.54	-29.31	-28.99	-27.96
230	-2.90	-3.33	-3.12	0.21	-0.07	-26.31	-28.56	-29.34	-29.04	-27.92
240	-2.99	-3.23	-3.11	0.11	-0.04	-26.29	-28.62	-29.40	-29.08	-27.93
250	-3.08	-3.14	-3.11	0.02	-0.02	-26.31	-28.80	-29.52	-29.21	-27.99
260	-3.16	-3.06	-3.11	0.07	-0.01	-26.46	-28.99	-29.65	-29.41	-28.12
270	-3.24	-3.00	-3.12	0.14	0.04	-26.54	-29.20	-29.69	-29.46	-28.32
280	-3.30	-2.94	-3.12	0.19	0.09	-26.68	-29.53	-29.93	-29.69	-28.56
290	-3.35	-2.90	-3.13	0.24	0.15	-26.93	-30.00	-30.24	-30.01	-28.90
300	-3.39	-2.87	-3.14	0.28	0.18	-27.17	-30.57	-30.74	-30.37	-29.29
310	-3.42	-2.84	-3.14	0.31	0.22	-27.43	-31.25	-31.28	-30.86	-29.74
320	-3.44	-2.83	-3.15	0.32	0.28	-27.75	-31.84	-31.71	-31.33	-30.16
330	-3.45	-2.82	-3.15	0.33	0.33	-28.05	-32.38	-32.13	-31.70	-30.56
340	-3.45	-2.83	-3.15	0.33	0.39	-28.33	-33.05	-32.74	-32.23	-31.09
350	-3.45	-2.84	-3.16	0.32	0.45	-28.67	-33.91	-33.52	-32.92	-31.74
360	-3.43	-2.86	-3.15	0.30	0.50	-29.10	-34.79	-34.40	-33.63	-32.35
370	-3.40	-2.90	-3.16	0.27	0.56	-29.44	-35.76	-35.38	-34.49	-33.01
380	-3.36	-2.94	-3.16	0.23	0.63	-29.76	-36.65	-36.06	-35.43	-33.58
390	-3.31	-2.99	-3.15	0.18	0.68	-30.14	-37.10	-36.52	-36.27	-34.09
400	-3.25	-3.06	-3.16	0.12	0.74	-30.35	-37.64	-37.00	-37.11	-34.72
410	-3.19	-3.13	-3.16	0.05	0.81	-30.55	-38.33	-37.58	-38.38	-35.52
420	-3.11	-3.22	-3.17	0.03	0.90	-30.86	-38.48	-37.76	-39.42	-36.09
430	-3.03	-3.32	-3.18	0.13	1.00	-31.03	-38.07	-37.36	-39.95	-36.46
440	-2.93	-3.44	-3.19	0.23	1.10	-30.91	-36.93	-36.31	-39.72	-36.38
450	-2.83	-3.58	-3.22	0.35	1.19	-30.70	-35.32	-34.89	-38.12	-35.65
460	-2.72	-3.74	-3.26	0.48	1.28	-30.30	-33.63	-33.33	-36.26	-34.61
470	-2.60	-3.91	-3.30	0.63	1.41	-29.71	-32.23	-32.01	-34.54	-33.33
480	-2.48	-4.11	-3.37	0.79	1.57	-29.04	-30.68	-30.50	-32.64	-31.78
490	-2.35	-4.34	-3.46	0.96	1.75	-28.23	-29.15	-29.05	-30.88	-30.21
500	-2.22	-4.60	-3.57	1.16	1.93	-27.25	-27.69	-27.61	-29.23	-28.75
510	-2.07	-4.90	-3.71	1.38	2.15	-26.20	-26.25	-26.20	-27.61	-27.23
520	-1.93	-5.23	-3.89	1.61	2.40	-25.20	-24.92	-24.91	-26.10	-25.81
530	-1.80	-5.62	-4.12	1.87	2.72	-24.25	-23.75	-23.73	-24.78	-24.57
540	-1.66	-6.05	-4.39	2.16	3.10	-23.29	-22.66	-22.59	-23.55	-23.38
550	-1.52	-6.55	-4.73	2.47	3.56	-22.37	-21.56	-21.50	-22.38	-22.26

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.

2-Way 90° Power Splitter/Combiner

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = -55°C, Configuration B.

Freq. (MHz)	Total Loss*			Amp. Unb.	Ph. Unb.	Isolation	Return Loss			
	Sum-Port 1	Sum-Port 2	Average	(±dB) Half P-P	(deg) Rel. to 90°	(dB) Port1-Port2	Sum	Port 1	Port 2	Iso
150	-1.82	-4.91	-3.63	1.53	-0.25	-27.39	-28.47	-28.46	-29.01	-29.06
160	-1.98	-4.61	-3.49	1.31	-0.22	-27.24	-28.52	-28.69	-29.22	-29.13
170	-2.13	-4.35	-3.38	1.10	-0.20	-27.01	-28.47	-28.82	-29.31	-29.08
180	-2.28	-4.12	-3.30	0.91	-0.18	-26.83	-28.38	-28.97	-29.43	-29.05
190	-2.42	-3.92	-3.23	0.74	-0.17	-26.66	-28.24	-29.01	-29.44	-28.96
200	-2.55	-3.75	-3.19	0.58	-0.14	-26.44	-28.08	-28.96	-29.35	-28.74
210	-2.67	-3.59	-3.15	0.44	-0.11	-26.24	-27.97	-28.94	-29.29	-28.58
220	-2.79	-3.45	-3.13	0.32	-0.09	-26.21	-27.96	-28.99	-29.31	-28.54
230	-2.90	-3.33	-3.12	0.20	-0.07	-26.20	-27.92	-29.04	-29.34	-28.56
240	-2.99	-3.23	-3.11	0.10	-0.04	-26.20	-27.93	-29.08	-29.40	-28.62
250	-3.08	-3.14	-3.11	0.01	-0.03	-26.24	-27.99	-29.21	-29.52	-28.80
260	-3.16	-3.06	-3.11	0.07	-0.03	-26.39	-28.12	-29.41	-29.65	-28.99
270	-3.23	-2.99	-3.11	0.14	0.03	-26.50	-28.32	-29.46	-29.69	-29.20
280	-3.30	-2.94	-3.12	0.20	0.08	-26.63	-28.56	-29.69	-29.93	-29.53
290	-3.35	-2.90	-3.13	0.24	0.13	-26.89	-28.90	-30.01	-30.24	-30.00
300	-3.39	-2.87	-3.14	0.28	0.17	-27.12	-29.29	-30.37	-30.74	-30.57
310	-3.42	-2.84	-3.14	0.31	0.20	-27.41	-29.74	-30.86	-31.28	-31.25
320	-3.44	-2.83	-3.15	0.33	0.26	-27.70	-30.16	-31.33	-31.71	-31.84
330	-3.45	-2.82	-3.15	0.34	0.31	-27.99	-30.56	-31.70	-32.13	-32.38
340	-3.45	-2.82	-3.15	0.34	0.37	-28.26	-31.09	-32.23	-32.74	-33.05
350	-3.45	-2.84	-3.16	0.33	0.42	-28.60	-31.74	-32.92	-33.52	-33.91
360	-3.43	-2.86	-3.15	0.31	0.47	-28.98	-32.35	-33.63	-34.40	-34.79
370	-3.40	-2.89	-3.15	0.28	0.53	-29.32	-33.01	-34.49	-35.38	-35.76
380	-3.36	-2.94	-3.16	0.24	0.60	-29.66	-33.58	-35.43	-36.06	-36.65
390	-3.31	-2.99	-3.15	0.19	0.66	-29.99	-34.09	-36.27	-36.52	-37.10
400	-3.25	-3.05	-3.15	0.13	0.71	-30.22	-34.72	-37.11	-37.00	-37.64
410	-3.19	-3.13	-3.16	0.06	0.77	-30.44	-35.52	-38.38	-37.58	-38.33
420	-3.11	-3.22	-3.17	0.03	0.85	-30.74	-36.09	-39.42	-37.76	-38.48
430	-3.02	-3.32	-3.17	0.12	0.94	-30.88	-36.46	-39.95	-37.36	-38.07
440	-2.93	-3.44	-3.19	0.23	1.03	-30.82	-36.38	-39.72	-36.31	-36.93
450	-2.82	-3.58	-3.22	0.35	1.11	-30.58	-35.65	-38.12	-34.89	-35.32
460	-2.71	-3.73	-3.25	0.48	1.20	-30.22	-34.61	-36.26	-33.33	-33.63
470	-2.60	-3.91	-3.30	0.62	1.33	-29.66	-33.33	-34.54	-32.01	-32.23
480	-2.48	-4.11	-3.37	0.79	1.48	-28.96	-31.78	-32.64	-30.50	-30.68
490	-2.35	-4.34	-3.46	0.96	1.65	-28.13	-30.21	-30.88	-29.05	-29.15
500	-2.21	-4.60	-3.57	1.16	1.83	-27.17	-28.75	-29.23	-27.61	-27.69
510	-2.07	-4.90	-3.71	1.37	2.04	-26.14	-27.23	-27.61	-26.20	-26.25
520	-1.93	-5.23	-3.89	1.61	2.29	-25.17	-25.81	-26.10	-24.91	-24.92
530	-1.79	-5.62	-4.11	1.87	2.59	-24.22	-24.57	-24.78	-23.73	-23.75
540	-1.65	-6.06	-4.39	2.16	2.97	-23.27	-23.38	-23.55	-22.59	-22.66
550	-1.51	-6.56	-4.73	2.47	3.40	-22.35	-22.26	-22.38	-21.50	-21.56

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.

2-Way 90° Power Splitter/Combiner

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = -55°C, Configuration C.

Freq. (MHz)	Total Loss*			Amp. Unb. (±dB) Half P-P	Ph. Unb. (deg) Rel. to 90°	Isolation (dB) Port1-Port2	Return Loss (dB)			
	Sum-Port 1	Sum-Port 2	Average				Sum	Port 1	Port 2	Iso
150	-1.82	-4.91	-3.63	1.54	-0.33	-27.51	-29.01	-29.06	-28.47	-28.46
160	-1.97	-4.61	-3.49	1.31	-0.31	-27.48	-29.22	-29.13	-28.52	-28.69
170	-2.12	-4.35	-3.38	1.10	-0.30	-27.40	-29.31	-29.08	-28.47	-28.82
180	-2.27	-4.12	-3.29	0.91	-0.30	-27.31	-29.43	-29.05	-28.38	-28.97
190	-2.41	-3.92	-3.23	0.74	-0.29	-27.23	-29.44	-28.96	-28.24	-29.01
200	-2.54	-3.75	-3.19	0.59	-0.27	-27.17	-29.35	-28.74	-28.08	-28.96
210	-2.66	-3.59	-3.15	0.45	-0.25	-27.04	-29.29	-28.58	-27.97	-28.94
220	-2.78	-3.45	-3.13	0.32	-0.23	-27.03	-29.31	-28.54	-27.96	-28.99
230	-2.89	-3.33	-3.12	0.21	-0.21	-27.01	-29.34	-28.56	-27.92	-29.04
240	-2.98	-3.23	-3.11	0.10	-0.18	-26.90	-29.40	-28.62	-27.93	-29.08
250	-3.07	-3.14	-3.11	0.02	-0.16	-26.87	-29.52	-28.80	-27.99	-29.21
260	-3.15	-3.06	-3.11	0.07	-0.16	-26.97	-29.65	-28.99	-28.12	-29.41
270	-3.22	-3.00	-3.11	0.14	-0.11	-27.02	-29.69	-29.20	-28.32	-29.46
280	-3.29	-2.94	-3.12	0.19	-0.07	-27.14	-29.93	-29.53	-28.56	-29.69
290	-3.34	-2.90	-3.13	0.24	-0.03	-27.35	-30.24	-30.00	-28.90	-30.01
300	-3.38	-2.86	-3.13	0.28	0.01	-27.58	-30.74	-30.57	-29.29	-30.37
310	-3.41	-2.84	-3.13	0.31	0.05	-27.76	-31.28	-31.25	-29.74	-30.86
320	-3.43	-2.83	-3.14	0.32	0.10	-28.06	-31.71	-31.84	-30.16	-31.33
330	-3.44	-2.82	-3.14	0.33	0.14	-28.30	-32.13	-32.38	-30.56	-31.70
340	-3.44	-2.83	-3.15	0.33	0.19	-28.59	-32.74	-33.05	-31.09	-32.23
350	-3.43	-2.84	-3.15	0.32	0.23	-28.89	-33.52	-33.91	-31.74	-32.92
360	-3.42	-2.86	-3.15	0.30	0.28	-29.32	-34.40	-34.79	-32.35	-33.63
370	-3.39	-2.89	-3.15	0.27	0.35	-29.67	-35.38	-35.76	-33.01	-34.49
380	-3.35	-2.94	-3.15	0.23	0.41	-30.08	-36.06	-36.65	-33.58	-35.43
390	-3.30	-2.99	-3.15	0.18	0.46	-30.45	-36.52	-37.10	-34.09	-36.27
400	-3.24	-3.05	-3.15	0.12	0.51	-30.78	-37.00	-37.64	-34.72	-37.11
410	-3.18	-3.13	-3.16	0.05	0.57	-31.03	-37.58	-38.33	-35.52	-38.38
420	-3.10	-3.22	-3.16	0.03	0.64	-31.44	-37.76	-38.48	-36.09	-39.42
430	-3.02	-3.32	-3.17	0.13	0.74	-31.66	-37.36	-38.07	-36.46	-39.95
440	-2.92	-3.44	-3.19	0.23	0.82	-31.62	-36.31	-36.93	-36.38	-39.72
450	-2.82	-3.58	-3.22	0.35	0.90	-31.41	-34.89	-35.32	-35.65	-38.12
460	-2.71	-3.73	-3.25	0.48	0.98	-31.05	-33.33	-33.63	-34.61	-36.26
470	-2.59	-3.91	-3.30	0.63	1.11	-30.43	-32.01	-32.23	-33.33	-34.54
480	-2.47	-4.11	-3.37	0.79	1.26	-29.78	-30.50	-30.68	-31.78	-32.64
490	-2.34	-4.34	-3.45	0.96	1.42	-28.95	-29.05	-29.15	-30.21	-30.88
500	-2.20	-4.60	-3.56	1.16	1.59	-27.91	-27.61	-27.69	-28.75	-29.23
510	-2.06	-4.90	-3.71	1.38	1.79	-26.82	-26.20	-26.25	-27.23	-27.61
520	-1.92	-5.24	-3.89	1.61	2.04	-25.80	-24.91	-24.92	-25.81	-26.10
530	-1.78	-5.62	-4.11	1.87	2.34	-24.79	-23.73	-23.75	-24.57	-24.78
540	-1.65	-6.06	-4.39	2.16	2.71	-23.78	-22.59	-22.66	-23.38	-23.55
550	-1.51	-6.56	-4.73	2.47	3.14	-22.80	-21.50	-21.56	-22.26	-22.38

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.

2-Way 90° Power Splitter/Combiner

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = -55°C, Configuration D.

Freq. (MHz)	Total Loss*			Amp. Unb.	Ph. Unb.	Isolation	Return Loss			
	Sum-Port 1	Sum-Port 2	Average	(±dB) Half P-P	(deg) Rel. to 90°	(dB) Port1-Port2	Sum	Port 1	Port 2	Iso
150	-1.83	-4.90	-3.63	1.54	-0.15	-27.63	-28.46	-28.47	-29.06	-29.01
160	-1.98	-4.60	-3.48	1.31	-0.11	-27.59	-28.69	-28.52	-29.13	-29.22
170	-2.13	-4.35	-3.38	1.10	-0.07	-27.48	-28.82	-28.47	-29.08	-29.31
180	-2.28	-4.12	-3.30	0.91	-0.05	-27.40	-28.97	-28.38	-29.05	-29.43
190	-2.42	-3.92	-3.23	0.74	-0.03	-27.32	-29.01	-28.24	-28.96	-29.44
200	-2.55	-3.74	-3.19	0.58	-0.01	-27.24	-28.96	-28.08	-28.74	-29.35
210	-2.68	-3.59	-3.16	0.44	0.02	-27.09	-28.94	-27.97	-28.58	-29.29
220	-2.79	-3.45	-3.13	0.32	0.04	-27.11	-28.99	-27.96	-28.54	-29.31
230	-2.90	-3.33	-3.12	0.20	0.08	-27.12	-29.04	-27.92	-28.56	-29.34
240	-3.00	-3.22	-3.11	0.10	0.11	-27.08	-29.08	-27.93	-28.62	-29.40
250	-3.09	-3.13	-3.11	0.01	0.14	-27.08	-29.21	-27.99	-28.80	-29.52
260	-3.17	-3.06	-3.12	0.07	0.14	-27.15	-29.41	-28.12	-28.99	-29.65
270	-3.24	-2.99	-3.12	0.14	0.20	-27.22	-29.46	-28.32	-29.20	-29.69
280	-3.30	-2.93	-3.12	0.20	0.25	-27.28	-29.69	-28.56	-29.53	-29.93
290	-3.35	-2.89	-3.13	0.24	0.31	-27.47	-30.01	-28.90	-30.00	-30.24
300	-3.39	-2.86	-3.13	0.28	0.34	-27.65	-30.37	-29.29	-30.57	-30.74
310	-3.42	-2.83	-3.14	0.31	0.39	-27.84	-30.86	-29.74	-31.25	-31.28
320	-3.45	-2.82	-3.15	0.33	0.45	-28.16	-31.33	-30.16	-31.84	-31.71
330	-3.46	-2.82	-3.15	0.34	0.51	-28.44	-31.70	-30.56	-32.38	-32.13
340	-3.46	-2.82	-3.15	0.34	0.57	-28.67	-32.23	-31.09	-33.05	-32.74
350	-3.45	-2.83	-3.15	0.32	0.63	-29.02	-32.92	-31.74	-33.91	-33.52
360	-3.43	-2.85	-3.15	0.31	0.69	-29.47	-33.63	-32.35	-34.79	-34.40
370	-3.40	-2.89	-3.15	0.28	0.76	-29.82	-34.49	-33.01	-35.76	-35.38
380	-3.36	-2.93	-3.15	0.24	0.83	-30.18	-35.43	-33.58	-36.65	-36.06
390	-3.31	-2.98	-3.15	0.19	0.90	-30.64	-36.27	-34.09	-37.10	-36.52
400	-3.26	-3.05	-3.16	0.13	0.95	-30.92	-37.11	-34.72	-37.64	-37.00
410	-3.19	-3.12	-3.16	0.06	1.03	-31.18	-38.38	-35.52	-38.33	-37.58
420	-3.11	-3.21	-3.16	0.03	1.12	-31.65	-39.42	-36.09	-38.48	-37.76
430	-3.03	-3.32	-3.18	0.12	1.22	-31.86	-39.95	-36.46	-38.07	-37.36
440	-2.93	-3.44	-3.19	0.23	1.32	-31.81	-39.72	-36.38	-36.93	-36.31
450	-2.83	-3.57	-3.22	0.35	1.42	-31.58	-38.12	-35.65	-35.32	-34.89
460	-2.72	-3.73	-3.25	0.48	1.52	-31.20	-36.26	-34.61	-33.63	-33.33
470	-2.60	-3.91	-3.30	0.62	1.65	-30.59	-34.54	-33.33	-32.23	-32.01
480	-2.48	-4.11	-3.37	0.78	1.82	-29.88	-32.64	-31.78	-30.68	-30.50
490	-2.35	-4.34	-3.46	0.96	2.00	-29.06	-30.88	-30.21	-29.15	-29.05
500	-2.21	-4.60	-3.57	1.16	2.18	-28.02	-29.23	-28.75	-27.69	-27.61
510	-2.07	-4.89	-3.70	1.37	2.41	-26.93	-27.61	-27.23	-26.25	-26.20
520	-1.93	-5.23	-3.89	1.61	2.68	-25.89	-26.10	-25.81	-24.92	-24.91
530	-1.79	-5.61	-4.11	1.87	3.00	-24.87	-24.78	-24.57	-23.75	-23.73
540	-1.65	-6.05	-4.38	2.15	3.38	-23.83	-23.55	-23.38	-22.66	-22.59
550	-1.52	-6.55	-4.73	2.47	3.84	-22.85	-22.38	-22.26	-21.56	-21.50

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.

2-Way 90° Power Splitter/Combiner

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = +25°C, Configuration A.

Freq. (MHz)	Total Loss*			Amp. Unb. (±dB) Half P-P	Ph. Unb. (deg) Rel. to 90°	Isolation (dB) Port1-Port2	Return Loss (dB)			
	Sum-Port 1	Sum-Port 2	Average				Sum	Port 1	Port 2	Iso
150	-1.83	-4.91	-3.64	1.55	-0.35	-25.98	-26.63	-26.58	-26.13	-26.03
160	-1.99	-4.61	-3.49	1.32	-0.30	-25.99	-26.77	-26.75	-26.28	-26.13
170	-2.14	-4.35	-3.38	1.11	-0.27	-25.98	-26.93	-26.88	-26.45	-26.27
180	-2.28	-4.12	-3.30	0.93	-0.24	-26.01	-27.21	-27.11	-26.67	-26.48
190	-2.42	-3.92	-3.23	0.76	-0.20	-26.10	-27.53	-27.39	-26.91	-26.70
200	-2.55	-3.75	-3.19	0.60	-0.15	-26.21	-27.81	-27.66	-27.12	-26.96
210	-2.67	-3.59	-3.15	0.46	-0.11	-26.30	-28.14	-28.03	-27.43	-27.28
220	-2.79	-3.45	-3.13	0.34	-0.07	-26.53	-28.55	-28.49	-27.84	-27.70
230	-2.90	-3.33	-3.12	0.22	-0.01	-26.72	-28.99	-28.91	-28.25	-28.08
240	-2.99	-3.23	-3.11	0.12	0.03	-26.86	-29.44	-29.38	-28.65	-28.46
250	-3.08	-3.14	-3.11	0.03	0.07	-27.04	-30.01	-29.91	-29.12	-28.88
260	-3.16	-3.06	-3.11	0.05	0.11	-27.33	-30.58	-30.45	-29.63	-29.33
270	-3.24	-3.00	-3.12	0.12	0.16	-27.56	-31.06	-31.00	-30.04	-29.78
280	-3.30	-2.94	-3.12	0.18	0.23	-27.80	-31.67	-31.67	-30.56	-30.22
290	-3.35	-2.90	-3.13	0.23	0.29	-28.12	-32.38	-32.37	-31.19	-30.73
300	-3.39	-2.87	-3.14	0.26	0.33	-28.39	-33.18	-33.26	-31.85	-31.35
310	-3.42	-2.84	-3.14	0.29	0.37	-28.67	-34.12	-34.25	-32.69	-31.99
320	-3.44	-2.83	-3.15	0.31	0.43	-29.05	-35.03	-35.21	-33.52	-32.59
330	-3.45	-2.82	-3.15	0.32	0.49	-29.43	-35.73	-36.18	-34.22	-33.15
340	-3.45	-2.83	-3.15	0.31	0.56	-29.76	-36.70	-37.49	-35.11	-33.82
350	-3.45	-2.84	-3.16	0.30	0.62	-30.14	-38.07	-39.14	-36.38	-34.73
360	-3.43	-2.86	-3.15	0.28	0.67	-30.58	-39.43	-40.95	-37.81	-35.75
370	-3.40	-2.90	-3.16	0.25	0.74	-30.95	-40.86	-43.00	-39.53	-36.79
380	-3.36	-2.94	-3.16	0.21	0.81	-31.36	-42.03	-44.05	-41.61	-37.76
390	-3.31	-2.99	-3.15	0.16	0.88	-31.82	-41.77	-43.45	-43.57	-38.49
400	-3.25	-3.06	-3.16	0.10	0.93	-32.01	-41.34	-41.95	-45.43	-39.24
410	-3.19	-3.13	-3.16	0.03	1.02	-32.10	-40.72	-40.12	-46.88	-39.97
420	-3.11	-3.22	-3.17	0.06	1.11	-32.24	-39.07	-38.07	-44.35	-39.56
430	-3.03	-3.32	-3.18	0.15	1.22	-32.19	-37.05	-35.99	-40.79	-38.38
440	-2.93	-3.44	-3.19	0.26	1.34	-31.79	-34.99	-34.15	-37.88	-36.69
450	-2.83	-3.58	-3.22	0.38	1.45	-31.21	-33.06	-32.41	-35.34	-34.84
460	-2.72	-3.74	-3.26	0.51	1.55	-30.43	-31.48	-30.85	-33.34	-33.19
470	-2.60	-3.91	-3.30	0.66	1.70	-29.57	-30.11	-29.49	-31.63	-31.63
480	-2.48	-4.11	-3.37	0.82	1.89	-28.67	-28.82	-28.19	-30.04	-30.11
490	-2.35	-4.34	-3.46	1.00	2.09	-27.77	-27.53	-26.95	-28.54	-28.67
500	-2.22	-4.60	-3.57	1.20	2.30	-26.79	-26.27	-25.76	-27.17	-27.36
510	-2.07	-4.90	-3.71	1.42	2.55	-25.76	-25.04	-24.62	-25.86	-26.05
520	-1.93	-5.23	-3.89	1.65	2.84	-24.78	-23.91	-23.55	-24.65	-24.82
530	-1.80	-5.62	-4.12	1.92	3.20	-23.87	-22.91	-22.58	-23.58	-23.77
540	-1.66	-6.05	-4.39	2.20	3.63	-22.96	-21.97	-21.63	-22.57	-22.72
550	-1.52	-6.55	-4.73	2.52	4.12	-22.11	-21.02	-20.73	-21.57	-21.74

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = +25°C, Configuration B.

Freq. (MHz)	Total Loss*			Amp. Unb.	Ph. Unb.	Isolation	Return Loss			
	Sum-Port 1	Sum-Port 2	Average	(±dB) Half P-P	(deg) Rel. to 90°	(dB) Port1-Port2	Sum	Port 1	Port 2	Iso
150	-1.82	-4.91	-3.63	1.54	-0.37	-25.91	-26.03	-26.13	-26.58	-26.63
160	-1.98	-4.61	-3.49	1.32	-0.33	-25.93	-26.13	-26.28	-26.75	-26.77
170	-2.13	-4.35	-3.38	1.11	-0.29	-25.91	-26.27	-26.45	-26.88	-26.93
180	-2.28	-4.12	-3.30	0.92	-0.26	-25.96	-26.48	-26.67	-27.11	-27.21
190	-2.42	-3.92	-3.23	0.75	-0.22	-26.07	-26.70	-26.91	-27.39	-27.53
200	-2.55	-3.75	-3.19	0.60	-0.17	-26.14	-26.96	-27.12	-27.66	-27.81
210	-2.67	-3.59	-3.15	0.46	-0.13	-26.21	-27.28	-27.43	-28.03	-28.14
220	-2.79	-3.45	-3.13	0.33	-0.08	-26.43	-27.70	-27.84	-28.49	-28.55
230	-2.90	-3.33	-3.12	0.22	-0.04	-26.62	-28.08	-28.25	-28.91	-28.99
240	-2.99	-3.23	-3.11	0.12	0.00	-26.78	-28.46	-28.65	-29.38	-29.44
250	-3.08	-3.14	-3.11	0.03	0.03	-26.98	-28.88	-29.12	-29.91	-30.01
260	-3.16	-3.06	-3.11	0.06	0.07	-27.25	-29.33	-29.63	-30.45	-30.58
270	-3.23	-2.99	-3.11	0.12	0.11	-27.52	-29.78	-30.04	-31.00	-31.06
280	-3.30	-2.94	-3.12	0.18	0.17	-27.75	-30.22	-30.56	-31.67	-31.67
290	-3.35	-2.90	-3.13	0.23	0.23	-28.08	-30.73	-31.19	-32.37	-32.38
300	-3.39	-2.87	-3.14	0.27	0.27	-28.34	-31.35	-31.85	-33.26	-33.18
310	-3.42	-2.84	-3.14	0.29	0.31	-28.65	-31.99	-32.69	-34.25	-34.12
320	-3.44	-2.83	-3.15	0.31	0.36	-29.01	-32.59	-33.52	-35.21	-35.03
330	-3.45	-2.82	-3.15	0.32	0.42	-29.37	-33.15	-34.22	-36.18	-35.73
340	-3.45	-2.82	-3.15	0.32	0.48	-29.68	-33.82	-35.11	-37.49	-36.70
350	-3.45	-2.84	-3.16	0.31	0.53	-30.05	-34.73	-36.38	-39.14	-38.07
360	-3.43	-2.86	-3.15	0.29	0.59	-30.45	-35.75	-37.81	-40.95	-39.43
370	-3.40	-2.89	-3.15	0.26	0.64	-30.82	-36.79	-39.53	-43.00	-40.86
380	-3.36	-2.94	-3.16	0.22	0.72	-31.24	-37.76	-41.61	-44.05	-42.03
390	-3.31	-2.99	-3.15	0.17	0.79	-31.64	-38.49	-43.57	-43.45	-41.77
400	-3.25	-3.05	-3.15	0.10	0.85	-31.86	-39.24	-45.43	-41.95	-41.34
410	-3.19	-3.13	-3.16	0.03	0.92	-31.96	-39.97	-46.88	-40.12	-40.72
420	-3.11	-3.22	-3.17	0.05	1.01	-32.10	-39.56	-44.35	-38.07	-39.07
430	-3.02	-3.32	-3.17	0.15	1.11	-32.01	-38.38	-40.79	-35.99	-37.05
440	-2.93	-3.44	-3.19	0.26	1.22	-31.69	-36.69	-37.88	-34.15	-34.99
450	-2.82	-3.58	-3.22	0.38	1.31	-31.09	-34.84	-35.34	-32.41	-33.06
460	-2.71	-3.73	-3.25	0.51	1.43	-30.35	-33.19	-33.34	-30.85	-31.48
470	-2.60	-3.91	-3.30	0.66	1.56	-29.51	-31.63	-31.63	-29.49	-30.11
480	-2.48	-4.11	-3.37	0.82	1.75	-28.58	-30.11	-30.04	-28.19	-28.82
490	-2.35	-4.34	-3.46	1.00	1.94	-27.68	-28.67	-28.54	-26.95	-27.53
500	-2.21	-4.60	-3.57	1.20	2.15	-26.71	-27.36	-27.17	-25.76	-26.27
510	-2.07	-4.90	-3.71	1.42	2.39	-25.70	-26.05	-25.86	-24.62	-25.04
520	-1.93	-5.23	-3.89	1.65	2.68	-24.75	-24.82	-24.65	-23.55	-23.91
530	-1.79	-5.62	-4.11	1.92	3.02	-23.84	-23.77	-23.58	-22.58	-22.91
540	-1.65	-6.06	-4.39	2.20	3.44	-22.95	-22.72	-22.57	-21.63	-21.97
550	-1.51	-6.56	-4.73	2.52	3.92	-22.09	-21.74	-21.57	-20.73	-21.02

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = +25°C, Configuration C.

Freq. (MHz)	Total Loss*			Amp. Unb.	Ph. Unb.	Isolation	Return Loss			
	Sum-Port 1	Sum-Port 2	Average	(±dB) Half P-P	(deg) Rel. to 90°	(dB) Port1-Port2	Sum	Port 1	Port 2	Iso
150	-1.82	-4.91	-3.63	1.54	-0.42	-26.02	-26.58	-26.63	-26.03	-26.13
160	-1.97	-4.61	-3.49	1.32	-0.38	-26.02	-26.75	-26.77	-26.13	-26.28
170	-2.12	-4.35	-3.38	1.11	-0.36	-26.01	-26.88	-26.93	-26.27	-26.45
180	-2.27	-4.12	-3.29	0.92	-0.33	-26.04	-27.11	-27.21	-26.48	-26.67
190	-2.41	-3.92	-3.23	0.75	-0.30	-26.12	-27.39	-27.53	-26.70	-26.91
200	-2.54	-3.75	-3.19	0.60	-0.26	-26.23	-27.66	-27.81	-26.96	-27.12
210	-2.66	-3.59	-3.15	0.46	-0.22	-26.33	-28.03	-28.14	-27.28	-27.43
220	-2.78	-3.45	-3.13	0.33	-0.17	-26.54	-28.49	-28.55	-27.70	-27.84
230	-2.89	-3.33	-3.12	0.22	-0.13	-26.72	-28.91	-28.99	-28.08	-28.25
240	-2.98	-3.23	-3.11	0.12	-0.08	-26.82	-29.38	-29.44	-28.46	-28.65
250	-3.07	-3.14	-3.11	0.03	-0.04	-27.00	-29.91	-30.01	-28.88	-29.12
260	-3.15	-3.06	-3.11	0.05	0.00	-27.32	-30.45	-30.58	-29.33	-29.63
270	-3.22	-3.00	-3.11	0.12	0.04	-27.55	-31.00	-31.06	-29.78	-30.04
280	-3.29	-2.94	-3.12	0.18	0.10	-27.86	-31.67	-31.67	-30.22	-30.56
290	-3.34	-2.90	-3.13	0.23	0.15	-28.24	-32.37	-32.38	-30.73	-31.19
300	-3.38	-2.86	-3.13	0.26	0.20	-28.61	-33.26	-33.18	-31.35	-31.85
310	-3.41	-2.84	-3.13	0.29	0.24	-28.97	-34.25	-34.12	-31.99	-32.69
320	-3.43	-2.83	-3.14	0.31	0.29	-29.47	-35.21	-35.03	-32.59	-33.52
330	-3.44	-2.82	-3.14	0.32	0.35	-29.88	-36.18	-35.73	-33.15	-34.22
340	-3.44	-2.83	-3.15	0.32	0.40	-30.32	-37.49	-36.70	-33.82	-35.11
350	-3.43	-2.84	-3.15	0.31	0.45	-30.77	-39.14	-38.07	-34.73	-36.38
360	-3.42	-2.86	-3.15	0.29	0.50	-31.34	-40.95	-39.43	-35.75	-37.81
370	-3.39	-2.89	-3.15	0.26	0.57	-31.81	-43.00	-40.86	-36.79	-39.53
380	-3.35	-2.94	-3.15	0.21	0.64	-32.42	-44.05	-42.03	-37.76	-41.61
390	-3.30	-2.99	-3.15	0.16	0.71	-32.95	-43.45	-41.77	-38.49	-43.57
400	-3.24	-3.05	-3.15	0.10	0.76	-33.30	-41.95	-41.34	-39.24	-45.43
410	-3.18	-3.13	-3.16	0.03	0.83	-33.42	-40.12	-40.72	-39.97	-46.88
420	-3.10	-3.22	-3.16	0.05	0.92	-33.65	-38.07	-39.07	-39.56	-44.35
430	-3.02	-3.32	-3.17	0.15	1.02	-33.56	-35.99	-37.05	-38.38	-40.79
440	-2.92	-3.44	-3.19	0.26	1.12	-33.08	-34.15	-34.99	-36.69	-37.88
450	-2.82	-3.58	-3.22	0.38	1.22	-32.30	-32.41	-33.06	-34.84	-35.34
460	-2.71	-3.73	-3.25	0.51	1.32	-31.34	-30.85	-31.48	-33.19	-33.34
470	-2.59	-3.91	-3.30	0.66	1.45	-30.29	-29.49	-30.11	-31.63	-31.63
480	-2.47	-4.11	-3.37	0.82	1.64	-29.25	-28.19	-28.82	-30.11	-30.04
490	-2.34	-4.34	-3.45	1.00	1.83	-28.24	-26.95	-27.53	-28.67	-28.54
500	-2.20	-4.60	-3.56	1.20	2.03	-27.13	-25.76	-26.27	-27.36	-27.17
510	-2.06	-4.90	-3.71	1.41	2.27	-26.02	-24.62	-25.04	-26.05	-25.86
520	-1.92	-5.24	-3.89	1.65	2.55	-25.00	-23.55	-23.91	-24.82	-24.65
530	-1.78	-5.62	-4.11	1.91	2.90	-24.04	-22.58	-22.91	-23.77	-23.58
540	-1.65	-6.06	-4.39	2.20	3.31	-23.11	-21.63	-21.97	-22.72	-22.57
550	-1.51	-6.56	-4.73	2.52	3.79	-22.24	-20.73	-21.02	-21.74	-21.57

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.

2-Way 90° Power Splitter/Combiner

QCH-451+

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = +25°C, Configuration D.

Freq. (MHz)	Total Loss*			Amp. Unb.	Ph. Unb.	Isolation	Return Loss			
	Sum-Port 1	Sum-Port 2	Average	(±dB) Half P-P	(deg) Rel. to 90°	(dB) Port1-Port2	Sum	Port 1	Port 2	Iso
150	-1.83	-4.90	-3.63	1.55	-0.29	-26.10	-26.13	-26.03	-26.63	-26.58
160	-1.98	-4.60	-3.48	1.32	-0.24	-26.10	-26.28	-26.13	-26.77	-26.75
170	-2.13	-4.35	-3.38	1.11	-0.20	-26.07	-26.45	-26.27	-26.93	-26.88
180	-2.28	-4.12	-3.30	0.93	-0.16	-26.10	-26.67	-26.48	-27.21	-27.11
190	-2.42	-3.92	-3.23	0.76	-0.12	-26.19	-26.91	-26.70	-27.53	-27.39
200	-2.55	-3.74	-3.19	0.60	-0.07	-26.29	-27.12	-26.96	-27.81	-27.66
210	-2.68	-3.59	-3.16	0.46	-0.03	-26.36	-27.43	-27.28	-28.14	-28.03
220	-2.79	-3.45	-3.13	0.33	0.02	-26.60	-27.84	-27.70	-28.55	-28.49
230	-2.90	-3.33	-3.12	0.22	0.07	-26.82	-28.25	-28.08	-28.99	-28.91
240	-3.00	-3.22	-3.11	0.12	0.12	-26.98	-28.65	-28.46	-29.44	-29.38
250	-3.09	-3.13	-3.11	0.03	0.16	-27.18	-29.12	-28.88	-30.01	-29.91
260	-3.17	-3.06	-3.12	0.05	0.20	-27.48	-29.63	-29.33	-30.58	-30.45
270	-3.24	-2.99	-3.12	0.12	0.25	-27.73	-30.04	-29.78	-31.06	-31.00
280	-3.30	-2.93	-3.12	0.18	0.31	-27.97	-30.56	-30.22	-31.67	-31.67
290	-3.35	-2.89	-3.13	0.23	0.37	-28.33	-31.19	-30.73	-32.38	-32.37
300	-3.39	-2.86	-3.13	0.26	0.41	-28.67	-31.85	-31.35	-33.18	-33.26
310	-3.42	-2.83	-3.14	0.29	0.45	-29.03	-32.69	-31.99	-34.12	-34.25
320	-3.45	-2.82	-3.15	0.31	0.51	-29.56	-33.52	-32.59	-35.03	-35.21
330	-3.46	-2.82	-3.15	0.32	0.58	-30.02	-34.22	-33.15	-35.73	-36.18
340	-3.46	-2.82	-3.15	0.32	0.64	-30.38	-35.11	-33.82	-36.70	-37.49
350	-3.45	-2.83	-3.15	0.31	0.70	-30.90	-36.38	-34.73	-38.07	-39.14
360	-3.43	-2.85	-3.15	0.28	0.76	-31.49	-37.81	-35.75	-39.43	-40.95
370	-3.40	-2.89	-3.15	0.25	0.83	-31.97	-39.53	-36.79	-40.86	-43.00
380	-3.36	-2.93	-3.15	0.21	0.91	-32.53	-41.61	-37.76	-42.03	-44.05
390	-3.31	-2.98	-3.15	0.16	0.98	-33.19	-43.57	-38.49	-41.77	-43.45
400	-3.26	-3.05	-3.16	0.10	1.05	-33.50	-45.43	-39.24	-41.34	-41.95
410	-3.19	-3.12	-3.16	0.03	1.13	-33.63	-46.88	-39.97	-40.72	-40.12
420	-3.11	-3.21	-3.16	0.06	1.23	-33.91	-44.35	-39.56	-39.07	-38.07
430	-3.03	-3.32	-3.18	0.15	1.34	-33.80	-40.79	-38.38	-37.05	-35.99
440	-2.93	-3.44	-3.19	0.26	1.45	-33.28	-37.88	-36.69	-34.99	-34.15
450	-2.83	-3.57	-3.22	0.38	1.56	-32.47	-35.34	-34.84	-33.06	-32.41
460	-2.72	-3.73	-3.25	0.51	1.68	-31.49	-33.34	-33.19	-31.48	-30.85
470	-2.60	-3.91	-3.30	0.66	1.82	-30.43	-31.63	-31.63	-30.11	-29.49
480	-2.48	-4.11	-3.37	0.82	2.02	-29.34	-30.04	-30.11	-28.82	-28.19
490	-2.35	-4.34	-3.46	1.00	2.22	-28.33	-28.54	-28.67	-27.53	-26.95
500	-2.21	-4.60	-3.57	1.20	2.44	-27.22	-27.17	-27.36	-26.27	-25.76
510	-2.07	-4.89	-3.70	1.42	2.69	-26.11	-25.86	-26.05	-25.04	-24.62
520	-1.93	-5.23	-3.89	1.66	3.00	-25.07	-24.65	-24.82	-23.91	-23.55
530	-1.79	-5.61	-4.11	1.92	3.36	-24.10	-23.58	-23.77	-22.91	-22.58
540	-1.65	-6.05	-4.38	2.20	3.78	-23.15	-22.57	-22.72	-21.97	-21.63
550	-1.52	-6.55	-4.73	2.52	4.28	-22.27	-21.57	-21.74	-21.02	-20.73

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.

2-Way 90° Power Splitter/Combiner

QCH-451+

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = +105°C, Configuration A.

Freq. (MHz)	Total Loss*			Amp. Unb. (±dB) Half P-P	Ph. Unb. (deg) Rel. to 90°	Isolation (dB) Port1-Port2	Return Loss (dB)			
	Sum-Port 1	Sum-Port 2	Average				Sum	Port 1	Port 2	Iso
150	-1.83	-4.91	-3.64	1.54	-0.50	-24.50	-24.92	-25.03	-24.74	-24.43
160	-1.99	-4.61	-3.49	1.32	-0.47	-24.43	-24.87	-24.95	-24.64	-24.35
170	-2.14	-4.35	-3.38	1.12	-0.43	-24.39	-24.86	-24.95	-24.66	-24.35
180	-2.28	-4.12	-3.30	0.93	-0.39	-24.45	-24.98	-25.05	-24.72	-24.47
190	-2.42	-3.92	-3.23	0.76	-0.33	-24.62	-25.26	-25.31	-24.91	-24.68
200	-2.55	-3.75	-3.19	0.61	-0.27	-24.80	-25.59	-25.64	-25.15	-24.98
210	-2.67	-3.59	-3.15	0.47	-0.22	-24.95	-26.01	-26.01	-25.42	-25.35
220	-2.79	-3.45	-3.13	0.35	-0.16	-25.21	-26.52	-26.49	-25.81	-25.81
230	-2.90	-3.33	-3.12	0.23	-0.08	-25.46	-27.05	-26.95	-26.23	-26.26
240	-2.99	-3.23	-3.11	0.13	-0.01	-25.71	-27.55	-27.45	-26.65	-26.74
250	-3.08	-3.14	-3.11	0.04	0.05	-26.07	-28.19	-28.05	-27.13	-27.29
260	-3.16	-3.06	-3.11	0.04	0.11	-26.53	-28.95	-28.78	-27.79	-27.96
270	-3.24	-3.00	-3.12	0.11	0.17	-26.94	-29.79	-29.55	-28.36	-28.66
280	-3.30	-2.94	-3.12	0.17	0.24	-27.34	-30.70	-30.38	-28.99	-29.37
290	-3.35	-2.90	-3.13	0.21	0.32	-27.82	-31.68	-31.18	-29.64	-30.10
300	-3.39	-2.87	-3.14	0.25	0.36	-28.30	-32.70	-32.23	-30.33	-30.88
310	-3.42	-2.84	-3.14	0.28	0.41	-28.82	-33.80	-33.30	-31.07	-31.72
320	-3.44	-2.83	-3.15	0.30	0.47	-29.47	-35.00	-34.56	-31.99	-32.67
330	-3.45	-2.82	-3.15	0.30	0.54	-30.08	-36.49	-36.02	-33.03	-33.77
340	-3.45	-2.83	-3.15	0.30	0.61	-30.65	-38.23	-37.81	-34.14	-35.03
350	-3.45	-2.84	-3.16	0.29	0.66	-31.33	-40.59	-39.96	-35.42	-36.46
360	-3.43	-2.86	-3.15	0.27	0.72	-32.05	-43.60	-42.79	-36.86	-38.13
370	-3.40	-2.90	-3.16	0.24	0.78	-32.70	-47.67	-45.86	-38.46	-40.06
380	-3.36	-2.94	-3.16	0.20	0.86	-33.37	-52.06	-47.51	-40.45	-42.73
390	-3.31	-2.99	-3.15	0.15	0.93	-34.14	-51.10	-45.17	-42.81	-47.15
400	-3.25	-3.06	-3.16	0.09	0.99	-34.55	-45.43	-41.57	-43.76	-54.99
410	-3.19	-3.13	-3.16	0.01	1.08	-34.73	-41.07	-38.43	-42.33	-50.13
420	-3.11	-3.22	-3.17	0.07	1.18	-34.74	-38.08	-36.06	-40.00	-43.32
430	-3.03	-3.32	-3.18	0.17	1.30	-34.33	-35.99	-34.17	-37.64	-39.46
440	-2.93	-3.44	-3.19	0.28	1.42	-33.52	-33.98	-32.45	-35.20	-36.68
450	-2.83	-3.58	-3.22	0.40	1.54	-32.63	-32.25	-30.84	-33.04	-34.31
460	-2.72	-3.74	-3.26	0.54	1.66	-31.57	-30.65	-29.35	-31.25	-32.33
470	-2.60	-3.91	-3.30	0.68	1.83	-30.40	-29.10	-27.98	-29.63	-30.49
480	-2.48	-4.11	-3.37	0.85	2.04	-29.20	-27.66	-26.72	-28.14	-28.85
490	-2.35	-4.34	-3.46	1.03	2.26	-28.06	-26.39	-25.57	-26.82	-27.42
500	-2.22	-4.60	-3.57	1.23	2.50	-26.95	-25.25	-24.51	-25.63	-26.18
510	-2.07	-4.90	-3.71	1.45	2.77	-25.86	-24.14	-23.47	-24.45	-24.95
520	-1.93	-5.23	-3.89	1.69	3.09	-24.85	-23.05	-22.47	-23.32	-23.77
530	-1.80	-5.62	-4.12	1.95	3.49	-23.90	-22.01	-21.52	-22.29	-22.70
540	-1.66	-6.05	-4.39	2.24	3.97	-22.95	-21.01	-20.59	-21.30	-21.66
550	-1.52	-6.55	-4.73	2.57	4.54	-22.06	-20.08	-19.74	-20.39	-20.70

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.

NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>



2-Way 90° Power Splitter/Combiner

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = +105°C, Configuration B.

Freq. (MHz)	Total Loss*			Amp. Unb. (±dB) Half P-P	Ph. Unb. (deg) Rel. to 90°	Isolation (dB) Port1-Port2	Return Loss (dB)			
	Sum-Port 1	Sum-Port 2	Average				Sum	Port 1	Port 2	Iso
150	-1.82	-4.91	-3.63	1.54	-0.47	-24.45	-24.43	-24.74	-25.03	-24.92
160	-1.98	-4.61	-3.49	1.32	-0.43	-24.38	-24.35	-24.64	-24.95	-24.87
170	-2.13	-4.35	-3.38	1.11	-0.38	-24.33	-24.35	-24.66	-24.95	-24.86
180	-2.28	-4.12	-3.30	0.93	-0.33	-24.42	-24.47	-24.72	-25.05	-24.98
190	-2.42	-3.92	-3.23	0.76	-0.27	-24.59	-24.68	-24.91	-25.31	-25.26
200	-2.55	-3.75	-3.19	0.61	-0.20	-24.74	-24.98	-25.15	-25.64	-25.59
210	-2.67	-3.59	-3.15	0.47	-0.13	-24.88	-25.35	-25.42	-26.01	-26.01
220	-2.79	-3.45	-3.13	0.34	-0.07	-25.14	-25.81	-25.81	-26.49	-26.52
230	-2.90	-3.33	-3.12	0.23	-0.01	-25.39	-26.26	-26.23	-26.95	-27.05
240	-2.99	-3.23	-3.11	0.13	0.05	-25.66	-26.74	-26.65	-27.45	-27.55
250	-3.08	-3.14	-3.11	0.04	0.11	-26.03	-27.29	-27.13	-28.05	-28.19
260	-3.16	-3.06	-3.11	0.04	0.16	-26.47	-27.96	-27.79	-28.78	-28.95
270	-3.23	-2.99	-3.11	0.11	0.23	-26.92	-28.66	-28.36	-29.55	-29.79
280	-3.30	-2.94	-3.12	0.17	0.31	-27.30	-29.37	-28.99	-30.38	-30.70
290	-3.35	-2.90	-3.13	0.22	0.38	-27.79	-30.10	-29.64	-31.18	-31.68
300	-3.39	-2.87	-3.14	0.26	0.43	-28.26	-30.88	-30.33	-32.23	-32.70
310	-3.42	-2.84	-3.14	0.28	0.48	-28.82	-31.72	-31.07	-33.30	-33.80
320	-3.44	-2.83	-3.15	0.30	0.54	-29.43	-32.67	-31.99	-34.56	-35.00
330	-3.45	-2.82	-3.15	0.31	0.61	-30.02	-33.77	-33.03	-36.02	-36.49
340	-3.45	-2.82	-3.15	0.31	0.68	-30.59	-35.03	-34.14	-37.81	-38.23
350	-3.45	-2.84	-3.16	0.30	0.73	-31.25	-36.46	-35.42	-39.96	-40.59
360	-3.43	-2.86	-3.15	0.28	0.79	-31.93	-38.13	-36.86	-42.79	-43.60
370	-3.40	-2.89	-3.15	0.25	0.86	-32.57	-40.06	-38.46	-45.86	-47.67
380	-3.36	-2.94	-3.16	0.20	0.93	-33.24	-42.73	-40.45	-47.51	-52.06
390	-3.31	-2.99	-3.15	0.15	1.01	-33.92	-47.15	-42.81	-45.17	-51.10
400	-3.25	-3.05	-3.15	0.09	1.08	-34.37	-54.99	-43.76	-41.57	-45.43
410	-3.19	-3.13	-3.16	0.02	1.16	-34.55	-50.13	-42.33	-38.43	-41.07
420	-3.11	-3.22	-3.17	0.07	1.26	-34.54	-43.32	-40.00	-36.06	-38.08
430	-3.02	-3.32	-3.17	0.17	1.37	-34.11	-39.46	-37.64	-34.17	-35.99
440	-2.93	-3.44	-3.19	0.28	1.48	-33.39	-36.68	-35.20	-32.45	-33.98
450	-2.82	-3.58	-3.22	0.40	1.59	-32.49	-34.31	-33.04	-30.84	-32.25
460	-2.71	-3.73	-3.25	0.53	1.72	-31.47	-32.33	-31.25	-29.35	-30.65
470	-2.60	-3.91	-3.30	0.68	1.89	-30.33	-30.49	-29.63	-27.98	-29.10
480	-2.48	-4.11	-3.37	0.85	2.09	-29.11	-28.85	-28.14	-26.72	-27.66
490	-2.35	-4.34	-3.46	1.03	2.32	-27.97	-27.42	-26.82	-25.57	-26.39
500	-2.21	-4.60	-3.57	1.23	2.55	-26.87	-26.18	-25.63	-24.51	-25.25
510	-2.07	-4.90	-3.71	1.45	2.83	-25.80	-24.95	-24.45	-23.47	-24.14
520	-1.93	-5.23	-3.89	1.69	3.15	-24.82	-23.77	-23.32	-22.47	-23.05
530	-1.79	-5.62	-4.11	1.96	3.55	-23.87	-22.70	-22.29	-21.52	-22.01
540	-1.65	-6.06	-4.39	2.25	4.03	-22.93	-21.66	-21.30	-20.59	-21.01
550	-1.51	-6.56	-4.73	2.57	4.58	-22.04	-20.70	-20.39	-19.74	-20.08

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.

NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>



2-Way 90° Power Splitter/Combiner

QCH-451+

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = +105°C, Configuration C.

Freq. (MHz)	Total Loss*			Amp. Unb. (±dB) Half P-P	Ph. Unb. (deg) Rel. to 90°	Isolation (dB) Port1-Port2	Return Loss (dB)			
	Sum-Port 1	Sum-Port 2	Average				Sum	Port 1	Port 2	Iso
150	-1.82	-4.91	-3.63	1.54	-0.54	-24.71	-25.03	-24.92	-24.43	-24.74
160	-1.97	-4.61	-3.49	1.32	-0.51	-24.63	-24.95	-24.87	-24.35	-24.64
170	-2.12	-4.35	-3.38	1.12	-0.49	-24.58	-24.95	-24.86	-24.35	-24.66
180	-2.27	-4.12	-3.29	0.93	-0.45	-24.62	-25.05	-24.98	-24.47	-24.72
190	-2.41	-3.92	-3.23	0.77	-0.41	-24.73	-25.31	-25.26	-24.68	-24.91
200	-2.54	-3.75	-3.19	0.61	-0.34	-24.87	-25.64	-25.59	-24.98	-25.15
210	-2.66	-3.59	-3.15	0.47	-0.28	-24.96	-26.01	-26.01	-25.35	-25.42
220	-2.78	-3.45	-3.13	0.35	-0.22	-25.15	-26.49	-26.52	-25.81	-25.81
230	-2.89	-3.33	-3.12	0.24	-0.15	-25.35	-26.95	-27.05	-26.26	-26.23
240	-2.98	-3.23	-3.11	0.14	-0.08	-25.53	-27.45	-27.55	-26.74	-26.65
250	-3.07	-3.14	-3.11	0.05	-0.02	-25.84	-28.05	-28.19	-27.29	-27.13
260	-3.15	-3.06	-3.11	0.04	0.03	-26.29	-28.78	-28.95	-27.96	-27.79
270	-3.22	-3.00	-3.11	0.11	0.10	-26.64	-29.55	-29.79	-28.66	-28.36
280	-3.29	-2.94	-3.12	0.16	0.17	-27.05	-30.38	-30.70	-29.37	-28.99
290	-3.34	-2.90	-3.13	0.21	0.23	-27.51	-31.18	-31.68	-30.10	-29.64
300	-3.38	-2.86	-3.13	0.25	0.29	-28.02	-32.23	-32.70	-30.88	-30.33
310	-3.41	-2.84	-3.13	0.28	0.34	-28.59	-33.30	-33.80	-31.72	-31.07
320	-3.43	-2.83	-3.14	0.30	0.39	-29.30	-34.56	-35.00	-32.67	-31.99
330	-3.44	-2.82	-3.14	0.30	0.45	-29.98	-36.02	-36.49	-33.77	-33.03
340	-3.44	-2.83	-3.15	0.30	0.51	-30.71	-37.81	-38.23	-35.03	-34.14
350	-3.43	-2.84	-3.15	0.29	0.56	-31.52	-39.96	-40.59	-36.46	-35.42
360	-3.42	-2.86	-3.15	0.27	0.62	-32.49	-42.79	-43.60	-38.13	-36.86
370	-3.39	-2.89	-3.15	0.24	0.68	-33.39	-45.86	-47.67	-40.06	-38.46
380	-3.35	-2.94	-3.15	0.20	0.77	-34.53	-47.51	-52.06	-42.73	-40.45
390	-3.30	-2.99	-3.15	0.15	0.83	-35.69	-45.17	-51.10	-47.15	-42.81
400	-3.24	-3.05	-3.15	0.08	0.89	-36.76	-41.57	-45.43	-54.99	-43.76
410	-3.18	-3.13	-3.16	0.01	0.97	-37.33	-38.43	-41.07	-50.13	-42.33
420	-3.10	-3.22	-3.16	0.08	1.06	-37.54	-36.06	-38.08	-43.32	-40.00
430	-3.02	-3.32	-3.17	0.17	1.17	-36.79	-34.17	-35.99	-39.46	-37.64
440	-2.92	-3.44	-3.19	0.28	1.29	-35.43	-32.45	-33.98	-36.68	-35.20
450	-2.82	-3.58	-3.22	0.40	1.40	-33.89	-30.84	-32.25	-34.31	-33.04
460	-2.71	-3.73	-3.25	0.54	1.52	-32.38	-29.35	-30.65	-32.33	-31.25
470	-2.59	-3.91	-3.30	0.69	1.68	-30.85	-27.98	-29.10	-30.49	-29.63
480	-2.47	-4.11	-3.37	0.85	1.88	-29.47	-26.72	-27.66	-28.85	-28.14
490	-2.34	-4.34	-3.45	1.03	2.09	-28.21	-25.57	-26.39	-27.42	-26.82
500	-2.20	-4.60	-3.56	1.23	2.33	-26.98	-24.51	-25.25	-26.18	-25.63
510	-2.06	-4.90	-3.71	1.45	2.59	-25.83	-23.47	-24.14	-24.95	-24.45
520	-1.92	-5.24	-3.89	1.69	2.92	-24.79	-22.47	-23.05	-23.77	-23.32
530	-1.78	-5.62	-4.11	1.96	3.31	-23.82	-21.52	-22.01	-22.70	-22.29
540	-1.65	-6.06	-4.39	2.25	3.78	-22.88	-20.59	-21.01	-21.66	-21.30
550	-1.51	-6.56	-4.73	2.57	4.32	-22.00	-19.74	-20.08	-20.70	-20.39

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.

NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>



2-Way 90° Power Splitter/Combiner

QCH-451+

Typical Performance Data

Test Conditions: Input Power = +5 dbm, Temperature = +105°C, Configuration D.

Freq. (MHz)	Total Loss*			Amp. Unb. (±dB) Half P-P	Ph. Unb. (deg) Rel. to 90°	Isolation (dB) Port1-Port2	Return Loss (dB)			
	Sum-Port 1	Sum-Port 2	Average				Sum	Port 1	Port 2	Iso
150	-1.83	-4.90	-3.63	1.54	-0.43	-24.80	-24.74	-24.43	-24.92	-25.03
160	-1.98	-4.60	-3.48	1.31	-0.38	-24.72	-24.64	-24.35	-24.87	-24.95
170	-2.13	-4.35	-3.38	1.11	-0.33	-24.65	-24.66	-24.35	-24.86	-24.95
180	-2.28	-4.12	-3.30	0.93	-0.27	-24.70	-24.72	-24.47	-24.98	-25.05
190	-2.42	-3.92	-3.23	0.76	-0.20	-24.82	-24.91	-24.68	-25.26	-25.31
200	-2.55	-3.74	-3.19	0.61	-0.14	-24.94	-25.15	-24.98	-25.59	-25.64
210	-2.68	-3.59	-3.16	0.47	-0.08	-25.02	-25.42	-25.35	-26.01	-26.01
220	-2.79	-3.45	-3.13	0.34	-0.01	-25.23	-25.81	-25.81	-26.52	-26.49
230	-2.90	-3.33	-3.12	0.23	0.06	-25.46	-26.23	-26.26	-27.05	-26.95
240	-3.00	-3.22	-3.11	0.13	0.13	-25.68	-26.65	-26.74	-27.55	-27.45
250	-3.09	-3.13	-3.11	0.04	0.20	-26.00	-27.13	-27.29	-28.19	-28.05
260	-3.17	-3.06	-3.12	0.05	0.25	-26.43	-27.79	-27.96	-28.95	-28.78
270	-3.24	-2.99	-3.12	0.11	0.32	-26.80	-28.36	-28.66	-29.79	-29.55
280	-3.30	-2.93	-3.12	0.17	0.39	-27.14	-28.99	-29.37	-30.70	-30.38
290	-3.35	-2.89	-3.13	0.22	0.46	-27.59	-29.64	-30.10	-31.68	-31.18
300	-3.39	-2.86	-3.13	0.26	0.51	-28.06	-30.33	-30.88	-32.70	-32.23
310	-3.42	-2.83	-3.14	0.29	0.57	-28.63	-31.07	-31.72	-33.80	-33.30
320	-3.45	-2.82	-3.15	0.30	0.64	-29.37	-31.99	-32.67	-35.00	-34.56
330	-3.46	-2.82	-3.15	0.31	0.71	-30.09	-33.03	-33.77	-36.49	-36.02
340	-3.46	-2.82	-3.15	0.31	0.77	-30.73	-34.14	-35.03	-38.23	-37.81
350	-3.45	-2.83	-3.15	0.30	0.84	-31.62	-35.42	-36.46	-40.59	-39.96
360	-3.43	-2.85	-3.15	0.28	0.90	-32.57	-36.86	-38.13	-43.60	-42.79
370	-3.40	-2.89	-3.15	0.25	0.97	-33.49	-38.46	-40.06	-47.67	-45.86
380	-3.36	-2.93	-3.15	0.21	1.05	-34.61	-40.45	-42.73	-52.06	-47.51
390	-3.31	-2.98	-3.15	0.15	1.13	-35.97	-42.81	-47.15	-51.10	-45.17
400	-3.26	-3.05	-3.16	0.09	1.20	-37.00	-43.76	-54.99	-45.43	-41.57
410	-3.19	-3.12	-3.16	0.02	1.29	-37.64	-42.33	-50.13	-41.07	-38.43
420	-3.11	-3.21	-3.16	0.07	1.40	-37.98	-40.00	-43.32	-38.08	-36.06
430	-3.03	-3.32	-3.18	0.17	1.51	-37.17	-37.64	-39.46	-35.99	-34.17
440	-2.93	-3.44	-3.19	0.27	1.63	-35.70	-35.20	-36.68	-33.98	-32.45
450	-2.83	-3.57	-3.22	0.40	1.75	-34.12	-33.04	-34.31	-32.25	-30.84
460	-2.72	-3.73	-3.25	0.53	1.89	-32.56	-31.25	-32.33	-30.65	-29.35
470	-2.60	-3.91	-3.30	0.68	2.06	-31.01	-29.63	-30.49	-29.10	-27.98
480	-2.48	-4.11	-3.37	0.84	2.27	-29.58	-28.14	-28.85	-27.66	-26.72
490	-2.35	-4.34	-3.46	1.02	2.49	-28.31	-26.82	-27.42	-26.39	-25.57
500	-2.21	-4.60	-3.57	1.23	2.73	-27.09	-25.63	-26.18	-25.25	-24.51
510	-2.07	-4.89	-3.70	1.44	3.02	-25.93	-24.45	-24.95	-24.14	-23.47
520	-1.93	-5.23	-3.89	1.69	3.36	-24.89	-23.32	-23.77	-23.05	-22.47
530	-1.79	-5.61	-4.11	1.95	3.76	-23.89	-22.29	-22.70	-22.01	-21.52
540	-1.65	-6.05	-4.38	2.24	4.25	-22.93	-21.30	-21.66	-21.01	-20.59
550	-1.52	-6.55	-4.73	2.56	4.82	-22.05	-20.39	-20.70	-20.08	-19.74

* Total loss is the loss from Sum to each coupled port including the 3 dB theoretical split.




NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>





Typical Performance Graphs

Test Conditions: Input Power = +5 dbm, Configuration A.






Typical Performance Graphs

Test Conditions: Input Power = +5 dbm, Configuration A.





Typical Performance Graphs

Test Conditions: Input Power = +5 dbm, Configuration B.






Typical Performance Graphs

Test Conditions: Input Power = +5 dbm, Configuration B.





Typical Performance Graphs

Test Conditions: Input Power = +5 dbm, Configuration C.






Typical Performance Graphs

Test Conditions: Input Power = +5 dbm, Configuration C.





Typical Performance Graphs

Test Conditions: Input Power = +5 dbm, Configuration D.






Typical Performance Graphs

Test Conditions: Input Power = +5 dbm, Configuration D.



Typical Performance Graphs

Test Conditions: Input Power = +5 dbm, Configuration A.





NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>



Typical Performance Graphs

Test Conditions: Input Power = +5 dbm, Configuration A.



NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>




Case Style

PQ


Outline Dimensions

PQ2185-1



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M163111	NEW RELEASE	10/17	YS	YB
OR	R92246	NEW RELEASE	10/17	YS	YB

SUGGESTED MOUNTING CONFIGURATION

FOR PQ2185 CASE STYLE 04DC01 PIN CONNECTION, 50 OHM



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04003C WITH DIELECTRIC THICKNESS. .032" ± .0015". COPPER: 1 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN YS (RAVON)	02 OCT 17
TOLERANCES ON:	CHECKED HH (RAVON)	02 OCT 17
2 PL DECIMALS ±	APPROVED YB (RAVON)	02 OCT 17
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		




Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL FOR QCH PQ2185
TB-914 (50 Ω)

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-529	REV: OR
FILE: 98PL529(OR)		SCALE: 4:1	SHEET: 1 OF 1


Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit



NOTES:

1. SMA FEMALE CONNECTORS.
2. PCB MATERIAL: ROGERS RO4003C OR EQUIVALENT, DIELECTRIC CONSTANT=3.5, DIELECTRIC THICKNESS=.032 INCH.



TB-914
Schematic Diagram



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105° C Case Environment	Individual Model Data Sheet
Storage Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (high Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215