



USB / ETHERNET

Programmable Attenuator

RCDAT-6000-30

50Ω 1 to 6000 MHz, 0 - 30 dB, 0.25 dB step

THE BIG DEAL

- Wide attenuation range, 30 dB
- Fine attenuation resolution, 0.25 dB
- Short attenuation transition time (650 ns)
- Compact size, 3.0 x 2.5 x 0.85"
- USB and Ethernet control

APPLICATIONS

- LTE, 5G FR1, DVB fading simulators
- Wi-Fi device testing
- Signal level calibration
- Automated gain control
- Laboratory instrumentation



Generic photo used for illustration purposes only.

Model No.	RCDAT-6000-30
Case Style	MS1897
Connectors	SMA (female)

DOWNLOAD

SOFTWARE PACKAGE

Refer to our website for compliance methodologies and qualifications



PRODUCT OVERVIEW

Mini-Circuits' RCDAT-6000-30 is a general purpose, single channel programmable attenuator suitable for a wide range of signal level control applications from 1 to 6000 MHz. The attenuator provides 0 to 30 dB attenuation in 0.25 dB steps. Its unique design maintains linear attenuation change per dB, even at the highest attenuation settings.

The attenuator is housed in a compact and rugged package with SMA female connectors on the bi-directional input and output RF ports, a standard Ethernet port (RJ45) and a USB type Mini-B power and control port.

Full software support is provided, including our user-friendly GUI application for Windows and a full API with programming instructions for Windows and Linux environments (both 32-bit and 64-bit systems).

KEY FEATURES

Feature	Advantages
Programmable attenuation sweep and hop sequences	The module can be programmed with a timed sequence of attenuation settings, to run without any additional external control.
30 dB attenuation range	The module provides high-accuracy attenuation up to 30 dB in 0.25 dB steps, allowing the user precise level control over a broad attenuation and frequency range.
High linearity	Typical input IP3 of +51 dBm up to 6000 MHz.
USB and Ethernet control	USB HID and Ethernet (HTTP / Telnet) interfaces provide easy compatibility with a wide range of software setups and programming environments.
Full software support	User friendly Windows GUI (graphical user interface) allows manual control straight out of the box, while the comprehensive API (application programming interface) with examples and instructions allows easy automation in most programming environments

Trademarks:

Windows is a registered trademark of Microsoft Corporation in the United States and other countries ; Linux is a registered trademark of Linus Torvalds ; Pentium is a registered trademark of Intel Corporation. Neither Mini-Circuits nor the Mini-Circuits products are affiliated with or endorsed by the owners of the referenced trademarks. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation.



ELECTRICAL SPECIFICATIONS¹ AT 0 TO 50°C

Parameter	Conditions	Frequency (MHz)	Min.	Typ.	Max.	Unit
Attenuation range	0.25 dB step	1 - 6000	0	-	30	dB
Attenuation accuracy ²	0.25 - 20 dB	1 - 2000	-	±0.30	±(0.35 + 6.0% of Atten.)	dB
		2000 - 4000	-	±0.20	±(0.40 + 5.5% of Atten.)	
		4000 - 6000	-	±0.15	±(0.30 + 9.0% of Atten.)	
	20.25 - 30 dB	1 - 2000	-	±0.70	±(1.00 + 1.5% of Atten.)	
		2000 - 4000	-	±0.45	±(0.90 + 1.5% of Atten.)	
		4000 - 6000	-	±0.35	±(0.90 + 2.0% of Atten.)	
Insertion loss	0 dB	1 - 2000	-	1.8	3.0	dB
		2000 - 4000	-	2.5	4.5	
		4000 - 6000	-	3.5	5.0	
Isolation in-out ³	-	1 - 6000	-	31.5	-	dB
Return loss in	0 - 10 dB	1 - 4000	-	19	-	dB
		4000 - 6000	-	16	-	
	10.25 - 30 dB	1 - 4000	-	18	-	
		4000 - 6000	-	20	-	
Return loss out	0 - 10 dB	1 - 500	-	23	-	dB
		500 - 6000	-	19	-	
	10.25 - 30 dB	1 - 500	-	20	-	
		500 - 6000	-	17	-	
IP3 input ⁴	0 dB setting (P _{IN} = +5 dBm)	1 - 3000	-	+53	-	dBm
		3000 - 6000	-	+51	-	
Input operating power ⁵	0 - 30 dB	1 - 50	-	-	Note 6	dBm
		50 - 6000	-	-	+23	
Attenuation transition time ⁷	-	1 - 6000	-	650	-	ns
Minimum dwell time ⁸	High-speed mode	1 - 6000	-	600	-	µs
Supply voltage (V _{CC})	USB port	-	4.75	5	5.25	V _{DC}
Supply current (I _{CC})		-	-	190	250	mA
Ethernet communication	Protocol	TCP / IP, HTTP, Telnet, DHCP, UDP (limited)				
	Max data rate	10 Mbps (10 base-T Half Duplex)				
USB communication	Protocol	HID (Human Interface Device) - Full Speed				
	Min communication time ⁹	3 ms typ. (full transmit/receive cycle)				

1. Attenuator RF ports support simultaneous, bi-directional signal transmission, within the specified power limits. However the specifications are guaranteed for the RF in and RF out as noted on the label. There may be minor changes in performance when injecting signals to the RF Out port.
2. Max accuracy defined as $\pm[\text{absolute error} + \% \text{ of attenuation setting}]$. For example, if a 20 dB attenuation at a given frequency is defined as max accuracy of " $\pm(-0.5 + 3.0\%)$ " then the maximum error at those settings will be: $\pm(-0.5 + 0.03 \times 20) = \pm(-0.5 + 0.6) = \pm 0.1$ dB.
3. Isolation is defined as max attenuation plus insertion loss; this is the path loss through the attenuator when initially powered up. After a brief delay (~0.5 sec typically) the attenuator will revert to a user defined "power-up" state (either max attenuation or a pre-set value).
4. Tested with 1 MHz span between signals.
5. Total operating input power from both RF In and RF Out out ports. Compression level not noted as it exceeds max safe operating power level.
6. Derates linearly from +23 dBm at 50 MHz to +9 dBm at 1 MHz.
7. Attenuation Transition Time is specified as the time between starting to change the attenuation state and settling on the requested attenuation state.
8. Minimum Dwell Time is the time the module will take to respond to a command to change attenuation states without communication delays. In PC control add communication delays (on the order of msec for USB) to get actual response time.
9. USB min communication time is based on the polling interval of the USB HID protocol (1 ms polling interval, 64 bytes per packet), medium CPU load and no other high speed USB devices using the USB bus.




ABSOLUTE MAXIMUM RATINGS


Operating temperature	0°C to 50°C	
Storage temperature	-20°C to 85°C	
DC voltage at RF ports	16 V	
V _{USB} MAX	6 V	
Total RF power for RF in & RF out	1 - 50 MHz	Derates linearly from +26 dBm @ 50 MHz to +12 dBm @ 1 MHz
	50 - 6000 MHz	+26 dBm

Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

PROGRAMMABLE ATTENUATOR RESPONSE TO COMMUNICATION INTERRUPT



BLOCK DIAGRAM



Simultaneous, bidirectional RF signal transmission with symmetrical performance




USB / ETHERNET


Programmable Attenuator

RCDAT-6000-30


OUTLINE DRAWING (MS1897)



Top View




Bottom View



CONNECTIONS

Port Name	Connector Type
RF in	SMA female
RF out	SMA female
USB	USB type Mini-B female
Network (Ethernet/ LAN)	RJ45 socket

Bracket Option



OUTLINE DIMENSIONS (INCH MM)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	weight
3.00	2.50	0.85	0.28	0.50	2.20	2.70	0.188	2.50	2.125	0.188	0.144	3.75	3.375	0.10	grams
76.20	63.50	21.60	7.10	12.70	55.88	68.58	4.760	63.50	53.980	4.760	3.660	95.30	85.720	2.54	200





TYPICAL PERFORMANCE DATA

Freq. [MHz]	I.Loss [dB]	Attenuation relative to I. Loss (at 25°C)									
		[dB]									
		@ Attenuation setting [dB]									
		0.25	4	8	12	15	18	21	24	27	30
1	-1.01	-0.26	-4.03	-7.85	-11.65	-14.71	-17.75	-20.83	-23.89	-26.75	-29.79
100	-1.08	-0.26	-4.03	-7.85	-11.66	-14.72	-17.76	-20.84	-23.90	-26.76	-29.80
375	-1.20	-0.26	-4.04	-7.86	-11.67	-14.73	-17.77	-20.85	-23.91	-26.76	-29.80
625	-1.33	-0.26	-4.04	-7.86	-11.68	-14.73	-17.77	-20.85	-23.91	-26.75	-29.80
875	-1.47	-0.26	-4.04	-7.86	-11.67	-14.72	-17.77	-20.84	-23.90	-26.74	-29.79
1125	-1.63	-0.26	-4.03	-7.84	-11.65	-14.70	-17.74	-20.82	-23.87	-26.72	-29.76
1375	-1.79	-0.26	-4.02	-7.82	-11.63	-14.68	-17.72	-20.80	-23.85	-26.70	-29.74
1625	-1.93	-0.26	-4.01	-7.82	-11.62	-14.67	-17.70	-20.79	-23.84	-26.70	-29.75
1875	-2.05	-0.26	-4.01	-7.82	-11.63	-14.67	-17.71	-20.81	-23.87	-26.74	-29.79
2125	-2.15	-0.27	-4.02	-7.83	-11.65	-14.69	-17.73	-20.85	-23.91	-26.80	-29.85
2625	-2.36	-0.26	-4.01	-7.83	-11.67	-14.73	-17.78	-20.92	-24.00	-26.92	-30.00
3125	-2.52	-0.26	-4.06	-7.90	-11.76	-14.84	-17.92	-21.06	-24.17	-27.11	-30.22
3375	-2.60	-0.27	-4.09	-7.95	-11.82	-14.90	-18.00	-21.14	-24.25	-27.21	-30.34
3875	-2.81	-0.28	-4.13	-8.01	-11.88	-14.97	-18.07	-21.23	-24.36	-27.36	-30.50
4125	-2.92	-0.29	-4.13	-8.02	-11.90	-14.99	-18.09	-21.27	-24.41	-27.43	-30.57
4375	-3.03	-0.29	-4.15	-8.04	-11.92	-15.02	-18.13	-21.32	-24.47	-27.51	-30.65
4500	-3.08	-0.29	-4.15	-8.06	-11.94	-15.04	-18.15	-21.35	-24.50	-27.55	-30.70
4750	-3.22	-0.30	-4.18	-8.09	-11.98	-15.09	-18.20	-21.41	-24.57	-27.64	-30.78
4875	-3.29	-0.30	-4.20	-8.12	-12.01	-15.12	-18.24	-21.44	-24.60	-27.68	-30.81
5125	-3.46	-0.31	-4.22	-8.15	-12.05	-15.15	-18.27	-21.48	-24.64	-27.72	-30.84
5250	-3.56	-0.32	-4.22	-8.16	-12.04	-15.15	-18.26	-21.47	-24.63	-27.71	-30.82
5500	-3.77	-0.32	-4.21	-8.15	-12.02	-15.13	-18.23	-21.46	-24.61	-27.70	-30.78
5625	-3.86	-0.33	-4.21	-8.14	-12.02	-15.12	-18.21	-21.45	-24.60	-27.70	-30.76
5875	-3.96	-0.33	-4.21	-8.16	-12.04	-15.15	-18.23	-21.52	-24.66	-27.77	-30.80
6000	-3.97	-0.33	-4.22	-8.19	-12.08	-15.19	-18.26	-21.58	-24.73	-27.85	-30.86



TYPICAL PERFORMANCE DATA (CONTINUED)

Freq. [MHz]	I.Loss [dB]	Attenuation relative to I. Loss (at 0°C)									
		[dB]									
		@ Attenuation setting [dB]									
		0.25	4	8	12	15	18	21	24	27	30
1	-0.94	-0.27	-4.05	-7.89	-11.70	-14.77	-17.82	-20.90	-23.97	-26.83	-29.88
100	-1.02	-0.27	-4.05	-7.89	-11.70	-14.77	-17.82	-20.90	-23.97	-26.83	-29.87
375	-1.13	-0.26	-4.07	-7.91	-11.73	-14.79	-17.84	-20.92	-23.99	-26.84	-29.89
625	-1.25	-0.26	-4.08	-7.91	-11.73	-14.80	-17.85	-20.92	-23.99	-26.84	-29.89
875	-1.40	-0.26	-4.07	-7.90	-11.72	-14.79	-17.84	-20.91	-23.97	-26.82	-29.87
1125	-1.55	-0.26	-4.05	-7.88	-11.69	-14.76	-17.80	-20.88	-23.94	-26.79	-29.84
1375	-1.70	-0.26	-4.04	-7.85	-11.67	-14.73	-17.77	-20.85	-23.91	-26.76	-29.81
1625	-1.83	-0.26	-4.03	-7.84	-11.66	-14.72	-17.76	-20.85	-23.91	-26.77	-29.82
1875	-1.94	-0.26	-4.03	-7.84	-11.66	-14.72	-17.76	-20.87	-23.93	-26.80	-29.85
2125	-2.04	-0.26	-4.03	-7.85	-11.68	-14.73	-17.78	-20.90	-23.97	-26.85	-29.92
2625	-2.25	-0.26	-4.03	-7.86	-11.71	-14.78	-17.84	-20.98	-24.07	-26.98	-30.07
3125	-2.42	-0.26	-4.08	-7.94	-11.81	-14.90	-17.99	-21.13	-24.24	-27.18	-30.30
3375	-2.49	-0.27	-4.12	-7.99	-11.88	-14.97	-18.07	-21.21	-24.33	-27.29	-30.42
3875	-2.69	-0.28	-4.16	-8.05	-11.94	-15.05	-18.16	-21.31	-24.45	-27.44	-30.58
4125	-2.79	-0.29	-4.16	-8.07	-11.96	-15.07	-18.18	-21.35	-24.50	-27.51	-30.65
4375	-2.89	-0.29	-4.18	-8.09	-11.98	-15.10	-18.22	-21.40	-24.55	-27.58	-30.72
4500	-2.95	-0.29	-4.18	-8.09	-11.99	-15.11	-18.23	-21.42	-24.57	-27.61	-30.75
4750	-3.07	-0.30	-4.20	-8.13	-12.03	-15.15	-18.27	-21.48	-24.64	-27.69	-30.82
4875	-3.14	-0.30	-4.21	-8.15	-12.06	-15.17	-18.30	-21.50	-24.67	-27.72	-30.85
5125	-3.29	-0.31	-4.24	-8.18	-12.09	-15.21	-18.33	-21.55	-24.71	-27.77	-30.89
5250	-3.38	-0.31	-4.25	-8.19	-12.10	-15.22	-18.34	-21.56	-24.72	-27.78	-30.89
5500	-3.59	-0.32	-4.24	-8.18	-12.08	-15.19	-18.31	-21.54	-24.69	-27.76	-30.83
5625	-3.66	-0.32	-4.23	-8.18	-12.08	-15.19	-18.30	-21.54	-24.69	-27.76	-30.82
5875	-3.80	-0.33	-4.22	-8.18	-12.08	-15.19	-18.28	-21.57	-24.72	-27.80	-30.82
6000	-3.82	-0.33	-4.22	-8.19	-12.09	-15.21	-18.29	-21.61	-24.76	-27.85	-30.85

Freq. [MHz]	I.Loss [dB]	Attenuation relative to I. Loss (at 50°C)									
		[dB]									
		@ Attenuation setting [dB]									
		0.25	4	8	12	15	18	21	24	27	30
1	-1.04	-0.26	-4.01	-7.83	-11.63	-14.68	-17.72	-20.80	-23.85	-26.71	-29.75
100	-1.11	-0.26	-4.02	-7.84	-11.64	-14.69	-17.73	-20.81	-23.86	-26.72	-29.76
375	-1.23	-0.26	-4.03	-7.84	-11.65	-14.70	-17.74	-20.81	-23.86	-26.72	-29.75
625	-1.36	-0.26	-4.03	-7.84	-11.65	-14.70	-17.74	-20.81	-23.86	-26.71	-29.75
875	-1.50	-0.26	-4.03	-7.84	-11.65	-14.69	-17.73	-20.81	-23.86	-26.70	-29.74
1125	-1.66	-0.26	-4.02	-7.83	-11.63	-14.68	-17.71	-20.79	-23.84	-26.68	-29.72
1375	-1.81	-0.26	-4.01	-7.81	-11.62	-14.66	-17.69	-20.77	-23.82	-26.67	-29.71
1625	-1.95	-0.26	-4.01	-7.81	-11.61	-14.65	-17.68	-20.77	-23.82	-26.67	-29.71
1875	-2.07	-0.27	-4.01	-7.81	-11.62	-14.66	-17.69	-20.79	-23.84	-26.71	-29.75
2125	-2.17	-0.27	-4.01	-7.82	-11.64	-14.68	-17.71	-20.83	-23.89	-26.77	-29.82
2625	-2.37	-0.26	-4.01	-7.83	-11.66	-14.72	-17.76	-20.91	-23.98	-26.90	-29.98
3125	-2.53	-0.26	-4.05	-7.89	-11.74	-14.81	-17.89	-21.03	-24.13	-27.07	-30.18
3375	-2.60	-0.27	-4.08	-7.93	-11.80	-14.87	-17.96	-21.10	-24.21	-27.17	-30.29
3875	-2.81	-0.28	-4.12	-7.99	-11.85	-14.94	-18.03	-21.19	-24.32	-27.32	-30.45
4125	-2.91	-0.29	-4.12	-8.00	-11.87	-14.96	-18.06	-21.23	-24.37	-27.39	-30.53
4375	-3.02	-0.29	-4.14	-8.03	-11.91	-15.00	-18.10	-21.29	-24.43	-27.48	-30.62
4500	-3.07	-0.29	-4.15	-8.05	-11.92	-15.02	-18.12	-21.32	-24.47	-27.52	-30.67
4750	-3.20	-0.30	-4.18	-8.09	-11.97	-15.07	-18.18	-21.38	-24.54	-27.61	-30.75
4875	-3.28	-0.30	-4.20	-8.11	-12.00	-15.10	-18.21	-21.41	-24.57	-27.65	-30.79
5125	-3.46	-0.32	-4.22	-8.14	-12.02	-15.12	-18.23	-21.44	-24.59	-27.68	-30.81
5250	-3.57	-0.32	-4.22	-8.15	-12.02	-15.12	-18.22	-21.43	-24.59	-27.68	-30.80
5500	-3.80	-0.33	-4.20	-8.13	-12.00	-15.09	-18.18	-21.41	-24.56	-27.66	-30.74
5625	-3.89	-0.33	-4.20	-8.13	-11.99	-15.09	-18.17	-21.41	-24.56	-27.67	-30.73
5875	-3.97	-0.33	-4.21	-8.16	-12.04	-15.14	-18.21	-21.50	-24.65	-27.77	-30.80
6000	-3.98	-0.34	-4.22	-8.19	-12.08	-15.18	-18.25	-21.58	-24.72	-27.87	-30.88







TYPICAL PERFORMANCE DATA (CONTINUED)

Freq. [MHz]	Return Loss In (at 25°C)										
	[dB]										
	@ Attenuation setting [dB]										
	0	0.25	4	8	12	15	18	21	24	27	30
1	-19.69	-19.40	-18.13	-17.93	-18.22	-18.69	-19.31	-19.28	-19.99	-20.82	-21.75
100	-19.56	-19.29	-18.09	-17.93	-18.22	-18.69	-19.29	-19.26	-19.96	-20.76	-21.66
375	-19.89	-19.64	-18.69	-18.60	-18.92	-19.39	-19.98	-19.96	-20.63	-21.39	-22.21
625	-20.93	-20.66	-19.83	-19.79	-20.15	-20.64	-21.26	-21.23	-21.92	-22.68	-23.46
875	-21.48	-21.19	-20.65	-20.72	-21.16	-21.74	-22.44	-22.41	-23.19	-24.04	-24.91
1125	-20.63	-20.39	-20.30	-20.49	-21.01	-21.65	-22.42	-22.39	-23.28	-24.26	-25.30
1375	-19.44	-19.23	-19.19	-19.33	-19.77	-20.33	-21.02	-20.99	-21.78	-22.68	-23.64
1625	-19.27	-19.03	-18.41	-18.24	-18.48	-18.88	-19.39	-19.36	-19.97	-20.65	-21.37
1875	-20.82	-20.39	-18.32	-17.63	-17.56	-17.76	-18.08	-18.03	-18.43	-18.86	-19.30
2125	-24.01	-23.24	-18.90	-17.64	-17.27	-17.27	-17.37	-17.32	-17.50	-17.70	-17.88
2625	-21.00	-21.39	-20.30	-19.09	-18.30	-17.86	-17.47	-17.45	-17.11	-16.79	-16.46
3125	-20.08	-20.93	-23.50	-23.38	-22.04	-20.85	-19.71	-19.73	-18.67	-17.72	-16.85
3375	-22.98	-24.14	-27.67	-27.74	-25.50	-23.53	-21.75	-21.79	-20.22	-18.88	-17.70
3875	-26.83	-26.22	-27.52	-29.63	-31.94	-30.36	-27.18	-27.23	-24.32	-21.98	-20.08
4125	-25.16	-24.40	-25.53	-27.59	-31.11	-31.93	-29.02	-29.09	-25.66	-22.91	-20.73
4375	-24.26	-23.49	-24.26	-26.00	-29.17	-30.85	-29.06	-29.14	-25.84	-23.01	-20.73
4500	-23.49	-22.76	-23.38	-24.91	-27.62	-29.14	-28.03	-28.10	-25.31	-22.65	-20.43
4750	-21.45	-20.72	-20.86	-21.93	-23.88	-25.31	-25.60	-25.63	-24.25	-22.14	-20.10
4875	-20.36	-19.60	-19.59	-20.48	-22.20	-23.58	-24.28	-24.30	-23.61	-21.92	-20.02
5125	-17.34	-16.71	-16.91	-17.72	-19.17	-20.52	-21.80	-21.80	-22.41	-21.90	-20.53
5250	-15.99	-15.47	-15.89	-16.73	-18.13	-19.49	-20.96	-20.96	-22.12	-22.31	-21.36
5500	-14.07	-13.74	-14.42	-15.27	-16.53	-17.83	-19.42	-19.43	-21.26	-23.02	-23.86
5625	-13.75	-13.50	-14.20	-15.03	-16.21	-17.45	-19.04	-19.05	-21.06	-23.53	-26.05
5875	-15.05	-14.87	-15.10	-15.63	-16.46	-17.46	-18.75	-18.76	-20.50	-22.88	-26.41
6000	-17.27	-17.06	-16.44	-16.53	-17.00	-17.71	-18.65	-18.64	-19.88	-21.44	-23.41

Freq. [MHz]	Return Loss Out (at 25°C)										
	[dB]										
	@ Attenuation setting [dB]										
	0	0.25	4	8	12	15	18	21	24	27	30
1	-19.72	-19.80	-36.22	-26.93	-24.40	-22.35	-20.36	-23.95	-23.01	-26.21	-24.21
100	-19.63	-19.72	-42.80	-27.94	-25.01	-22.78	-20.70	-24.48	-23.48	-26.91	-24.75
375	-20.24	-20.33	-36.82	-26.26	-23.71	-21.78	-19.91	-23.24	-22.40	-25.26	-23.45
625	-21.76	-21.84	-31.18	-24.10	-22.01	-20.41	-18.77	-21.70	-20.99	-23.33	-21.82
875	-22.38	-22.44	-26.40	-22.37	-20.78	-19.40	-17.92	-20.66	-20.02	-22.02	-20.69
1125	-20.81	-20.83	-23.06	-21.12	-20.10	-18.89	-17.53	-20.20	-19.59	-21.31	-20.13
1375	-18.97	-18.94	-21.31	-20.65	-20.18	-19.08	-17.81	-20.51	-19.90	-21.36	-20.33
1625	-18.14	-18.04	-20.90	-21.01	-21.10	-20.07	-18.86	-21.66	-21.02	-22.13	-21.34
1875	-18.54	-18.30	-22.06	-22.71	-23.43	-22.36	-21.10	-24.16	-23.46	-23.96	-23.62
2125	-19.35	-18.97	-24.64	-26.21	-28.27	-27.04	-25.36	-28.91	-28.26	-27.02	-28.01
2625	-18.94	-18.82	-26.67	-30.25	-28.96	-29.65	-26.77	-28.44	-29.55	-29.01	-29.74
3125	-20.26	-20.58	-24.63	-22.79	-20.80	-20.13	-18.66	-20.96	-20.84	-22.23	-21.05
3375	-24.54	-25.02	-24.59	-21.15	-19.30	-18.43	-17.03	-19.53	-19.24	-20.60	-19.38
3875	-25.14	-24.27	-23.05	-20.28	-18.99	-17.88	-16.45	-19.52	-18.99	-20.30	-19.01
4125	-22.63	-21.96	-23.06	-20.78	-19.65	-18.43	-16.91	-20.36	-19.72	-21.07	-19.68
4375	-22.03	-21.38	-23.44	-21.30	-20.22	-18.92	-17.29	-21.07	-20.36	-21.74	-20.24
4500	-21.94	-21.31	-23.65	-21.44	-20.27	-18.97	-17.30	-21.16	-20.44	-21.84	-20.30
4750	-21.82	-21.18	-22.33	-20.31	-19.17	-18.02	-16.49	-20.01	-19.43	-20.64	-19.24
4875	-20.84	-20.26	-20.97	-19.33	-18.38	-17.33	-15.90	-19.21	-18.66	-19.72	-18.46
5125	-17.52	-17.18	-18.25	-17.57	-17.10	-16.20	-14.96	-17.97	-17.45	-18.27	-17.24
5250	-15.87	-15.64	-16.97	-16.74	-16.54	-15.72	-14.58	-17.45	-16.94	-17.63	-16.72
5500	-13.30	-13.22	-15.10	-15.62	-15.97	-15.31	-14.36	-16.96	-16.46	-16.90	-16.25
5625	-12.64	-12.60	-14.63	-15.39	-15.99	-15.40	-14.55	-16.98	-16.50	-16.79	-16.30
5875	-12.65	-12.61	-14.81	-15.82	-16.87	-16.49	-15.96	-17.61	-17.21	-17.11	-17.11
6000	-13.38	-13.28	-15.52	-16.52	-17.77	-17.54	-17.34	-18.11	-17.83	-17.47	-17.83




TYPICAL PERFORMANCE CURVES

Attenuation Accuracy @ 25°C vs. Frequency over
Attenuation settingsAttenuation Accuracy @ 0°C vs. Frequency over
Attenuation settingsAttenuation Accuracy @ 50°C vs. Frequency over
Attenuation settingsAttenuation Accuracy @ 1 - 6000 MHz vs. Attenuation
settings over Temperature




TYPICAL PERFORMANCE CURVES (CONTINUED)


Insertion Loss vs. Frequency over Temperature




R. Loss In vs. Frequency over Attenuation settings



R. Loss Out vs. Frequency over Attenuation settings



IP3 @ 0 dB Attenuation



**SOFTWARE SPECIFICATIONS****SOFTWARE & DOCUMENTATION DOWNLOAD:**

- Mini-Circuits' full software and support package including user guide, Windows GUI, DLL files, programming manual and examples can be downloaded free of charge from: <https://www.minicircuits.com/softwaredownload/patt.html>
- Please contact testsolutions@minicircuits.com for support

MINIMUM SYSTEM REQUIREMENTS:

Parameter	Requirements	
Interface	USB HID or Daisy-chain dynamic addressing	
System Requirements	GUI	Windows 7 or later
	USB API DLL	Windows 7 or later and programming environment with ActiveX or .NET support
	USB Direct Programming	Linux, Windows 7 or later
	Daisy-chain dynamic addressing	An additional Mini-Circuits model supporting dynamic addressing
Hardware	Intel i3 (or equivalent) or later	

APPLICATION PROGRAMMING INTERFACE (API)**ETHERNET SUPPORT:**

- Simple ASCII / SCPI command set for attenuator control
- Communication via HTTP or Telnet
- Supported by most common programming environments

USB SUPPORT (WINDOWS):

- ActiveX COM DLL file for creation of 32-bit programs
- .NET library DLL file for creation of 32 / 64-bit programs
- Supported by most common programming environments


USB SUPPORT (LINUX):

- Direct USB programming using a series of USB interrupt codes
- Full programming instructions and examples available for a wide range of programming environments / languages.



GRAPHICAL USER INTERFACE (GUI) FOR WINDOWS - KEY FEATURES

- Connect via USB to control the module.
- Run GUI in "demo mode" to evaluate software without a hardware connection.



- Manual attenuation setting.
- Sweep and Hop attenuation sequences directed from the PC, or entire sequence loaded into the module.
- Attenuator address configuration and firmware upgrade.
- Attenuation at power up may be set to selected attenuation level or last attenuation state recorded.



**ORDERING INFORMATION**

Please contact Mini-Circuits' Test Solutions department for price and availability: testsolutions@minicircuits.com

Model	Description
RCDAT-6000-30	USB / Ethernet Programmable Attenuator

Included Accessories	Part No.	Description
	MUSB-CBL-3+	3.3 ft (1.0 m) USB cable: USB type A (Male) to USB type Mini-B (Male)

OPTIONAL ACCESSORIES

MUSB-CBL-3+ (spare)	3.3 ft (1.0 m) USB cable: USB type A (Male) to USB type Mini-B (Male)
MUSB-CBL-7+	6.6 ft (2.0 m) USB cable: USB type A (Male) to USB type Mini-B (Male)
CBL-RJ45-MM-5+	5.0 ft (1.5 m) Ethernet cable: RJ45 (Male) to RJ45 (Male) Cat 5E cable
BKT-66-02+	Bracket kit
USB-AC/DC-5	AC/DC +5V _{DC} power adaptor with USB connector ^{10, 11}

10. The USB-AC/DC-5 may be used to provide the 5V_{DC} power input via USB port if operating the module with Ethernet control. Not required if using USB control.

11. Includes power plugs for US, UK, EU, IL, AU & China. Plugs for other countries are also available. If you need a power cord for a country not listed please contact testsolutions@minicircuits.com

NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>

Programmable Attenuator RCDAT-6000-30

Typical Performance Data @ 0°C

FREQUENCY (MHz)	Attenuation relative to Insertion Loss (dB)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	0.25	4.76	9.48	14.46	19.41	24.40	29.37
5	0.25	4.76	9.48	14.46	19.41	24.41	29.37
10	0.25	4.76	9.49	14.47	19.42	24.41	29.37
20	0.24	4.76	9.49	14.47	19.42	24.41	29.37
50	0.25	4.76	9.48	14.46	19.41	24.40	29.37
100	0.24	4.76	9.49	14.47	19.42	24.41	29.37
200	0.24	4.75	9.48	14.46	19.41	24.41	29.36
500	0.24	4.72	9.43	14.41	19.35	24.36	29.31
750	0.23	4.69	9.39	14.36	19.30	24.31	29.24
1000	0.23	4.68	9.37	14.35	19.27	24.30	29.23
1500	0.23	4.67	9.36	14.35	19.25	24.30	29.24
2000	0.23	4.69	9.40	14.42	19.30	24.37	29.36
2500	0.24	4.85	9.64	14.68	19.59	24.69	29.71
3000	0.23	4.84	9.67	14.71	19.61	24.78	29.80
3500	0.22	4.77	9.59	14.64	19.50	24.72	29.74
4000	0.22	4.74	9.57	14.65	19.42	24.69	29.75
4500	0.24	4.85	9.76	14.88	19.62	24.91	29.98
5000	0.26	5.23	10.35	15.49	20.28	25.59	30.62
5500	0.25	5.26	10.48	15.60	20.35	25.71	30.62
6000	0.22	4.99	10.12	15.23	19.75	25.14	29.98

FREQUENCY (MHz)	Attenuation accuracy relative to nominal attenuation setting (dB)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	0.00	0.24	0.52	0.54	0.59	0.60	0.63
5	0.00	0.24	0.52	0.54	0.59	0.59	0.63
10	0.00	0.24	0.51	0.53	0.58	0.59	0.63
20	0.01	0.24	0.51	0.53	0.58	0.59	0.63
50	0.00	0.24	0.52	0.54	0.59	0.60	0.63
100	0.01	0.24	0.51	0.53	0.58	0.59	0.63
200	0.01	0.25	0.52	0.54	0.59	0.59	0.64
500	0.01	0.28	0.57	0.59	0.65	0.64	0.69
750	0.02	0.31	0.61	0.64	0.70	0.69	0.76
1000	0.02	0.32	0.63	0.65	0.73	0.70	0.77
1500	0.03	0.33	0.64	0.65	0.75	0.70	0.76
2000	0.02	0.31	0.60	0.59	0.70	0.63	0.64
2500	0.01	0.16	0.36	0.32	0.41	0.31	0.29
3000	0.02	0.16	0.33	0.29	0.39	0.23	0.20
3500	0.03	0.23	0.41	0.36	0.50	0.28	0.26
4000	0.03	0.26	0.43	0.35	0.58	0.31	0.25
4500	0.01	0.15	0.24	0.12	0.38	0.09	0.02
5000	-0.01	-0.23	-0.35	-0.49	-0.28	-0.59	-0.61
5500	0.00	-0.26	-0.48	-0.60	-0.35	-0.71	-0.62
6000	0.03	0.01	-0.12	-0.23	0.25	-0.14	0.02

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCStore/terms.jsp



Programmable Attenuator RCDAT-6000-30

Typical Performance Data @ 0°C

FREQUENCY (MHz)	Input VSWR (:1)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	1.29	1.18	1.07	1.12	1.06	1.04	1.06
5	1.28	1.17	1.05	1.11	1.04	1.01	1.04
10	1.28	1.17	1.05	1.11	1.04	1.01	1.04
20	1.28	1.17	1.05	1.11	1.04	1.01	1.04
50	1.28	1.17	1.06	1.11	1.04	1.01	1.04
100	1.29	1.18	1.07	1.12	1.04	1.02	1.04
200	1.29	1.19	1.08	1.13	1.03	1.04	1.04
500	1.33	1.24	1.13	1.18	1.08	1.10	1.08
750	1.33	1.28	1.18	1.24	1.11	1.14	1.11
1000	1.30	1.29	1.21	1.28	1.13	1.17	1.13
1500	1.36	1.32	1.23	1.28	1.15	1.18	1.15
2000	1.51	1.32	1.22	1.22	1.17	1.15	1.17
2500	1.35	1.16	1.12	1.09	1.15	1.12	1.16
3000	1.26	1.11	1.01	1.03	1.09	1.08	1.09
3500	1.22	1.16	1.08	1.11	1.02	1.02	1.02
4000	1.43	1.30	1.24	1.22	1.20	1.16	1.19
4500	1.59	1.43	1.44	1.39	1.46	1.42	1.46
5000	1.18	1.36	1.53	1.52	1.65	1.64	1.66
5500	1.35	1.38	1.49	1.51	1.64	1.67	1.65
6000	1.46	1.30	1.29	1.29	1.37	1.41	1.38

FREQUENCY (MHz)	Output VSWR (:1)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	1.29	1.09	1.07	1.05	1.06	1.05	1.04
5	1.28	1.08	1.05	1.03	1.04	1.03	1.01
10	1.28	1.08	1.05	1.02	1.04	1.03	1.01
20	1.28	1.08	1.05	1.02	1.04	1.03	1.01
50	1.28	1.08	1.06	1.02	1.05	1.04	1.01
100	1.29	1.09	1.07	1.02	1.06	1.05	1.02
200	1.29	1.10	1.08	1.03	1.07	1.06	1.03
500	1.33	1.16	1.14	1.08	1.14	1.12	1.09
750	1.34	1.20	1.19	1.12	1.19	1.18	1.14
1000	1.33	1.23	1.23	1.16	1.24	1.23	1.19
1500	1.42	1.30	1.28	1.24	1.26	1.26	1.24
2000	1.54	1.35	1.28	1.29	1.24	1.24	1.26
2500	1.28	1.17	1.16	1.23	1.17	1.17	1.20
3000	1.20	1.04	1.07	1.08	1.11	1.10	1.09
3500	1.30	1.17	1.13	1.09	1.09	1.10	1.09
4000	1.49	1.35	1.27	1.32	1.24	1.24	1.27
4500	1.60	1.49	1.45	1.53	1.48	1.44	1.47
5000	1.19	1.42	1.55	1.61	1.68	1.63	1.62
5500	1.40	1.44	1.56	1.53	1.66	1.64	1.58
6000	1.56	1.39	1.39	1.29	1.37	1.40	1.35

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCStore/terms.jsp



Programmable Attenuator RCDAT-6000-30

Typical Performance Data @ 0°C

FREQUENCY (MHz)	IP3 (dBm)	Insertion Loss @P _{IN} =0 dBm (dB)	Insertion Loss @P _{IN} =+20 dBm (dB)
1	50.30	-	-
5	54.15	-	-
10	56.12	1.10	1.01
20	58.14	1.12	1.01
50	57.49	1.37	1.15
100	57.84	1.30	1.08
200	58.18	1.17	1.02
500	58.50	1.51	1.29
750	57.91	1.57	1.37
1000	54.54	1.79	1.61
1500	60.48	1.56	1.41
2000	55.56	1.98	1.85
2500	59.38	2.01	1.83
3000	60.26	2.23	2.05
3500	60.53	2.22	2.05
4000	54.04	2.37	2.20
4500	51.01	2.66	2.49
5000	55.79	2.91	2.69
5500	51.54	3.35	3.25
6000	49.78	3.33	3.26

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCStore/terms.jsp



Programmable Attenuator RCDAT-6000-30

Typical Performance Data @ +25°C

FREQUENCY (MHz)	Attenuation relative to Insertion Loss (dB)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	0.24	4.74	9.46	14.42	19.38	24.37	29.34
5	0.24	4.74	9.46	14.43	19.39	24.38	29.34
10	0.24	4.74	9.46	14.43	19.39	24.39	29.34
20	0.24	4.74	9.46	14.44	19.39	24.40	29.34
50	0.24	4.74	9.46	14.43	19.39	24.39	29.33
100	0.24	4.74	9.47	14.44	19.40	24.40	29.35
200	0.24	4.74	9.46	14.43	19.39	24.39	29.34
500	0.24	4.70	9.41	14.38	19.33	24.34	29.27
750	0.23	4.68	9.37	14.34	19.28	24.30	29.22
1000	0.23	4.67	9.36	14.33	19.26	24.30	29.21
1500	0.22	4.66	9.35	14.33	19.24	24.29	29.22
2000	0.23	4.67	9.38	14.39	19.28	24.36	29.34
2500	0.24	4.82	9.61	14.64	19.55	24.66	29.67
3000	0.23	4.82	9.65	14.68	19.59	24.76	29.76
3500	0.22	4.75	9.57	14.61	19.46	24.70	29.71
4000	0.22	4.72	9.54	14.62	19.39	24.67	29.72
4500	0.23	4.83	9.73	14.85	19.59	24.88	29.96
5000	0.26	5.20	10.32	15.46	20.25	25.56	30.59
5500	0.25	5.21	10.42	15.52	20.28	25.65	30.57
6000	0.22	4.95	10.07	15.17	19.68	25.10	29.93

FREQUENCY (MHz)	Attenuation accuracy relative to nominal attenuation setting (dB)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	0.01	0.26	0.54	0.58	0.62	0.63	0.67
5	0.01	0.26	0.54	0.57	0.61	0.62	0.66
10	0.01	0.26	0.54	0.57	0.61	0.61	0.66
20	0.01	0.26	0.54	0.56	0.61	0.60	0.66
50	0.01	0.26	0.54	0.57	0.61	0.61	0.67
100	0.01	0.26	0.53	0.56	0.60	0.60	0.65
200	0.01	0.26	0.54	0.57	0.61	0.61	0.66
500	0.02	0.30	0.59	0.63	0.67	0.66	0.73
750	0.02	0.32	0.63	0.66	0.72	0.70	0.78
1000	0.03	0.33	0.64	0.67	0.74	0.70	0.79
1500	0.03	0.34	0.65	0.67	0.76	0.71	0.78
2000	0.02	0.33	0.62	0.61	0.72	0.64	0.66
2500	0.01	0.18	0.39	0.36	0.45	0.34	0.33
3000	0.02	0.18	0.35	0.32	0.41	0.24	0.24
3500	0.03	0.26	0.43	0.39	0.54	0.30	0.29
4000	0.03	0.28	0.46	0.38	0.61	0.33	0.28
4500	0.02	0.18	0.27	0.15	0.41	0.12	0.04
5000	-0.01	-0.20	-0.32	-0.46	-0.25	-0.56	-0.59
5500	0.00	-0.21	-0.42	-0.52	-0.27	-0.65	-0.57
6000	0.03	0.05	-0.07	-0.17	0.32	-0.10	0.07

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Programmable Attenuator RCDAT-6000-30

Typical Performance Data @ +25°C

FREQUENCY (MHz)	Input VSWR (:1)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	1.30	1.20	1.09	1.15	1.04	1.05	1.04
5	1.29	1.20	1.08	1.14	1.01	1.03	1.01
10	1.29	1.20	1.08	1.14	1.01	1.03	1.01
20	1.29	1.20	1.08	1.14	1.01	1.03	1.01
50	1.29	1.20	1.08	1.14	1.01	1.03	1.01
100	1.30	1.20	1.09	1.14	1.02	1.04	1.02
200	1.31	1.21	1.10	1.16	1.04	1.06	1.04
500	1.34	1.27	1.16	1.22	1.09	1.12	1.09
750	1.34	1.31	1.21	1.28	1.14	1.17	1.14
1000	1.31	1.32	1.24	1.32	1.17	1.21	1.17
1500	1.38	1.35	1.27	1.33	1.19	1.22	1.19
2000	1.52	1.34	1.24	1.24	1.17	1.16	1.17
2500	1.35	1.17	1.11	1.08	1.13	1.09	1.13
3000	1.27	1.13	1.03	1.06	1.07	1.07	1.07
3500	1.25	1.20	1.12	1.15	1.05	1.07	1.05
4000	1.47	1.33	1.28	1.25	1.23	1.19	1.23
4500	1.59	1.43	1.43	1.38	1.45	1.41	1.45
5000	1.16	1.33	1.50	1.49	1.62	1.61	1.63
5500	1.37	1.38	1.47	1.49	1.61	1.64	1.62
6000	1.45	1.30	1.27	1.29	1.35	1.39	1.35

FREQUENCY (MHz)	Output VSWR (:1)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	1.30	1.11	1.09	1.04	1.08	1.07	1.05
5	1.29	1.10	1.08	1.01	1.07	1.06	1.02
10	1.29	1.10	1.08	1.01	1.07	1.06	1.02
20	1.29	1.10	1.08	1.01	1.07	1.06	1.02
50	1.29	1.10	1.08	1.01	1.07	1.06	1.03
100	1.30	1.11	1.09	1.02	1.08	1.07	1.03
200	1.31	1.12	1.10	1.04	1.10	1.09	1.05
500	1.34	1.18	1.17	1.10	1.17	1.16	1.12
750	1.36	1.23	1.22	1.15	1.23	1.22	1.18
1000	1.35	1.26	1.27	1.20	1.28	1.27	1.23
1500	1.44	1.33	1.32	1.28	1.31	1.31	1.29
2000	1.54	1.35	1.29	1.29	1.24	1.25	1.26
2500	1.28	1.17	1.14	1.21	1.14	1.14	1.17
3000	1.21	1.05	1.07	1.06	1.10	1.09	1.07
3500	1.31	1.20	1.17	1.13	1.13	1.15	1.14
4000	1.54	1.39	1.31	1.36	1.26	1.27	1.31
4500	1.62	1.51	1.46	1.55	1.49	1.45	1.49
5000	1.20	1.42	1.55	1.61	1.68	1.63	1.61
5500	1.43	1.45	1.57	1.51	1.65	1.64	1.58
6000	1.56	1.39	1.38	1.27	1.35	1.39	1.34

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Programmable Attenuator RCDAT-6000-30

Typical Performance Data @ +25°C

FREQUENCY (MHz)	IP3 (dBm)	Insertion Loss @P _{IN} =0 dBm (dB)	Insertion Loss @P _{IN} =+20 dBm (dB)
1	51.37	-	-
5	53.43	-	-
10	55.67	1.15	1.05
20	57.90	1.17	1.07
50	57.50	1.45	1.28
100	57.82	1.37	1.21
200	58.52	1.24	1.16
500	59.92	1.58	1.46
750	56.71	1.64	1.52
1000	54.53	1.85	1.78
1500	60.18	1.63	1.58
2000	55.54	2.07	2.02
2500	60.30	2.09	2.02
3000	60.40	2.33	2.26
3500	59.23	2.34	2.26
4000	52.80	2.53	2.46
4500	51.41	2.85	2.79
5000	58.90	3.22	3.14
5500	52.27	3.41	3.31
6000	50.26	3.29	3.21

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Programmable Attenuator RCDAT-6000-30

Typical Performance Data @ +50°C

FREQUENCY (MHz)	Attenuation relative to Insertion Loss (dB)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	0.24	4.71	9.42	14.38	19.34	24.34	29.27
5	0.24	4.71	9.42	14.38	19.35	24.34	29.26
10	0.24	4.71	9.42	14.38	19.35	24.35	29.27
20	0.24	4.71	9.43	14.38	19.35	24.35	29.28
50	0.24	4.71	9.42	14.38	19.35	24.35	29.27
100	0.24	4.72	9.43	14.39	19.36	24.36	29.29
200	0.24	4.71	9.42	14.38	19.35	24.36	29.28
500	0.23	4.68	9.37	14.33	19.29	24.30	29.21
750	0.23	4.66	9.34	14.30	19.25	24.27	29.17
1000	0.22	4.66	9.34	14.30	19.24	24.27	29.17
1500	0.22	4.65	9.33	14.30	19.21	24.27	29.18
2000	0.23	4.65	9.35	14.34	19.23	24.31	29.27
2500	0.24	4.78	9.57	14.58	19.49	24.60	29.59
3000	0.23	4.79	9.60	14.62	19.53	24.70	29.69
3500	0.22	4.72	9.54	14.56	19.42	24.65	29.64
4000	0.22	4.70	9.51	14.57	19.33	24.60	29.65
4500	0.23	4.79	9.68	14.78	19.51	24.80	29.87
5000	0.26	5.17	10.27	15.39	20.18	25.48	30.51
5500	0.24	5.16	10.33	15.42	20.17	25.55	30.46
6000	0.21	4.92	10.02	15.10	19.61	25.04	29.87

FREQUENCY (MHz)	Attenuation accuracy relative to nominal attenuation setting (dB)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	0.01	0.29	0.59	0.63	0.66	0.66	0.73
5	0.01	0.29	0.58	0.62	0.65	0.66	0.74
10	0.01	0.29	0.58	0.62	0.65	0.65	0.73
20	0.01	0.29	0.57	0.62	0.65	0.65	0.73
50	0.01	0.29	0.58	0.62	0.65	0.65	0.73
100	0.01	0.28	0.57	0.61	0.64	0.64	0.71
200	0.01	0.29	0.58	0.62	0.65	0.64	0.72
500	0.02	0.32	0.63	0.67	0.71	0.70	0.79
750	0.03	0.34	0.66	0.70	0.75	0.73	0.83
1000	0.03	0.34	0.66	0.70	0.76	0.73	0.83
1500	0.03	0.36	0.67	0.70	0.79	0.73	0.82
2000	0.03	0.35	0.65	0.66	0.77	0.69	0.73
2500	0.02	0.22	0.43	0.42	0.51	0.40	0.41
3000	0.02	0.21	0.40	0.38	0.47	0.30	0.31
3500	0.04	0.28	0.46	0.44	0.58	0.35	0.36
4000	0.03	0.30	0.49	0.43	0.67	0.40	0.35
4500	0.02	0.21	0.32	0.22	0.49	0.20	0.13
5000	0.00	-0.17	-0.27	-0.39	-0.17	-0.48	-0.51
5500	0.01	-0.16	-0.33	-0.42	-0.17	-0.55	-0.46
6000	0.04	0.08	-0.02	-0.10	0.39	-0.04	0.13

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Programmable Attenuator RCDAT-6000-30

Typical Performance Data @ +50°C

FREQUENCY (MHz)	Input VSWR (:1)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	1.32	1.24	1.12	1.18	1.05	1.07	1.05
5	1.31	1.23	1.11	1.18	1.02	1.06	1.02
10	1.31	1.23	1.12	1.18	1.02	1.06	1.02
20	1.31	1.23	1.12	1.18	1.02	1.06	1.02
50	1.31	1.23	1.12	1.18	1.03	1.06	1.02
100	1.31	1.23	1.12	1.18	1.03	1.06	1.03
200	1.32	1.24	1.13	1.19	1.05	1.08	1.05
500	1.36	1.30	1.20	1.26	1.12	1.16	1.12
750	1.36	1.34	1.25	1.32	1.17	1.21	1.17
1000	1.33	1.36	1.28	1.35	1.20	1.24	1.20
1500	1.39	1.38	1.30	1.36	1.22	1.25	1.22
2000	1.53	1.35	1.25	1.26	1.18	1.18	1.18
2500	1.36	1.18	1.10	1.09	1.11	1.07	1.11
3000	1.29	1.16	1.06	1.09	1.04	1.06	1.04
3500	1.27	1.23	1.16	1.19	1.09	1.10	1.09
4000	1.48	1.34	1.29	1.26	1.24	1.20	1.23
4500	1.59	1.42	1.42	1.37	1.43	1.39	1.43
5000	1.15	1.31	1.47	1.46	1.59	1.58	1.59
5500	1.38	1.37	1.45	1.47	1.58	1.61	1.59
6000	1.44	1.30	1.27	1.29	1.34	1.38	1.34

FREQUENCY (MHz)	Output VSWR (:1)						
	0.25 dB	5 dB	10 dB	15 dB	20 dB	25 dB	30 dB
1	1.32	1.14	1.12	1.05	1.12	1.11	1.07
5	1.31	1.13	1.11	1.04	1.11	1.10	1.06
10	1.31	1.13	1.11	1.04	1.11	1.10	1.06
20	1.31	1.13	1.11	1.04	1.11	1.10	1.06
50	1.31	1.13	1.11	1.04	1.11	1.10	1.06
100	1.31	1.13	1.11	1.04	1.11	1.10	1.06
200	1.32	1.15	1.13	1.06	1.13	1.12	1.08
500	1.36	1.21	1.20	1.13	1.20	1.19	1.15
750	1.37	1.25	1.26	1.18	1.26	1.25	1.21
1000	1.36	1.28	1.30	1.23	1.31	1.30	1.26
1500	1.45	1.36	1.35	1.31	1.34	1.34	1.32
2000	1.55	1.37	1.30	1.31	1.26	1.26	1.28
2500	1.29	1.16	1.12	1.19	1.11	1.11	1.15
3000	1.22	1.07	1.07	1.03	1.09	1.08	1.05
3500	1.32	1.22	1.20	1.16	1.16	1.18	1.17
4000	1.55	1.41	1.32	1.38	1.28	1.28	1.32
4500	1.63	1.52	1.46	1.55	1.48	1.44	1.48
5000	1.20	1.42	1.54	1.60	1.67	1.61	1.60
5500	1.45	1.44	1.56	1.49	1.64	1.63	1.56
6000	1.57	1.39	1.39	1.26	1.34	1.39	1.33

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Programmable Attenuator RCDAT-6000-30

Typical Performance Data @ +50°C

FREQUENCY (MHz)	IP3 (dBm)	Insertion Loss @P _{IN} =0 dBm (dB)	Insertion Loss @P _{IN} =+20 dBm (dB)
1	49.85	-	-
5	54.14	-	-
10	55.81	1.19	1.09
20	58.36	1.22	1.12
50	57.25	1.47	1.26
100	57.67	1.44	1.24
200	58.63	1.25	1.12
500	58.32	1.59	1.39
750	56.59	1.67	1.48
1000	54.69	1.89	1.72
1500	60.33	1.71	1.58
2000	55.38	2.17	2.05
2500	59.03	2.19	2.03
3000	62.07	2.43	2.24
3500	59.95	2.43	2.26
4000	52.86	2.65	2.49
4500	51.20	3.03	2.86
5000	58.22	3.39	3.17
5500	51.49	3.56	3.45
6000	50.07	3.43	3.35

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCStore/terms.jsp




Programmable Attenuator


RCDAT-6000-30

Typical Performance Curves @ 0°C


Attenuation Accuracy
vs. Frequency over Attenuation settings




Attenuation relative to I.L.
vs. Frequency over Attenuation settings




Input VSWR
vs. Frequency over Attenuation settings




Output VSWR
vs. Frequency over Attenuation settings



IP3 @ 0dB Attenuation



Insertion Loss



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



www.minicircuits.com P.O. Box 35166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com


REV. OR
RCDAT-6000-30
140304
Page 1 of 3

Programmable Attenuator


RCDAT-6000-30

Typical Performance Curves @ +25°C


Attenuation Accuracy
vs. Frequency over Attenuation settings




Attenuation relative to I.L.
vs. Frequency over Attenuation settings




Input VSWR
vs. Frequency over Attenuation settings




Output VSWR
vs. Frequency over Attenuation settings



IP3 @ 0dB Attenuation



Insertion Loss



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp




Programmable Attenuator


RCDAT-6000-30

Typical Performance Curves @ +50°C


Attenuation Accuracy
vs. Frequency over Attenuation settings




Attenuation relative to I.L.
vs. Frequency over Attenuation settings




Input VSWR
vs. Frequency over Attenuation settings




Output VSWR
vs. Frequency over Attenuation settings



IP3 @ 0dB Attenuation



Insertion Loss




Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Outline Dimensions

MS1897



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	WT. GRAMS
MS1897	3.00 (76.2)	2.50 (63.5)	.85 (21.6)	.28 (7.1)	.50 (12.7)	2.200 (55.88)	2.700 (68.58)	.188 (4.76)	2.50 (63.5)	2.125 (53.98)	.188 (4.76)	.144 (3.66)	3.75 (95.3)	3.375 (85.72)	.100 (2.54)	200

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Nickel Plated Aluminum.

Mini-Circuits®
 ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Environmental Specifications ENV55T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 85° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3