



ULTRA LOW NOISE, MEDIUM CURRENT

E-PHEMT Transistor

SAV-541+

50Ω 0.045-6GHz

THE BIG DEAL

- Low Noise Figure, 0.5 dB
- Gain, 17 dB at 2 GHz
- High Output IP3, +33 dBm
- Output Power at 1dB comp., +20 dBm
- High Current, 60mA
- Wide bandwidth
- External biasing and matching required
- May be used as replacement ^{a,b} for Avago ATF-54143



Generic photo used for illustration purposes only

CASE STYLE: MMM1362

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


APPLICATIONS

- Cellular
- ISM
- GSM
- WCDMA
- WiMax
- WLAN
- UNII and HIPERLAN

PRODUCT OVERVIEW

SAV-541+ is an ultra-low noise, high IP3 transistor device, manufactured using E-PHEMT* technology enabling it to work with a single positive supply voltage. It has outstanding Noise Figure, particularly below 2.5 GHz, and when combining this noise figure with high IP3 performance in a single device it makes it an ideal amplifier for demanding base station applications. We offer these units assembled into a complete module, 50Ω in/out, noise matched and fully specified. For more information please see our TAMP family of models on our web site.

SIMPLIFIED SCHEMATIC AND PIN DESCRIPTION



| Function | Pin Number | Description |
|----------|------------|---|
| Source | 2 & 4 | Source terminal, normally connected to ground |
| Gate | 3 | Gate used for RF Input |
| Drain | 1 | Drain used for RF output |

* Enhancement mode Pseudomorphic High Electron Mobility Transistor.

a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.
 b. The Avago ATF-54143 part number is used for identification and comparison purposes only.

REV. F
ECO-010314
SAV-541+
211022





ULTRA LOW NOISE, MEDIUM CURRENT

E-PHEMT Transistor

SAV-541+

Mini-Circuits

ELECTRICAL SPECIFICATIONS AT $T_{AMB}=25^{\circ}\text{C}$, FREQUENCY 0.045 TO 6 GHz

| Symbol | Parameter | Condition | Min. | Typ. | Max. | Units |
|--|----------------------------------|---|-------------------------|-------------------------|-------------------------|---------------|
| DC Specifications | | | | | | |
| V_{GS} | Operational Gate Voltage | $V_{DS}=3\text{V}, I_{DS}=60\text{ mA}$ | 0.37 | 0.48 | 0.69 | V |
| V_{TH} | Threshold Voltage | $V_{DS}=3\text{V}, I_{DS}=4\text{ mA}$ | 0.18 | 0.26 | 0.38 | V |
| I_{DSS} | Saturated Drain Current | $V_{DS}=3\text{V}, V_{GS}=0\text{ V}$ | | 1.0 | 5.0 | μA |
| G_M | Transconductance | $V_{DS}=3\text{V}, G_m=\Delta I_{DS}/\Delta V_{GS}$ $\Delta V_{GS}=V_{GS1}-V_{GS2}$ $V_{GS1}=V_{GS}$ at $I_{DS}=60\text{ mA}$ $V_{GS2}=V_{GS1}+0.05\text{V}$ | — — 230 — — | — — 392 — — | — — 560 — — | mS |
| I_{GSS} | Gate leakage Current | $V_{GD}=V_{GS}=-3\text{V}$ | | | 200 | μA |
| RF Specifications, $Z_0=50\text{ Ohms}$ (Figure 1) | | | | | | |
| $NF^{(1)}$ | Noise Figure | $V_{DS}=3\text{V}, I_{DS}=60\text{ mA}$ | $f=0.9\text{ GHz}$ | 0.4 | — | dB |
| | | | $f=2.0\text{ GHz}$ | 0.5 | 0.9 | |
| | | | $f=3.9\text{ GHz}$ | 1.0 | — | |
| | | $V_{DS}=4\text{V}, I_{DS}=60\text{ mA}$ | $f=5.8\text{ GHz}$ | 1.9 | — | |
| | | | $f=2.0\text{ GHz}$ | 0.5 | — | |
| Gain | Gain | $V_{DS}=3\text{V}, I_{DS}=60\text{ mA}$ | $f=0.9\text{ GHz}$ | — | 23.2 | — |
| | | | $f=2.0\text{ GHz}$ | 15.0 | 17.6 | 18.5 |
| | | | $f=3.9\text{ GHz}$ | — | 12.5 | — |
| | | $V_{DS}=4\text{V}, I_{DS}=60\text{ mA}$ | $f=5.8\text{ GHz}$ | — | 8.7 | — |
| | | | $f=2.0\text{ GHz}$ | — | 17.4 | — |
| OIP3 | Output IP3 | $V_{DS}=3\text{V}, I_{DS}=60\text{ mA}$ | $f=0.9\text{ GHz}$ | — | 32.6 | dBm |
| | | | $f=2.0\text{ GHz}$ | 30.0 | 33.1 | |
| | | | $f=3.9\text{ GHz}$ | — | 33.0 | |
| | | $V_{DS}=4\text{V}, I_{DS}=60\text{ mA}$ | $f=5.8\text{ GHz}$ | — | 31.0 | |
| | | | $f=2.0\text{ GHz}$ | — | 35.1 | |
| $P_{1dB}^{(2)}$ | Power output at 1 dB Compression | $V_{DS}=3\text{V}, I_{DS}=60\text{ mA}$ | $f=0.9\text{ GHz}$ | — | 19.1 | dBm |
| | | | $f=2.0\text{ GHz}$ | — | 19.2 | |
| | | | $f=3.9\text{ GHz}$ | — | 19.0 | |
| | | $V_{DS}=4\text{V}, I_{DS}=60\text{ mA}$ | $f=5.8\text{ GHz}$ | — | 18.2 | |
| | | | $f=2.0\text{ GHz}$ | — | 21.5 | |

MAXIMUM RATINGS⁽³⁾

| Symbol | Parameter | Max. | Units |
|----------------|------------------------|------------|-----------------------------|
| $V_{DS}^{(4)}$ | Drain-Source Voltage | 5 | V |
| $V_{GS}^{(4)}$ | Gate-Source Voltage | -5 to 0.7 | V |
| $V_{GD}^{(4)}$ | Gate-Drain Voltage | -5 to 0.7 | V |
| $I_{DS}^{(4)}$ | Drain Current | 120 | mA |
| I_{GS} | Gate Current | 2 | mA |
| P_{DISS} | Total Dissipated Power | 360 | mW |
| $P_{IN}^{(5)}$ | RF Input Power | 17 | dBm |
| T_{CH} | Channel Temperature | 150 | $^{\circ}\text{C}$ |
| T_{OP} | Operating Temperature | -40 to 85 | $^{\circ}\text{C}$ |
| T_{STD} | Storage Temperature | -65 to 150 | $^{\circ}\text{C}$ |
| θ_{JC} | Thermal Resistance | 160 | $^{\circ}\text{C}/\text{W}$ |

(1) Includes test board loss (tested on Mini-Circuits TB-471+ test board)
 (2) Drain current was allowed to increase during compression measurements.
 (3) Operation of this device above any one of these parameters may cause permanent damage.
 (4) Assumes DC quiescent conditions.
 (5) IGS is limited to 2 mA during test.





CHARACTERIZATION TEST CIRCUIT




Fig 1. Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Test Board TB-471+)

Gain, Output power at 1dB compression (P1 dB) and output IP3 (OIP3) are measured using R&S Network Analyzer ZVA-24. Noise Figure measured using Agilent Noise Figure meter N8975A and Noise Source N4000A.

Conditions:

1. Drain voltage (with reference to source, VDS)= 3 or 4V as shown.
2. Gate Voltage (with reference to source, VGS) is set to obtain desired Drain-Source current (IDS) as shown in graphs or specification table.
3. Gain: Pin= -25dBm
4. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.
5. No external matching components used.










Fig 2. Test Board used for characterization, Mini-Circuits P/N TB-471+ (Material: Rogers 4350, Thickness: 0.02")









TYPICAL PERFORMANCE CURVES



(1) Includes test board loss, set-up and conditions per Figure 1.
 (2) Measured using HP4155B semiconductor parameter analyzer.
 (3) F Min is minimum Noise Figure.
 (4) Drain Current was allowed to increase during compression measurement.



TYPICAL PERFORMANCE CURVES




(1) Includes test board loss, set-up and conditions per Figure 1.
 (2) Measured using HP4155B semiconductor parameter analyzer.
 (3) F Min is minimum Noise Figure.
 (4) Drain Current was allowed to increase during compression measurement.




TYPICAL PERFORMANCE CURVES


GAIN vs FREQUENCY & TEMPERATURE (1)
@ VDS=3V, IDS=60mA




OIP3 vs FREQUENCY & TEMPERATURE (1)
@ VDS=3V, IDS=60mA




P1dB vs FREQUENCY & TEMPERATURE (1,4)
@ VDS=3V, IDS=60mA




NF vs FREQUENCY & TEMPERATURE (1)
@ VDS=4V, IDS=60mA



GAIN vs FREQUENCY & TEMPERATURE (1)
@ VDS=4V, IDS=60mA



OIP3 vs FREQUENCY & TEMPERATURE (1)
@ VDS=4V, IDS=60mA





(1) Includes test board loss, set-up and conditions per Figure 1.
 (2) Measured using HP4155B semiconductor parameter analyzer.
 (3) F Min is minimum Noise Figure.
 (4) Drain Current was allowed to increase during compression measurement.



ULTRA LOW NOISE, MEDIUM CURRENT E-PHEMT Transistor

SAV-541+

TYPICAL PERFORMANCE CURVES



- (1) Includes test board loss, set-up and conditions per Figure 1.
- (2) Measured using HP4155B semiconductor parameter analyzer.
- (3) F Min is minimum Noise Figure.
- (4) Drain Current was allowed to increase during compression measurement.

REFERENCE PLANE LOCATION FOR S AND NOISE PARAMETERS

(see data in pages 8-11) (Refer to Application Note AN-60-040)




Fig 3. Reference Plane Location

Noise parameters were measured over 0.5 to 6 GHz by Modelithics® using a solid state tuner-based noise parameter (NP) test system available from Maury Microwave. F Min, optimum source reflection coefficient and noise resistance values are calculated values based on a set of measurements made at approximately 16 different impedances. Some data smoothing was applied to arrive at the presented data set.

S-parameters were measured by Modelithics® on an Anritsu Lightning vector network analyzer over 0.1 to 18GHz using 350um pitch RF probes from GGB industries combined with customized thru-reflect-line (TRL) calibration standards. The reference plane is at the device package leads, as shown in the picture.



ULTRA LOW NOISE, MEDIUM CURRENT


E-PHEMT Transistor

SAV-541+

TYPICAL S-PARAMETERS, $V_{DS}=3V$ AND $I_{DS}=40\text{ MA}$ (FIG. 3)

| Freq. (GHz) | S11 | | S21 | | | S12 | | S22 | | MSG/MAG (dB) |
|-------------|------|--------|------|----------|--------|-------|--------|------|--------|--------------|
| | Mag. | Ang. | Mag. | Mag (dB) | Ang. | Mag. | Ang. | Mag. | Ang. | |
| 0.1 | 0.99 | -16.6 | 25.3 | 28.1 | 169.5 | 0.008 | 89.1 | 0.55 | -14.7 | 34.8 |
| 0.5 | 0.86 | -74.6 | 19.6 | 25.8 | 132.2 | 0.035 | 54.4 | 0.43 | -55.3 | 27.5 |
| 0.9 | 0.75 | -112.6 | 14.2 | 23.0 | 109.0 | 0.047 | 40.5 | 0.32 | -83.3 | 24.8 |
| 1.0 | 0.74 | -120.4 | 13.2 | 22.4 | 104.6 | 0.049 | 38.4 | 0.30 | -89.5 | 24.3 |
| 1.5 | 0.68 | -149.6 | 9.5 | 19.6 | 86.7 | 0.057 | 31.3 | 0.23 | -114.1 | 22.3 |
| 1.9 | 0.66 | -166.7 | 7.7 | 17.8 | 75.4 | 0.062 | 27.5 | 0.19 | -131.2 | 21.0 |
| 2.0 | 0.66 | -170.5 | 7.4 | 17.4 | 72.9 | 0.063 | 26.6 | 0.19 | -135.2 | 20.7 |
| 2.5 | 0.65 | 172.8 | 6.0 | 15.6 | 61.0 | 0.07 | 22.9 | 0.17 | -153.9 | 19.3 |
| 3.0 | 0.65 | 158.7 | 5.0 | 14.1 | 50.2 | 0.077 | 19.5 | 0.16 | -171.3 | 18.2 |
| 4.0 | 0.66 | 134.4 | 3.8 | 11.6 | 30.0 | 0.091 | 11.9 | 0.16 | 156.7 | 15.8 |
| 5.0 | 0.68 | 113.5 | 3.0 | 9.7 | 11.1 | 0.104 | 2.7 | 0.18 | 130.5 | 13.3 |
| 6.0 | 0.71 | 94.7 | 2.5 | 8.0 | -7.1 | 0.118 | -7.5 | 0.22 | 109.1 | 11.7 |
| 7.0 | 0.75 | 77.8 | 2.1 | 6.4 | -24.7 | 0.13 | -18.3 | 0.28 | 90.7 | 10.5 |
| 8.0 | 0.78 | 62.4 | 1.8 | 5.0 | -41.5 | 0.14 | -29.4 | 0.33 | 74.8 | 9.6 |
| 9.0 | 0.82 | 47.8 | 1.5 | 3.6 | -57.8 | 0.146 | -41.0 | 0.40 | 60.0 | 9.0 |
| 10.0 | 0.85 | 33.7 | 1.3 | 2.3 | -73.9 | 0.15 | -52.7 | 0.46 | 46.1 | 8.8 |
| 11.0 | 0.88 | 20.6 | 1.1 | 1.0 | -89.3 | 0.152 | -64.4 | 0.53 | 33.2 | 8.7 |
| 12.0 | 0.90 | 8.4 | 1.0 | -0.2 | -104.0 | 0.153 | -75.8 | 0.58 | 21.2 | 8.0 |
| 13.0 | 0.91 | -3.5 | 0.9 | -1.3 | -118.3 | 0.154 | -87.1 | 0.62 | 10.3 | 7.5 |
| 14.0 | 0.92 | -14.4 | 0.8 | -2.3 | -131.9 | 0.154 | -97.9 | 0.66 | 0.0 | 7.0 |
| 15.0 | 0.94 | -23.0 | 0.7 | -3.6 | -143.0 | 0.148 | -106.3 | 0.70 | -8.7 | 6.5 |
| 16.0 | 0.95 | -30.4 | 0.6 | -4.9 | -153.0 | 0.139 | -114.2 | 0.75 | -16.6 | 6.1 |
| 17.0 | 0.95 | -39.0 | 0.5 | -6.0 | -164.0 | 0.134 | -122.6 | 0.77 | -25.2 | 5.7 |
| 18.0 | 0.94 | -48.3 | 0.5 | -6.9 | -175.7 | 0.131 | -131.4 | 0.79 | -33.9 | 5.4 |

MAXIMUM STABLE GAIN (MSG)/MAXIMUM AVAILABLE GAIN (MAG) vs. FREQUENCY



Notes:
 F Min.: Minimum Noise Figure
 GOpt: Optimum Source Reflection Coefficient
 Rn: Equivalent noise resistance

TYPICAL NOISE PARAMETERS, $V_{DS}=3V$ AND $I_{DS}=40\text{ MA}$ (FIG. 3)

| Freq. (GHz) | F Min. (dB) | GOpt (Magnitude) | GOpt (Angle) | Rn/50 | Ga Associated Gain (dB) |
|-------------|-------------|------------------|--------------|-------|-------------------------|
| 0.5 | 0.071 | 0.34 | 27.00 | 0.05 | 27.9 |
| 0.7 | 0.101 | 0.35 | 37.65 | 0.05 | 25.7 |
| 0.9 | 0.131 | 0.35 | 48.14 | 0.04 | 23.9 |
| 1.0 | 0.146 | 0.36 | 53.32 | 0.04 | 23.2 |
| 1.9 | 0.281 | 0.39 | 98.07 | 0.03 | 18.3 |
| 2.0 | 0.296 | 0.39 | 102.83 | 0.03 | 17.9 |
| 2.4 | 0.356 | 0.40 | 121.48 | 0.03 | 16.6 |
| 3.0 | 0.446 | 0.42 | 148.20 | 0.03 | 15.0 |
| 3.9 | 0.581 | 0.45 | -174.52 | 0.05 | 13.4 |
| 5.0 | 0.747 | 0.48 | -133.51 | 0.10 | 11.9 |
| 5.8 | 0.867 | 0.50 | -106.84 | 0.14 | 10.9 |
| 6.0 | 0.897 | 0.50 | -100.59 | 0.15 | 10.6 |





ULTRA LOW NOISE, MEDIUM CURRENT

E-PHEMT Transistor


SAV-541+

Mini-Circuits

TYPICAL S-PARAMETERS, V_{DS}=3V AND I_{DS}=60 MA (FIG. 3)

| Freq. (GHz) | S11 | | S21 | | | S12 | | S22 | | MSG/MAG (dB) |
|-------------|------|--------|------|----------|--------|-------|--------|------|--------|--------------|
| | Mag. | Ang. | Mag. | Mag (dB) | Ang. | Mag. | Ang. | Mag. | Ang. | |
| 0.1 | 0.99 | -18.2 | 27.8 | 28.9 | 168.7 | 0.009 | 78.4 | 0.50 | -14.8 | 35.0 |
| 0.5 | 0.85 | -78.1 | 21.0 | 26.5 | 130.2 | 0.032 | 53.5 | 0.39 | -60.2 | 28.1 |
| 0.9 | 0.74 | -116.2 | 14.9 | 23.5 | 107.3 | 0.044 | 41.8 | 0.29 | -90.1 | 25.3 |
| 1.0 | 0.72 | -123.9 | 13.8 | 22.8 | 102.9 | 0.045 | 39.7 | 0.27 | -96.8 | 24.9 |
| 1.5 | 0.67 | -152.5 | 9.9 | 19.9 | 85.5 | 0.053 | 33.6 | 0.21 | -122.9 | 22.7 |
| 1.9 | 0.65 | -169.2 | 8.0 | 18.1 | 74.5 | 0.059 | 30.3 | 0.18 | -140.6 | 21.4 |
| 2.0 | 0.65 | -172.8 | 7.7 | 17.7 | 72.0 | 0.06 | 29.8 | 0.18 | -144.8 | 21.0 |
| 2.5 | 0.65 | 170.9 | 6.2 | 15.9 | 60.5 | 0.068 | 26.6 | 0.17 | -163.6 | 19.6 |
| 3.0 | 0.64 | 157.0 | 5.2 | 14.3 | 49.9 | 0.075 | 22.8 | 0.16 | 179.6 | 18.4 |
| 4.0 | 0.66 | 133.3 | 3.9 | 11.9 | 29.9 | 0.091 | 14.6 | 0.17 | 149.8 | 15.7 |
| 5.0 | 0.68 | 112.7 | 3.1 | 9.9 | 11.2 | 0.105 | 4.8 | 0.20 | 125.6 | 13.3 |
| 6.0 | 0.71 | 94.1 | 2.6 | 8.2 | -6.8 | 0.12 | -5.7 | 0.24 | 105.4 | 11.8 |
| 7.0 | 0.74 | 77.4 | 2.2 | 6.7 | -24.1 | 0.132 | -17.3 | 0.29 | 87.9 | 10.6 |
| 8.0 | 0.78 | 62.1 | 1.8 | 5.3 | -40.8 | 0.142 | -28.5 | 0.35 | 72.6 | 9.8 |
| 9.0 | 0.81 | 47.7 | 1.6 | 3.9 | -56.9 | 0.149 | -40.4 | 0.41 | 58.1 | 9.1 |
| 10.0 | 0.85 | 33.6 | 1.3 | 2.5 | -72.8 | 0.152 | -52.4 | 0.48 | 44.4 | 8.8 |
| 11.0 | 0.88 | 20.5 | 1.2 | 1.2 | -88.0 | 0.154 | -64.1 | 0.54 | 31.6 | 8.7 |
| 12.0 | 0.90 | 8.3 | 1.0 | 0.0 | -102.6 | 0.154 | -75.7 | 0.59 | 19.8 | 8.1 |
| 13.0 | 0.91 | -3.5 | 0.9 | -1.0 | -116.9 | 0.155 | -87.1 | 0.63 | 8.9 | 7.6 |
| 14.0 | 0.92 | -14.4 | 0.8 | -2.0 | -130.4 | 0.155 | -97.8 | 0.66 | -1.3 | 7.1 |
| 15.0 | 0.93 | -23.0 | 0.7 | -3.2 | -141.3 | 0.149 | -106.3 | 0.71 | -9.9 | 6.7 |
| 16.0 | 0.95 | -30.5 | 0.6 | -4.6 | -151.3 | 0.14 | -114.0 | 0.75 | -17.6 | 6.3 |
| 17.0 | 0.95 | -39.1 | 0.5 | -5.6 | -162.3 | 0.134 | -122.4 | 0.77 | -26.1 | 5.9 |
| 18.0 | 0.94 | -48.4 | 0.5 | -6.4 | -174.0 | 0.132 | -131.7 | 0.79 | -34.7 | 5.6 |

MAXIMUM STABLE GAIN (MSG)/MAXIMUM AVAILABLE GAIN (MAG) vs. FREQUENCY



Notes:
 F Min: Minimum Noise Figure
 GOpt: Optimum Source Reflection Coefficient
 Rn: Equivalent noise resistance

TYPICAL NOISE PARAMETERS, V_{DS}=3V AND I_{DS}=60 MA (FIG. 3)

| Freq. (GHz) | F Min. (dB) | GOpt (Magnitude) | GOpt (Angle) | Rn/50 | Ga Associated Gain (dB) |
|-------------|-------------|------------------|--------------|-------|-------------------------|
| 0.5 | 0.071 | 0.34 | 27.00 | 0.05 | 27.9 |
| 0.7 | 0.101 | 0.35 | 37.65 | 0.05 | 25.7 |
| 0.9 | 0.131 | 0.35 | 48.14 | 0.04 | 23.9 |
| 1.0 | 0.146 | 0.36 | 53.32 | 0.04 | 23.2 |
| 1.9 | 0.281 | 0.39 | 98.07 | 0.03 | 18.3 |
| 2.0 | 0.296 | 0.39 | 102.83 | 0.03 | 17.9 |
| 2.4 | 0.356 | 0.40 | 121.48 | 0.03 | 16.6 |
| 3.0 | 0.446 | 0.42 | 148.20 | 0.03 | 15.0 |
| 3.9 | 0.581 | 0.45 | -174.52 | 0.05 | 13.4 |
| 5.0 | 0.747 | 0.48 | -133.51 | 0.10 | 11.9 |
| 5.8 | 0.867 | 0.50 | -106.84 | 0.14 | 10.9 |
| 6.0 | 0.897 | 0.50 | -100.59 | 0.15 | 10.6 |





ULTRA LOW NOISE, MEDIUM CURRENT

E-PHEMT Transistor


SAV-541+

Mini-Circuits

TYPICAL S-PARAMETERS, $V_{DS}=3V$ AND $I_{DS}=80\text{ MA}$ (FIG. 3)

| Freq. (GHz) | S11 | | S21 | | | S12 | | S22 | | MSG/MAG (dB) |
|-------------|------|--------|------|----------|--------|-------|--------|------|--------|--------------|
| | Mag. | Ang. | Mag. | Mag (dB) | Ang. | Mag. | Ang. | Mag. | Ang. | |
| 0.1 | 0.99 | -18.3 | 29.4 | 29.4 | 168.4 | 0.008 | 84.4 | 0.48 | -16.4 | 35.6 |
| 0.5 | 0.84 | -79.6 | 21.8 | 26.8 | 129.4 | 0.031 | 54.8 | 0.36 | -62.3 | 28.4 |
| 0.9 | 0.73 | -117.7 | 15.4 | 23.7 | 106.5 | 0.041 | 42.7 | 0.27 | -93.1 | 25.7 |
| 1.0 | 0.71 | -125.3 | 14.2 | 23.1 | 102.2 | 0.043 | 40.4 | 0.25 | -99.8 | 25.2 |
| 1.5 | 0.66 | -153.7 | 10.2 | 20.2 | 85.0 | 0.051 | 35.2 | 0.20 | -126.4 | 23.0 |
| 1.9 | 0.65 | -170.2 | 8.2 | 18.3 | 74.1 | 0.057 | 32.5 | 0.18 | -144.2 | 21.6 |
| 2.0 | 0.65 | -173.8 | 7.8 | 17.9 | 71.7 | 0.059 | 31.6 | 0.18 | -148.3 | 21.3 |
| 2.5 | 0.64 | 170.2 | 6.3 | 16.1 | 60.2 | 0.066 | 28.2 | 0.16 | -167.0 | 19.8 |
| 3.0 | 0.64 | 156.4 | 5.3 | 14.5 | 49.8 | 0.074 | 24.7 | 0.16 | 176.5 | 18.6 |
| 4.0 | 0.65 | 132.9 | 4.0 | 12.1 | 30.0 | 0.09 | 16.1 | 0.17 | 147.5 | 15.7 |
| 5.0 | 0.67 | 112.4 | 3.2 | 10.1 | 11.4 | 0.106 | 6.1 | 0.20 | 124.0 | 13.4 |
| 6.0 | 0.70 | 94.0 | 2.6 | 8.4 | -6.5 | 0.12 | -5.0 | 0.24 | 104.4 | 11.9 |
| 7.0 | 0.74 | 77.4 | 2.2 | 6.9 | -23.8 | 0.133 | -16.3 | 0.29 | 87.2 | 10.8 |
| 8.0 | 0.77 | 62.1 | 1.9 | 5.4 | -40.4 | 0.142 | -27.9 | 0.35 | 71.9 | 9.9 |
| 9.0 | 0.81 | 47.7 | 1.6 | 4.0 | -56.4 | 0.15 | -39.9 | 0.42 | 57.5 | 9.3 |
| 10.0 | 0.85 | 33.6 | 1.4 | 2.7 | -72.3 | 0.153 | -52.0 | 0.48 | 43.8 | 8.9 |
| 11.0 | 0.87 | 20.5 | 1.2 | 1.4 | -87.4 | 0.155 | -63.9 | 0.54 | 31.2 | 8.8 |
| 12.0 | 0.90 | 8.3 | 1.0 | 0.2 | -102.0 | 0.155 | -75.4 | 0.59 | 19.4 | 8.2 |
| 13.0 | 0.91 | -3.5 | 0.9 | -0.8 | -116.2 | 0.156 | -86.8 | 0.63 | 8.6 | 7.6 |
| 14.0 | 0.92 | -14.4 | 0.8 | -1.8 | -129.6 | 0.156 | -97.7 | 0.66 | -1.6 | 7.2 |
| 15.0 | 0.93 | -23.0 | 0.7 | -3.0 | -140.7 | 0.15 | -106.2 | 0.71 | -10.2 | 6.7 |
| 16.0 | 0.95 | -30.5 | 0.6 | -4.4 | -150.6 | 0.14 | -113.9 | 0.75 | -17.9 | 6.4 |
| 17.0 | 0.95 | -39.1 | 0.5 | -5.4 | -161.5 | 0.135 | -122.3 | 0.77 | -26.4 | 6.0 |
| 18.0 | 0.94 | -48.5 | 0.5 | -6.2 | -173.4 | 0.133 | -131.2 | 0.78 | -35.0 | 5.7 |

MAXIMUM STABLE GAIN (MSG)/MAXIMUM AVAILABLE GAIN (MAG) vs. FREQUENCY



Notes:
 F Min: Minimum Noise Figure
 GOpt: Optimum Source Reflection Coefficient
 Rn: Equivalent noise resistance

TYPICAL NOISE PARAMETERS, $V_{DS}=3V$ AND $I_{DS}=80\text{ MA}$ (FIG. 3)

| Freq. (GHz) | F Min. (dB) | GOpt (Magnitude) | GOpt (Angle) | Rn/50 | Ga Associated Gain (dB) |
|-------------|-------------|------------------|--------------|-------|-------------------------|
| 0.5 | 0.086 | 0.31 | 27.68 | 0.05 | 28.4 |
| 0.7 | 0.123 | 0.31 | 39.97 | 0.05 | 26.3 |
| 0.9 | 0.159 | 0.32 | 51.98 | 0.04 | 24.6 |
| 1.0 | 0.178 | 0.32 | 57.88 | 0.04 | 23.8 |
| 1.9 | 0.342 | 0.35 | 107.88 | 0.03 | 19.1 |
| 2.0 | 0.360 | 0.35 | 113.08 | 0.03 | 18.7 |
| 2.4 | 0.433 | 0.36 | 133.22 | 0.03 | 17.4 |
| 3.0 | 0.543 | 0.39 | 161.34 | 0.04 | 15.9 |
| 3.9 | 0.707 | 0.43 | -161.16 | 0.07 | 14.1 |
| 5.0 | 0.908 | 0.49 | -122.96 | 0.13 | 12.5 |
| 5.8 | 1.055 | 0.54 | -100.45 | 0.20 | 11.4 |
| 6.0 | 1.091 | 0.56 | -95.52 | 0.22 | 11.2 |





ULTRA LOW NOISE, MEDIUM CURRENT


E-PHEMT Transistor

SAV-541+

TYPICAL S-PARAMETERS, V_{DS}=4V AND I_{DS}=60 MA (FIG. 3)

| Freq. (GHz) | S11 | | S21 | | | S12 | | S22 | | MSG/MAG (dB) |
|-------------|------|--------|------|----------|--------|-------|--------|------|--------|--------------|
| | Mag. | Ang. | Mag. | Mag (dB) | Ang. | Mag. | Ang. | Mag. | Ang. | |
| 0.1 | 0.99 | -17.9 | 27.9 | 28.9 | 168.5 | 0.008 | 83.7 | 0.53 | -14.7 | 35.2 |
| 0.5 | 0.85 | -77.9 | 21.0 | 26.5 | 130.2 | 0.032 | 54.0 | 0.40 | -57.1 | 28.2 |
| 0.9 | 0.74 | -116.0 | 15.0 | 23.5 | 107.3 | 0.043 | 41.4 | 0.29 | -84.8 | 25.5 |
| 1.0 | 0.72 | -123.7 | 13.9 | 22.8 | 102.9 | 0.044 | 39.3 | 0.27 | -90.9 | 25.0 |
| 1.5 | 0.67 | -152.3 | 10.0 | 20.0 | 85.5 | 0.052 | 33.5 | 0.21 | -115.1 | 22.8 |
| 1.9 | 0.65 | -169.0 | 8.1 | 18.1 | 74.5 | 0.058 | 30.2 | 0.18 | -131.8 | 21.5 |
| 2.0 | 0.65 | -172.6 | 7.7 | 17.7 | 72.0 | 0.059 | 29.6 | 0.17 | -135.9 | 21.1 |
| 2.5 | 0.64 | 171.1 | 6.2 | 15.9 | 60.4 | 0.066 | 26.5 | 0.15 | -154.5 | 19.7 |
| 3.0 | 0.64 | 157.3 | 5.2 | 14.4 | 49.8 | 0.073 | 22.9 | 0.14 | -171.8 | 18.5 |
| 4.0 | 0.66 | 133.5 | 3.9 | 11.9 | 29.9 | 0.088 | 15.0 | 0.15 | 156.0 | 15.7 |
| 5.0 | 0.68 | 112.9 | 3.1 | 10.0 | 11.1 | 0.103 | 5.6 | 0.17 | 129.9 | 13.4 |
| 6.0 | 0.71 | 94.4 | 2.6 | 8.3 | -6.9 | 0.117 | -4.9 | 0.21 | 108.6 | 11.9 |
| 7.0 | 0.74 | 77.7 | 2.2 | 6.8 | -24.3 | 0.13 | -16.2 | 0.26 | 90.7 | 10.8 |
| 8.0 | 0.78 | 62.3 | 1.9 | 5.3 | -41.1 | 0.14 | -27.3 | 0.32 | 74.9 | 9.9 |
| 9.0 | 0.81 | 47.9 | 1.6 | 4.0 | -57.4 | 0.147 | -39.2 | 0.39 | 60.2 | 9.3 |
| 10.0 | 0.85 | 33.8 | 1.4 | 2.6 | -73.5 | 0.151 | -51.1 | 0.46 | 46.3 | 9.5 |
| 11.0 | 0.88 | 20.6 | 1.2 | 1.3 | -88.9 | 0.154 | -62.9 | 0.52 | 33.4 | 8.8 |
| 12.0 | 0.90 | 8.5 | 1.0 | 0.1 | -103.6 | 0.154 | -74.4 | 0.57 | 21.5 | 8.2 |
| 13.0 | 0.91 | -3.4 | 0.9 | -1.0 | -118.0 | 0.156 | -85.9 | 0.61 | 10.6 | 7.6 |
| 14.0 | 0.92 | -14.3 | 0.8 | -2.0 | -131.6 | 0.156 | -96.8 | 0.65 | 0.3 | 7.1 |
| 15.0 | 0.94 | -22.9 | 0.7 | -3.2 | -142.8 | 0.149 | -105.4 | 0.70 | -8.5 | 6.7 |
| 16.0 | 0.95 | -30.4 | 0.6 | -4.6 | -152.9 | 0.14 | -113.3 | 0.74 | -16.4 | 6.3 |
| 17.0 | 0.95 | -39.0 | 0.5 | -5.6 | -164.0 | 0.135 | -121.7 | 0.77 | -25.0 | 5.9 |
| 18.0 | 0.95 | -48.3 | 0.5 | -6.5 | -175.7 | 0.133 | -131.0 | 0.78 | -33.7 | 5.5 |

MAXIMUM STABLE GAIN (MSG)/MAXIMUM AVAILABLE GAIN (MAG) vs. FREQUENCY



Notes:
 F Min: Minimum Noise Figure
 GOpt: Optimum Source Reflection Coefficient
 Rn: Equivalent noise resistance

TYPICAL NOISE PARAMETERS, V_{DS}=4V AND I_{DS}=60 MA (FIG. 3)

| Freq. (GHz) | F Min. (dB) | GOpt (Magnitude) | GOpt (Angle) | Rn/50 | Ga Associated Gain (dB) |
|-------------|-------------|------------------|--------------|-------|-------------------------|
| 0.5 | 0.086 | 0.34 | 26.43 | 0.06 | 28.1 |
| 0.7 | 0.121 | 0.34 | 37.91 | 0.05 | 26.0 |
| 0.9 | 0.156 | 0.34 | 49.17 | 0.05 | 24.2 |
| 1.0 | 0.173 | 0.34 | 54.72 | 0.04 | 23.4 |
| 1.9 | 0.331 | 0.35 | 102.19 | 0.03 | 18.7 |
| 2.0 | 0.349 | 0.35 | 107.19 | 0.03 | 18.3 |
| 2.4 | 0.419 | 0.36 | 126.64 | 0.03 | 17.0 |
| 3.0 | 0.524 | 0.37 | 154.19 | 0.04 | 15.4 |
| 3.9 | 0.682 | 0.41 | -168.19 | 0.06 | 13.7 |
| 5.0 | 0.875 | 0.47 | -128.23 | 0.12 | 12.2 |
| 5.8 | 1.016 | 0.52 | -103.33 | 0.17 | 11.2 |
| 6.0 | 1.051 | 0.54 | -97.65 | 0.18 | 11.0 |






ULTRA LOW NOISE, MEDIUM CURRENT

E-PHEMT Transistor

SAV-541+

RECOMMENDED APPLICATION CIRCUIT




| VDS, V (nom) | 3 | 4 |
|---------------|-----------|-----------|
| IDS, mA (nom) | 60mA | 60mA |
| R1 | 4320Ω | 4320Ω |
| R2 | 4320Ω | 4320Ω |
| R3 | 3570Ω | 1210Ω |
| R4 | 33.2Ω | 16.7Ω |
| Q1 | MMBT3906* | MMBT3906* |
| Q2 | MMBT3906* | MMBT3906* |
| C1 | 0.01μF | 0.01μF |
| C2 | 0.01μF | 0.01μF |
| L1** | 840nH | 840nH |
| L2** | 840nH | 840nH |

*Fairchild Semiconductor™ part number
 **Piconics™ part number CC45T47K240G5

OPTIMIZED AMPLIFIER CIRCUITS

For band specific, drop-in modules, and as an alternative to designing circuits, please refer to Mini-Circuits TAMP and RAMP series models which are based upon SAV/TAV E-PHEMT's and include all DC blocking, bias, matching and stabilization circuitry, without need for any external components.

PRODUCT MARKING





ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

| | |
|--|---|
| Performance Data | Data Table |
| | Swept Graphs |
| | Performance data, graphs, s-parameter data set (.zip file) |
| Case Style | MMM1362 Plastic molded SOT-343 (SC-70) style package, lead finish: matte tin |
| Tape & Reel Standard quantities available on reel | F90 Standard quantities available on reel: 7" reels with 20, 50, 100, 200, 500, 1K, 2K, or 3K devices. |
| Suggested Layout for PCB Design | PL-300 |
| Evaluation Board | TB-471+ |
| Environmental Ratings | ENV08T2 |

ESD RATING


Human Body Model (HBM): Class 1A (250 V to < 500 V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (40 V) in accordance with ANSI/ESD STM 5.2 - 1999

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDECJ-STD-020D

MSL TEST FLOW CHART



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

| VDS (V) | IDS (mA) | | | | | |
|---------|----------|-------|-------|-------|--------|--------|
| | @ VGS= | | | | | |
| | 0.20V | 0.30V | 0.40V | 0.50V | 0.60V | 0.70V |
| 0.00 | 0.01 | 0.04 | 0.08 | 0.08 | 0.10 | 0.09 |
| 0.10 | 0.27 | 3.65 | 12.61 | 18.97 | 21.95 | 23.61 |
| 0.20 | 0.29 | 4.15 | 18.82 | 34.57 | 42.39 | 46.35 |
| 0.30 | 0.30 | 4.34 | 20.58 | 45.11 | 60.56 | 68.02 |
| 0.40 | 0.33 | 4.50 | 21.37 | 50.24 | 75.24 | 88.05 |
| 0.50 | 0.34 | 4.65 | 21.90 | 52.30 | 85.18 | 105.70 |
| 0.60 | 0.34 | 4.85 | 22.33 | 53.38 | 90.38 | 120.00 |
| 0.70 | 0.36 | 4.99 | 22.76 | 54.18 | 92.66 | |
| 0.80 | 0.38 | 5.13 | 23.24 | 54.89 | 93.88 | |
| 0.90 | 0.40 | 5.25 | 23.62 | 55.49 | 94.80 | |
| 1.00 | 0.42 | 5.38 | 23.97 | 56.03 | 95.53 | |
| 1.10 | 0.43 | 5.51 | 24.29 | 56.51 | 96.14 | |
| 1.20 | 0.45 | 5.63 | 24.61 | 56.97 | 96.68 | |
| 1.30 | 0.45 | 5.75 | 24.91 | 57.39 | 97.18 | |
| 1.40 | 0.47 | 5.86 | 25.22 | 57.82 | 97.65 | |
| 1.50 | 0.48 | 5.98 | 25.50 | 58.21 | 98.08 | |
| 1.60 | 0.52 | 6.10 | 25.77 | 58.60 | 98.49 | |
| 1.70 | 0.53 | 6.21 | 26.04 | 58.97 | 98.89 | |
| 1.80 | 0.55 | 6.32 | 26.32 | 59.33 | 99.30 | |
| 1.90 | 0.57 | 6.45 | 26.58 | 59.70 | 99.68 | |
| 2.00 | 0.55 | 6.55 | 26.87 | 60.08 | 100.07 | |
| 2.10 | 0.58 | 6.69 | 27.17 | 60.50 | 100.48 | |
| 2.20 | 0.60 | 6.82 | 27.51 | 60.97 | 100.97 | |
| 2.30 | 0.63 | 6.99 | 27.89 | 61.47 | 101.50 | |
| 2.40 | 0.64 | 7.17 | 28.29 | 62.05 | 102.12 | |
| 2.50 | 0.67 | 7.34 | 28.74 | 62.68 | 102.78 | |
| 2.60 | 0.70 | 7.52 | 29.19 | 63.32 | 103.50 | |
| 2.70 | 0.71 | 7.69 | 29.65 | 63.99 | 104.22 | |
| 2.80 | 0.73 | 7.90 | 30.15 | 64.64 | 104.94 | |
| 2.90 | 0.76 | 8.10 | 30.62 | 65.31 | 105.64 | |
| 3.00 | 0.82 | 8.34 | 31.13 | 65.99 | 106.33 | |
| 3.10 | 0.84 | 8.56 | 31.63 | 66.65 | 107.02 | |
| 3.20 | 0.87 | 8.79 | 32.17 | 67.32 | 107.70 | |
| 3.30 | 0.90 | 9.03 | 32.72 | 68.02 | 108.37 | |
| 3.40 | 0.92 | 9.30 | 33.28 | 68.69 | 109.02 | |
| 3.50 | 0.95 | 9.58 | 33.87 | 69.41 | 109.67 | |
| 3.60 | 1.01 | 9.89 | 34.46 | 70.12 | 110.34 | |
| 3.70 | 1.06 | 10.20 | 35.06 | 70.81 | 111.00 | |
| 3.80 | 1.10 | 10.53 | 35.67 | 71.53 | 111.64 | |
| 3.90 | 1.14 | 10.86 | 36.29 | 72.24 | 112.30 | |
| 4.00 | 1.14 | 11.21 | 36.89 | 72.93 | 112.96 | |
| 4.10 | 1.30 | 11.55 | 37.51 | 73.65 | 113.60 | |
| 4.20 | 1.37 | 11.90 | 38.13 | 74.35 | 114.25 | |
| 4.30 | 1.45 | 12.26 | 38.74 | 75.03 | 114.88 | |
| 4.40 | 1.54 | 12.63 | 39.36 | 75.76 | 115.53 | |
| 4.50 | 1.62 | 13.00 | 39.99 | 76.47 | 116.18 | |
| 4.60 | 1.69 | 13.38 | 40.62 | 77.15 | 116.80 | |
| 4.70 | 1.78 | 13.76 | 41.23 | 77.86 | 117.44 | |
| 4.80 | 1.90 | 14.14 | 41.86 | 78.56 | 118.06 | |
| 4.90 | 1.98 | 14.53 | 42.50 | 79.26 | 118.67 | |
| 5.00 | 2.07 | 14.94 | 43.13 | 79.96 | 119.30 | |

Typical Performance Data

| IDS (mA) | GAIN (dB) ⁽¹⁾ | | | | OIP3 (dBm) ⁽¹⁾ | | | |
|-------------|--------------------------|-------|---------|-------|---------------------------|-------|---------|-------|
| | VDS=+3V | | VDS=+4V | | VDS=+3V | | VDS=+4V | |
| | 0.9 GHz | 2 GHz | 0.9 GHz | 2 GHz | 0.9 GHz | 2 GHz | 0.9 GHz | 2 GHz |
| 10.00 | 20.02 | 15.36 | 20.05 | 15.39 | 20.31 | 21.12 | 20.16 | 20.91 |
| 15.00 | 21.22 | 16.22 | 21.17 | 16.18 | 22.82 | 24.10 | 22.70 | 23.93 |
| 30.00 | 22.62 | 17.15 | 22.67 | 17.14 | 28.66 | 30.74 | 28.32 | 30.23 |
| 60.00 | 23.53 | 17.74 | 23.51 | 17.73 | 32.60 | 33.81 | 33.41 | 35.32 |

| IDS (mA) | Pout @ 1dB Compression ^(1,2) (dBm) | | | | NOISE FIGURE ⁽¹⁾ (dB) | | | |
|-------------|--|-------|---------|-------|-------------------------------------|-------|---------|-------|
| | VDS=+3V | | VDS=+4V | | VDS=+3V | | VDS=+4V | |
| | 0.9 GHz | 2 GHz | 0.9 GHz | 2 GHz | 0.9 GHz | 2 GHz | 0.9 GHz | 2 GHz |
| 10.00 | 17.56 | 18.18 | 20.03 | 20.90 | 0.48 | 0.63 | -- | -- |
| 15.00 | 17.05 | 17.50 | 19.29 | 20.00 | 0.48 | 0.54 | 0.47 | 0.54 |
| 30.00 | 18.50 | 19.00 | 19.50 | 20.59 | 0.39 | 0.50 | 0.39 | 0.47 |
| 60.00 | 18.85 | 19.20 | 21.12 | 21.50 | 0.34 | 0.43 | 0.38 | 0.51 |

| FREQ (GHz) | NF vs FREQ & TEMPERATURE ⁽¹⁾ @ VDS=3V, IDS=60mA | | | NF vs FREQ & TEMPERATURE ⁽¹⁾ @ VDS=4V, IDS=60mA | | |
|---------------|---|-------|-------|---|-------|-------|
| | -40°C | +25°C | +85°C | -40°C | +25°C | +85°C |
| | 0.25 | 0.27 | 0.26 | 0.40 | 0.26 | 0.31 |
| 0.30 | 0.27 | 0.31 | 0.45 | 0.25 | 0.35 | 0.51 |
| 0.40 | 0.38 | 0.26 | 0.40 | 0.40 | 0.29 | 0.44 |
| 0.50 | 0.40 | 0.30 | 0.46 | 0.40 | 0.34 | 0.48 |
| 0.60 | 0.32 | 0.30 | 0.46 | 0.35 | 0.38 | 0.53 |
| 0.70 | 0.25 | 0.34 | 0.49 | 0.33 | 0.38 | 0.55 |
| 0.80 | 0.31 | 0.29 | 0.44 | 0.30 | 0.35 | 0.51 |
| 0.90 | 0.31 | 0.34 | 0.50 | 0.31 | 0.38 | 0.56 |
| 1.00 | 0.32 | 0.34 | 0.52 | 0.35 | 0.40 | 0.56 |
| 1.25 | 0.33 | 0.40 | 0.58 | 0.36 | 0.45 | 0.62 |
| 1.50 | 0.33 | 0.46 | 0.65 | 0.35 | 0.54 | 0.72 |
| 1.75 | 0.42 | 0.46 | 0.65 | 0.42 | 0.52 | 0.71 |
| 2.00 | 0.28 | 0.43 | 0.65 | 0.30 | 0.51 | 0.69 |
| 2.25 | 0.37 | 0.56 | 0.76 | 0.39 | 0.55 | 0.78 |
| 2.50 | 0.36 | 0.60 | 0.85 | 0.41 | 0.61 | 0.85 |
| 2.75 | 0.63 | 0.74 | 1.05 | 0.61 | 0.85 | 1.05 |
| 3.00 | 0.45 | 0.61 | 0.94 | 0.42 | 0.70 | 1.01 |
| 3.25 | 0.53 | 0.77 | 1.09 | 0.51 | 0.79 | 1.23 |
| 3.50 | 0.54 | 0.82 | 1.15 | 0.46 | 0.90 | 1.33 |
| 3.75 | 0.57 | 0.88 | 1.27 | 0.59 | 0.98 | 1.41 |
| 4.00 | 0.58 | 0.95 | 1.42 | 0.66 | 0.99 | 1.50 |
| 4.25 | 0.49 | 1.08 | 1.51 | 0.57 | 1.12 | 1.69 |
| 4.50 | 0.78 | 1.19 | 1.65 | 0.57 | 1.27 | 1.85 |
| 4.75 | 0.79 | 1.25 | 1.83 | 0.86 | 1.36 | 2.02 |
| 5.00 | 0.87 | 1.47 | 1.95 | 1.00 | 1.46 | 2.16 |
| 5.25 | 0.72 | 1.54 | 2.13 | 0.78 | 1.60 | 2.34 |
| 5.50 | 0.79 | 1.79 | 2.45 | 0.60 | 1.73 | 2.49 |
| 5.75 | 0.93 | 1.80 | 2.44 | 1.09 | 1.93 | 2.65 |
| 6.00 | 0.83 | 1.98 | 2.67 | 1.25 | 2.03 | 2.79 |

(1) Includes test board loss

(2) Drain current was allowed to increase during compression measurement

Typical Performance Data

| FREQ (GHz) | GAIN vs FREQ & TEMPERATURE @ VDS=3V, IDS=60mA | | | OIP3 vs FREQ & TEMPERATURE ⁽¹⁾ @ VDS=3V, IDS=60mA | | | P1dB vs FREQ & TEMPERATURE ^(1,2) @ VDS=3V, IDS=60mA | | |
|---------------|--|-------|-------|---|-------|-------|---|-------|-------|
| | -45°C | +25°C | +85°C | -45°C | +25°C | +85°C | -45°C | +25°C | +85°C |
| 0.40 | 27.44 | 27.18 | 26.59 | 32.59 | 32.19 | 31.58 | 18.79 | 19.05 | 19.13 |
| 0.50 | 26.86 | 26.34 | 25.99 | 32.70 | 32.28 | 31.66 | 18.81 | 19.07 | 19.14 |
| 0.60 | 26.11 | 25.71 | 25.26 | 32.81 | 32.36 | 31.73 | 18.82 | 19.09 | 19.15 |
| 0.70 | 25.33 | 24.92 | 24.51 | 32.91 | 32.44 | 31.80 | 18.84 | 19.11 | 19.17 |
| 0.80 | 24.60 | 24.24 | 23.72 | 33.00 | 32.52 | 31.86 | 18.85 | 19.12 | 19.18 |
| 0.90 | 23.96 | 23.53 | 23.04 | 33.09 | 32.59 | 31.92 | 18.87 | 19.14 | 19.18 |
| 1.00 | 23.28 | 22.89 | 22.49 | 33.18 | 32.66 | 31.98 | 18.88 | 19.15 | 19.19 |
| 1.10 | 22.72 | 22.28 | 21.86 | 33.26 | 32.72 | 32.03 | 18.89 | 19.16 | 19.20 |
| 1.20 | 22.03 | 21.63 | 21.28 | 33.33 | 32.78 | 32.08 | 18.90 | 19.18 | 19.20 |
| 1.30 | 21.46 | 21.06 | 20.66 | 33.40 | 32.83 | 32.13 | 18.91 | 19.19 | 19.21 |
| 1.40 | 20.94 | 20.49 | 20.11 | 33.47 | 32.88 | 32.17 | 18.91 | 19.19 | 19.21 |
| 1.50 | 20.39 | 20.01 | 19.66 | 33.53 | 32.93 | 32.21 | 18.92 | 19.20 | 19.22 |
| 1.60 | 19.90 | 19.51 | 19.18 | 33.59 | 32.97 | 32.24 | 18.92 | 19.21 | 19.22 |
| 1.70 | 19.44 | 19.02 | 18.69 | 33.64 | 33.01 | 32.28 | 18.93 | 19.21 | 19.22 |
| 1.80 | 18.99 | 18.61 | 18.23 | 33.69 | 33.05 | 32.30 | 18.93 | 19.21 | 19.22 |
| 1.90 | 18.55 | 18.17 | 17.80 | 33.73 | 33.08 | 32.33 | 18.93 | 19.22 | 19.22 |
| 2.00 | 18.14 | 17.74 | 17.37 | 33.77 | 33.10 | 32.35 | 18.93 | 19.22 | 19.21 |
| 2.10 | 17.75 | 17.35 | 16.97 | 33.80 | 33.12 | 32.36 | 18.93 | 19.22 | 19.21 |
| 2.20 | 17.35 | 16.98 | 16.61 | 33.83 | 33.14 | 32.38 | 18.93 | 19.21 | 19.20 |
| 2.30 | 17.01 | 16.61 | 16.25 | 33.85 | 33.16 | 32.39 | 18.93 | 19.21 | 19.20 |
| 2.40 | 16.67 | 16.28 | 15.89 | 33.87 | 33.16 | 32.39 | 18.92 | 19.21 | 19.19 |
| 2.50 | 16.38 | 16.01 | 15.61 | 33.88 | 33.17 | 32.39 | 18.92 | 19.20 | 19.18 |
| 2.60 | 16.04 | 15.67 | 15.25 | 33.89 | 33.17 | 32.39 | 18.91 | 19.19 | 19.17 |
| 2.70 | 15.74 | 15.34 | 14.91 | 33.89 | 33.17 | 32.39 | 18.90 | 19.18 | 19.16 |
| 2.80 | 15.47 | 15.05 | 14.65 | 33.89 | 33.16 | 32.38 | 18.89 | 19.17 | 19.15 |
| 2.90 | 15.32 | 14.87 | 14.44 | 33.88 | 33.15 | 32.37 | 18.88 | 19.16 | 19.14 |
| 3.00 | 14.99 | 14.54 | 14.10 | 33.87 | 33.13 | 32.35 | 18.87 | 19.15 | 19.13 |
| 3.10 | 14.76 | 14.32 | 13.87 | 33.86 | 33.11 | 32.33 | 18.86 | 19.13 | 19.11 |
| 3.20 | 14.53 | 14.08 | 13.61 | 33.84 | 33.09 | 32.30 | 18.85 | 19.12 | 19.10 |
| 3.30 | 14.27 | 13.81 | 13.33 | 33.81 | 33.06 | 32.28 | 18.83 | 19.10 | 19.08 |
| 3.40 | 13.99 | 13.53 | 13.02 | 33.78 | 33.03 | 32.25 | 18.82 | 19.08 | 19.06 |
| 3.50 | 13.78 | 13.33 | 12.81 | 33.75 | 32.99 | 32.21 | 18.80 | 19.06 | 19.04 |
| 3.60 | 13.56 | 13.09 | 12.59 | 33.70 | 32.95 | 32.17 | 18.78 | 19.04 | 19.02 |
| 3.70 | 13.30 | 12.83 | 12.31 | 33.66 | 32.91 | 32.13 | 18.76 | 19.02 | 19.00 |
| 3.80 | 13.05 | 12.56 | 12.04 | 33.61 | 32.86 | 32.08 | 18.74 | 18.99 | 18.98 |
| 3.90 | 12.81 | 12.30 | 11.81 | 33.56 | 32.81 | 32.03 | 18.72 | 18.97 | 18.96 |
| 4.00 | 12.58 | 12.06 | 11.57 | 33.50 | 32.75 | 31.98 | 18.70 | 18.94 | 18.93 |
| 4.10 | 12.42 | 11.94 | 11.43 | 33.43 | 32.69 | 31.92 | 18.68 | 18.91 | 18.91 |
| 4.20 | 12.23 | 11.74 | 11.27 | 33.36 | 32.62 | 31.86 | 18.65 | 18.88 | 18.88 |
| 4.30 | 12.01 | 11.51 | 11.02 | 33.29 | 32.55 | 31.80 | 18.63 | 18.85 | 18.86 |
| 4.40 | 11.80 | 11.28 | 10.78 | 33.21 | 32.48 | 31.73 | 18.60 | 18.82 | 18.83 |
| 4.50 | 11.54 | 11.06 | 10.60 | 33.13 | 32.40 | 31.66 | 18.57 | 18.79 | 18.80 |
| 4.60 | 11.17 | 10.69 | 10.23 | 33.04 | 32.32 | 31.58 | 18.54 | 18.75 | 18.77 |
| 4.70 | 11.02 | 10.56 | 10.09 | 32.94 | 32.23 | 31.50 | 18.51 | 18.72 | 18.74 |
| 4.80 | 10.79 | 10.37 | 9.92 | 32.85 | 32.14 | 31.42 | 18.48 | 18.68 | 18.70 |
| 4.90 | 10.58 | 10.12 | 9.73 | 32.74 | 32.05 | 31.33 | 18.45 | 18.64 | 18.67 |
| 5.00 | 10.30 | 9.88 | 9.42 | 32.63 | 31.95 | 31.24 | 18.41 | 18.60 | 18.64 |
| 5.10 | 10.06 | 9.64 | 9.21 | 32.52 | 31.85 | 31.15 | 18.38 | 18.56 | 18.60 |
| 5.20 | 9.82 | 9.43 | 9.02 | 32.40 | 31.74 | 31.05 | 18.34 | 18.51 | 18.56 |
| 5.30 | 9.65 | 9.24 | 8.85 | 32.28 | 31.63 | 30.95 | 18.31 | 18.47 | 18.53 |
| 5.40 | 9.40 | 9.08 | 8.70 | 32.15 | 31.52 | 30.85 | 18.27 | 18.42 | 18.49 |
| 5.50 | 9.23 | 8.88 | 8.51 | 32.02 | 31.40 | 30.74 | 18.23 | 18.38 | 18.45 |
| 5.60 | 9.04 | 8.60 | 8.23 | 31.89 | 31.27 | 30.62 | 18.19 | 18.33 | 18.41 |
| 5.70 | 8.90 | 8.46 | 8.19 | 31.74 | 31.15 | 30.51 | 18.15 | 18.28 | 18.36 |
| 5.80 | 8.72 | 8.29 | 8.01 | 31.60 | 31.01 | 30.39 | 18.10 | 18.23 | 18.32 |
| 5.90 | 8.35 | 7.93 | 7.64 | 31.45 | 30.88 | 30.26 | 18.06 | 18.17 | 18.28 |
| 6.00 | 8.09 | 7.72 | 7.34 | 31.29 | 30.74 | 30.14 | 18.01 | 18.12 | 18.23 |

(1) Includes test board loss

(2) Drain current was allowed to increase during compression measurement

Typical Performance Data

| FREQ (GHz) | GAIN vs FREQ & TEMPERATURE @ VDS=4V, IDS=60mA | | | OIP3 vs FREQ & TEMPERATURE ⁽¹⁾ @ VDS=4V, IDS=60mA | | | P1dB vs FREQ & TEMPERATURE ^(1,2) @ VDS=4V, IDS=60mA | | |
|---------------|--|-------|-------|---|-------|-------|---|-------|-------|
| | -45°C | +25°C | +85°C | -45°C | +25°C | +85°C | -45°C | +25°C | +85°C |
| 0.40 | 27.61 | 27.07 | 26.52 | 32.28 | 32.21 | 31.90 | 20.95 | 21.09 | 21.09 |
| 0.50 | 26.77 | 26.34 | 25.91 | 32.59 | 32.45 | 32.12 | 20.98 | 21.12 | 21.10 |
| 0.60 | 26.10 | 25.64 | 25.16 | 32.89 | 32.68 | 32.33 | 21.00 | 21.16 | 21.11 |
| 0.70 | 25.31 | 24.93 | 24.44 | 33.17 | 32.90 | 32.53 | 21.03 | 21.19 | 21.12 |
| 0.80 | 24.62 | 24.22 | 23.78 | 33.45 | 33.11 | 32.73 | 21.06 | 21.22 | 21.13 |
| 0.90 | 23.93 | 23.51 | 23.09 | 33.72 | 33.32 | 32.92 | 21.09 | 21.24 | 21.14 |
| 1.00 | 23.29 | 22.87 | 22.46 | 33.97 | 33.52 | 33.10 | 21.11 | 21.27 | 21.15 |
| 1.10 | 22.64 | 22.25 | 21.82 | 34.22 | 33.71 | 33.27 | 21.13 | 21.29 | 21.16 |
| 1.20 | 22.06 | 21.65 | 21.23 | 34.46 | 33.89 | 33.44 | 21.16 | 21.32 | 21.17 |
| 1.30 | 21.45 | 21.06 | 20.66 | 34.69 | 34.06 | 33.60 | 21.18 | 21.34 | 21.18 |
| 1.40 | 20.88 | 20.51 | 20.11 | 34.91 | 34.23 | 33.75 | 21.20 | 21.36 | 21.18 |
| 1.50 | 20.40 | 20.01 | 19.65 | 35.12 | 34.39 | 33.90 | 21.21 | 21.38 | 21.19 |
| 1.60 | 19.89 | 19.52 | 19.21 | 35.32 | 34.54 | 34.04 | 21.23 | 21.40 | 21.20 |
| 1.70 | 19.42 | 19.00 | 18.65 | 35.51 | 34.68 | 34.17 | 21.25 | 21.41 | 21.20 |
| 1.80 | 18.97 | 18.60 | 18.22 | 35.69 | 34.82 | 34.29 | 21.26 | 21.43 | 21.21 |
| 1.90 | 18.52 | 18.18 | 17.81 | 35.86 | 34.94 | 34.41 | 21.28 | 21.44 | 21.21 |
| 2.00 | 18.10 | 17.73 | 17.36 | 36.02 | 35.06 | 34.52 | 21.29 | 21.45 | 21.21 |
| 2.10 | 17.69 | 17.36 | 17.00 | 36.18 | 35.17 | 34.62 | 21.30 | 21.46 | 21.21 |
| 2.20 | 17.32 | 17.00 | 16.62 | 36.32 | 35.27 | 34.72 | 21.31 | 21.47 | 21.22 |
| 2.30 | 17.00 | 16.60 | 16.24 | 36.45 | 35.37 | 34.81 | 21.32 | 21.48 | 21.22 |
| 2.40 | 16.64 | 16.25 | 15.88 | 36.57 | 35.45 | 34.89 | 21.33 | 21.49 | 21.22 |
| 2.50 | 16.35 | 15.99 | 15.62 | 36.69 | 35.53 | 34.96 | 21.34 | 21.49 | 21.22 |
| 2.60 | 16.02 | 15.65 | 15.27 | 36.79 | 35.60 | 35.03 | 21.34 | 21.50 | 21.22 |
| 2.70 | 15.73 | 15.33 | 14.90 | 36.89 | 35.67 | 35.09 | 21.35 | 21.50 | 21.21 |
| 2.80 | 15.45 | 15.05 | 14.64 | 36.97 | 35.72 | 35.14 | 21.35 | 21.50 | 21.21 |
| 2.90 | 15.28 | 14.86 | 14.44 | 37.05 | 35.77 | 35.19 | 21.35 | 21.50 | 21.21 |
| 3.00 | 14.96 | 14.53 | 14.10 | 37.11 | 35.80 | 35.23 | 21.35 | 21.50 | 21.21 |
| 3.10 | 14.73 | 14.29 | 13.88 | 37.17 | 35.83 | 35.26 | 21.35 | 21.50 | 21.20 |
| 3.20 | 14.50 | 14.06 | 13.61 | 37.21 | 35.86 | 35.28 | 21.35 | 21.49 | 21.20 |
| 3.30 | 14.24 | 13.79 | 13.30 | 37.25 | 35.87 | 35.30 | 21.35 | 21.48 | 21.19 |
| 3.40 | 13.97 | 13.51 | 13.02 | 37.28 | 35.88 | 35.31 | 21.34 | 21.48 | 21.18 |
| 3.50 | 13.75 | 13.30 | 12.83 | 37.30 | 35.88 | 35.31 | 21.34 | 21.47 | 21.18 |
| 3.60 | 13.55 | 13.10 | 12.60 | 37.30 | 35.87 | 35.30 | 21.33 | 21.46 | 21.17 |
| 3.70 | 13.28 | 12.80 | 12.32 | 37.30 | 35.85 | 35.29 | 21.32 | 21.45 | 21.16 |
| 3.80 | 13.04 | 12.56 | 12.05 | 37.29 | 35.82 | 35.27 | 21.32 | 21.43 | 21.15 |
| 3.90 | 12.79 | 12.32 | 11.84 | 37.27 | 35.79 | 35.25 | 21.31 | 21.42 | 21.14 |
| 4.00 | 12.55 | 12.08 | 11.57 | 37.24 | 35.75 | 35.21 | 21.30 | 21.40 | 21.13 |
| 4.10 | 12.41 | 11.92 | 11.43 | 37.20 | 35.70 | 35.17 | 21.28 | 21.39 | 21.12 |
| 4.20 | 12.24 | 11.75 | 11.27 | 37.15 | 35.64 | 35.13 | 21.27 | 21.37 | 21.11 |
| 4.30 | 12.00 | 11.52 | 11.04 | 37.09 | 35.58 | 35.07 | 21.26 | 21.35 | 21.10 |
| 4.40 | 11.78 | 11.28 | 10.82 | 37.02 | 35.50 | 35.01 | 21.24 | 21.33 | 21.09 |
| 4.50 | 11.55 | 11.05 | 10.63 | 36.94 | 35.42 | 34.94 | 21.22 | 21.31 | 21.07 |
| 4.60 | 11.17 | 10.71 | 10.23 | 36.86 | 35.33 | 34.86 | 21.21 | 21.28 | 21.06 |
| 4.70 | 11.03 | 10.57 | 10.10 | 36.76 | 35.23 | 34.78 | 21.19 | 21.26 | 21.04 |
| 4.80 | 10.79 | 10.39 | 9.98 | 36.65 | 35.13 | 34.69 | 21.17 | 21.23 | 21.03 |
| 4.90 | 10.56 | 10.16 | 9.74 | 36.53 | 35.01 | 34.59 | 21.14 | 21.20 | 21.01 |
| 5.00 | 10.32 | 9.89 | 9.43 | 36.41 | 34.89 | 34.49 | 21.12 | 21.17 | 20.99 |
| 5.10 | 10.06 | 9.67 | 9.29 | 36.27 | 34.76 | 34.37 | 21.10 | 21.14 | 20.98 |
| 5.20 | 9.83 | 9.41 | 9.05 | 36.13 | 34.63 | 34.26 | 21.07 | 21.11 | 20.96 |
| 5.30 | 9.66 | 9.30 | 8.89 | 35.97 | 34.48 | 34.13 | 21.05 | 21.07 | 20.94 |
| 5.40 | 9.43 | 9.08 | 8.72 | 35.81 | 34.33 | 34.00 | 21.02 | 21.04 | 20.92 |
| 5.50 | 9.24 | 8.87 | 8.57 | 35.63 | 34.17 | 33.85 | 20.99 | 21.00 | 20.90 |
| 5.60 | 9.04 | 8.61 | 8.23 | 35.45 | 34.00 | 33.71 | 20.96 | 20.96 | 20.88 |
| 5.70 | 8.91 | 8.51 | 8.15 | 35.25 | 33.82 | 33.55 | 20.93 | 20.93 | 20.86 |
| 5.80 | 8.73 | 8.34 | 8.05 | 35.05 | 33.63 | 33.39 | 20.90 | 20.88 | 20.84 |
| 5.90 | 8.38 | 8.00 | 7.68 | 34.84 | 33.44 | 33.22 | 20.86 | 20.84 | 20.81 |
| 6.00 | 8.08 | 7.80 | 7.39 | 34.62 | 33.24 | 33.04 | 20.83 | 20.80 | 20.79 |

(1) Includes test board loss

(2) Drain current was allowed to increase during compression measurement

Typical Performance Data


| IDS (mA) | F _{MIN} (dB) (1) | | | | | |
|-------------|---------------------------|-------|---------|-------|---------|-------|
| | VDS=+2V | | VDS=+3V | | VDS=+4V | |
| | 0.9 GHz | 2 GHz | 0.9 GHz | 2 GHz | 0.9 GHz | 2 GHz |
| 10.00 | 0.155 | 0.348 | 0.154 | 0.345 | | |
| 15.00 | 0.153 | 0.347 | 0.135 | 0.306 | 0.134 | 0.302 |
| 20.00 | 0.166 | 0.370 | 0.134 | 0.303 | | |
| 30.00 | 0.179 | 0.395 | 0.138 | 0.309 | 0.129 | 0.291 |
| 40.00 | 0.177 | 0.390 | 0.131 | 0.296 | 0.135 | 0.306 |
| 60.00 | 0.170 | 0.378 | 0.141 | 0.320 | 0.156 | 0.349 |

| FREQUENCY (GHz) | F _{MIN} (dB) (1) | | |
|--------------------|---------------------------|-------|-------|
| | VDS=3V | | |
| | 40 mA | 60 mA | 80 mA |
| 0.50 | 0.07 | 0.08 | 0.09 |
| 0.70 | 0.10 | 0.11 | 0.12 |
| 0.90 | 0.13 | 0.14 | 0.16 |
| 1.00 | 0.15 | 0.16 | 0.18 |
| 1.90 | 0.28 | 0.30 | 0.34 |
| 2.00 | 0.30 | 0.32 | 0.36 |
| 2.40 | 0.36 | 0.39 | 0.43 |
| 3.00 | 0.45 | 0.48 | 0.54 |
| 3.90 | 0.58 | 0.63 | 0.71 |
| 5.00 | 0.75 | 0.81 | 0.91 |
| 5.80 | 0.87 | 0.94 | 1.06 |
| 6.00 | 0.90 | 0.97 | 1.09 |


(1) F MIN is minimum Noise Figure

Typical Performance Curves


I-V (VGS=0.1V PER STEP) (2)




NOISE FIGURE vs IDS @ 2 GHz (1)




NOISE FIGURE vs IDS @ 0.9 GHz (1)




GAIN vs IDS @ 2 GHz (1)



GAIN vs IDS @ 0.9 GHz (1)









OIP3 vs IDS @ 2GHz (1)



(1) Includes test board loss

(2) Measured using HP4155B semiconductor parameter analyzer


Typical Performance Curves




- (1) Includes test board loss
- (2) Drain current was allowed to increase during compression measurement

Typical Performance Curves


P1dB vs FREQUENCY & TEMPERATURE (1,2)
@ VDS=3V, IDS=60mA




NF vs FREQUENCY & TEMPERATURE (1)
@ VDS=4V, IDS=60mA




GAIN vs FREQUENCY & TEMPERATURE (1)
@ VDS=4V, IDS=60mA



OIP3 vs FREQUENCY & TEMPERATURE (1)
@ VDS=4V, IDS=60mA






P1dB vs FREQUENCY & TEMPERATURE (1,2)
@ VDS=4V, IDS=60mA




- (1) Includes test board loss
- (2) Drain current was allowed to increase during compression measurement

Typical Performance Curves




(1) F_{MIN} is minimum Noise Figure

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE #. | A | B | C | D | E | F | G | H | J | K | L | M | N | P |
|---------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|---|---|----------------|----------------|
| MMM1362 | .045 (1.15) | .053 (1.35) | .073 (1.85) | .089 (2.25) | .043 (1.10) | .004 (0.10) | .071 (1.80) | .094 (2.40) | .046 (1.17) | .056 (1.43) | - | - | .022 (0.55) | .028 (0.70) |

| CASE #. | Q | R | S | T | WT, GRAM |
|---------|----------------|----------------|----------------|----------------|----------|
| MMM1362 | .010 (0.25) | .016 (0.40) | .017 (0.43) | .006 (0.15) | .007 |


Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Matte Tin plate.

Tape & Reel Packaging TR-F90

DEVICE ORIENTATION IN T&R



Applicable Case Style
MMM1362

NONE

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel | |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8 | 4 | 7 | Small quantity standards (see note) | 20 |
| | | | | 50 |
| | | | | 100 |
| | | | | 200 |
| | | | | 500 |
| | | | | 1000 |
| | | 7 | Standards | 2000 |
| | | | | 3000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

| [Applicable Case Styles](#) |

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

| [MZ4532C](#) |

 **Mini-Circuits**[®]


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION





REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|---------|-------------|----------|----|------|
| OR | M121884 | NEW RELEASE | 03/10/09 | AV | TH |
| | | | | | |
| | | | | | |

SUGGESTED MOUNTING CONFIGURATION FOR
MMM1362 CASE STYLE, "04AM02" PIN CODE



NOTES:

1. TRACE WIDTH IS SHOWN FOR REFERENCE ONLY. ACTUAL LINE WIDTH IS A FUNCTION OF SPECIFIC MATCHING CIRCUIT.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3.  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER);
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
2 PL DECIMALS ±
3 PL DECIMALS ± .005
ANGLES ±
FRACTIONS ±



INITIALS

DATE

| | | |
|----------|----|----------|
| DRAWN | AV | 03/09/09 |
| CHECKED | IL | 03/10/09 |
| APPROVED | TH | 03/10/09 |



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235


PL, 04AM02, FG873, SAV

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


| | | | |
|-----------|---------------------|--------------------------|------------|
| SIZE A | CODE IDENT 15542 | DRAWING NO: 98-PL-300 | REV: OR |
|-----------|---------------------|--------------------------|------------|

| | | |
|------------------|----------------|------------------|
| FILE: 98PL300 | SCALE: 20:1 | SHEET: 1 OF 1 |
|------------------|----------------|------------------|

Characterization Test Board




TB-471+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350B or its equivalent, Dielectric Constant=3.5, Thickness=.020"

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|--|--|
| Operating Temperature | -45° to 85°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -65° to 150° C Ambient Environment | Individual Model Data Sheet |
| Thermal Shock | -65° to 150°C, 500 Cycles | MIL-STD-883E, Method 1010.7 |
| Autoclave | 15 psig, 100% RH, 121°C, 96 hours | JESD22-A102-C, Condition C |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Solder Reflow Heat | Pb-Free Process: 260°C peak | J-STD-020C, Table 4-1, 4-2 and 5-2; Figure 5-1 |
| Moisture Sensitivity: Level 1 | Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak | J-STD-020C |
| Marking Resistance to Solvents | Solution A, C and D followed by 3 reflow cycles at 260°C peak | MIL-STD-202F, Method 215J |
| Lead Integrity | Tension - Cond. A Bonding Stress - Cond. B1 | MIL-STD-883E, Method 2004.5 |