



MMIC DIE

IQ Mixer


SMIQ-653H-D+

Mini-Circuits

Level 18 (LO Power +18 dBm) 18 to 65 GHz

THE BIG DEAL

- Wideband RF & LO, 18 to 65 GHz
- Wideband IF, DC to 20 GHz
- High L-R Isolation, 40 dB typ. at 40 GHz
- High Input IP3, +23 dBm typ.
- Useable as Up & Down Converter



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- Test & Measurement
- 5G mmWave and Back Haul Radio
- Satellite Communications
- Radar, EW and ECM Defense Systems

SEE ORDERING INFORMATION ON THE LAST PAGE

PRODUCT OVERVIEW

The SMIQ-653H-D+ is a passive, wideband in phase/ quadrature (I/Q) mixer fabricated using GaAs HBT technology. The SMIQ-653H-D+ is usable as a single-sideband upconverter for transmit applications or an image rejection mixer for receiver applications. The SMIQ-653H-D+ is ideal for application requiring excellent RF performance and a wide frequency range with RF and LO frequency range of 18 to 65 GHz and an IF frequency range of DC to 20 GHz. As a passive mixer, the SMIQ-653H-D+ offers lower noise figure than active mixers ensuring superior dynamic range for high performance applications.

KEY FEATURES

Features	Advantages
High image rejection, 25 dB typical	Improves image rejection in receiver applications
High LO-RF Isolation, 45 to 50 dB typ.	Enables excellent carrier rejection in single-sideband upconvert transmit applications
High LO-IF Isolation, 30 dB typ.	Minimizes filtering requirement in image reject mixers
Wide Bandwidth, 18 to 65 GHz	Useful in wideband systems or in several narrowband systems requiring fewer components.
Wide IF Bandwidth, DC to 20 GHz	Usable in first and second down converter applications. IF as low as DC enables use in phase detector applications
Unpackaged Die	Suitable for chip and wire hybrid assemblies.





MMIC DIE

IQ Mixer

SMIQ-653H-D+

Mini-Circuits

Level 18 (LO Power +18 dBm) 18 to 65 GHz

ELECTRICAL SPECIFICATIONS¹ AT +25°C, 50Ω, UNLESS OTHERWISE NOTED.

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
RF Frequency Range		18		65	GHz
LO Frequency Range		18		65	GHz
IF Frequency Range		DC		20	GHz
LO Power		+17	+18	+19	dBm
Conversion Loss	18 - 43.5		10.5		dB
	43.5 - 65		11.3		
Amplitude Unbalance	18 - 43.5		0.5		dB
	43.5 - 65		0.2		
Phase Unbalance	18 - 43.5		3.9		deg
	43.5 - 65		8.6		
Image Rejection (Tested as an Upconverter)	18 - 43.5		25		dB
	43.5 - 65		30		
Image Rejection (Tested as a Downconverter)	18 - 43.5		21		dB
	43.5 - 65		24		
LO-RF Isolation	18 - 43.5		45		dB
	43.5 - 65		50		
LO-I Isolation	18 - 43.5		43		dB
	43.5 - 65		38		
LO-Q Isolation	18 - 43.5		33		dB
	43.5 - 65		30		
RF-I Isolation	18 - 43.5		29		dB
	43.5 - 65		50		
RF-Q Isolation	18 - 43.5		38		dB
	43.5 - 65		41		
Input Power at 1dB Compression	18 - 65		10		dBm
Input IP3 (I) Lower Side Band	20 - 43.5		26		dBm
	43.5 - 65		25		
Input IP3 (Q) Lower Side Band	20 - 43.5		27		dBm
	43.5 - 65		25		
Input IP3 (I) Upper Side Band	20 - 43.5		26		dBm
	43.5 - 65		25		
Input IP3 (Q) Upper Side Band	20 - 43.5		27		dBm
	43.5 - 65		25		

1. Electrical specifications are measured by soldering Die to Mini-Circuits Die Test and characterization board. Data is de-embedded to the bondwires.

2. Unless otherwise specified IF=200 MHz, LO Power = +18 dBm.

MAXIMUM RATINGS³

Parameter	Ratings
Operating Temperature	-40°C to +85°C

3. Permanent damage may occur if any of these limits are exceeded.





MMIC DIE


IQ Mixer

SMIQ-653H-D+

Mini-Circuits

Level 18 (LO Power +18 dBm) 18 to 65 GHz

BONDING PAD POSITION



PAD DESCRIPTION

Function	Pad Number	Description
RF	1	RF Port. Connects to RF Output for Up converters and RF Input for Down converters.
LO	4	LO Port. Connects to LO Input
IF Q	7	IF Q Port. Connects to the IF Q Input for Up converters and IF Q Output for Down converters
IF I	10	IF I Port. Connects to the IF I Input for Up converters and IF I Output for Down converters
GROUND	2, 3, 5, 6, 8, 9, 11, 12	Ground

DIE DIMENSIONS IN μm , TYP.

L1	L2	L3	L4	L5	L6
86.0	1996.0	2186.0	2376.0	2585.0	2670.0

H1	H2	H3	H4	H5	H6
86.0	586.0	660.0	776.0	850.0	966.0

H7	H8	H9	H10	H11
1040.0	1260.0	1450.0	1640.0	1900.0

Thickness	Die Size	Pad Size 1,7 &10	Pad Size 4	Pad Size 2, 3, 5, 6, 8, 9, 11, 12
100	2670 x 1900	92 x 172	172 x 92	92 x 92



MMIC DIE

IQ Mixer

SMIQ-653H-D+

Level 18 (LO Power +18 dBm) 18 to 65 GHz

CHARACTERIZATION TEST AND APPLICATION CIRCUITS




Figure 1A: Block diagram of test circuit used to characterize: Conversion Loss, Amp. Unbl., Ph. Unbl. Isolation, Return Loss (RF, I & Q) & IP3 from 20-45 GHz

Test conditions:

For CL, Return loss and isolation:

RF= -10 dBm, LO=+17 to +19 dBm, IF=200 MHz, 2 GHz, 3 GHz

For IP3: RF =-10dBm/Tone, LO= +17 to +19 dBm. Two tones, spaced 1 MHz Apart




Figure 1B: Block diagram of test circuit used to characterize: Conversion Loss, Amp. Unbl., Ph. Unbl. Isolation , Return Loss (RF, I & Q) & IP3 from 35-67GHz

Test conditions:

For CL, Return loss and isolation:

RF= -10 dBm. LO=+17 to +19 dBm, IF=200 MHz, 2 GHz, 3 GHz

For IP3: RF =-10 dBm/Tone, LO= +17 to +19 dBm. Two tones, spaced 1 MHz Apart





MMIC DIE

IQ Mixer

SMIQ-653H-D+

Mini-Circuits

Level 18 (LO Power +18 dBm) 18 to 65 GHz




Figure 1C: Block diagram of Test Circuit used for characterization of Image Rejection from 20-45GHz

Test conditions:
RF= -10 dBm, LO=+17 to +19 dBm, IF=200 MHz, 2 GHz, 3 GHz




Figure 1D: Block diagram of Test Circuit used for characterization of Image Rejection from 35-67GHz

Test conditions:
RF= -10 dBm, LO=+17 to +19 dBm, IF=200 MHz, 2 GHz, 3 GHz



MMIC DIE

IQ Mixer

SMIQ-653H-D+

Mini-Circuits

Level 18 (LO Power +18 dBm) 18 to 65 GHz




Figure 1E: Block diagram of test circuit used to characterize: Compression from 20-45GHz

Test Conditions:

RF = +10 dBm & -10 dBm, LO = +17 to +19 dBm, IF = 200 MHz, 2 GHz, 3 GHz

Compression = CL(RF=+10 dBm) - CL(RF=-10 dBm)




Figure 1F: Block diagram of test circuit used to characterize: Compression from 35-67GHz

Test Conditions:

RF = +10 dBm & -10 dBm, LO = +17 to +19 dBm, IF = 200 MHz, 2 GHz, 3 GHz

Compression = CL(RF=+10 dBm) - CL(RF=-10 dBm)





MMIC DIE

IQ Mixer

SMIQ-653H-D+

Mini-Circuits

Level 18 (LO Power +18 dBm) 18 to 65 GHz

APPLICATION CONFIGURATION AND SIDE BAND SELECTION

For side band selection in up or down converter configurations an external 90deg Hybrid is needed. This will allow for the termination of the phase difference from the two IF ports. See Simplified schematic below for port orientation.

In Downconverter applications


For lower side band selection connect the I port to the 90 deg port of the hybrid and the Q port to the 0deg port of the hybrid. This will send the upper sideband signal to the terminated output. For upper side band selection connect the I port to the 0 deg port of the hybrid and the Q port to the 90deg port of the hybrid. This will send the lower sideband signal to the terminated output.

In Upconverter applications


For lower side band selection connect the I port to the 0 deg port of the hybrid and the Q port to the 90deg port of the hybrid. This will send the upper sideband signal to the terminated output.

For upper side band selection connect the I port to the 0 deg port of the hybrid and the Q port to the 90deg port of the hybrid. This will send the lower sideband signal to the terminated output.


SIMPLIFIED SCHEMATIC



ASSEMBLY DIAGRAM



ASSEMBLY PROCEDURE

1. Storage
Die should be stored in a dry nitrogen purged desiccators or equivalent.
2.  ESD
MMIC Mixer Die are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be open in clean room conditions at an appropriately grounded antistatic workstation.
3. Die Handling and Attachment
Devices need careful handling using correctly designed collets, it is recommended to handle the chip along the edges with a custom design collet. The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are Ablestik 84-1 LMISR4 or equivalents. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. The surface of the chip has exposed air bridges and should not be touched with vacuum collet, tweezers or fingers.
4. Wire Bonding
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the Die gold bond pads. Thermo-sonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1mil diameter. Bonds must be made from the bond pads on the die to the packaged or substrate. All bond wire length and bond wire height should be kept as short as possible unless specified by the Assembly Drawing to minimize performance degradation due to undesirable series inductance.



MMIC DIE







IQ Mixer

SMIQ-653H-D+

Mini-Circuits

Level 18 (LO Power +18 dBm) 18 to 65 GHz

TYPICAL PERFORMANCE CURVES





MMIC DIE

IQ Mixer






SMIQ-653H-D+

Level 18 (LO Power +18 dBm) 18 to 65 GHz

TYPICAL PERFORMANCE CURVES

Conversion Loss with Fixed IF

Conversion Loss with Variable IF





MMIC DIE

IQ Mixer


SMIQ-653H-D+

Mini-Circuits


Level 18 (LO Power +18 dBm) 18 to 65 GHz

TYPICAL PERFORMANCE CURVES


L-(I) Isolation




L-(Q) Isolation




L-R Isolation



R-(I) Isolation



R-(Q) Isolation





MMIC DIE







IQ Mixer

SMIQ-653H-D+

Mini-Circuits

Level 18 (LO Power +18 dBm) 18 to 65 GHz

TYPICAL PERFORMANCE CURVES





MMIC DIE

IQ Mixer


SMIQ-653H-D+

Mini-Circuits


Level 18 (LO Power +18 dBm) 18 to 65 GHz

TYPICAL PERFORMANCE CURVES


Gain Compression (I) @ Fixed IF = 200 MHz
RF_IN = +10dBm




Gain Compression (Q) @ Fixed IF = 200 MHz
RF_IN = +10dBm




Gain Compression (I) @ Fixed IF = 2000 MHz
RF_IN = +10dBm




Gain Compression (Q) @ Fixed IF = 2000 MHz
RF_IN = +10dBm



Gain Compression (I) @ Fixed IF = 3000 MHz
RF_IN = +10dBm



Gain Compression (Q) @ Fixed IF = 3000 MHz
RF_IN = +10dBm





MMIC DIE









IQ Mixer

SMIQ-653H-D+

Mini-Circuits

Level 18 (LO Power +18 dBm) 18 to 65 GHz

TYPICAL PERFORMANCE CURVES POUT = -10 dBm/TONE WITH 1 MHz SPACING (RF2 = RF1 + 1 MHz)









MMIC DIE

IQ Mixer

SMIQ-653H-D+

Level 18 (LO Power +18 dBm) 18 to 65 GHz

TYPICAL PERFORMANCE CURVES POUT = -10 dBm/TONE WITH 1 MHz SPACING (RF2 = RF1 + 1 MHz)





MMIC DIE









IQ Mixer

SMIQ-653H-D+

Mini-Circuits

Level 18 (LO Power +18 dBm) 18 to 65 GHz

TYPICAL PERFORMANCE CURVES POUT = -10 dBm/TONE WITH 1 MHz SPACING (RF2 = RF1 + 1 MHz)





MMIC DIE





IQ Mixer

SMIQ-653H-D+

Mini-Circuits

Level 18 (LO Power +18 dBm) 18 to 65 GHz

TYPICAL PERFORMANCE CURVES POUT = -10 dBm/TONE WITH 1 MHz SPACING (RF2 = RF1 + 1 MHz)





MMIC DIE

IQ Mixer

SMIQ-653H-D+

Mini-Circuits


Level 18 (LO Power +18 dBm) 18 to 65 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD.

Performance Data	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set with and without port extension(.zip file)
Case Style	Die
Die Ordering and packaging information	Quantity, Package Small, Gel - Pak: 5,10,50,KGD* Medium†, Partial wafer: KGD*<475 Full wafer †Available upon request contact sales representative Refer to AN-60-067
Die Marking	EL-MIX-8_A
Environmental Ratings	ENV80

*Known Good Die ('KGD') means that the die in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such die fall within a predefined range. While DC testing is not definitive, it does provide a higher degree of confidence that die are capable of meeting typical RF electrical performance specified by Mini-Circuits.

MSL TEST FLOW CHART



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained there in. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an As is basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Die (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Die.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



Frequency Mixer

SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	Image Rejection (UP Conv. Mode) IF FIXED @IF(OUT)=200MHz			RF (IN) (MHz)	LO (MHz)	Image Rejection (UP Conv. Mode) IF FIXED @IF(OUT)=200MHz			RF (IN) (MHz)	LO (MHz)	Image Rejection (UP Conv. Mode) IF FIXED @IF(OUT)=3000MHz		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+17	+18	+19			+17	+18	+19			+17	+18	+19
18400.0	18200.0	13.84	13.78	13.88	18000.0	16000.0				18000.0	15000.0			
19000.0	18800.0	16.72	17.25	17.73	19000.0	17000.0				19000.0	16000.0			
20000.0	19800.0	23.51	23.47	22.94	20000.0	18000.0				20000.0	17000.0			
21000.0	20800.0	23.70	23.18	22.62	21000.0	19000.0				21000.0	18000.0			
22000.0	21800.0	25.15	24.51	23.78	22000.0	20000.0	29.64	28.35	27.47	22000.0	19000.0			
23000.0	22800.0	26.57	25.48	24.38	23000.0	21000.0	24.86	24.66	24.59	23000.0	20000.0			
24000.0	23800.0	26.28	25.19	24.21	24000.0	22000.0	31.29	34.01	36.69	24000.0	21000.0	20.57	21.19	22.21
25000.0	24800.0	23.41	22.99	22.59	25000.0	23000.0	31.77	34.32	37.20	25000.0	22000.0	24.13	25.17	26.59
26000.0	25800.0	24.40	23.67	22.86	26000.0	24000.0	30.74	31.20	31.12	26000.0	23000.0	25.29	26.38	27.79
27000.0	26800.0	26.11	25.90	25.96	27000.0	25000.0	29.26	29.18	28.75	27000.0	24000.0	27.17	28.00	28.58
28000.0	27800.0	28.17	28.13	28.27	28000.0	26000.0	29.78	29.60	29.06	28000.0	25000.0	26.50	26.82	27.02
29000.0	28800.0	33.02	33.95	34.53	29000.0	27000.0	30.66	32.27	33.46	29000.0	26000.0	27.08	27.16	27.15
30000.0	29800.0	31.37	34.57	37.42	30000.0	28000.0	28.03	28.63	29.63	30000.0	27000.0	26.38	27.27	27.96
31000.0	30800.0	26.35	28.01	29.79	31000.0	29000.0	25.97	25.84	25.96	31000.0	28000.0	24.28	24.59	24.85
32000.0	31800.0	28.22	30.81	32.40	32000.0	30000.0	24.92	24.74	24.56	32000.0	29000.0	22.87	22.82	22.85
33000.0	32800.0	30.74	35.51	34.23	33000.0	31000.0	24.02	23.75	23.45	33000.0	30000.0	21.09	20.97	20.85
34000.0	33800.0	26.90	27.01	26.46	34000.0	32000.0	26.07	24.21	22.44	34000.0	31000.0	19.85	19.73	19.58
35200.0	35000.0	29.35	26.68	25.55	35000.0	33000.0	24.49	23.23	22.34	35000.0	32000.0	21.23	20.12	19.01
36000.0	35800.0	38.68	31.89	28.70	36000.0	34000.0	34.83	29.63	26.19	36000.0	33000.0	23.76	22.93	21.92
37000.0	36800.0	37.33	33.17	29.75	37000.0	35000.0	34.60	29.37	26.85	37000.0	34000.0	26.06	23.64	21.78
38000.0	37800.0	32.55	30.99	28.80	38000.0	36000.0	26.37	25.43	23.87	38000.0	35000.0	25.65	23.71	22.67
39000.0	38800.0	30.04	29.71	28.45	39000.0	37000.0	25.34	24.96	24.25	39000.0	36000.0	24.69	22.48	20.67
40000.0	39800.0	22.32	22.55	22.96	40000.0	38000.0	21.54	21.56	21.47	40000.0	37000.0	23.67	22.86	21.85
41000.0	40800.0	20.10	20.42	20.63	41000.0	39000.0	19.80	19.52	18.89	41000.0	38000.0	20.68	19.80	18.91
42000.0	41800.0	20.02	20.46	20.73	42000.0	40000.0	20.91	20.64	20.35	42000.0	39000.0	21.24	20.35	19.36
43000.0	42800.0	19.50	19.82	20.12	43000.0	41000.0	21.71	21.66	21.44	43000.0	40000.0	22.70	22.00	21.68
44000.0	43800.0	19.70	19.81	20.05	44000.0	42000.0	22.97	22.97	22.90	44000.0	41000.0	23.65	23.13	22.47
45000.0	44800.0	24.63	24.75	24.71	45000.0	43000.0	24.24	24.48	24.71	45000.0	42000.0	25.12	24.95	24.84
46000.0	45800.0	23.89	24.20	24.28	46000.0	44000.0	24.82	25.14	25.22	46000.0	43000.0	24.66	24.93	24.85
47000.0	46800.0	23.86	24.16	24.57	47000.0	45000.0	22.65	23.05	23.38	47000.0	44000.0	24.76	24.90	24.90
48000.0	47800.0	24.57	25.01	25.57	48000.0	46000.0	20.37	20.69	21.06	48000.0	45000.0	23.35	23.94	24.01
49000.0	48800.0	27.24	26.21	26.33	49000.0	47000.0	20.46	21.07	21.62	49000.0	46000.0	22.18	22.66	23.05
50000.0	49800.0	30.57	33.56	32.74	50000.0	48000.0	21.82	22.23	22.58	50000.0	47000.0	21.90	22.78	23.60
51000.0	50800.0	35.23	32.27	30.50	51000.0	49000.0	24.97	23.85	23.83	51000.0	48000.0	23.48	24.24	24.96
52000.0	51800.0	31.44	29.20	27.70	52000.0	50000.0	30.44	27.54	25.32	52000.0	49000.0	24.32	24.51	24.76
53000.0	52800.0	30.54	30.36	29.79	53000.0	51000.0	24.93	24.09	23.47	53000.0	50000.0	24.43	25.00	24.92
54000.0	53800.0	37.24	36.30	33.49	54000.0	52000.0	23.23	22.49	22.05	54000.0	51000.0	24.46	24.12	23.83
55000.0	54800.0	35.34	32.13	30.40	55000.0	53000.0	29.59	25.86	24.91	55000.0	52000.0	25.44	25.14	24.84
56000.0	55800.0	39.31	34.57	32.32	56000.0	54000.0	26.33	24.94	24.22	56000.0	53000.0	29.21	29.53	28.63
57000.0	56800.0	44.45	38.44	34.20	57000.0	55000.0	27.61	26.61	25.56	57000.0	54000.0	26.96	26.77	26.30
58000.0	57800.0	40.64	34.32	31.64	58000.0	56000.0	28.42	27.08	26.64	58000.0	55000.0	26.97	26.90	26.90
59000.0	58800.0	42.50	42.50	37.55	59000.0	57000.0	31.60	30.43	29.45	59000.0	56000.0	24.71	25.05	25.78
60000.0	59800.0	30.25	35.49	36.89	60000.0	58000.0	31.18	29.83	27.89	60000.0	57000.0	25.44	26.23	27.00
61000.0	60800.0	34.01	31.59	31.23	61000.0	59000.0	34.99	32.56	31.31	61000.0	58000.0	30.08	31.36	31.85
62000.0	61800.0	30.49	28.73	27.47	62000.0	60000.0	36.92	32.65	31.78	62000.0	59000.0	28.09	28.83	28.57
63000.0	62800.0	28.46	29.88	28.88	63000.0	61000.0	29.03	28.04	27.25	63000.0	60000.0	29.25	29.49	29.56
64000.0	63800.0	26.54	25.07	23.33	64000.0	62000.0	27.79	26.34	25.89	64000.0	61000.0	28.41	28.07	27.65
65000.0	64800.0	21.26	19.75	19.08	65000.0	63000.0	27.29	24.96	24.10	65000.0	62000.0	26.40	25.89	25.57



Frequency Mixer

SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	Image Rejection (DOWN Conv. Mode) IF FIXED @IF(OUT)=200MHz			RF (IN) (MHz)	LO (MHz)	Image Rejection (DOWN Conv. Mode) IF FIXED @IF(OUT)=200MHz			RF (IN) (MHz)	LO (MHz)	Image Rejection (DOWN Conv. Mode) IF FIXED @IF(OUT)=3000MHz		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+17	+18	+19			+17	+18	+19			+17	+18	+19
18400.0	18200.0	18.63	20.34	22.11	18400.0	16400.0				18400.0	15400.0			
19000.0	18800.0	21.35	21.93	22.59	19000.0	17000.0				19000.0	16000.0			
20000.0	19800.0	22.56	22.96	23.41	20000.0	18000.0				20000.0	17000.0			
21000.0	20800.0	23.30	22.70	22.41	21000.0	19000.0				21000.0	18000.0			
22000.0	21800.0	22.43	23.88	26.12	22000.0	20000.0	35.35	40.88	29.71	22000.0	19000.0			
23000.0	22800.0	22.53	23.51	24.75	23000.0	21000.0	22.53	23.61	24.99	23000.0	20000.0			
24000.0	23800.0	22.49	23.45	24.76	24000.0	22000.0	25.48	27.62	31.10	24000.0	21000.0	27.20	26.52	25.76
25000.0	24800.0	22.86	23.63	24.56	25000.0	23000.0	27.40	29.94	33.49	25000.0	22000.0	31.53	32.81	31.89
26000.0	25800.0	22.24	22.82	23.56	26000.0	24000.0	32.86	36.28	41.45	26000.0	23000.0	26.90	27.93	28.54
27000.0	26800.0	21.41	21.51	21.63	27000.0	25000.0	31.48	32.97	34.84	27000.0	24000.0	29.38	30.07	30.59
28000.0	27800.0	19.15	19.49	19.61	28000.0	26000.0	30.64	30.83	31.53	28000.0	25000.0	33.22	33.28	33.16
29000.0	28800.0	17.93	17.95	18.06	29000.0	27000.0	28.26	29.85	31.11	29000.0	26000.0	30.84	32.09	33.01
30000.0	29800.0	17.11	17.09	17.13	30000.0	28000.0	25.03	25.64	25.88	30000.0	27000.0	30.59	31.77	32.95
31000.0	30800.0	16.92	16.61	16.36	31000.0	29000.0	23.74	23.69	23.71	31000.0	28000.0	28.32	29.81	30.79
32000.0	31800.0	17.24	16.62	15.88	32000.0	30000.0	23.10	22.82	22.63	32000.0	29000.0	26.29	26.71	27.87
33000.0	32800.0	17.33	16.34	15.49	33000.0	31000.0	24.63	23.64	22.63	33000.0	30000.0	25.88	26.10	26.41
34000.0	33800.0	17.97	16.96	16.01	34000.0	32000.0	25.28	22.93	20.79	34000.0	31000.0	25.92	26.19	26.36
35000.0	34800.0	21.25	19.85	18.41	35000.0	33000.0	21.44	20.02	18.96	35000.0	32000.0	35.44	34.23	29.28
36000.0	35800.0	21.69	20.49	18.99	36000.0	34000.0	30.12	27.66	24.30	36000.0	33000.0	31.66	36.64	33.01
37000.0	36800.0	22.13	21.34	19.98	37000.0	35000.0	28.00	30.78	27.36	37000.0	34000.0	27.22	31.64	34.43
38000.0	37800.0	22.38	21.97	20.88	38000.0	36000.0	25.46	26.66	25.13	38000.0	35000.0	25.37	29.25	32.68
39000.0	38800.0	22.53	22.31	21.15	39000.0	37000.0	25.21	27.01	27.23	39000.0	36000.0	22.00	26.83	36.90
40000.0	39800.0	23.10	24.33	25.53	40000.0	38000.0	26.03	28.19	31.28	40000.0	37000.0	21.42	22.70	24.03
41000.0	40800.0	33.99	38.53	40.53	41000.0	39000.0	44.27	35.01	30.54	41000.0	38000.0	25.70	26.55	27.31
42000.0	41800.0	31.74	32.53	32.07	42000.0	40000.0	31.41	32.17	30.94	42000.0	39000.0	32.58	34.10	32.17
43000.0	42800.0	31.26	31.38	30.91	43000.0	41000.0	29.00	29.17	27.77	43000.0	40000.0	32.98	36.35	40.45
44000.0	43800.0	24.69	25.08	25.09	44000.0	42000.0	25.47	25.36	24.87	44000.0	41000.0	34.64	39.72	36.64
45000.0	44800.0	23.88	24.57	25.15	45000.0	43000.0	23.43	24.35	24.94	45000.0	42000.0	27.23	29.08	31.66
46000.0	45800.0	23.87	24.38	24.89	46000.0	44000.0	26.29	27.67	28.58	46000.0	43000.0	27.37	29.38	31.69
47000.0	46800.0	26.09	26.54	26.92	47000.0	45000.0	25.34	26.52	27.29	47000.0	44000.0	27.89	30.75	32.61
48000.0	47800.0	30.20	29.87	29.71	48000.0	46000.0	24.34	25.74	26.94	48000.0	45000.0	27.14	27.97	28.85
49000.0	48800.0	34.34	36.51	36.09	49000.0	47000.0	30.12	30.77	31.05	49000.0	46000.0	25.97	26.30	27.02
50000.0	49800.0	23.86	31.58	38.86	50000.0	48000.0	38.87	37.38	35.93	50000.0	47000.0	27.97	27.25	27.14
51000.0	50800.0	42.67	37.23	34.86	51000.0	49000.0	34.38	39.76	43.72	51000.0	48000.0	26.96	25.88	25.20
52000.0	51800.0	27.89	27.99	27.30	52000.0	50000.0	26.61	34.22	35.07	52000.0	49000.0	28.82	26.43	24.88
53000.0	52800.0	20.88	21.77	22.45	53000.0	51000.0	26.40	25.61	25.07	53000.0	50000.0	24.18	24.28	22.53
54000.0	53800.0	20.89	21.61	22.21	54000.0	52000.0	19.80	20.40	20.81	54000.0	51000.0	18.38	18.16	18.11
55000.0	54800.0	20.47	20.89	21.22	55000.0	53000.0	18.44	19.14	19.80	55000.0	52000.0	17.80	17.82	17.76
56000.0	55800.0	18.10	18.79	19.36	56000.0	54000.0	19.88	20.09	20.26	56000.0	53000.0	18.33	18.23	18.25
57000.0	56800.0	16.34	17.04	17.77	57000.0	55000.0	19.28	20.04	20.64	57000.0	54000.0	17.79	17.93	18.30
58000.0	57800.0	17.06	17.83	18.52	58000.0	56000.0	18.13	19.01	19.85	58000.0	55000.0	17.83	17.96	18.23
59000.0	58800.0	16.40	17.15	17.91	59000.0	57000.0	17.37	17.99	18.63	59000.0	56000.0	17.08	17.55	17.81
60000.0	59800.0	16.89	17.19	17.40	60000.0	58000.0	17.67	18.83	19.88	60000.0	57000.0	15.58	16.17	16.69
61000.0	60800.0	18.53	19.01	19.32	61000.0	59000.0	15.65	16.45	17.02	61000.0	58000.0	15.81	16.88	17.79
62000.0	61800.0	18.59	19.18	19.67	62000.0	60000.0	16.28	16.85	17.13	62000.0	59000.0	15.76	16.09	16.31
63000.0	62800.0	18.49	19.07	19.33	63000.0	61000.0	18.01	18.85	19.20	63000.0	60000.0	14.76	15.27	15.46
64000.0	63800.0	18.82	20.80	21.45	64000.0	62000.0	17.90	18.64	19.01	64000.0	61000.0	13.99	14.67	15.35
65000.0	64800.0	21.74	23.18	24.18	65000.0	63000.0	17.43	17.92	18.01	65000.0	62000.0			



Frequency Mixer

SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS VS. RF FREQUENCY @IF = 200 MHz			IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. RF FREQUENCY @IF = 2000 MHz			IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. RF FREQUENCY @IF = 3000 MHz		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+17	+18	+19			+17	+18	+19			+17	+18	+19
18000.0	18200.0	11.46	11.41	11.47	18000.0	20000.0	12.14	12.14	12.25	18000.0	21000.0	11.79	11.91	12.15
19000.0	19200.0	10.39	10.28	10.24	19000.0	21000.0	10.08	10.21	10.41	19000.0	22000.0	10.01	10.18	10.46
20000.0	20200.0	9.44	9.31	9.25	20000.0	22000.0	9.11	9.21	9.41	20000.0	23000.0	9.30	9.51	9.80
21000.0	21200.0	8.71	8.65	8.69	21000.0	23000.0	8.72	8.89	9.15	21000.0	24000.0	9.00	9.20	9.49
22000.0	22200.0	8.29	8.33	8.48	22000.0	24000.0	8.67	8.88	9.18	22000.0	25000.0	8.77	9.03	9.39
23000.0	23200.0	8.93	9.09	9.37	23000.0	25000.0	9.31	9.56	9.86	23000.0	26000.0	9.54	9.77	10.01
24000.0	24200.0	10.07	10.24	10.45	24000.0	26000.0	10.53	10.76	11.00	24000.0	27000.0	10.74	11.06	11.30
25000.0	25200.0	10.61	10.82	11.02	25000.0	27000.0	10.97	11.28	11.54	25000.0	28000.0	10.97	11.37	11.81
26000.0	26200.0	10.84	11.14	11.51	26000.0	28000.0	11.09	11.49	11.98	26000.0	29000.0	11.22	11.56	12.08
27000.0	27200.0	11.37	11.72	12.19	27000.0	29000.0	11.66	12.03	12.58	27000.0	30000.0	11.69	11.98	12.47
28000.0	28200.0	11.77	12.16	12.72	28000.0	30000.0	11.89	12.20	12.64	28000.0	31000.0	11.92	12.17	12.60
29000.0	29200.0	11.39	11.78	12.39	29000.0	31000.0	11.48	11.77	12.24	29000.0	32000.0	11.40	11.60	11.99
30000.0	30200.0	11.70	12.05	12.59	30000.0	32000.0	11.60	11.79	12.22	30000.0	33000.0	11.57	11.85	12.35
31000.0	31200.0	11.70	12.02	12.56	31000.0	33000.0	11.77	12.08	12.61	31000.0	34000.0	11.81	12.09	12.59
32000.0	32200.0	11.13	11.39	11.90	32000.0	34000.0	11.29	11.62	12.19	32000.0	35000.0	11.47	11.69	12.14
33000.0	33200.0	10.78	11.07	11.59	33000.0	35000.0	11.60	11.72	12.05	33000.0	36000.0	12.29	12.36	12.62
34000.0	34200.0	10.17	10.39	10.83	34000.0	36000.0	10.76	10.93	11.28	34000.0	37000.0	10.56	10.70	11.08
35000.0	35200.0	9.94	10.59	11.00	35000.0	37000.0	9.55	9.47	9.76	35000.0	38000.0	9.60	9.58	9.92
36000.0	36200.0	8.78	9.02	9.55	36000.0	38000.0	9.21	9.15	9.44	36000.0	39000.0	9.23	9.26	9.61
37000.0	37200.0	8.99	9.17	9.41	37000.0	39000.0	9.40	9.42	9.74	37000.0	40000.0	9.36	9.34	9.53
38000.0	38200.0	9.32	9.51	9.82	38000.0	40000.0	9.69	9.58	9.76	38000.0	41000.0	9.48	9.50	9.88
39000.0	39200.0	9.28	9.45	9.74	39000.0	41000.0	9.53	9.46	9.81	39000.0	42000.0	9.33	9.26	9.53
40000.0	40200.0	9.48	9.55	9.73	40000.0	42000.0	9.55	9.38	9.55	40000.0	43000.0	9.78	9.51	9.59
41000.0	41200.0	9.24	9.28	9.52	41000.0	43000.0	9.78	9.41	9.47	41000.0	44000.0	9.83	9.60	9.71
42000.0	42200.0	9.77	9.70	9.80	42000.0	44000.0	10.20	9.97	10.13	42000.0	45000.0	10.38	10.09	10.16
43000.0	43200.0	11.07	10.98	11.06	43000.0	45000.0	11.57	11.21	11.22	43000.0	46000.0	11.64	11.38	11.48
44000.0	44200.0	12.00	11.88	11.94	44000.0	46000.0	12.56	12.17	12.26	44000.0	47000.0	13.07	12.47	12.37
45000.0	45200.0	12.18	11.98	11.97	45000.0	47000.0	13.00	12.35	12.22	45000.0	48000.0	12.77	12.35	12.37
47000.0	47200.0	11.69	11.30	11.29	47000.0	49000.0	12.46	11.69	11.51	47000.0	50000.0	13.70	12.29	11.90
48000.0	48200.0	11.16	10.96	11.04	48000.0	50000.0	13.17	11.81	11.53	48000.0	51000.0	12.31	11.67	11.53
49000.0	49200.0	11.40	10.69	10.43	49000.0	51000.0	11.47	10.90	10.81	49000.0	52000.0	11.57	11.08	10.96
50000.0	50200.0	12.16	11.05	10.59	50000.0	52000.0	11.34	10.86	10.86	50000.0	53000.0	11.85	11.02	10.75
51000.0	51200.0	11.35	11.20	11.32	51000.0	53000.0	12.38	11.57	11.34	51000.0	54000.0	12.01	11.50	11.44
52000.0	52200.0	11.65	11.42	11.41	52000.0	54000.0	12.17	11.67	11.60	52000.0	55000.0	12.31	11.90	11.87
53000.0	53200.0	11.10	10.72	10.69	53000.0	55000.0	11.81	11.38	11.41	53000.0	56000.0	12.23	11.82	11.79
54000.0	54200.0	10.43	10.22	10.26	54000.0	56000.0	11.44	11.00	11.00	54000.0	57000.0	11.43	10.98	10.93
55000.0	55200.0	10.33	10.17	10.18	55000.0	57000.0	10.87	10.42	10.35	55000.0	58000.0	10.46	10.26	10.47
56000.0	56200.0	10.73	10.57	10.59	56000.0	58000.0	10.83	10.62	10.82	56000.0	59000.0	10.81	10.55	10.57
57000.0	57200.0	11.19	10.99	10.96	57000.0	59000.0	11.20	10.95	10.97	57000.0	60000.0	11.31	10.95	10.96
58000.0	58200.0	10.83	10.87	11.01	58000.0	60000.0	11.43	11.02	11.00	58000.0	61000.0	11.04	10.89	10.91
59000.0	59200.0	10.92	10.76	10.68	59000.0	61000.0	10.87	10.66	10.67	59000.0	62000.0	11.07	10.79	10.72
60000.0	60200.0	10.43	10.35	10.31	60000.0	62000.0	10.76	10.44	10.41	60000.0	63000.0	11.77	11.19	10.90
61000.0	61200.0	10.36	10.40	10.54	61000.0	63000.0	11.58	11.13	10.93	61000.0	64000.0	11.80	10.98	10.82
62000.0	62200.0	11.92	11.68	11.60	62000.0	64000.0	13.06	12.14	11.95	62000.0	65000.0	12.97	12.32	12.10
63000.0	63200.0	14.17	13.71	13.42	63000.0	65000.0	14.26	13.56	13.30	63000.0	66000.0	14.93	14.10	13.66
64000.0	64200.0	13.86	13.34	13.06	64000.0	66000.0	14.70	13.89	13.48	64000.0	67000.0	15.71	15.04	14.66
65000.0	65200.0	12.33	11.98	11.87	65000.0	67000.0	14.23	13.62	13.26					



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site www.minicircuits.com



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
SMIQ-653H-D+
9/14/2022
Page 3 of 16

Frequency Mixer

SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	IF (MHz)	CONVERSION LOSS VS. IF FREQUENCY @ FIXED LO = 20GHz			RF (IN) (MHz)	IF (MHz)	CONVERSION LOSS VS. IF FREQUENCY @ FIXED LO = 65GHz		
		@LO (dBm)					@LO (dBm)		
		+17	+18	+19			+17	+18	+19
20010.0	10.0	9.73	9.55	9.46	35000.0	30000.0	29.63	29.99	30.27
20100.0	100.0	9.56	9.38	9.27	36000.0	29000.0	25.95	26.34	26.67
20200.0	200.0	9.54	9.33	9.22	37000.0	28000.0	23.36	23.69	23.96
20300.0	300.0	9.77	9.54	9.41	38000.0	27000.0	21.40	21.59	21.74
20400.0	400.0	9.75	9.51	9.37	39000.0	26000.0	18.97	18.94	19.06
20500.0	500.0	9.80	9.55	9.40	40000.0	25000.0	17.80	17.60	17.68
20600.0	600.0	9.76	9.51	9.36	41000.0	24000.0	16.71	16.22	16.17
20700.0	700.0	9.75	9.51	9.36	42000.0	23000.0	16.04	15.41	15.32
20800.0	800.0	9.84	9.60	9.46	43000.0	22000.0	16.99	16.20	15.96
20900.0	900.0	9.82	9.59	9.45	44000.0	21000.0	18.51	17.48	17.13
21000.0	1000.0	9.79	9.58	9.45	45000.0	20000.0	20.26	18.84	18.37
22000.0	2000.0	9.34	9.33	9.39	46000.0	19000.0	20.65	19.04	18.63
23000.0	3000.0	9.62	9.71	9.89	47000.0	18000.0	19.75	18.25	17.79
24000.0	4000.0	10.71	10.83	11.07	48000.0	17000.0	18.46	17.38	16.84
25000.0	5000.0	11.57	11.65	11.87	49000.0	16000.0	16.85	15.87	15.36
26000.0	6000.0	12.12	12.19	12.42	50000.0	15000.0	15.25	14.39	14.04
27000.0	7000.0	12.93	12.99	13.23	51000.0	14000.0	15.46	14.60	14.22
28000.0	8000.0	13.51	13.54	13.78	52000.0	13000.0	15.85	14.96	14.55
29000.0	9000.0	13.38	13.37	13.57	53000.0	12000.0	14.83	14.02	13.69
30000.0	10000.0	13.43	13.39	13.58	54000.0	11000.0	13.63	12.81	12.56
31000.0	11000.0	13.69	13.60	13.78	55000.0	10000.0	13.43	12.64	12.31
32000.0	12000.0	13.56	13.43	13.60	56000.0	9000.0	13.75	12.97	12.65
33000.0	13000.0	12.80	12.67	12.87	57000.0	8000.0	13.69	12.91	12.61
34000.0	14000.0	11.26	11.16	11.37	58000.0	7000.0	13.23	12.54	12.20
35000.0	15000.0	10.75	10.62	10.80	59000.0	6000.0	12.45	11.86	11.61
36000.0	16000.0	11.53	11.41	11.58	60000.0	5000.0	11.75	11.31	11.08
37000.0	17000.0	12.30	12.23	12.46	61000.0	4000.0	11.60	11.15	11.08
38000.0	18000.0	12.90	12.91	13.21	62000.0	3000.0	12.95	12.28	12.13
39000.0	19000.0	13.35	13.43	13.82	63000.0	2000.0	14.21	13.48	13.26
40000.0	20000.0	13.12	13.19	13.30	64000.0	1000.0	13.76	13.33	13.08
					64990.0	10.0	12.43	12.08	11.96

Frequency Mixer

SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	L-R ISOLATION (dB)			L-(I) ISOLATION (dB)			L-(Q) ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)			@LO (dBm)		
	+17	+18	+19	+17	+18	+19	+17	+18	+19
18200	33.85	34.49	34.92	43.78	43.86	43.57	29.09	29.18	29.34
19200	33.00	34.06	34.86	42.30	42.06	42.48	29.74	30.02	30.33
20200	32.54	33.48	34.22	37.73	38.29	39.30	29.56	30.00	30.46
21200	34.63	35.62	36.38	36.36	37.22	38.40	30.10	30.50	30.95
22200	36.11	37.01	37.71	36.17	36.79	37.59	31.25	31.64	32.04
23200	38.60	39.24	39.61	38.34	38.66	39.00	31.11	31.56	31.94
24200	41.69	42.34	42.74	41.09	39.44	38.41	31.65	31.91	32.12
25200	44.35	45.00	45.18	41.32	39.47	38.42	31.29	31.46	31.54
26200	48.21	48.74	48.86	43.52	41.84	40.79	31.43	31.50	31.60
27200	50.25	50.91	50.99	44.84	43.81	43.01	33.06	33.00	33.00
28200	51.83	54.00	56.17	43.41	43.04	42.35	33.94	33.76	33.69
29200	49.51	50.58	51.84	42.69	42.75	42.50	34.74	34.42	34.25
30200	51.67	53.77	56.14	42.36	42.63	42.67	35.20	34.84	34.62
31200	51.62	53.71	57.43	42.33	42.67	42.87	35.64	35.28	35.05
32200	56.08	58.23	61.13	42.75	43.03	43.19	36.05	35.72	35.48
33200	52.56	53.01	53.11	42.70	42.90	42.96	35.03	34.83	34.67
34200	51.25	52.14	52.92	42.79	42.98	43.03	33.37	33.27	33.20
35200	44.80	45.26	45.72	43.62	43.88	44.02	33.39	33.37	33.35
36200	42.91	43.28	43.74	43.96	44.24	44.42	33.53	33.56	33.59
37200	44.30	44.58	44.72	45.09	45.34	45.51	33.79	33.84	33.87
38200	43.26	43.68	43.97	45.01	45.26	45.46	33.01	33.12	33.21
39200	41.35	41.80	42.15	43.90	44.09	44.27	31.95	32.10	32.23
40200	40.47	41.37	42.12	42.79	43.01	43.26	35.04	35.15	35.21
41200	46.52	47.59	47.98	47.46	47.63	47.81	31.83	31.97	32.05
42200	42.28	42.72	43.08	49.47	49.41	49.40	30.84	31.00	31.13
43200	39.22	39.37	39.51	47.12	47.31	47.45	29.45	29.61	29.74
44200	35.66	36.02	36.30	35.47	35.91	36.25	28.55	28.68	28.79
45200	42.60	43.30	43.82	35.08	35.41	35.65	26.83	26.96	27.06
47200	51.49	53.26	55.22	35.77	36.12	36.43	56.00	57.95	58.10
48200	54.80	57.50	56.84	34.85	35.16	35.40	52.87	53.25	53.24
49200	54.80	55.60	55.62	35.11	35.49	35.87	49.01	48.55	49.04
50200	55.89	56.92	57.36	34.78	35.12	35.53	46.86	46.67	46.39
51200	54.03	55.52	54.49	30.29	30.53	30.71	44.78	44.61	44.72
52200	54.34	55.71	56.22	25.82	26.16	26.48	40.68	40.64	40.87
53200	52.21	54.27	56.14	27.91	28.11	28.27	36.97	36.94	36.75
54200	52.11	51.95	51.33	31.01	31.24	31.47	34.72	34.50	34.27
55200	51.16	50.48	50.74	33.36	33.43	33.47	42.45	42.43	42.16
56200	51.72	52.40	52.52	44.36	44.23	44.10	49.20	49.01	48.92
57200	52.41	53.45	53.66	49.35	49.72	49.98	53.72	53.59	52.62
58200	49.65	48.28	47.23	36.31	36.08	35.96	48.52	48.90	48.83
59200	52.20	53.78	53.77	41.07	41.08	41.07	52.12	51.90	52.18
60200	48.93	49.93	50.69	42.31	42.13	42.04	56.23	54.54	56.07
61200	46.53	47.17	47.59	39.93	40.09	40.07	58.07	57.48	58.79
62200	45.51	46.25	46.53	41.32	41.61	41.70	61.88	61.11	59.00
63200	46.02	46.81	47.65	41.95	42.52	43.08	61.65	60.59	63.16
64200	44.98	45.48	46.03	41.73	42.03	42.49	62.66	59.78	60.29
65200	43.61	43.94	44.24	41.58	41.85	42.22	59.81	59.62	60.37

Frequency Mixer

SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	R-(I) ISOLATION (dB)			R-(Q) ISOLATION (dB)			RF-R ISOLATION (dB)		
		@LO (dBm)			@LO (dBm)			@LO (dBm)		
		+17	+18	+19	+17	+18	+19	+17	+18	+19
18000.0	18200.0	26.12	26.36	26.60	31.78	32.17	32.38	3.77	3.71	3.65
19000.0	19200.0	26.58	26.54	26.58	32.78	33.20	33.57	5.64	5.41	5.25
20000.0	20200.0	27.04	26.96	26.97	30.82	31.01	31.17	7.21	7.26	7.32
21000.0	21200.0	25.24	25.50	25.84	36.46	35.91	35.07	11.03	11.35	11.68
22000.0	22200.0	22.46	22.66	23.01	31.47	30.41	29.48	13.13	13.06	13.42
23000.0	23200.0	23.54	23.46	23.48	34.49	33.77	33.06	11.83	11.99	12.41
24000.0	24200.0	24.90	24.91	25.00	38.19	37.71	37.30	6.83	6.94	7.14
25000.0	25200.0	25.05	25.10	25.19	37.50	37.16	36.92	3.92	3.94	4.05
26000.0	26200.0	26.22	26.32	26.45	39.23	39.20	39.20	4.59	4.65	4.72
27000.0	27200.0	28.07	28.12	28.28	42.73	42.64	42.47	5.58	5.71	5.76
28000.0	28200.0	28.87	28.89	28.97	43.15	42.86	42.80	4.02	4.08	4.14
29000.0	29200.0	29.44	29.48	29.55	43.70	43.59	43.30	4.25	4.35	4.40
30000.0	30200.0	30.78	30.84	30.95	45.08	44.90	44.81	4.24	4.30	4.34
31000.0	31200.0	31.58	31.62	31.74	45.00	45.20	45.48	3.67	3.82	3.82
32000.0	32200.0	31.94	31.99	32.11	42.69	42.37	42.78	4.04	4.13	4.10
33000.0	33200.0	32.27	32.29	32.37	45.28	45.56	45.36	4.55	4.73	4.70
34000.0	34200.0	31.76	31.84	31.92	43.92	44.07	44.00	5.44	5.74	5.68
35000.0	35200.0	31.00	30.85	30.83	41.28	41.21	41.37	9.62	9.44	9.25
36000.0	36200.0	31.39	31.50	31.66	40.56	40.86	40.72	13.24	13.60	13.81
37000.0	37200.0	32.73	32.84	32.95	40.15	40.13	40.23	9.66	9.95	10.21
38000.0	38200.0	34.14	34.17	34.20	37.73	37.80	37.85	8.79	9.04	9.27
39000.0	39200.0	35.05	35.14	35.13	32.42	32.45	32.64	8.35	8.57	8.66
40000.0	40200.0	32.13	32.07	32.13	26.68	26.83	26.93	9.10	9.44	9.64
41000.0	41200.0	29.81	29.97	30.03	31.63	31.77	32.03	10.78	11.21	11.37
42000.0	42200.0	29.83	29.87	30.05	38.70	38.62	38.87	8.41	8.54	8.71
43000.0	43200.0	29.00	29.09	29.23	43.00	43.19	43.14	5.60	5.75	5.84
44000.0	44200.0	26.00	26.03	26.13	35.50	35.47	35.57	4.32	4.43	4.49
45000.0	45200.0	32.36	32.54	32.69	33.52	33.64	33.79	3.55	3.66	3.73
47000.0	47200.0	56.00	57.95	58.10	37.32	37.53	37.59	4.74	4.90	5.04
48000.0	48200.0	52.87	53.25	53.24	38.36	38.40	38.52	7.25	7.54	7.79
49000.0	49200.0	49.01	48.55	49.04	37.85	38.07	38.36	7.43	7.85	8.15
50000.0	50200.0	46.86	46.67	46.39	38.81	38.63	38.77	5.78	6.11	6.35
51000.0	51200.0	44.78	44.61	44.72	39.42	39.37	39.45	5.31	5.58	5.64
52000.0	52200.0	40.68	40.64	40.87	37.15	37.24	37.45	4.86	5.04	5.20
53000.0	53200.0	36.97	36.94	36.75	32.83	32.62	32.76	6.60	6.79	6.89
54000.0	54200.0	34.72	34.50	34.27	29.01	28.88	28.79	9.88	9.83	9.74
55000.0	55200.0	42.45	42.43	42.16	34.87	34.56	34.53	17.13	16.62	16.42
56000.0	56200.0	49.20	49.01	48.92	39.04	39.14	38.63	10.59	10.64	10.88
57000.0	57200.0	53.72	53.59	52.62	40.16	39.72	39.53	6.80	6.91	7.04
58000.0	58200.0	48.52	48.90	48.83	36.37	36.21	36.08	7.24	7.52	7.49
59000.0	59200.0	52.12	51.90	52.18	44.57	44.54	44.81	8.11	8.35	8.58
60000.0	60200.0	56.23	54.54	56.07	50.41	49.21	50.29	14.70	15.04	15.26
61000.0	61200.0	58.07	57.48	58.79	52.52	53.28	52.89	9.41	9.40	9.71
62000.0	62200.0	61.88	61.11	59.00	55.06	54.59	54.83	6.21	6.31	6.47
63000.0	63200.0	61.65	60.59	63.16	53.98	54.29	53.27	4.09	4.15	4.22
64000.0	64200.0	62.66	59.78	60.29	53.02	53.93	53.61	4.44	4.50	4.62
65000.0	65200.0	59.81	59.62	60.37	51.80	50.98	51.77	9.30	9.51	9.56

Frequency Mixer **SMIQ-653H-D+**

Typical Performance Data

RF (IN) (MHz)	IF (MHz)	AMP UNBALANCE VS. RF FREQUENCY @IF = 200 MHz			PHASE UNBALANCE VS. RF FREQUENCY @IF = 200 MHz		
		@LO (dBm)			@LO (dBm)		
		+17	+18	+19	+17	+18	+19
18000.0	18200.0	-0.90	-0.61	-0.42	-6.10	-6.32	-6.33
19000.0	19200.0	-0.48	-0.31	-0.14	-7.70	-7.91	-7.43
20000.0	20200.0	-0.29	-0.28	-0.23	-4.43	-3.45	-2.54
21000.0	21200.0	-0.14	-0.10	-0.04	-1.06	-0.11	0.72
22000.0	22200.0	-0.33	-0.16	0.02	-9.55	-8.90	-7.84
23000.0	23200.0	-0.27	-0.12	0.03	-5.48	-4.72	-3.83
24000.0	24200.0	-0.18	-0.05	0.06	-4.77	-4.20	-3.59
25000.0	25200.0	-0.08	0.02	0.11	-3.94	-3.50	-3.01
26000.0	26200.0	-0.22	-0.17	-0.11	-2.64	-2.27	-2.15
27000.0	27200.0	-0.26	-0.32	-0.40	-2.77	-1.77	-1.35
28000.0	28200.0	-0.65	-0.65	-0.65	-5.97	-5.30	-4.94
29000.0	29200.0	-0.89	-0.90	-0.92	-6.43	-6.13	-5.79
30000.0	30200.0	-1.12	-1.19	-1.26	-6.11	-5.95	-5.64
31000.0	31200.0	-1.10	-1.25	-1.43	-4.54	-4.41	-4.13
32000.0	32200.0	-1.15	-1.38	-1.66	-0.09	0.37	0.62
33000.0	33200.0	-1.15	-1.48	-1.76	0.22	0.95	1.45
34000.0	34200.0	-0.98	-1.30	-1.60	5.70	5.11	4.21
35000.0	35200.0	-0.97	-1.11	-1.15	2.78	2.55	2.70
36000.0	36200.0	0.00	-0.36	-0.81	6.30	5.65	4.91
37000.0	37200.0	0.19	-0.07	-0.41	6.43	5.81	5.41
38000.0	38200.0	0.27	-0.01	-0.37	6.50	5.50	4.90
39000.0	39200.0	0.36	0.14	-0.17	6.74	5.71	4.96
40000.0	40200.0	0.99	0.79	0.55	5.12	3.99	3.07
41000.0	41200.0	0.24	0.01	-0.33	1.39	0.47	-0.31
42000.0	42200.0	0.09	-0.13	-0.37	2.83	1.89	1.08
43000.0	43200.0	-0.21	-0.38	-0.57	3.19	1.95	0.79
44000.0	44200.0	-0.58	-0.64	-0.75	4.17	3.37	2.49
45000.0	45200.0	-0.37	-0.41	-0.46	7.08	6.16	5.34
47000.0	47200.0	-0.28	-0.18	-0.17	4.09	3.89	3.61
48000.0	48200.0	-0.19	-0.08	-0.04	1.98	2.05	2.18
49000.0	49200.0	-0.66	-0.21	-0.06	0.28	0.12	0.29
50000.0	50200.0	-1.62	-0.48	-0.15	0.47	-0.04	-0.17
51000.0	51200.0	0.03	0.24	0.43	-2.14	-1.89	-1.67
52000.0	52200.0	0.01	0.26	0.42	-6.62	-5.89	-5.12
53000.0	53200.0	-0.26	0.09	0.27	-10.62	-9.40	-8.19
54000.0	54200.0	-0.20	0.06	0.28	-10.53	-9.50	-8.67
55000.0	55200.0	0.10	0.27	0.50	-13.13	-11.87	-10.61
56000.0	56200.0	0.02	0.18	0.36	-16.81	-15.07	-13.30
57000.0	57200.0	-0.18	0.01	0.13	-19.38	-17.59	-15.96
58000.0	58200.0	0.02	0.11	0.32	-17.41	-15.72	-13.75
59000.0	59200.0	-0.24	-0.11	-0.04	-17.80	-16.72	-15.70
60000.0	60200.0	-0.31	-0.18	-0.13	-16.27	-15.46	-14.89
61000.0	61200.0	-0.24	-0.14	0.01	-14.20	-13.35	-12.13
62000.0	62200.0	-0.37	-0.23	-0.14	-13.57	-13.05	-12.55
63000.0	63200.0	-1.07	-0.61	-0.41	-11.28	-11.52	-11.47
64000.0	64200.0	-1.04	-0.41	-0.23	-9.80	-9.27	-8.67
65000.0	65200.0	-1.43	-0.59	-0.26	-8.48	-7.70	-6.73

Frequency Mixer SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	IF (MHz)	AMP UNBALANCE VS. RF FREQUENCY @IF = 2000 MHz			PHASE UNBALANCE VS. RF FREQUENCY @IF = 2000 MHz		
		@LO (dBm)			@LO (dBm)		
		+17	+18	+19	+17	+18	+19
18000.0	20000.0	-0.64	-0.53	-0.37	-1.13	-0.18	0.90
19000.0	21000.0	-0.54	-0.49	-0.41	5.87	5.62	5.14
20000.0	22000.0	-0.34	-0.29	-0.23	3.71	3.39	3.34
21000.0	23000.0	0.08	0.21	0.34	-1.29	-0.72	0.06
22000.0	24000.0	-0.37	-0.25	-0.16	-1.89	-1.64	-1.07
23000.0	25000.0	-0.28	-0.17	-0.07	-0.31	-0.14	0.21
24000.0	26000.0	-0.48	-0.37	-0.25	-0.87	-0.36	0.23
25000.0	27000.0	-0.66	-0.72	-0.77	-1.39	-1.01	-0.73
26000.0	28000.0	-0.54	-0.61	-0.71	-1.89	-0.94	-0.61
27000.0	29000.0	-0.96	-0.98	-0.99	-4.79	-4.13	-3.58
28000.0	30000.0	-1.30	-1.33	-1.36	-6.46	-5.99	-5.24
29000.0	31000.0	-1.46	-1.58	-1.71	-6.43	-5.97	-5.20
30000.0	32000.0	-1.56	-1.78	-2.01	-2.68	-2.08	-1.62
31000.0	33000.0	-1.53	-1.90	-2.24	0.19	0.49	0.63
32000.0	34000.0	-1.67	-2.03	-2.31	2.09	2.04	1.77
33000.0	35000.0	-1.64	-1.91	-2.13	7.94	7.43	6.80
34000.0	36000.0	-0.82	-1.17	-1.51	7.97	7.38	6.91
35000.0	37000.0	-0.66	-0.98	-1.32	9.24	8.92	8.74
36000.0	38000.0	-0.54	-0.83	-1.12	9.63	9.13	9.02
37000.0	39000.0	-0.28	-0.51	-0.82	10.17	9.44	8.95
38000.0	40000.0	-0.16	-0.38	-0.66	10.51	9.63	9.05
39000.0	41000.0	-0.02	-0.29	-0.67	10.81	9.82	9.21
40000.0	42000.0	0.69	0.42	0.13	8.41	7.08	6.08
41000.0	43000.0	-0.08	-0.26	-0.44	4.32	3.06	2.05
42000.0	44000.0	-0.52	-0.62	-0.67	5.07	4.12	3.39
43000.0	45000.0	-0.77	-0.83	-0.86	4.49	3.80	3.29
44000.0	44200.0	-1.20	-1.27	-1.33	5.19	3.77	3.02
45000.0	45200.0	-0.89	-0.84	-0.87	7.24	6.35	5.90
47000.0	47200.0	-0.95	-0.67	-0.59	3.23	2.43	2.36
48000.0	48200.0	-0.95	-0.67	-0.59	3.23	2.43	2.36
49000.0	49200.0	-1.07	-0.73	-0.52	1.36	0.55	0.36
50000.0	50200.0	-0.66	-0.43	-0.24	-1.48	-1.65	-1.24
51000.0	51200.0	-0.99	-0.52	-0.34	-5.25	-5.11	-4.42
52000.0	52200.0	-0.61	-0.40	-0.21	-7.30	-6.53	-5.42
53000.0	53200.0	-0.58	-0.39	-0.14	-7.46	-6.82	-5.89
54000.0	54200.0	-0.04	0.06	0.19	-9.97	-9.26	-8.17
55000.0	55200.0	-0.20	-0.05	0.02	-13.86	-12.97	-11.66
56000.0	56200.0	-0.19	-0.11	0.10	-14.09	-13.02	-11.21
57000.0	57200.0	-0.41	-0.34	-0.28	-14.02	-13.34	-12.29
58000.0	58200.0	-0.69	-0.52	-0.47	-14.02	-13.79	-13.19
59000.0	59200.0	-0.61	-0.53	-0.43	-12.82	-12.33	-11.36
60000.0	60200.0	-0.72	-0.61	-0.54	-11.20	-11.24	-10.53
61000.0	61200.0	-1.20	-0.96	-0.85	-8.47	-9.03	-8.93
62000.0	62200.0	-1.64	-0.95	-0.79	-5.97	-6.74	-6.51
63000.0	63200.0	-1.87	-1.12	-0.78	-4.75	-5.32	-4.94
64000.0	64200.0	-3.03	-1.92	-1.02	-3.15	-4.50	-4.09
65000.0	65200.0	-4.29	-3.59	-3.03	0.77	-1.42	-2.80

Frequency Mixer **SMIQ-653H-D+**

Typical Performance Data

RF (IN) (MHz)	IF (MHz)	AMP UNBALANCE VS. RF FREQUENCY @IF = 3000 MHz			PHASE UNBALANCE VS. RF FREQUENCY @IF = 3000 MHz		
		@LO (dBm)			@LO (dBm)		
		+17	+18	+19	+17	+18	+19
18000.0	21000.0	-1.53	-1.39	-1.21	8.84	8.48	7.95
19000.0	22000.0	-1.45	-1.37	-1.28	5.75	4.94	4.43
20000.0	23000.0	-0.85	-0.76	-0.66	3.60	3.60	3.84
21000.0	24000.0	-0.72	-0.59	-0.48	-0.77	-0.74	-0.47
22000.0	25000.0	-0.75	-0.63	-0.53	1.42	1.71	2.26
23000.0	26000.0	-0.87	-0.79	-0.69	1.38	2.24	3.00
24000.0	27000.0	-1.01	-1.04	-1.07	-0.07	-0.11	-0.19
25000.0	28000.0	-0.99	-1.09	-1.18	-0.54	-0.01	-0.11
26000.0	29000.0	-1.09	-1.12	-1.18	-4.12	-3.36	-2.76
27000.0	30000.0	-1.41	-1.46	-1.53	-6.39	-5.70	-4.84
28000.0	31000.0	-1.55	-1.70	-1.85	-6.55	-6.05	-5.25
29000.0	32000.0	-1.68	-1.92	-2.20	-2.91	-2.50	-2.08
30000.0	33000.0	-1.97	-2.29	-2.59	0.43	0.39	0.17
31000.0	34000.0	-2.12	-2.45	-2.73	1.73	1.55	1.23
32000.0	35000.0	-2.10	-2.44	-2.74	4.56	4.42	4.38
33000.0	36000.0	-1.31	-1.66	-2.01	9.91	9.32	8.69
34000.0	37000.0	-1.28	-1.57	-1.90	9.82	9.50	9.32
35000.0	38000.0	-1.05	-1.28	-1.59	10.31	9.31	9.33
36000.0	39000.0	-0.89	-1.16	-1.49	11.35	10.06	9.94
37000.0	40000.0	-0.66	-0.90	-1.15	12.06	10.51	10.02
38000.0	41000.0	-0.53	-0.83	-1.18	12.15	10.10	9.16
39000.0	42000.0	-0.28	-0.52	-0.80	11.70	9.83	8.81
40000.0	43000.0	0.40	0.17	-0.05	8.77	6.74	5.61
41000.0	44000.0	-0.62	-0.71	-0.85	3.94	2.33	1.46
42000.0	45000.0	-0.92	-1.00	-1.06	4.59	3.02	2.35
43000.0	43200.0	-1.14	-1.18	-1.24	4.63	2.90	2.04
44000.0	44200.0	-1.69	-1.66	-1.69	5.57	4.14	3.60
45000.0	45200.0	-1.23	-1.19	-1.19	6.49	5.21	4.73
47000.0	47200.0	-2.65	-1.46	-1.12	3.77	1.70	1.61
48000.0	48200.0	-1.65	-1.22	-0.95	1.58	0.65	0.58
49000.0	49200.0	-1.31	-1.04	-0.82	-0.09	-0.53	-0.13
50000.0	50200.0	-1.56	-1.08	-0.85	-4.25	-4.27	-3.47
51000.0	51200.0	-1.00	-0.77	-0.60	-5.82	-5.37	-4.25
52000.0	52200.0	-1.01	-0.83	-0.53	-7.31	-6.83	-5.66
53000.0	53200.0	-0.67	-0.54	-0.34	-6.34	-6.11	-5.32
54000.0	54200.0	-0.62	-0.42	-0.32	-10.74	-10.46	-9.38
55000.0	55200.0	-0.56	-0.48	-0.25	-12.42	-11.74	-10.13
56000.0	56200.0	-0.81	-0.74	-0.68	-12.97	-12.68	-11.58
57000.0	57200.0	-1.07	-0.89	-0.83	-13.56	-13.46	-12.67
58000.0	58200.0	-0.91	-0.83	-0.74	-11.91	-11.80	-10.75
59000.0	59200.0	-1.10	-1.00	-0.91	-10.11	-10.39	-9.82
60000.0	60200.0	-1.72	-1.46	-1.32	-7.57	-8.29	-8.12
61000.0	61200.0	-2.16	-1.42	-1.21	-4.94	-6.02	-5.96
62000.0	62200.0	-2.24	-1.52	-1.16	-3.83	-4.68	-4.23
63000.0	63200.0	-3.45	-2.25	-1.38	-1.92	-3.70	-3.41
64000.0	64200.0	-4.85	-4.02	-3.41	2.56	-0.01	-1.60

Frequency Mixer

SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	GAIN COMPRESSION (I)			GAIN COMPRESSION (Q)			GAIN COMPRESSION (I)			GAIN COMPRESSION (Q)			GAIN COMPRESSION (I)			GAIN COMPRESSION (Q)											
	IF = 200MHz									IF = 2000MHz									IF = 3000MHz								
	@LO (dBm)			@LO (dBm)			@LO (dBm)			@LO (dBm)			@LO (dBm)			@LO (dBm)			@LO (dBm)								
	+17	+18	+19	+17	+18	+19	+17	+18	+19	+17	+18	+19	+17	+18	+19	+17	+18	+19	+17	+18	+19						
18000.0	0.75	0.70	0.59	0.79	0.68	0.57	0.22	0.27	0.27	0.27	0.29	0.28	0.25	0.31	0.32	0.36	0.36	0.34									
19000.0	0.36	0.36	0.35	0.44	0.39	0.34	0.44	0.45	0.44	0.42	0.38	0.36	0.44	0.44	0.42	0.48	0.46	0.43									
20000.0	0.21	0.25	0.27	0.19	0.23	0.24	0.49	0.49	0.47	0.47	0.45	0.43	0.52	0.50	0.46	0.49	0.47	0.44									
21000.0	0.29	0.31	0.32	0.26	0.29	0.30	0.50	0.49	0.45	0.43	0.42	0.39	0.58	0.56	0.51	0.47	0.44	0.40									
22000.0	0.24	0.28	0.27	0.27	0.28	0.27	0.53	0.53	0.49	0.46	0.42	0.38	0.61	0.61	0.59	0.53	0.49	0.44									
23000.0	0.27	0.30	0.30	0.31	0.30	0.28	0.49	0.49	0.46	0.43	0.42	0.38	0.44	0.45	0.46	0.45	0.45	0.44									
24000.0	0.23	0.26	0.26	0.27	0.26	0.24	0.33	0.34	0.34	0.33	0.33	0.32	0.34	0.31	0.29	0.30	0.29	0.29									
25000.0	0.16	0.18	0.19	0.20	0.20	0.19	0.23	0.21	0.21	0.25	0.25	0.26	0.31	0.27	0.23	0.27	0.24	0.22									
26000.0	0.18	0.19	0.18	0.21	0.20	0.19	0.27	0.24	0.22	0.25	0.21	0.19	0.32	0.31	0.28	0.30	0.27	0.24									
27000.0	0.16	0.16	0.15	0.15	0.14	0.15	0.24	0.25	0.23	0.27	0.24	0.22	0.27	0.28	0.28	0.28	0.27	0.25									
28000.0	0.17	0.17	0.16	0.22	0.19	0.17	0.25	0.25	0.25	0.32	0.29	0.27	0.29	0.28	0.27	0.32	0.29	0.26									
29000.0	0.17	0.18	0.17	0.23	0.21	0.18	0.27	0.26	0.25	0.31	0.29	0.26	0.29	0.30	0.27	0.32	0.32	0.30									
30000.0	0.17	0.16	0.16	0.24	0.22	0.19	0.27	0.28	0.26	0.32	0.33	0.31	0.26	0.25	0.23	0.29	0.30	0.29									
31000.0	0.20	0.22	0.20	0.28	0.27	0.24	0.25	0.23	0.22	0.30	0.31	0.30	0.25	0.25	0.24	0.30	0.29	0.29									
32000.0	0.25	0.27	0.26	0.28	0.30	0.32	0.28	0.26	0.25	0.35	0.33	0.32	0.24	0.24	0.23	0.35	0.33	0.32									
33000.0	0.35	0.34	0.33	0.42	0.42	0.41	0.31	0.30	0.31	0.42	0.41	0.40	0.32	0.31	0.31	0.29	0.31	0.31									
34000.0	0.26	0.27	0.27	0.34	0.34	0.34	0.34	0.32	0.30	0.29	0.31	0.31	0.35	0.36	0.33	0.39	0.38	0.39									
35000.0	0.37	0.35	0.34	0.28	0.32	0.34	0.42	0.43	0.38	0.45	0.44	0.45	0.44	0.46	0.42	0.54	0.45	0.45									
36000.0	0.36	0.34	0.28	0.33	0.36	0.36	0.40	0.42	0.38	0.48	0.39	0.40	0.42	0.42	0.36	0.47	0.44	0.45									
37000.0	0.30	0.33	0.28	0.28	0.28	0.32	0.37	0.37	0.31	0.40	0.38	0.40	0.41	0.42	0.40	0.56	0.40	0.39									
38000.0	0.26	0.30	0.27	0.34	0.32	0.35	0.36	0.39	0.39	0.58	0.40	0.38	0.45	0.45	0.41	0.58	0.45	0.44									
39000.0	0.27	0.31	0.27	0.29	0.29	0.32	0.37	0.40	0.37	0.50	0.40	0.39	0.45	0.46	0.47	0.59	0.46	0.45									
40000.0	0.24	0.29	0.33	0.43	0.32	0.32	0.43	0.45	0.46	0.55	0.45	0.43	0.44	0.46	0.51	0.44	0.39	0.42									
41000.0	0.21	0.23	0.25	0.27	0.22	0.25	0.29	0.31	0.36	0.32	0.28	0.32	0.32	0.30	0.34	0.45	0.34	0.33									
42000.0	0.13	0.15	0.19	0.21	0.16	0.22	0.26	0.25	0.29	0.43	0.30	0.30	0.33	0.30	0.31	0.41	0.29	0.33									
43000.0	0.52	0.52	0.54	0.54	0.53	0.53	0.55	0.53	0.55	0.58	0.54	0.55	0.56	0.53	0.55	0.57	0.54	0.55									
44000.0	0.38	0.37	0.38	0.35	0.34	0.34	0.39	0.37	0.38	0.40	0.38	0.39	0.45	0.39	0.38	0.43	0.39	0.38									
45000.0	0.49	0.48	0.48	0.53	0.51	0.50	0.60	0.52	0.49	0.60	0.54	0.50	0.59	0.53	0.53	0.55	0.51	0.52									
46000.0	0.43	0.41	0.42	0.44	0.42	0.42	0.46	0.43	0.43	0.44	0.43	0.45	0.59	0.49	0.46	0.51	0.47	0.44									
47000.0	0.63	0.55	0.52	0.62	0.57	0.55	0.81	0.67	0.61	0.74	0.63	0.61	0.58	0.81	0.68	0.88	0.70	0.62									
48000.0	0.45	0.40	0.41	0.43	0.42	0.44	0.52	0.54	0.46	0.70	0.52	0.45	0.38	0.35	0.36	0.41	0.39	0.40									
49000.0	0.69	0.59	0.51	0.69	0.56	0.54	0.53	0.47	0.46	0.55	0.52	0.53	0.47	0.48	0.51	0.47	0.50	0.53									
50000.0	0.50	0.58	0.48	0.70	0.51	0.45	0.44	0.44	0.47	0.44	0.46	0.50	0.48	0.43	0.43	0.47	0.43	0.44									
51000.0	0.61	0.56	0.56	0.51	0.51	0.53	0.59	0.54	0.52	0.59	0.55	0.54	0.52	0.49	0.50	0.50	0.49	0.53									
52000.0	0.51	0.48	0.47	0.46	0.45	0.47	0.47	0.44	0.45	0.45	0.45	0.47	0.41	0.41	0.43	0.44	0.46	0.47									
53000.0	0.77	0.64	0.59	0.62	0.58	0.59	0.49	0.49	0.51	0.51	0.55	0.55	0.44	0.42	0.43	0.46	0.47	0.49									
54000.0	0.47	0.43	0.44	0.44	0.45	0.48	0.40	0.38	0.38	0.32	0.34	0.36	0.57	0.45	0.42	0.36	0.36	0.38									
55000.0	0.45	0.47	0.49	0.46	0.49	0.50	0.67	0.53	0.52	0.44	0.44	0.45	0.52	0.54	0.56	0.55	0.56	0.54									
56000.0	0.64	0.60	0.60	0.53	0.55	0.57	0.66	0.69	0.70	0.60	0.63	0.58	0.88	0.75	0.72	0.68	0.64	0.64									
57000.0	0.58	0.50	0.47	0.44	0.44	0.46	0.62	0.53	0.51	0.52	0.51	0.51	0.92	0.71	0.63	0.64	0.57	0.55									
58000.0	0.49	0.51	0.53	0.51	0.53	0.51	0.94	0.76	0.63	0.65	0.57	0.55	0.62	0.59	0.61	0.58	0.62	0.64									
59000.0	0.98	0.81	0.75	0.74	0.70	0.69	0.79	0.76	0.76	0.78	0.79	0.81	1.04	0.87	0.80	0.84	0.79	0.80									
60000.0	0.87	0.72	0.67	0.71	0.66	0.64	1.10	0.84	0.76	0.86	0.75	0.74	1.08	1.39	1.41	1.34	1.13	1.01									
61000.0	0.79	0.76	0.77	0.81	0.81	0.82	1.25	1.32	1.24	1.20	1.00	0.97	1.19	1.14	1.03	1.01	0.89	0.86									
62000.0	1.00	0.85	0.80	0.93	0.84	0.83	1.25	1.14	1.00	1.06	0.90	0.84	1.07	0.99	0.91	0.81	0.84	0.88									
63000.0	0.86	0.93	0.96	1.10	0.93	0.84	0.85	0.80	0.76	0.76	0.77	0.79	0.46	0.73	0.84	0.75	0.76	0.79									
64000.0	0.69	0.61	0.56	0.61	0.57	0.57	0.23	0.50	0.65	0.60	0.62	0.64	0.70	0.34	0.13	0.61	0.57	0.57									
65000.0	0.56	0.53	0.51	0.49	0.52	0.55	0.54	0.21	0.05	0.56	0.52	0.51															



Frequency Mixer SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	IM3_L(I)			IM3_L(Q)			IM3_H(I)			IM3_H(Q)		
	IF = 200MHz											
	@LO (dBm)			@LO (dBm)			@LO (dBm)			@LO (dBm)		
	+17	+18	+19	+17	+18	+19	+17	+18	+19	+17	+18	+19
20000.0	-73.43	-70.43	-68.71	-62.57	-65.67	-67.07	-73.16	-70.02	-68.60	-62.71	-65.56	-67.11
21000.0	-71.09	-71.02	-70.50	-74.53	-74.86	-73.38	-71.00	-71.12	-70.41	-74.49	-74.31	-74.02
22000.0	-73.59	-73.67	-73.45	-74.75	-72.99	-73.18	-73.51	-73.37	-73.35	-74.43	-73.56	-73.48
23000.0	-70.32	-70.41	-70.98	-70.88	-70.78	-70.71	-70.58	-70.62	-70.76	-70.91	-70.95	-70.40
24000.0	-73.75	-73.95	-73.81	-71.77	-72.18	-71.74	-73.75	-74.20	-74.57	-72.38	-72.90	-72.05
25000.0	-76.03	-78.55	-79.36	-80.23	-79.53	-78.32	-75.36	-77.86	-77.48	-78.79	-78.58	-77.67
26000.0	-74.30	-76.02	-76.83	-78.07	-78.04	-78.72	-75.31	-76.18	-78.37	-78.01	-78.82	-80.65
27000.0	-75.68	-76.68	-76.43	-80.86	-80.35	-80.66	-75.02	-75.77	-75.98	-80.01	-80.13	-79.61
28000.0	-78.11	-78.82	-76.73	-78.77	-80.36	-79.04	-76.97	-78.41	-77.25	-77.78	-80.23	-79.94
29000.0	-77.46	-79.00	-80.33	-76.27	-78.10	-79.28	-76.67	-78.97	-80.07	-76.13	-77.65	-78.87
30000.0	-78.68	-81.40	-83.95	-76.14	-79.58	-82.65	-79.23	-81.40	-84.94	-75.81	-78.76	-84.08
31000.0	-75.53	-76.10	-79.09	-73.08	-74.75	-77.31	-76.65	-77.40	-80.40	-74.00	-75.11	-79.23
32000.0	-72.45	-72.28	-74.05	-72.50	-71.70	-72.11	-71.87	-72.05	-74.13	-72.73	-71.74	-72.03
33000.0	-70.62	-71.22	-71.07	-69.29	-70.06	-70.86	-70.61	-70.55	-70.73	-69.09	-70.06	-70.29
34000.0	-76.16	-75.36	-74.66	-74.52	-73.71	-73.16	-76.88	-75.50	-74.71	-74.66	-74.61	-73.15
35000.0	-69.36	-69.61	-69.39	-68.98	-68.49	-68.64	-69.13	-69.85	-69.52	-69.49	-68.93	-68.65
36000.0	-67.44	-67.91	-68.41	-71.23	-69.70	-68.54	-67.57	-67.92	-68.47	-70.97	-69.94	-69.18
37000.0	-68.45	-68.54	-69.13	-71.14	-70.78	-70.45	-68.37	-68.41	-69.12	-70.85	-70.87	-70.44
38000.0	-69.10	-68.95	-69.97	-69.59	-69.86	-69.30	-68.63	-68.88	-69.50	-69.55	-69.55	-68.85
39000.0	-67.30	-67.39	-68.55	-69.14	-69.47	-68.83	-67.68	-67.77	-68.64	-69.59	-69.74	-69.14
40000.0	-69.17	-68.33	-67.38	-67.62	-69.26	-69.45	-69.88	-68.36	-67.24	-67.66	-69.81	-69.25
41000.0	-69.97	-68.29	-67.66	-70.89	-70.70	-69.48	-70.04	-68.03	-68.16	-70.35	-71.18	-69.91
42000.0	-70.88	-70.45	-69.60	-72.17	-72.36	-71.52	-71.38	-70.41	-69.29	-72.03	-71.76	-72.63
43000.0	-71.26	-71.05	-70.94	-69.97	-70.58	-70.98	-72.51	-72.33	-70.93	-71.27	-71.46	-72.49
44000.0	-71.42	-72.80	-72.47	-72.19	-74.41	-76.03	-71.42	-73.15	-72.99	-72.68	-73.55	-76.53
45000.0	-72.67	-73.98	-74.71	-72.96	-73.75	-74.69	-73.17	-74.64	-73.88	-73.43	-73.25	-76.69
46000.0	-70.83	-72.07	-72.42	-71.99	-72.93	-73.28	-71.75	-73.02	-73.27	-72.47	-72.90	-74.77
47000.0	-67.08	-68.94	-69.34	-68.48	-69.56	-69.75	-67.05	-68.75	-69.33	-69.16	-70.37	-70.07
48000.0	-68.16	-68.80	-68.87	-68.75	-69.22	-69.44	-67.62	-67.81	-68.57	-68.21	-68.36	-68.69
49000.0	-63.51	-67.99	-68.86	-66.91	-67.66	-68.77	-62.92	-67.39	-68.69	-65.71	-66.95	-67.81
50000.0	-62.38	-68.27	-69.89	-69.21	-70.99	-71.66	-61.75	-66.59	-68.99	-66.75	-69.09	-70.48
51000.0	-68.70	-68.82	-68.76	-71.07	-70.77	-70.08	-67.22	-67.39	-67.51	-69.62	-69.04	-68.26
52000.0	-66.43	-67.52	-68.17	-68.46	-68.43	-68.99	-66.87	-67.98	-68.07	-68.25	-68.68	-68.73
53000.0	-67.00	-70.08	-70.90	-70.65	-70.13	-70.32	-66.27	-68.73	-69.55	-69.13	-69.84	-69.51
54000.0	-73.46	-73.68	-72.55	-73.21	-72.19	-70.60	-71.77	-74.16	-71.49	-72.67	-72.17	-71.25
55000.0	-69.14	-68.22	-67.49	-70.14	-69.65	-69.67	-68.01	-67.64	-67.25	-69.60	-68.72	-68.55
56000.0	-67.57	-66.88	-66.46	-67.54	-67.14	-66.85	-68.42	-67.31	-67.05	-68.13	-67.41	-66.87
57000.0	-70.58	-70.02	-69.48	-69.16	-68.67	-68.32	-70.02	-69.92	-69.78	-70.08	-69.12	-68.99
58000.0	-70.23	-69.32	-68.72	-68.10	-67.49	-68.62	-69.61	-69.55	-68.33	-67.99	-67.81	-69.22
59000.0	-63.27	-68.22	-69.24	-69.53	-70.62	-70.21	-62.95	-67.20	-69.19	-68.90	-69.53	-69.35
60000.0	-67.01	-69.59	-69.77	-68.16	-68.20	-68.40	-67.87	-69.85	-70.33	-67.88	-68.31	-68.48
61000.0	-71.92	-71.28	-70.45	-69.99	-69.29	-67.21	-72.14	-71.22	-69.70	-69.69	-69.08	-67.99
62000.0	-71.07	-72.64	-74.32	-71.59	-71.66	-71.83	-71.38	-73.60	-74.74	-71.60	-73.29	-73.04
63000.0	-62.63	-61.51	-60.86	-62.25	-64.94	-66.49	-62.89	-61.94	-61.21	-63.07	-65.99	-67.87
64000.0	-66.04	-68.14	-71.55	-72.37	-73.79	-74.15	-65.43	-69.24	-72.14	-71.48	-73.02	-73.21
65000.0	-66.00	-68.65	-69.36	-71.02	-69.81	-68.71	-65.79	-69.06	-69.67	-72.17	-70.18	-68.57



Frequency Mixer SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	IM3_L(I)			IM3_L(Q)			IM3_H(I)			IM3_H(Q)		
	IF = 2000MHz											
	@LO (dBm)			@LO (dBm)			@LO (dBm)			@LO (dBm)		
	+17	+18	+19	+17	+18	+19	+17	+18	+19	+17	+18	+19
20000.0	-65.33	-66.07	-66.37	-68.85	-69.08	-69.26	-65.19	-65.70	-66.23	-68.57	-69.29	-68.81
21000.0	-66.98	-67.86	-69.12	-70.87	-70.55	-71.37	-67.25	-68.04	-69.36	-71.03	-70.78	-70.64
22000.0	-65.97	-66.34	-67.40	-68.52	-68.83	-69.34	-65.69	-66.41	-67.11	-68.62	-68.59	-69.28
23000.0	-67.18	-67.97	-68.78	-68.13	-68.38	-69.29	-67.17	-68.13	-68.88	-67.96	-68.36	-69.08
24000.0	-70.85	-70.29	-70.32	-72.19	-71.57	-73.07	-70.61	-70.88	-70.49	-72.15	-72.33	-73.07
25000.0	-74.09	-74.78	-73.99	-75.46	-75.93	-73.45	-73.45	-74.64	-73.79	-75.68	-74.48	-73.17
26000.0	-72.30	-73.48	-72.31	-75.04	-77.06	-76.84	-73.25	-73.91	-73.35	-77.90	-79.22	-76.31
27000.0	-75.20	-75.92	-75.75	-76.58	-77.61	-79.77	-76.45	-75.96	-75.72	-74.56	-76.40	-77.77
28000.0	-76.22	-76.13	-76.63	-73.38	-73.97	-75.35	-76.28	-76.34	-76.84	-73.19	-75.02	-75.69
29000.0	-73.38	-74.90	-76.45	-73.69	-74.55	-76.26	-73.62	-73.62	-76.13	-72.36	-72.99	-75.91
30000.0	-73.92	-74.02	-76.55	-73.05	-72.10	-74.21	-75.07	-75.32	-77.22	-72.97	-72.20	-73.33
31000.0	-73.52	-75.89	-75.96	-72.35	-72.23	-71.51	-74.83	-75.05	-77.14	-72.89	-72.26	-71.94
32000.0	-72.06	-72.77	-73.52	-68.86	-70.07	-69.97	-72.17	-73.15	-74.29	-69.17	-69.25	-69.91
33000.0	-77.84	-74.76	-74.75	-73.81	-73.16	-74.58	-77.84	-75.82	-75.00	-73.26	-73.30	-72.81
34000.0	-72.35	-73.21	-72.87	-75.97	-74.88	-74.36	-72.62	-73.41	-72.81	-78.12	-73.72	-73.98
35000.0	-69.34	-69.67	-69.49	-70.78	-71.02	-69.86	-69.73	-69.26	-69.55	-70.52	-70.78	-70.22
36000.0	-69.51	-69.78	-70.25	-70.69	-70.33	-70.20	-69.41	-69.63	-70.21	-70.55	-70.60	-70.22
37000.0	-69.68	-69.83	-70.09	-70.62	-70.22	-69.47	-69.66	-69.41	-69.87	-70.58	-69.99	-69.14
38000.0	-71.67	-70.59	-69.79	-68.86	-70.70	-70.48	-70.72	-70.21	-69.58	-68.92	-70.78	-70.69
39000.0	-70.06	-68.09	-68.03	-68.52	-69.53	-69.16	-70.32	-68.67	-67.58	-68.69	-69.86	-69.52
40000.0	-68.18	-67.49	-66.27	-68.60	-69.56	-69.37	-68.46	-68.08	-66.80	-68.94	-69.50	-68.95
41000.0	-69.71	-69.26	-68.55	-70.81	-71.24	-69.84	-69.34	-68.76	-68.62	-70.20	-71.41	-71.01
42000.0	-69.11	-69.47	-69.74	-68.05	-70.56	-69.94	-68.98	-69.32	-69.22	-68.46	-70.27	-70.06
43000.0	-69.03	-70.42	-70.36	-68.90	-71.06	-70.90	-70.05	-71.16	-71.60	-69.21	-72.26	-72.60
44000.0	-71.81	-74.34	-74.58	-70.39	-72.85	-72.52	-72.12	-73.03	-74.19	-70.59	-72.04	-72.34
45000.0	-69.94	-72.69	-73.00	-70.19	-72.47	-72.84	-70.10	-72.18	-73.65	-70.73	-73.30	-72.99
46000.0	-71.91	-73.18	-74.02	-72.95	-72.53	-72.52	-71.87	-74.39	-73.74	-72.45	-73.64	-72.67
47000.0	-65.45	-68.76	-69.57	-67.21	-69.14	-70.34	-65.38	-68.95	-69.85	-67.15	-68.91	-69.18
48000.0	-60.23	-67.84	-68.70	-64.53	-67.97	-69.07	-59.54	-66.99	-68.36	-63.43	-67.01	-68.35
49000.0	-66.51	-66.72	-66.80	-67.80	-67.71	-67.47	-66.38	-65.97	-66.51	-67.09	-67.21	-66.64
50000.0	-68.19	-68.21	-69.07	-69.21	-69.90	-69.49	-67.44	-67.72	-68.14	-68.66	-68.47	-68.37
51000.0	-69.76	-71.05	-71.98	-69.94	-71.79	-71.72	-68.70	-69.43	-69.59	-68.59	-70.06	-69.71
52000.0	-71.55	-70.88	-70.82	-71.91	-71.50	-70.83	-70.94	-69.91	-70.06	-71.00	-70.94	-69.82
53000.0	-74.46	-74.22	-72.54	-74.58	-72.32	-71.65	-72.98	-71.86	-71.20	-73.11	-70.77	-70.44
54000.0	-69.03	-68.29	-68.12	-71.72	-71.34	-70.62	-69.31	-68.73	-68.11	-72.05	-71.66	-70.97
55000.0	-67.93	-67.82	-66.84	-69.50	-68.82	-68.82	-67.12	-66.47	-66.47	-69.40	-68.32	-67.66
56000.0	-66.87	-66.13	-65.30	-67.67	-67.16	-68.12	-67.24	-66.35	-65.74	-67.49	-67.77	-69.12
57000.0	-69.17	-70.86	-70.31	-70.61	-70.77	-71.15	-68.83	-70.58	-70.00	-70.36	-70.84	-70.36
58000.0	-63.87	-68.48	-70.46	-69.79	-70.46	-70.54	-63.53	-68.16	-69.70	-68.48	-69.67	-70.28
59000.0	-70.37	-69.54	-68.79	-68.62	-67.36	-66.68	-69.39	-69.57	-68.81	-67.72	-66.70	-66.09
60000.0	-67.41	-68.46	-68.76	-66.45	-67.04	-66.55	-67.05	-69.11	-69.57	-67.11	-66.99	-66.83
61000.0	-54.71	-55.77	-56.95	-61.95	-64.56	-65.41	-54.46	-55.66	-57.00	-62.02	-64.35	-65.44
62000.0	-61.33	-62.59	-66.96	-66.97	-70.40	-70.72	-61.14	-62.55	-66.89	-67.07	-69.09	-70.56
63000.0	-64.10	-67.23	-68.60	-68.23	-68.01	-67.68	-64.87	-68.50	-70.67	-70.81	-70.11	-69.36
64000.0	-62.20	-71.70	-67.98	-71.51	-70.11	-70.01	-62.46	-73.25	-67.90	-71.37	-71.66	-69.95
65000.0	-66.50	-65.01	-60.72	-69.13	-69.65	-69.81	-66.07	-67.09	-60.79	-69.06	-69.82	-69.81



Frequency Mixer SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	IM3_L(I)			IM3_L(Q)			IM3_H(I)			IM3_H(Q)		
	IF = 3000MHz											
	@LO (dBm)			@LO (dBm)			@LO (dBm)			@LO (dBm)		
	+17	+18	+19	+17	+18	+19	+17	+18	+19	+17	+18	+19
20000.0	-64.65	-65.64	-67.70	-68.74	-68.89	-69.77	-64.79	-66.36	-67.35	-68.33	-68.50	-69.32
21000.0	-65.53	-66.31	-67.50	-69.37	-69.73	-69.89	-65.45	-66.29	-67.27	-69.07	-69.43	-70.27
22000.0	-64.86	-65.40	-65.78	-67.07	-67.13	-67.84	-64.81	-65.66	-66.21	-66.82	-67.50	-68.21
23000.0	-67.22	-66.91	-66.83	-68.24	-68.23	-68.51	-67.02	-67.25	-66.55	-68.33	-68.11	-68.90
24000.0	-71.01	-71.92	-71.98	-73.79	-73.53	-71.71	-71.40	-73.13	-72.67	-75.11	-73.83	-71.48
25000.0	-71.99	-72.98	-73.13	-77.61	-78.20	-79.68	-71.13	-73.16	-73.43	-76.55	-77.96	-78.29
26000.0	-73.14	-73.16	-73.10	-74.23	-75.11	-75.97	-73.40	-73.81	-73.51	-74.92	-75.04	-77.68
27000.0	-75.39	-74.60	-76.03	-74.72	-75.09	-74.81	-75.34	-73.49	-74.74	-74.17	-75.13	-74.87
28000.0	-74.25	-74.61	-75.70	-72.76	-74.01	-76.76	-73.26	-73.96	-74.48	-72.81	-75.06	-76.81
29000.0	-74.10	-74.43	-75.63	-73.59	-72.16	-73.59	-73.84	-73.07	-75.66	-72.46	-72.44	-73.25
30000.0	-73.48	-74.58	-75.03	-72.30	-71.75	-72.97	-73.21	-75.14	-75.48	-73.23	-72.43	-73.14
31000.0	-74.43	-75.26	-74.10	-71.05	-71.21	-71.85	-73.89	-75.49	-74.20	-71.52	-71.31	-71.62
32000.0	-77.96	-75.54	-74.09	-71.42	-71.18	-70.71	-75.02	-74.88	-75.26	-72.24	-70.47	-71.24
33000.0	-78.50	-77.75	-74.51	-84.54	-85.67	-78.49	-77.80	-77.13	-75.92	-85.60	-81.24	-78.50
34000.0	-74.48	-73.66	-72.52	-73.17	-74.18	-72.80	-76.88	-73.45	-71.81	-73.86	-73.73	-72.44
35000.0	-70.26	-69.47	-70.19	-70.66	-70.96	-70.48	-70.65	-70.31	-69.98	-70.37	-71.23	-70.32
36000.0	-69.10	-69.71	-69.64	-70.02	-69.92	-69.17	-69.22	-69.75	-70.18	-70.30	-70.22	-69.28
37000.0	-71.63	-70.14	-69.64	-69.57	-70.89	-71.29	-71.51	-69.94	-69.17	-69.81	-71.29	-70.91
38000.0	-70.69	-68.68	-68.76	-69.84	-69.58	-68.74	-69.83	-68.28	-67.67	-68.59	-69.96	-69.27
39000.0	-68.00	-67.03	-66.08	-67.03	-68.12	-67.68	-67.84	-66.98	-66.17	-66.85	-68.29	-67.85
40000.0	-67.96	-67.33	-66.47	-69.29	-69.35	-69.17	-68.09	-67.47	-66.82	-69.18	-69.57	-69.35
41000.0	-68.74	-70.40	-69.02	-69.47	-71.07	-70.64	-68.81	-69.52	-69.09	-69.72	-70.23	-71.09
42000.0	-68.16	-68.68	-68.95	-67.32	-69.42	-68.98	-67.92	-68.98	-68.70	-67.45	-68.72	-69.36
43000.0	-69.26	-69.63	-70.21	-69.40	-69.99	-69.79	-69.87	-71.09	-71.01	-69.48	-70.73	-71.31
44000.0	-69.18	-72.21	-72.74	-70.01	-71.30	-71.67	-69.85	-71.76	-72.32	-69.89	-70.97	-72.01
45000.0	-72.71	-73.36	-74.42	-73.83	-73.18	-71.62	-72.28	-74.47	-74.21	-72.89	-73.36	-73.00
46000.0	-65.99	-68.67	-70.77	-69.79	-72.21	-72.01	-65.95	-70.43	-70.80	-68.92	-72.72	-72.87
47000.0	-59.90	-66.84	-67.71	-65.71	-68.24	-69.40	-59.01	-65.97	-67.88	-65.19	-68.07	-68.75
48000.0	-69.02	-68.66	-68.96	-68.83	-68.71	-68.75	-68.24	-68.73	-68.46	-68.43	-68.08	-68.16
49000.0	-66.58	-66.95	-67.42	-67.63	-68.05	-68.43	-66.25	-66.71	-66.42	-67.92	-67.86	-67.45
50000.0	-70.57	-71.56	-70.72	-69.73	-70.43	-70.01	-69.85	-70.25	-70.02	-69.12	-69.69	-70.08
51000.0	-71.70	-71.92	-70.89	-72.87	-73.12	-72.36	-70.19	-69.53	-68.94	-71.11	-70.80	-69.52
52000.0	-73.13	-71.56	-72.46	-71.81	-71.36	-70.63	-74.08	-72.30	-70.99	-72.50	-71.36	-70.19
53000.0	-76.70	-74.52	-73.55	-85.86	-77.71	-76.74	-75.14	-73.13	-71.81	-79.72	-77.03	-74.94
54000.0	-69.32	-68.14	-66.88	-72.12	-71.44	-69.97	-68.95	-67.93	-67.33	-72.47	-72.19	-71.23
55000.0	-66.68	-65.96	-65.52	-68.52	-68.04	-69.43	-66.13	-65.63	-65.02	-67.48	-67.45	-68.44
56000.0	-65.21	-67.03	-67.52	-68.07	-68.27	-68.26	-65.59	-67.70	-67.91	-68.19	-69.57	-68.75
57000.0	-62.68	-68.16	-69.20	-68.67	-68.59	-69.50	-62.14	-66.78	-69.30	-67.50	-68.94	-69.91
58000.0	-69.99	-69.39	-69.36	-69.49	-68.10	-67.37	-70.04	-69.73	-68.90	-69.24	-68.06	-67.56
59000.0	-66.36	-68.14	-68.22	-68.43	-68.05	-67.46	-65.50	-67.47	-67.94	-68.00	-67.60	-67.13
60000.0	-53.21	-54.58	-56.03	-60.28	-63.22	-64.53	-53.47	-54.76	-56.02	-60.82	-62.67	-64.76
61000.0	-58.07	-59.95	-63.73	-65.88	-67.92	-67.75	-57.83	-60.18	-63.79	-65.51	-67.93	-67.89
62000.0	-62.58	-66.07	-69.12	-70.16	-69.30	-68.32	-62.86	-66.57	-69.43	-71.07	-70.03	-68.80
63000.0	-61.19	-68.22	-65.89	-68.51	-67.76	-67.32	-61.31	-70.14	-66.10	-70.82	-70.25	-68.18
64000.0	-64.53	-65.67	-60.97	-70.88	-71.53	-70.48	-66.38	-66.60	-61.90	-71.37	-71.56	-71.46



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
SMIQ-653H-D+
9/14/2022
Page 13 of 16

Frequency Mixer

SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	Inp_IP3_L(I)			Inp_IP3_L(Q)			Inp_IP3_H(I)			Inp_IP3_H(Q)		
	IF = 200MHz											
	@LO (dBm)			@LO (dBm)			@LO (dBm)			@LO (dBm)		
	+17	+18	+19	+17	+18	+19	+17	+18	+19	+17	+18	+19
20000.0	26.72	25.21	24.35	21.28	22.83	23.53	26.58	25.01	24.30	21.35	22.78	23.55
21000.0	25.55	25.51	25.25	27.27	27.43	26.69	25.50	25.56	25.21	27.25	27.15	27.01
22000.0	26.80	26.83	26.73	27.38	26.50	26.59	26.75	26.68	26.68	27.21	26.78	26.74
23000.0	25.16	25.21	25.49	25.44	25.39	25.35	25.29	25.31	25.38	25.46	25.48	25.20
24000.0	26.88	26.98	26.91	25.88	26.09	25.87	26.88	27.10	27.29	26.19	26.45	26.03
25000.0	28.01	29.28	29.68	30.11	29.77	29.16	27.68	28.93	28.74	29.39	29.29	28.83
26000.0	27.15	28.01	28.41	29.04	29.02	29.36	27.65	28.09	29.19	29.00	29.41	30.33
27000.0	27.84	28.34	28.22	30.43	30.18	30.33	27.51	27.89	27.99	30.00	30.07	29.81
28000.0	29.05	29.41	28.37	29.38	30.18	29.52	28.49	29.20	28.62	28.89	30.12	29.97
29000.0	28.73	29.50	30.16	28.13	29.05	29.64	28.33	29.48	30.04	28.06	28.83	29.44
30000.0	29.34	30.70	31.97	28.07	29.79	31.32	29.62	30.70	32.47	27.91	29.38	32.04
31000.0	27.77	28.05	29.55	26.54	27.37	28.65	28.33	28.70	30.20	27.00	27.55	29.62
32000.0	26.22	26.14	27.02	26.25	25.85	26.06	25.93	26.02	27.06	26.37	25.87	26.02
33000.0	25.31	25.61	25.53	24.65	25.03	25.43	25.30	25.27	25.36	24.55	25.03	25.15
34000.0	28.08	27.68	27.33	27.26	26.86	26.58	28.44	27.75	27.35	27.33	27.31	26.58
35000.0	24.68	24.80	24.70	24.49	24.24	24.32	24.56	24.92	24.76	24.75	24.46	24.32
36000.0	23.72	23.95	24.20	25.61	24.85	24.27	23.78	23.96	24.24	25.48	24.97	24.59
37000.0	24.23	24.27	24.57	25.57	25.39	25.22	24.18	24.20	24.56	25.42	25.44	25.22
38000.0	24.55	24.48	24.98	24.79	24.93	24.65	24.32	24.44	24.75	24.77	24.77	24.42
39000.0	23.65	23.69	24.28	24.57	24.74	24.42	23.84	23.89	24.32	24.79	24.87	24.57
40000.0	24.59	24.16	23.69	23.81	24.63	24.73	24.94	24.18	23.62	23.83	24.90	24.62
41000.0	24.99	24.15	23.83	25.45	25.35	24.74	25.02	24.02	24.08	25.18	25.59	24.95
42000.0	25.44	25.23	24.80	26.09	26.18	25.76	25.69	25.21	24.65	26.01	25.88	26.31
43000.0	25.63	25.53	25.47	24.99	25.29	25.49	26.25	26.16	25.47	25.64	25.73	26.25
44000.0	25.71	26.40	26.23	26.09	27.20	28.02	25.71	26.57	26.49	26.34	26.78	28.26
45000.0	26.34	26.99	27.35	26.48	26.88	27.35	26.59	27.32	26.94	26.72	26.63	28.34
46000.0	25.42	26.04	26.21	26.00	26.47	26.64	25.88	26.51	26.63	26.23	26.45	27.39
47000.0	23.54	24.47	24.67	24.24	24.78	24.87	23.52	24.37	24.67	24.58	25.19	25.03
48000.0	24.08	24.40	24.43	24.37	24.61	24.72	23.81	23.91	24.29	24.11	24.18	24.35
49000.0	21.75	24.00	24.43	23.46	23.83	24.39	21.46	23.69	24.35	22.86	23.47	23.91
50000.0	21.19	24.13	24.94	24.61	25.50	25.83	20.88	23.30	24.49	23.37	24.54	25.24
51000.0	24.35	24.41	24.38	25.53	25.39	25.04	23.61	23.69	23.75	24.81	24.52	24.13
52000.0	23.22	23.76	24.09	24.23	24.21	24.50	23.43	23.99	24.03	24.12	24.34	24.37
53000.0	23.50	25.04	25.45	25.33	25.07	25.16	23.13	24.37	24.77	24.56	24.92	24.75
54000.0	26.73	26.84	26.28	26.61	26.09	25.30	25.88	27.08	25.75	26.33	26.08	25.63
55000.0	24.57	24.11	23.74	25.07	24.82	24.84	24.00	23.82	23.62	24.80	24.36	24.27
56000.0	23.79	23.44	23.23	23.77	23.57	23.42	24.21	23.66	23.52	24.06	23.70	23.43
57000.0	25.29	25.01	24.74	24.58	24.34	24.16	25.01	24.96	24.89	25.04	24.56	24.50
58000.0	25.11	24.66	24.36	24.05	23.74	24.31	24.81	24.77	24.16	24.00	23.90	24.61
59000.0	21.64	24.11	24.62	24.76	25.31	25.10	21.48	23.60	24.59	24.45	24.77	24.68
60000.0	23.51	24.79	24.89	24.08	24.10	24.20	23.93	24.92	25.17	23.94	24.15	24.24
61000.0	25.96	25.64	25.22	24.99	24.65	23.61	26.07	25.61	24.85	24.85	24.54	24.00
62000.0	25.54	26.32	27.16	25.80	25.83	25.92	25.57	26.80	27.37	25.80	26.64	26.52
63000.0	21.31	20.76	20.43	21.13	22.47	23.24	21.45	20.97	20.60	21.54	22.99	23.93
64000.0	23.02	24.07	25.77	26.18	26.90	27.07	22.71	24.62	26.07	25.74	26.51	26.60
65000.0	23.00	24.33	24.68	25.51	24.90	24.35	22.89	24.53	24.83	26.08	25.09	24.29



Frequency Mixer

SMIQ-653H-D+

Typical Performance Data

RF (IN) (MHz)	Inp_IP3_L(I)			Inp_IP3_L(Q)			Inp_IP3_H(I)			Inp_IP3_H(Q)		
	IF = 2000MHz											
	@LO (dBm)			@LO (dBm)			@LO (dBm)			@LO (dBm)		
	+17	+18	+19	+17	+18	+19	+17	+18	+19	+17	+18	+19
20000.0	22.67	23.03	23.19	24.43	24.54	24.63	22.59	22.85	23.12	24.28	24.64	24.41
21000.0	23.49	23.93	24.56	25.43	25.27	25.68	23.63	24.02	24.68	25.51	25.39	25.32
22000.0	22.99	23.17	23.70	24.26	24.41	24.67	22.85	23.21	23.55	24.31	24.30	24.64
23000.0	23.59	23.98	24.39	24.07	24.19	24.64	23.59	24.07	24.44	23.98	24.18	24.54
24000.0	25.43	25.15	25.16	26.10	25.78	26.54	25.30	25.44	25.24	26.07	26.16	26.53
25000.0	27.05	27.39	26.99	27.73	27.97	26.72	26.72	27.32	26.89	27.84	27.24	26.59
26000.0	26.15	26.74	26.16	27.52	28.53	28.42	26.62	26.95	26.67	28.95	29.61	28.15
27000.0	27.60	27.96	27.88	28.29	28.80	29.88	28.23	27.98	27.86	27.28	28.20	28.89
28000.0	28.11	28.07	28.32	26.69	26.98	27.68	28.14	28.17	28.42	26.59	27.51	27.85
29000.0	26.69	27.45	28.22	26.85	27.28	28.13	26.81	26.81	28.06	26.18	26.49	27.95
30000.0	26.96	27.01	28.27	26.52	26.05	27.11	27.54	27.66	28.61	26.49	26.10	26.66
31000.0	26.76	27.95	27.98	26.17	26.12	25.76	27.42	27.53	28.57	26.45	26.13	25.97
32000.0	26.03	26.39	26.76	24.43	25.03	24.98	26.08	26.58	27.14	24.59	24.62	24.96
33000.0	28.92	27.38	27.38	26.91	26.58	27.29	28.92	27.91	27.50	26.63	26.65	26.40
34000.0	26.18	26.61	26.43	27.98	27.44	27.18	26.31	26.71	26.41	29.06	26.86	26.99
35000.0	24.67	24.83	24.74	25.39	25.51	24.93	24.86	24.63	24.78	25.26	25.39	25.11
36000.0	24.76	24.89	25.13	25.35	25.17	25.10	24.70	24.81	25.10	25.28	25.30	25.11
37000.0	24.84	24.92	25.05	25.31	25.11	24.74	24.83	24.70	24.94	25.29	25.00	24.57
38000.0	25.84	25.30	24.90	24.43	25.35	25.24	25.36	25.11	24.79	24.46	25.39	25.35
39000.0	25.03	24.05	24.02	24.26	24.76	24.58	25.16	24.33	23.79	24.34	24.93	24.76
40000.0	24.09	23.74	23.13	24.30	24.78	24.68	24.23	24.04	23.40	24.47	24.75	24.47
41000.0	24.86	24.63	24.27	25.41	25.62	24.92	24.67	24.38	24.31	25.10	25.71	25.50
42000.0	24.56	24.74	24.87	24.03	25.28	24.97	24.49	24.66	24.61	24.23	25.14	25.03
43000.0	24.52	25.21	25.18	24.45	25.53	25.45	25.03	25.58	25.80	24.61	26.13	26.30
44000.0	25.91	27.17	27.29	25.19	26.43	26.26	26.06	26.52	27.09	25.30	26.02	26.17
45000.0	24.97	26.35	26.50	25.09	26.23	26.42	25.05	26.09	26.83	25.36	26.65	26.50
46000.0	25.95	26.59	27.01	26.47	26.26	26.26	25.94	27.20	26.87	26.22	26.82	26.34
47000.0	22.72	24.38	24.79	23.61	24.57	25.17	22.69	24.47	24.92	23.58	24.46	24.59
48000.0	20.12	23.92	24.35	22.27	23.98	24.53	19.77	23.50	24.18	21.72	23.50	24.18
49000.0	23.26	23.36	23.40	23.90	23.86	23.73	23.19	22.99	23.25	23.55	23.61	23.32
50000.0	24.10	24.11	24.53	24.60	24.95	24.75	23.72	23.86	24.07	24.33	24.23	24.18
51000.0	24.88	25.53	25.99	24.97	25.90	25.86	24.35	24.72	24.80	24.30	25.03	24.86
52000.0	25.78	25.44	25.41	25.96	25.75	25.42	25.47	24.95	25.03	25.50	25.47	24.91
53000.0	27.23	27.11	26.27	27.29	26.16	25.82	26.49	25.93	25.60	26.55	25.39	25.22
54000.0	24.52	24.15	24.06	25.86	25.67	25.31	24.65	24.37	24.05	26.02	25.83	25.49
55000.0	23.96	23.91	23.42	24.75	24.41	24.41	23.56	23.24	23.23	24.70	24.16	23.83
56000.0	23.43	23.07	22.65	23.84	23.58	24.06	23.62	23.18	22.87	23.74	23.88	24.56
57000.0	24.59	25.43	25.15	25.31	25.39	25.58	24.42	25.29	25.00	25.18	25.42	25.18
58000.0	21.93	24.24	25.23	24.89	25.23	25.27	21.76	24.08	24.85	24.24	24.84	25.14
59000.0	25.18	24.77	24.39	24.31	23.68	23.34	24.69	24.79	24.41	23.86	23.35	23.04
60000.0	23.71	24.23	24.38	23.22	23.52	23.27	23.53	24.55	24.78	23.56	23.49	23.42
61000.0	17.35	17.88	18.48	20.97	22.28	22.70	17.23	17.83	18.50	21.01	22.17	22.72
62000.0	20.66	21.30	23.48	23.49	25.20	25.36	20.57	21.27	23.45	23.54	24.55	25.28
63000.0	22.05	23.62	24.30	24.12	24.01	23.84	22.43	24.25	25.34	25.41	25.05	24.68
64000.0	21.10	25.85	23.99	25.76	25.06	25.01	21.23	26.62	23.95	25.69	25.83	24.98
65000.0	23.25	22.50	20.36	24.56	24.82	24.91	23.03	23.54	20.39	24.53	24.91	24.90



Frequency Mixer

SMIQ-653H-D+

Typical Performance Data







RF (IN) (MHz)	Inp_IP3_L(I)			Inp_IP3_L(Q)			Inp_IP3_H(I)			Inp_IP3_H(Q)		
	IF = 3000MHz											
	@LO (dBm)			@LO (dBm)			@LO (dBm)			@LO (dBm)		
	+17	+18	+19	+17	+18	+19	+17	+18	+19	+17	+18	+19
20000.0	22.33	22.82	23.85	24.37	24.45	24.89	22.39	23.18	23.68	24.17	24.25	24.66
21000.0	22.76	23.15	23.75	24.69	24.87	24.95	22.72	23.14	23.63	24.54	24.72	25.14
22000.0	22.43	22.70	22.89	23.53	23.57	23.92	22.41	22.83	23.10	23.41	23.75	24.10
23000.0	23.61	23.46	23.41	24.12	24.12	24.26	23.51	23.63	23.28	24.16	24.06	24.45
24000.0	25.50	25.96	25.99	26.90	26.77	25.86	25.70	26.57	26.34	27.56	26.92	25.74
25000.0	26.00	26.49	26.57	28.81	29.10	29.84	25.57	26.58	26.71	28.28	28.98	29.14
26000.0	26.57	26.58	26.55	27.12	27.55	27.99	26.70	26.90	26.75	27.46	27.52	28.84
27000.0	27.69	27.30	28.01	27.36	27.55	27.40	27.67	26.74	27.37	27.08	27.56	27.43
28000.0	27.12	27.30	27.85	26.38	27.00	28.38	26.63	26.98	27.24	26.41	27.53	28.41
29000.0	27.05	27.21	27.82	26.79	26.08	26.79	26.92	26.54	27.83	26.23	26.22	26.62
30000.0	26.74	27.29	27.51	26.15	25.87	26.48	26.61	27.57	27.74	26.62	26.21	26.57
31000.0	27.22	27.63	27.05	25.53	25.60	25.92	26.94	27.75	27.10	25.76	25.65	25.81
32000.0	28.98	27.77	27.05	25.71	25.59	25.36	27.51	27.44	27.63	26.12	25.24	25.62
33000.0	29.25	28.87	27.26	32.27	32.84	29.24	28.90	28.57	27.96	32.80	30.62	29.25
34000.0	27.24	26.83	26.26	26.58	27.09	26.40	28.44	26.73	25.90	26.93	26.87	26.22
35000.0	25.63	25.16	24.81	25.10	26.26	25.18	25.40	25.13	24.79	25.40	26.02	25.73
36000.0	25.06	24.73	24.94	24.43	24.93	24.39	25.33	24.93	24.96	24.38	25.09	24.24
37000.0	25.73	25.31	24.76	23.57	25.82	25.69	25.20	24.71	24.60	23.23	25.53	25.16
38000.0	25.87	24.67	25.42	24.91	25.62	24.38	25.75	24.68	25.22	25.00	25.32	24.47
39000.0	24.20	24.24	23.61	23.25	24.51	24.41	24.11	24.02	23.76	23.29	24.60	24.40
40000.0	24.10	23.82	23.10	24.24	24.99	24.38	24.11	24.01	23.18	24.29	24.94	24.49
41000.0	23.59	24.10	23.94	23.53	25.08	24.76	23.72	24.18	23.61	23.76	24.99	24.98
42000.0	24.82	25.12	24.54	24.40	25.10	24.25	24.79	25.24	24.83	24.64	25.39	24.45
43000.0	24.63	24.82	25.10	24.70	25.00	24.90	24.93	25.54	25.50	24.74	25.36	25.66
44000.0	24.59	26.11	26.37	25.01	25.65	25.83	24.92	25.88	26.16	24.95	25.48	26.01
45000.0	26.35	26.68	27.21	26.92	26.59	25.81	26.14	27.23	27.10	26.44	26.68	26.50
46000.0	23.00	24.33	25.38	24.90	26.11	26.01	22.98	25.22	25.40	24.46	26.36	26.44
47000.0	19.95	23.42	23.85	22.85	24.12	24.70	19.51	22.99	23.94	22.59	24.04	24.37
48000.0	24.51	24.33	24.48	24.41	24.35	24.37	24.12	24.36	24.23	24.21	24.04	24.08
49000.0	23.29	23.48	23.71	23.81	24.03	24.21	23.13	23.36	23.21	23.96	23.93	23.73
50000.0	25.28	25.78	25.36	24.86	25.22	25.01	24.93	25.13	25.01	24.56	24.85	25.04
51000.0	25.85	25.96	25.45	26.43	26.56	26.18	25.10	24.77	24.47	25.55	25.40	24.76
52000.0	26.57	25.78	26.23	25.91	25.68	25.31	27.04	26.15	25.50	26.25	25.68	25.09
53000.0	28.35	27.26	26.78	32.93	28.85	28.37	27.57	26.57	25.91	29.86	28.51	27.47
54000.0	24.66	24.07	23.44	26.06	25.72	24.98	24.47	23.96	23.66	26.24	26.09	25.62
55000.0	23.34	22.98	22.76	24.26	24.02	24.71	23.06	22.82	22.51	23.74	23.72	24.22
56000.0	22.61	23.51	23.76	24.03	24.13	24.13	22.80	23.85	23.96	24.10	24.78	24.38
57000.0	21.34	24.08	24.60	24.33	24.30	24.75	21.07	23.39	24.65	23.75	24.47	24.96
58000.0	24.99	24.70	24.68	24.75	24.05	23.69	25.02	24.86	24.45	24.62	24.03	23.78
59000.0	23.18	24.07	24.11	24.22	24.03	23.73	22.75	23.74	23.97	24.00	23.80	23.57
60000.0	16.60	17.29	18.01	20.14	21.61	22.26	16.73	17.38	18.01	20.41	21.34	22.38
61000.0	19.03	19.97	21.86	22.94	23.96	23.87	18.92	20.09	21.89	22.75	23.96	23.94
62000.0	21.29	23.03	24.56	25.08	24.65	24.16	21.43	23.29	24.71	25.53	25.01	24.40
63000.0	20.60	24.11	22.94	24.26	23.88	23.66	20.65	25.07	23.05	25.41	25.12	24.09
64000.0	22.26	22.83	20.48	25.44	25.77	25.24	23.19	23.30	20.95	25.68	25.78	25.73



Frequency Mixer


SMIQ-653H-D+

Typical Performance Curves




Typical Performance Curves


Conversion Loss with Fixed IF




Conversion Loss with Variable IF




Conversion Loss vs. RF @ IF=2000MHz








Conversion Loss vs. IF @ FIXED LO=65GHz



Conversion Loss vs. RF @ IF=3000MHz




Typical Performance Curves




Typical Performance Curves


Amp Unbalance @ Fixed IF = 200 MHz




Phase Unbalance @ Fixed IF = 200 MHz




Amp Unbalance @ Fixed IF = 2000 MHz




Phase Unbalance @ Fixed IF = 2000 MHz



Amp Unbalance @ Fixed IF = 3000 MHz



Phase Unbalance @ Fixed IF = 3000 MHz




Frequency Mixer


SMIQ-653H-D+

Typical Performance Curves


Gain Compression (I) @ Fixed IF = 200 MHz
RF_IN = +10dBm




Gain Compression (Q) @ Fixed IF = 200 MHz
RF_IN = +10dBm




Gain Compression (I) @ Fixed IF = 2000 MHz
RF_IN = +10dBm




Gain Compression (Q) @ Fixed IF = 2000 MHz
RF_IN = +10dBm



Gain Compression (I) @ Fixed IF = 3000 MHz
RF_IN = +10dBm



Gain Compression (Q) @ Fixed IF = 3000 MHz
RF_IN = +10dBm




Frequency Mixer

SMIQ-653H-D+


Typical Performance Curves

Pout = -10dBm/tone with 1MHz spacing (RF2 = RF1 + 1MHz)


IM3_L(I) @ Fixed IF = 200 MHz




IM3_L(Q) @ Fixed IF = 200 MHz




IM3_H(I) @ Fixed IF = 200 MHz




IM3_H(Q) @ Fixed IF = 200 MHz




IM3_L(I) @ Fixed IF = 2000 MHz




IM3_L(Q) @ Fixed IF = 2000 MHz



IM3_H(I) @ Fixed IF = 2000 MHz







IM3_H(Q) @ Fixed IF = 2000 MHz



Typical Performance Curves

Pout = -10dBm/tone with 1MHz spacing (RF2 = RF1 + 1MHz)











Frequency Mixer

SMIQ-653H-D+

Typical Performance Curves

Pout = -10dBm/tone with 1MHz spacing (RF2 = RF1 + 1MHz)







Frequency Mixer

SMIQ-653H-D+

Typical Performance Curves

Pout = -10dBm/tone with 1MHz spacing (RF2 = RF1 + 1MHz)



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	