

*Wideband*

# Monolithic Amplifier

TSY-13LNB+

50Ω    0.03 to 1 GHz



2mm x 2mm

## The Big Deal

- Very wideband, 30 MHz – 1 GHz
- Low NF over entire frequency band, 1.2 dB
- Low current and low voltage (2.7V and 7.7 mA)
- Internal bypass switching

## Product Overview

TSY-13LNB+ (RoHS compliant) is an advanced Low Voltage, Low Current, Low Noise wideband Bypass amplifier fabricated using GaAs E-PHEMT technology offering extremely high dynamic range over a broad frequency range. It has integrated switches enabling users to bypass the amplifier. TSY is enclosed in a 8-lead 2 x 2 mm MLP package for good thermal performance.

## Key Features

Feature	Advantages
Ultra-wideband: 30 MHz – 1 GHz	Ideal for a wide range of receiver applications including military, commercial wireless, and instrumentation.
Low Voltage & Low Current 2.7V & 7.7 mA	Ideal for Battery operates systems
High IP3 26.4 dBm typ at 0.5 GHz	Provides enhanced linearity over broad frequency range under high signal conditions.
Bypass feature Low insertion loss	Unlike other amplifiers, insertion loss is low in Bypass mode. (For Bypass, both V <sub>DD</sub> and V <sub>E</sub> are set to 0V.)
Compact size: 2 x 2 x 1 mm	Saves space in dense system layouts. Low inductance, repeatable transitions, and excellent thermal contact.



*Wideband*

# Monolithic Amplifier

TSY-13LNB+

50Ω 0.03 to 1 GHz

## Product Features

- Wideband: 0.03-1 GHz
- Built-in Bypass switching
- Low Noise figure: 1.2 dB typ.
- P<sub>1dB</sub>: +17.1 dBm typ.
- Low current and low voltage (2.7V and 7.7 mA)



Generic photo used for illustration purposes only

CASE STYLE: MC1631-1

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



## Typical Applications

- Wireless Base Station Systems
- Test and Measurement Systems
- Multi-Band Receivers

## General Description

TSY-13LNB+(RoHS compliant) is an advanced Low Voltage, Low Current, Low Noise wideband Bypass amplifier fabricated using GaAs E-PHEMT technology offering extremely high dynamic range over a broad frequency range. It has integrated switches enabling users to bypass the amplifier. TSY is enclosed in a 8-lead 2 x 2 mm MCLP package for good thermal performance.

### *simplified schematic & pad description*



Function	Pad Number	Description (See Figure 1)
RF-IN 1 & RF-IN 2	3,4	RF-Input pads. Pad 4 is connected to Pad 3 via two 0.1μF Capacitors
RF-OUT 1 & RF-OUT 2 & VDD	5,6	RF-Output pads. Pad 6 is connected to Pad 5 via 0.1μF Capacitor.
Voltage Enable (Ve)	1	Enable Voltage pad. Ve is always connected to V <sub>DD</sub> . For amplifier bypass, V <sub>DD</sub> & Ve should be turned OFF simultaneously.
Ground	Paddle	Connect to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.
N/C	2,7,8	No connection

**Electrical Specifications<sup>1</sup> at 25°C, Zo=50Ω & V<sub>DD</sub>=2.7V unless otherwise noted**

Parameter	Condition (GHz)	Amplifier - ON			Amplifier - Bypass	Units
		Min.	Typ.	Max.		
Frequency Range		0.03			0.03 - 1	GHz
Noise Figure	0.03		1.3		0.5	dB
	0.3		1.2		0.6	
	0.5		1.2		0.8	
	0.8		1.4		1.8	
	1.0		1.4		1.9	
Gain	0.03	—	15.3	—	-0.5	dB
	0.3	—	15.1	—	-0.6	
	0.5	13.3	14.7	16.3	-0.8	
	0.8	—	13.9	—	-1.8	
	1.0	—	13.1	—	-1.9	
Input Return Loss	0.03		13		19	dB
	0.3		14		19	
	0.5		14		14	
	0.8		11		10	
	1.0		10		8	
Output Return Loss	0.03		16		18	dB
	0.3		20		18	
	0.5		18		13	
	0.8		16		9	
	1.0		14		7	
Output Power at 1dB Compression, AMP-ON <sup>2</sup>	0.03		15.9		1.2	dBm
	0.3		16.8		2.6	
	0.5		17.1		2.7	
	0.8		17.3		1.9	
	1.0		17.6		3.1	
Output IP3 <sup>3</sup>	0.03		25.6		24.9	dBm
	0.3		27.5		27.6	
	0.5		26.4		28.4	
	0.8		27.8		26.9	
	1.0		24.7		30.4	
Device Operating Voltage (V <sub>DD</sub> ) <sup>5</sup>		2.5	2.7	2.9	0	V
Device Operating Current (I <sub>D+</sub> , I <sub>e</sub> )		—	7.7	10.6	0	mA
Enable Voltage (V <sub>e</sub> ) <sup>5</sup>		2.5	2.7	2.9	0	V
Device Current Variation vs. Temperature <sup>4</sup>			1.5		—	µA/°C
Device Current Variation vs. Voltage			0.0067		—	mA/mV
Thermal Resistance, junction-to-ground lead			229		—	°C/W

1. Measured on Mini-Circuits Characterization Test Board TB-943-13LNB+. See Characterization Test Circuit (Fig. 1)

2. Current increases to 28-54 mA typ. at P1dB

3. Tested at Pout=+6 dBm/tone

4. ((Current at 85°C - Current at -45°C)/130)

5. V<sub>DD</sub> is always connected to V<sub>e</sub>**Absolute Maximum Ratings<sup>6</sup>**

Parameter	Ratings	
Operating Temperature (ground lead)	-40°C to 85°C	
Storage Temperature	-65°C to 150°C	
Total Power Dissipation	0.2W	
Input Power	Amplifier - ON	10 dBm (continuous), +23 dBm (5 min. max)
	Amplifier Bypass	15 dBm (continuous), +22 dBm (5 min. max)
DC Voltage V <sub>DD</sub> (Pad 5)	6V	
DC Voltage V <sub>e</sub> (Pad 1)	6V	

6. Permanent damage may occur if any of these limits are exceeded.

Electrical maximum ratings are not intended for continuous normal operation.


	Min.	Typ.	Max.	Units
Amplifier-ON (V <sub>DD</sub> , V <sub>e</sub> )	2.5	2.7	2.9	V
Amplifier-Bypass (V <sub>DD</sub> , V <sub>e</sub> )	—	—	0.3	



## Switching Specifications

Parameter		Min.	Typ.	Max.	Units
Amplifier ON to Bypass	OFF TIME (50% Control to 10% RF)	—	6	—	$\mu\text{s}$
	FALL TIME (90 TO 10% RF)	—	7	—	
Amplifier Bypass to ON	ON TIME (50% Control to 90% RF)	—	59	—	$\mu\text{s}$
	RISE TIME (10% to 90% RF)	—	20	—	
Control Voltage Leakage		—	443	—	mV

## Characterization Test Circuit




Component	P/N	Supplier	Value	Size
$L_1$	1008CS-102XJLC	Coilcraft	1uH	0.115" x 0.11"
$L_2$	LQG15HS3N0S02D	Murata	3nH	0402
$C_1$ to $C_8$	GRM155R71C104KA88D	Murata	0.1uF	0402
$C_9$	GRM1555C1H102JA01D	Murata	1000pF	0402
$R_1$	RK73H1ETTP4320F	KOA	$432 \Omega$	0402

**Fig 1.** Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-943-13LNB+) Gain, Return loss, Output power at 1dB compression (P1dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

### Conditions:

1. Gain and Return loss:  $\text{Pin} = -25\text{dBm}$
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +6 dBm/tone at output.
3. Switching Time RF Signal:  $\text{Pin} = -10\text{ dBm}$  at 500 MHz.  $V_{DD} = V_e = 0$  to 2.5. / 2.7 / 2.9V, Pulse Signal=500 Hz, 50% duty cycle.

## Product Marking



**Mini-Circuits®**

**Additional Detailed Technical Information**

additional information is available on our dash board. To access this information [click here](#)


<b>Performance Data</b>	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
<b>Case Style</b>	MC1631-1 Plastic package, exposed paddle, lead finish: matte-tin
<b>Tape &amp; Reel</b>	F66
Standard quantities available on reel	7" reels with 20, 50, 100, 200, 500, 1K or 2K devices
<b>Suggested Layout for PCB Design</b>	PL-536
<b>Evaluation Board</b>	TB-943-13LNB+
<b>Environmental Ratings</b>	ENV08T1

**ESD Rating**

Human Body Model (HBM): Class 1A (Pass 250) in accordance with ANSI/ESD STM 5.1 - 2001 Machine.

**MSL Rating**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

**MSL Test Flow Chart****Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

*Typical Performance Data***NOTE: Use PDF Bookmarks to view DATA at required conditions****Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.70V, Id = 7.97mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
10	14.51	20.00	8.64	7.65	1.08	0.50	30.75	15.13	1.74
20	15.26	19.32	12.44	12.85	1.08	0.55	27.96	15.68	1.31
30	15.39	19.18	13.59	15.85	1.07	0.56	26.81	16.01	1.27
40	15.45	19.12	14.14	17.82	1.07	0.56	26.60	16.71	1.24
50	15.46	19.11	14.64	19.13	1.07	0.56	25.89	17.01	1.22
60	15.47	19.09	14.85	20.01	1.07	0.57	26.79	16.80	1.17
70	15.47	19.08	14.89	20.58	1.07	0.57	27.29	16.72	1.19
80	15.46	19.07	14.95	20.97	1.07	0.57	28.00	16.77	1.15
90	15.46	19.06	15.08	21.19	1.07	0.57	27.74	16.95	1.15
100	15.46	19.05	15.11	21.34	1.07	0.57	27.91	16.57	1.16
150	15.42	19.06	15.09	21.39	1.07	0.57	31.46	16.75	1.18
200	15.37	19.03	15.09	20.62	1.07	0.58	28.28	16.73	1.14
250	15.31	19.05	15.09	20.11	1.07	0.59	36.03	16.98	1.18
300	15.24	19.02	15.07	19.23	1.07	0.59	28.04	16.94	1.15
350	15.15	19.03	14.97	18.64	1.07	0.60	33.82	16.85	1.20
400	15.05	19.00	14.80	17.95	1.07	0.61	28.48	16.98	1.22
450	14.95	18.98	14.63	17.23	1.06	0.62	27.57	17.21	1.22
500	14.83	18.97	14.36	16.65	1.06	0.64	33.07	17.39	1.22
550	14.70	18.98	14.04	16.17	1.06	0.65	30.16	17.13	1.25
600	14.56	18.97	13.72	15.70	1.06	0.67	28.52	17.17	1.29
650	14.41	18.96	13.31	15.20	1.06	0.69	29.00	17.32	1.30
700	14.23	18.98	12.85	14.75	1.06	0.71	29.57	17.19	1.31
750	14.09	18.96	12.47	14.52	1.06	0.72	29.69	17.57	1.29
800	13.92	18.97	12.02	14.21	1.06	0.74	30.49	17.47	1.36
850	13.74	18.97	11.57	13.86	1.06	0.76	29.93	17.28	1.36
900	13.54	18.99	11.10	13.49	1.05	0.78	28.79	17.37	1.39
950	13.34	19.01	10.64	13.16	1.05	0.81	28.75	17.76	1.40
1000	13.12	19.06	10.20	12.80	1.06	0.83	33.08	17.87	1.40
1100	12.50	19.34	9.11	12.10	1.08	0.90	27.48	17.63	1.48
1200	12.25	19.22	8.32	12.77	1.07	0.94	26.96	17.81	1.56
1300	11.86	19.25	7.76	11.77	1.07	0.96	27.01	17.86	1.65
1400	11.40	19.35	7.13	10.98	1.07	0.99	26.64	17.76	1.69
1500	10.93	19.48	6.54	10.25	1.07	1.01	24.66	18.36	1.75
1600	10.44	19.62	6.02	9.51	1.08	1.03	23.52	18.36	1.80
1700	9.95	19.79	5.56	8.83	1.09	1.04	22.65	17.89	1.93
1800	9.46	19.94	5.14	8.16	1.10	1.04	22.24	17.66	2.05
1900	8.97	20.13	4.76	7.51	1.11	1.03	21.17	17.36	2.15
2000	8.47	20.35	4.42	6.91	1.12	1.02	20.74	17.19	2.21

# MMIC Amplifier

# TSY-13LNB+

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.50V, Id = 6.69mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
10	13.81	19.70	8.06	7.17	1.09	0.51	25.08	14.59	1.83
20	14.59	18.95	11.17	11.88	1.08	0.56	24.80	15.14	1.38
30	14.74	18.81	12.11	14.29	1.08	0.57	24.43	15.44	1.34
40	14.79	18.74	12.53	15.66	1.08	0.58	23.87	16.15	1.27
50	14.81	18.73	12.87	16.45	1.08	0.58	23.33	16.48	1.29
60	14.82	18.71	13.02	16.91	1.08	0.58	23.98	16.27	1.24
70	14.82	18.69	13.07	17.17	1.08	0.58	25.14	16.19	1.28
80	14.82	18.69	13.09	17.34	1.08	0.58	26.18	16.24	1.23
90	14.82	18.67	13.17	17.41	1.08	0.58	26.97	16.44	1.21
100	14.81	18.66	13.19	17.45	1.08	0.58	29.32	16.05	1.22
150	14.77	18.67	13.22	17.50	1.08	0.59	28.57	16.23	1.23
200	14.72	18.64	13.25	17.07	1.08	0.59	29.06	16.22	1.22
250	14.67	18.65	13.28	16.87	1.07	0.60	27.18	16.47	1.26
300	14.60	18.62	13.31	16.33	1.07	0.60	26.77	16.43	1.29
350	14.51	18.62	13.27	15.99	1.07	0.62	27.50	16.34	1.27
400	14.42	18.60	13.18	15.52	1.07	0.62	26.45	16.48	1.28
450	14.31	18.57	13.11	15.02	1.06	0.63	25.99	16.73	1.30
500	14.20	18.56	12.95	14.60	1.06	0.65	27.53	16.90	1.24
550	14.06	18.57	12.75	14.24	1.06	0.66	28.64	16.64	1.29
600	13.93	18.55	12.54	13.87	1.06	0.68	27.77	16.66	1.33
650	13.77	18.55	12.22	13.47	1.05	0.69	27.82	16.86	1.33
700	13.60	18.56	11.88	13.12	1.05	0.71	27.68	16.71	1.38
750	13.46	18.54	11.59	12.93	1.05	0.73	27.01	17.10	1.39
800	13.28	18.55	11.21	12.67	1.05	0.75	26.83	16.98	1.44
850	13.10	18.55	10.84	12.36	1.05	0.77	26.30	16.76	1.42
900	12.90	18.57	10.45	12.06	1.04	0.79	25.92	16.86	1.44
950	12.70	18.60	10.02	11.78	1.04	0.81	25.43	17.24	1.47
1000	12.48	18.65	9.63	11.47	1.04	0.83	26.20	17.35	1.48
1100	11.85	18.95	8.60	10.95	1.06	0.90	24.23	17.09	1.56
1200	11.61	18.82	7.91	11.49	1.05	0.94	24.10	17.24	1.62
1300	11.21	18.87	7.36	10.61	1.05	0.96	24.21	17.29	1.71
1400	10.74	18.99	6.75	9.95	1.05	0.99	23.81	17.14	1.76
1500	10.26	19.14	6.17	9.34	1.05	1.01	22.74	17.93	1.83
1600	9.77	19.31	5.66	8.71	1.06	1.02	22.14	17.95	1.89
1700	9.27	19.50	5.21	8.12	1.07	1.03	21.47	17.57	2.01
1800	8.77	19.68	4.81	7.55	1.08	1.03	21.20	17.20	2.13
1900	8.28	19.90	4.44	6.98	1.09	1.03	20.35	16.84	2.25
2000	7.77	20.15	4.10	6.47	1.10	1.02	19.93	16.70	2.34

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.90V, Id = 9.31mA @ Temperature = +25°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
10	15.11	20.25	9.33	7.98	1.08	0.49	28.88	15.61	1.71
20	15.78	19.62	13.40	13.47	1.07	0.53	28.43	16.10	1.28
30	15.91	19.50	14.99	16.93	1.07	0.54	27.55	16.45	1.22
40	15.96	19.44	15.75	19.46	1.07	0.55	28.14	17.15	1.18
50	15.97	19.43	16.34	21.41	1.07	0.55	27.58	17.42	1.17
60	15.98	19.41	16.63	22.89	1.07	0.55	28.02	17.22	1.12
70	15.98	19.40	16.76	24.14	1.07	0.55	26.69	17.14	1.13
80	15.98	19.39	16.84	25.12	1.07	0.55	26.34	17.20	1.11
90	15.97	19.38	16.95	25.82	1.07	0.55	25.77	17.35	1.08
100	15.96	19.38	16.97	26.32	1.07	0.55	25.53	17.00	1.09
150	15.93	19.38	17.00	26.69	1.07	0.56	26.52	17.17	1.10
200	15.88	19.36	16.97	24.96	1.07	0.56	25.58	17.14	1.10
250	15.82	19.38	16.89	23.71	1.07	0.57	27.33	17.39	1.13
300	15.74	19.35	16.80	22.26	1.07	0.58	26.05	17.33	1.17
350	15.66	19.36	16.57	21.23	1.07	0.59	27.37	17.27	1.16
400	15.56	19.34	16.30	20.28	1.07	0.60	26.66	17.38	1.16
450	15.45	19.32	16.00	19.33	1.07	0.61	26.01	17.58	1.16
500	15.33	19.32	15.59	18.58	1.06	0.63	27.13	17.76	1.19
550	15.20	19.33	15.13	17.96	1.06	0.64	26.63	17.51	1.19
600	15.07	19.32	14.70	17.39	1.06	0.66	26.02	17.56	1.20
650	14.92	19.31	14.16	16.81	1.06	0.68	26.20	17.66	1.24
700	14.74	19.33	13.61	16.28	1.06	0.70	26.48	17.58	1.26
750	14.60	19.31	13.14	16.01	1.06	0.72	26.91	17.94	1.30
800	14.43	19.32	12.62	15.65	1.06	0.74	27.34	17.85	1.29
850	14.25	19.32	12.11	15.25	1.06	0.76	27.79	17.70	1.31
900	14.05	19.34	11.61	14.83	1.06	0.78	27.46	17.79	1.34
950	13.85	19.36	11.10	14.45	1.06	0.80	28.01	18.17	1.34
1000	13.64	19.40	10.64	14.02	1.07	0.82	28.09	18.28	1.33
1100	13.02	19.67	9.50	13.13	1.09	0.89	30.59	18.07	1.42
1200	12.76	19.55	8.63	13.93	1.08	0.93	28.90	18.25	1.50
1300	12.38	19.57	8.07	12.78	1.08	0.95	28.43	18.31	1.59
1400	11.93	19.65	7.44	11.84	1.08	0.98	29.34	18.24	1.66
1500	11.46	19.76	6.84	10.98	1.09	1.01	26.30	18.65	1.69
1600	10.98	19.89	6.32	10.12	1.09	1.02	24.68	18.61	1.76
1700	10.50	20.03	5.85	9.34	1.10	1.03	23.72	18.08	1.88
1800	10.01	20.16	5.42	8.58	1.11	1.03	23.19	17.99	1.97
1900	9.52	20.34	5.03	7.86	1.12	1.03	21.93	17.73	2.07
2000	9.02	20.53	4.68	7.19	1.13	1.02	21.47	17.52	2.15

# MMIC Amplifier

# TSY-13LNB+

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.70V, Id = 7.01mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
10	14.56	19.98	8.67	7.48	1.08	0.49	27.62	15.14	1.47
20	15.30	19.30	12.32	12.64	1.07	0.54	27.11	15.53	1.05
30	15.43	19.18	13.44	15.55	1.07	0.55	26.33	15.97	1.01
40	15.48	19.12	13.98	17.39	1.07	0.55	26.05	16.81	0.96
50	15.50	19.10	14.41	18.51	1.07	0.56	25.30	17.17	0.93
60	15.51	19.09	14.58	19.17	1.07	0.56	26.16	16.92	0.93
70	15.50	19.07	14.56	19.51	1.07	0.56	27.25	16.80	0.96
80	15.50	19.07	14.54	19.69	1.07	0.56	28.47	16.91	0.91
90	15.50	19.06	14.59	19.72	1.07	0.56	28.68	17.04	0.88
100	15.49	19.05	14.55	19.72	1.07	0.56	29.10	16.60	0.90
150	15.45	19.06	14.37	19.45	1.07	0.57	33.23	16.83	0.92
200	15.41	19.03	14.43	18.94	1.07	0.57	29.90	16.76	0.89
250	15.37	19.03	14.67	19.07	1.07	0.58	33.19	17.08	0.92
300	15.31	18.99	14.97	18.81	1.07	0.58	29.46	16.94	0.95
350	15.24	19.00	15.11	18.68	1.07	0.59	37.21	16.86	0.90
400	15.15	18.97	15.02	18.17	1.06	0.60	29.82	16.94	0.92
450	15.05	18.96	14.78	17.48	1.06	0.61	28.68	17.23	0.92
500	14.93	18.96	14.44	16.87	1.06	0.63	37.52	17.47	0.90
550	14.80	18.98	14.02	16.34	1.06	0.64	34.05	17.08	0.91
600	14.66	18.97	13.66	15.79	1.06	0.66	30.83	17.20	0.98
650	14.52	18.98	13.22	15.17	1.05	0.68	32.36	17.33	0.99
700	14.35	18.99	12.80	14.61	1.05	0.70	34.07	17.27	1.00
750	14.20	18.99	12.41	14.30	1.05	0.71	32.92	17.69	1.01
800	14.04	19.00	11.96	13.94	1.05	0.73	32.80	17.57	1.03
850	13.87	19.00	11.52	13.61	1.05	0.75	30.55	17.38	1.02
900	13.68	19.02	11.03	13.31	1.05	0.77	29.66	17.47	1.05
950	13.49	19.04	10.53	13.07	1.05	0.79	28.91	18.01	1.06
1000	13.28	19.09	10.08	12.76	1.05	0.82	27.71	18.23	1.07
1100	12.73	19.32	9.09	11.97	1.06	0.88	26.35	18.03	1.12
1200	12.39	19.30	8.11	13.07	1.06	0.94	26.34	18.16	1.22
1300	12.02	19.32	7.60	11.77	1.06	0.96	26.30	18.28	1.28
1400	11.56	19.44	6.96	10.83	1.06	0.98	25.24	18.17	1.30
1500	11.09	19.58	6.39	10.03	1.06	1.01	23.94	19.29	1.35
1600	10.61	19.73	5.88	9.26	1.06	1.02	23.24	19.22	1.39
1700	10.12	19.92	5.43	8.56	1.07	1.03	22.40	18.99	1.53
1800	9.63	20.08	5.02	7.88	1.07	1.03	22.19	18.56	1.58
1900	9.14	20.28	4.63	7.24	1.08	1.02	21.23	18.18	1.67
2000	8.66	20.49	4.28	6.67	1.09	1.01	20.61	18.08	1.73

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.50V, Id = 5.74mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
10	13.79	19.67	8.01	7.01	1.09	0.50	23.71	14.81	1.56
20	14.57	18.95	10.95	11.67	1.08	0.56	23.95	15.28	1.12
30	14.72	18.80	11.88	13.99	1.08	0.57	23.71	15.55	1.05
40	14.77	18.74	12.28	15.26	1.08	0.57	23.13	16.38	1.05
50	14.78	18.72	12.55	15.93	1.08	0.58	22.61	16.77	1.00
60	14.80	18.71	12.65	16.28	1.08	0.58	23.20	16.53	0.97
70	14.80	18.69	12.66	16.42	1.08	0.58	24.39	16.41	1.01
80	14.79	18.69	12.66	16.48	1.08	0.58	25.34	16.50	0.97
90	14.78	18.67	12.66	16.45	1.08	0.58	26.10	16.67	0.93
100	14.77	18.67	12.63	16.42	1.08	0.58	28.01	16.22	0.95
150	14.74	18.68	12.51	16.20	1.08	0.58	26.41	16.44	0.96
200	14.70	18.64	12.57	15.88	1.07	0.58	27.56	16.40	0.96
250	14.66	18.64	12.79	16.05	1.07	0.59	25.55	16.70	0.98
300	14.61	18.59	13.06	15.90	1.07	0.60	26.06	16.56	0.99
350	14.54	18.59	13.21	15.91	1.07	0.61	25.95	16.47	0.96
400	14.45	18.56	13.21	15.57	1.07	0.62	25.77	16.57	1.01
450	14.35	18.53	13.11	15.08	1.06	0.63	25.35	16.89	1.00
500	14.23	18.53	12.89	14.65	1.06	0.64	25.95	17.11	0.94
550	14.10	18.55	12.61	14.27	1.06	0.66	27.11	16.71	0.98
600	13.96	18.54	12.36	13.83	1.05	0.67	26.78	16.83	1.02
650	13.82	18.54	12.03	13.34	1.05	0.69	26.63	17.01	1.07
700	13.64	18.55	11.70	12.90	1.05	0.71	26.36	16.96	1.08
750	13.50	18.55	11.41	12.64	1.04	0.72	25.80	17.36	1.10
800	13.33	18.55	11.04	12.35	1.04	0.74	25.52	17.24	1.07
850	13.16	18.55	10.68	12.07	1.04	0.76	25.04	17.01	1.09
900	12.97	18.57	10.27	11.83	1.04	0.78	24.84	17.11	1.09
950	12.78	18.60	9.83	11.63	1.04	0.80	24.33	17.58	1.11
1000	12.57	18.64	9.43	11.39	1.04	0.82	24.15	17.74	1.12
1100	12.00	18.88	8.52	10.77	1.05	0.89	23.15	17.51	1.19
1200	11.68	18.85	7.67	11.72	1.04	0.95	23.20	17.61	1.28
1300	11.30	18.88	7.17	10.62	1.04	0.96	23.17	17.71	1.33
1400	10.83	19.02	6.55	9.85	1.04	0.99	22.54	17.54	1.37
1500	10.35	19.18	5.99	9.18	1.04	1.01	21.78	18.71	1.45
1600	9.85	19.35	5.49	8.54	1.04	1.02	21.45	18.65	1.47
1700	9.35	19.55	5.06	7.94	1.05	1.03	20.96	18.49	1.59
1800	8.86	19.73	4.66	7.35	1.05	1.03	20.91	18.00	1.69
1900	8.36	19.96	4.28	6.79	1.06	1.02	20.25	17.57	1.78
2000	7.87	20.20	3.95	6.29	1.07	1.01	19.76	17.46	1.84

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.90V, Id = 8.38mA @ Temperature = -45°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
10	15.24	20.27	9.39	7.88	1.07	0.47	33.18	15.40	1.39
20	15.90	19.65	13.44	13.40	1.07	0.52	28.67	15.56	1.02
30	16.02	19.53	15.03	16.83	1.07	0.53	27.46	16.19	0.96
40	16.07	19.48	15.82	19.32	1.07	0.54	28.26	17.04	0.93
50	16.08	19.47	16.29	21.13	1.07	0.54	27.81	17.36	0.87
60	16.09	19.45	16.56	22.41	1.07	0.54	28.26	17.13	0.85
70	16.09	19.44	16.64	23.35	1.07	0.54	26.84	17.02	0.89
80	16.09	19.43	16.65	23.95	1.07	0.54	26.48	17.14	0.81
90	16.08	19.42	16.66	24.30	1.07	0.54	25.95	17.24	0.81
100	16.07	19.41	16.64	24.46	1.07	0.54	25.59	16.84	0.84
150	16.04	19.43	16.42	24.10	1.07	0.55	26.57	17.08	0.84
200	15.99	19.40	16.47	23.14	1.06	0.55	25.68	16.96	0.81
250	15.95	19.40	16.74	23.00	1.06	0.56	27.37	17.31	0.86
300	15.89	19.37	17.02	22.35	1.06	0.56	26.32	17.17	0.86
350	15.81	19.38	17.03	21.78	1.06	0.58	27.51	17.10	0.86
400	15.72	19.36	16.80	20.95	1.06	0.59	27.05	17.19	0.87
450	15.62	19.34	16.40	19.98	1.06	0.60	26.49	17.41	0.88
500	15.50	19.35	15.86	19.15	1.06	0.61	27.41	17.68	0.84
550	15.37	19.36	15.29	18.44	1.06	0.63	26.85	17.29	0.90
600	15.24	19.36	14.81	17.77	1.06	0.65	26.32	17.42	0.91
650	15.09	19.36	14.25	17.02	1.06	0.67	26.66	17.49	0.92
700	14.93	19.38	13.73	16.35	1.06	0.69	27.04	17.45	0.95
750	14.78	19.38	13.25	15.98	1.06	0.70	27.76	17.88	0.94
800	14.62	19.38	12.74	15.56	1.06	0.72	28.20	17.77	0.97
850	14.45	19.38	12.21	15.18	1.06	0.74	28.98	17.66	0.97
900	14.26	19.40	11.67	14.84	1.06	0.76	28.89	17.75	1.00
950	14.07	19.42	11.11	14.54	1.06	0.79	30.33	18.33	0.98
1000	13.87	19.46	10.63	14.18	1.06	0.81	27.59	18.61	1.01
1100	13.32	19.68	9.60	13.17	1.07	0.87	35.42	18.44	1.08
1200	12.97	19.66	8.50	14.45	1.08	0.93	32.88	18.60	1.12
1300	12.62	19.66	7.99	12.93	1.07	0.95	32.52	18.75	1.20
1400	12.17	19.76	7.35	11.82	1.07	0.98	30.42	18.67	1.23
1500	11.71	19.87	6.76	10.87	1.07	1.00	27.05	19.72	1.28
1600	11.23	20.00	6.25	9.97	1.08	1.01	25.26	19.67	1.33
1700	10.75	20.16	5.79	9.16	1.08	1.02	24.00	19.37	1.44
1800	10.27	20.29	5.37	8.38	1.09	1.02	23.56	19.03	1.52
1900	9.78	20.47	4.95	7.66	1.09	1.02	22.20	18.68	1.58
2000	9.29	20.65	4.60	7.00	1.10	1.00	21.51	18.58	1.61

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.70V, Id = 8.93mA @ Temperature = +85°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
10	14.43	19.96	8.66	7.65	1.08	0.51	33.40	14.38	2.03
20	15.17	19.28	12.24	12.80	1.08	0.55	28.97	15.03	1.55
30	15.31	19.14	13.42	15.80	1.08	0.56	27.51	15.46	1.53
40	15.36	19.08	13.99	17.76	1.07	0.57	27.46	16.06	1.48
50	15.37	19.06	14.49	19.09	1.08	0.57	26.66	16.27	1.44
60	15.39	19.05	14.75	20.00	1.07	0.57	27.60	16.12	1.41
70	15.39	19.03	14.84	20.68	1.07	0.57	27.57	16.08	1.44
80	15.39	19.02	14.95	21.19	1.07	0.57	27.89	16.10	1.41
90	15.39	19.01	15.12	21.58	1.07	0.57	27.35	16.26	1.37
100	15.38	19.00	15.20	21.90	1.07	0.57	27.18	15.95	1.40
150	15.35	19.00	15.44	22.59	1.07	0.58	29.18	16.09	1.40
200	15.30	18.98	15.51	21.87	1.07	0.58	27.44	16.08	1.40
250	15.23	19.00	15.37	20.88	1.07	0.59	31.32	16.27	1.42
300	15.14	18.98	15.17	19.55	1.07	0.60	27.65	16.26	1.45
350	15.05	18.99	14.88	18.57	1.07	0.61	31.02	16.20	1.45
400	14.94	18.97	14.62	17.67	1.07	0.62	28.18	16.32	1.46
450	14.83	18.95	14.39	16.84	1.07	0.63	27.25	16.44	1.48
500	14.71	18.94	14.15	16.25	1.06	0.65	30.60	16.59	1.43
550	14.57	18.95	13.84	15.74	1.06	0.66	28.77	16.43	1.49
600	14.43	18.93	13.54	15.28	1.06	0.68	27.70	16.44	1.55
650	14.27	18.93	13.13	14.80	1.06	0.69	27.96	16.53	1.55
700	14.09	18.94	12.69	14.37	1.06	0.72	28.40	16.42	1.61
750	13.95	18.92	12.34	14.11	1.06	0.73	28.73	16.75	1.62
800	13.77	18.92	11.90	13.77	1.06	0.75	29.43	16.69	1.65
850	13.59	18.93	11.48	13.41	1.06	0.77	29.50	16.56	1.64
900	13.38	18.94	11.06	13.05	1.06	0.79	28.39	16.61	1.67
950	13.18	18.97	10.61	12.73	1.06	0.81	28.69	16.87	1.71
1000	12.96	19.01	10.19	12.38	1.06	0.83	33.23	16.88	1.69
1100	12.32	19.30	9.05	11.99	1.08	0.91	28.76	16.63	1.78
1200	12.11	19.12	8.43	12.29	1.07	0.93	27.71	16.80	1.86
1300	11.71	19.16	7.85	11.49	1.07	0.95	27.62	16.82	1.95
1400	11.25	19.25	7.22	10.82	1.07	0.98	27.58	16.74	2.01
1500	10.78	19.37	6.63	10.17	1.08	1.01	25.11	16.80	2.07
1600	10.30	19.51	6.10	9.50	1.09	1.02	23.94	16.74	2.19
1700	9.81	19.68	5.63	8.87	1.10	1.04	22.96	16.24	2.25
1800	9.32	19.83	5.20	8.25	1.11	1.04	22.45	16.21	2.44
1900	8.82	20.02	4.80	7.63	1.12	1.04	21.31	15.99	2.51
2000	8.30	20.25	4.45	7.06	1.13	1.03	20.81	15.71	2.64

# MMIC Amplifier

# TSY-13LNB+

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.50V, Id = 7.61mA @ Temperature = +85°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
10	13.79	19.67	8.09	7.22	1.09	0.51	26.14	13.92	2.11
20	14.57	18.95	11.12	11.92	1.08	0.56	25.83	14.51	1.64
30	14.71	18.80	12.09	14.36	1.08	0.58	25.33	14.88	1.58
40	14.77	18.74	12.57	15.77	1.08	0.58	24.78	15.54	1.54
50	14.79	18.71	12.91	16.63	1.08	0.58	24.18	15.79	1.50
60	14.80	18.70	13.09	17.16	1.08	0.58	24.95	15.63	1.48
70	14.81	18.68	13.20	17.52	1.08	0.58	26.18	15.58	1.49
80	14.81	18.67	13.29	17.77	1.08	0.58	27.45	15.59	1.48
90	14.81	18.65	13.40	17.96	1.08	0.58	28.20	15.79	1.47
100	14.80	18.64	13.46	18.11	1.08	0.58	30.51	15.45	1.47
150	14.78	18.64	13.69	18.56	1.08	0.59	32.42	15.60	1.49
200	14.72	18.61	13.78	18.20	1.08	0.59	31.11	15.60	1.48
250	14.66	18.63	13.71	17.74	1.08	0.61	29.70	15.81	1.47
300	14.57	18.61	13.58	16.88	1.07	0.61	28.02	15.79	1.50
350	14.47	18.63	13.38	16.24	1.07	0.62	30.06	15.71	1.51
400	14.37	18.61	13.21	15.59	1.07	0.63	27.64	15.85	1.53
450	14.26	18.59	13.07	14.96	1.07	0.64	26.94	16.02	1.56
500	14.14	18.58	12.90	14.50	1.06	0.65	29.93	16.17	1.53
550	14.00	18.58	12.71	14.12	1.06	0.67	30.76	15.99	1.58
600	13.86	18.57	12.50	13.76	1.06	0.68	28.93	15.99	1.59
650	13.71	18.56	12.19	13.35	1.06	0.70	29.14	16.12	1.63
700	13.52	18.58	11.85	13.00	1.06	0.72	29.20	15.98	1.67
750	13.38	18.56	11.56	12.77	1.05	0.73	28.37	16.34	1.68
800	13.20	18.56	11.20	12.47	1.05	0.75	28.32	16.26	1.69
850	13.02	18.57	10.85	12.16	1.05	0.77	27.64	16.10	1.73
900	12.82	18.59	10.46	11.85	1.05	0.79	26.93	16.17	1.74
950	12.62	18.62	10.06	11.56	1.05	0.81	26.43	16.48	1.74
1000	12.39	18.67	9.67	11.25	1.05	0.83	27.95	16.52	1.74
1100	11.75	18.96	8.62	10.98	1.07	0.91	25.28	16.22	1.85
1200	11.55	18.79	8.07	11.18	1.06	0.93	24.99	16.40	1.95
1300	11.14	18.85	7.50	10.47	1.06	0.95	25.18	16.43	2.00
1400	10.68	18.97	6.88	9.88	1.06	0.98	24.83	16.30	2.11
1500	10.20	19.10	6.30	9.32	1.06	1.00	23.38	16.55	2.16
1600	9.71	19.27	5.79	8.74	1.07	1.02	22.66	16.55	2.27
1700	9.21	19.46	5.33	8.19	1.08	1.03	21.87	16.07	2.39
1800	8.71	19.63	4.91	7.65	1.09	1.03	21.52	15.93	2.53
1900	8.20	19.86	4.52	7.11	1.11	1.03	20.56	15.67	2.65
2000	7.69	20.11	4.18	6.61	1.12	1.03	20.09	15.45	2.74

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)









TEST CONDITIONS: Vd = 2.90V, Id = 10.24mA @ Temperature = +85°C

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
10	14.95	20.17	9.28	7.95	1.08	0.50	28.32	14.71	1.98
20	15.63	19.54	13.11	13.36	1.07	0.54	28.62	15.43	1.51
30	15.76	19.41	14.62	16.74	1.07	0.55	27.90	15.92	1.45
40	15.82	19.35	15.38	19.18	1.07	0.55	28.49	16.48	1.44
50	15.82	19.34	15.94	21.02	1.07	0.56	27.85	16.63	1.39
60	15.84	19.32	16.27	22.45	1.07	0.56	28.04	16.51	1.38
70	15.84	19.30	16.46	23.68	1.07	0.56	26.58	16.48	1.37
80	15.84	19.30	16.62	24.69	1.07	0.56	26.15	16.51	1.34
90	15.83	19.29	16.77	25.57	1.07	0.56	25.58	16.62	1.32
100	15.83	19.28	16.86	26.26	1.07	0.56	25.33	16.36	1.34
150	15.80	19.28	17.18	27.81	1.07	0.56	26.14	16.49	1.34
200	15.74	19.27	17.22	26.03	1.07	0.57	25.38	16.46	1.34
250	15.67	19.28	16.97	24.02	1.07	0.58	26.87	16.64	1.35
300	15.59	19.27	16.63	22.16	1.07	0.59	25.87	16.63	1.41
350	15.49	19.28	16.25	20.74	1.07	0.60	26.96	16.58	1.40
400	15.39	19.27	15.89	19.64	1.07	0.61	26.44	16.68	1.42
450	15.27	19.25	15.57	18.64	1.07	0.62	25.75	16.74	1.40
500	15.16	19.25	15.21	17.91	1.07	0.64	26.68	16.88	1.44
550	15.02	19.25	14.82	17.30	1.07	0.65	26.23	16.77	1.41
600	14.88	19.25	14.41	16.77	1.07	0.67	25.71	16.80	1.52
650	14.72	19.24	13.91	16.21	1.07	0.69	25.80	16.81	1.50
700	14.54	19.26	13.39	15.70	1.07	0.71	26.02	16.76	1.54
750	14.40	19.25	12.94	15.41	1.06	0.72	26.38	17.02	1.56
800	14.22	19.25	12.47	15.02	1.07	0.74	26.74	17.01	1.59
850	14.04	19.25	11.99	14.61	1.07	0.76	27.18	16.93	1.58
900	13.84	19.27	11.53	14.20	1.07	0.78	26.84	16.94	1.61
950	13.64	19.29	11.04	13.81	1.07	0.80	27.26	17.11	1.62
1000	13.42	19.34	10.59	13.40	1.07	0.83	27.35	17.07	1.64
1100	12.78	19.63	9.40	12.87	1.09	0.90	29.90	16.89	1.71
1200	12.57	19.45	8.72	13.23	1.08	0.92	28.33	17.02	1.80
1300	12.17	19.48	8.13	12.30	1.08	0.95	27.76	17.05	1.86
1400	11.72	19.57	7.49	11.50	1.09	0.98	28.75	17.01	1.92
1500	11.25	19.68	6.88	10.74	1.09	1.00	26.25	16.91	2.00
1600	10.77	19.81	6.35	9.96	1.10	1.02	24.91	16.82	2.06
1700	10.28	19.96	5.87	9.25	1.11	1.03	23.88	16.31	2.22
1800	9.79	20.09	5.43	8.55	1.12	1.03	23.27	16.36	2.34
1900	9.29	20.28	5.03	7.87	1.14	1.03	21.96	16.15	2.43
2000	8.79	20.48	4.67	7.24	1.15	1.02	21.44	15.74	2.55








# MMIC Amplifier

**TSY-13LNB+**

## Typical Performance Curves



## Typical Performance Curves





# Case Style

MC

MC1631-1

## Outline Dimensions

### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

SE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	P
MC1631-1	.079 (2.00)	.079 (2.00)	.039 (1.00)	.047 (1.20)	.024 (.60)	.009 (.23)	.014 (.35)	.020 (.50)	.008 (.20)	.002 (.05)	.106 (2.70)	.049 (1.25)	.026 (.65)	.031 (.80)

CASE #.	Q	R	WT, GRAM
MC1631-1	.010 (.25)	.012 (.30)	.006

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

1. Case material: Plastic.
2. Termination finish:

For RoHS Case Styles: Tin-Silver over Nickel plated or Matte-Tin Plated (See Data sheet).  
All models, (+) suffix.

3. Lead #1 identifier shall be located in the cross-hatched area shown.  
Identifier may be either a molded or marked feature.

 **Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
[minicircuits.com](http://minicircuits.com)

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/I/F MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F66

## DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified


## THIRD ANGLE PROJECTION



## REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M165468	NEW RELEASE	01/05/18	ITG	GH

SUGGESTED MOUNTING CONFIGURATION  
FOR MC1631-1 CASE STYLE, "08AM17" PIN CODE



## NOTES:

1. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS  $.010'' \pm .001''$ . COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
2. CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE.  
FOR COMPONENT VALUES REFER TO TB-943+ & TB-943-13LNB+.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	01/03/17
TOLERANCES ON: 2 PL DECIMALS $\pm .005$	CHECKED	IL	01/05/18
ANGLES $\pm$	APPROVED	GH	01/05/18
FRACTIONS $\pm$			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.  
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE  
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY  
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.  
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE  
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, 08AM17, MC1631-1, TB-943+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-536	OR
FILE: 98PL536	SCALE: 8:1	SHEET: 1	OF 1

# Evaluation Board and Circuit



ITEM	DESCRIPTION	SIZE
C1-C8	CAP, 0,1 uF	
C9	CAP, 1000 pF	
R1	RES, 432 Ohm	.04"x02"
L1	IND, 3 nH	
L2	IND, 1000 nH	.115"x.110"
DUT	TSY-13LNB+	

Schematic Diagram

## NOTES:

1. SMA Female connectors.
2. PCB material: Rogers RO4350 or equivalent, dielectric constant=3.5, dielectric thickness=.010 inch.

Mini-Circuits®



## Environmental Specifications

## ENV08T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215