



TTL

# Solid-State Switch

50Ω 0.1 to 18 GHz SP4T SMA female

**TTL-1SP4T-183**

Mini-Circuits

**THE BIG DEAL**

- Fast-switching, absorptive solid-state SP4T
- 100 ns switching time with no control delays
- TTL for simple control integration
- Low insertion loss



Generic photo used for illustration purposes only

**APPLICATIONS**

- RF signal routing / switch matrices
- 5G FR1, WiFi 6E, UWB, Bluetooth
- Military radio, radar & electronic warfare
- Microwave radio / cellular infrastructure
- Test & measurement systems

**PRODUCT OVERVIEW**

Mini-Circuits' TTL-1SP4T-183 is a fast switching SP4T featuring low loss and high isolation over a wide bandwidth. The switch has an absorptive configuration with internal terminations on ports J1 to J4.

Simple control via TTL logic levels allows integration with a wide range of microcontroller, embedded or custom systems, without the communication delays associated with USB or Ethernet control. This complete package enables exceptionally fast switching times down to 100 ns typically.

The switch is supplied in a low profile package (5.00" x 1.50" x 0.70") with 5 precision SMA (F) RF connectors and a D-Sub 9 pin port for power and control.

**KEY FEATURES**

Feature	Advantages
Excellent RF performance	Low loss, high isolation and exceptional switching speeds support applications requiring rapid signal transitions and minimal interference such as semi-conductor and telecoms testing.
Solid-state design	Long-term reliability in the most demanding automated test applications
Optimized for hot switching	+30 dBm power rating applies even when hot switching or terminating inactive ports internally. Ideal for radio test applications where the signal can't be removed during switching.
TTL control	Simple control via TTL logic levels allows integration with a wide range of microcontroller, embedded or custom systems; and extremely fast switching times without the communication delays inherent to USB or Ethernet.

**Trademarks:**

Windows is a registered trademark of Microsoft Corporation in the United States and other countries ; Linux is a registered trademark of Linus Torvalds ; Pentium is a registered trademark of Intel Corporation. Neither Mini-Circuits nor the Mini-Circuits products are affiliated with or endorsed by the owners of the referenced trademarks. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation.

Rev. A  
ECO-020163  
EDR-11941  
TTL-1SP4T-183  
MCIL  
231206  
PAGE 1 OF 10

**Mini-Circuits®**

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com



TTL

# Solid-State Switch

TTL-1SP4T-183

Mini-Circuits

50Ω 0.1 to 18 GHz SP4T SMA female

## ELECTRICAL SPECIFICATIONS AT -10 TO 60°C

Parameter	Ports	Condition (GHz)	Min.	Typ.	Max.	Unit
Frequency Range	-	-	0.1	-	18	GHz
Insertion Loss	COM to any active port	0.1 - 0.5	-	2.0	3.5	dB
		0.5 - 10	-	2.5	4.0	
		10 - 14	-	3.5	5.0	
		14 - 18	-	4.0	5.5	
Isolation	Between ports J1 to J4	0.1 - 0.5	60	80	-	dB
		0.5 - 10	50	65	-	
		10 - 14	45	64	-	
		14 - 18	45	60	-	
	COM to any terminated port (including Disconnected state)	0.1 - 0.5	60	80	-	dB
		0.5 - 10	52	70	-	
		10 - 14	47	65	-	
		14 - 18	47	65	-	
Return Loss	COM port (in all active states)	0.1 - 10	-	16	-	dB
		10 - 18	-	11	-	
	Any port connected to COM	0.1 - 0.5	-	13	-	dB
		0.5 - 10	-	14	-	
		10 - 14	-	15	-	
		14 - 18	-	13	-	
	Any terminated port	0.1 - 0.5	-	23	-	dB
		0.5 - 10	-	16	-	
		10 - 14	-	12	-	
		14 - 18	-	10	-	
Power Input @1 dB Compression	COM to any active port	0.1 - 4	-	+20	-	dBm
		4 - 18	-	+30	-	
IP3 <sup>1</sup>	COM to any active port	0.5 - 18	-	+40	-	dBm
Transition Time <sup>2</sup>	-	-	-	50	-	ns
Switching Time <sup>3</sup>	-	-	-	100	-	ns
Operating RF Input Power	Between COM & active port	Hot switching	-	-	+30	dBm
	Between COM & active port	Cold switching	-	-	+30	
	Into any termination	-	-	-	+30	

1. IP3 degrades below 500 MHz. Tested with 1 MHz span between signals, 0 dBm per tone

2. Transition Time spec represents the time that the RF signal paths are interrupted during switching (from steady state to steady state) and thus is specified without communication delays.

3. Switching time is the time from 50% control to 90 / 10% of RF signal.



TTL

# Solid-State Switch

**TTL-1SP4T-183**

Mini-Circuits

50Ω 0.1 to 18 GHz SP4T SMA female

**DC ELECTRICAL SPECIFICATION**

Parameter	Min.	Typ.	Max.	Units
Positive Supply	Voltage	4.75	-	V <sub>DC</sub>
	Current	-	40	mA
Negative Supply	Voltage	-5.25	-	V <sub>DC</sub>
	Current	-15	-12	mA
Control Current per bit	-	-	100	µA

**ABSOLUTE MAXIMUM RATINGS<sup>4</sup>**

Operating Temperature	-10°C to 60°C
Storage Temperature	-20°C to 85°C
DC Supply Voltage @ positive supply (Pin#6)	0 to 6 V
DC Supply Voltage @ negative supply (Pin#6)	-5.3 to 0 V
Voltage at TTL control pins	5.5V
DC Voltage @ RF Ports	5.5V

4. Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

**Mini-Circuits®**

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 3 OF 10



TTL

# Solid-State Switch


**TTL-1SP4T-183**

Mini-Circuits


50Ω 0.1 to 18 GHz SP4T SMA female

## TYPICAL PERFORMANCE GRAPHS


Insertion Loss over Temperature (J1 Active)




Insertion Loss J1 - J4 Active




Isolation Com to J1 (J2 Active)




Isolation Com to J2 (J3 Active)



Isolation J2 to J3 (J3 Active)



Isolation J3 to J4 (J3 Active)

**Mini-Circuits®**[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 4 OF 10



TTL

# Solid-State Switch


**TTL-1SP4T-183**

Mini-Circuits


50Ω 0.1 to 18 GHz SP4T SMA female

## TYPICAL PERFORMANCE GRAPHS (CONTINUED)


Return Loss @ COM over Temperature (J1 Active)




Return Loss @ 1 over Temperature (J1 Active)




Return Loss @ J1 over Temperature (J1 Terminated)



Return Loss @ Active ports (J1- J4 Active)



Return Loss @ Terminated ports (J1 - J4 Terminated)

**Mini-Circuits®**[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 5 OF 10



TTL

# Solid-State Switch

50Ω 0.1 to 18 GHz SP4T SMA female

TTL-1SP4T-183

Mini-Circuits

## TTL CONTROL LOGIC

Parameter	Conditions		Min.	Typ.	Max.	Units
Voltage Levels	Logic Low Voltage	Input	0	-	0.8	V
	Logic High Voltage	Input	3.5	-	5.0	

The switch's TTL control interface consists of 3 parallel control bits that select the desired switch state, as shown in the truth table below. The parallel control does not have any latch and thus will respond immediately to any change.

The TTL inputs have internal 100kΩ pull-down (inputs D1 & D2) and pull-up (input D3) resistors to set the switch to the disconnected state (all ports including COM internally terminated) when no control signal is applied.

The DC voltage supplies to the switch are provided via the D-sub port.

Switch State	Control Bits		
	D1	D2	D3
Disconnected	Logic Low	Logic Low	Logic High
COM -> J4	Logic Low	Logic Low	Logic Low
COM -> J3	Logic High	Logic Low	Logic Low
COM -> J2	Logic Low	Logic High	Logic Low
COM -> J1	Logic High	Logic High	Logic Low

## D-SUB PIN CONNECTIONS

Pin	Function
1	D1
2	D2
3	D3
4,5	Not connected
6	Supply +5V
7,9	GND
8	Supply -5V




TTL

# Solid-State Switch

**TTL-1SP4T-183**

Mini-Circuits

50Ω 0.1 to 18 GHz SP4T SMA female

**BLOCK DIAGRAM**Switch functional diagram shown in disconnected state**CONNECTIONS**

Port Name	Connector Type
RF Ports (COM, J1 to J4)	SMA Female
TTL	9-pin D-Sub Male

**Mini-Circuits®**[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 7 OF 10




TTL

# Solid-State Switch

**TTL-1SP4T-183**

Mini-Circuits

50Ω 0.1 to 18 GHz SP4T SMA female

**CASE STYLE DRAWING (RB3522)****NOTES:**

1. Case material: Aluminum alloy.
2. Case Finish: Nickel Plate.
3. Dimensions: Inches [mm]
4. Weight: 300 grams
5. Marking may contain other features or characters for internal lot control.

**Mini-Circuits®**



TTL

# Solid-State Switch

**TTL-1SP4T-183**


Mini-Circuits

50Ω 0.1 to 18 GHz SP4T SMA female

## RECOMMENDED ACCESSORIES

TTL-1SP4T-183 is controlled via a standard 9 pin D-Sub connector and is supplied with a male-female D-Sub 9 cable. The cable is 6 feet (1.8 meter) long and uses 28 AWG wires.

**CONTROL CABLE D-SUB9-MF-6+**



Pin Number (Male)	Function	Description	Pin Number (Female)
1	D1	Control bit 1	1
2	D2	Control bit 2	2
3	D3	Control bit 3	3
4	Not Connected	Not Connected	4
5	Not Connected	Not Connected	5
6	Supply +5V	Supply Voltage (Positive)	6
7	GND	Ground connection	7
8	Supply -5V	Supply Voltage (Negative)	8
9	GND	Ground connection	9

**Mini-Circuits®**[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 9 OF 10



TTL

# Solid-State Switch

50Ω 0.1 to 18 GHz SP4T SMA female

TTL-1SP4T-183

Mini-Circuits

DETAILED MODEL INFORMATION IS AVAILABLE ON OUR WEBSITE

CLICK HERE

Performance Data & Graphs	Data Graphs
Case Style	RB3522
Environmental Rating	ENV55T2
User Guide	<a href="https://www.minicircuits.com/softwaredownload/solidstate.html">https://www.minicircuits.com/softwaredownload/solidstate.html</a>
Regulatory Compliance	Refer to user guide for compliance information  <a href="https://www.minicircuits.com/app/AN49-012.pdf">https://www.minicircuits.com/app/AN49-012.pdf</a>
Support	<a href="mailto:testsolutions@minicircuits.com">testsolutions@minicircuits.com</a>

## INCLUDED ACCESSORIES

	Part No.	Description
See drawing on page 9	D-SUB9-MF-6+	6.0 ft (1.8 m) D-Sub cable: 9 pin D-sub (Male) to 9 pin D-sub (Female)

### NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>

 Mini-Circuits®

**Typical Performance Data**

Test Conditions: @ Temperature = -10°C, Pin = 5 dBm.

Freq. (GHz)	Insertion Loss (dB)			
	COM-J1	COM-J2	COM-J3	COM-J4
0.10	-2.50	-2.51	-2.50	-2.52
0.50	-1.57	-1.54	-1.54	-1.56
1.00	-1.59	-1.56	-1.55	-1.58
1.50	-1.62	-1.62	-1.60	-1.61
2.00	-1.69	-1.69	-1.68	-1.67
2.50	-1.79	-1.79	-1.78	-1.77
3.00	-1.90	-1.90	-1.89	-1.87
3.50	-1.84	-1.78	-1.80	-1.81
4.00	-1.88	-1.81	-1.79	-1.86
4.50	-2.04	-1.89	-1.84	-2.00
5.00	-2.07	-2.03	-1.96	-2.03
5.50	-2.26	-2.40	-2.42	-2.15
6.00	-2.29	-2.36	-2.37	-2.32
6.50	-2.37	-2.19	-2.27	-2.37
7.00	-2.46	-2.16	-2.25	-2.56
7.50	-2.39	-2.18	-2.23	-2.50
8.00	-2.34	-2.40	-2.35	-2.32
8.50	-2.58	-2.55	-2.52	-2.43
9.00	-2.73	-2.57	-2.61	-2.65
9.50	-2.65	-2.44	-2.56	-2.71
10.00	-2.66	-2.49	-2.59	-2.73
10.50	-2.93	-2.85	-2.89	-3.04
11.00	-2.62	-2.55	-2.54	-2.62
11.50	-2.67	-2.51	-2.52	-2.60
12.00	-2.92	-2.66	-2.63	-2.80
12.50	-3.12	-2.86	-2.95	-2.98
13.00	-2.94	-2.87	-3.15	-2.95
13.50	-2.86	-2.93	-3.35	-2.89
14.00	-2.99	-3.01	-3.60	-2.86
14.50	-3.68	-3.41	-3.97	-3.22
15.00	-3.98	-3.49	-3.52	-3.80
15.50	-3.69	-3.24	-3.11	-3.92
16.00	-3.46	-2.99	-2.95	-3.81
16.50	-3.20	-3.03	-3.03	-3.55
17.00	-3.54	-3.34	-3.56	-3.45
17.50	-3.41	-3.21	-3.41	-3.28
18.00	-3.53	-3.36	-3.62	-3.44
18.50	-3.62	-3.80	-3.55	-3.63
19.00	-4.00	-4.32	-3.73	-3.62
19.50	-4.44	-4.58	-4.34	-4.24
20.00	-4.90	-4.70	-4.41	-4.54

**SP4T Solid-State Switch****TTL-1SP4T-183****Typical Performance Data**

Test Conditions: @ Temperature = -10°C, Pin = 5 dBm.

Freq. (GHz)	Return Loss, Active ports (dB)					R. Loss, Internally terminated ports (dB)			
	COM	J1	J2	J3	J4	J1	J2	J3	J4
	-10.84	-8.46	-8.40	-8.46	-8.38	-29.22	-29.21	-29.29	-29.21
0.50	-22.85	-17.73	-18.39	-18.39	-17.73	-29.05	-29.05	-29.19	-29.55
1.00	-31.96	-21.10	-20.99	-20.71	-21.24	-26.52	-26.52	-26.71	-26.55
1.50	-27.18	-26.34	-22.76	-22.44	-26.02	-24.47	-24.47	-25.29	-24.26
2.00	-19.48	-28.10	-24.79	-24.32	-30.42	-22.55	-22.55	-23.15	-22.76
2.50	-16.82	-26.31	-23.06	-23.35	-27.18	-20.23	-20.23	-21.12	-20.92
3.00	-16.88	-25.26	-21.34	-21.97	-25.39	-18.29	-18.28	-18.17	-18.63
3.50	-20.28	-19.88	-22.42	-23.61	-20.04	-16.71	-16.71	-16.50	-17.15
4.00	-27.24	-18.24	-21.84	-25.22	-18.42	-15.45	-15.45	-15.17	-16.37
4.50	-19.23	-16.52	-18.69	-21.55	-16.36	-14.33	-14.33	-14.00	-15.12
5.00	-16.76	-18.27	-14.53	-15.35	-17.25	-13.38	-13.38	-13.20	-14.46
5.50	-16.65	-17.11	-12.11	-11.79	-17.65	-12.83	-12.83	-12.66	-13.84
6.00	-19.58	-16.85	-15.02	-13.44	-18.04	-12.64	-12.64	-12.33	-13.63
6.50	-17.17	-12.12	-15.81	-12.65	-11.82	-12.66	-12.65	-12.58	-13.79
7.00	-17.30	-12.28	-18.34	-14.13	-10.74	-13.36	-13.36	-13.17	-14.72
7.50	-21.66	-15.61	-15.59	-15.57	-12.34	-14.63	-14.62	-14.56	-16.04
8.00	-17.94	-16.80	-12.53	-13.86	-16.20	-16.38	-16.37	-16.64	-17.63
8.50	-11.95	-12.44	-11.89	-11.75	-14.03	-19.75	-19.73	-20.39	-20.59
9.00	-11.93	-11.75	-13.31	-11.84	-11.65	-28.58	-28.53	-25.80	-25.55
9.50	-16.10	-13.63	-15.78	-13.20	-11.87	-25.16	-25.16	-21.80	-20.29
10.00	-23.25	-19.20	-20.86	-15.07	-13.68	-16.51	-16.50	-15.86	-15.08
10.50	-34.02	-21.51	-18.82	-18.20	-21.73	-12.99	-12.97	-13.14	-12.38
11.00	-18.56	-20.31	-19.66	-21.76	-29.15	-11.28	-11.27	-11.97	-11.17
11.50	-14.82	-33.03	-27.56	-22.53	-35.69	-11.20	-11.20	-12.61	-10.99
12.00	-10.93	-16.95	-22.65	-25.03	-22.44	-11.40	-11.41	-13.73	-11.53
12.50	-10.26	-13.82	-16.91	-17.57	-15.82	-11.94	-11.94	-14.27	-12.04
13.00	-12.40	-15.71	-15.43	-13.75	-14.90	-12.27	-12.25	-14.02	-12.13
13.50	-17.22	-20.91	-14.53	-11.00	-16.07	-12.46	-12.45	-14.18	-13.03
14.00	-20.57	-22.52	-15.24	-9.66	-22.69	-13.10	-13.09	-13.56	-14.02
14.50	-11.49	-13.45	-14.34	-9.82	-19.46	-12.82	-12.82	-12.12	-13.65
15.00	-9.63	-13.53	-13.65	-14.47	-14.20	-11.56	-11.56	-10.89	-11.72
15.50	-9.65	-13.21	-14.64	-16.31	-11.29	-11.06	-11.04	-10.78	-10.58
16.00	-11.63	-12.69	-25.17	-20.55	-10.58	-11.14	-11.12	-11.88	-10.77
16.50	-18.64	-16.99	-18.67	-22.46	-11.27	-12.82	-12.81	-13.92	-12.65
17.00	-23.22	-16.03	-18.37	-13.04	-18.16	-12.70	-12.72	-11.58	-12.19
17.50	-23.38	-16.60	-18.84	-12.18	-19.24	-9.65	-9.64	-8.30	-8.54
18.00	-20.45	-17.66	-17.13	-11.88	-14.98	-7.30	-7.29	-6.65	-6.52
18.50	-22.68	-26.21	-11.73	-17.77	-14.99	-6.41	-6.41	-6.27	-5.94
19.00	-17.43	-14.62	-9.19	-18.42	-21.84	-6.53	-6.53	-6.20	-6.10
19.50	-23.90	-13.00	-9.28	-12.30	-12.27	-6.65	-6.66	-6.41	-6.60
20.00	-11.51	-11.03	-8.61	-11.85	-11.63	-7.22	-7.22	-6.63	-7.27

## Typical Performance Data

Test Conditions: @ Temperature = -10°C, Pin = 5 dBm.

Freq. (GHz)	Isolation, Active states (dB)				Isolation, Disconnected states (dB)			
	COM-J1	COM-J2	J2-J3	J3-J4	COM-J1	COM-J2	COM-J3	COM-J4
0.10	-97.05	-93.99	-96.27	-97.01	-99.19	-105.27	-89.74	-93.49
0.50	-93.64	-93.68	-92.64	-81.89	-98.22	-96.87	-93.84	-92.42
1.00	-94.57	-91.10	-86.89	-82.04	-92.82	-94.65	-99.29	-89.66
1.50	-88.05	-93.65	-87.40	-101.87	-88.95	-90.76	-94.35	-97.48
2.00	-103.17	-95.38	-89.91	-81.69	-96.13	-98.10	-89.05	-90.37
2.50	-78.81	-75.49	-73.63	-77.07	-89.75	-90.71	-91.08	-99.91
3.00	-80.94	-82.40	-81.62	-77.78	-89.61	-88.73	-106.15	-88.24
3.50	-77.12	-71.40	-69.74	-78.37	-82.85	-94.77	-87.44	-81.70
4.00	-77.24	-72.90	-71.21	-64.88	-91.41	-103.73	-91.25	-87.76
4.50	-88.79	-68.15	-64.98	-57.73	-98.11	-83.78	-86.33	-89.74
5.00	-82.59	-83.28	-70.64	-63.93	-93.80	-86.71	-87.11	-93.71
5.50	-78.73	-67.16	-62.25	-63.99	-83.89	-86.02	-88.30	-88.15
6.00	-72.48	-71.38	-70.40	-65.50	-83.76	-108.92	-96.40	-84.50
6.50	-68.00	-69.46	-67.09	-61.56	-77.36	-97.96	-92.66	-80.47
7.00	-67.87	-71.90	-71.20	-58.78	-77.51	-111.17	-96.28	-72.19
7.50	-94.41	-70.50	-65.21	-63.54	-81.49	-90.55	-93.14	-80.03
8.00	-79.17	-70.54	-68.95	-60.80	-92.81	-84.28	-91.45	-85.27
8.50	-85.60	-68.53	-63.81	-62.92	-84.50	-83.29	-98.14	-91.93
9.00	-69.88	-67.19	-65.13	-68.36	-80.81	-84.72	-109.72	-91.31
9.50	-77.08	-69.10	-65.64	-60.67	-78.95	-82.25	-89.51	-85.28
10.00	-66.65	-69.31	-78.66	-61.48	-71.22	-75.92	-82.91	-77.60
10.50	-72.59	-64.33	-66.96	-63.16	-72.88	-80.53	-80.07	-69.84
11.00	-73.07	-61.11	-59.45	-63.50	-79.28	-90.52	-84.28	-75.61
11.50	-77.03	-63.77	-62.71	-64.42	-78.72	-82.90	-84.35	-81.51
12.00	-74.68	-78.16	-73.24	-66.29	-80.54	-82.47	-81.31	-81.86
12.50	-74.54	-66.00	-71.48	-58.62	-76.29	-80.63	-88.61	-92.37
13.00	-66.62	-61.50	-61.76	-52.58	-70.60	-82.94	-78.74	-81.37
13.50	-68.39	-64.67	-70.64	-62.79	-71.51	-78.61	-81.40	-76.48
14.00	-68.78	-79.59	-71.61	-65.31	-79.18	-82.59	-83.70	-71.60
14.50	-69.04	-71.36	-68.87	-60.53	-80.41	-80.45	-92.18	-80.63
15.00	-67.64	-64.35	-66.82	-57.04	-78.56	-84.61	-84.18	-89.20
15.50	-78.74	-67.32	-64.57	-57.77	-80.46	-86.96	-75.91	-80.89
16.00	-67.39	-77.51	-72.25	-53.54	-68.91	-81.07	-76.19	-82.19
16.50	-62.85	-71.25	-72.15	-52.47	-62.87	-86.69	-79.08	-75.01
17.00	-75.66	-79.01	-73.55	-57.57	-71.79	-85.85	-86.96	-70.72
17.50	-69.99	-79.08	-79.97	-63.85	-78.44	-88.49	-84.19	-79.70
18.00	-70.49	-72.30	-69.38	-60.57	-76.73	-87.00	-84.94	-81.98
18.50	-78.42	-74.74	-74.16	-62.40	-74.89	-81.48	-80.29	-82.77
19.00	-70.26	-66.27	-71.13	-74.28	-77.82	-84.22	-80.71	-73.54
19.50	-60.96	-68.46	-71.71	-72.42	-66.76	-74.69	-76.14	-81.22
20.00	-66.30	-69.26	-70.04	-76.73	-68.72	-74.72	-73.21	-72.74

**Typical Performance Data**

Test Conditions: @ Temperature = +25°C, Pin = 5 dBm.

Freq. (GHz)	Insertion Loss (dB)			
	COM-J1	COM-J2	COM-J3	COM-J4
0.10	-2.58	-2.58	-2.58	-2.60
0.50	-1.61	-1.59	-1.59	-1.61
1.00	-1.64	-1.62	-1.61	-1.64
1.50	-1.70	-1.70	-1.68	-1.69
2.00	-1.78	-1.79	-1.77	-1.76
2.50	-1.88	-1.90	-1.88	-1.86
3.00	-1.97	-1.99	-1.96	-1.94
3.50	-1.91	-1.86	-1.87	-1.89
4.00	-1.99	-1.91	-1.88	-1.98
4.50	-2.14	-2.00	-1.94	-2.11
5.00	-2.18	-2.17	-2.08	-2.15
5.50	-2.38	-2.56	-2.56	-2.28
6.00	-2.38	-2.49	-2.48	-2.42
6.50	-2.48	-2.33	-2.39	-2.50
7.00	-2.59	-2.29	-2.36	-2.68
7.50	-2.51	-2.35	-2.35	-2.62
8.00	-2.46	-2.54	-2.46	-2.45
8.50	-2.66	-2.69	-2.58	-2.53
9.00	-2.83	-2.74	-2.70	-2.74
9.50	-2.78	-2.63	-2.70	-2.85
10.00	-2.79	-2.68	-2.72	-2.87
10.50	-3.05	-3.05	-2.99	-3.15
11.00	-2.78	-2.76	-2.72	-2.81
11.50	-2.85	-2.78	-2.74	-2.82
12.00	-3.07	-2.95	-2.83	-2.99
12.50	-3.31	-3.12	-3.10	-3.16
13.00	-3.25	-3.28	-3.42	-3.28
13.50	-3.12	-3.38	-3.78	-3.20
14.00	-3.32	-3.44	-3.93	-3.13
14.50	-4.08	-3.95	-4.22	-3.67
15.00	-4.10	-3.79	-3.64	-4.01
15.50	-3.90	-3.65	-3.31	-4.12
16.00	-3.69	-3.49	-3.18	-4.09
16.50	-3.48	-3.61	-3.32	-3.88
17.00	-3.79	-4.03	-3.85	-3.79
17.50	-3.66	-3.80	-3.68	-3.51
18.00	-3.79	-3.99	-3.79	-3.69
18.50	-3.90	-4.40	-3.77	-3.88
19.00	-4.24	-4.86	-3.98	-3.95
19.50	-4.84	-5.35	-4.66	-4.61
20.00	-5.36	-5.50	-4.94	-5.07

**SP4T Solid-State Switch****TTL-1SP4T-183****Typical Performance Data**

Test Conditions: @ Temperature = +25°C, Pin = 5 dBm.

Freq. (GHz)	Return Loss, Active ports (dB)					R. Loss, Internally terminated ports (dB)			
	COM	J1	J2	J3	J4	J1	J2	J3	J4
	-10.98	-8.46	-8.42	-8.47	-8.39	-29.13	-29.13	-29.20	-29.07
0.50	-22.51	-17.72	-18.32	-18.22	-17.59	-28.97	-28.97	-29.03	-29.55
1.00	-30.73	-20.83	-21.10	-20.40	-20.92	-26.70	-26.70	-27.72	-26.46
1.50	-27.12	-25.68	-22.46	-22.32	-25.63	-24.14	-24.14	-24.58	-24.26
2.00	-19.35	-28.37	-24.27	-23.37	-30.02	-22.08	-22.08	-23.18	-22.20
2.50	-16.65	-27.26	-23.13	-22.98	-28.19	-20.03	-20.03	-20.50	-20.61
3.00	-16.83	-24.70	-22.31	-23.11	-25.16	-18.29	-18.29	-18.48	-18.76
3.50	-20.78	-19.67	-23.07	-24.42	-19.67	-16.68	-16.68	-16.56	-17.30
4.00	-27.00	-17.78	-21.79	-25.43	-17.92	-15.43	-15.43	-15.17	-16.30
4.50	-19.50	-16.53	-18.50	-20.70	-16.33	-14.40	-14.40	-14.26	-15.16
5.00	-16.44	-18.14	-14.17	-14.87	-17.30	-13.41	-13.41	-13.07	-14.35
5.50	-16.39	-17.07	-12.08	-11.70	-17.66	-12.88	-12.88	-12.81	-14.02
6.00	-19.65	-16.64	-14.76	-13.29	-17.78	-12.71	-12.71	-12.50	-13.92
6.50	-16.90	-12.11	-16.01	-12.67	-11.67	-12.79	-12.79	-12.81	-13.97
7.00	-17.33	-12.25	-18.59	-14.24	-10.75	-13.49	-13.49	-13.36	-14.73
7.50	-22.22	-15.55	-15.28	-15.34	-12.45	-14.78	-14.78	-14.66	-16.14
8.00	-17.31	-16.59	-12.76	-14.06	-16.00	-16.89	-16.89	-17.25	-18.26
8.50	-12.55	-12.93	-12.05	-12.42	-14.62	-21.41	-21.41	-21.61	-22.41
9.00	-12.14	-12.13	-13.86	-12.32	-12.19	-36.51	-36.50	-29.42	-27.88
9.50	-15.18	-14.19	-16.66	-13.66	-12.32	-23.83	-23.83	-21.97	-21.04
10.00	-22.65	-21.21	-24.07	-16.32	-14.82	-17.09	-17.09	-17.01	-16.11
10.50	-25.63	-21.48	-18.42	-18.45	-21.85	-13.81	-13.81	-13.96	-13.21
11.00	-18.20	-21.80	-22.19	-19.62	-25.55	-11.84	-11.84	-12.75	-11.60
11.50	-15.62	-35.45	-25.82	-21.64	-35.61	-11.12	-11.12	-12.11	-10.81
12.00	-12.26	-19.00	-24.45	-30.50	-26.74	-10.99	-10.99	-13.79	-10.87
12.50	-10.31	-13.94	-17.49	-19.91	-16.72	-11.64	-11.65	-14.32	-11.77
13.00	-11.26	-14.43	-15.22	-13.29	-13.84	-12.81	-12.81	-15.63	-12.95
13.50	-17.09	-22.84	-14.41	-10.37	-15.89	-13.31	-13.31	-14.86	-14.16
14.00	-16.85	-19.58	-15.92	-9.98	-31.61	-13.25	-13.25	-12.94	-13.83
14.50	-11.91	-13.83	-14.12	-10.77	-17.66	-12.39	-12.39	-12.88	-12.81
15.00	-10.61	-14.36	-14.22	-14.48	-14.82	-11.52	-11.52	-11.39	-11.96
15.50	-10.44	-12.64	-18.27	-16.65	-11.55	-11.86	-11.86	-12.48	-11.75
16.00	-11.72	-13.21	-24.09	-25.59	-10.52	-12.32	-12.32	-12.67	-12.01
16.50	-16.40	-18.55	-20.04	-21.79	-12.02	-12.72	-12.71	-13.70	-12.13
17.00	-29.34	-19.87	-21.49	-14.16	-20.90	-11.68	-11.67	-11.88	-11.05
17.50	-21.69	-17.23	-25.62	-12.85	-23.60	-9.96	-9.96	-9.89	-9.02
18.00	-22.09	-20.57	-18.03	-14.00	-16.95	-8.28	-8.28	-7.74	-7.49
18.50	-27.55	-29.07	-12.98	-19.86	-17.64	-7.23	-7.23	-7.34	-6.73
19.00	-24.95	-16.79	-9.64	-20.69	-19.71	-6.68	-6.68	-6.47	-6.35
19.50	-18.35	-12.07	-9.61	-12.74	-12.48	-6.30	-6.29	-7.33	-6.40
20.00	-12.16	-9.39	-8.04	-10.12	-9.66	-6.98	-6.98	-7.53	-7.05

USB / Ethernet

# SP4T Solid-State Switch

**TTL-1SP4T-183**

## Typical Performance Data

Test Conditions: @ Temperature = +25°C, Pin = 5 dBm.

Freq. (GHz)	Isolation, Active states (dB)				Isolation, Disconnected states (dB)			
	COM-J1	COM-J2	J2-J3	J3-J4	COM-J1	COM-J2	COM-J3	COM-J4
0.10	-90.75	-94.77	-96.48	-98.57	-100.84	-102.76	-91.52	-97.73
0.50	-93.51	-93.25	-96.30	-89.31	-88.51	-95.96	-92.20	-94.00
1.00	-85.04	-96.80	-93.01	-81.38	-93.11	-95.12	-98.90	-93.46
1.50	-83.23	-94.53	-85.76	-89.15	-86.84	-92.64	-95.16	-97.12
2.00	-89.43	-94.51	-90.50	-83.19	-99.94	-103.89	-98.88	-88.90
2.50	-78.35	-77.98	-75.58	-77.07	-91.54	-93.33	-96.21	-94.49
3.00	-78.94	-83.77	-84.44	-77.87	-85.89	-87.24	-95.91	-85.97
3.50	-78.50	-73.01	-70.58	-76.72	-85.87	-100.41	-92.67	-80.37
4.00	-78.68	-72.74	-71.09	-64.75	-85.91	-89.16	-105.22	-86.02
4.50	-96.77	-69.80	-65.73	-58.15	-88.71	-103.81	-93.37	-95.09
5.00	-82.42	-81.43	-71.66	-64.39	-88.24	-89.90	-94.31	-86.00
5.50	-78.46	-66.56	-62.61	-64.18	-97.38	-84.67	-97.46	-84.04
6.00	-74.75	-72.83	-70.88	-64.60	-84.49	-90.75	-92.79	-83.83
6.50	-68.77	-72.99	-68.67	-62.16	-75.86	-93.50	-91.29	-79.51
7.00	-68.20	-71.51	-71.02	-59.61	-76.34	-92.02	-95.34	-72.13
7.50	-85.15	-71.62	-66.94	-64.07	-80.06	-94.62	-89.19	-81.29
8.00	-78.54	-72.12	-70.43	-61.68	-90.84	-92.48	-96.19	-88.39
8.50	-78.32	-70.00	-65.62	-64.44	-84.42	-83.62	-94.69	-82.31
9.00	-70.09	-67.54	-65.97	-67.82	-80.23	-89.84	-103.02	-92.73
9.50	-80.66	-72.69	-67.39	-60.92	-82.56	-81.72	-84.45	-81.54
10.00	-65.18	-69.65	-79.24	-62.14	-70.98	-80.91	-85.06	-77.09
10.50	-72.02	-64.84	-67.59	-64.64	-75.62	-85.40	-77.44	-68.80
11.00	-75.07	-63.89	-60.74	-63.48	-80.39	-92.80	-81.03	-75.96
11.50	-78.85	-66.40	-65.87	-66.26	-80.47	-88.48	-88.46	-80.20
12.00	-73.82	-73.92	-75.43	-67.43	-78.23	-88.01	-88.60	-82.73
12.50	-73.56	-66.86	-68.71	-58.37	-75.83	-79.70	-83.11	-91.73
13.00	-68.83	-62.60	-63.31	-54.43	-71.64	-84.68	-80.41	-85.14
13.50	-68.86	-67.09	-72.79	-65.04	-70.54	-89.39	-85.56	-82.47
14.00	-67.76	-79.69	-74.31	-65.50	-76.99	-82.58	-82.13	-74.53
14.50	-73.11	-68.94	-71.87	-61.66	-90.26	-78.24	-92.43	-77.57
15.00	-68.67	-65.79	-66.12	-57.87	-90.38	-92.39	-88.26	-87.80
15.50	-78.47	-70.11	-67.13	-58.45	-77.62	-85.80	-79.81	-80.09
16.00	-65.73	-73.68	-75.31	-54.44	-68.03	-81.04	-77.12	-83.34
16.50	-63.28	-73.34	-74.87	-53.59	-64.49	-89.32	-87.04	-75.16
17.00	-75.87	-85.91	-78.44	-60.32	-74.76	-87.58	-79.52	-72.99
17.50	-70.75	-82.43	-83.09	-64.94	-76.45	-92.09	-82.47	-84.85
18.00	-73.03	-71.59	-70.21	-60.76	-75.49	-83.68	-92.80	-78.10
18.50	-78.62	-77.43	-86.06	-63.81	-76.65	-82.70	-84.79	-81.47
19.00	-68.70	-67.59	-71.45	-81.92	-78.53	-79.56	-98.44	-73.24
19.50	-62.16	-69.00	-72.99	-74.70	-66.58	-74.65	-78.07	-96.03
20.00	-69.76	-69.90	-72.88	-80.41	-71.42	-82.72	-74.77	-70.77

**Typical Performance Data**

Test Conditions: @ Temperature = +60°C, Pin = 5 dBm.

Freq. (GHz)	Insertion Loss (dB)			
	COM-J1	COM-J2	COM-J3	COM-J4
0.10	-2.64	-2.64	-2.64	-2.66
0.50	-1.66	-1.63	-1.63	-1.66
1.00	-1.71	-1.67	-1.67	-1.71
1.50	-1.77	-1.77	-1.77	-1.78
2.00	-1.85	-1.86	-1.86	-1.85
2.50	-1.94	-1.95	-1.96	-1.94
3.00	-2.01	-2.01	-2.01	-2.00
3.50	-1.97	-1.89	-1.93	-1.96
4.00	-2.07	-1.96	-1.95	-2.07
4.50	-2.22	-2.07	-2.03	-2.21
5.00	-2.26	-2.24	-2.19	-2.25
5.50	-2.47	-2.64	-2.68	-2.38
6.00	-2.41	-2.51	-2.54	-2.46
6.50	-2.52	-2.34	-2.45	-2.55
7.00	-2.64	-2.28	-2.42	-2.74
7.50	-2.55	-2.34	-2.41	-2.68
8.00	-2.48	-2.50	-2.49	-2.51
8.50	-2.64	-2.66	-2.58	-2.54
9.00	-2.84	-2.74	-2.73	-2.76
9.50	-2.87	-2.67	-2.78	-2.95
10.00	-2.90	-2.74	-2.85	-3.01
10.50	-3.14	-3.05	-3.09	-3.26
11.00	-2.93	-2.86	-2.89	-2.99
11.50	-3.00	-2.86	-2.94	-3.01
12.00	-3.15	-2.95	-2.96	-3.11
12.50	-3.46	-3.16	-3.23	-3.31
13.00	-3.51	-3.42	-3.65	-3.56
13.50	-3.33	-3.52	-4.16	-3.50
14.00	-3.59	-3.55	-4.27	-3.38
14.50	-4.28	-3.99	-4.35	-3.93
15.00	-4.26	-3.80	-3.78	-4.25
15.50	-4.06	-3.50	-3.48	-4.30
16.00	-3.83	-3.39	-3.37	-4.25
16.50	-3.65	-3.52	-3.54	-4.08
17.00	-3.97	-3.85	-4.10	-4.01
17.50	-3.86	-3.64	-3.92	-3.73
18.00	-4.03	-3.86	-3.98	-3.93
18.50	-4.14	-4.36	-4.00	-4.13
19.00	-4.48	-4.77	-4.24	-4.26
19.50	-5.18	-5.39	-4.91	-4.92
20.00	-5.90	-5.81	-5.41	-5.48

**NOTES:**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>.



## Typical Performance Data

Test Conditions: @ Temperature = +60°C, Pin = 5 dBm.

Freq. (GHz)	Return Loss, Active ports (dB)					R. Loss, Internally terminated ports (dB)			
	COM	J1	J2	J3	J4	J1	J2	J3	J4
	-11.07	-8.47	-8.43	-29.23	-8.44	-29.23	-29.24	-29.06	-29.17
0.50	-21.92	-17.39	-18.02	-28.43	-17.31	-28.43	-28.43	-28.35	-28.74
1.00	-30.43	-20.71	-20.60	-25.95	-20.73	-25.95	-25.95	-26.62	-26.11
1.50	-26.95	-25.32	-22.29	-23.78	-25.36	-23.78	-23.79	-24.58	-23.74
2.00	-19.28	-28.87	-23.47	-21.83	-30.59	-21.83	-21.83	-22.26	-21.89
2.50	-16.50	-28.00	-23.41	-19.86	-29.26	-19.86	-19.86	-20.41	-20.50
3.00	-16.73	-23.89	-23.66	-18.19	-24.27	-18.20	-18.19	-18.38	-18.78
3.50	-20.22	-19.18	-23.43	-16.64	-19.12	-16.63	-16.64	-16.64	-17.22
4.00	-26.82	-17.45	-21.21	-15.41	-17.58	-15.41	-15.41	-15.07	-16.21
4.50	-19.86	-16.34	-17.70	-14.37	-16.22	-14.37	-14.37	-13.98	-14.96
5.00	-16.01	-17.87	-13.80	-13.33	-16.99	-13.32	-13.33	-12.94	-14.12
5.50	-15.69	-16.69	-11.79	-12.78	-17.12	-12.78	-12.78	-12.57	-13.99
6.00	-18.82	-16.38	-14.35	-12.76	-17.47	-12.76	-12.76	-12.38	-14.03
6.50	-16.60	-11.95	-15.69	-12.88	-11.65	-12.88	-12.88	-12.71	-14.05
7.00	-17.27	-11.99	-18.48	-13.56	-10.74	-13.57	-13.56	-13.39	-14.63
7.50	-21.90	-15.18	-15.24	-14.85	-12.34	-14.85	-14.86	-14.72	-15.96
8.00	-16.94	-16.56	-12.74	-17.21	-15.71	-17.21	-17.21	-17.12	-18.35
8.50	-13.14	-13.36	-12.06	-22.76	-15.22	-22.77	-22.77	-22.35	-23.28
9.00	-12.30	-12.30	-13.12	-46.81	-12.44	-46.74	-46.85	-27.63	-26.96
9.50	-14.16	-14.26	-17.27	-22.67	-12.50	-22.66	-22.67	-21.58	-20.82
10.00	-19.67	-22.39	-26.62	-17.48	-15.33	-17.47	-17.47	-17.00	-16.80
10.50	-23.04	-21.26	-19.62	-14.60	-22.14	-14.60	-14.60	-14.63	-14.01
11.00	-17.21	-21.23	-21.27	-12.15	-22.76	-12.15	-12.15	-12.85	-11.94
11.50	-16.21	-33.48	-27.12	-10.97	-32.31	-10.97	-10.97	-12.16	-10.61
12.00	-13.10	-20.29	-26.96	-10.62	-29.28	-10.63	-10.62	-12.26	-10.16
12.50	-10.07	-13.60	-17.75	-11.22	-17.42	-11.22	-11.22	-13.91	-11.18
13.00	-10.17	-13.18	-13.67	-13.13	-12.91	-13.14	-13.13	-16.50	-13.53
13.50	-15.85	-23.08	-14.05	-14.45	-14.91	-14.45	-14.45	-15.68	-15.99
14.00	-14.26	-17.43	-15.81	-13.81	-45.13	-13.81	-13.81	-12.89	-14.16
14.50	-11.22	-14.16	-12.68	-12.29	-16.16	-12.29	-12.29	-11.36	-11.98
15.00	-10.91	-14.44	-13.91	-11.23	-15.02	-11.24	-11.24	-11.30	-11.40
15.50	-11.12	-12.19	-18.99	-12.29	-11.65	-12.29	-12.29	-12.29	-12.32
16.00	-12.34	-13.48	-27.68	-13.43	-10.55	-13.43	-13.43	-13.55	-13.52
16.50	-16.14	-19.57	-19.89	-13.28	-12.40	-13.28	-13.27	-13.46	-12.39
17.00	-25.91	-22.04	-19.79	-11.14	-23.20	-11.14	-11.14	-11.03	-10.29
17.50	-21.01	-17.97	-29.81	-9.99	-24.89	-9.99	-9.99	-9.26	-9.05
18.00	-19.72	-20.91	-18.62	-9.00	-18.12	-9.00	-8.99	-7.77	-8.30
18.50	-26.01	-31.56	-11.93	-7.95	-19.69	-7.95	-7.95	-6.68	-7.65
19.00	-37.91	-17.50	-9.78	-7.01	-19.08	-7.00	-7.01	-6.17	-6.75
19.50	-16.43	-12.00	-8.22	-6.05	-12.51	-6.05	-6.05	-6.16	-6.36
20.00	-10.36	-8.13	-6.94	-6.53	-8.88	-6.53	-6.53	-7.08	-6.60

## NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>.



## Typical Performance Data

Test Conditions: @ Temperature = +60°C, Pin = 5 dBm.

Freq. (GHz)	Isolation, Active states (dB)				Isolation, Disconnected states (dB)			
	COM-J1	COM-J2	J2-J3	J3-J4	COM-J1	COM-J2	COM-J3	COM-J4
0.10	-104.52	-90.25	-94.64	-97.34	-102.17	-92.88	-93.22	-88.43
0.50	-100.34	-96.82	-100.07	-84.68	-84.56	-105.59	-98.84	-97.92
1.00	-107.18	-91.01	-90.34	-84.01	-90.85	-94.89	-99.83	-90.87
1.50	-97.19	-89.95	-93.85	-90.89	-92.27	-93.92	-106.13	-93.38
2.00	-90.22	-87.95	-84.10	-87.58	-89.81	-105.05	-88.40	-92.09
2.50	-79.86	-78.13	-76.64	-82.22	-89.46	-92.16	-91.21	-91.28
3.00	-78.12	-81.10	-82.60	-77.40	-89.92	-88.44	-91.63	-87.99
3.50	-79.65	-74.58	-71.44	-77.50	-81.06	-89.80	-91.15	-78.61
4.00	-80.48	-72.06	-71.03	-65.03	-85.30	-92.27	-91.90	-85.26
4.50	-84.03	-71.63	-67.82	-58.94	-90.15	-91.58	-89.23	-83.96
5.00	-78.63	-82.12	-71.90	-65.74	-86.21	-88.29	-86.93	-85.76
5.50	-77.85	-67.09	-63.54	-64.09	-92.51	-118.71	-93.10	-87.60
6.00	-76.36	-72.19	-69.44	-63.50	-82.23	-105.61	-91.61	-89.18
6.50	-69.47	-75.44	-72.08	-62.15	-76.97	-92.80	-109.94	-80.19
7.00	-70.89	-73.15	-71.10	-60.39	-75.80	-88.97	-93.94	-73.34
7.50	-83.38	-73.48	-69.14	-65.20	-77.13	-97.71	-94.41	-81.92
8.00	-76.53	-71.09	-70.92	-62.87	-85.46	-93.78	-97.69	-86.21
8.50	-80.47	-71.69	-67.64	-65.40	-83.50	-86.33	-101.97	-82.44
9.00	-70.13	-68.31	-66.35	-67.63	-80.81	-86.95	-85.94	-88.63
9.50	-79.55	-73.41	-70.32	-62.25	-78.10	-79.61	-97.34	-82.33
10.00	-64.28	-70.42	-81.37	-62.79	-69.60	-81.65	-81.43	-77.48
10.50	-72.25	-64.57	-66.96	-65.03	-73.79	-84.15	-77.69	-68.93
11.00	-78.50	-67.07	-62.53	-64.62	-76.55	-82.36	-81.69	-75.76
11.50	-78.43	-68.80	-70.12	-67.49	-79.03	-94.80	-81.46	-78.66
12.00	-76.37	-72.17	-74.92	-68.05	-78.72	-81.16	-83.66	-86.40
12.50	-72.68	-67.37	-67.70	-57.66	-76.03	-84.32	-91.54	-83.44
13.00	-71.38	-64.67	-66.20	-57.17	-70.80	-92.01	-86.81	-89.31
13.50	-69.02	-69.94	-83.17	-68.20	-71.54	-84.88	-88.33	-77.13
14.00	-68.76	-78.69	-76.27	-65.81	-79.27	-80.02	-87.80	-74.58
14.50	-78.97	-66.15	-74.74	-62.54	-78.77	-80.18	-103.43	-83.65
15.00	-71.71	-66.68	-67.31	-59.72	-84.86	-88.34	-89.53	-83.11
15.50	-75.52	-73.04	-69.44	-58.80	-75.80	-85.79	-76.62	-83.11
16.00	-65.16	-79.15	-77.32	-55.37	-68.06	-83.77	-77.14	-85.74
16.50	-65.22	-82.85	-77.55	-55.10	-65.28	-83.65	-92.33	-75.05
17.00	-70.49	-84.06	-78.43	-62.68	-74.05	-88.24	-84.79	-74.49
17.50	-71.16	-88.32	-77.75	-64.86	-78.75	-85.69	-104.03	-85.96
18.00	-81.72	-73.73	-72.83	-62.06	-74.00	-84.67	-85.57	-85.56
18.50	-79.00	-73.72	-93.80	-66.07	-75.50	-85.06	-84.63	-77.98
19.00	-67.85	-67.98	-71.46	-82.76	-73.12	-77.73	-91.67	-72.96
19.50	-63.06	-68.62	-71.86	-75.73	-66.85	-74.24	-78.87	-90.51
20.00	-70.92	-70.11	-72.47	-79.33	-72.70	-86.13	-81.31	-70.69

## NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>.






# SP4T Solid-State Switch

TTL-1SP4T-183

## Typical Performance Graphs

Test Conditions: @ Temperature = -10°C, Pin = 5 dBm.





USB / Ethernet

# SP4T Solid-State Switch

TTL-1SP4T-183

## Typical Performance Graphs

Test Conditions: @ Temperature = -10°C, Pin = 5 dBm.






# SP4T Solid-State Switch

**TTL-1SP4T-183**

## Typical Performance Graphs

Test Conditions: @ Temperature = +25°C, Pin = 5 dBm.





USB / Ethernet

# SP4T Solid-State Switch

TTL-1SP4T-183

## Typical Performance Graphs

Test Conditions: @ Temperature = +25°C, Pin = 5 dBm.





# SP4T Solid-State Switch

TTL-1SP4T-183

## Typical Performance Graphs

Test Conditions: @ Temperature = +60°C, Pin = 5 dBm.



### NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>.




# SP4T Solid-State Switch

**TTL-1SP4T-183**


## Typical Performance Graphs

Test Conditions: @ Temperature = +60°C, Pin = 5 dBm.

Return Loss, Active ports



Return Loss, Terminated ports



**NOTES:**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>




# Case Style

RB

## Outline Dimensions

RB3522



### NOTES:

1. Case material: Aluminum alloy.
2. Case Finish: Nickel Plate.
3. Dimensions: Inches [mm]
4. Weight: 300 grams
5. Marking may contain other features or characters for internal lot control.

 Mini-Circuits®

[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)

Environmental Specifications **ENV55T2**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-10° to 60° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 85° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3