

Solid state

USB / LVTTTL RF SP16T Switch USB-1SP16T-83H

50Ω 1 to 8000 MHz

The Big Deal

- Very high isolation, 90 dB typ
- High speed switch transition, 5 μs typ
- High power handling, +30 dBm max
- Daisy-chain control of up to 35 modules



Typical Applications

- Cellular handset / BTS testing
- High volume production testing / ATE
- Design verification testing
- RF signal routing / switch matrices

Model No.	Description	Qty.
USB-1SP16T-83H	Switch Matrix	1

Included Accessories

MUSB-CBL-3+	2.6 ft USB cable	1
-------------	------------------	---

RoHS Compliant

See our web site for RoHS Compliance methodologies and qualifications

Product Overview

Mini-Circuits' USB-1SP16T-83H is a high isolation (90 dB typical), absorptive SP16T switch with USB and LVTTTL control. The fast switching, solid state switch operates from 1 MHz to 8000 MHz with 5 μs typical switch transition speed and high linearity (+50 dBm typ IP3) which allow the model to be used for a wide variety of RF applications.

Full software support is provided for USB control, including our user-friendly GUI application for Windows and a full API with programming instructions for Windows and Linux environments (both 32-bit and 64-bit systems). The latest version of the full software package can be downloaded from <https://www.minicircuits.com/softwaredownload/solidstate.html> at any time.

The USB-1SP16T-83H is housed in a low profile, rugged metal case (10.98" x 2.50" x 0.6") with 17 SMA (F) connectors (COM, and J1 to J16), a USB Mini-B port and a D-Sub 9 pin port for power and two data bus connectors for Master / Slave connections to other modules.

Key Features

Feature	Advantages
RF SP16T absorptive switch	Wideband (1 to 8000 MHz) with high isolation (90 dB typ.), and high power rating (+30 dBm through path) makes this switch suitable for a wide range of applications.
High Linearity (IP3 +50 dBm typ.)	Results in little or negligible inter-modulation generation, meeting requirements for digital communications signals
Internal DC Blocking capacitors at RF ports	No need for external DC blocking circuitry
Dynamic daisy-chain control	Simplify control software and interconnections by cascading up to 35 modules of multiple switch types into a Master / Slave chain with a single USB interface.
Full software support included	Mini-Circuits' full software package, programming and user manual are available for download from https://www.minicircuits.com/softwaredownload/solidstate.html at no extra cost.

Trademarks: Windows is a registered trademark of Microsoft Corporation in the United States and other countries. Linux is a registered trademark of Linus Torvalds. Pentium is a registered trademark of Intel Corporation. Neither Mini-Circuits nor the Mini-Circuits USB-1SP16T-83H are affiliated with or endorsed by the owners of the above referenced trademarks

Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation.

Rev. D
M177161
EDR-11610/1
USB-1SP16T-83H
RAV
201221
Page 1 of 11



Electrical Specifications @ 0 to 50°C

Parameter	Port	Conditions	Min.	Typ.	Max.	Units
Operating Frequency			1		8000	MHz
Insertion Loss	COM to any active port	1 to 3000 MHz	-	5.5	7.5	dB
		3000 to 7000 MHz	-	7.5	11.0	
		7000 to 8000 MHz	-	9.5	13.0	
Isolation	Between any ports J1 to J16	1 to 3000 MHz	63	90	-	dB
		3000 to 7000 MHz	67	88	-	
		7000 to 8000 MHz	60	78	-	
	COM to any terminated port @ disconnected state	1 to 3000 MHz	80	100	-	
		3000 to 7000 MHz	83	100	-	
		7000 to 8000 MHz	75	100	-	
	COM to any terminated port @ active states	1 to 3000 MHz	67	85	-	
		3000 to 7000 MHz	67	85	-	
		7000 to 8000 MHz	62	78	-	
VSWR	COM port @ active states	1 to 3000 MHz	-	1.25	-	:1
		3000 to 7000 MHz	-	1.45	-	
		7000 to 8000 MHz	-	1.50	-	
	Any port connected to COM @ active states	1 to 3000 MHz	-	1.25	-	
		3000 to 7000 MHz	-	1.40	-	
		7000 to 8000 MHz	-	1.35	-	
	Any terminated port (includes COM in disconnected state)	1 to 3000 MHz	-	1.25	-	
		3000 to 7000 MHz	-	1.20	-	
		7000 to 8000 MHz	-	1.30	-	
Power Input @ 1 dB Compression ¹	COM to any active port	10 to 8000 MHz	-	+31.5	-	dBm
IP3 ^{1,2}	COM to any active port	10 to 5000 MHz	-	+50	-	dBm
		5000 to 8000 MHz	-	+45	-	
Transition Time ⁴	-	-	-	5	9.5	µs
Minimum dwell time ⁵	High Speed Mode	-	-	15	-	µs
Switching Time (USB) ⁶	-	-	-	2	-	ms
Switching Time (LVTTTL) ⁷	-	-	-	12	-	µs
Supply voltage (Vcc)	USB or D-Sub port	-	4.75	5	5.25	V _{DC}
Supply Current (Icc) ⁸		-	-	60	90	mA
Current Pass-through ⁹		-	-	-	500	
Operating RF Input Power	Through path	Hot Switching		-	-	+20
		Cold switching	1 - 10 MHz	Derate Linearly from +30 dBm @ 10 MHz to +25 dBm @ 1 MHz		
			10 - 8000 MHz	-	-	+30
	Any terminated port	-	-	-	+25	dBm

¹ Compression and IP3 may degrade below 10 MHz.

² IP3 Tested with 1 MHz span between signals, +5 dBm per tone.

³ Switching time spec represents the time that the RF signal paths are interrupted during switching and thus is specified without communication delays.

⁴ Transition time spec represents the time that the RF signal paths are interrupted during switching and thus is specified without communication delays.

⁵ Minimum dwell time is the shortest time that can be achieved between 2 switch transitions when programming an automated switch sequence.

⁶ Switching time(USB) is the time from issuing a single software command via USB to the switch state changing. The most significant factor is the host PC, influenced by CPU load and USB protocol. The time shown is an estimate for a medium CPU load and USB 2.0 connection.

⁷ Switching time(LVTTTL) is the time from setting the control at the LVTTTL input to the desired logic state, to the RF signal at the specified output reaching 90% of the steady state.

⁸ Current consumption specified for a single unit without any slave modules.

⁹ Pass through current is the maximum current handling of a unit with slave modules attached. If controlling a large number of slave modules additional power supplies should be included to ensure this limit is not exceeded. See page 5 for details.

Control voltages for LVTTTL Control

Parameter		Min.	Typ.	Max.	Units
Control Input	Low	0	—	0.8	V
	High	2.0	—	3.3	

Connections

RF SP16T Switch (J1 to J16, COM)	(SMA female)
USB	(USB type Mini-B receptacle)
Serial In (Digital Control 2 port)	(Digital Snap Fit Connector)
Serial Out (Digital Control 1 port)	(Digital Snap Fit Connector)
LVTTTL control & power	(9 pin D-sub - Female)*

Absolute Maximum Ratings


Operating Temperature	0°C to 50°C	
Storage Temperature	-20°C to 60°C	
DC supply voltage max. (USB or D-Sub pin 1)	6V	
Voltage at LVTTTL control pins	3.6V	
RF power into termination	+26 dBm	
RF power @ Through path	1 to 10 MHz	Derate linearly from +31 dBm @ 10 MHz to +30 dBm @ 1 MHz
	10 to 8000 MHz	+31 dBm
DC voltage @ RF Ports	16V	

Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

*9 Pin D-Sub Pin Connections

PIN Number	Function
1	Vcc
2	GND
3	D0
4	D1
5	D2
6	D3
7	D4
8	Not Connected
9	Not Connected

Simplified Diagram



LVTTTL communication parameters

Parameter	Conditions		Min.	Typ.	Max.	Units
Voltage levels	Logic Low Voltage	Input	0	-	0.8	V
	Logic High Voltage	Input	2.0	-	3.3	

The USB-1SP16T-83H LVTTTL control interface consists of 5 unlatched parallel control bits that select the desired switch state, as shown in the truth table below. The parallel control does not have any latch and thus will respond immediately to any change.

Connecting the switch to USB control and establishing USB communication will disable the LVTTTL control until the switch is reset by disconnecting and then reconnecting power.

All LVTTTL controls are connected with internal pull-down resistors so the default state of the switch is disconnected state.

Power can be provided via either the D-Sub port or USB port, regardless of the control method used.

Switch state	Control Bits				
	D0	D1	D2	D3	D4
Disconnected	Logic Low	Logic Low	Logic Low	Logic Low	Logic Low
COM -> 1	Logic High	Logic Low	Logic Low	Logic Low	Logic Low
COM -> 2	Logic Low	Logic High	Logic Low	Logic Low	Logic Low
COM -> 3	Logic High	Logic High	Logic Low	Logic Low	Logic Low
COM -> 4	Logic Low	Logic Low	Logic High	Logic Low	Logic Low
COM -> 5	Logic High	Logic Low	Logic High	Logic Low	Logic Low
COM -> 6	Logic Low	Logic High	Logic High	Logic Low	Logic Low
COM -> 7	Logic High	Logic High	Logic High	Logic Low	Logic Low
COM -> 8	Logic Low	Logic Low	Logic Low	Logic High	Logic Low
COM -> 9	Logic High	Logic Low	Logic Low	Logic High	Logic Low
COM -> 10	Logic Low	Logic High	Logic Low	Logic High	Logic Low
COM -> 11	Logic High	Logic High	Logic Low	Logic High	Logic Low
COM -> 12	Logic Low	Logic Low	Logic High	Logic High	Logic Low
COM -> 13	Logic High	Logic Low	Logic High	Logic High	Logic Low
COM -> 14	Logic Low	Logic High	Logic High	Logic High	Logic Low
COM -> 15	Logic High	Logic High	Logic High	Logic High	Logic Low
COM -> 16	Logic Low	Logic Low	Logic Low	Logic Low	Logic High


All inactive ports will be internally terminated to 50 Ω.

In disconnected state, all ports including COM port will be terminated internally.

Note maximum input power to internal termination listed on page 2 & 3.

Connecting multiple modules (Daisy Chain)

The USB-1SP16T-83H is designed to connect up to 35 modules in series (Daisy chain) using dynamic addressing, meaning there is no need to specifically set the address of the modules, the addresses will be set automatically as part of establishing the communications with the PC. The module connected to the PC USB port will be assigned address 0 (Master), the first module connected to it will get address 1 (slave) and subsequent modules incrementing up to address 34 (slave).




Connections between modules will be made using the serial in/out ports with the module connected to the PC as a master and all others as slave modules. All control will be through the master module (address zero) which is the only one communicating with the PC. Serial control out port of each module should be connected to the serial control in port of the next module. Power will be supplied from the PC via the master module up to a maximum of 500mA.

If connecting USB-1SP16T-83H units in series, additional power supply will generally be needed every six to eight modules. If mixing modules of different types ensure the max current through any unit does not exceed 500mA. All power supplies should be connected to the module via the module's USB port, connecting an additional power supply will automatically cut off power draw from the serial control in port for that module.

The Serial master/slave bus allows connecting modules of different types to the same daisy chain as long as all support Mini-Circuits Dynamic addressing setup. To add a new module to the set up simply connect the module to the setup and refresh the address listing, no need to reset any of the existing modules or assign addresses manually.

Connecting slave units should be done only with control cables provided by Mini-Circuits

Outline Drawing (RB2574-2)




Outline Dimensions (Inch / mm)


A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAMS
10.98	2.50	0.60	0.69	0.640	0.278	0.10	10.780	1.500	0.50	0.106	5.49	0.73	2.25	650
278.9	63.5	15.2	17.5	16.26	7.06	2.54	273.81	38.10	12.7	2.69	139.45	18.5	57.15	

Typical Performance Curves


Insertion Loss over Temp.




Insertion Loss of outputs J1-J8 in switch




Insertion Loss of outputs J9-J16 in switch



VSWR of active ports J1- J8




VSWR of active ports J9- J16




Typical Performance Curves


VSWR Common Port (Active) over Temp.




VSWR Common Port (Terminated) over Temp.




VSWR Output (Terminated) over Temp.




VSWR Output (Active) over Temp.




Isolation COM to J2 with J1 active over Temp.




Isolation COM to J1 with J16 active over Temp.




Isolation COM to J8 with J7 active over Temp




Isolation J1 to J2 with J1 active over Temp




Isolation J7 to J8 with J7 active over Temp.



Isolation J1 to J16 with J1 active over Temp



Isolation COM to J1 @ Disconnected State over Temp.



Software & Documentation Download:

- Mini-Circuits' full software and support package including user guide, Windows GUI, DLL files, programming manual and examples can be downloaded free of charge from <https://www.minicircuits.com/softwaredownload/solidstate.html>
- Please contact testsolutions@minicircuits.com for support


Minimum System Requirements

Parameter	Requirements	
Interface	USB HID or LVTTTL or Daisy Chain Dynamic addressing	
System requirements	GUI	Windows 32 & 64 bit systems from Windows 98 up to Windows 10
	USB API (ActiveX & .Net)	Windows 32 & 64 bit systems with ActiveX or .Net support from Windows 98 up to Windows 10
	Daisy Chain Dynamic addressing	Additional unit of this model or another Mini-Circuits model supporting Dynamic addressing
	LVTTTL control	Any computer with a suitable I/O port
	USB direct programming support	Linux, Windows systems from Windows 98 up to Windows 10
Hardware	Pentium® II or higher, RAM 256 MB	

Graphical User Interface (GUI) for Windows

Key Features:

- Set each switch manually
- Set timed sequence of switching states
- Configure switch address and upgrade Firmware
- Controlling up to 35 modules in 'daisy chain' configuration



Application Programming Interface (API)

Programming Manual: https://www.minicircuits.com/softwaredownload/Prog_Manual-H_Series_Switches.pdf

Windows Support:


- API DLL files exposing the full switch functionality
 - ActiveX COM DLL file for creation of 32-bit programs
 - .Net library DLL file for creation of 32 / 64-bit programs
- Supported by most common programming environments (refer to application note [AN-49-001](#) for summary of tested environments)

Linux Support:

- Full switch control in a Linux environment is achieved by way of USB interrupt commands.

Ordering, Pricing & Availability Information see our web site

Model	Description
USB-1SP16T-83H	USB / LVTTTL RF SP16T Switch

Included Accessories	Part No.	Description
	MUSB-CBL-3+	2.6 ft (0.8 m) USB Cable: USB type A(Male) to USB type Mini-B(Male)

Optional Accessories	Description
MUSB-CBL-3+ (Spare)	2.6 ft (0.8 m) USB Cable: USB type A(Male) to USB type Mini-B(Male)
MUSB-CBL-7+	6.6 ft (2.0 m) USB Cable: USB type A(Male) to USB type Mini-B(Male)
D-SUB9-MF-6+	6 ft LVTTTL Cable: 9 pin D-sub(Male) to 9 pin D-sub(Female)
CBL-1.5FT-MMD+	1.5 ft cable assembly for serial control Daisy Chain with snap fit connectors
USB-AC/DC-5+	AC/DC +5V power adaptor with USB connector ^{10,11}

¹⁰ The USB-AC/DC-5 may be used to provide power via USB port when control is via LVTTTL, or to provide additional power if needing to connect a number of switches in series exceeding 500mA total current draw.

¹¹ Includes power plugs for US, UK, EU, IL, AU & China. Plugs for other countries are also available, if you need a power plug for a country not listed please contact testsolutions@minicircuits.com

Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J1	COM-J2	COM-J3	COM-J4	COM-J5	COM-J6	COM-J7	COM-J8
0.1	4.77	4.75	4.78	4.77	4.80	4.74	4.74	4.77
0.5	4.10	4.08	4.10	4.10	4.10	4.07	4.07	4.09
1	4.08	4.05	4.08	4.08	4.07	4.04	4.05	4.06
5	4.08	4.05	4.08	4.08	4.07	4.04	4.05	4.06
10	4.09	4.06	4.08	4.08	4.08	4.04	4.05	4.06
20	4.10	4.07	4.10	4.10	4.09	4.05	4.06	4.07
50	4.14	4.11	4.13	4.14	4.12	4.07	4.08	4.10
100	4.21	4.18	4.20	4.21	4.16	4.12	4.13	4.15
200	4.35	4.31	4.33	4.35	4.23	4.18	4.19	4.21
400	4.61	4.55	4.58	4.60	4.39	4.32	4.32	4.36
600	4.66	4.61	4.63	4.65	4.57	4.47	4.48	4.54
800	4.74	4.64	4.67	4.74	4.72	4.62	4.63	4.70
1000	5.02	4.89	4.92	5.02	4.81	4.71	4.72	4.79
1200	5.19	5.09	5.11	5.18	4.88	4.76	4.77	4.84
1400	5.27	5.11	5.14	5.27	4.96	4.80	4.79	4.91
1600	5.47	5.28	5.32	5.47	5.07	4.87	4.87	5.04
1800	5.69	5.56	5.59	5.68	5.20	5.00	5.00	5.17
2000	5.83	5.67	5.69	5.82	5.31	5.16	5.17	5.29
2200	5.92	5.73	5.77	5.92	5.42	5.30	5.31	5.40
2400	6.03	5.95	5.97	6.02	5.54	5.40	5.41	5.51
2600	6.21	6.10	6.12	6.20	5.63	5.48	5.49	5.59
2800	6.30	6.20	6.23	6.29	5.69	5.56	5.57	5.64
3000	6.40	6.35	6.37	6.39	5.76	5.65	5.66	5.72
3200	6.57	6.43	6.45	6.57	5.90	5.72	5.73	5.87
3400	6.64	6.52	6.54	6.64	6.03	5.77	5.78	6.00
3600	6.85	6.56	6.59	6.85	6.05	5.83	5.84	6.01
3800	6.95	6.61	6.64	6.95	6.04	5.89	5.90	6.01
4000	6.97	6.71	6.75	6.97	6.16	5.89	5.90	6.15
4200	7.17	6.62	6.68	7.17	6.31	5.81	5.82	6.31
4400	7.17	6.75	6.79	7.18	6.33	5.79	5.80	6.33
4600	7.25	7.00	7.03	7.26	6.30	5.97	5.97	6.29
4800	7.28	6.84	6.91	7.29	6.46	6.25	6.26	6.41
5000	7.37	7.13	7.13	7.38	6.69	6.39	6.39	6.65
5200	7.91	7.62	7.62	7.94	6.67	6.30	6.30	6.66
5400	7.85	7.50	7.53	7.88	6.55	6.23	6.24	6.54
5600	8.07	7.80	7.78	8.11	6.84	6.50	6.52	6.77
5800	8.82	8.36	8.40	8.88	7.42	6.94	6.99	7.33
6000	8.71	8.28	8.33	8.72	7.71	7.19	7.24	7.66
6200	8.68	8.30	8.33	8.71	7.60	7.16	7.18	7.58
6400	8.93	8.55	8.63	8.93	7.45	7.02	7.06	7.40
6600	8.82	8.49	8.53	8.79	7.41	7.03	7.07	7.37
6800	8.71	8.44	8.44	8.72	7.36	7.09	7.10	7.36
7000	8.76	8.50	8.48	8.77	7.44	7.09	7.08	7.42
7200	8.91	8.61	8.58	8.92	7.67	7.14	7.16	7.63
7400	9.14	8.84	8.78	9.16	7.74	7.28	7.33	7.70
7600	9.91	9.33	9.17	9.97	7.83	7.45	7.49	7.78
7800	10.12	9.67	9.58	10.12	8.41	7.74	7.77	8.34
8000	10.22	9.90	9.73	10.26	9.16	8.25	8.30	9.11
8200	11.09	10.52	10.33	11.08	9.60	8.74	8.82	9.56
8400	11.50	10.93	10.86	11.35	9.75	9.00	9.11	9.65
8500	11.42	10.95	10.86	11.28	9.75	9.03	9.15	9.64

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J9	COM-J10	COM-J11	COM-J12	COM-J13	COM-J14	COM-J15	COM-J16
0.1	4.80	4.79	4.82	4.80	4.76	4.83	4.78	4.77
0.5	4.12	4.11	4.16	4.14	4.08	4.17	4.10	4.11
1	4.09	4.08	4.13	4.11	4.06	4.14	4.07	4.09
5	4.09	4.08	4.13	4.11	4.06	4.15	4.07	4.09
10	4.10	4.09	4.14	4.11	4.06	4.15	4.08	4.09
20	4.11	4.10	4.14	4.12	4.08	4.16	4.09	4.10
50	4.13	4.12	4.17	4.15	4.11	4.20	4.13	4.14
100	4.18	4.17	4.21	4.20	4.19	4.28	4.19	4.21
200	4.25	4.23	4.28	4.28	4.32	4.41	4.32	4.35
400	4.41	4.37	4.42	4.43	4.56	4.64	4.55	4.59
600	4.58	4.52	4.58	4.61	4.60	4.68	4.59	4.63
800	4.73	4.67	4.73	4.76	4.70	4.75	4.65	4.73
1000	4.83	4.76	4.82	4.85	4.99	5.03	4.93	5.04
1200	4.89	4.81	4.86	4.91	5.17	5.23	5.14	5.21
1400	4.96	4.84	4.88	4.98	5.22	5.23	5.13	5.26
1600	5.07	4.90	4.95	5.08	5.40	5.36	5.26	5.44
1800	5.21	5.03	5.08	5.22	5.61	5.63	5.54	5.65
2000	5.33	5.19	5.26	5.35	5.75	5.75	5.65	5.79
2200	5.43	5.34	5.42	5.46	5.86	5.83	5.73	5.90
2400	5.54	5.45	5.52	5.57	5.96	6.06	5.96	6.01
2600	5.62	5.52	5.59	5.65	6.14	6.21	6.11	6.19
2800	5.68	5.61	5.68	5.71	6.24	6.31	6.22	6.29
3000	5.78	5.71	5.77	5.81	6.35	6.45	6.35	6.39
3200	5.95	5.78	5.83	5.98	6.53	6.55	6.45	6.57
3400	6.08	5.82	5.87	6.12	6.62	6.63	6.54	6.66
3600	6.09	5.87	5.93	6.13	6.86	6.68	6.60	6.90
3800	6.08	5.92	5.98	6.12	6.97	6.78	6.69	7.02
4000	6.20	5.93	5.95	6.23	6.98	6.88	6.80	7.01
4200	6.35	5.87	5.87	6.38	7.18	6.77	6.72	7.22
4400	6.37	5.86	5.87	6.42	7.21	6.91	6.84	7.25
4600	6.36	6.02	6.08	6.42	7.29	7.15	7.09	7.32
4800	6.51	6.28	6.37	6.56	7.33	6.99	6.96	7.36
5000	6.70	6.42	6.46	6.75	7.43	7.34	7.23	7.48
5200	6.67	6.34	6.34	6.73	8.01	7.86	7.77	8.07
5400	6.57	6.27	6.31	6.64	7.96	7.71	7.66	8.01
5600	6.87	6.51	6.65	6.95	8.11	7.99	7.87	8.15
5800	7.46	6.96	7.13	7.50	8.86	8.52	8.45	8.87
6000	7.75	7.26	7.34	7.79	8.77	8.44	8.41	8.79
6200	7.65	7.25	7.26	7.71	8.78	8.51	8.45	8.77
6400	7.49	7.09	7.14	7.55	9.00	8.71	8.71	9.01
6600	7.43	7.09	7.14	7.50	8.90	8.65	8.63	8.94
6800	7.39	7.16	7.13	7.51	8.83	8.63	8.59	8.88
7000	7.51	7.19	7.13	7.65	8.89	8.69	8.63	8.94
7200	7.76	7.25	7.25	7.87	9.04	8.81	8.75	9.07
7400	7.80	7.39	7.40	7.92	9.25	9.01	8.92	9.27
7600	7.85	7.55	7.50	7.99	9.96	9.44	9.30	9.97
7800	8.39	7.81	7.73	8.49	10.14	9.78	9.70	10.17
8000	9.08	8.26	8.23	9.17	10.33	10.03	9.88	10.36
8200	9.50	8.76	8.78	9.65	11.17	10.63	10.46	11.17
8400	9.67	9.05	9.08	9.84	11.54	11.03	10.93	11.49
8500	9.69	9.10	9.13	9.87	11.49	11.06	10.95	11.44

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	2.03	2.01	2.00	2.02	2.01	2.04	2.01	2.01	2.02
0.5	1.30	1.30	1.29	1.30	1.29	1.30	1.29	1.29	1.29
1	1.26	1.26	1.25	1.26	1.26	1.26	1.25	1.25	1.25
5	1.24	1.24	1.24	1.24	1.24	1.24	1.24	1.24	1.24
10	1.24	1.25	1.24	1.24	1.24	1.24	1.24	1.24	1.24
20	1.24	1.25	1.24	1.25	1.25	1.25	1.24	1.24	1.24
50	1.25	1.25	1.24	1.25	1.25	1.25	1.24	1.25	1.25
100	1.25	1.25	1.24	1.25	1.25	1.26	1.26	1.25	1.26
200	1.19	1.20	1.20	1.20	1.20	1.26	1.25	1.25	1.25
400	1.02	1.03	1.04	1.04	1.04	1.25	1.23	1.23	1.23
600	1.20	1.17	1.16	1.16	1.16	1.18	1.18	1.18	1.17
800	1.29	1.28	1.29	1.30	1.28	1.07	1.10	1.09	1.08
1000	1.18	1.14	1.19	1.20	1.16	1.05	1.02	1.02	1.03
1200	1.10	1.06	1.05	1.06	1.04	1.15	1.15	1.14	1.12
1400	1.21	1.14	1.25	1.26	1.16	1.17	1.26	1.24	1.16
1600	1.17	1.20	1.23	1.24	1.20	1.15	1.29	1.27	1.17
1800	1.05	1.23	1.08	1.07	1.21	1.20	1.24	1.23	1.21
2000	1.04	1.08	1.09	1.09	1.08	1.27	1.14	1.14	1.26
2200	1.07	1.22	1.09	1.11	1.22	1.26	1.06	1.08	1.25
2400	1.01	1.31	1.15	1.12	1.31	1.19	1.06	1.06	1.19
2600	1.18	1.18	1.14	1.11	1.19	1.17	1.05	1.04	1.15
2800	1.28	1.18	1.13	1.10	1.19	1.18	1.08	1.08	1.17
3000	1.13	1.14	1.23	1.20	1.15	1.14	1.16	1.15	1.13
3200	1.41	1.03	1.22	1.20	1.04	1.03	1.21	1.20	1.03
3400	1.55	1.01	1.26	1.24	1.01	1.10	1.18	1.18	1.07
3600	1.27	1.14	1.31	1.32	1.13	1.14	1.14	1.14	1.10
3800	1.48	1.21	1.19	1.22	1.22	1.07	1.25	1.25	1.03
4000	1.57	1.16	1.28	1.30	1.16	1.18	1.41	1.41	1.17
4200	1.35	1.40	1.36	1.44	1.41	1.39	1.49	1.50	1.38
4400	1.41	1.39	1.15	1.21	1.43	1.50	1.41	1.42	1.50
4600	1.32	1.14	1.12	1.17	1.18	1.39	1.19	1.19	1.42
4800	1.33	1.37	1.28	1.37	1.41	1.14	1.04	1.04	1.17
5000	1.18	1.31	1.22	1.21	1.32	1.10	1.24	1.25	1.10
5200	1.19	1.04	1.07	1.11	1.05	1.28	1.35	1.35	1.28
5400	1.31	1.23	1.20	1.28	1.26	1.27	1.30	1.30	1.31
5600	1.12	1.10	1.24	1.14	1.06	1.10	1.14	1.12	1.14
5800	1.56	1.25	1.15	1.18	1.34	1.19	1.16	1.17	1.18
6000	1.57	1.28	1.15	1.22	1.31	1.36	1.29	1.31	1.35
6200	1.40	1.13	1.09	1.02	1.19	1.34	1.29	1.28	1.35
6400	1.60	1.38	1.14	1.26	1.42	1.21	1.16	1.15	1.21
6600	1.55	1.30	1.17	1.24	1.28	1.21	1.15	1.17	1.21
6800	1.42	1.20	1.12	1.16	1.17	1.24	1.24	1.24	1.26
7000	1.25	1.19	1.19	1.18	1.13	1.17	1.23	1.19	1.18
7200	1.20	1.12	1.19	1.12	1.06	1.07	1.13	1.07	1.06
7400	1.48	1.20	1.35	1.23	1.16	1.03	1.05	1.03	1.03
7600	1.63	1.13	1.49	1.27	1.17	1.16	1.20	1.14	1.14
7800	1.40	1.09	1.28	1.11	1.06	1.22	1.39	1.33	1.21
8000	1.57	1.14	1.48	1.26	1.10	1.11	1.49	1.50	1.16
8200	1.75	1.16	1.62	1.43	1.12	1.20	1.42	1.47	1.17
8400	1.44	1.54	1.32	1.22	1.41	1.46	1.25	1.31	1.34
8500	1.24	1.60	1.31	1.16	1.47	1.55	1.19	1.24	1.42

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	2.03	2.02	2.01	2.01	2.01	2.00	2.02	2.00
0.5	1.30	1.30	1.30	1.30	1.29	1.30	1.30	1.29
1	1.26	1.26	1.27	1.26	1.25	1.27	1.26	1.26
5	1.25	1.24	1.25	1.25	1.24	1.25	1.24	1.24
10	1.25	1.24	1.25	1.25	1.24	1.25	1.24	1.24
20	1.25	1.24	1.26	1.25	1.24	1.26	1.24	1.25
50	1.26	1.25	1.26	1.26	1.25	1.26	1.25	1.25
100	1.27	1.26	1.27	1.27	1.25	1.26	1.25	1.25
200	1.27	1.26	1.27	1.27	1.21	1.21	1.20	1.20
400	1.25	1.24	1.24	1.25	1.05	1.04	1.04	1.05
600	1.18	1.18	1.17	1.17	1.18	1.18	1.16	1.17
800	1.06	1.09	1.07	1.06	1.30	1.32	1.30	1.30
1000	1.06	1.03	1.05	1.06	1.15	1.18	1.19	1.16
1200	1.15	1.16	1.18	1.16	1.09	1.10	1.06	1.08
1400	1.16	1.27	1.26	1.17	1.18	1.31	1.28	1.19
1600	1.16	1.31	1.26	1.14	1.21	1.24	1.26	1.20
1800	1.23	1.25	1.19	1.21	1.23	1.05	1.08	1.22
2000	1.30	1.16	1.13	1.29	1.08	1.12	1.08	1.09
2200	1.29	1.09	1.13	1.29	1.23	1.04	1.10	1.23
2400	1.21	1.07	1.13	1.22	1.29	1.16	1.14	1.32
2600	1.17	1.07	1.12	1.18	1.16	1.19	1.13	1.19
2800	1.17	1.11	1.16	1.18	1.15	1.18	1.11	1.18
3000	1.12	1.18	1.22	1.12	1.11	1.27	1.20	1.13
3200	1.03	1.22	1.24	1.02	1.03	1.26	1.20	1.05
3400	1.08	1.19	1.20	1.10	1.02	1.31	1.25	1.02
3600	1.11	1.13	1.16	1.12	1.14	1.32	1.30	1.16
3800	1.05	1.21	1.26	1.06	1.19	1.19	1.19	1.23
4000	1.18	1.36	1.41	1.18	1.12	1.30	1.29	1.15
4200	1.38	1.47	1.49	1.38	1.36	1.36	1.40	1.38
4400	1.50	1.45	1.40	1.50	1.37	1.13	1.19	1.38
4600	1.43	1.27	1.19	1.43	1.15	1.15	1.18	1.15
4800	1.18	1.05	1.03	1.20	1.38	1.28	1.35	1.36
5000	1.06	1.14	1.21	1.03	1.31	1.18	1.18	1.31
5200	1.23	1.29	1.30	1.19	1.05	1.10	1.12	1.04
5400	1.26	1.33	1.25	1.24	1.25	1.21	1.29	1.22
5600	1.11	1.22	1.12	1.17	1.09	1.21	1.14	1.14
5800	1.19	1.14	1.19	1.18	1.24	1.14	1.17	1.20
6000	1.34	1.19	1.29	1.28	1.23	1.15	1.20	1.21
6200	1.32	1.20	1.25	1.28	1.13	1.08	1.02	1.08
6400	1.19	1.11	1.12	1.17	1.32	1.12	1.25	1.29
6600	1.18	1.06	1.14	1.15	1.20	1.16	1.21	1.24
6800	1.22	1.14	1.20	1.23	1.13	1.11	1.15	1.17
7000	1.18	1.15	1.18	1.26	1.12	1.19	1.18	1.19
7200	1.11	1.11	1.11	1.18	1.08	1.20	1.13	1.15
7400	1.03	1.05	1.03	1.11	1.18	1.36	1.23	1.24
7600	1.18	1.08	1.18	1.25	1.14	1.46	1.23	1.15
7800	1.24	1.29	1.41	1.29	1.08	1.28	1.07	1.11
8000	1.11	1.49	1.53	1.11	1.18	1.57	1.31	1.21
8200	1.17	1.51	1.42	1.15	1.10	1.62	1.40	1.10
8400	1.43	1.39	1.24	1.42	1.45	1.34	1.18	1.45
8500	1.52	1.32	1.21	1.52	1.50	1.40	1.18	1.53

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/VCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	2.02	1.49	1.58	1.57	1.54	1.59	1.56	1.55	1.60
0.5	1.29	1.19	1.31	1.27	1.25	1.29	1.28	1.27	1.31
1	1.25	1.18	1.30	1.26	1.23	1.27	1.27	1.26	1.30
5	1.24	1.17	1.29	1.25	1.23	1.27	1.26	1.25	1.30
10	1.23	1.17	1.29	1.25	1.23	1.27	1.26	1.25	1.29
20	1.23	1.17	1.29	1.25	1.23	1.27	1.26	1.25	1.29
50	1.23	1.16	1.28	1.24	1.22	1.26	1.26	1.25	1.29
100	1.22	1.16	1.27	1.24	1.21	1.25	1.25	1.24	1.27
200	1.21	1.15	1.27	1.23	1.20	1.24	1.24	1.23	1.27
400	1.21	1.15	1.27	1.23	1.21	1.25	1.24	1.23	1.27
600	1.20	1.15	1.26	1.23	1.21	1.24	1.24	1.23	1.27
800	1.20	1.14	1.25	1.22	1.20	1.23	1.24	1.23	1.27
1000	1.19	1.14	1.24	1.21	1.20	1.23	1.23	1.22	1.26
1200	1.18	1.13	1.23	1.20	1.19	1.21	1.23	1.21	1.25
1400	1.18	1.12	1.21	1.19	1.18	1.20	1.22	1.21	1.24
1600	1.17	1.11	1.20	1.18	1.17	1.19	1.21	1.20	1.23
1800	1.15	1.11	1.18	1.16	1.16	1.17	1.20	1.19	1.22
2000	1.14	1.10	1.17	1.15	1.15	1.16	1.19	1.18	1.20
2200	1.13	1.09	1.15	1.14	1.13	1.15	1.18	1.17	1.19
2400	1.12	1.08	1.14	1.13	1.12	1.13	1.16	1.16	1.17
2600	1.11	1.08	1.14	1.12	1.11	1.12	1.15	1.15	1.16
2800	1.09	1.07	1.13	1.11	1.10	1.11	1.14	1.15	1.15
3000	1.07	1.06	1.12	1.10	1.08	1.10	1.13	1.14	1.14
3200	1.06	1.05	1.12	1.09	1.07	1.09	1.12	1.13	1.13
3400	1.05	1.05	1.12	1.09	1.07	1.08	1.11	1.12	1.12
3600	1.05	1.05	1.12	1.08	1.06	1.07	1.10	1.11	1.12
3800	1.05	1.04	1.13	1.07	1.05	1.06	1.09	1.10	1.11
4000	1.06	1.03	1.14	1.07	1.04	1.05	1.09	1.09	1.11
4200	1.08	1.03	1.14	1.07	1.04	1.05	1.09	1.08	1.10
4400	1.08	1.03	1.15	1.07	1.03	1.06	1.08	1.07	1.10
4600	1.11	1.04	1.16	1.07	1.02	1.06	1.07	1.06	1.09
4800	1.13	1.04	1.17	1.07	1.02	1.06	1.07	1.06	1.09
5000	1.15	1.05	1.17	1.06	1.01	1.06	1.07	1.05	1.08
5200	1.17	1.04	1.18	1.06	1.01	1.06	1.07	1.04	1.08
5400	1.19	1.06	1.16	1.06	1.01	1.05	1.05	1.04	1.07
5600	1.20	1.05	1.18	1.05	1.01	1.06	1.07	1.04	1.08
5800	1.23	1.07	1.16	1.06	1.02	1.05	1.05	1.04	1.07
6000	1.24	1.06	1.16	1.05	1.03	1.06	1.06	1.04	1.08
6200	1.27	1.06	1.17	1.06	1.04	1.07	1.07	1.06	1.09
6400	1.26	1.07	1.17	1.06	1.06	1.08	1.08	1.07	1.10
6600	1.26	1.07	1.18	1.08	1.08	1.09	1.10	1.10	1.12
6800	1.23	1.09	1.20	1.10	1.10	1.12	1.12	1.13	1.14
7000	1.24	1.12	1.21	1.12	1.12	1.13	1.14	1.16	1.15
7200	1.23	1.15	1.23	1.14	1.14	1.15	1.17	1.19	1.16
7400	1.22	1.18	1.25	1.17	1.17	1.18	1.19	1.23	1.18
7600	1.19	1.22	1.26	1.19	1.20	1.20	1.22	1.26	1.20
7800	1.17	1.27	1.29	1.23	1.23	1.23	1.24	1.30	1.22
8000	1.15	1.32	1.31	1.26	1.27	1.26	1.27	1.34	1.24
8200	1.15	1.36	1.33	1.28	1.30	1.29	1.29	1.37	1.26
8400	1.16	1.41	1.35	1.31	1.34	1.32	1.31	1.40	1.28
8500	1.16	1.42	1.36	1.32	1.35	1.33	1.32	1.41	1.29

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	1.56	1.58	1.53	1.50	1.57	1.49	1.55	1.53
0.5	1.25	1.28	1.24	1.20	1.29	1.19	1.26	1.25
1	1.24	1.26	1.23	1.18	1.27	1.18	1.25	1.24
5	1.23	1.26	1.22	1.18	1.27	1.17	1.25	1.24
10	1.23	1.26	1.22	1.18	1.27	1.17	1.25	1.24
20	1.23	1.26	1.22	1.17	1.27	1.17	1.25	1.24
50	1.23	1.25	1.22	1.17	1.27	1.17	1.24	1.23
100	1.22	1.24	1.21	1.16	1.25	1.16	1.23	1.22
200	1.21	1.23	1.20	1.15	1.24	1.15	1.22	1.21
400	1.21	1.24	1.20	1.16	1.25	1.15	1.23	1.22
600	1.21	1.23	1.19	1.15	1.24	1.15	1.22	1.21
800	1.20	1.23	1.19	1.15	1.23	1.14	1.22	1.21
1000	1.19	1.22	1.18	1.14	1.22	1.13	1.21	1.20
1200	1.18	1.21	1.17	1.14	1.21	1.13	1.20	1.20
1400	1.17	1.20	1.16	1.13	1.20	1.11	1.19	1.19
1600	1.15	1.19	1.14	1.12	1.18	1.11	1.17	1.17
1800	1.14	1.18	1.13	1.11	1.16	1.09	1.16	1.16
2000	1.13	1.17	1.12	1.10	1.15	1.08	1.15	1.15
2200	1.12	1.15	1.11	1.09	1.14	1.07	1.14	1.13
2400	1.11	1.14	1.10	1.09	1.13	1.06	1.13	1.12
2600	1.10	1.13	1.10	1.07	1.13	1.04	1.12	1.10
2800	1.09	1.12	1.10	1.07	1.12	1.03	1.11	1.09
3000	1.09	1.11	1.10	1.06	1.12	1.02	1.10	1.08
3200	1.09	1.11	1.10	1.05	1.11	1.01	1.10	1.07
3400	1.08	1.10	1.09	1.05	1.11	1.01	1.09	1.06
3600	1.07	1.10	1.08	1.04	1.10	1.02	1.08	1.06
3800	1.06	1.09	1.07	1.04	1.09	1.02	1.07	1.05
4000	1.06	1.09	1.07	1.04	1.08	1.03	1.07	1.05
4200	1.06	1.09	1.07	1.04	1.08	1.04	1.08	1.05
4400	1.05	1.09	1.06	1.04	1.08	1.05	1.08	1.06
4600	1.05	1.08	1.05	1.04	1.07	1.06	1.08	1.07
4800	1.05	1.09	1.05	1.05	1.07	1.08	1.08	1.07
5000	1.04	1.08	1.05	1.05	1.06	1.09	1.08	1.08
5200	1.04	1.08	1.04	1.06	1.07	1.11	1.08	1.09
5400	1.04	1.07	1.04	1.05	1.06	1.11	1.08	1.08
5600	1.04	1.08	1.04	1.06	1.07	1.13	1.08	1.09
5800	1.04	1.07	1.05	1.06	1.07	1.13	1.07	1.08
6000	1.04	1.08	1.05	1.07	1.08	1.15	1.07	1.09
6200	1.06	1.09	1.07	1.09	1.10	1.17	1.07	1.10
6400	1.07	1.10	1.09	1.10	1.11	1.19	1.06	1.10
6600	1.09	1.12	1.10	1.12	1.13	1.21	1.08	1.12
6800	1.11	1.15	1.13	1.14	1.15	1.23	1.10	1.13
7000	1.13	1.17	1.16	1.17	1.17	1.26	1.12	1.15
7200	1.16	1.19	1.19	1.20	1.20	1.29	1.14	1.18
7400	1.19	1.22	1.22	1.23	1.22	1.32	1.16	1.20
7600	1.21	1.25	1.25	1.27	1.25	1.35	1.18	1.23
7800	1.25	1.28	1.29	1.30	1.28	1.39	1.22	1.26
8000	1.28	1.31	1.33	1.34	1.32	1.42	1.25	1.29
8200	1.31	1.34	1.35	1.37	1.33	1.45	1.27	1.33
8400	1.34	1.37	1.38	1.40	1.35	1.47	1.30	1.36
8500	1.34	1.38	1.38	1.41	1.35	1.48	1.31	1.37

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION COM to terminated port								
	(dB)								
	COM-J1 @J16 Active	COM-J2 @J1 Active	COM-J4 @J3 Active	COM-J5 @J6 Active	COM-J7 @J6 Active	COM-J8 @J7 Active	COM-J10 @J9 Active	COM-J13 @J12 Active	COM-J15 @J14 Active
0.1	104.83	95.37	95.76	103.09	103.09	97.51	96.60	94.48	97.87
0.5	97.59	96.10	94.36	99.98	99.98	93.23	97.03	94.26	110.62
1	96.63	103.45	107.04	98.61	98.61	96.46	96.81	99.91	101.40
5	94.48	104.63	93.99	103.55	103.55	93.52	98.77	93.11	97.30
10	119.55	105.16	101.04	103.87	103.87	106.23	107.36	100.58	100.02
20	124.71	104.47	95.69	101.88	101.88	99.89	100.20	105.46	96.81
50	119.45	104.28	93.55	95.40	95.40	98.18	98.60	99.02	95.56
100	113.20	106.78	90.06	95.03	95.03	95.26	94.32	99.43	98.33
200	110.74	105.97	88.93	92.98	92.98	94.74	94.62	98.72	95.42
400	112.10	116.98	89.41	94.05	94.05	94.36	92.84	94.91	93.27
600	119.67	117.17	89.86	93.72	93.72	94.58	90.90	94.98	92.35
800	111.45	123.27	89.61	95.34	95.34	96.13	89.69	94.00	92.84
1000	106.78	110.96	90.15	95.52	95.52	97.60	90.21	95.07	91.89
1200	115.99	130.35	90.95	96.73	96.73	104.33	90.07	95.74	92.03
1400	114.24	113.69	90.77	97.62	97.62	104.23	89.75	93.48	92.68
1600	109.29	102.43	91.24	98.11	98.11	107.08	90.14	95.89	92.11
1800	116.97	110.55	91.89	99.90	99.90	118.60	89.78	94.90	91.69
2000	124.15	116.13	93.87	101.63	101.63	126.55	89.79	97.09	91.13
2200	105.27	112.93	92.35	102.14	102.14	126.83	88.36	96.56	91.03
2400	109.09	109.55	92.11	98.51	98.51	107.98	88.54	96.33	90.93
2600	111.61	100.38	93.13	113.05	113.05	106.00	88.33	98.55	90.75
2800	115.51	100.49	92.05	100.47	100.47	97.49	86.20	97.25	90.07
3000	107.67	102.48	92.47	103.09	103.09	98.49	86.41	97.71	89.58
3200	113.65	97.79	89.90	100.89	100.89	92.44	86.86	94.23	89.33
3400	116.97	98.46	89.97	113.17	113.17	91.25	87.02	96.06	90.13
3600	118.25	98.94	87.94	105.01	105.01	89.95	86.11	94.15	88.41
3800	118.51	97.02	87.02	106.64	106.64	88.78	85.15	95.23	89.15
4000	115.29	95.03	86.74	110.38	110.38	88.72	84.49	95.00	89.62
4200	109.93	95.56	87.06	106.33	106.33	88.49	83.82	94.11	88.67
4400	110.48	92.46	85.73	101.86	101.86	87.18	83.54	94.14	88.47
4600	110.48	91.95	85.49	102.32	102.32	86.11	83.81	96.57	88.64
4800	109.64	90.79	84.80	97.50	97.50	84.85	83.21	95.42	88.77
5000	112.27	90.30	84.28	97.57	97.57	84.02	83.63	99.51	87.23
5200	112.74	89.66	84.89	97.43	97.43	83.36	84.85	96.57	87.55
5400	105.64	89.72	84.83	98.01	98.01	83.10	86.84	94.96	86.12
5600	117.77	89.34	84.35	97.93	97.93	82.77	88.96	96.03	85.54
5800	112.84	89.58	84.82	94.67	94.67	82.37	92.77	100.10	85.45
6000	112.77	88.39	83.87	98.12	98.12	82.42	95.22	101.92	84.21
6200	106.07	87.71	83.80	94.64	94.64	82.19	96.02	99.99	83.89
6400	108.43	87.07	82.69	95.34	95.34	81.41	91.79	98.30	83.27
6600	117.09	85.68	81.92	92.11	92.11	80.50	87.40	98.67	82.39
6800	107.54	84.37	81.43	91.30	91.30	79.79	83.19	94.56	81.67
7000	103.33	83.86	80.59	89.45	89.45	78.78	80.90	94.27	80.58
7200	105.41	81.40	79.19	87.12	87.12	77.60	78.60	93.40	80.15
7400	102.11	80.10	77.77	84.28	84.28	76.25	76.54	91.97	79.87
7600	99.04	79.45	76.39	82.39	82.39	74.68	75.36	94.16	80.50
7800	98.23	78.40	74.50	81.46	81.46	73.18	74.15	91.30	80.09
8000	98.08	76.93	72.65	79.93	79.93	71.74	74.06	91.42	80.65
8200	96.88	77.03	71.05	78.57	78.57	70.34	73.52	89.17	81.30
8400	93.44	75.48	69.70	78.50	78.50	69.05	72.54	89.42	82.16
8500	96.44	74.29	68.90	77.49	77.49	68.25	72.23	88.94	82.07

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION between adjacent ports								
	(dB)								
	J1-J2 @J1 Active	J3-J4 @J3 Active	J5-J6 @J5 Active	J6-J7 @J6 Active	J8-J9 @J8 Active	J10-J11 @J10 Active	J12-J13 @J12 Active	J14-J15 @J14 Active	J15-J16 @J15 Active
0.1	94.45	95.05	106.40	101.09	96.07	98.05	101.50	91.04	97.50
0.5	92.72	97.79	94.25	98.05	99.08	97.90	101.20	97.29	95.77
1	99.75	100.38	100.24	94.18	104.09	93.25	101.78	94.11	100.24
5	93.38	94.07	96.38	95.36	109.12	90.44	91.93	98.35	96.91
10	101.85	96.96	96.62	98.61	98.03	98.18	102.00	97.88	93.95
20	98.27	93.92	93.44	95.54	95.47	96.14	97.57	97.28	93.23
50	103.78	89.64	90.36	91.54	92.11	95.82	96.17	94.73	93.33
100	105.06	87.22	88.84	90.18	89.84	94.15	94.61	92.48	92.16
200	102.16	85.69	88.09	88.97	87.94	91.67	93.88	92.23	91.96
400	109.90	85.07	87.61	88.31	86.12	90.82	90.62	90.06	91.58
600	110.02	85.92	88.09	89.08	85.53	89.66	89.96	89.47	91.02
800	113.15	84.20	88.58	90.91	86.50	90.36	89.99	87.66	89.22
1000	132.54	84.43	91.05	92.09	87.02	90.12	89.94	87.00	88.14
1200	108.42	84.07	89.55	93.13	86.24	89.99	89.16	87.94	88.74
1400	105.16	84.04	90.56	93.02	86.47	89.81	89.74	86.67	87.11
1600	101.94	83.97	90.07	92.91	87.43	88.99	90.24	86.35	87.98
1800	104.91	85.88	91.33	93.31	87.39	89.72	91.48	86.39	88.80
2000	104.24	87.16	90.79	94.42	86.55	89.92	91.05	85.59	88.92
2200	102.48	88.82	91.52	93.66	86.00	89.46	89.33	85.57	89.94
2400	97.70	89.56	92.99	93.15	86.02	89.64	89.29	85.63	89.22
2600	98.02	88.05	95.18	92.69	86.62	88.36	90.02	85.00	86.68
2800	97.44	86.34	98.65	92.50	86.08	88.95	89.60	84.68	85.61
3000	96.70	84.73	107.03	92.69	86.38	88.08	90.22	84.19	83.30
3200	95.67	84.30	106.41	93.63	87.06	88.25	90.33	84.22	82.70
3400	93.71	83.13	97.75	96.31	86.46	88.67	89.16	84.24	81.47
3600	94.03	82.80	94.57	100.64	85.55	90.28	88.76	83.54	81.23
3800	94.54	83.55	91.75	103.02	85.94	92.26	89.72	83.19	81.81
4000	93.71	84.16	91.22	100.21	84.97	93.25	89.07	81.49	81.58
4200	92.92	84.31	88.09	97.26	85.59	97.42	88.35	80.63	81.22
4400	92.53	85.34	87.82	95.13	85.65	105.26	87.17	79.70	83.39
4600	94.16	85.12	87.07	90.98	86.39	95.89	89.17	78.28	82.77
4800	90.09	83.81	88.54	88.79	86.64	92.23	89.12	78.05	81.97
5000	88.81	85.74	89.77	87.79	86.29	90.02	89.23	77.23	82.88
5200	90.49	83.01	89.49	86.21	85.09	87.82	90.12	76.13	80.53
5400	89.23	83.59	88.14	85.62	85.51	86.91	91.59	76.77	80.22
5600	87.17	86.72	89.53	84.73	87.26	85.00	91.00	75.79	81.51
5800	88.09	84.17	91.49	84.41	86.97	83.33	89.33	75.85	80.24
6000	91.09	85.29	90.80	84.49	87.21	83.18	92.07	76.76	81.22
6200	87.47	89.99	91.22	84.95	88.34	82.46	92.45	76.19	83.02
6400	86.89	85.26	89.07	84.13	89.01	82.10	91.90	77.20	82.31
6600	86.51	85.85	86.11	83.56	88.93	81.47	89.51	78.60	82.62
6800	87.47	83.20	84.64	82.73	90.04	81.19	89.86	78.66	81.65
7000	87.12	81.03	82.93	81.59	88.26	80.67	88.06	79.48	79.76
7200	84.41	79.04	83.96	80.96	87.11	80.23	87.79	79.01	77.80
7400	82.19	77.13	83.51	79.32	88.08	79.28	86.77	77.72	76.05
7600	82.23	77.76	81.14	77.13	87.32	77.41	86.68	74.75	75.83
7800	79.61	74.83	79.94	74.64	85.76	75.72	85.51	73.91	73.77
8000	75.87	73.61	79.73	72.83	90.26	74.14	85.05	71.23	72.52
8200	74.12	77.97	80.81	71.40	88.00	72.99	84.85	68.98	74.82
8400	73.72	77.89	82.42	70.35	84.66	71.70	83.71	67.59	74.72
8500	74.76	75.39	81.85	69.77	83.68	71.09	83.16	66.85	73.86

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J1	COM-J2	COM-J3	COM-J4	COM-J5	COM-J6	COM-J7	COM-J8
0.1	4.83	4.80	4.84	4.82	4.85	4.80	4.79	4.82
0.5	4.17	4.14	4.17	4.17	4.18	4.14	4.13	4.15
1	4.15	4.12	4.15	4.15	4.16	4.12	4.11	4.13
5	4.16	4.12	4.15	4.15	4.16	4.12	4.11	4.13
10	4.16	4.13	4.16	4.16	4.16	4.12	4.12	4.13
20	4.17	4.14	4.17	4.17	4.17	4.13	4.12	4.14
50	4.21	4.17	4.21	4.20	4.20	4.15	4.15	4.17
100	4.28	4.24	4.27	4.28	4.24	4.19	4.19	4.21
200	4.44	4.39	4.42	4.44	4.32	4.27	4.26	4.29
400	4.71	4.65	4.68	4.70	4.51	4.43	4.41	4.46
600	4.76	4.70	4.73	4.75	4.70	4.59	4.58	4.65
800	4.86	4.75	4.78	4.86	4.84	4.74	4.73	4.80
1000	5.14	5.01	5.05	5.14	4.94	4.84	4.82	4.89
1200	5.32	5.21	5.24	5.30	5.01	4.89	4.87	4.95
1400	5.40	5.23	5.27	5.39	5.10	4.93	4.90	5.03
1600	5.61	5.41	5.45	5.60	5.22	5.01	4.98	5.15
1800	5.83	5.70	5.74	5.81	5.34	5.15	5.12	5.29
2000	5.97	5.80	5.83	5.96	5.46	5.31	5.29	5.42
2200	6.07	5.87	5.92	6.05	5.58	5.46	5.44	5.53
2400	6.18	6.10	6.13	6.17	5.70	5.57	5.54	5.64
2600	6.36	6.25	6.28	6.34	5.80	5.64	5.62	5.72
2800	6.45	6.35	6.39	6.44	5.86	5.73	5.71	5.78
3000	6.55	6.49	6.52	6.55	5.93	5.82	5.79	5.86
3200	6.73	6.58	6.61	6.72	6.08	5.89	5.87	6.02
3400	6.82	6.68	6.71	6.82	6.21	5.95	5.92	6.15
3600	7.05	6.71	6.76	7.04	6.23	6.01	5.99	6.17
3800	7.14	6.78	6.84	7.13	6.23	6.07	6.06	6.19
4000	7.17	6.87	6.93	7.16	6.34	6.06	6.04	6.32
4200	7.37	6.80	6.87	7.36	6.49	5.98	5.97	6.48
4400	7.36	6.95	7.00	7.38	6.51	5.97	5.95	6.50
4600	7.45	7.19	7.24	7.47	6.49	6.17	6.14	6.47
4800	7.46	7.03	7.11	7.49	6.68	6.46	6.43	6.61
5000	7.58	7.35	7.36	7.61	6.90	6.59	6.55	6.84
5200	8.15	7.84	7.86	8.19	6.86	6.49	6.45	6.84
5400	8.05	7.72	7.75	8.11	6.77	6.46	6.41	6.73
5600	8.37	8.06	8.06	8.39	7.10	6.75	6.74	7.00
5800	9.07	8.60	8.67	9.14	7.68	7.19	7.21	7.58
6000	8.91	8.49	8.55	8.94	7.92	7.40	7.41	7.85
6200	8.93	8.54	8.60	8.96	7.82	7.35	7.35	7.73
6400	9.12	8.77	8.86	9.16	7.70	7.27	7.26	7.60
6600	9.06	8.73	8.78	9.05	7.69	7.31	7.28	7.60
6800	9.00	8.72	8.74	9.01	7.67	7.38	7.32	7.61
7000	9.10	8.80	8.79	9.10	7.78	7.40	7.34	7.71
7200	9.25	8.92	8.94	9.25	8.01	7.48	7.46	7.93
7400	9.53	9.17	9.15	9.54	8.09	7.62	7.63	8.00
7600	10.25	9.64	9.54	10.31	8.18	7.77	7.79	8.11
7800	10.44	9.97	9.92	10.44	8.70	8.06	8.06	8.66
8000	10.60	10.22	10.08	10.62	9.45	8.57	8.55	9.39
8200	11.48	10.85	10.70	11.43	9.97	9.11	9.10	9.87
8400	11.95	11.26	11.25	11.74	10.15	9.40	9.44	10.02
8500	11.88	11.30	11.26	11.70	10.15	9.45	9.50	10.04

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J9	COM-J10	COM-J11	COM-J12	COM-J13	COM-J14	COM-J15	COM-J16
0.1	4.85	4.85	4.86	4.84	4.81	4.88	4.84	4.83
0.5	4.18	4.18	4.21	4.19	4.15	4.24	4.18	4.19
1	4.16	4.15	4.19	4.17	4.12	4.21	4.16	4.17
5	4.16	4.15	4.19	4.17	4.13	4.22	4.16	4.17
10	4.16	4.16	4.19	4.18	4.13	4.22	4.17	4.18
20	4.17	4.17	4.20	4.19	4.15	4.23	4.18	4.19
50	4.20	4.19	4.23	4.21	4.18	4.27	4.21	4.22
100	4.24	4.23	4.27	4.26	4.25	4.34	4.28	4.30
200	4.32	4.31	4.34	4.34	4.41	4.49	4.42	4.45
400	4.50	4.46	4.50	4.52	4.65	4.74	4.67	4.70
600	4.69	4.63	4.67	4.70	4.70	4.77	4.70	4.74
800	4.84	4.77	4.82	4.85	4.81	4.86	4.77	4.86
1000	4.93	4.87	4.92	4.95	5.11	5.15	5.07	5.17
1200	5.00	4.92	4.96	5.01	5.29	5.34	5.27	5.34
1400	5.07	4.95	4.99	5.08	5.34	5.35	5.26	5.39
1600	5.19	5.02	5.05	5.19	5.52	5.49	5.41	5.57
1800	5.33	5.15	5.19	5.32	5.74	5.76	5.69	5.79
2000	5.45	5.33	5.38	5.46	5.88	5.88	5.80	5.93
2200	5.56	5.48	5.54	5.58	5.98	5.96	5.88	6.03
2400	5.67	5.59	5.64	5.69	6.10	6.19	6.11	6.16
2600	5.76	5.66	5.72	5.77	6.28	6.35	6.27	6.34
2800	5.82	5.75	5.81	5.84	6.38	6.45	6.38	6.44
3000	5.92	5.84	5.91	5.94	6.50	6.58	6.51	6.54
3200	6.09	5.92	5.96	6.11	6.67	6.68	6.61	6.71
3400	6.22	5.97	6.00	6.25	6.77	6.78	6.71	6.82
3600	6.24	6.02	6.07	6.26	7.02	6.82	6.77	7.07
3800	6.25	6.08	6.12	6.26	7.12	6.92	6.87	7.18
4000	6.37	6.08	6.07	6.37	7.14	7.01	6.97	7.18
4200	6.51	6.03	5.97	6.52	7.34	6.90	6.88	7.39
4400	6.52	6.03	5.99	6.57	7.36	7.08	7.03	7.41
4600	6.51	6.20	6.24	6.58	7.46	7.31	7.27	7.49
4800	6.68	6.47	6.54	6.73	7.48	7.15	7.13	7.52
5000	6.88	6.60	6.61	6.92	7.63	7.54	7.45	7.67
5200	6.82	6.52	6.46	6.89	8.22	8.05	7.98	8.28
5400	6.74	6.46	6.48	6.81	8.13	7.89	7.85	8.20
5600	7.11	6.74	6.88	7.16	8.35	8.22	8.13	8.39
5800	7.70	7.20	7.34	7.73	9.05	8.72	8.69	9.09
6000	7.92	7.45	7.49	7.97	8.94	8.63	8.62	8.97
6200	7.80	7.40	7.39	7.86	9.00	8.72	8.69	8.99
6400	7.67	7.29	7.32	7.73	9.19	8.91	8.91	9.20
6600	7.63	7.32	7.32	7.71	9.12	8.88	8.85	9.14
6800	7.63	7.40	7.32	7.74	9.08	8.88	8.83	9.11
7000	7.79	7.44	7.37	7.92	9.17	8.96	8.90	9.21
7200	8.04	7.54	7.53	8.14	9.33	9.10	9.07	9.35
7400	8.09	7.70	7.69	8.20	9.58	9.32	9.29	9.60
7600	8.18	7.86	7.82	8.32	10.29	9.77	9.70	10.29
7800	8.68	8.12	8.10	8.84	10.48	10.12	10.06	10.48
8000	9.35	8.59	8.61	9.50	10.70	10.38	10.26	10.69
8200	9.81	9.10	9.12	9.97	11.54	10.98	10.87	11.52
8400	10.01	9.40	9.42	10.18	11.89	11.38	11.35	11.86
8500	10.04	9.47	9.48	10.22	11.86	11.43	11.39	11.83

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	2.04	2.02	2.01	2.03	2.01	2.04	2.01	2.01	2.03
0.5	1.31	1.31	1.30	1.31	1.30	1.31	1.30	1.30	1.30
1	1.27	1.27	1.26	1.27	1.27	1.27	1.26	1.26	1.26
5	1.25	1.26	1.25	1.26	1.25	1.26	1.25	1.25	1.25
10	1.25	1.26	1.25	1.26	1.25	1.26	1.25	1.25	1.25
20	1.25	1.26	1.25	1.26	1.26	1.26	1.25	1.25	1.25
50	1.25	1.26	1.25	1.26	1.26	1.26	1.25	1.25	1.25
100	1.25	1.25	1.25	1.25	1.25	1.27	1.26	1.26	1.26
200	1.19	1.21	1.20	1.21	1.21	1.27	1.26	1.26	1.26
400	1.02	1.03	1.04	1.04	1.03	1.25	1.24	1.24	1.24
600	1.21	1.19	1.17	1.17	1.18	1.18	1.18	1.18	1.17
800	1.31	1.28	1.30	1.31	1.28	1.06	1.08	1.08	1.06
1000	1.18	1.12	1.18	1.19	1.15	1.06	1.04	1.03	1.04
1200	1.11	1.08	1.06	1.06	1.05	1.15	1.16	1.15	1.12
1400	1.21	1.12	1.25	1.26	1.15	1.16	1.26	1.24	1.15
1600	1.16	1.20	1.23	1.24	1.21	1.14	1.29	1.27	1.16
1800	1.04	1.26	1.07	1.07	1.22	1.21	1.23	1.22	1.22
2000	1.04	1.10	1.09	1.10	1.08	1.28	1.13	1.14	1.27
2200	1.06	1.26	1.08	1.10	1.23	1.27	1.06	1.08	1.26
2400	1.02	1.33	1.14	1.12	1.32	1.20	1.07	1.07	1.19
2600	1.20	1.19	1.15	1.12	1.19	1.18	1.06	1.06	1.16
2800	1.28	1.19	1.15	1.11	1.19	1.19	1.09	1.09	1.17
3000	1.12	1.12	1.25	1.21	1.14	1.14	1.17	1.17	1.13
3200	1.42	1.04	1.24	1.22	1.04	1.04	1.21	1.21	1.03
3400	1.57	1.04	1.28	1.26	1.01	1.11	1.18	1.19	1.06
3600	1.29	1.18	1.30	1.32	1.14	1.14	1.15	1.16	1.09
3800	1.52	1.23	1.18	1.22	1.21	1.07	1.25	1.26	1.04
4000	1.58	1.19	1.27	1.31	1.16	1.18	1.42	1.41	1.17
4200	1.37	1.41	1.36	1.44	1.41	1.41	1.51	1.50	1.38
4400	1.43	1.36	1.15	1.22	1.44	1.52	1.42	1.40	1.51
4600	1.31	1.12	1.13	1.19	1.19	1.39	1.18	1.18	1.44
4800	1.35	1.35	1.30	1.39	1.44	1.12	1.07	1.06	1.18
5000	1.14	1.26	1.21	1.19	1.31	1.13	1.27	1.25	1.12
5200	1.23	1.06	1.08	1.12	1.08	1.29	1.36	1.36	1.31
5400	1.30	1.18	1.21	1.27	1.26	1.24	1.28	1.27	1.31
5600	1.17	1.14	1.23	1.12	1.06	1.08	1.10	1.12	1.10
5800	1.56	1.23	1.15	1.19	1.35	1.21	1.18	1.18	1.20
6000	1.48	1.18	1.13	1.19	1.27	1.34	1.27	1.27	1.34
6200	1.36	1.08	1.08	1.05	1.21	1.29	1.25	1.22	1.32
6400	1.52	1.27	1.12	1.23	1.39	1.17	1.14	1.11	1.19
6600	1.49	1.26	1.16	1.20	1.25	1.19	1.15	1.15	1.21
6800	1.41	1.22	1.13	1.15	1.17	1.22	1.22	1.21	1.23
7000	1.24	1.25	1.20	1.16	1.11	1.17	1.19	1.17	1.15
7200	1.24	1.21	1.19	1.12	1.07	1.08	1.10	1.07	1.06
7400	1.51	1.29	1.34	1.23	1.17	1.05	1.05	1.04	1.02
7600	1.56	1.12	1.45	1.26	1.16	1.17	1.18	1.16	1.15
7800	1.34	1.18	1.27	1.09	1.04	1.19	1.37	1.33	1.23
8000	1.50	1.22	1.48	1.25	1.11	1.09	1.49	1.45	1.15
8200	1.63	1.27	1.59	1.38	1.11	1.20	1.43	1.42	1.13
8400	1.35	1.67	1.32	1.18	1.42	1.43	1.25	1.27	1.34
8500	1.18	1.71	1.33	1.13	1.47	1.51	1.19	1.21	1.43

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	2.04	2.03	2.01	2.01	2.02	2.01	2.02	2.00
0.5	1.31	1.31	1.31	1.31	1.30	1.32	1.31	1.31
1	1.27	1.27	1.28	1.27	1.26	1.28	1.27	1.27
5	1.26	1.25	1.26	1.26	1.25	1.27	1.26	1.26
10	1.26	1.25	1.26	1.26	1.25	1.27	1.26	1.26
20	1.26	1.26	1.27	1.26	1.25	1.27	1.26	1.26
50	1.26	1.26	1.27	1.26	1.25	1.27	1.26	1.26
100	1.27	1.26	1.27	1.27	1.25	1.26	1.25	1.26
200	1.28	1.27	1.27	1.27	1.22	1.22	1.21	1.21
400	1.26	1.25	1.25	1.25	1.05	1.04	1.04	1.04
600	1.17	1.18	1.18	1.17	1.19	1.20	1.18	1.19
800	1.05	1.08	1.07	1.04	1.30	1.33	1.31	1.29
1000	1.07	1.05	1.07	1.07	1.14	1.17	1.18	1.14
1200	1.15	1.17	1.19	1.15	1.09	1.10	1.07	1.08
1400	1.15	1.27	1.27	1.16	1.18	1.31	1.28	1.18
1600	1.15	1.30	1.25	1.14	1.21	1.23	1.26	1.20
1800	1.24	1.25	1.17	1.21	1.24	1.05	1.08	1.23
2000	1.32	1.15	1.12	1.30	1.09	1.12	1.08	1.09
2200	1.30	1.09	1.14	1.30	1.25	1.04	1.09	1.24
2400	1.23	1.08	1.16	1.23	1.32	1.16	1.14	1.34
2600	1.19	1.08	1.15	1.19	1.18	1.20	1.15	1.20
2800	1.18	1.12	1.20	1.18	1.17	1.19	1.13	1.19
3000	1.11	1.19	1.27	1.12	1.11	1.28	1.22	1.13
3200	1.02	1.22	1.28	1.01	1.02	1.28	1.22	1.06
3400	1.10	1.18	1.22	1.09	1.03	1.33	1.28	1.03
3600	1.12	1.13	1.19	1.12	1.17	1.33	1.31	1.17
3800	1.07	1.22	1.28	1.06	1.20	1.20	1.19	1.23
4000	1.20	1.37	1.40	1.17	1.14	1.31	1.30	1.16
4200	1.40	1.48	1.44	1.38	1.37	1.36	1.39	1.39
4400	1.50	1.46	1.33	1.51	1.35	1.12	1.16	1.39
4600	1.40	1.28	1.15	1.45	1.13	1.16	1.17	1.15
4800	1.16	1.05	1.07	1.21	1.38	1.28	1.34	1.38
5000	1.07	1.17	1.18	1.05	1.29	1.18	1.16	1.31
5200	1.23	1.32	1.24	1.22	1.06	1.10	1.13	1.04
5400	1.23	1.32	1.21	1.24	1.22	1.21	1.25	1.22
5600	1.13	1.18	1.19	1.14	1.10	1.20	1.14	1.13
5800	1.21	1.14	1.21	1.20	1.22	1.12	1.16	1.20
6000	1.30	1.19	1.21	1.28	1.18	1.14	1.15	1.18
6200	1.25	1.18	1.13	1.25	1.12	1.08	1.06	1.08
6400	1.14	1.06	1.05	1.13	1.28	1.11	1.18	1.26
6600	1.16	1.08	1.05	1.14	1.19	1.15	1.15	1.22
6800	1.22	1.13	1.12	1.21	1.14	1.13	1.11	1.18
7000	1.21	1.11	1.20	1.24	1.14	1.20	1.15	1.20
7200	1.12	1.10	1.19	1.18	1.11	1.19	1.12	1.16
7400	1.09	1.06	1.12	1.12	1.19	1.36	1.26	1.25
7600	1.22	1.06	1.28	1.27	1.11	1.42	1.27	1.13
7800	1.22	1.29	1.54	1.31	1.10	1.27	1.13	1.12
8000	1.06	1.50	1.63	1.13	1.16	1.55	1.35	1.20
8200	1.20	1.53	1.48	1.15	1.11	1.58	1.39	1.10
8400	1.44	1.40	1.31	1.43	1.42	1.34	1.16	1.43
8500	1.52	1.33	1.31	1.52	1.46	1.41	1.19	1.50

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	2.01	1.48	1.56	1.55	1.52	1.57	1.53	1.53	1.58
0.5	1.26	1.16	1.27	1.23	1.21	1.25	1.24	1.24	1.28
1	1.22	1.14	1.26	1.22	1.20	1.23	1.23	1.22	1.26
5	1.20	1.14	1.25	1.22	1.20	1.23	1.23	1.22	1.26
10	1.20	1.14	1.25	1.22	1.20	1.23	1.22	1.22	1.26
20	1.20	1.14	1.25	1.22	1.20	1.23	1.22	1.22	1.26
50	1.20	1.13	1.25	1.21	1.19	1.23	1.22	1.22	1.26
100	1.19	1.13	1.25	1.21	1.19	1.23	1.22	1.22	1.25
200	1.19	1.13	1.24	1.21	1.19	1.22	1.22	1.21	1.25
400	1.18	1.12	1.24	1.20	1.18	1.21	1.21	1.21	1.24
600	1.17	1.12	1.22	1.19	1.17	1.21	1.20	1.20	1.23
800	1.17	1.11	1.21	1.18	1.17	1.20	1.20	1.19	1.23
1000	1.16	1.11	1.21	1.18	1.16	1.19	1.19	1.19	1.22
1200	1.15	1.10	1.20	1.17	1.16	1.18	1.19	1.18	1.21
1400	1.14	1.10	1.18	1.16	1.15	1.17	1.18	1.18	1.20
1600	1.13	1.09	1.17	1.15	1.14	1.16	1.18	1.17	1.19
1800	1.12	1.09	1.16	1.14	1.13	1.15	1.17	1.16	1.19
2000	1.12	1.08	1.14	1.13	1.12	1.13	1.16	1.15	1.17
2200	1.11	1.07	1.12	1.12	1.11	1.12	1.15	1.14	1.16
2400	1.10	1.07	1.11	1.10	1.10	1.11	1.14	1.13	1.14
2600	1.09	1.06	1.10	1.09	1.09	1.10	1.13	1.13	1.13
2800	1.09	1.06	1.09	1.08	1.08	1.08	1.12	1.12	1.12
3000	1.09	1.05	1.08	1.08	1.07	1.07	1.11	1.11	1.11
3200	1.08	1.04	1.09	1.07	1.06	1.06	1.10	1.10	1.11
3400	1.08	1.04	1.09	1.06	1.06	1.05	1.10	1.09	1.11
3600	1.09	1.03	1.10	1.06	1.05	1.04	1.09	1.08	1.10
3800	1.10	1.02	1.11	1.05	1.05	1.04	1.08	1.08	1.09
4000	1.11	1.02	1.11	1.05	1.05	1.03	1.08	1.07	1.08
4200	1.12	1.02	1.12	1.05	1.04	1.03	1.08	1.07	1.08
4400	1.13	1.02	1.13	1.05	1.04	1.03	1.07	1.06	1.07
4600	1.14	1.03	1.13	1.05	1.04	1.03	1.06	1.06	1.06
4800	1.15	1.03	1.13	1.04	1.03	1.02	1.06	1.05	1.05
5000	1.17	1.04	1.14	1.04	1.02	1.02	1.05	1.05	1.05
5200	1.18	1.05	1.15	1.04	1.02	1.02	1.04	1.04	1.05
5400	1.20	1.06	1.15	1.04	1.02	1.03	1.04	1.04	1.04
5600	1.20	1.07	1.16	1.04	1.01	1.03	1.04	1.03	1.05
5800	1.21	1.10	1.15	1.05	1.02	1.04	1.03	1.05	1.06
6000	1.20	1.11	1.17	1.05	1.01	1.05	1.05	1.05	1.06
6200	1.20	1.12	1.17	1.06	1.03	1.07	1.06	1.07	1.08
6400	1.20	1.15	1.18	1.07	1.05	1.08	1.08	1.09	1.10
6600	1.20	1.16	1.18	1.08	1.06	1.09	1.10	1.10	1.12
6800	1.19	1.19	1.19	1.10	1.09	1.11	1.12	1.12	1.13
7000	1.18	1.21	1.21	1.11	1.11	1.13	1.14	1.14	1.15
7200	1.17	1.25	1.23	1.14	1.14	1.15	1.17	1.17	1.17
7400	1.16	1.28	1.25	1.16	1.18	1.17	1.20	1.20	1.19
7600	1.14	1.32	1.28	1.18	1.21	1.19	1.23	1.23	1.22
7800	1.13	1.35	1.30	1.21	1.25	1.22	1.26	1.27	1.24
8000	1.12	1.39	1.34	1.24	1.30	1.26	1.30	1.31	1.27
8200	1.12	1.43	1.36	1.27	1.33	1.28	1.32	1.34	1.29
8400	1.12	1.47	1.38	1.29	1.36	1.31	1.34	1.38	1.30
8500	1.13	1.49	1.39	1.30	1.38	1.31	1.34	1.39	1.31

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	1.54	1.56	1.51	1.48	1.55	1.47	1.53	1.50
0.5	1.22	1.24	1.21	1.17	1.25	1.16	1.22	1.22
1	1.21	1.23	1.19	1.15	1.24	1.14	1.21	1.20
5	1.20	1.23	1.19	1.15	1.23	1.14	1.21	1.20
10	1.20	1.23	1.19	1.15	1.23	1.14	1.21	1.20
20	1.20	1.23	1.19	1.15	1.23	1.14	1.21	1.20
50	1.20	1.22	1.19	1.15	1.23	1.14	1.21	1.20
100	1.20	1.22	1.19	1.14	1.23	1.13	1.20	1.19
200	1.19	1.22	1.18	1.14	1.22	1.13	1.20	1.19
400	1.19	1.21	1.17	1.14	1.22	1.12	1.19	1.19
600	1.18	1.20	1.17	1.13	1.21	1.12	1.18	1.18
800	1.17	1.19	1.15	1.12	1.20	1.11	1.18	1.17
1000	1.16	1.19	1.15	1.12	1.19	1.11	1.17	1.17
1200	1.15	1.18	1.13	1.11	1.18	1.10	1.16	1.16
1400	1.14	1.17	1.12	1.11	1.17	1.10	1.15	1.15
1600	1.12	1.16	1.11	1.10	1.15	1.10	1.14	1.14
1800	1.11	1.15	1.10	1.10	1.14	1.09	1.13	1.13
2000	1.10	1.14	1.08	1.09	1.13	1.09	1.12	1.12
2200	1.09	1.13	1.07	1.09	1.11	1.08	1.10	1.11
2400	1.08	1.12	1.06	1.08	1.10	1.07	1.09	1.10
2600	1.07	1.11	1.05	1.07	1.09	1.07	1.08	1.09
2800	1.06	1.10	1.04	1.06	1.08	1.06	1.07	1.07
3000	1.05	1.09	1.04	1.06	1.07	1.05	1.07	1.06
3200	1.05	1.09	1.04	1.05	1.07	1.04	1.06	1.05
3400	1.04	1.09	1.04	1.05	1.06	1.03	1.05	1.04
3600	1.04	1.09	1.04	1.04	1.06	1.02	1.05	1.03
3800	1.04	1.08	1.05	1.05	1.06	1.01	1.05	1.02
4000	1.04	1.08	1.05	1.05	1.06	1.01	1.05	1.02
4200	1.04	1.08	1.05	1.05	1.06	1.02	1.06	1.03
4400	1.04	1.08	1.06	1.06	1.06	1.03	1.06	1.04
4600	1.04	1.07	1.06	1.06	1.06	1.05	1.06	1.04
4800	1.03	1.07	1.06	1.06	1.06	1.06	1.06	1.05
5000	1.04	1.06	1.07	1.05	1.06	1.08	1.07	1.05
5200	1.04	1.05	1.07	1.05	1.06	1.10	1.07	1.06
5400	1.04	1.04	1.08	1.05	1.07	1.11	1.08	1.06
5600	1.05	1.05	1.10	1.05	1.06	1.13	1.07	1.07
5800	1.06	1.05	1.12	1.05	1.08	1.14	1.09	1.07
6000	1.06	1.06	1.12	1.07	1.08	1.17	1.09	1.09
6200	1.09	1.08	1.15	1.08	1.10	1.18	1.10	1.10
6400	1.10	1.11	1.17	1.10	1.11	1.20	1.12	1.11
6600	1.11	1.13	1.18	1.13	1.12	1.22	1.12	1.13
6800	1.13	1.16	1.21	1.15	1.14	1.24	1.14	1.14
7000	1.14	1.18	1.23	1.18	1.15	1.26	1.15	1.15
7200	1.17	1.22	1.26	1.22	1.18	1.29	1.17	1.17
7400	1.19	1.25	1.29	1.26	1.20	1.32	1.19	1.20
7600	1.21	1.28	1.32	1.30	1.23	1.35	1.21	1.23
7800	1.25	1.32	1.35	1.34	1.26	1.39	1.23	1.27
8000	1.28	1.36	1.39	1.39	1.30	1.43	1.26	1.31
8200	1.31	1.38	1.42	1.42	1.32	1.46	1.27	1.34
8400	1.33	1.40	1.45	1.44	1.35	1.50	1.29	1.37
8500	1.34	1.41	1.46	1.45	1.36	1.51	1.29	1.38

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION COM to terminated port								
	(dB)								
	COM-J1 @J16 Active	COM-J2 @J1 Active	COM-J4 @J3 Active	COM-J5 @J6 Active	COM-J7 @J6 Active	COM-J8 @J7 Active	COM-J10 @J9 Active	COM-J13 @J12 Active	COM-J15 @J14 Active
0.1	95.55	95.25	97.00	105.90	105.90	110.23	109.91	98.47	103.68
0.5	97.04	95.42	108.17	96.94	96.94	100.28	98.84	99.41	96.84
1	105.57	104.30	105.42	96.88	96.88	92.32	95.85	94.22	97.49
5	115.48	94.81	99.45	97.30	97.30	97.06	96.41	104.52	91.22
10	115.11	111.26	104.12	103.03	103.03	107.81	106.63	103.22	100.03
20	124.43	102.85	97.40	98.15	98.15	103.42	103.54	100.91	99.94
50	121.65	101.82	94.58	97.53	97.53	99.65	99.12	100.05	99.38
100	137.11	102.43	92.82	94.79	94.79	96.98	100.45	99.73	97.96
200	127.40	110.59	92.83	94.87	94.87	96.77	96.43	99.33	97.41
400	110.21	109.99	92.39	95.20	95.20	97.97	98.44	95.89	96.38
600	115.07	111.44	93.05	95.13	95.13	98.11	95.71	95.44	94.40
800	122.92	114.31	93.65	95.52	95.52	99.21	95.97	96.92	93.27
1000	121.43	115.16	92.51	93.79	93.79	98.94	95.78	94.72	93.17
1200	114.32	113.55	92.41	95.27	95.27	101.19	99.52	95.15	92.68
1400	114.48	110.32	94.36	95.68	95.68	116.66	100.43	96.39	92.77
1600	114.96	109.31	93.16	97.26	97.26	134.00	97.25	94.96	92.08
1800	112.39	112.39	94.22	98.29	98.29	115.30	97.74	94.83	91.55
2000	114.13	115.91	93.98	98.48	98.48	119.93	101.75	94.62	91.97
2200	110.52	109.60	92.27	97.22	97.22	112.64	96.75	95.60	90.82
2400	117.81	100.96	92.75	97.66	97.66	104.03	95.19	93.84	91.19
2600	112.90	103.39	92.09	100.22	100.22	98.61	94.40	94.31	89.44
2800	107.64	102.48	90.32	98.80	98.80	96.72	96.24	94.08	91.24
3000	117.01	100.80	90.78	98.90	98.90	96.00	94.46	94.51	89.73
3200	119.59	103.72	89.20	101.91	101.91	92.13	95.65	92.62	89.30
3400	108.34	96.99	88.75	101.36	101.36	90.66	92.75	91.55	89.41
3600	105.04	98.07	87.37	105.71	105.71	90.87	92.05	91.47	88.48
3800	109.38	96.59	86.29	101.79	101.79	90.27	91.26	92.03	89.14
4000	116.08	93.92	87.30	106.90	106.90	89.55	89.74	92.39	89.11
4200	110.68	93.26	85.98	102.44	102.44	88.22	89.15	91.05	89.24
4400	105.82	93.38	85.23	99.60	99.60	86.86	87.75	90.85	88.95
4600	114.57	93.20	85.25	97.84	97.84	85.94	88.13	92.49	89.14
4800	106.86	90.21	85.13	96.14	96.14	84.79	87.48	92.63	87.29
5000	122.69	89.96	84.91	100.03	100.03	83.71	88.32	94.33	87.37
5200	108.74	90.24	84.81	95.21	95.21	83.33	87.03	93.82	89.07
5400	109.70	89.70	85.02	94.84	94.84	82.17	88.49	94.04	88.09
5600	113.79	89.11	85.24	95.82	95.82	82.65	90.77	94.82	86.86
5800	106.22	89.46	85.16	93.43	93.43	82.40	91.11	94.70	86.44
6000	122.78	89.45	84.12	94.10	94.10	82.52	93.62	95.11	85.35
6200	110.82	87.89	83.85	92.61	92.61	82.18	94.26	97.08	85.02
6400	115.24	87.59	83.11	91.51	91.51	81.52	90.49	96.42	83.99
6600	106.79	85.81	82.28	90.61	90.61	80.58	89.27	95.78	82.83
6800	109.19	84.32	81.31	89.41	89.41	79.68	84.84	94.19	82.71
7000	101.43	82.69	79.91	88.34	88.34	78.27	82.12	93.95	81.68
7200	102.78	81.34	78.86	85.66	85.66	76.97	80.39	93.13	80.95
7400	105.13	79.88	77.42	83.59	83.59	75.73	78.24	91.46	81.00
7600	105.01	79.44	75.88	81.57	81.57	74.05	76.71	90.72	81.79
7800	99.55	78.10	74.50	80.94	80.94	72.76	75.73	89.52	80.98
8000	107.64	77.01	72.45	79.73	79.73	71.37	75.16	89.35	82.14
8200	97.40	76.50	70.99	79.01	79.01	70.21	74.30	88.21	83.67
8400	95.47	75.40	69.82	77.86	77.86	68.93	73.53	86.90	84.11
8500	95.32	74.28	68.99	76.90	76.90	68.35	72.99	87.03	83.65

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION between adjacent ports								
	(dB)								
	J1-J2 @J1 Active	J3-J4 @J3 Active	J5-J6 @J5 Active	J6-J7 @J6 Active	J8-J9 @J8 Active	J10-J11 @J10 Active	J12-J13 @J12 Active	J14-J15 @J14 Active	J15-J16 @J15 Active
0.1	114.95	99.41	109.29	105.32	100.21	92.71	93.52	96.58	94.54
0.5	98.54	101.37	93.16	95.87	103.60	98.52	98.38	94.80	102.35
1	96.87	107.96	95.83	97.58	95.60	98.79	93.94	96.18	97.42
5	99.40	96.34	96.22	100.94	101.96	93.02	101.98	98.13	97.89
10	102.42	96.72	99.52	98.51	100.07	105.59	99.93	95.96	99.04
20	98.11	93.63	94.39	96.13	96.65	98.84	98.15	97.07	95.40
50	99.86	91.12	92.10	92.64	94.95	96.44	99.16	94.26	97.08
100	99.00	89.22	90.43	90.71	93.46	96.76	96.13	94.07	96.24
200	104.63	87.90	89.88	90.89	92.47	96.11	95.34	94.41	95.37
400	110.80	87.96	88.66	89.04	90.79	93.75	92.02	90.68	94.01
600	104.00	88.10	90.25	90.74	89.88	94.22	90.59	90.16	94.92
800	106.00	87.21	91.72	90.37	91.64	95.50	91.47	88.42	92.95
1000	108.84	86.28	91.61	92.27	90.98	96.09	90.47	88.20	92.60
1200	105.23	86.02	90.92	91.46	89.51	96.42	89.61	88.09	92.31
1400	105.66	85.65	91.52	91.06	90.48	95.62	89.64	86.14	91.74
1600	102.91	86.39	91.59	91.76	91.55	94.84	90.50	86.32	94.00
1800	103.13	87.84	92.40	93.23	91.22	94.31	89.94	86.46	94.90
2000	102.68	88.45	91.84	92.14	89.32	98.05	88.74	85.14	98.56
2200	99.44	88.63	92.11	91.48	88.54	94.42	87.85	84.95	103.22
2400	101.36	90.07	93.89	90.83	87.74	93.92	87.91	84.89	101.54
2600	100.01	88.00	94.76	91.42	89.52	93.05	86.87	83.80	93.88
2800	101.56	86.10	97.00	90.64	88.73	91.36	87.27	84.06	92.46
3000	99.13	84.38	104.86	90.66	88.14	92.94	87.08	83.69	89.39
3200	95.38	82.90	104.37	91.30	88.84	93.59	87.54	82.99	87.91
3400	95.91	82.40	96.52	93.07	88.31	93.35	86.53	82.77	86.75
3600	93.78	81.96	94.39	97.51	87.00	96.22	86.36	82.44	86.94
3800	93.82	82.67	91.02	101.85	86.74	96.55	85.91	82.66	88.63
4000	91.81	82.48	89.03	110.65	86.29	98.45	85.58	81.39	89.61
4200	91.90	82.59	87.70	100.40	84.71	98.84	83.86	80.89	89.27
4400	92.51	84.07	86.64	93.20	85.23	95.24	85.28	80.42	93.95
4600	92.18	83.81	87.08	90.46	86.63	93.08	86.29	79.03	92.34
4800	90.54	82.42	88.14	88.19	86.86	91.43	86.67	78.77	89.20
5000	89.76	84.04	88.99	87.24	85.89	90.01	85.61	77.46	94.87
5200	90.68	81.94	89.58	85.40	85.49	88.35	86.19	76.59	86.96
5400	90.88	82.38	88.59	84.30	86.83	86.89	88.04	77.10	87.73
5600	87.76	84.71	90.30	83.31	87.04	85.33	87.36	76.15	93.81
5800	88.85	82.99	91.20	82.98	85.19	84.25	86.67	76.14	88.42
6000	91.75	84.88	91.36	83.14	85.73	84.26	87.74	76.97	92.95
6200	88.19	89.27	92.57	83.71	85.80	83.95	89.33	76.49	92.73
6400	86.60	86.27	89.50	83.11	86.23	83.31	89.57	77.40	88.79
6600	87.75	86.46	86.82	82.62	85.51	82.42	88.20	78.52	89.42
6800	85.47	84.19	84.58	82.19	86.10	81.58	88.05	79.33	84.31
7000	84.45	81.91	83.67	81.58	84.67	80.69	86.61	80.05	82.45
7200	83.10	78.92	83.58	81.22	83.27	79.94	84.70	80.64	80.04
7400	80.75	77.23	82.74	79.34	83.73	78.46	85.11	80.48	79.04
7600	80.84	77.74	80.49	77.04	82.85	76.87	83.31	76.89	79.49
7800	79.87	74.60	79.24	74.63	82.62	74.86	82.51	75.67	76.31
8000	76.31	73.84	79.26	72.69	83.79	73.33	82.98	72.39	76.27
8200	75.73	78.46	81.42	71.51	83.56	72.13	82.80	70.11	80.66
8400	76.98	78.14	81.71	70.14	81.26	70.92	81.29	68.51	79.80
8500	76.53	75.23	81.24	69.50	80.49	70.32	81.78	67.70	77.24

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J1	COM-J2	COM-J3	COM-J4	COM-J5	COM-J6	COM-J7	COM-J8
0.1	4.89	4.86	4.90	4.89	4.92	4.86	4.85	4.89
0.5	4.26	4.23	4.26	4.25	4.26	4.22	4.21	4.23
1	4.24	4.20	4.23	4.23	4.24	4.20	4.19	4.21
5	4.24	4.21	4.24	4.24	4.24	4.20	4.19	4.21
10	4.25	4.21	4.24	4.24	4.25	4.20	4.19	4.22
20	4.26	4.23	4.26	4.26	4.26	4.21	4.20	4.23
50	4.29	4.26	4.29	4.29	4.28	4.23	4.23	4.25
100	4.37	4.33	4.36	4.36	4.32	4.27	4.26	4.29
200	4.54	4.49	4.52	4.53	4.41	4.35	4.34	4.37
400	4.82	4.75	4.79	4.81	4.61	4.52	4.51	4.56
600	4.86	4.80	4.82	4.85	4.80	4.69	4.68	4.75
800	4.97	4.86	4.88	4.97	4.95	4.85	4.83	4.91
1000	5.25	5.12	5.16	5.25	5.04	4.94	4.92	5.00
1200	5.42	5.32	5.34	5.42	5.11	4.99	4.97	5.06
1400	5.50	5.34	5.37	5.50	5.20	5.02	5.00	5.14
1600	5.71	5.51	5.56	5.71	5.32	5.10	5.07	5.26
1800	5.93	5.81	5.84	5.92	5.44	5.25	5.22	5.40
2000	6.07	5.91	5.93	6.06	5.56	5.41	5.39	5.51
2200	6.16	5.98	6.02	6.15	5.68	5.55	5.54	5.62
2400	6.27	6.20	6.23	6.26	5.80	5.65	5.64	5.74
2600	6.45	6.35	6.37	6.44	5.88	5.73	5.71	5.82
2800	6.54	6.46	6.48	6.53	5.94	5.82	5.80	5.88
3000	6.65	6.59	6.61	6.65	6.02	5.90	5.88	5.96
3200	6.81	6.67	6.70	6.81	6.17	5.97	5.95	6.12
3400	6.91	6.76	6.79	6.91	6.29	6.03	6.00	6.24
3600	7.14	6.81	6.84	7.14	6.31	6.10	6.07	6.26
3800	7.24	6.90	6.94	7.24	6.33	6.16	6.14	6.29
4000	7.27	6.98	7.02	7.28	6.46	6.14	6.12	6.43
4200	7.47	6.90	6.97	7.47	6.60	6.07	6.06	6.58
4400	7.48	7.08	7.12	7.50	6.62	6.09	6.06	6.60
4600	7.57	7.30	7.34	7.59	6.62	6.30	6.26	6.58
4800	7.58	7.16	7.22	7.60	6.81	6.58	6.54	6.74
5000	7.71	7.49	7.49	7.76	7.02	6.70	6.66	6.95
5200	8.29	7.97	8.00	8.33	6.98	6.60	6.56	6.94
5400	8.18	7.84	7.88	8.23	6.88	6.56	6.52	6.84
5600	8.51	8.22	8.22	8.55	7.24	6.88	6.87	7.14
5800	9.24	8.78	8.83	9.33	7.85	7.37	7.35	7.75
6000	9.06	8.66	8.70	9.11	8.08	7.58	7.55	8.03
6200	9.08	8.72	8.75	9.16	7.94	7.50	7.47	7.90
6400	9.25	8.93	8.99	9.32	7.81	7.40	7.38	7.76
6600	9.18	8.86	8.91	9.19	7.79	7.42	7.42	7.74
6800	9.14	8.85	8.89	9.14	7.79	7.46	7.46	7.73
7000	9.26	8.95	8.96	9.27	7.94	7.50	7.49	7.87
7200	9.44	9.13	9.13	9.45	8.19	7.64	7.64	8.13
7400	9.78	9.44	9.37	9.80	8.28	7.82	7.83	8.22
7600	10.51	9.95	9.81	10.59	8.44	8.01	8.02	8.39
7800	10.68	10.24	10.17	10.70	9.01	8.34	8.34	8.95
8000	10.85	10.48	10.35	10.90	9.75	8.86	8.85	9.69
8200	11.75	11.16	10.99	11.76	10.26	9.40	9.40	10.21
8400	12.20	11.62	11.54	12.14	10.44	9.73	9.73	10.41
8500	12.15	11.66	11.57	12.10	10.45	9.79	9.80	10.42

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J9	COM-J10	COM-J11	COM-J12	COM-J13	COM-J14	COM-J15	COM-J16
0.1	4.92	4.91	4.92	4.91	4.85	4.94	4.89	4.89
0.5	4.26	4.25	4.29	4.27	4.21	4.31	4.25	4.26
1	4.24	4.23	4.27	4.24	4.19	4.29	4.22	4.24
5	4.24	4.23	4.27	4.25	4.20	4.29	4.23	4.24
10	4.24	4.23	4.27	4.25	4.20	4.30	4.23	4.25
20	4.25	4.24	4.28	4.26	4.21	4.31	4.25	4.26
50	4.28	4.26	4.30	4.28	4.25	4.34	4.28	4.30
100	4.32	4.30	4.34	4.33	4.32	4.41	4.34	4.37
200	4.40	4.38	4.41	4.41	4.48	4.58	4.50	4.54
400	4.60	4.55	4.59	4.61	4.74	4.83	4.75	4.80
600	4.79	4.73	4.76	4.80	4.78	4.86	4.78	4.83
800	4.94	4.88	4.91	4.95	4.90	4.96	4.86	4.96
1000	5.03	4.97	5.01	5.04	5.20	5.26	5.16	5.27
1200	5.10	5.02	5.05	5.11	5.38	5.44	5.36	5.44
1400	5.17	5.04	5.07	5.18	5.43	5.45	5.35	5.49
1600	5.29	5.11	5.14	5.28	5.61	5.60	5.49	5.67
1800	5.42	5.25	5.28	5.41	5.83	5.87	5.78	5.89
2000	5.54	5.43	5.47	5.54	5.97	5.98	5.88	6.03
2200	5.65	5.58	5.63	5.66	6.06	6.07	5.97	6.13
2400	5.76	5.68	5.72	5.77	6.18	6.30	6.20	6.25
2600	5.84	5.76	5.80	5.85	6.36	6.45	6.35	6.43
2800	5.90	5.85	5.89	5.92	6.46	6.55	6.46	6.53
3000	6.01	5.94	5.98	6.02	6.58	6.69	6.59	6.65
3200	6.18	6.01	6.03	6.20	6.75	6.79	6.69	6.81
3400	6.30	6.05	6.08	6.33	6.86	6.88	6.78	6.92
3600	6.31	6.11	6.14	6.34	7.10	6.92	6.84	7.17
3800	6.34	6.17	6.19	6.36	7.20	7.03	6.95	7.27
4000	6.45	6.17	6.15	6.47	7.22	7.11	7.04	7.28
4200	6.59	6.12	6.07	6.61	7.42	7.00	6.96	7.48
4400	6.62	6.14	6.10	6.65	7.45	7.21	7.13	7.53
4600	6.63	6.33	6.34	6.68	7.56	7.43	7.36	7.61
4800	6.81	6.59	6.63	6.84	7.58	7.26	7.22	7.63
5000	6.99	6.72	6.70	7.01	7.75	7.69	7.57	7.81
5200	6.94	6.62	6.56	6.98	8.34	8.18	8.09	8.41
5400	6.85	6.57	6.56	6.91	8.24	8.02	7.95	8.32
5600	7.23	6.86	6.98	7.28	8.48	8.37	8.25	8.53
5800	7.84	7.37	7.46	7.89	9.19	8.86	8.81	9.23
6000	8.07	7.63	7.61	8.14	9.06	8.78	8.74	9.11
6200	7.92	7.55	7.50	8.00	9.13	8.89	8.82	9.15
6400	7.78	7.43	7.41	7.85	9.32	9.07	9.04	9.36
6600	7.74	7.45	7.42	7.81	9.26	9.04	8.99	9.31
6800	7.75	7.52	7.42	7.84	9.23	9.06	8.99	9.29
7000	7.94	7.57	7.47	8.05	9.34	9.15	9.07	9.41
7200	8.20	7.72	7.66	8.31	9.51	9.31	9.24	9.56
7400	8.26	7.91	7.82	8.39	9.80	9.55	9.49	9.84
7600	8.39	8.09	7.96	8.56	10.51	10.02	9.93	10.55
7800	8.91	8.37	8.24	9.07	10.71	10.38	10.31	10.75
8000	9.57	8.84	8.74	9.70	10.96	10.67	10.55	11.00
8200	10.05	9.40	9.29	10.25	11.81	11.28	11.16	11.84
8400	10.26	9.75	9.61	10.54	12.18	11.69	11.65	12.20
8500	10.29	9.82	9.68	10.58	12.14	11.74	11.68	12.17

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/VCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	2.03	2.01	2.00	2.02	2.01	2.04	2.00	2.01	2.02
0.5	1.32	1.32	1.31	1.32	1.32	1.32	1.31	1.31	1.31
1	1.28	1.28	1.28	1.28	1.28	1.28	1.28	1.28	1.28
5	1.27	1.27	1.26	1.27	1.27	1.27	1.26	1.26	1.26
10	1.27	1.27	1.26	1.27	1.27	1.27	1.26	1.26	1.27
20	1.27	1.27	1.27	1.27	1.27	1.27	1.27	1.26	1.27
50	1.27	1.27	1.26	1.27	1.27	1.27	1.27	1.27	1.27
100	1.25	1.26	1.26	1.26	1.26	1.28	1.27	1.27	1.27
200	1.20	1.21	1.21	1.21	1.21	1.28	1.27	1.27	1.27
400	1.03	1.03	1.04	1.03	1.03	1.26	1.25	1.25	1.24
600	1.22	1.20	1.18	1.19	1.19	1.17	1.19	1.18	1.17
800	1.31	1.27	1.31	1.31	1.28	1.05	1.08	1.08	1.06
1000	1.18	1.12	1.18	1.19	1.14	1.07	1.05	1.04	1.05
1200	1.12	1.08	1.07	1.07	1.05	1.15	1.17	1.16	1.12
1400	1.20	1.12	1.25	1.26	1.14	1.15	1.26	1.24	1.14
1600	1.15	1.21	1.22	1.23	1.21	1.15	1.29	1.27	1.16
1800	1.03	1.25	1.08	1.07	1.23	1.22	1.23	1.22	1.23
2000	1.04	1.10	1.09	1.10	1.08	1.29	1.12	1.13	1.28
2200	1.06	1.25	1.08	1.10	1.24	1.27	1.06	1.08	1.26
2400	1.03	1.33	1.14	1.12	1.32	1.21	1.07	1.07	1.19
2600	1.21	1.19	1.14	1.12	1.20	1.19	1.06	1.06	1.18
2800	1.27	1.20	1.15	1.12	1.21	1.20	1.10	1.10	1.18
3000	1.12	1.13	1.24	1.21	1.15	1.14	1.18	1.17	1.13
3200	1.41	1.04	1.24	1.22	1.05	1.05	1.22	1.21	1.02
3400	1.56	1.03	1.29	1.28	1.01	1.12	1.19	1.18	1.07
3600	1.30	1.17	1.29	1.32	1.15	1.13	1.16	1.16	1.09
3800	1.53	1.21	1.18	1.22	1.21	1.07	1.27	1.27	1.04
4000	1.61	1.18	1.28	1.32	1.17	1.19	1.41	1.42	1.18
4200	1.40	1.41	1.35	1.44	1.41	1.40	1.49	1.50	1.37
4400	1.45	1.38	1.16	1.22	1.43	1.51	1.41	1.41	1.49
4600	1.34	1.15	1.12	1.20	1.19	1.40	1.20	1.19	1.43
4800	1.37	1.39	1.32	1.40	1.44	1.14	1.06	1.07	1.19
5000	1.14	1.29	1.21	1.19	1.34	1.14	1.28	1.27	1.13
5200	1.25	1.06	1.07	1.14	1.09	1.31	1.39	1.37	1.33
5400	1.30	1.21	1.22	1.27	1.27	1.25	1.28	1.27	1.32
5600	1.19	1.10	1.20	1.12	1.04	1.08	1.09	1.11	1.09
5800	1.58	1.26	1.16	1.20	1.37	1.23	1.21	1.20	1.22
6000	1.48	1.20	1.13	1.18	1.28	1.35	1.30	1.29	1.36
6200	1.35	1.12	1.08	1.07	1.23	1.28	1.25	1.22	1.31
6400	1.49	1.29	1.12	1.22	1.37	1.15	1.12	1.09	1.17
6600	1.45	1.24	1.12	1.18	1.21	1.19	1.15	1.15	1.19
6800	1.38	1.20	1.10	1.13	1.14	1.21	1.20	1.19	1.20
7000	1.23	1.21	1.18	1.15	1.10	1.17	1.17	1.15	1.15
7200	1.26	1.19	1.18	1.11	1.09	1.08	1.10	1.07	1.08
7400	1.57	1.28	1.36	1.24	1.21	1.07	1.05	1.02	1.05
7600	1.59	1.12	1.47	1.27	1.16	1.19	1.20	1.16	1.19
7800	1.34	1.15	1.30	1.11	1.05	1.20	1.40	1.34	1.24
8000	1.50	1.19	1.50	1.27	1.13	1.08	1.51	1.46	1.13
8200	1.58	1.23	1.59	1.39	1.11	1.20	1.44	1.43	1.13
8400	1.27	1.59	1.31	1.18	1.42	1.42	1.26	1.28	1.33
8500	1.11	1.63	1.31	1.14	1.46	1.49	1.19	1.21	1.41

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	2.03	2.03	2.01	2.01	2.01	2.00	2.01	1.99
0.5	1.32	1.32	1.32	1.32	1.31	1.33	1.32	1.32
1	1.29	1.28	1.29	1.29	1.28	1.29	1.28	1.28
5	1.27	1.27	1.28	1.27	1.26	1.28	1.27	1.27
10	1.27	1.27	1.28	1.27	1.27	1.28	1.27	1.27
20	1.27	1.27	1.28	1.27	1.27	1.28	1.27	1.27
50	1.28	1.27	1.28	1.28	1.27	1.28	1.27	1.27
100	1.28	1.27	1.28	1.28	1.26	1.27	1.26	1.26
200	1.29	1.28	1.28	1.28	1.22	1.22	1.21	1.22
400	1.26	1.25	1.25	1.25	1.05	1.05	1.04	1.04
600	1.17	1.18	1.17	1.17	1.21	1.21	1.19	1.20
800	1.04	1.08	1.06	1.04	1.30	1.34	1.31	1.29
1000	1.08	1.06	1.08	1.08	1.13	1.17	1.18	1.14
1200	1.15	1.18	1.20	1.16	1.10	1.12	1.08	1.09
1400	1.14	1.28	1.26	1.15	1.17	1.31	1.28	1.17
1600	1.15	1.30	1.25	1.14	1.21	1.22	1.25	1.21
1800	1.25	1.24	1.17	1.22	1.24	1.05	1.07	1.23
2000	1.32	1.14	1.12	1.30	1.09	1.12	1.08	1.09
2200	1.30	1.09	1.14	1.30	1.25	1.03	1.08	1.24
2400	1.23	1.08	1.14	1.23	1.32	1.16	1.14	1.33
2600	1.20	1.07	1.14	1.20	1.18	1.20	1.15	1.20
2800	1.19	1.12	1.19	1.19	1.17	1.19	1.14	1.20
3000	1.12	1.20	1.25	1.12	1.11	1.28	1.22	1.14
3200	1.01	1.23	1.27	1.01	1.03	1.28	1.23	1.06
3400	1.09	1.19	1.21	1.10	1.03	1.34	1.28	1.03
3600	1.10	1.14	1.18	1.11	1.17	1.34	1.31	1.17
3800	1.06	1.23	1.28	1.07	1.20	1.21	1.19	1.23
4000	1.19	1.37	1.41	1.19	1.14	1.32	1.30	1.16
4200	1.39	1.47	1.47	1.37	1.38	1.36	1.40	1.39
4400	1.52	1.45	1.37	1.49	1.36	1.12	1.17	1.39
4600	1.44	1.29	1.17	1.45	1.15	1.17	1.19	1.16
4800	1.18	1.07	1.04	1.23	1.39	1.28	1.34	1.39
5000	1.09	1.18	1.21	1.06	1.29	1.16	1.15	1.31
5200	1.27	1.34	1.29	1.24	1.07	1.10	1.14	1.04
5400	1.24	1.33	1.21	1.25	1.23	1.21	1.24	1.23
5600	1.09	1.17	1.14	1.12	1.10	1.20	1.13	1.13
5800	1.22	1.15	1.22	1.22	1.23	1.12	1.16	1.20
6000	1.33	1.21	1.25	1.30	1.18	1.13	1.14	1.17
6200	1.26	1.18	1.17	1.25	1.13	1.08	1.06	1.08
6400	1.13	1.05	1.04	1.11	1.27	1.11	1.17	1.26
6600	1.15	1.09	1.08	1.11	1.18	1.15	1.14	1.21
6800	1.19	1.12	1.13	1.18	1.14	1.13	1.10	1.18
7000	1.20	1.10	1.18	1.25	1.14	1.20	1.15	1.20
7200	1.12	1.11	1.16	1.20	1.11	1.20	1.12	1.17
7400	1.09	1.08	1.10	1.16	1.21	1.36	1.26	1.27
7600	1.22	1.08	1.26	1.30	1.12	1.43	1.28	1.15
7800	1.23	1.31	1.50	1.33	1.10	1.28	1.13	1.14
8000	1.07	1.51	1.58	1.14	1.16	1.56	1.35	1.21
8200	1.18	1.54	1.44	1.15	1.11	1.59	1.39	1.11
8400	1.43	1.40	1.26	1.42	1.41	1.35	1.17	1.44
8500	1.50	1.33	1.25	1.52	1.45	1.42	1.19	1.50

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	1.96	1.46	1.53	1.52	1.49	1.54	1.50	1.50	1.55
0.5	1.23	1.13	1.23	1.20	1.18	1.21	1.20	1.20	1.24
1	1.18	1.11	1.22	1.18	1.17	1.20	1.19	1.19	1.22
5	1.17	1.10	1.22	1.18	1.16	1.19	1.19	1.18	1.22
10	1.17	1.10	1.22	1.18	1.16	1.19	1.19	1.18	1.22
20	1.16	1.10	1.22	1.18	1.16	1.19	1.18	1.18	1.22
50	1.16	1.10	1.22	1.18	1.16	1.19	1.19	1.18	1.22
100	1.16	1.10	1.22	1.18	1.16	1.19	1.18	1.18	1.22
200	1.16	1.10	1.22	1.18	1.16	1.19	1.18	1.18	1.22
400	1.15	1.09	1.20	1.17	1.15	1.18	1.18	1.17	1.21
600	1.14	1.09	1.19	1.16	1.14	1.17	1.17	1.16	1.20
800	1.14	1.08	1.18	1.15	1.14	1.16	1.16	1.16	1.19
1000	1.13	1.08	1.17	1.14	1.13	1.15	1.16	1.15	1.19
1200	1.12	1.08	1.16	1.13	1.12	1.14	1.15	1.15	1.18
1400	1.11	1.08	1.15	1.13	1.12	1.14	1.15	1.14	1.17
1600	1.10	1.08	1.14	1.12	1.11	1.13	1.14	1.14	1.16
1800	1.10	1.08	1.13	1.11	1.11	1.12	1.14	1.13	1.15
2000	1.10	1.08	1.11	1.10	1.10	1.11	1.14	1.13	1.14
2200	1.09	1.08	1.10	1.10	1.10	1.10	1.13	1.12	1.13
2400	1.09	1.08	1.09	1.09	1.09	1.09	1.12	1.12	1.12
2600	1.09	1.08	1.08	1.08	1.08	1.08	1.12	1.11	1.11
2800	1.09	1.08	1.07	1.07	1.08	1.07	1.11	1.11	1.10
3000	1.09	1.08	1.06	1.07	1.07	1.07	1.10	1.10	1.09
3200	1.10	1.08	1.06	1.06	1.06	1.05	1.09	1.09	1.08
3400	1.11	1.07	1.07	1.05	1.05	1.04	1.08	1.09	1.07
3600	1.12	1.07	1.08	1.05	1.05	1.04	1.08	1.08	1.07
3800	1.14	1.07	1.08	1.05	1.05	1.03	1.07	1.08	1.07
4000	1.15	1.06	1.09	1.05	1.05	1.03	1.08	1.08	1.06
4200	1.16	1.06	1.10	1.05	1.06	1.03	1.08	1.08	1.07
4400	1.17	1.06	1.10	1.04	1.06	1.02	1.09	1.07	1.06
4600	1.18	1.06	1.11	1.04	1.06	1.02	1.08	1.07	1.06
4800	1.19	1.06	1.11	1.04	1.07	1.02	1.09	1.06	1.05
5000	1.20	1.06	1.10	1.04	1.07	1.02	1.08	1.06	1.03
5200	1.20	1.06	1.11	1.03	1.06	1.01	1.06	1.04	1.02
5400	1.20	1.06	1.11	1.04	1.05	1.01	1.05	1.04	1.01
5600	1.20	1.06	1.11	1.02	1.05	1.01	1.04	1.02	1.01
5800	1.20	1.08	1.12	1.05	1.04	1.03	1.02	1.04	1.04
6000	1.19	1.08	1.14	1.04	1.02	1.03	1.03	1.03	1.05
6200	1.18	1.09	1.15	1.05	1.03	1.06	1.04	1.06	1.07
6400	1.18	1.12	1.18	1.08	1.05	1.08	1.08	1.09	1.10
6600	1.17	1.14	1.20	1.08	1.08	1.09	1.11	1.10	1.13
6800	1.17	1.17	1.22	1.11	1.11	1.12	1.14	1.14	1.14
7000	1.17	1.20	1.24	1.13	1.13	1.13	1.16	1.16	1.16
7200	1.14	1.24	1.26	1.15	1.17	1.16	1.19	1.19	1.18
7400	1.13	1.27	1.29	1.18	1.21	1.19	1.23	1.22	1.21
7600	1.12	1.31	1.32	1.20	1.25	1.21	1.25	1.26	1.23
7800	1.11	1.35	1.35	1.23	1.29	1.24	1.29	1.29	1.26
8000	1.11	1.39	1.37	1.26	1.33	1.27	1.31	1.33	1.28
8200	1.11	1.43	1.39	1.29	1.37	1.30	1.34	1.36	1.31
8400	1.12	1.47	1.40	1.31	1.39	1.32	1.35	1.39	1.32
8500	1.12	1.49	1.40	1.32	1.40	1.33	1.36	1.40	1.32

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	1.52	1.53	1.49	1.46	1.52	1.45	1.50	1.48
0.5	1.19	1.21	1.18	1.14	1.22	1.13	1.19	1.19
1	1.17	1.20	1.16	1.12	1.20	1.11	1.18	1.17
5	1.16	1.19	1.16	1.12	1.20	1.11	1.17	1.17
10	1.16	1.19	1.16	1.12	1.20	1.11	1.17	1.17
20	1.16	1.19	1.16	1.12	1.20	1.11	1.17	1.17
50	1.16	1.19	1.16	1.12	1.20	1.10	1.17	1.17
100	1.17	1.19	1.16	1.12	1.20	1.11	1.17	1.17
200	1.16	1.19	1.16	1.12	1.20	1.11	1.17	1.17
400	1.15	1.18	1.15	1.11	1.18	1.10	1.16	1.15
600	1.14	1.17	1.14	1.10	1.18	1.09	1.15	1.15
800	1.13	1.16	1.13	1.10	1.17	1.09	1.15	1.14
1000	1.13	1.16	1.12	1.10	1.16	1.09	1.14	1.14
1200	1.12	1.15	1.11	1.09	1.15	1.09	1.13	1.13
1400	1.11	1.14	1.10	1.09	1.14	1.09	1.12	1.12
1600	1.10	1.13	1.09	1.09	1.13	1.09	1.11	1.12
1800	1.09	1.12	1.08	1.09	1.12	1.09	1.11	1.11
2000	1.08	1.12	1.07	1.08	1.10	1.09	1.10	1.11
2200	1.08	1.11	1.07	1.08	1.10	1.09	1.09	1.10
2400	1.07	1.10	1.06	1.08	1.08	1.09	1.08	1.09
2600	1.07	1.09	1.05	1.08	1.07	1.09	1.07	1.08
2800	1.06	1.09	1.05	1.08	1.06	1.08	1.06	1.07
3000	1.05	1.08	1.05	1.07	1.05	1.08	1.05	1.06
3200	1.05	1.07	1.04	1.07	1.05	1.07	1.05	1.05
3400	1.04	1.07	1.04	1.06	1.04	1.06	1.04	1.04
3600	1.04	1.07	1.04	1.05	1.04	1.05	1.04	1.03
3800	1.04	1.07	1.04	1.05	1.04	1.04	1.04	1.03
4000	1.04	1.07	1.04	1.06	1.04	1.02	1.04	1.02
4200	1.05	1.08	1.05	1.07	1.04	1.02	1.05	1.03
4400	1.04	1.08	1.04	1.08	1.04	1.02	1.04	1.03
4600	1.04	1.08	1.04	1.08	1.04	1.03	1.05	1.03
4800	1.04	1.09	1.03	1.10	1.04	1.05	1.05	1.03
5000	1.04	1.07	1.04	1.09	1.04	1.06	1.05	1.03
5200	1.03	1.06	1.03	1.08	1.03	1.09	1.05	1.05
5400	1.02	1.04	1.04	1.07	1.05	1.10	1.06	1.04
5600	1.01	1.03	1.03	1.06	1.05	1.13	1.06	1.06
5800	1.03	1.02	1.07	1.04	1.07	1.14	1.09	1.07
6000	1.03	1.04	1.07	1.05	1.07	1.17	1.09	1.08
6200	1.06	1.07	1.10	1.06	1.09	1.19	1.10	1.10
6400	1.09	1.11	1.13	1.10	1.10	1.21	1.12	1.11
6600	1.10	1.14	1.15	1.14	1.12	1.24	1.13	1.13
6800	1.13	1.17	1.19	1.17	1.15	1.26	1.15	1.15
7000	1.15	1.20	1.21	1.21	1.17	1.29	1.17	1.18
7200	1.18	1.23	1.24	1.25	1.20	1.32	1.19	1.20
7400	1.21	1.27	1.28	1.30	1.23	1.35	1.21	1.23
7600	1.24	1.30	1.31	1.34	1.25	1.39	1.23	1.26
7800	1.27	1.34	1.35	1.39	1.29	1.43	1.25	1.30
8000	1.31	1.38	1.38	1.42	1.32	1.46	1.27	1.33
8200	1.33	1.41	1.41	1.46	1.35	1.50	1.29	1.36
8400	1.36	1.42	1.42	1.46	1.37	1.53	1.31	1.39
8500	1.37	1.42	1.43	1.47	1.38	1.54	1.31	1.40

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION COM to terminated port								
	(dB)								
	COM-J1 @J16 Active	COM-J2 @J1 Active	COM-J4 @J3 Active	COM-J5 @J6 Active	COM-J7 @J6 Active	COM-J8 @J7 Active	COM-J10 @J9 Active	COM-J13 @J12 Active	COM-J15 @J14 Active
0.1	102.34	100.44	96.93	93.25	93.25	94.84	107.28	98.64	94.80
0.5	103.20	97.10	94.72	101.72	101.72	106.14	93.76	101.81	100.85
1	98.27	98.46	91.39	95.36	95.36	93.25	97.93	91.35	97.97
5	95.56	105.26	95.87	99.55	99.55	102.91	98.22	116.91	102.31
10	108.28	109.56	102.85	112.07	112.07	105.68	101.80	105.94	103.06
20	115.34	102.98	100.21	102.66	102.66	107.56	100.96	101.78	99.39
50	111.18	104.81	96.97	102.89	102.89	100.57	97.31	101.54	100.19
100	105.31	104.03	94.32	100.91	100.91	102.69	100.40	100.93	101.33
200	132.22	111.49	97.47	101.55	101.55	102.16	95.75	99.54	98.17
400	112.38	110.41	97.97	104.42	104.42	108.62	97.40	98.61	98.99
600	119.97	113.18	100.31	109.62	109.62	108.75	95.59	96.67	102.17
800	109.29	111.36	102.63	104.61	104.61	108.37	95.36	96.73	102.36
1000	111.87	114.94	102.24	113.68	113.68	109.90	95.81	97.86	100.69
1200	111.37	117.78	103.14	114.07	114.07	112.24	97.25	99.16	100.37
1400	116.57	114.66	110.64	109.97	109.97	113.22	99.31	98.62	98.37
1600	119.52	107.68	106.07	106.83	106.83	105.98	97.32	97.26	97.40
1800	109.89	110.96	105.62	110.44	110.44	106.82	100.39	98.93	102.30
2000	106.80	122.87	103.84	112.13	112.13	99.90	98.67	97.93	100.38
2200	116.49	108.72	100.88	105.87	105.87	100.91	98.93	98.72	102.16
2400	110.59	106.71	99.59	104.54	104.54	101.45	98.75	96.70	100.64
2600	126.85	100.80	95.68	109.15	109.15	97.12	99.87	96.80	101.30
2800	108.89	99.93	94.63	105.93	105.93	95.21	97.42	97.65	101.57
3000	113.00	101.16	94.41	112.88	112.88	93.61	95.92	97.50	105.31
3200	117.58	97.46	93.74	111.75	111.75	92.47	93.64	97.63	103.63
3400	104.93	98.74	91.20	106.97	106.97	91.71	92.82	95.63	106.36
3600	107.28	96.80	90.24	123.61	123.61	89.95	92.03	96.39	102.91
3800	114.25	100.04	89.04	114.37	114.37	89.01	90.90	94.43	106.87
4000	110.02	95.46	89.00	108.94	108.94	87.34	90.59	96.32	107.44
4200	110.66	95.18	88.40	102.85	102.85	86.93	89.80	97.82	103.31
4400	105.90	93.61	86.88	101.91	101.91	85.77	89.86	96.21	109.22
4600	113.45	90.50	86.08	106.69	106.69	85.13	89.43	95.25	104.42
4800	109.06	89.13	85.42	101.66	101.66	84.57	88.54	98.21	103.71
5000	113.72	90.57	85.67	99.86	99.86	83.95	89.21	95.52	99.68
5200	119.89	89.64	85.37	98.39	98.39	83.80	88.68	99.14	99.39
5400	108.83	89.46	84.12	101.08	101.08	82.93	90.26	96.55	97.20
5600	129.88	88.31	83.86	97.47	97.47	83.09	90.64	97.20	96.66
5800	107.30	88.76	83.54	95.70	95.70	82.46	91.38	100.56	97.12
6000	123.69	88.18	82.78	99.80	99.80	82.21	92.87	98.50	95.39
6200	110.38	87.46	81.93	97.36	97.36	81.33	90.48	99.20	92.34
6400	113.06	86.28	81.27	96.15	96.15	80.46	88.87	96.55	93.15
6600	117.95	84.93	79.89	92.00	92.00	79.42	86.06	99.06	91.85
6800	106.34	83.84	79.15	90.00	90.00	78.85	83.11	96.11	90.92
7000	111.13	82.05	77.97	87.76	87.76	77.74	81.14	95.61	89.34
7200	104.15	80.47	77.13	86.16	86.16	76.53	79.46	93.66	88.58
7400	104.90	80.12	75.81	84.50	84.50	75.27	77.77	91.81	87.48
7600	101.05	78.67	74.50	82.27	82.27	73.95	76.55	90.59	85.99
7800	101.32	78.32	73.09	80.91	80.91	72.85	76.05	90.05	85.19
8000	100.08	76.70	71.74	80.23	80.23	71.37	75.55	90.99	84.23
8200	94.00	76.20	70.43	78.57	78.57	70.26	74.69	90.07	83.05
8400	96.16	75.10	69.40	77.97	77.97	68.80	74.06	89.21	81.71
8500	93.83	74.49	68.54	77.49	77.49	68.24	73.17	87.69	81.09

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Solid State USB RF SP16T Switch

USB-1SP16T-83H

Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION between adjacent ports								
	(dB)								
	J1-J2 @J1 Active	J3-J4 @J3 Active	J5-J6 @J5 Active	J6-J7 @J6 Active	J8-J9 @J8 Active	J10-J11 @J10 Active	J12-J13 @J12 Active	J14-J15 @J14 Active	J15-J16 @J15 Active
0.1	127.16	98.88	117.95	108.32	97.72	101.79	98.22	103.70	98.35
0.5	118.20	108.83	94.15	97.19	107.76	97.11	95.90	90.79	91.91
1	89.21	97.26	99.21	96.83	102.95	101.00	98.85	106.38	99.90
5	96.32	101.88	103.02	95.51	93.01	98.71	97.02	95.76	92.95
10	104.36	100.44	101.14	99.09	102.90	97.08	101.04	100.48	96.91
20	105.60	96.01	98.02	100.04	98.26	99.07	99.05	95.51	97.02
50	98.89	94.60	96.88	97.96	94.09	95.85	96.18	95.90	96.10
100	102.36	92.64	97.09	96.92	93.99	96.99	95.96	97.36	97.65
200	104.22	92.42	96.90	97.92	92.65	94.72	97.25	95.27	97.45
400	111.59	94.29	97.15	101.22	91.45	94.43	92.40	96.13	97.72
600	108.23	95.34	96.65	100.90	91.20	93.88	91.52	98.29	101.20
800	109.53	94.13	101.84	102.95	92.45	96.02	92.40	95.18	99.22
1000	119.06	95.01	102.83	104.84	92.92	96.62	91.79	95.76	97.93
1200	114.76	94.41	100.40	118.42	93.35	94.98	90.98	95.20	96.34
1400	108.11	93.98	100.88	104.64	92.05	95.45	91.95	96.47	95.19
1600	104.14	94.32	100.90	111.11	93.94	95.19	91.96	95.17	95.74
1800	102.89	97.09	98.82	106.39	93.99	98.14	93.30	94.07	97.35
2000	106.04	98.34	100.18	108.69	93.73	95.24	90.81	95.84	101.82
2200	101.50	102.16	97.22	101.77	94.26	95.19	90.65	94.14	111.42
2400	100.76	107.30	100.83	100.27	92.31	94.35	89.75	92.86	106.44
2600	99.60	100.41	100.90	102.06	93.51	93.20	91.26	92.70	99.01
2800	102.26	97.43	101.14	100.44	92.48	93.27	91.99	93.42	95.50
3000	98.42	93.13	101.45	97.32	94.95	91.98	92.51	92.91	91.49
3200	94.43	93.05	103.58	97.08	92.31	90.98	90.40	94.04	90.49
3400	93.49	93.66	96.35	97.38	90.81	92.97	91.33	97.12	90.20
3600	94.55	92.36	95.54	98.10	92.67	93.86	90.19	100.31	89.04
3800	94.38	94.70	95.05	96.59	92.46	93.91	90.25	116.03	90.91
4000	92.05	96.12	92.48	95.45	91.90	96.94	89.14	100.86	92.11
4200	91.95	95.19	91.17	93.08	91.26	98.83	88.93	93.84	92.31
4400	91.97	102.31	89.65	92.70	90.93	95.17	88.71	90.82	99.24
4600	93.84	98.95	90.08	91.05	93.73	93.24	90.87	88.55	97.15
4800	90.78	95.75	90.04	89.62	93.11	91.50	91.76	87.99	92.60
5000	89.13	107.50	92.45	89.70	92.13	90.94	90.80	85.10	101.33
5200	91.04	95.12	90.34	87.88	91.10	88.11	91.12	85.28	91.86
5400	89.65	92.74	88.22	86.28	92.06	86.15	92.03	84.96	90.37
5600	88.06	100.66	87.18	86.38	92.91	84.74	89.37	84.13	101.61
5800	87.51	99.87	86.96	85.35	93.27	84.01	89.51	83.69	93.57
6000	91.51	99.71	87.63	85.37	92.55	83.64	90.66	84.22	96.54
6200	86.39	91.06	88.49	84.57	93.31	83.55	90.63	84.08	99.99
6400	85.97	89.50	86.38	83.98	92.94	81.87	89.88	84.25	92.92
6600	86.12	89.07	85.54	82.11	91.20	81.36	89.76	84.86	94.32
6800	85.18	85.27	84.20	81.05	91.79	80.63	88.99	85.23	87.64
7000	84.18	83.69	84.36	79.73	93.39	80.07	86.95	84.08	84.78
7200	82.52	81.23	84.02	78.51	89.44	79.31	86.26	83.59	81.81
7400	80.36	80.84	83.22	77.39	90.39	78.35	86.04	81.43	80.63
7600	80.31	83.19	81.38	75.65	88.37	76.66	85.08	79.02	81.65
7800	78.79	78.09	80.00	73.64	89.37	74.70	85.35	78.00	77.84
8000	75.76	75.72	80.21	71.99	90.32	73.08	84.21	74.86	76.01
8200	75.72	78.64	81.02	71.13	91.93	72.21	84.71	72.81	79.45
8400	76.86	78.11	81.23	70.24	87.78	70.72	82.80	71.29	78.47
8500	75.29	74.72	81.65	69.46	86.80	70.23	83.01	70.93	76.44

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Solid State USB RF SP16T Switch

USB-1SP16T-83H


Typical Performance Curves

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm


Insertion Loss (ports J1-J8)




Insertion Loss (ports J9-J16)



Isolation COM to Terminated port



Isolation



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp




Solid State USB RF SP16T Switch

USB-1SP16T-83H


Typical Performance Curves

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm


VSWR, Internally Terminated Ports




VSWR, Internally Terminated Ports



VSWR, Active Ports



VSWR, Active Ports



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MGStore/terms.jsp




Solid State USB RF SP16T Switch

USB-1SP16T-83H


Typical Performance Curves

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm


Insertion Loss (ports J1-J8)




Insertion Loss (ports J9-J16)



Isolation COM to Terminated port



Isolation



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Solid State USB RF SP16T Switch

USB-1SP16T-83H


Typical Performance Curves

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm


VSWR, Internally Terminated Ports




VSWR, Internally Terminated Ports



VSWR, Active Ports



VSWR, Active Ports



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp




Solid State USB RF SP16T Switch

USB-1SP16T-83H


Typical Performance Curves

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm


Insertion Loss (ports J1-J8)




Insertion Loss (ports J9-J16)



Isolation COM to Terminated port



Isolation



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MGStore/terms.jsp




Solid State USB RF SP16T Switch

USB-1SP16T-83H


Typical Performance Curves

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm


VSWR, Internally Terminated Ports




VSWR, Internally Terminated Ports



VSWR, Active Ports



VSWR, Active Ports



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp




Case Style

RB

Outline Dimensions

RB2574-2



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
RB2574-2	10.98 (278.9)	2.50 (63.5)	.60 (15.2)	.69 (17.5)	.640 (16.26)	.278 (7.06)	.10 (2.54)	10.780 (273.81)	1.500 (38.10)	.50 (12.7)	.106 (2.69)	5.49 (139.45)	.73 (18.5)

CASE#	P	WT. GRAMS
RB2574-2	2.25 (57.15)	650

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Aluminum alloy.
2. Case finish for RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



Environmental Specifications **ENV55**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 60° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3