



ULTRA HIGH DYNAMIC RANGE, SHUTDOWN


# Monolithic Amplifier

## TSS-23LN+

50Ω 30 MHz to 2 GHz

### THE BIG DEAL

- High IP3, +36.4 dBm typ. at 1GHz
- Gain, 21.5 dB typ. at 1 GHz
- Low noise figure, 1.2 dB at 1 GHz
- Low voltage, +5V and +3V
- Shutdown feature



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

### APPLICATIONS

- Base station infrastructure
- CATV
- Cellular

### PRODUCT OVERVIEW

TSS-23LN+ (RoHS compliant) is an advanced wideband amplifier with shutdown feature. It is fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the TSS-23LN+ has good input and output return loss over a broad frequency range. TSS-23LN+ is enclosed in a 3mm x 3mm, 12-lead MCLP package and has very good thermal performance.

### KEY FEATURES

| Feature   | Advantages   |
|---|--|
| Broad Band: 30MHz to 2GHz   | Broadband covering primary wireless communications bands: VHF, UHF, Cellular   |
| Extremely High IP3<br>+39.8 dBm typical at 30 MHz<br>+36.4 dBm typical at 1 GHz | The TSS-23LN+ matches industry leading IP3 performance relative to device size and power consumption. The combination of the design and E-PHEMT Structure provides enhanced linearity over a broad frequency range as evidence in the IP3 being approximately 11-17 dB above the P1dB point. This feature makes this amplifier ideal for use in: <ul style="list-style-type: none"> <li>• Driver amplifiers for complex waveform up converter paths</li> <li>• Drivers in linearized transmit systems</li> <li>• Secondary amplifiers in ultra-High Dynamic range receivers</li> </ul> |
| Shutdown feature  | Allow users to turn on and off the amplifier with pulsed signals while keeping the power supply at constant voltage to minimize DC power consumption   |
| Low Noise Figure, 1.2 dB at 1 GHz   | Enables lower system noise figure performance and along with High OIP3 provides high dynamic range   |
| Low Supply Voltage  | TSS-23LN+ supports low supply voltage operation which indicate low power consumption.  |

REV. B  
ECO-022590  
TSS-23LN+  
MCL NY  
240731





ULTRA HIGH DYNAMIC RANGE, SHUTDOWN

# Monolithic Amplifier

TSS-23LN+

Mini-Circuits

## ELECTRICAL SPECIFICATIONS<sup>1</sup> AT +25°C & 50Ω, UNLESS NOTED OTHERWISE

| Parameter  | Condition (MHz) | Amplifier-ON |       |       | Amplifier-OFF | Amplifier-ON | Amplifier-OFF | Units   |
|--|-----------------|--------------|-------|-------|---------------|--------------|---------------|---------|
|  |                 | VDD = +5V    |       |       | VDD = +5V     | VDD = +3V    | VDD = +3V     |         |
|  |                 | Min.         | Typ.  | Max.  | Typ.          | Typ.         | Typ.          |         |
| Frequency Range  |                 | 30           |       | 2000  | 30-2000       | 30-2000      | 30-2000       | MHz     |
| Noise Figure   | 30              |              | 1.2   |       |               | 1.1          |               | dB      |
|  | 500             |              | 1.2   |       |               | 1.2          |               |         |
|  | 1000            |              | 1.2   |       |               | 1.2          |               |         |
|  | 1500            |              | 1.3   |       |               | 1.4          |               |         |
|  | 2000            |              | 1.4   |       |               | 1.5          |               |         |
| Gain   | 30              | 20.7         | 23.1  | 25.3  | -21           | 22.4         | -21           | dB      |
|  | 500             | —            | 22.2  | —     | -21           | 21.4         | -21           |         |
|  | 1000            | 19.2         | 21.5  | 23.4  | -23           | 20.2         | -24           |         |
|  | 1500            | —            | 20.7  | —     | -26           | 19.1         | -26           |         |
|  | 2000            | 17.6         | 19.9  | 21.6  | -28           | 18           | -27           |         |
| Reversed Isolation                                     | 30-2000         |              | 27    |       | 26            | 27           | 25            | dB      |
| Input Return Loss                                      | 30              |              | 12    |       | 12            | 12           | 12            | dB      |
|  | 500             |              | 12    |       | 12            | 11           | 12            |         |
|  | 1000            |              | 10    |       | 12            | 8            | 12            |         |
|  | 1500            |              | 10    |       | 15            | 8            | 15            |         |
|  | 2000            |              | 11    |       | 19            | 8            | 19            |         |
| Output Return Loss                                     | 30              |              | 15    |       | 2             | 17           | 2             | dB      |
|  | 500             |              | 15    |       | 2             | 19           | 2             |         |
|  | 1000            |              | 16    |       | 2             | 18           | 2             |         |
|  | 1500            |              | 12    |       | 2             | 11           | 2             |         |
|  | 2000            |              | 10    |       | 2             | 9            | 2             |         |
| Output Power @1dB compression AMP-ON                   | 30              |              | +22.8 |       |               | +17.1        |               | dBm     |
|  | 500             |              | +23.8 |       |               | +18.9        |               |         |
|  | 1000            |              | +24.1 |       |               | +19          |               |         |
|  | 1500            |              | +23.5 |       |               | +18.8        |               |         |
|  | 2000            |              | +22.8 |       |               | +18.1        |               |         |
| Output IP3 (Pout = 0dBm/Tone)                          | 30              | —            | +39.8 |       |               | +34.1        |               | dBm     |
|  | 500             | —            | +38.0 |       |               | +33.7        |               |         |
|  | 1000            | —            | +36.4 |       |               | +31.8        |               |         |
|  | 1500            | +33          | +35.5 |       |               | +31.1        |               |         |
|  | 2000            | —            | +34.0 |       |               | +30.3        |               |         |
| Device Operating Voltage (VDD)                         |                 | +4.75        | +5    | +5.25 | +5            | +3           | +3            | V       |
| Device Operating Current (ID)                          |                 |              | 139   | 163   | 5             | 74           | 3             | mA      |
| Control Voltage (VG)                                   |                 |              | 0     |       | +5            | 0            | +5            | V       |
| DC Current (ID) Variation Vs. Temperature <sup>2</sup> |                 |              | -13   |       |               | 27           |               | uA/degC |
| DC Current (ID) Variation Vs. Voltage                  |                 |              | 0.034 |       |               | 0.033        |               | mA/mV   |
| Thermal Resistance                                     |                 |              | 23.3  |       |               | 23.3         |               | degC/W  |

1. Measured on Mini-Circuits Characterization test board TB-TSS-23LN+. See Characterization Test Circuit (Fig. 1)

2. (Current at 105°C – Current at -45°C)/150

## ABSOLUTE MAXIMUM RATINGS<sup>3</sup>

| Parameter                                       | Ratings   |
|---|---|
| Operating Temperature (ground lead)             | -40°C to 105°C  |
| Storage Temperature                             | -65°C to 150°C  |
| Total Power Dissipation                         | 3.3W  |
| Input Power                                     | +28 dBm (5 minutes max.)<br>+10 dBm (continuous) for 0.03-1 GHz<br>+13 dBm (continuous) for 1-2 GHz |
| DC Voltage V <sub>DD</sub> <sup>4</sup> (Pad 7) | +10 V   |
| DC Voltage V <sub>G</sub> <sup>5</sup> (Pad 1)  | +10 V   |

3 Permanent damage may occur if these limits are exceeded.

4 Measured by keeping VG=0V.

5 Measured by keeping Vdd=5V.

## CONTROL VOLTAGE (V<sub>G</sub>) FIG. 1

|               | Min. | Typ. | Max. | Units |
|---------------|------|------|------|-------|
| Amplifier-ON  | —    | 0    | 0.7  | V     |
| Amplifier-OFF | 1.9  | 5    | —    | V     |







### SWITCHING SPECIFICATIONS

| Parameter                |                                  | Min. | +5V Typ. | +3V Typ. | Units |
|--------------------------|----------------------------------|------|----------|----------|-------|
| Amplifier ON to Shutdown | OFF TIME (50% Control to 10% RF) | –    | 4.8      | 6.2      | µs    |
|                          | FALL TIME (90 to 10% RF)         | –    | 7.4      | 3.6      |       |
| Amplifier Shutdown to ON | ON TIME (50% Control to 90% RF)  | –    | 95.2     | 144.7    | µs    |
|                          | RISE TIME (10% to 90% RF)        | –    | 60.0     | 200.7    |       |
| Control Voltage Leakage  |                                  | –    | 482.9    | 311.0    | mV    |

### SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



| Function         | Pad Number   | Description                        |
|------------------|--------------|------------------------------------|
| RF-IN            | 3            | RF Input                           |
| RF-OUT and DC-IN | 7            | RF Output and DC Bias              |
| GND              | Paddle       | Connections to ground.             |
| NC               | 2, 4-6, 8-12 | No connection, grounded externally |
| VG               | 1            | Control voltage for shutdown (VG)  |




ULTRA HIGH DYNAMIC RANGE, SHUTDOWN

# Monolithic Amplifier

# TSS-23LN+

## CHARACTERIZATION TEST CIRCUIT / RECOMMENDED APPLICATION CIRCUIT



| Component | Size | Value   | Part Number        | Manufacturer |
|-----------|------|---------|--------------------|--------------|
| C1        | 0402 | 0.1uF   | GRM155R71C104KA88D | Murata       |
| C2        | 0402 | 1.2pF   | GRM1555C1H1R2CA1D  | Murata       |
| C3        | 0402 | 0.1uF   | GRM155R71C104KA88D | Murata       |
| C4        | 0402 | 0.1uF   | GRM155R71C104KA88D | Murata       |
| C5        | 0402 | 1000pF  | GRM1555C1H102JA01D | Murata       |
| C6        | 0402 | 10000pF | GRM155R71E103KA01D | Murata       |
| C7        | 0402 | 0.1uF   | GRM155R71C104KA88D | Murata       |
| L1        | 0805 | 680nH   | 0805LS-681XJLB     | Coilcraft    |
| L2        | 0402 | 1.0nH   | 0402CS-1N0XJLW     | Coilcraft    |
| R1        | 0402 | 1.2KOhm | RK73H1ETTP1201F    | Koa          |

Fig 1. Block diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-TSS-13LN+) Gain, Return loss, Output power at 1dB compression (P1dB) , output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return Loss:  $P_{IN} = -25\text{dBm}$
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +0dBm/tone at output.
3. Switching Time  
 RF Signal:  $P_{IN} = -25\text{ dBm}$ ,  $f_{RF} = 500\text{ MHz}$ .  
 $V_{DD} = +3\text{ & } +5\text{V DC}$ ,  $V_G = \text{Pulse signal at 1 KHz with } V_{HIGH} = +5\text{V, } V_{LOW} = 0\text{V, } 50\% \text{ duty cycle.}$

## PRODUCT MARKING



Marking may contain other features or characters for internal lot control





ULTRA HIGH DYNAMIC RANGE, SHUTDOWN

# Monolithic Amplifier

# TSS-23LN+


ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. [CLICK HERE](#)

|  |  |
|--|--|
| Performance Data                                     | Data Table<br>Swept Graphs<br>S-Parameter (S2P Files) Data Set (.zip file) |
| Case Style   | DQ1225<br>Plastic package, exposed paddle lead finish: Matte-Tin           |
| Tape & Reel<br>Standard quantities available on reel | F66<br>7" reels with 20, 50, 100, 200, 500, 1K, or 2K devices              |
| Suggested Layout for PCB Design                      | PL-619   |
| Evaluation Board                                     | TB-TSS-23LN+   |
| Environmental Ratings                                | ENV08T9  |

### ESD RATING

Human Body Model (HBM): Class 1A (Pass 250 V) in accordance with ANSI/ESD STM 5.1 - 2001

### MSL FLOW CHART



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
  - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
  - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.75V, Id = 64mA @ Temperature = +25°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 20    | 22.55 | 25.80     | 10.51             | 15.85              | 1.03      | 0.53    | 30.81       | 14.56            | 1.13         |
| 30    | 22.27 | 25.29     | 12.15             | 16.81              | 1.03      | 0.50    | 33.06       | 15.77            | 1.07         |
| 40    | 22.07 | 25.00     | 13.12             | 16.48              | 1.03      | 0.48    | 32.74       | 16.96            | 1.04         |
| 50    | 21.92 | 25.08     | 14.05             | 15.81              | 1.04      | 0.50    | 32.52       | 17.66            | 1.09         |
| 60    | 21.86 | 24.80     | 14.18             | 15.84              | 1.04      | 0.47    | 32.93       | 17.76            | 1.08         |
| 70    | 21.81 | 24.75     | 14.40             | 15.66              | 1.04      | 0.47    | 33.12       | 17.98            | 1.09         |
| 80    | 21.77 | 24.66     | 14.56             | 15.63              | 1.04      | 0.46    | 33.16       | 17.97            | 1.13         |
| 90    | 21.74 | 24.76     | 14.68             | 15.57              | 1.04      | 0.47    | 33.59       | 18.03            | 1.16         |
| 100   | 21.71 | 24.68     | 14.74             | 15.54              | 1.04      | 0.46    | 33.89       | 18.02            | 1.15         |
| 150   | 21.64 | 24.73     | 14.61             | 15.65              | 1.05      | 0.48    | 33.29       | 18.18            | 1.22         |
| 200   | 21.58 | 24.76     | 14.20             | 15.93              | 1.05      | 0.50    | 34.22       | 18.24            | 1.17         |
| 250   | 21.53 | 24.78     | 13.65             | 16.37              | 1.05      | 0.51    | 33.83       | 18.33            | 1.16         |
| 300   | 21.47 | 24.84     | 13.05             | 16.85              | 1.05      | 0.53    | 33.09       | 18.46            | 1.16         |
| 350   | 21.40 | 24.90     | 12.39             | 17.53              | 1.05      | 0.56    | 32.82       | 18.44            | 1.19         |
| 400   | 21.32 | 25.04     | 11.77             | 18.29              | 1.06      | 0.59    | 32.84       | 18.36            | 1.21         |
| 450   | 21.23 | 25.16     | 11.17             | 19.18              | 1.06      | 0.62    | 32.38       | 18.19            | 1.18         |
| 500   | 21.13 | 25.29     | 10.57             | 20.16              | 1.07      | 0.66    | 32.51       | 17.98            | 1.20         |
| 550   | 21.02 | 25.45     | 10.05             | 21.11              | 1.07      | 0.70    | 31.91       | 18.26            | 1.20         |
| 600   | 20.90 | 25.54     | 9.57              | 21.97              | 1.07      | 0.73    | 31.67       | 18.09            | 1.26         |
| 650   | 20.78 | 25.66     | 9.13              | 22.43              | 1.08      | 0.76    | 31.19       | 18.17            | 1.27         |
| 700   | 20.65 | 25.82     | 8.78              | 22.44              | 1.08      | 0.79    | 31.21       | 18.06            | 1.25         |
| 750   | 20.50 | 25.93     | 8.44              | 22.00              | 1.09      | 0.82    | 31.08       | 17.93            | 1.24         |
| 800   | 20.36 | 26.01     | 8.17              | 21.12              | 1.09      | 0.85    | 30.91       | 17.88            | 1.32         |
| 850   | 20.22 | 26.18     | 7.94              | 20.09              | 1.10      | 0.87    | 30.65       | 18.02            | 1.27         |
| 900   | 20.09 | 26.30     | 7.72              | 19.00              | 1.10      | 0.90    | 30.36       | 17.94            | 1.27         |
| 950   | 19.97 | 26.41     | 7.52              | 17.98              | 1.10      | 0.92    | 30.62       | 17.89            | 1.27         |
| 1000  | 19.84 | 26.48     | 7.39              | 17.01              | 1.11      | 0.93    | 30.35       | 18.08            | 1.26         |
| 1100  | 19.59 | 26.66     | 7.18              | 15.28              | 1.11      | 0.96    | 30.13       | 17.89            | 1.31         |
| 1200  | 19.35 | 26.80     | 7.10              | 13.84              | 1.12      | 0.97    | 30.04       | 17.89            | 1.36         |
| 1300  | 19.12 | 26.93     | 7.13              | 12.70              | 1.12      | 0.98    | 30.00       | 17.66            | 1.36         |
| 1400  | 18.92 | 27.01     | 7.24              | 11.71              | 1.13      | 0.98    | 29.87       | 17.67            | 1.37         |
| 1500  | 18.73 | 27.07     | 7.43              | 10.88              | 1.13      | 0.97    | 29.76       | 17.80            | 1.38         |
| 1600  | 18.54 | 27.11     | 7.68              | 10.18              | 1.13      | 0.96    | 29.41       | 17.58            | 1.39         |
| 1700  | 18.36 | 27.17     | 7.96              | 9.63               | 1.14      | 0.96    | 29.28       | 17.18            | 1.42         |
| 1800  | 18.15 | 27.21     | 8.19              | 9.20               | 1.14      | 0.95    | 29.49       | 17.42            | 1.42         |
| 1900  | 17.90 | 27.27     | 8.28              | 8.86               | 1.15      | 0.96    | 29.08       | 17.32            | 1.44         |
| 2000  | 17.60 | 27.37     | 8.13              | 8.62               | 1.16      | 0.97    | 28.98       | 17.12            | 1.50         |
| 2100  | 17.22 | 27.51     | 7.69              | 8.47               | 1.17      | 1.00    | 28.57       | 17.00            | 1.57         |
| 2200  | 16.77 | 27.80     | 6.99              | 8.38               | 1.19      | 1.04    | 28.54       | 16.80            | 1.71         |
| 2300  | 16.22 | 28.15     | 6.18              | 8.32               | 1.22      | 1.09    | 28.14       | 16.76            | 1.86         |
| 2400  | 15.57 | 28.46     | 5.35              | 8.31               | 1.24      | 1.14    | 27.77       | 16.54            | 2.03         |
| 2500  | 14.86 | 28.93     | 4.57              | 8.31               | 1.28      | 1.20    | 27.84       | 16.53            | 3.00         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.00V, Id = 73mA @ Temperature = +25°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 20    | 22.74 | 25.90     | 10.52             | 15.57              | 1.03      | 0.52    | 32.76       | 15.76            | 1.16         |
| 30    | 22.45 | 25.37     | 12.04             | 16.35              | 1.03      | 0.49    | 34.88       | 16.98            | 1.13         |
| 40    | 22.24 | 25.17     | 12.91             | 15.92              | 1.03      | 0.48    | 33.86       | 18.16            | 1.08         |
| 50    | 22.09 | 25.43     | 13.62             | 15.26              | 1.05      | 0.51    | 34.02       | 18.75            | 1.08         |
| 60    | 22.03 | 25.00     | 13.85             | 15.29              | 1.04      | 0.47    | 34.94       | 18.84            | 1.09         |
| 70    | 21.97 | 24.92     | 14.08             | 15.11              | 1.04      | 0.46    | 34.98       | 18.95            | 1.11         |
| 80    | 21.93 | 24.80     | 14.20             | 15.08              | 1.04      | 0.45    | 34.69       | 18.91            | 1.13         |
| 90    | 21.91 | 24.87     | 14.30             | 15.00              | 1.04      | 0.46    | 34.66       | 18.98            | 1.18         |
| 100   | 21.88 | 24.84     | 14.35             | 15.00              | 1.04      | 0.46    | 35.65       | 19.04            | 1.17         |
| 150   | 21.81 | 24.84     | 14.27             | 15.08              | 1.04      | 0.47    | 34.88       | 19.11            | 1.12         |
| 200   | 21.75 | 24.91     | 13.98             | 15.32              | 1.05      | 0.49    | 36.52       | 19.25            | 1.17         |
| 250   | 21.70 | 24.86     | 13.49             | 15.72              | 1.05      | 0.49    | 35.19       | 19.34            | 1.17         |
| 300   | 21.65 | 24.96     | 13.03             | 16.13              | 1.05      | 0.52    | 34.53       | 19.40            | 1.16         |
| 350   | 21.59 | 25.02     | 12.47             | 16.71              | 1.05      | 0.54    | 34.69       | 19.38            | 1.17         |
| 400   | 21.52 | 25.18     | 11.94             | 17.36              | 1.06      | 0.58    | 34.35       | 19.29            | 1.18         |
| 450   | 21.44 | 25.23     | 11.39             | 18.10              | 1.06      | 0.60    | 33.97       | 19.14            | 1.19         |
| 500   | 21.35 | 25.41     | 10.83             | 18.97              | 1.06      | 0.64    | 33.79       | 18.92            | 1.21         |
| 550   | 21.25 | 25.51     | 10.36             | 19.81              | 1.07      | 0.67    | 33.11       | 19.23            | 1.21         |
| 600   | 21.15 | 25.62     | 9.88              | 20.69              | 1.07      | 0.70    | 32.96       | 19.04            | 1.26         |
| 650   | 21.03 | 25.71     | 9.46              | 21.40              | 1.07      | 0.73    | 32.91       | 19.04            | 1.27         |
| 700   | 20.91 | 25.85     | 9.11              | 21.87              | 1.08      | 0.76    | 32.61       | 18.94            | 1.24         |
| 750   | 20.78 | 25.97     | 8.78              | 21.93              | 1.09      | 0.79    | 32.36       | 18.89            | 1.23         |
| 800   | 20.64 | 26.11     | 8.50              | 21.55              | 1.09      | 0.82    | 32.23       | 18.77            | 1.19         |
| 850   | 20.52 | 26.27     | 8.26              | 20.89              | 1.10      | 0.85    | 32.18       | 19.01            | 1.25         |
| 900   | 20.39 | 26.35     | 8.03              | 20.02              | 1.10      | 0.87    | 31.73       | 18.94            | 1.23         |
| 950   | 20.28 | 26.53     | 7.83              | 19.05              | 1.11      | 0.89    | 31.91       | 18.80            | 1.25         |
| 1000  | 20.15 | 26.57     | 7.68              | 18.06              | 1.11      | 0.91    | 31.67       | 19.02            | 1.25         |
| 1100  | 19.91 | 26.76     | 7.46              | 16.26              | 1.12      | 0.94    | 31.41       | 18.92            | 1.31         |
| 1200  | 19.67 | 26.92     | 7.36              | 14.71              | 1.13      | 0.95    | 31.52       | 18.93            | 1.32         |
| 1300  | 19.45 | 27.07     | 7.39              | 13.43              | 1.14      | 0.96    | 31.27       | 18.71            | 1.33         |
| 1400  | 19.25 | 27.16     | 7.49              | 12.32              | 1.14      | 0.96    | 31.15       | 18.64            | 1.34         |
| 1500  | 19.07 | 27.24     | 7.69              | 11.41              | 1.15      | 0.96    | 31.08       | 18.80            | 1.37         |
| 1600  | 18.90 | 27.34     | 7.98              | 10.62              | 1.16      | 0.95    | 30.82       | 18.59            | 1.40         |
| 1700  | 18.73 | 27.32     | 8.33              | 9.99               | 1.16      | 0.94    | 30.49       | 18.09            | 1.42         |
| 1800  | 18.54 | 27.35     | 8.66              | 9.49               | 1.16      | 0.93    | 30.88       | 18.49            | 1.40         |
| 1900  | 18.33 | 27.42     | 8.87              | 9.08               | 1.16      | 0.94    | 30.42       | 18.42            | 1.46         |
| 2000  | 18.06 | 27.56     | 8.83              | 8.79               | 1.18      | 0.95    | 30.48       | 18.13            | 1.48         |
| 2100  | 17.73 | 27.66     | 8.46              | 8.60               | 1.19      | 0.97    | 29.90       | 18.14            | 1.56         |
| 2200  | 17.31 | 27.89     | 7.72              | 8.51               | 1.20      | 1.01    | 29.88       | 17.86            | 1.71         |
| 2300  | 16.78 | 28.22     | 6.80              | 8.47               | 1.23      | 1.06    | 29.49       | 17.83            | 1.86         |
| 2400  | 16.15 | 28.66     | 5.85              | 8.47               | 1.27      | 1.12    | 29.16       | 17.53            | 2.08         |
| 2500  | 15.43 | 29.10     | 4.97              | 8.51               | 1.31      | 1.18    | 29.36       | 17.68            | 2.36         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.25V, Id = 81mA @ Temperature = +25°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 20    | 22.87 | 25.93     | 10.51             | 15.50              | 1.02      | 0.51    | 33.20       | 16.78            | 1.11         |
| 30    | 22.57 | 25.45     | 11.98             | 15.94              | 1.02      | 0.48    | 35.23       | 18.08            | 1.06         |
| 40    | 22.37 | 25.23     | 12.79             | 15.47              | 1.03      | 0.47    | 34.63       | 19.16            | 1.02         |
| 50    | 22.21 | 25.81     | 13.40             | 14.83              | 1.06      | 0.53    | 34.99       | 19.72            | 1.07         |
| 60    | 22.15 | 25.11     | 13.67             | 14.86              | 1.04      | 0.46    | 36.53       | 19.79            | 1.07         |
| 70    | 22.09 | 25.00     | 13.88             | 14.70              | 1.04      | 0.45    | 35.67       | 19.82            | 1.10         |
| 80    | 22.05 | 24.92     | 13.99             | 14.66              | 1.03      | 0.44    | 35.38       | 19.76            | 1.10         |
| 90    | 22.02 | 24.98     | 14.08             | 14.57              | 1.04      | 0.45    | 36.43       | 19.83            | 1.13         |
| 100   | 22.00 | 24.90     | 14.13             | 14.57              | 1.04      | 0.45    | 35.11       | 19.89            | 1.14         |
| 150   | 21.93 | 24.98     | 14.10             | 14.61              | 1.04      | 0.46    | 36.98       | 19.95            | 1.21         |
| 200   | 21.87 | 25.00     | 13.87             | 14.86              | 1.05      | 0.48    | 35.92       | 20.02            | 1.16         |
| 250   | 21.83 | 25.00     | 13.47             | 15.24              | 1.05      | 0.49    | 35.49       | 20.13            | 1.17         |
| 300   | 21.78 | 25.09     | 13.09             | 15.63              | 1.05      | 0.51    | 36.50       | 20.26            | 1.16         |
| 350   | 21.72 | 25.17     | 12.59             | 16.18              | 1.05      | 0.54    | 35.92       | 20.24            | 1.17         |
| 400   | 21.66 | 25.26     | 12.12             | 16.81              | 1.06      | 0.56    | 35.57       | 20.16            | 1.19         |
| 450   | 21.59 | 25.36     | 11.62             | 17.56              | 1.06      | 0.59    | 34.76       | 20.01            | 1.17         |
| 500   | 21.50 | 25.45     | 11.10             | 18.39              | 1.06      | 0.62    | 35.31       | 19.71            | 1.19         |
| 550   | 21.41 | 25.56     | 10.64             | 19.24              | 1.07      | 0.65    | 34.01       | 20.12            | 1.19         |
| 600   | 21.31 | 25.69     | 10.19             | 20.10              | 1.07      | 0.68    | 33.75       | 19.92            | 1.24         |
| 650   | 21.21 | 25.82     | 9.80              | 20.87              | 1.08      | 0.72    | 33.91       | 19.94            | 1.25         |
| 700   | 21.10 | 25.95     | 9.45              | 21.39              | 1.08      | 0.75    | 33.53       | 19.83            | 1.23         |
| 750   | 20.97 | 26.06     | 9.12              | 21.62              | 1.09      | 0.77    | 33.03       | 19.71            | 1.23         |
| 800   | 20.85 | 26.21     | 8.86              | 21.38              | 1.10      | 0.80    | 33.23       | 19.59            | 1.28         |
| 850   | 20.73 | 26.26     | 8.63              | 20.86              | 1.10      | 0.82    | 32.76       | 19.85            | 1.24         |
| 900   | 20.62 | 26.42     | 8.41              | 20.06              | 1.11      | 0.85    | 32.51       | 19.78            | 1.25         |
| 950   | 20.51 | 26.52     | 8.22              | 19.13              | 1.11      | 0.87    | 32.92       | 19.64            | 1.21         |
| 1000  | 20.40 | 26.62     | 8.07              | 18.19              | 1.11      | 0.88    | 32.66       | 19.88            | 1.24         |
| 1100  | 20.17 | 26.79     | 7.86              | 16.40              | 1.12      | 0.91    | 32.44       | 19.79            | 1.30         |
| 1200  | 19.96 | 26.95     | 7.77              | 14.84              | 1.13      | 0.93    | 32.16       | 19.81            | 1.33         |
| 1300  | 19.76 | 27.06     | 7.82              | 13.59              | 1.14      | 0.93    | 32.20       | 19.60            | 1.35         |
| 1400  | 19.57 | 27.17     | 7.94              | 12.50              | 1.14      | 0.93    | 32.24       | 19.53            | 1.34         |
| 1500  | 19.40 | 27.26     | 8.15              | 11.59              | 1.15      | 0.93    | 31.97       | 19.70            | 1.33         |
| 1600  | 19.23 | 27.34     | 8.44              | 10.84              | 1.15      | 0.93    | 31.45       | 19.41            | 1.39         |
| 1700  | 19.07 | 27.40     | 8.76              | 10.23              | 1.16      | 0.92    | 31.29       | 18.97            | 1.37         |
| 1800  | 18.88 | 27.45     | 9.05              | 9.77               | 1.16      | 0.92    | 31.53       | 19.40            | 1.37         |
| 1900  | 18.66 | 27.55     | 9.18              | 9.39               | 1.17      | 0.93    | 30.94       | 19.24            | 1.40         |
| 2000  | 18.38 | 27.69     | 9.03              | 9.12               | 1.18      | 0.94    | 31.06       | 19.03            | 1.47         |
| 2100  | 18.05 | 27.85     | 8.55              | 8.95               | 1.20      | 0.97    | 30.66       | 18.96            | 1.52         |
| 2200  | 17.64 | 28.07     | 7.76              | 8.84               | 1.21      | 1.01    | 30.59       | 18.75            | 1.63         |
| 2300  | 17.13 | 28.33     | 6.83              | 8.79               | 1.22      | 1.06    | 30.19       | 18.66            | 1.78         |
| 2400  | 16.53 | 28.73     | 5.88              | 8.77               | 1.25      | 1.12    | 29.86       | 18.36            | 1.95         |
| 2500  | 15.86 | 29.14     | 5.00              | 8.76               | 1.27      | 1.18    | 29.89       | 18.47            | 2.24         |



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 134mA @ Temperature = +25°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 20    | 23.37 | 26.36     | 10.44             | 14.76              | 1.02      | 0.49    | 36.40       | 21.36            | 1.17         |
| 30    | 23.04 | 25.86     | 11.65             | 14.81              | 1.02      | 0.46    | 39.34       | 22.32            | 1.09         |
| 40    | 22.82 | 25.61     | 12.23             | 14.31              | 1.02      | 0.44    | 39.72       | 23.00            | 1.04         |
| 50    | 22.66 | 25.97     | 12.77             | 13.69              | 1.04      | 0.49    | 36.78       | 23.36            | 1.09         |
| 60    | 22.60 | 25.46     | 12.83             | 13.68              | 1.03      | 0.43    | 38.54       | 23.32            | 1.11         |
| 70    | 22.54 | 25.38     | 12.97             | 13.54              | 1.03      | 0.42    | 41.60       | 23.32            | 1.10         |
| 80    | 22.49 | 25.36     | 13.02             | 13.48              | 1.03      | 0.42    | 38.21       | 23.24            | 1.15         |
| 90    | 22.47 | 25.40     | 13.12             | 13.41              | 1.04      | 0.43    | 40.48       | 23.38            | 1.14         |
| 100   | 22.44 | 25.36     | 13.17             | 13.39              | 1.04      | 0.43    | 38.87       | 23.36            | 1.15         |
| 150   | 22.37 | 25.36     | 13.21             | 13.38              | 1.04      | 0.43    | 39.42       | 23.44            | 1.24         |
| 200   | 22.33 | 25.36     | 13.19             | 13.51              | 1.04      | 0.44    | 42.51       | 23.59            | 1.18         |
| 250   | 22.30 | 25.36     | 13.06             | 13.73              | 1.04      | 0.45    | 39.89       | 23.73            | 1.18         |
| 300   | 22.27 | 25.45     | 12.93             | 13.96              | 1.05      | 0.47    | 37.61       | 23.81            | 1.16         |
| 350   | 22.23 | 25.47     | 12.73             | 14.25              | 1.05      | 0.48    | 39.37       | 23.81            | 1.20         |
| 400   | 22.19 | 25.58     | 12.51             | 14.59              | 1.05      | 0.50    | 37.85       | 23.71            | 1.19         |
| 450   | 22.15 | 25.65     | 12.25             | 14.97              | 1.06      | 0.52    | 38.47       | 23.52            | 1.18         |
| 500   | 22.09 | 25.72     | 11.91             | 15.39              | 1.06      | 0.55    | 37.80       | 23.31            | 1.19         |
| 550   | 22.04 | 25.85     | 11.62             | 15.77              | 1.07      | 0.57    | 38.31       | 23.76            | 1.20         |
| 600   | 21.97 | 25.94     | 11.30             | 16.17              | 1.07      | 0.59    | 37.76       | 23.47            | 1.25         |
| 650   | 21.90 | 26.04     | 10.99             | 16.49              | 1.08      | 0.62    | 36.69       | 23.53            | 1.25         |
| 700   | 21.83 | 26.14     | 10.72             | 16.76              | 1.08      | 0.64    | 36.68       | 23.43            | 1.23         |
| 750   | 21.74 | 26.22     | 10.45             | 16.97              | 1.09      | 0.66    | 36.40       | 23.23            | 1.21         |
| 800   | 21.65 | 26.42     | 10.23             | 17.04              | 1.10      | 0.69    | 35.79       | 23.23            | 1.23         |
| 850   | 21.57 | 26.50     | 10.04             | 17.10              | 1.10      | 0.71    | 36.35       | 23.44            | 1.22         |
| 900   | 21.49 | 26.62     | 9.83              | 16.98              | 1.11      | 0.73    | 35.67       | 23.27            | 1.24         |
| 950   | 21.41 | 26.69     | 9.64              | 16.73              | 1.11      | 0.74    | 35.09       | 23.16            | 1.25         |
| 1000  | 21.33 | 26.84     | 9.50              | 16.39              | 1.12      | 0.76    | 36.12       | 23.55            | 1.20         |
| 1100  | 21.16 | 27.02     | 9.30              | 15.52              | 1.14      | 0.79    | 35.59       | 23.35            | 1.27         |
| 1200  | 21.00 | 27.26     | 9.24              | 14.55              | 1.15      | 0.81    | 35.31       | 23.40            | 1.30         |
| 1300  | 20.84 | 27.47     | 9.30              | 13.62              | 1.17      | 0.82    | 34.86       | 23.01            | 1.32         |
| 1400  | 20.70 | 27.69     | 9.47              | 12.77              | 1.19      | 0.83    | 34.81       | 22.95            | 1.33         |
| 1500  | 20.57 | 27.82     | 9.75              | 11.97              | 1.20      | 0.83    | 34.64       | 23.15            | 1.31         |
| 1600  | 20.44 | 27.99     | 10.13             | 11.33              | 1.21      | 0.83    | 34.11       | 22.77            | 1.34         |
| 1700  | 20.31 | 28.18     | 10.60             | 10.79              | 1.23      | 0.84    | 33.13       | 22.07            | 1.33         |
| 1800  | 20.17 | 28.35     | 11.05             | 10.36              | 1.25      | 0.84    | 34.08       | 22.88            | 1.36         |
| 1900  | 20.00 | 28.55     | 11.36             | 10.01              | 1.27      | 0.85    | 33.55       | 22.74            | 1.38         |
| 2000  | 19.80 | 28.69     | 11.26             | 9.75               | 1.27      | 0.87    | 33.32       | 22.42            | 1.42         |
| 2100  | 19.54 | 28.92     | 10.68             | 9.56               | 1.29      | 0.90    | 33.93       | 22.45            | 1.48         |
| 2200  | 19.22 | 29.28     | 9.65              | 9.42               | 1.31      | 0.95    | 32.50       | 22.07            | 1.59         |
| 2300  | 18.81 | 29.70     | 8.43              | 9.33               | 1.34      | 1.00    | 32.51       | 22.11            | 1.73         |
| 2400  | 18.32 | 30.14     | 7.19              | 9.23               | 1.37      | 1.06    | 32.16       | 21.68            | 1.89         |
| 2500  | 17.75 | 30.53     | 6.05              | 9.15               | 1.38      | 1.12    | 32.50       | 21.90            | 2.16         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 143mA @ Temperature = +25°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 20    | 23.44 | 26.51     | 10.42             | 14.74              | 1.02      | 0.50    | 38.03       | 21.98            | 1.20         |
| 30    | 23.11 | 25.94     | 11.59             | 14.76              | 1.02      | 0.46    | 38.75       | 22.79            | 1.16         |
| 40    | 22.88 | 25.69     | 12.12             | 14.23              | 1.02      | 0.44    | 39.63       | 23.39            | 1.10         |
| 50    | 22.72 | 25.49     | 12.71             | 13.77              | 1.03      | 0.42    | 39.07       | 23.80            | 1.09         |
| 60    | 22.65 | 25.47     | 12.70             | 13.63              | 1.03      | 0.43    | 39.61       | 23.70            | 1.11         |
| 70    | 22.59 | 25.40     | 12.83             | 13.47              | 1.03      | 0.42    | 42.10       | 23.76            | 1.11         |
| 80    | 22.55 | 25.47     | 12.89             | 13.42              | 1.03      | 0.43    | 40.26       | 23.69            | 1.14         |
| 90    | 22.52 | 25.31     | 12.99             | 13.37              | 1.03      | 0.41    | 42.01       | 23.76            | 1.17         |
| 100   | 22.50 | 25.38     | 13.02             | 13.33              | 1.03      | 0.42    | 37.95       | 23.80            | 1.19         |
| 150   | 22.43 | 25.35     | 13.07             | 13.32              | 1.04      | 0.42    | 41.98       | 23.82            | 1.16         |
| 200   | 22.38 | 25.39     | 13.03             | 13.43              | 1.04      | 0.44    | 40.57       | 23.97            | 1.18         |
| 250   | 22.35 | 25.46     | 12.94             | 13.59              | 1.04      | 0.45    | 37.96       | 24.11            | 1.16         |
| 300   | 22.33 | 25.47     | 12.82             | 13.79              | 1.05      | 0.46    | 38.94       | 24.25            | 1.16         |
| 350   | 22.29 | 25.57     | 12.64             | 14.03              | 1.05      | 0.48    | 36.74       | 24.19            | 1.18         |
| 400   | 22.25 | 25.60     | 12.45             | 14.30              | 1.05      | 0.49    | 36.45       | 24.17            | 1.21         |
| 450   | 22.22 | 25.67     | 12.21             | 14.59              | 1.06      | 0.51    | 37.28       | 23.98            | 1.19         |
| 500   | 22.16 | 25.75     | 11.91             | 14.93              | 1.06      | 0.53    | 38.33       | 23.78            | 1.19         |
| 550   | 22.11 | 25.87     | 11.67             | 15.22              | 1.07      | 0.56    | 38.08       | 24.14            | 1.20         |
| 600   | 22.05 | 25.94     | 11.35             | 15.53              | 1.07      | 0.58    | 37.21       | 23.93            | 1.28         |
| 650   | 21.98 | 26.06     | 11.06             | 15.77              | 1.08      | 0.60    | 37.95       | 24.00            | 1.28         |
| 700   | 21.91 | 26.17     | 10.82             | 15.98              | 1.08      | 0.62    | 37.12       | 23.81            | 1.23         |
| 750   | 21.83 | 26.34     | 10.56             | 16.14              | 1.09      | 0.65    | 36.45       | 23.70            | 1.23         |
| 800   | 21.74 | 26.40     | 10.34             | 16.22              | 1.10      | 0.67    | 36.52       | 23.62            | 1.20         |
| 850   | 21.67 | 26.50     | 10.16             | 16.29              | 1.10      | 0.69    | 36.32       | 23.83            | 1.22         |
| 900   | 21.59 | 26.59     | 9.94              | 16.22              | 1.11      | 0.71    | 36.16       | 23.76            | 1.23         |
| 950   | 21.52 | 26.73     | 9.77              | 16.07              | 1.12      | 0.73    | 35.94       | 23.66            | 1.23         |
| 1000  | 21.44 | 26.83     | 9.63              | 15.81              | 1.12      | 0.74    | 36.80       | 24.05            | 1.22         |
| 1100  | 21.27 | 27.07     | 9.41              | 15.11              | 1.14      | 0.77    | 36.25       | 23.74            | 1.26         |
| 1200  | 21.11 | 27.34     | 9.32              | 14.29              | 1.16      | 0.80    | 35.24       | 23.79            | 1.32         |
| 1300  | 20.95 | 27.58     | 9.38              | 13.46              | 1.18      | 0.81    | 35.24       | 23.51            | 1.32         |
| 1400  | 20.81 | 27.76     | 9.53              | 12.66              | 1.20      | 0.82    | 35.32       | 23.45            | 1.30         |
| 1500  | 20.68 | 27.94     | 9.81              | 11.90              | 1.21      | 0.82    | 35.24       | 23.53            | 1.35         |
| 1600  | 20.55 | 28.15     | 10.22             | 11.26              | 1.23      | 0.82    | 34.29       | 23.27            | 1.34         |
| 1700  | 20.43 | 28.27     | 10.76             | 10.72              | 1.24      | 0.82    | 33.98       | 22.46            | 1.34         |
| 1800  | 20.30 | 28.48     | 11.34             | 10.28              | 1.26      | 0.83    | 34.57       | 23.39            | 1.34         |
| 1900  | 20.15 | 28.64     | 11.80             | 9.91               | 1.28      | 0.83    | 34.35       | 23.26            | 1.42         |
| 2000  | 19.97 | 28.98     | 11.92             | 9.63               | 1.31      | 0.85    | 33.93       | 22.85            | 1.44         |
| 2100  | 19.74 | 29.21     | 11.47             | 9.42               | 1.33      | 0.88    | 34.05       | 22.90            | 1.51         |
| 2200  | 19.44 | 29.52     | 10.42             | 9.29               | 1.35      | 0.92    | 33.06       | 22.43            | 1.65         |
| 2300  | 19.05 | 29.90     | 9.07              | 9.19               | 1.37      | 0.97    | 33.40       | 22.47            | 1.78         |
| 2400  | 18.56 | 30.34     | 7.70              | 9.12               | 1.40      | 1.03    | 32.57       | 22.04            | 1.96         |
| 2500  | 17.99 | 30.83     | 6.45              | 9.03               | 1.43      | 1.10    | 32.95       | 22.25            | 2.24         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 151mA @ Temperature = +25°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 20    | 23.47 | 26.51     | 10.43             | 14.70              | 1.02      | 0.49    | 35.45       | 22.49            | 1.22         |
| 30    | 23.14 | 25.93     | 11.56             | 14.74              | 1.02      | 0.45    | 40.19       | 23.18            | 1.14         |
| 40    | 22.91 | 25.70     | 12.11             | 14.19              | 1.02      | 0.44    | 38.43       | 23.84            | 1.10         |
| 50    | 22.75 | 25.25     | 12.57             | 13.72              | 1.02      | 0.39    | 40.22       | 24.20            | 1.14         |
| 60    | 22.68 | 25.51     | 12.66             | 13.55              | 1.03      | 0.43    | 38.35       | 24.16            | 1.14         |
| 70    | 22.62 | 25.46     | 12.79             | 13.41              | 1.03      | 0.42    | 44.88       | 24.15            | 1.11         |
| 80    | 22.58 | 25.52     | 12.85             | 13.35              | 1.04      | 0.43    | 39.98       | 24.08            | 1.15         |
| 90    | 22.55 | 25.36     | 12.94             | 13.31              | 1.03      | 0.41    | 39.60       | 24.22            | 1.17         |
| 100   | 22.52 | 25.37     | 12.98             | 13.26              | 1.03      | 0.42    | 37.44       | 24.20            | 1.20         |
| 150   | 22.46 | 25.42     | 13.06             | 13.24              | 1.04      | 0.43    | 42.74       | 24.28            | 1.24         |
| 200   | 22.41 | 25.44     | 13.04             | 13.33              | 1.04      | 0.44    | 39.31       | 24.44            | 1.18         |
| 250   | 22.39 | 25.52     | 12.97             | 13.50              | 1.04      | 0.45    | 37.42       | 24.58            | 1.19         |
| 300   | 22.36 | 25.48     | 12.87             | 13.68              | 1.04      | 0.46    | 41.52       | 24.66            | 1.20         |
| 350   | 22.32 | 25.61     | 12.69             | 13.92              | 1.05      | 0.48    | 38.79       | 24.67            | 1.21         |
| 400   | 22.29 | 25.65     | 12.52             | 14.17              | 1.05      | 0.49    | 38.50       | 24.66            | 1.22         |
| 450   | 22.25 | 25.69     | 12.32             | 14.48              | 1.06      | 0.51    | 39.29       | 24.47            | 1.22         |
| 500   | 22.20 | 25.81     | 12.02             | 14.80              | 1.06      | 0.53    | 38.38       | 24.20            | 1.21         |
| 550   | 22.15 | 25.92     | 11.77             | 15.07              | 1.07      | 0.56    | 38.41       | 24.64            | 1.22         |
| 600   | 22.09 | 25.98     | 11.49             | 15.35              | 1.07      | 0.57    | 38.87       | 24.44            | 1.29         |
| 650   | 22.02 | 26.06     | 11.20             | 15.57              | 1.07      | 0.59    | 37.71       | 24.43            | 1.28         |
| 700   | 21.96 | 26.19     | 10.96             | 15.70              | 1.08      | 0.62    | 38.09       | 24.33            | 1.26         |
| 750   | 21.87 | 26.29     | 10.70             | 15.82              | 1.09      | 0.64    | 37.14       | 24.13            | 1.24         |
| 800   | 21.79 | 26.46     | 10.50             | 15.85              | 1.10      | 0.66    | 36.78       | 24.15            | 1.28         |
| 850   | 21.72 | 26.52     | 10.32             | 15.84              | 1.10      | 0.68    | 37.58       | 24.36            | 1.28         |
| 900   | 21.64 | 26.64     | 10.13             | 15.73              | 1.11      | 0.70    | 36.57       | 24.29            | 1.24         |
| 950   | 21.57 | 26.73     | 9.94              | 15.54              | 1.11      | 0.71    | 36.09       | 24.20            | 1.25         |
| 1000  | 21.50 | 26.85     | 9.82              | 15.26              | 1.12      | 0.73    | 36.88       | 24.59            | 1.26         |
| 1100  | 21.34 | 27.11     | 9.62              | 14.56              | 1.14      | 0.76    | 36.16       | 24.29            | 1.29         |
| 1200  | 21.19 | 27.34     | 9.56              | 13.77              | 1.16      | 0.78    | 36.24       | 24.35            | 1.35         |
| 1300  | 21.04 | 27.55     | 9.64              | 13.00              | 1.17      | 0.79    | 35.78       | 23.97            | 1.34         |
| 1400  | 20.90 | 27.78     | 9.83              | 12.26              | 1.19      | 0.80    | 35.37       | 23.91            | 1.35         |
| 1500  | 20.78 | 28.02     | 10.13             | 11.58              | 1.21      | 0.81    | 36.00       | 24.10            | 1.36         |
| 1600  | 20.65 | 28.17     | 10.53             | 11.01              | 1.23      | 0.81    | 35.15       | 23.73            | 1.37         |
| 1700  | 20.54 | 28.43     | 11.05             | 10.54              | 1.25      | 0.81    | 34.28       | 22.91            | 1.37         |
| 1800  | 20.40 | 28.59     | 11.56             | 10.16              | 1.27      | 0.82    | 35.20       | 23.85            | 1.37         |
| 1900  | 20.25 | 28.93     | 11.90             | 9.82               | 1.30      | 0.84    | 35.11       | 23.72            | 1.38         |
| 2000  | 20.05 | 29.16     | 11.83             | 9.58               | 1.32      | 0.86    | 34.23       | 23.39            | 1.44         |
| 2100  | 19.81 | 29.46     | 11.21             | 9.39               | 1.34      | 0.89    | 34.68       | 23.43            | 1.50         |
| 2200  | 19.51 | 29.82     | 10.12             | 9.23               | 1.37      | 0.93    | 33.76       | 22.85            | 1.61         |
| 2300  | 19.12 | 30.24     | 8.81              | 9.10               | 1.39      | 0.98    | 33.42       | 22.89            | 1.76         |
| 2400  | 18.65 | 30.64     | 7.50              | 8.98               | 1.41      | 1.04    | 32.60       | 22.47            | 1.94         |
| 2500  | 18.11 | 31.18     | 6.32              | 8.84               | 1.44      | 1.10    | 33.09       | 22.82            | 3.16         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.75V, Id = 61mA @ Temperature = -45°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 20    | 22.61 | 25.91     | 10.40             | 15.84              | 1.03      | 0.54    | 30.58       | 14.39            | 0.94         |
| 30    | 22.33 | 25.29     | 12.11             | 16.93              | 1.03      | 0.50    | 31.38       | 15.79            | 0.87         |
| 40    | 22.14 | 24.98     | 13.10             | 16.65              | 1.03      | 0.47    | 32.60       | 17.01            | 0.87         |
| 50    | 22.00 | 25.49     | 14.09             | 15.99              | 1.06      | 0.53    | 32.20       | 17.71            | 0.90         |
| 60    | 21.94 | 24.82     | 14.19             | 16.06              | 1.04      | 0.46    | 33.60       | 17.92            | 0.92         |
| 70    | 21.89 | 24.74     | 14.44             | 15.92              | 1.04      | 0.46    | 33.63       | 18.08            | 0.94         |
| 80    | 21.85 | 24.68     | 14.63             | 15.89              | 1.04      | 0.45    | 32.81       | 18.07            | 0.95         |
| 90    | 21.82 | 24.70     | 14.78             | 15.83              | 1.04      | 0.46    | 34.05       | 18.14            | 0.98         |
| 100   | 21.80 | 24.63     | 14.85             | 15.85              | 1.04      | 0.45    | 33.19       | 18.20            | 0.98         |
| 150   | 21.74 | 24.65     | 14.85             | 15.95              | 1.04      | 0.46    | 33.72       | 18.30            | 1.04         |
| 200   | 21.68 | 24.68     | 14.48             | 16.19              | 1.04      | 0.47    | 33.17       | 18.43            | 0.99         |
| 250   | 21.64 | 24.77     | 13.95             | 16.50              | 1.05      | 0.50    | 33.45       | 18.50            | 0.96         |
| 300   | 21.59 | 24.82     | 13.37             | 16.81              | 1.05      | 0.51    | 33.30       | 18.55            | 1.01         |
| 350   | 21.52 | 24.89     | 12.75             | 17.33              | 1.05      | 0.54    | 32.21       | 18.52            | 1.01         |
| 400   | 21.46 | 25.01     | 12.17             | 17.92              | 1.05      | 0.57    | 31.89       | 18.45            | 1.01         |
| 450   | 21.39 | 25.09     | 11.59             | 18.68              | 1.06      | 0.59    | 31.62       | 18.28            | 0.99         |
| 500   | 21.30 | 25.23     | 10.99             | 19.38              | 1.06      | 0.63    | 31.80       | 18.09            | 1.01         |
| 550   | 21.21 | 25.34     | 10.48             | 20.02              | 1.06      | 0.66    | 31.48       | 18.38            | 1.05         |
| 600   | 21.10 | 25.46     | 10.01             | 20.58              | 1.07      | 0.69    | 31.32       | 18.21            | 1.06         |
| 650   | 20.99 | 25.61     | 9.57              | 20.92              | 1.07      | 0.72    | 31.18       | 18.30            | 1.08         |
| 700   | 20.88 | 25.69     | 9.22              | 20.92              | 1.08      | 0.75    | 30.90       | 18.12            | 1.07         |
| 750   | 20.75 | 25.85     | 8.86              | 20.59              | 1.08      | 0.78    | 30.63       | 18.01            | 1.05         |
| 800   | 20.62 | 26.00     | 8.57              | 19.95              | 1.09      | 0.81    | 30.38       | 17.96            | 1.06         |
| 850   | 20.50 | 26.12     | 8.36              | 19.22              | 1.10      | 0.83    | 30.27       | 18.09            | 1.06         |
| 900   | 20.38 | 26.23     | 8.11              | 18.42              | 1.10      | 0.85    | 29.89       | 18.13            | 1.05         |
| 950   | 20.28 | 26.34     | 7.92              | 17.65              | 1.10      | 0.87    | 30.01       | 18.01            | 1.07         |
| 1000  | 20.16 | 26.44     | 7.75              | 16.80              | 1.10      | 0.89    | 29.94       | 18.22            | 1.03         |
| 1100  | 19.93 | 26.61     | 7.52              | 15.28              | 1.11      | 0.91    | 29.71       | 18.12            | 1.08         |
| 1200  | 19.72 | 26.79     | 7.42              | 13.94              | 1.12      | 0.93    | 29.45       | 18.14            | 1.13         |
| 1300  | 19.52 | 26.93     | 7.44              | 12.81              | 1.12      | 0.94    | 29.49       | 17.94            | 1.12         |
| 1400  | 19.33 | 27.06     | 7.54              | 11.83              | 1.13      | 0.94    | 29.18       | 17.87            | 1.16         |
| 1500  | 19.16 | 27.19     | 7.73              | 11.01              | 1.14      | 0.94    | 29.18       | 17.93            | 1.17         |
| 1600  | 19.00 | 27.29     | 8.00              | 10.32              | 1.14      | 0.93    | 28.89       | 17.73            | 1.11         |
| 1700  | 18.83 | 27.28     | 8.30              | 9.77               | 1.14      | 0.93    | 28.40       | 17.36            | 1.15         |
| 1800  | 18.65 | 27.42     | 8.58              | 9.33               | 1.15      | 0.93    | 28.80       | 17.75            | 1.13         |
| 1900  | 18.44 | 27.44     | 8.72              | 8.99               | 1.15      | 0.93    | 28.36       | 17.58            | 1.15         |
| 2000  | 18.18 | 27.60     | 8.60              | 8.76               | 1.16      | 0.95    | 28.21       | 17.31            | 1.19         |
| 2100  | 17.85 | 27.73     | 8.16              | 8.59               | 1.17      | 0.98    | 27.82       | 17.31            | 1.22         |
| 2200  | 17.44 | 27.97     | 7.42              | 8.49               | 1.17      | 1.02    | 27.67       | 17.05            | 1.33         |
| 2300  | 16.94 | 28.25     | 6.53              | 8.46               | 1.18      | 1.07    | 27.35       | 17.05            | 1.43         |
| 2400  | 16.34 | 28.64     | 5.62              | 8.45               | 1.21      | 1.13    | 27.06       | 16.84            | 1.62         |
| 2500  | 15.66 | 29.10     | 4.77              | 8.44               | 1.23      | 1.19    | 27.12       | 16.83            | 1.88         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.00V, Id = 70mA @ Temperature = -45°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 20    | 22.78 | 25.95     | 10.45             | 15.60              | 1.03      | 0.52    | 34.22       | 15.85            | 0.94         |
| 30    | 22.50 | 25.44     | 12.03             | 16.50              | 1.03      | 0.49    | 33.99       | 17.09            | 0.89         |
| 40    | 22.30 | 25.15     | 12.94             | 16.12              | 1.03      | 0.47    | 35.31       | 18.39            | 0.87         |
| 50    | 22.15 | 24.47     | 13.86             | 15.70              | 1.02      | 0.39    | 33.58       | 18.99            | 0.92         |
| 60    | 22.09 | 24.87     | 13.95             | 15.54              | 1.03      | 0.45    | 35.30       | 19.10            | 0.92         |
| 70    | 22.04 | 24.86     | 14.19             | 15.40              | 1.03      | 0.45    | 35.45       | 19.22            | 0.93         |
| 80    | 22.00 | 24.91     | 14.32             | 15.35              | 1.04      | 0.46    | 35.09       | 19.18            | 0.95         |
| 90    | 21.98 | 24.77     | 14.49             | 15.35              | 1.04      | 0.44    | 35.43       | 19.25            | 0.97         |
| 100   | 21.95 | 24.82     | 14.55             | 15.33              | 1.04      | 0.45    | 35.20       | 19.31            | 1.00         |
| 150   | 21.89 | 24.73     | 14.60             | 15.45              | 1.04      | 0.45    | 34.92       | 19.40            | 1.03         |
| 200   | 21.84 | 24.83     | 14.35             | 15.63              | 1.04      | 0.47    | 35.44       | 19.46            | 0.98         |
| 250   | 21.80 | 24.91     | 13.91             | 15.86              | 1.05      | 0.49    | 34.59       | 19.54            | 0.99         |
| 300   | 21.76 | 24.95     | 13.45             | 16.18              | 1.05      | 0.50    | 34.73       | 19.67            | 1.00         |
| 350   | 21.70 | 25.04     | 12.92             | 16.59              | 1.05      | 0.53    | 33.29       | 19.57            | 1.03         |
| 400   | 21.64 | 25.09     | 12.42             | 17.15              | 1.05      | 0.54    | 32.93       | 19.49            | 1.01         |
| 450   | 21.58 | 25.24     | 11.89             | 17.81              | 1.06      | 0.58    | 33.02       | 19.34            | 1.00         |
| 500   | 21.50 | 25.32     | 11.34             | 18.43              | 1.06      | 0.60    | 33.05       | 19.14            | 1.00         |
| 550   | 21.42 | 25.39     | 10.87             | 19.04              | 1.06      | 0.63    | 32.94       | 19.35            | 1.02         |
| 600   | 21.33 | 25.52     | 10.43             | 19.56              | 1.07      | 0.66    | 32.81       | 19.27            | 1.06         |
| 650   | 21.23 | 25.62     | 10.00             | 19.99              | 1.07      | 0.69    | 32.40       | 19.29            | 1.03         |
| 700   | 21.13 | 25.74     | 9.65              | 20.18              | 1.08      | 0.71    | 32.15       | 19.10            | 1.05         |
| 750   | 21.02 | 25.89     | 9.30              | 20.08              | 1.08      | 0.74    | 31.76       | 18.99            | 1.02         |
| 800   | 20.90 | 26.05     | 9.03              | 19.69              | 1.09      | 0.77    | 31.51       | 18.95            | 1.05         |
| 850   | 20.79 | 26.14     | 8.80              | 19.19              | 1.10      | 0.79    | 31.50       | 19.11            | 1.06         |
| 900   | 20.68 | 26.25     | 8.56              | 18.57              | 1.10      | 0.81    | 31.19       | 19.06            | 1.04         |
| 950   | 20.59 | 26.36     | 8.36              | 17.92              | 1.10      | 0.83    | 31.32       | 18.94            | 1.05         |
| 1000  | 20.48 | 26.48     | 8.19              | 17.13              | 1.11      | 0.85    | 31.28       | 19.17            | 1.02         |
| 1100  | 20.27 | 26.69     | 7.96              | 15.67              | 1.12      | 0.88    | 30.74       | 18.98            | 1.09         |
| 1200  | 20.07 | 26.87     | 7.86              | 14.34              | 1.13      | 0.90    | 30.72       | 19.01            | 1.11         |
| 1300  | 19.88 | 27.02     | 7.88              | 13.20              | 1.13      | 0.91    | 30.46       | 18.82            | 1.13         |
| 1400  | 19.71 | 27.19     | 7.98              | 12.19              | 1.14      | 0.91    | 30.26       | 18.76            | 1.13         |
| 1500  | 19.55 | 27.31     | 8.18              | 11.34              | 1.15      | 0.91    | 30.46       | 18.93            | 1.10         |
| 1600  | 19.40 | 27.38     | 8.48              | 10.64              | 1.15      | 0.91    | 29.90       | 18.66            | 1.09         |
| 1700  | 19.25 | 27.51     | 8.81              | 10.06              | 1.16      | 0.90    | 29.45       | 18.27            | 1.13         |
| 1800  | 19.09 | 27.56     | 9.13              | 9.63               | 1.17      | 0.90    | 29.91       | 18.71            | 1.10         |
| 1900  | 18.90 | 27.66     | 9.32              | 9.27               | 1.17      | 0.91    | 29.59       | 18.56            | 1.14         |
| 2000  | 18.65 | 27.77     | 9.22              | 9.02               | 1.18      | 0.93    | 29.23       | 18.29            | 1.16         |
| 2100  | 18.35 | 27.92     | 8.76              | 8.85               | 1.18      | 0.95    | 29.06       | 18.24            | 1.20         |
| 2200  | 17.97 | 28.17     | 7.96              | 8.75               | 1.19      | 1.00    | 28.87       | 18.07            | 1.30         |
| 2300  | 17.50 | 28.54     | 6.99              | 8.71               | 1.21      | 1.05    | 28.65       | 18.00            | 1.41         |
| 2400  | 16.93 | 28.85     | 6.00              | 8.69               | 1.22      | 1.11    | 28.24       | 17.73            | 1.55         |
| 2500  | 16.28 | 29.28     | 5.08              | 8.69               | 1.24      | 1.17    | 28.34       | 17.84            | 1.81         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.25V, Id = 79mA @ Temperature = -45°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 20    | 22.92 | 26.05     | 10.43             | 15.44              | 1.03      | 0.51    | 35.40       | 26.78            | 0.94         |
| 30    | 22.63 | 25.52     | 11.94             | 16.14              | 1.02      | 0.48    | 34.58       | 26.80            | 0.87         |
| 40    | 22.43 | 25.16     | 12.80             | 15.79              | 1.02      | 0.45    | 35.66       | 28.15            | 0.87         |
| 50    | 22.28 | 25.25     | 13.52             | 15.23              | 1.04      | 0.47    | 34.98       | 28.31            | 0.90         |
| 60    | 22.22 | 25.04     | 13.73             | 15.19              | 1.03      | 0.45    | 35.51       | 28.03            | 0.92         |
| 70    | 22.17 | 24.94     | 13.95             | 15.02              | 1.03      | 0.44    | 35.44       | 27.78            | 0.94         |
| 80    | 22.13 | 24.96     | 14.10             | 15.00              | 1.04      | 0.44    | 36.06       | 28.20            | 0.95         |
| 90    | 22.10 | 24.87     | 14.24             | 14.96              | 1.03      | 0.43    | 35.51       | 28.50            | 0.98         |
| 100   | 22.08 | 24.85     | 14.31             | 14.97              | 1.03      | 0.43    | 36.03       | 28.06            | 0.98         |
| 150   | 22.02 | 24.91     | 14.43             | 15.03              | 1.04      | 0.45    | 36.43       | 28.32            | 1.04         |
| 200   | 21.97 | 24.96     | 14.21             | 15.21              | 1.04      | 0.46    | 35.67       | 28.43            | 0.99         |
| 250   | 21.94 | 24.99     | 13.87             | 15.41              | 1.04      | 0.47    | 35.52       | 28.52            | 0.96         |
| 300   | 21.90 | 25.01     | 13.48             | 15.65              | 1.05      | 0.48    | 35.60       | 28.68            | 1.01         |
| 350   | 21.85 | 25.09     | 13.02             | 16.01              | 1.05      | 0.51    | 34.73       | 28.70            | 1.01         |
| 400   | 21.80 | 25.24     | 12.60             | 16.46              | 1.05      | 0.54    | 34.25       | 28.71            | 1.01         |
| 450   | 21.74 | 25.25     | 12.14             | 17.03              | 1.05      | 0.55    | 34.17       | 28.61            | 0.99         |
| 500   | 21.67 | 25.37     | 11.64             | 17.55              | 1.06      | 0.58    | 33.69       | 28.50            | 1.01         |
| 550   | 21.60 | 25.50     | 11.22             | 18.03              | 1.06      | 0.61    | 33.38       | 28.79            | 1.05         |
| 600   | 21.52 | 25.60     | 10.79             | 18.51              | 1.07      | 0.63    | 32.94       | 28.73            | 1.06         |
| 650   | 21.44 | 25.68     | 10.37             | 18.88              | 1.07      | 0.66    | 32.70       | 28.83            | 1.08         |
| 700   | 21.35 | 25.79     | 10.05             | 19.08              | 1.08      | 0.68    | 32.61       | 28.71            | 1.07         |
| 750   | 21.24 | 25.93     | 9.70              | 19.10              | 1.08      | 0.71    | 31.89       | 28.64            | 1.05         |
| 800   | 21.13 | 26.07     | 9.42              | 18.90              | 1.09      | 0.74    | 31.94       | 28.68            | 1.06         |
| 850   | 21.03 | 26.14     | 9.21              | 18.57              | 1.09      | 0.76    | 31.85       | 28.83            | 1.06         |
| 900   | 20.94 | 26.29     | 8.97              | 18.18              | 1.10      | 0.78    | 31.48       | 28.80            | 1.05         |
| 950   | 20.85 | 26.43     | 8.77              | 17.65              | 1.11      | 0.80    | 31.62       | 28.88            | 1.07         |
| 1000  | 20.76 | 26.50     | 8.59              | 17.01              | 1.11      | 0.82    | 31.66       | 29.05            | 1.03         |
| 1100  | 20.56 | 26.72     | 8.36              | 15.70              | 1.12      | 0.84    | 31.25       | 28.83            | 1.08         |
| 1200  | 20.38 | 26.93     | 8.26              | 14.47              | 1.13      | 0.86    | 31.18       | 28.91            | 1.13         |
| 1300  | 20.20 | 27.10     | 8.28              | 13.38              | 1.14      | 0.88    | 30.88       | 28.83            | 1.12         |
| 1400  | 20.04 | 27.25     | 8.38              | 12.40              | 1.15      | 0.88    | 30.83       | 28.74            | 1.16         |
| 1500  | 19.89 | 27.37     | 8.60              | 11.57              | 1.16      | 0.88    | 30.86       | 28.69            | 1.17         |
| 1600  | 19.75 | 27.53     | 8.93              | 10.86              | 1.17      | 0.88    | 30.17       | 28.54            | 1.11         |
| 1700  | 19.62 | 27.65     | 9.30              | 10.29              | 1.18      | 0.88    | 29.60       | 28.09            | 1.15         |
| 1800  | 19.47 | 27.76     | 9.66              | 9.86               | 1.19      | 0.88    | 30.28       | 28.60            | 1.13         |
| 1900  | 19.30 | 27.86     | 9.90              | 9.50               | 1.19      | 0.89    | 29.88       | 28.36            | 1.15         |
| 2000  | 19.07 | 28.10     | 9.81              | 9.25               | 1.21      | 0.91    | 29.66       | 28.27            | 1.19         |
| 2100  | 18.79 | 28.16     | 9.35              | 9.07               | 1.21      | 0.93    | 29.45       | 28.08            | 1.22         |
| 2200  | 18.45 | 28.43     | 8.49              | 8.97               | 1.22      | 0.98    | 29.13       | 28.07            | 1.33         |
| 2300  | 18.00 | 28.78     | 7.44              | 8.92               | 1.23      | 1.03    | 28.94       | 27.80            | 1.43         |
| 2400  | 17.46 | 29.13     | 6.37              | 8.90               | 1.24      | 1.09    | 28.61       | 27.36            | 1.62         |
| 2500  | 16.84 | 29.62     | 5.38              | 8.88               | 1.27      | 1.16    | 28.73       | 27.67            | 1.88         |



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd =4.75V, Id = 132mA @ Temperature = -45°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 20    | 23.45 | 26.25     | 10.36             | 15.30              | 1.02      | 0.47    | 37.49       | 21.24            | 0.96         |
| 30    | 23.12 | 25.79     | 11.65             | 15.45              | 1.02      | 0.45    | 43.55       | 22.40            | 0.88         |
| 40    | 22.90 | 25.53     | 12.32             | 14.92              | 1.02      | 0.43    | 38.14       | 23.16            | 0.87         |
| 50    | 22.74 | 25.46     | 12.71             | 14.30              | 1.03      | 0.43    | 40.34       | 23.58            | 0.91         |
| 60    | 22.67 | 25.31     | 12.98             | 14.27              | 1.03      | 0.41    | 38.71       | 23.55            | 0.92         |
| 70    | 22.61 | 25.31     | 13.14             | 14.11              | 1.03      | 0.41    | 42.73       | 23.53            | 0.93         |
| 80    | 22.57 | 25.23     | 13.26             | 14.06              | 1.03      | 0.41    | 40.22       | 23.44            | 0.95         |
| 90    | 22.54 | 25.27     | 13.34             | 14.01              | 1.03      | 0.41    | 42.88       | 23.61            | 0.97         |
| 100   | 22.52 | 25.23     | 13.42             | 13.99              | 1.03      | 0.41    | 37.35       | 23.57            | 0.97         |
| 150   | 22.46 | 25.22     | 13.59             | 13.98              | 1.03      | 0.41    | 43.77       | 23.65            | 0.99         |
| 200   | 22.42 | 25.24     | 13.58             | 13.99              | 1.04      | 0.42    | 39.84       | 23.73            | 0.98         |
| 250   | 22.40 | 25.26     | 13.46             | 14.00              | 1.04      | 0.43    | 39.60       | 23.87            | 0.97         |
| 300   | 22.38 | 25.34     | 13.36             | 14.01              | 1.04      | 0.44    | 41.10       | 24.02            | 1.00         |
| 350   | 22.35 | 25.36     | 13.18             | 14.11              | 1.04      | 0.45    | 37.77       | 23.95            | 1.02         |
| 400   | 22.32 | 25.46     | 13.01             | 14.22              | 1.05      | 0.47    | 37.20       | 23.86            | 1.01         |
| 450   | 22.29 | 25.53     | 12.82             | 14.34              | 1.05      | 0.48    | 38.51       | 23.66            | 0.99         |
| 500   | 22.25 | 25.59     | 12.52             | 14.46              | 1.05      | 0.49    | 38.17       | 23.46            | 0.99         |
| 550   | 22.21 | 25.71     | 12.26             | 14.48              | 1.06      | 0.51    | 39.05       | 23.92            | 1.04         |
| 600   | 22.16 | 25.77     | 11.97             | 14.53              | 1.06      | 0.53    | 38.16       | 23.63            | 1.05         |
| 650   | 22.10 | 25.87     | 11.68             | 14.54              | 1.07      | 0.55    | 38.32       | 23.71            | 1.07         |
| 700   | 22.05 | 26.01     | 11.44             | 14.48              | 1.07      | 0.57    | 38.93       | 23.53            | 1.03         |
| 750   | 21.98 | 26.15     | 11.17             | 14.38              | 1.08      | 0.59    | 37.12       | 23.34            | 1.03         |
| 800   | 21.90 | 26.25     | 10.95             | 14.23              | 1.09      | 0.61    | 37.34       | 23.25            | 1.03         |
| 850   | 21.84 | 26.38     | 10.79             | 14.10              | 1.09      | 0.62    | 37.96       | 23.57            | 1.01         |
| 900   | 21.78 | 26.48     | 10.59             | 13.96              | 1.10      | 0.64    | 36.92       | 23.41            | 1.02         |
| 950   | 21.72 | 26.56     | 10.41             | 13.76              | 1.10      | 0.65    | 36.84       | 23.32            | 1.05         |
| 1000  | 21.66 | 26.67     | 10.26             | 13.51              | 1.11      | 0.66    | 36.95       | 23.74            | 0.99         |
| 1100  | 21.52 | 26.95     | 10.04             | 12.91              | 1.13      | 0.69    | 36.68       | 23.45            | 1.05         |
| 1200  | 21.39 | 27.19     | 9.97              | 12.33              | 1.14      | 0.71    | 36.83       | 23.51            | 1.07         |
| 1300  | 21.26 | 27.43     | 10.04             | 11.74              | 1.16      | 0.72    | 36.54       | 23.14            | 1.07         |
| 1400  | 21.14 | 27.73     | 10.20             | 11.15              | 1.18      | 0.74    | 35.91       | 23.19            | 1.09         |
| 1500  | 21.03 | 27.95     | 10.52             | 10.62              | 1.20      | 0.74    | 36.38       | 23.32            | 1.04         |
| 1600  | 20.93 | 28.23     | 10.99             | 10.18              | 1.23      | 0.75    | 35.48       | 23.06            | 1.08         |
| 1700  | 20.83 | 28.52     | 11.57             | 9.79               | 1.25      | 0.76    | 34.55       | 22.24            | 1.05         |
| 1800  | 20.73 | 28.82     | 12.22             | 9.49               | 1.28      | 0.77    | 35.46       | 23.13            | 1.05         |
| 1900  | 20.60 | 29.05     | 12.74             | 9.22               | 1.30      | 0.78    | 34.62       | 23.03            | 1.10         |
| 2000  | 20.44 | 29.40     | 12.84             | 9.01               | 1.32      | 0.80    | 34.28       | 22.72            | 1.11         |
| 2100  | 20.25 | 29.84     | 12.29             | 8.83               | 1.36      | 0.84    | 35.25       | 22.82            | 1.15         |
| 2200  | 20.00 | 30.21     | 11.12             | 8.67               | 1.38      | 0.88    | 33.63       | 22.38            | 1.24         |
| 2300  | 19.67 | 30.71     | 9.63              | 8.52               | 1.41      | 0.93    | 34.01       | 22.36            | 1.32         |
| 2400  | 19.26 | 31.24     | 8.16              | 8.36               | 1.44      | 0.98    | 32.95       | 21.88            | 1.49         |
| 2500  | 18.77 | 31.94     | 6.82              | 8.16               | 1.48      | 1.04    | 33.43       | 22.28            | 1.70         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 141mA @ Temperature = -45°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 20    | 23.50 | 26.30     | 10.37             | 15.17              | 1.02      | 0.47    | 36.40       | 21.80            | 0.96         |
| 30    | 23.17 | 25.77     | 11.61             | 15.38              | 1.02      | 0.44    | 38.37       | 22.91            | 0.92         |
| 40    | 22.94 | 25.57     | 12.24             | 14.77              | 1.02      | 0.43    | 41.22       | 23.72            | 0.89         |
| 50    | 22.78 | 24.82     | 12.64             | 14.31              | 1.01      | 0.33    | 40.09       | 24.07            | 0.91         |
| 60    | 22.71 | 25.37     | 12.87             | 14.13              | 1.03      | 0.41    | 41.39       | 24.03            | 0.93         |
| 70    | 22.65 | 25.38     | 13.03             | 13.97              | 1.03      | 0.42    | 42.75       | 24.02            | 0.93         |
| 80    | 22.61 | 25.30     | 13.14             | 13.92              | 1.03      | 0.41    | 41.65       | 23.93            | 0.94         |
| 90    | 22.58 | 25.27     | 13.23             | 13.87              | 1.03      | 0.41    | 45.40       | 24.04            | 0.95         |
| 100   | 22.56 | 25.31     | 13.28             | 13.83              | 1.03      | 0.41    | 40.66       | 24.06            | 0.99         |
| 150   | 22.50 | 25.22     | 13.44             | 13.81              | 1.03      | 0.41    | 43.99       | 24.07            | 0.98         |
| 200   | 22.46 | 25.29     | 13.44             | 13.81              | 1.04      | 0.42    | 43.31       | 24.22            | 0.98         |
| 250   | 22.44 | 25.35     | 13.35             | 13.83              | 1.04      | 0.43    | 38.98       | 24.37            | 0.99         |
| 300   | 22.41 | 25.43     | 13.24             | 13.83              | 1.04      | 0.44    | 41.38       | 24.52            | 1.00         |
| 350   | 22.38 | 25.42     | 13.08             | 13.91              | 1.04      | 0.45    | 40.88       | 24.45            | 1.02         |
| 400   | 22.36 | 25.48     | 12.94             | 14.03              | 1.05      | 0.46    | 40.39       | 24.44            | 0.99         |
| 450   | 22.33 | 25.57     | 12.75             | 14.17              | 1.05      | 0.48    | 41.89       | 24.17            | 0.94         |
| 500   | 22.29 | 25.64     | 12.49             | 14.27              | 1.05      | 0.49    | 40.67       | 23.97            | 1.03         |
| 550   | 22.25 | 25.74     | 12.26             | 14.32              | 1.06      | 0.51    | 40.15       | 24.36            | 1.04         |
| 600   | 22.20 | 25.86     | 11.98             | 14.33              | 1.06      | 0.53    | 41.14       | 24.14            | 1.04         |
| 650   | 22.14 | 25.95     | 11.71             | 14.32              | 1.07      | 0.55    | 39.55       | 24.23            | 1.10         |
| 700   | 22.09 | 26.05     | 11.48             | 14.26              | 1.07      | 0.56    | 40.26       | 24.06            | 1.03         |
| 750   | 22.02 | 26.19     | 11.22             | 14.18              | 1.08      | 0.59    | 38.94       | 23.86            | 1.04         |
| 800   | 21.95 | 26.28     | 11.01             | 14.01              | 1.09      | 0.60    | 40.04       | 23.88            | 1.01         |
| 850   | 21.88 | 26.43     | 10.86             | 13.89              | 1.10      | 0.62    | 39.35       | 24.11            | 1.01         |
| 900   | 21.82 | 26.50     | 10.65             | 13.71              | 1.10      | 0.63    | 38.23       | 24.04            | 1.03         |
| 950   | 21.77 | 26.59     | 10.49             | 13.54              | 1.10      | 0.64    | 38.25       | 23.95            | 1.02         |
| 1000  | 21.70 | 26.81     | 10.33             | 13.31              | 1.12      | 0.67    | 38.51       | 24.38            | 1.02         |
| 1100  | 21.57 | 26.99     | 10.14             | 12.75              | 1.13      | 0.68    | 38.49       | 24.10            | 1.00         |
| 1200  | 21.43 | 27.25     | 10.06             | 12.16              | 1.15      | 0.71    | 37.89       | 24.16            | 1.10         |
| 1300  | 21.31 | 27.47     | 10.15             | 11.61              | 1.16      | 0.72    | 37.45       | 23.79            | 1.01         |
| 1400  | 21.19 | 27.80     | 10.33             | 11.06              | 1.19      | 0.73    | 37.75       | 23.75            | 1.06         |
| 1500  | 21.08 | 28.05     | 10.65             | 10.53              | 1.21      | 0.74    | 38.19       | 23.96            | 1.08         |
| 1600  | 20.98 | 28.30     | 11.13             | 10.10              | 1.23      | 0.75    | 36.63       | 23.61            | 1.09         |
| 1700  | 20.88 | 28.56     | 11.74             | 9.73               | 1.25      | 0.75    | 35.63       | 22.78            | 1.11         |
| 1800  | 20.77 | 28.90     | 12.39             | 9.42               | 1.28      | 0.77    | 36.93       | 23.79            | 1.05         |
| 1900  | 20.65 | 29.15     | 12.90             | 9.16               | 1.30      | 0.78    | 36.76       | 23.68            | 1.10         |
| 2000  | 20.49 | 29.62     | 13.02             | 8.95               | 1.35      | 0.80    | 35.56       | 23.26            | 1.12         |
| 2100  | 20.29 | 29.92     | 12.44             | 8.76               | 1.37      | 0.83    | 35.97       | 23.38            | 1.16         |
| 2200  | 20.04 | 30.38     | 11.21             | 8.58               | 1.40      | 0.87    | 35.61       | 22.93            | 1.22         |
| 2300  | 19.71 | 30.91     | 9.71              | 8.43               | 1.43      | 0.92    | 35.80       | 23.01            | 1.32         |
| 2400  | 19.30 | 31.41     | 8.23              | 8.25               | 1.46      | 0.98    | 34.83       | 22.43            | 1.47         |
| 2500  | 18.82 | 32.12     | 6.89              | 8.03               | 1.50      | 1.04    | 35.41       | 22.85            | 1.65         |



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 148mA @ Temperature = -45°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 20    | 23.54 | 26.29     | 10.36             | 15.30              | 1.01      | 0.46    | 40.44       | 22.31            | 1.00         |
| 30    | 23.20 | 25.78     | 11.61             | 15.43              | 1.02      | 0.43    | 43.50       | 23.37            | 0.90         |
| 40    | 22.97 | 25.59     | 12.21             | 14.86              | 1.02      | 0.43    | 39.85       | 24.10            | 0.89         |
| 50    | 22.81 | 25.94     | 12.77             | 14.22              | 1.04      | 0.47    | 39.87       | 24.45            | 0.93         |
| 60    | 22.74 | 25.42     | 12.86             | 14.17              | 1.03      | 0.41    | 42.55       | 24.41            | 0.92         |
| 70    | 22.68 | 25.32     | 13.01             | 14.02              | 1.03      | 0.41    | 40.87       | 24.40            | 0.94         |
| 80    | 22.64 | 25.29     | 13.11             | 13.96              | 1.03      | 0.40    | 41.90       | 24.31            | 0.95         |
| 90    | 22.61 | 25.32     | 13.21             | 13.90              | 1.03      | 0.41    | 42.67       | 24.48            | 0.99         |
| 100   | 22.59 | 25.27     | 13.28             | 13.90              | 1.03      | 0.40    | 39.10       | 24.44            | 1.00         |
| 150   | 22.53 | 25.32     | 13.45             | 13.85              | 1.04      | 0.42    | 41.09       | 24.52            | 1.00         |
| 200   | 22.49 | 25.31     | 13.46             | 13.85              | 1.04      | 0.42    | 41.33       | 24.67            | 1.00         |
| 250   | 22.47 | 25.32     | 13.35             | 13.84              | 1.04      | 0.42    | 37.98       | 24.82            | 0.98         |
| 300   | 22.45 | 25.34     | 13.28             | 13.81              | 1.04      | 0.43    | 45.97       | 24.90            | 0.99         |
| 350   | 22.42 | 25.43     | 13.13             | 13.85              | 1.04      | 0.44    | 43.05       | 24.91            | 1.04         |
| 400   | 22.39 | 25.52     | 12.99             | 13.89              | 1.05      | 0.46    | 38.91       | 24.83            | 1.01         |
| 450   | 22.37 | 25.58     | 12.81             | 13.98              | 1.05      | 0.47    | 43.37       | 24.64            | 1.00         |
| 500   | 22.33 | 25.64     | 12.54             | 14.02              | 1.05      | 0.48    | 46.76       | 24.44            | 1.02         |
| 550   | 22.29 | 25.75     | 12.32             | 14.05              | 1.06      | 0.50    | 40.38       | 24.83            | 1.04         |
| 600   | 22.24 | 25.84     | 12.06             | 14.02              | 1.06      | 0.52    | 41.50       | 24.61            | 1.06         |
| 650   | 22.19 | 25.93     | 11.79             | 13.96              | 1.07      | 0.53    | 40.18       | 24.62            | 1.07         |
| 700   | 22.14 | 26.02     | 11.58             | 13.86              | 1.07      | 0.55    | 40.94       | 24.53            | 1.04         |
| 750   | 22.07 | 26.15     | 11.31             | 13.74              | 1.08      | 0.57    | 42.23       | 24.35            | 1.01         |
| 800   | 22.00 | 26.28     | 11.11             | 13.57              | 1.08      | 0.59    | 41.97       | 24.28            | 1.06         |
| 850   | 21.93 | 26.44     | 10.96             | 13.45              | 1.09      | 0.61    | 42.26       | 24.60            | 1.03         |
| 900   | 21.87 | 26.48     | 10.77             | 13.27              | 1.10      | 0.62    | 39.91       | 24.45            | 1.04         |
| 950   | 21.82 | 26.59     | 10.60             | 13.09              | 1.10      | 0.63    | 40.45       | 24.36            | 1.09         |
| 1000  | 21.76 | 26.74     | 10.45             | 12.84              | 1.11      | 0.64    | 38.84       | 24.88            | 1.00         |
| 1100  | 21.63 | 27.02     | 10.25             | 12.30              | 1.13      | 0.67    | 39.18       | 24.60            | 1.05         |
| 1200  | 21.50 | 27.29     | 10.20             | 11.76              | 1.15      | 0.69    | 39.69       | 24.67            | 1.12         |
| 1300  | 21.37 | 27.52     | 10.28             | 11.22              | 1.16      | 0.70    | 38.52       | 24.30            | 1.07         |
| 1400  | 21.25 | 27.82     | 10.47             | 10.70              | 1.19      | 0.72    | 39.75       | 24.25            | 1.10         |
| 1500  | 21.15 | 28.10     | 10.81             | 10.21              | 1.21      | 0.72    | 39.89       | 24.37            | 1.09         |
| 1600  | 21.05 | 28.38     | 11.31             | 9.79               | 1.23      | 0.73    | 38.33       | 24.12            | 1.10         |
| 1700  | 20.95 | 28.70     | 11.93             | 9.45               | 1.26      | 0.74    | 38.24       | 23.17            | 1.07         |
| 1800  | 20.85 | 29.01     | 12.63             | 9.15               | 1.29      | 0.75    | 39.57       | 24.20            | 1.06         |
| 1900  | 20.73 | 29.31     | 13.19             | 8.90               | 1.31      | 0.77    | 38.84       | 24.08            | 1.11         |
| 2000  | 20.57 | 29.72     | 13.32             | 8.68               | 1.35      | 0.79    | 37.62       | 23.77            | 1.13         |
| 2100  | 20.38 | 30.18     | 12.74             | 8.50               | 1.39      | 0.82    | 37.90       | 23.88            | 1.16         |
| 2200  | 20.13 | 30.56     | 11.47             | 8.31               | 1.41      | 0.86    | 38.78       | 23.34            | 1.28         |
| 2300  | 19.81 | 31.20     | 9.90              | 8.13               | 1.46      | 0.91    | 37.89       | 23.41            | 1.36         |
| 2400  | 19.41 | 31.78     | 8.38              | 7.94               | 1.49      | 0.96    | 36.87       | 22.83            | 1.53         |
| 2500  | 18.94 | 32.47     | 7.01              | 7.70               | 1.53      | 1.01    | 37.38       | 23.26            | 1.63         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.75V, Id = 66mA @ Temperature = +105°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 20    | 21.91 | 26.13     | 10.33             | 14.35              | 1.06      | 0.62    | 30.09       | 14.03            | 1.45         |
| 30    | 21.69 | 25.62     | 12.17             | 15.32              | 1.06      | 0.59    | 31.43       | 15.22            | 1.40         |
| 40    | 21.52 | 25.26     | 13.30             | 15.25              | 1.06      | 0.57    | 32.31       | 16.32            | 1.36         |
| 50    | 21.39 | 25.47     | 14.27             | 14.77              | 1.08      | 0.59    | 31.59       | 17.03            | 1.40         |
| 60    | 21.34 | 25.04     | 14.61             | 14.86              | 1.06      | 0.55    | 32.31       | 17.23            | 1.44         |
| 70    | 21.30 | 24.95     | 14.92             | 14.76              | 1.06      | 0.54    | 32.54       | 17.40            | 1.43         |
| 80    | 21.26 | 24.85     | 15.08             | 14.75              | 1.06      | 0.53    | 32.77       | 17.42            | 1.47         |
| 90    | 21.24 | 24.90     | 15.20             | 14.69              | 1.06      | 0.54    | 33.20       | 17.49            | 1.50         |
| 100   | 21.22 | 24.84     | 15.22             | 14.70              | 1.06      | 0.53    | 32.42       | 17.56            | 1.49         |
| 150   | 21.16 | 24.88     | 14.86             | 14.79              | 1.07      | 0.54    | 33.60       | 17.75            | 1.50         |
| 200   | 21.11 | 24.88     | 14.12             | 15.09              | 1.07      | 0.55    | 33.41       | 17.90            | 1.50         |
| 250   | 21.07 | 24.91     | 13.30             | 15.55              | 1.07      | 0.57    | 33.46       | 17.99            | 1.50         |
| 300   | 21.02 | 24.99     | 12.52             | 16.06              | 1.07      | 0.59    | 33.53       | 18.05            | 1.52         |
| 350   | 20.96 | 25.04     | 11.74             | 16.69              | 1.07      | 0.62    | 32.50       | 18.05            | 1.54         |
| 400   | 20.89 | 25.16     | 11.07             | 17.44              | 1.07      | 0.65    | 31.86       | 17.98            | 1.55         |
| 450   | 20.81 | 25.29     | 10.42             | 18.26              | 1.08      | 0.68    | 32.22       | 17.84            | 1.50         |
| 500   | 20.71 | 25.42     | 9.82              | 19.15              | 1.08      | 0.72    | 32.31       | 17.72            | 1.57         |
| 550   | 20.61 | 25.57     | 9.32              | 20.07              | 1.09      | 0.75    | 32.13       | 18.01            | 1.56         |
| 600   | 20.50 | 25.63     | 8.86              | 20.93              | 1.09      | 0.78    | 31.56       | 17.85            | 1.60         |
| 650   | 20.38 | 25.81     | 8.47              | 21.58              | 1.09      | 0.81    | 31.21       | 17.84            | 1.63         |
| 700   | 20.26 | 25.91     | 8.15              | 21.80              | 1.10      | 0.84    | 31.14       | 17.74            | 1.63         |
| 750   | 20.13 | 26.06     | 7.85              | 21.71              | 1.10      | 0.87    | 31.08       | 17.63            | 1.56         |
| 800   | 20.01 | 26.13     | 7.60              | 21.06              | 1.11      | 0.89    | 30.85       | 17.68            | 1.61         |
| 850   | 19.88 | 26.26     | 7.40              | 20.22              | 1.11      | 0.92    | 30.57       | 17.84            | 1.62         |
| 900   | 19.76 | 26.36     | 7.21              | 19.20              | 1.11      | 0.94    | 30.41       | 17.77            | 1.64         |
| 950   | 19.64 | 26.43     | 7.07              | 18.18              | 1.11      | 0.95    | 30.72       | 17.64            | 1.63         |
| 1000  | 19.53 | 26.57     | 6.95              | 17.21              | 1.12      | 0.97    | 30.56       | 17.84            | 1.62         |
| 1100  | 19.29 | 26.74     | 6.82              | 15.45              | 1.13      | 0.99    | 30.24       | 17.76            | 1.66         |
| 1200  | 19.06 | 26.84     | 6.79              | 13.95              | 1.13      | 1.00    | 30.04       | 17.78            | 1.74         |
| 1300  | 18.84 | 26.97     | 6.86              | 12.73              | 1.14      | 1.00    | 30.06       | 17.57            | 1.74         |
| 1400  | 18.64 | 27.02     | 7.01              | 11.69              | 1.14      | 0.99    | 29.78       | 17.50            | 1.78         |
| 1500  | 18.45 | 27.11     | 7.21              | 10.83              | 1.15      | 0.99    | 29.81       | 17.64            | 1.82         |
| 1600  | 18.25 | 27.17     | 7.47              | 10.11              | 1.15      | 0.98    | 29.37       | 17.41            | 1.77         |
| 1700  | 18.05 | 27.23     | 7.75              | 9.54               | 1.16      | 0.97    | 29.04       | 16.98            | 1.80         |
| 1800  | 17.83 | 27.29     | 7.97              | 9.08               | 1.17      | 0.97    | 29.33       | 17.35            | 1.80         |
| 1900  | 17.56 | 27.36     | 8.00              | 8.72               | 1.17      | 0.97    | 28.96       | 17.16            | 1.85         |
| 2000  | 17.24 | 27.51     | 7.81              | 8.45               | 1.18      | 0.99    | 28.80       | 16.94            | 1.92         |
| 2100  | 16.85 | 27.69     | 7.35              | 8.26               | 1.19      | 1.02    | 28.50       | 16.90            | 2.00         |
| 2200  | 16.38 | 27.87     | 6.66              | 8.13               | 1.20      | 1.05    | 28.50       | 16.67            | 2.14         |
| 2300  | 15.82 | 28.29     | 5.86              | 8.07               | 1.23      | 1.10    | 28.01       | 16.64            | 2.31         |
| 2400  | 15.15 | 28.74     | 5.07              | 8.06               | 1.27      | 1.15    | 27.68       | 16.29            | 2.55         |
| 2500  | 14.40 | 29.19     | 4.34              | 8.07               | 1.32      | 1.21    | 27.83       | 16.32            | 2.82         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.00V, Id = 74mA @ Temperature = +105°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 20    | 22.06 | 26.22     | 10.37             | 14.08              | 1.06      | 0.61    | 32.73       | 15.08            | 1.43         |
| 30    | 21.84 | 25.71     | 12.14             | 14.87              | 1.06      | 0.58    | 32.84       | 16.25            | 1.41         |
| 40    | 21.67 | 25.29     | 13.20             | 14.76              | 1.05      | 0.55    | 32.93       | 17.42            | 1.35         |
| 50    | 21.54 | 25.66     | 14.08             | 14.30              | 1.08      | 0.58    | 33.00       | 18.03            | 1.39         |
| 60    | 21.49 | 25.13     | 14.42             | 14.35              | 1.06      | 0.53    | 33.28       | 18.14            | 1.42         |
| 70    | 21.44 | 25.02     | 14.70             | 14.24              | 1.06      | 0.52    | 33.61       | 18.30            | 1.43         |
| 80    | 21.41 | 25.01     | 14.86             | 14.23              | 1.06      | 0.52    | 34.09       | 18.30            | 1.46         |
| 90    | 21.39 | 24.98     | 14.94             | 14.21              | 1.06      | 0.52    | 34.06       | 18.44            | 1.48         |
| 100   | 21.37 | 24.96     | 14.98             | 14.22              | 1.06      | 0.52    | 34.31       | 18.51            | 1.50         |
| 150   | 21.31 | 24.98     | 14.67             | 14.29              | 1.06      | 0.53    | 35.33       | 18.62            | 1.51         |
| 200   | 21.26 | 25.02     | 14.03             | 14.56              | 1.07      | 0.55    | 35.37       | 18.71            | 1.51         |
| 250   | 21.23 | 25.04     | 13.28             | 14.97              | 1.07      | 0.56    | 34.51       | 18.87            | 1.51         |
| 300   | 21.19 | 25.10     | 12.59             | 15.42              | 1.07      | 0.58    | 33.95       | 18.94            | 1.52         |
| 350   | 21.13 | 25.19     | 11.87             | 16.02              | 1.07      | 0.61    | 33.86       | 18.95            | 1.55         |
| 400   | 21.07 | 25.33     | 11.25             | 16.66              | 1.08      | 0.64    | 33.84       | 18.88            | 1.55         |
| 450   | 20.99 | 25.38     | 10.65             | 17.44              | 1.08      | 0.66    | 33.72       | 18.73            | 1.50         |
| 500   | 20.91 | 25.51     | 10.07             | 18.26              | 1.08      | 0.70    | 33.57       | 18.54            | 1.54         |
| 550   | 20.82 | 25.60     | 9.59              | 19.12              | 1.08      | 0.73    | 32.96       | 18.93            | 1.54         |
| 600   | 20.72 | 25.77     | 9.15              | 19.95              | 1.09      | 0.76    | 32.75       | 18.77            | 1.59         |
| 650   | 20.61 | 25.83     | 8.76              | 20.73              | 1.09      | 0.79    | 32.44       | 18.77            | 1.61         |
| 700   | 20.50 | 26.01     | 8.44              | 21.20              | 1.10      | 0.82    | 32.65       | 18.68            | 1.60         |
| 750   | 20.38 | 26.13     | 8.15              | 21.36              | 1.10      | 0.85    | 32.42       | 18.56            | 1.61         |
| 800   | 20.26 | 26.21     | 7.91              | 21.10              | 1.11      | 0.87    | 32.11       | 18.54            | 1.59         |
| 850   | 20.15 | 26.32     | 7.70              | 20.53              | 1.11      | 0.89    | 31.90       | 18.71            | 1.63         |
| 900   | 20.03 | 26.41     | 7.52              | 19.67              | 1.11      | 0.91    | 31.70       | 18.64            | 1.63         |
| 950   | 19.93 | 26.51     | 7.37              | 18.74              | 1.12      | 0.93    | 31.81       | 18.51            | 1.64         |
| 1000  | 19.82 | 26.61     | 7.25              | 17.77              | 1.12      | 0.94    | 31.94       | 18.73            | 1.63         |
| 1100  | 19.59 | 26.76     | 7.13              | 15.99              | 1.13      | 0.96    | 31.26       | 18.65            | 1.69         |
| 1200  | 19.38 | 26.94     | 7.09              | 14.44              | 1.14      | 0.98    | 31.30       | 18.68            | 1.73         |
| 1300  | 19.17 | 27.08     | 7.17              | 13.17              | 1.15      | 0.98    | 31.16       | 18.47            | 1.71         |
| 1400  | 18.98 | 27.13     | 7.32              | 12.08              | 1.15      | 0.98    | 31.09       | 18.40            | 1.76         |
| 1500  | 18.80 | 27.21     | 7.54              | 11.19              | 1.16      | 0.97    | 31.05       | 18.55            | 1.76         |
| 1600  | 18.61 | 27.30     | 7.81              | 10.44              | 1.17      | 0.96    | 30.66       | 18.34            | 1.79         |
| 1700  | 18.42 | 27.37     | 8.11              | 9.84               | 1.17      | 0.96    | 30.31       | 17.80            | 1.74         |
| 1800  | 18.21 | 27.43     | 8.34              | 9.36               | 1.18      | 0.95    | 30.59       | 18.21            | 1.81         |
| 1900  | 17.96 | 27.53     | 8.39              | 8.97               | 1.18      | 0.96    | 30.25       | 18.12            | 1.85         |
| 2000  | 17.65 | 27.64     | 8.19              | 8.70               | 1.19      | 0.98    | 30.06       | 17.90            | 1.87         |
| 2100  | 17.28 | 27.83     | 7.71              | 8.49               | 1.20      | 1.00    | 29.74       | 17.79            | 1.98         |
| 2200  | 16.83 | 28.17     | 6.98              | 8.36               | 1.23      | 1.04    | 29.66       | 17.56            | 2.12         |
| 2300  | 16.28 | 28.43     | 6.13              | 8.29               | 1.24      | 1.09    | 29.40       | 17.54            | 2.32         |
| 2400  | 15.64 | 28.82     | 5.30              | 8.27               | 1.27      | 1.15    | 28.97       | 17.20            | 2.52         |
| 2500  | 14.90 | 29.28     | 4.52              | 8.28               | 1.31      | 1.20    | 29.12       | 17.26            | 2.80         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.25V, Id = 83mA @ Temperature = +105°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 20    | 22.19 | 26.35     | 10.38             | 13.77              | 1.06      | 0.61    | 32.80       | 16.12            | 1.45         |
| 30    | 21.96 | 25.85     | 12.07             | 14.48              | 1.06      | 0.58    | 34.21       | 17.27            | 1.39         |
| 40    | 21.79 | 25.51     | 13.11             | 14.33              | 1.05      | 0.55    | 34.02       | 18.33            | 1.38         |
| 50    | 21.67 | 25.91     | 13.91             | 13.88              | 1.09      | 0.59    | 33.56       | 18.92            | 1.41         |
| 60    | 21.61 | 25.27     | 14.24             | 13.95              | 1.06      | 0.53    | 34.51       | 19.01            | 1.46         |
| 70    | 21.57 | 25.13     | 14.49             | 13.85              | 1.06      | 0.52    | 35.22       | 19.16            | 1.45         |
| 80    | 21.53 | 25.15     | 14.64             | 13.84              | 1.06      | 0.52    | 34.64       | 19.15            | 1.46         |
| 90    | 21.51 | 25.14     | 14.71             | 13.80              | 1.06      | 0.52    | 34.97       | 19.22            | 1.48         |
| 100   | 21.49 | 25.10     | 14.74             | 13.81              | 1.06      | 0.52    | 35.46       | 19.29            | 1.50         |
| 150   | 21.44 | 25.10     | 14.50             | 13.87              | 1.06      | 0.52    | 36.26       | 19.39            | 1.48         |
| 200   | 21.39 | 25.11     | 13.93             | 14.12              | 1.06      | 0.53    | 36.02       | 19.55            | 1.53         |
| 250   | 21.36 | 25.16     | 13.27             | 14.50              | 1.07      | 0.55    | 36.42       | 19.65            | 1.53         |
| 300   | 21.33 | 25.18     | 12.64             | 14.94              | 1.07      | 0.57    | 34.87       | 19.79            | 1.52         |
| 350   | 21.27 | 25.29     | 11.98             | 15.45              | 1.07      | 0.60    | 34.72       | 19.81            | 1.56         |
| 400   | 21.22 | 25.40     | 11.40             | 16.04              | 1.08      | 0.62    | 34.79       | 19.74            | 1.55         |
| 450   | 21.15 | 25.49     | 10.85             | 16.74              | 1.08      | 0.65    | 34.72       | 19.53            | 1.52         |
| 500   | 21.08 | 25.55     | 10.30             | 17.49              | 1.08      | 0.68    | 34.51       | 19.42            | 1.55         |
| 550   | 20.99 | 25.69     | 9.83              | 18.27              | 1.08      | 0.71    | 34.21       | 19.74            | 1.55         |
| 600   | 20.90 | 25.79     | 9.41              | 19.06              | 1.09      | 0.74    | 33.69       | 19.57            | 1.60         |
| 650   | 20.80 | 25.91     | 9.02              | 19.82              | 1.09      | 0.77    | 33.90       | 19.59            | 1.61         |
| 700   | 20.70 | 26.07     | 8.72              | 20.35              | 1.10      | 0.80    | 33.83       | 19.49            | 1.59         |
| 750   | 20.59 | 26.15     | 8.43              | 20.70              | 1.10      | 0.82    | 33.15       | 19.38            | 1.56         |
| 800   | 20.48 | 26.27     | 8.19              | 20.70              | 1.11      | 0.84    | 32.92       | 19.37            | 1.60         |
| 850   | 20.38 | 26.41     | 7.99              | 20.40              | 1.12      | 0.87    | 32.78       | 19.55            | 1.63         |
| 900   | 20.27 | 26.48     | 7.80              | 19.72              | 1.12      | 0.89    | 32.50       | 19.48            | 1.64         |
| 950   | 20.17 | 26.56     | 7.65              | 18.95              | 1.12      | 0.90    | 32.88       | 19.36            | 1.63         |
| 1000  | 20.07 | 26.65     | 7.54              | 18.08              | 1.12      | 0.92    | 32.93       | 19.59            | 1.64         |
| 1100  | 19.86 | 26.84     | 7.41              | 16.36              | 1.13      | 0.94    | 32.43       | 19.42            | 1.66         |
| 1200  | 19.66 | 27.01     | 7.38              | 14.81              | 1.14      | 0.95    | 32.31       | 19.45            | 1.70         |
| 1300  | 19.46 | 27.15     | 7.46              | 13.52              | 1.15      | 0.96    | 32.11       | 19.24            | 1.73         |
| 1400  | 19.28 | 27.26     | 7.61              | 12.41              | 1.16      | 0.96    | 32.28       | 19.18            | 1.76         |
| 1500  | 19.11 | 27.35     | 7.85              | 11.48              | 1.17      | 0.95    | 32.17       | 19.34            | 1.77         |
| 1600  | 18.93 | 27.36     | 8.14              | 10.71              | 1.17      | 0.94    | 31.77       | 19.13            | 1.75         |
| 1700  | 18.75 | 27.49     | 8.46              | 10.10              | 1.18      | 0.94    | 31.26       | 18.59            | 1.77         |
| 1800  | 18.55 | 27.56     | 8.71              | 9.61               | 1.19      | 0.94    | 31.62       | 19.02            | 1.73         |
| 1900  | 18.31 | 27.71     | 8.78              | 9.21               | 1.20      | 0.95    | 31.28       | 18.94            | 1.80         |
| 2000  | 18.02 | 27.84     | 8.57              | 8.92               | 1.21      | 0.96    | 31.23       | 18.72            | 1.89         |
| 2100  | 17.66 | 28.02     | 8.06              | 8.71               | 1.22      | 0.99    | 30.92       | 18.63            | 1.96         |
| 2200  | 17.23 | 28.25     | 7.29              | 8.57               | 1.23      | 1.03    | 30.68       | 18.41            | 2.09         |
| 2300  | 16.70 | 28.59     | 6.41              | 8.48               | 1.25      | 1.08    | 30.47       | 18.40            | 2.25         |
| 2400  | 16.08 | 28.96     | 5.51              | 8.47               | 1.27      | 1.14    | 30.04       | 17.98            | 2.48         |
| 2500  | 15.36 | 29.44     | 4.70              | 8.46               | 1.31      | 1.20    | 30.23       | 18.15            | 2.78         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 131mA @ Temperature = +105°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 20    | 22.37 | 27.01     | 9.88              | 11.98              | 1.07      | 0.62    | 34.29       | 19.65            | 1.48         |
| 30    | 22.20 | 26.37     | 11.44             | 12.71              | 1.06      | 0.58    | 36.69       | 20.72            | 1.45         |
| 40    | 22.06 | 25.94     | 12.30             | 12.71              | 1.06      | 0.54    | 38.50       | 21.56            | 1.42         |
| 50    | 21.95 | 26.16     | 13.06             | 12.44              | 1.08      | 0.56    | 38.13       | 22.05            | 1.47         |
| 60    | 21.91 | 25.82     | 13.23             | 12.48              | 1.06      | 0.53    | 36.54       | 22.17            | 1.48         |
| 70    | 21.88 | 25.70     | 13.43             | 12.43              | 1.06      | 0.52    | 38.28       | 22.33            | 1.49         |
| 80    | 21.85 | 25.69     | 13.54             | 12.43              | 1.06      | 0.52    | 37.80       | 22.35            | 1.51         |
| 90    | 21.84 | 25.62     | 13.62             | 12.42              | 1.06      | 0.51    | 39.05       | 22.46            | 1.55         |
| 100   | 21.83 | 25.55     | 13.63             | 12.43              | 1.06      | 0.50    | 36.40       | 22.49            | 1.55         |
| 150   | 21.80 | 25.58     | 13.49             | 12.49              | 1.07      | 0.51    | 37.23       | 22.72            | 1.56         |
| 200   | 21.78 | 25.52     | 13.13             | 12.66              | 1.06      | 0.51    | 39.21       | 22.91            | 1.58         |
| 250   | 21.78 | 25.61     | 12.75             | 12.90              | 1.07      | 0.52    | 35.73       | 22.97            | 1.58         |
| 300   | 21.77 | 25.61     | 12.37             | 13.17              | 1.07      | 0.53    | 39.27       | 23.15            | 1.57         |
| 350   | 21.74 | 25.68     | 11.99             | 13.48              | 1.07      | 0.55    | 38.02       | 23.18            | 1.61         |
| 400   | 21.72 | 25.73     | 11.65             | 13.80              | 1.07      | 0.57    | 39.13       | 23.14            | 1.61         |
| 450   | 21.69 | 25.73     | 11.30             | 14.18              | 1.07      | 0.58    | 38.23       | 23.04            | 1.57         |
| 500   | 21.64 | 25.86     | 10.93             | 14.57              | 1.08      | 0.60    | 39.28       | 22.88            | 1.61         |
| 550   | 21.60 | 25.97     | 10.63             | 14.96              | 1.08      | 0.63    | 37.76       | 23.21            | 1.61         |
| 600   | 21.55 | 26.06     | 10.31             | 15.34              | 1.09      | 0.65    | 37.75       | 23.05            | 1.66         |
| 650   | 21.49 | 26.15     | 10.02             | 15.70              | 1.09      | 0.67    | 37.50       | 23.12            | 1.67         |
| 700   | 21.42 | 26.27     | 9.80              | 15.99              | 1.10      | 0.69    | 37.72       | 23.03            | 1.66         |
| 750   | 21.35 | 26.33     | 9.57              | 16.27              | 1.10      | 0.71    | 37.08       | 22.86            | 1.63         |
| 800   | 21.28 | 26.47     | 9.37              | 16.43              | 1.11      | 0.73    | 36.67       | 22.87            | 1.63         |
| 850   | 21.21 | 26.57     | 9.22              | 16.51              | 1.12      | 0.75    | 36.71       | 23.06            | 1.66         |
| 900   | 21.14 | 26.67     | 9.05              | 16.45              | 1.12      | 0.77    | 36.59       | 22.91            | 1.65         |
| 950   | 21.07 | 26.76     | 8.93              | 16.28              | 1.13      | 0.78    | 36.75       | 22.92            | 1.62         |
| 1000  | 20.99 | 26.86     | 8.83              | 16.00              | 1.13      | 0.79    | 36.20       | 23.18            | 1.63         |
| 1100  | 20.84 | 27.09     | 8.71              | 15.24              | 1.15      | 0.82    | 36.02       | 22.89            | 1.68         |
| 1200  | 20.68 | 27.24     | 8.71              | 14.31              | 1.16      | 0.83    | 35.87       | 22.95            | 1.72         |
| 1300  | 20.53 | 27.47     | 8.81              | 13.41              | 1.18      | 0.85    | 35.68       | 22.69            | 1.71         |
| 1400  | 20.39 | 27.69     | 8.99              | 12.56              | 1.20      | 0.85    | 35.32       | 22.63            | 1.75         |
| 1500  | 20.26 | 27.90     | 9.28              | 11.78              | 1.22      | 0.86    | 35.67       | 22.70            | 1.78         |
| 1600  | 20.12 | 28.03     | 9.65              | 11.12              | 1.23      | 0.86    | 35.09       | 22.43            | 1.75         |
| 1700  | 19.98 | 28.27     | 10.09             | 10.57              | 1.25      | 0.86    | 34.67       | 21.75            | 1.77         |
| 1800  | 19.82 | 28.44     | 10.45             | 10.12              | 1.27      | 0.86    | 35.21       | 22.40            | 1.78         |
| 1900  | 19.64 | 28.65     | 10.60             | 9.73               | 1.28      | 0.88    | 35.03       | 22.36            | 1.81         |
| 2000  | 19.41 | 28.88     | 10.41             | 9.44               | 1.30      | 0.90    | 34.57       | 22.04            | 1.88         |
| 2100  | 19.13 | 29.16     | 9.79              | 9.22               | 1.32      | 0.93    | 34.07       | 22.02            | 1.95         |
| 2200  | 18.78 | 29.49     | 8.81              | 9.03               | 1.34      | 0.97    | 33.84       | 21.64            | 2.08         |
| 2300  | 18.34 | 29.74     | 7.69              | 8.90               | 1.34      | 1.02    | 34.02       | 21.55            | 2.26         |
| 2400  | 17.81 | 30.27     | 6.57              | 8.83               | 1.38      | 1.08    | 33.31       | 21.17            | 2.48         |
| 2500  | 17.19 | 30.74     | 5.56              | 8.72               | 1.40      | 1.14    | 33.62       | 21.34            | 2.75         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 139mA @ Temperature = +105°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 20    | 22.59 | 26.98     | 10.33             | 12.77              | 1.07      | 0.61    | 36.54       | 20.36            | 1.53         |
| 30    | 22.36 | 26.27     | 11.76             | 13.30              | 1.05      | 0.56    | 35.31       | 21.34            | 1.47         |
| 40    | 22.20 | 25.97     | 12.54             | 13.10              | 1.05      | 0.54    | 36.60       | 22.07            | 1.47         |
| 50    | 22.07 | 25.34     | 13.24             | 12.85              | 1.04      | 0.47    | 35.60       | 22.54            | 1.49         |
| 60    | 22.03 | 25.70     | 13.36             | 12.76              | 1.06      | 0.51    | 37.27       | 22.64            | 1.53         |
| 70    | 21.98 | 25.71     | 13.53             | 12.66              | 1.06      | 0.51    | 39.12       | 22.79            | 1.51         |
| 80    | 21.95 | 25.66     | 13.59             | 12.62              | 1.06      | 0.51    | 38.47       | 22.80            | 1.55         |
| 90    | 21.93 | 25.60     | 13.67             | 12.62              | 1.06      | 0.50    | 39.19       | 22.91            | 1.59         |
| 100   | 21.91 | 25.65     | 13.70             | 12.60              | 1.06      | 0.51    | 35.74       | 22.99            | 1.61         |
| 150   | 21.88 | 25.54     | 13.54             | 12.63              | 1.06      | 0.50    | 38.29       | 23.16            | 1.62         |
| 200   | 21.85 | 25.55     | 13.24             | 12.77              | 1.06      | 0.51    | 37.77       | 23.34            | 1.59         |
| 250   | 21.83 | 25.67     | 12.86             | 12.97              | 1.07      | 0.53    | 37.90       | 23.45            | 1.58         |
| 300   | 21.82 | 25.68     | 12.52             | 13.22              | 1.07      | 0.53    | 39.93       | 23.56            | 1.62         |
| 350   | 21.79 | 25.74     | 12.16             | 13.51              | 1.07      | 0.55    | 38.31       | 23.66            | 1.63         |
| 400   | 21.76 | 25.74     | 11.81             | 13.81              | 1.07      | 0.56    | 38.50       | 23.62            | 1.65         |
| 450   | 21.73 | 25.82     | 11.44             | 14.14              | 1.08      | 0.58    | 38.76       | 23.52            | 1.61         |
| 500   | 21.69 | 25.94     | 11.07             | 14.50              | 1.08      | 0.60    | 37.75       | 23.37            | 1.62         |
| 550   | 21.64 | 25.95     | 10.75             | 14.86              | 1.08      | 0.62    | 38.87       | 23.70            | 1.65         |
| 600   | 21.59 | 26.10     | 10.45             | 15.17              | 1.09      | 0.64    | 38.89       | 23.55            | 1.68         |
| 650   | 21.53 | 26.21     | 10.15             | 15.49              | 1.10      | 0.66    | 38.06       | 23.62            | 1.69         |
| 700   | 21.47 | 26.31     | 9.93              | 15.74              | 1.10      | 0.68    | 38.03       | 23.45            | 1.68         |
| 750   | 21.40 | 26.37     | 9.70              | 15.96              | 1.11      | 0.70    | 37.00       | 23.37            | 1.66         |
| 800   | 21.33 | 26.54     | 9.51              | 16.08              | 1.12      | 0.73    | 37.33       | 23.39            | 1.67         |
| 850   | 21.27 | 26.62     | 9.35              | 16.15              | 1.12      | 0.74    | 36.45       | 23.49            | 1.68         |
| 900   | 21.20 | 26.70     | 9.19              | 16.06              | 1.12      | 0.76    | 36.45       | 23.43            | 1.68         |
| 950   | 21.13 | 26.84     | 9.06              | 15.91              | 1.13      | 0.77    | 36.60       | 23.36            | 1.63         |
| 1000  | 21.07 | 26.93     | 8.96              | 15.63              | 1.14      | 0.79    | 36.75       | 23.61            | 1.66         |
| 1100  | 20.92 | 27.15     | 8.85              | 14.92              | 1.15      | 0.81    | 36.12       | 23.42            | 1.71         |
| 1200  | 20.78 | 27.30     | 8.85              | 14.07              | 1.17      | 0.82    | 36.69       | 23.39            | 1.76         |
| 1300  | 20.63 | 27.55     | 8.96              | 13.21              | 1.19      | 0.83    | 36.30       | 23.14            | 1.76         |
| 1400  | 20.50 | 27.70     | 9.16              | 12.41              | 1.20      | 0.84    | 36.18       | 23.07            | 1.80         |
| 1500  | 20.37 | 27.98     | 9.46              | 11.67              | 1.23      | 0.84    | 36.36       | 23.14            | 1.73         |
| 1600  | 20.24 | 28.15     | 9.85              | 11.04              | 1.24      | 0.84    | 36.11       | 22.88            | 1.77         |
| 1700  | 20.10 | 28.33     | 10.30             | 10.51              | 1.26      | 0.85    | 34.81       | 22.20            | 1.74         |
| 1800  | 19.95 | 28.59     | 10.69             | 10.07              | 1.28      | 0.85    | 35.41       | 22.96            | 1.79         |
| 1900  | 19.78 | 28.80     | 10.85             | 9.69               | 1.30      | 0.87    | 35.79       | 22.82            | 1.84         |
| 2000  | 19.56 | 29.05     | 10.66             | 9.40               | 1.32      | 0.89    | 35.28       | 22.51            | 1.90         |
| 2100  | 19.28 | 29.37     | 10.03             | 9.17               | 1.34      | 0.92    | 35.40       | 22.49            | 1.98         |
| 2200  | 18.95 | 29.65     | 9.02              | 8.98               | 1.35      | 0.96    | 34.04       | 22.12            | 2.12         |
| 2300  | 18.52 | 30.03     | 7.85              | 8.84               | 1.36      | 1.01    | 34.70       | 22.03            | 2.29         |
| 2400  | 18.00 | 30.51     | 6.71              | 8.73               | 1.40      | 1.07    | 33.72       | 21.56            | 2.50         |
| 2500  | 17.39 | 31.04     | 5.67              | 8.61               | 1.43      | 1.13    | 33.78       | 21.84            | 2.77         |



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 145mA @ Temperature = +105°C








| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 20    | 22.48 | 26.97     | 9.98              | 12.20              | 1.07      | 0.61    | 34.32       | 20.25            | 1.57         |
| 30    | 22.29 | 26.36     | 11.45             | 12.85              | 1.06      | 0.57    | 36.79       | 21.48            | 1.53         |
| 40    | 22.15 | 26.16     | 12.31             | 12.78              | 1.06      | 0.56    | 37.63       | 22.27            | 1.49         |
| 50    | 22.03 | 25.48     | 12.94             | 12.54              | 1.04      | 0.49    | 38.52       | 22.78            | 1.54         |
| 60    | 21.99 | 25.74     | 13.14             | 12.51              | 1.06      | 0.51    | 36.20       | 22.92            | 1.59         |
| 70    | 21.96 | 25.82     | 13.31             | 12.44              | 1.06      | 0.52    | 38.13       | 23.10            | 1.57         |
| 80    | 21.93 | 25.72     | 13.41             | 12.42              | 1.06      | 0.51    | 38.61       | 23.14            | 1.62         |
| 90    | 21.91 | 25.68     | 13.49             | 12.41              | 1.06      | 0.51    | 38.55       | 23.25            | 1.61         |
| 100   | 21.90 | 25.72     | 13.50             | 12.40              | 1.07      | 0.51    | 36.50       | 23.33            | 1.65         |
| 150   | 21.87 | 25.59     | 13.36             | 12.44              | 1.06      | 0.50    | 37.63       | 23.53            | 1.65         |
| 200   | 21.85 | 25.61     | 13.03             | 12.57              | 1.06      | 0.51    | 38.36       | 23.73            | 1.63         |
| 250   | 21.84 | 25.64     | 12.69             | 12.78              | 1.07      | 0.52    | 37.16       | 23.79            | 1.62         |
| 300   | 21.84 | 25.67     | 12.37             | 13.00              | 1.07      | 0.53    | 38.84       | 23.97            | 1.63         |
| 350   | 21.82 | 25.74     | 12.02             | 13.25              | 1.07      | 0.54    | 36.36       | 24.01            | 1.65         |
| 400   | 21.79 | 25.80     | 11.71             | 13.52              | 1.07      | 0.56    | 36.82       | 23.99            | 1.67         |
| 450   | 21.77 | 25.90     | 11.40             | 13.83              | 1.08      | 0.58    | 38.37       | 23.88            | 1.63         |
| 500   | 21.73 | 25.96     | 11.05             | 14.12              | 1.08      | 0.59    | 38.46       | 23.73            | 1.65         |
| 550   | 21.69 | 26.03     | 10.77             | 14.43              | 1.08      | 0.61    | 37.90       | 24.06            | 1.67         |
| 600   | 21.64 | 26.11     | 10.49             | 14.70              | 1.09      | 0.63    | 38.95       | 23.92            | 1.69         |
| 650   | 21.59 | 26.21     | 10.21             | 14.96              | 1.09      | 0.65    | 38.57       | 23.99            | 1.72         |
| 700   | 21.54 | 26.35     | 10.02             | 15.17              | 1.10      | 0.67    | 37.60       | 23.83            | 1.71         |
| 750   | 21.47 | 26.39     | 9.80              | 15.31              | 1.10      | 0.69    | 37.81       | 23.74            | 1.69         |
| 800   | 21.40 | 26.50     | 9.62              | 15.43              | 1.11      | 0.71    | 37.31       | 23.68            | 1.67         |
| 850   | 21.34 | 26.62     | 9.46              | 15.45              | 1.12      | 0.72    | 37.87       | 23.86            | 1.71         |
| 900   | 21.27 | 26.71     | 9.32              | 15.38              | 1.12      | 0.74    | 36.90       | 23.80            | 1.72         |
| 950   | 21.21 | 26.84     | 9.19              | 15.23              | 1.13      | 0.76    | 37.66       | 23.74            | 1.79         |
| 1000  | 21.14 | 26.92     | 9.10              | 15.00              | 1.14      | 0.77    | 37.54       | 24.00            | 1.67         |
| 1100  | 21.00 | 27.13     | 9.00              | 14.38              | 1.15      | 0.79    | 36.90       | 23.70            | 1.74         |
| 1200  | 20.86 | 27.35     | 9.00              | 13.62              | 1.17      | 0.81    | 36.57       | 23.76            | 1.73         |
| 1300  | 20.72 | 27.60     | 9.11              | 12.85              | 1.19      | 0.82    | 36.82       | 23.52            | 1.78         |
| 1400  | 20.59 | 27.82     | 9.32              | 12.12              | 1.21      | 0.83    | 36.71       | 23.45            | 1.79         |
| 1500  | 20.46 | 28.02     | 9.62              | 11.43              | 1.23      | 0.83    | 36.59       | 23.51            | 1.79         |
| 1600  | 20.33 | 28.26     | 10.01             | 10.84              | 1.25      | 0.83    | 36.23       | 23.26            | 1.82         |
| 1700  | 20.20 | 28.41     | 10.48             | 10.35              | 1.26      | 0.83    | 35.42       | 22.57            | 1.79         |
| 1800  | 20.06 | 28.69     | 10.88             | 9.93               | 1.29      | 0.84    | 36.47       | 23.35            | 1.82         |
| 1900  | 19.89 | 28.90     | 11.06             | 9.56               | 1.30      | 0.85    | 36.10       | 23.20            | 1.86         |
| 2000  | 19.67 | 29.29     | 10.87             | 9.29               | 1.34      | 0.88    | 35.97       | 22.90            | 1.93         |
| 2100  | 19.41 | 29.52     | 10.22             | 9.06               | 1.35      | 0.91    | 36.08       | 22.88            | 2.03         |
| 2200  | 19.08 | 29.82     | 9.19              | 8.86               | 1.36      | 0.95    | 34.71       | 22.52            | 2.14         |
| 2300  | 18.66 | 30.26     | 7.99              | 8.72               | 1.38      | 1.00    | 35.08       | 22.42            | 2.31         |
| 2400  | 18.15 | 30.76     | 6.83              | 8.60               | 1.42      | 1.06    | 34.61       | 21.85            | 2.52         |
| 2500  | 17.55 | 31.29     | 5.77              | 8.44               | 1.45      | 1.12    | 34.52       | 22.15            | 2.82         |

## Typical Performance Curves





## Typical Performance Curves



**Mini-Circuits®**  
ISO 9001 ISO 14001 AS 9100 CERTIFIED









[minicircuits.com](http://minicircuits.com)

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)










IF/RF MICROWAVE COMPONENTS


## Typical Performance Curves




## Typical Performance Curves



### Outline Dimensions



### PCB Land Pattern



SUGGESTED LAYOUT,  
TOLERANCE TO BE WITHIN  $\pm .002$

**Weight: .02 Grams**

**Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3 Pl.  $\pm .004$**

### Notes:

1. Case material: Plastic.
2. Termination finish:
  - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

# Tape & Reel Packaging TR-F66



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel<br>see note |                  |
|----------------|-------------------------|-------------------|------------------------------|------------------|
| 8              | 4                       | 7                 | Small quantity standard      | 20               |
|                |                         |                   |                              | 50               |
|                |                         |                   |                              | 100              |
|                |                         |                   |                              | 200              |
|                |                         |                   |                              | 500              |
|                |                         | 7                 | Standard                     | 1000, 2000, 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)

**Mini-Circuits®**


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION | DATE     | DR  | AUTH |
|-----|---------|-------------|----------|-----|------|
| OR  | M171588 | NEW RELEASE | 12/20/18 | ITG | GH   |
|     |         |             |          |     |      |
|     |         |             |          |     |      |

SUGGESTED MOUNTING CONFIGURATION FOR  
DQ1225 CASE STYLE, "12AM05" PIN CODE



| COMPONENT     | SIZE |
|---------------|------|
| C1...C7;L2;R1 | 0402 |
| L1            | 0805 |

NOTES:

- TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020"±.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- CHIP COMPONENT FOOTPRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-TSS-23LN+ OR TB-TSS-23HLN+.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED<br>DIMENSIONS ARE IN INCHES<br>TOLERANCES ON:<br>2 PL DECIMALS ±<br>3 PL DECIMALS ± .005<br>ANGLES ±<br>FRACTIONS ± | INITIALS |     | DATE     |
|--|----------|-----|----------|
|  | DRAWN    | ITG | 12/19/18 |
|  | CHECKED  | GF  | 12/20/18 |
|  | APPROVED | GH  | 12/20/18 |



**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

PL, 12AM05, DQ1225, TB-TSS-23LN+/23HLN+

Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

| SIZE  | CODE IDENT | DRAWING NO: | REV:   |
|-------|------------|-------------|--------|
| A     | 15542      | 98-PL-619   | OR     |
| FILE: | 98PL619    | SCALE:      | 8:1    |
|       |            | SHEET:      | 1 OF 1 |

# Evaluation Board and Circuit




Schematic Diagram

| Component | Size | Value   | Part Number        | Manufacturer |
|-----------|------|---------|--------------------|--------------|
| C1        | 0402 | 0.1uF   | GRM155R71C104KA88D | Murata       |
| C2        | 0402 | 1.2pF   | GRM1555C1H1R2CA1D  | Murata       |
| C3        | 0402 | 0.1uF   | GRM155R71C104KA88D | Murata       |
| C4        | 0402 | 0.1uF   | GRM155R71C104KA88D | Murata       |
| C5        | 0402 | 1000pF  | GRM1555C1H102JA01D | Murata       |
| C6        | 0402 | 10000pF | GRM155R71E103KA01D | Murata       |
| C7        | 0402 | 0.1uF   | GRM155R71C104KA88D | Murata       |
| L1        | 0805 | 680nH   | 0805LS-681XJLB     | Coilcraft    |
| L2        | 0402 | 1.0nH   | 0402CS-1N0XJLW     | Coilcraft    |
| R1        | 0402 | 1.2KOhm | RK73H1ETTP1201F    | Koa          |

**NOTES:**

1. 50 Ohm SMA Female Connectors.
2. PCB Material: Roger R04350B or equivalent, Dielectric constant=3.5, Thickness=0.02 inch





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition  | Reference/Spec  |
|--------------------------------|--|---|
| Operating Temperature          | -40° to 95° C / 105° C<br>Ambient Environment  | Individual Model Data Sheet                                     |
| Storage Temperature            | -55° to 100° C or -65° to 150°<br>Ambient Environment  | Individual Model Data Sheet                                     |
| Thermal Shock                  | -55° to 100°C, 100 cycles  | MIL-STD-202, Method 107, Condition A-3, except +100°C           |
| Mechanical Shock               | 1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only   | MIL-STD-883, Method 2002, Condition B, except Y1 direction only |
| Vibration (Variable Frequency) | 50g peak   | MIL-STD-883, Method 2007, Condition B                           |
| Autoclave                      | 15 psig, 100% RH, 121°C, 96 hours  | JESD22-A102-C, Condition C                                      |
| HAST                           | 130°C, 85% RH, 96 hours  | JESD22-A110   |
| Solderability                  | 10X Magnification  | J-STD-002, Para 4.2.5, Test S, 95% Coverage                     |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 240°C peak<br>Pb-Free Process: 260°C peak   | J-STD-020C, Table 4-1, 4-2 and 5-2; Figure 5-1                  |
| Moisture Sensitivity: Level 1  | Bake at 125°C for 24 hours. Soak at 85°C/85%RH for 168 hours<br>Reflow 3 cycles at 260°C peak                                  | J-STD-020   |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + | MIL-STD-202, Method 215   |





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition        | Reference/Spec |
|---------------|----------------------------------|----------------|
|               | monoethanolamine at 63°C to 70°C |                |