

**THE BIG DEAL**

- Very high isolation , 90 dB typ.
- High speed switch transition , 5 μs typ.
- High power handling, +30 dBm max
- Daisy-chain control of up to 35 modules

**APPLICATIONS**

- Cellular handset / BTS testing
- High volume production testing / ATE
- Design verification testing
- RF signal routing / switch matrices

*Generic photo used for illustration purposes only***PRODUCT OVERVIEW**

Mini-Circuits' USB-1SP16T-83H is a high isolation (90 dB typical), absorptive SP16T switch with USB and LVTTTL control. The fast switching, solid state switch operates from 1 MHz to 8000 MHz with 5 μs typical switch transition speed and high linearity (+50 dBm typ IP3) which allow the model to be used for a wide variety of RF applications.

The switch is supplied in a low profile, rugged metal case (10.98" x 2.50" x 0.60") with 17 SMA (F) RF connectors, a USB Mini-B port, a D-Sub 9 pin port for power and control, and two data bus connectors for Master / Slave connections to other switch modules.

**KEY FEATURES**

Feature	Advantages
RF SP16T absorptive switch	Wideband (1 to 8000 MHz) with high isolation (90 dB typ.), and high power rating (+30 dBm through path) makes this switch suitable for a wide range of applications.
High linearity	High IP3 (+50 dBm typ.) results in little or negligible inter-modulation generation, meeting requirements for digital communications signals.
Internal DC Blocking capacitors at RF ports	No need for external DC blocking circuitry.
Dynamic daisy-chain control	Simplify control software and interconnections by cascading up to 35 modules of multiple switch types into a Master / Slave chain with a single USB interface.

**Trademarks:**

Windows is a registered trademark of Microsoft Corporation in the United States and other countries ; Linux is a registered trademark of Linus Torvalds ; Pentium is a registered trademark of Intel Corporation. Neither Mini-Circuits nor the Mini-Circuits products are affiliated with or endorsed by the owners of the referenced trademarks. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation.

**USB & LVTTTL**

# Solid-State Switch

**USB-1SP16T-83H**

Mini-Circuits

50Ω

1 to 8000 MHz

Absorptive SP16T

SMA Female

**ELECTRICAL SPECIFICATIONS AT -10 TO 60°C**

Parameter	Ports	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range	-	-	1	-	8000	MHz
Insertion Loss	COM to any active port	1 - 3000	-	5.5	7.5	dB
		3000 - 7000	-	7.5	11.0	
		7000 - 8000	-	9.5	13.0	
Isolation	Between ports J1 to J16	1 - 3000	63	90	-	dB
		3000 - 7000	67	88	-	
		7000 - 8000	60	78	-	
	COM to any terminated port (including Disconnected states)	1 - 3000	80	100	-	dB
		3000 - 7000	83	100	-	
		7000 - 8000	75	100	-	
	COM to any terminated port (Active states)	1 - 3000	67	85	-	dB
		3000 - 7000	67	85	-	
		7000 - 8000	62	78	-	
Return Loss	COM port (in all active states)	1 - 3000	-	19.0	-	dB
		3000 - 7000	-	14.5	-	
		7000 - 8000	-	14.0	-	
	Any port connected to COM	1 - 3000	-	19.0	-	dB
		3000 - 7000	-	15.5	-	
		7000 - 8000	-	16.5	-	
	Any terminated port (including Disconnected states)	1 - 3000	-	19.0	-	dB
		3000 - 7000	-	21.0	-	
		7000 - 8000	-	17.5	-	
Power Input @1 dB Compression <sup>1</sup>	COM to any active port	10 - 8000	-	+31.5	-	dBm
IP3 <sup>1,2</sup>	COM to any active port	10 - 5000	-	+50	-	dBm
		5000 - 8000	-	+45	-	
Transition Time <sup>3</sup>	-	-	-	5.0	9.5	μs
Minimum Dwell Time <sup>4</sup>	High-Speed Mode	-	-	15	-	μs
Switching Time	USB <sup>5</sup>	-	-	2	-	ms
	LVTTTL <sup>6</sup>	-	-	12	-	μs

1. Compression and IP3 may degrade below 10 MHz.

2. IP3 Tested with 1 MHz span between signals, +5 dBm per tone.

3. Transition Time spec represents the time that the RF signal paths are interrupted during switching and thus is specified without communication delays.

4. Minimum dwell time is the shortest time that can be achieved between 2 switch transitions when programming an automated switch sequence.

5. Switching time (USB) is the time from issuing a single software command via USB to the switch state changing. The most significant factor is the host PC, influenced by CPU load and USB protocol. The time shown is an estimate for a medium CPU load and USB 2.0 connection.

6. Switching time (LVTTTL) is the time from setting the control at the LVTTTL input to the desired logic state, to the RF signal at the specified output reaching 90% of the steady state.



## ELECTRICAL SPECIFICATIONS AT -10 TO 60°C

Parameter	Ports	Condition (MHz)	Min.	Typ.	Max.	Unit
Supply Voltage ( $V_{dc}$ )	USB or D-Sub port	-	4.75	5	5.25	$V_{dc}$
Supply Current ( $I_{dc}$ ) <sup>7</sup>		-	-	60	90	mA
Current Pass-Through <sup>8</sup>		-	-	-	-	500
Operating RF Input Power	Through path (Hot switching)	1 - 8000	-	-	+20	dBm
	Through path (Cold switching)	1 - 10	-	-	Note 9	
		10 - 8000	-	-	+30	
	Into termination	1 - 8000	-	-	+25	

7. Current consumption is specified for a single unit without any slave modules.

8. Pass-Through current is the maximum current handling of a unit with slave modules attached. If controlling a large number of slave modules additional power supplies should be included to ensure this limit is not exceeded. Refer to "Connecting Multiple Modules" section for more details.

9. Derates linearly from +30 dBm at 10 MHz to +25 dBm at 1 MHz.

ABSOLUTE MAXIMUM RATINGS<sup>10</sup>


Operating Temperature	-10°C to 60°C
Storage Temperature	-20°C to 85°C
DC Supply Voltage max @ USB and pin #6 of D-Sub	6 V
Voltage at LVTTTL control pins	3.6 V
DC Voltage @ RF Ports	16 V

10. Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.




### TYPICAL PERFORMANCE GRAPHS


#### Insertion Loss over Temperature (J1 Active)




#### Insertion Loss, Ports J1 - J8




#### Insertion Loss, Ports J9 - J16



#### Isolation, J1 to J2 over Temperature (J1 Active)




#### Isolation, COM to J1 over Temperature (J16 Active)






### TYPICAL PERFORMANCE GRAPHS (CONTINUED)


#### Isolation, Ports J1 - J8 Active




#### Isolation, Ports J9 - J16 Active




#### Isolation, Ports J1 - J8 Terminated



#### Isolation, Ports J9 - J16 Terminated




#### Isolation, Com to Ports J1 - J9 (Disconnected)






### TYPICAL PERFORMANCE GRAPHS (CONTINUED)


Return Loss, Ports J1 - J8 Active




Return Loss, Ports J9 - J16 Active




Return Loss, Ports J1 - J8 Terminated




Return Loss, Ports J9 - J16 Terminated



Return Loss, COM over Temperature (J1 Active)



Return Loss, COM over Temperature (Disconnected)





## CONTROL INTERFACES

USB Control	Supported Protocols	HID (Human Interface Device) - Full-speed
	Min Communication Time <sup>11</sup>	3 ms typ (full transmit/receive cycle)
LVTTTL Control	Refer to "LVTTTL Communication Parameters" section for more details.	

11. USB Min Communication Time is based on the polling interval of the USB HID protocol (1 ms polling interval, 64 bytes per packet), medium CPU load and no other high speed USB devices using the USB bus.

## SOFTWARE & DOCUMENTATION

Mini-Circuits' full software and support package including user guide, Windows GUI, API, programming manual and examples can be downloaded free of charge (refer to the last page for the download path).

A comprehensive set of software control options is provided:

- GUI for Windows – Simple software interface for control via Ethernet and USB (model dependant).
- Programming / automation via USB:
  - DLL files provide a full API for Windows with a set of intuitive functions which can be implemented in any programming environment supporting .Net Framework or ActiveX.
  - Direct USB programming is possible in any other environment (not supporting .Net or ActiveX).

Please contact [testsolutions@minicircuits.com](mailto:testsolutions@minicircuits.com) for support.


## MINIMUM SYSTEM REQUIREMENTS

GUI	Windows 7 or later
USB API DLL	Windows 7 or later and programming environment with ActiveX or .NET support
USB Direct Programming	Linux, Windows 7 or later
Daisy-Chain Dynamic Addressing	An additional Mini-Circuits unit supporting dynamic addressing
Hardware	Intel i3 (or equivalent) or later




### GRAPHICAL USER INTERFACE (GUI) FOR WINDOWS - KEY FEATURES

- Connect via USB or Ethernet to control the module (model dependant).
- Password protected access for safe remote usage over Ethernet (model dependant).



- Run GUI in "demo mode" to evaluate software without a hardware connection.
- View and set switch states at the click of a button.
- Configure and run timed switching sequences.








### CONNECTING MULTIPLE MODULES (DAISY CHAIN)

The model is designed to connect up to 35 modules in series (daisy chain) using dynamic addressing, meaning there is no need to specifically set the address of the modules. The addresses will be set automatically as part of establishing the communications with the computer. The module connected to the computer's USB port will be assigned address 0 (master), the first module connected to it will get address 1 (slave) and subsequent modules incrementing up to address 24 (slave).



Connections between modules will be made using the serial in/out ports with the module connected to the PC act as a master and all other as slave modules. All control will be through the master module (address 0) which is the only one communicating with the PC. Serial control out port of each module should be connected to the serial control in port of the next module.

Power will be supplied from the PC via the master module up to a maximum of 500 mA. Generally, additional power supply will be needed to keep total current below 500 mA. All power supplies should be connected to the module via the module's USB port. Connecting an additional power supply will automatically cut off power draw from the serial control in port for that module.

The serial master/slave bus allows connecting modules of different types to the same daisy chain as long as all support Mini-Circuits Dynamic addressing setup. To add a new module to the setup, simply connect the module and refresh the address listing, no need to reset any of the existing modules or assign addresses manually.

**Note:** Different module types may have different current consumption which will change the number of units which can be connected before an additional power supply is needed. For example, if connecting units with a current consumption of 100 mA each, additional power supply is recommended every sixth module. If using units with current consumption of 50 mA additional power supply is recommended every eleventh module.



## LVTTTL COMMUNICATIONS PARAMETERS

Parameter	Conditions		Min.	Typ.	Max.	Units
Voltage Levels	Logic Low Voltage	Input	0	-	0.8	V
	Logic High Voltage	Input	2.0	-	3.3	

The switch model's LVTTTL control interface consists of 5 unlatched parallel control bits that select the desired switch state, as shown in the truth table below. The parallel control does not have any latch and thus will respond immediately to any change.

Connecting the switch to USB control and establishing USB communication will disable the LVTTTL control until the switch is reset by disconnecting and then reconnecting power.

All LVTTTL controls are connected with internal pull-down resistors so the default state of the switch is disconnected state.

Power can be provided via either the D-Sub port or USB port, regardless of the control method used.

Switch State	Control Bits				
	D0	D1	D2	D3	D4
Disconnected	Logic Low	Logic Low	Logic Low	Logic Low	Logic Low
COM -> J1	Logic High	Logic Low	Logic Low	Logic Low	Logic Low
COM -> J2	Logic Low	Logic High	Logic Low	Logic Low	Logic Low
COM -> J3	Logic High	Logic High	Logic Low	Logic Low	Logic Low
COM -> J4	Logic Low	Logic Low	Logic High	Logic Low	Logic Low
COM -> J5	Logic High	Logic Low	Logic High	Logic Low	Logic Low
COM -> J6	Logic Low	Logic High	Logic High	Logic Low	Logic Low
COM -> J7	Logic High	Logic High	Logic High	Logic Low	Logic Low
COM -> J8	Logic Low	Logic Low	Logic Low	Logic High	Logic Low
COM -> J9	Logic High	Logic Low	Logic Low	Logic High	Logic Low
COM -> J10	Logic Low	Logic High	Logic Low	Logic High	Logic Low
COM -> J11	Logic High	Logic High	Logic Low	Logic High	Logic Low
COM -> J12	Logic Low	Logic Low	Logic High	Logic High	Logic Low
COM -> J13	Logic High	Logic Low	Logic High	Logic High	Logic Low
COM -> J14	Logic Low	Logic High	Logic High	Logic High	Logic Low
COM -> J15	Logic High	Logic High	Logic High	Logic High	Logic Low
COM -> J16	Logic Low	Logic Low	Logic Low	Logic Low	Logic High

## Notes:


\* All inactive ports will be internally terminated to 50 Ω.

\* In disconnected state, all ports including COM port will be terminated internally.

\* Note maximum input power to internal termination listed on "Electrical Specifications" section.



### BLOCK DIAGRAM



Switch functional diagram shown in  
Common port to J12 (with J12 active)


### CONNECTIONS

Port name	Connector type
RF ports (COM, J1 to J16)	SMA female
USB	USB type Mini-B receptacle
Serial in (digital control 2 port)	Digital snap fit connector <sup>12</sup>
Serial out (digital control 1 port)	Digital snap fit connector <sup>12</sup>
TTL	9-pin D-Sub Female

12. Mating connector is Hirose ST40X-10S-CV(30).



### CASE STYLE DRAWING (RB2574-2)



#### NOTES:


1. Case material: Aluminum alloy.
2. Case Finish: Nickel Plate.
3. Dimensions: Inches [mm]. Tolerances 2 Pl. ±.03 inch; 3 Pl. ±.015 inch.
4. Weight: 650 grams
5. Marking may contain other features or characters for internal lot control.



### RECOMMENDED ACCESSORIES

USB-1SP16T-83H is controlled via a standard 9 pin D-Sub connector and is supplied with a male-female D-Sub 9 cable. The cable is 6 feet (1.8 meter) long and uses 28 AWG wires.

#### CONTROL CABLE D-SUB9-MF-6+



Pin Number (Male)	Function	Description	Pin Number (Female)
1	D1	Control bit 1	1
2	D2	Control bit 2	2
3	D3	Control bit 3	3
4	D4	Control bit 4	4
5	Not Connected	Not Connected	5
6	Supply +5V	Supply Voltage (Positive)	6
7	GND	Ground connection	7
8	Supply -5V	Supply Voltage (Negative)	8
9	GND	Ground connection	9



USB & LVTTL

# Solid-State Switch

## USB-1SP16T-83H

Mini-Circuits

50Ω

1 to 8000 MHz


Absorptive SP16T

SMA Female





DETAILED MODEL INFORMATION IS AVAILABLE ON OUR WEBSITE [CLICK HERE](#)

Performance Data & Graphs	Data Graphs
Case Style	RB2574-2
Environmental Rating	ENV55T2
User Guide	<a href="https://www.minicircuits.com/softwaredownload/solidstate.html">https://www.minicircuits.com/softwaredownload/solidstate.html</a>
Regulatory Compliance	<p>Refer to user guide for compliance information</p>  <a href="https://www.minicircuits.com/app/AN49-012.pdf">https://www.minicircuits.com/app/AN49-012.pdf</a>
Support	<a href="mailto:testsolutions@minicircuits.com">testsolutions@minicircuits.com</a>

### INCLUDED ACCESSORIES

	Part No.	Description	Qty.
	MUSB-CBL-3+	3.3 ft (1.0 m) USB Cable: USB type A (Male) to USB type Mini-B (Male)	1

### OPTIONAL ACCESSORIES

	Part No.	Description
	MUSB-CBL-3+ (spare)	3.3 ft (1.0 m) USB Cable: USB type A (Male) to USB type Mini-B (Male)
	MUSB-CBL-7+	6.6 ft (2.0 m) USB Cable: USB type A (Male) to USB type Mini-B (Male)
See drawing on page 13	D-SUB9-MF-6+	6.0 ft (1.8 m) D-Sub cable: 9 pin D-sub (Male) to 9 pin D-sub (Female)
	CBL-1.5FT-MMD+	1.5 ft (0.45 m) Cable assembly for serial control daisy chain with snap fit connectors
	USB-AC/DC-5+	AC/DC +5V power adaptor with USB connector <sup>13, 14</sup>

13. The power adaptor may be used to provide additional power via USB port when connecting several units in daisy chain control.

14. Includes power plugs for US, UK, EU, IL, AU & China. Plugs for other countries are also available. If you need a power cord for a country not listed, please contact [testsolutions@minicircuits.com](mailto:testsolutions@minicircuits.com)

#### NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J1	COM-J2	COM-J3	COM-J4	COM-J5	COM-J6	COM-J7	COM-J8
0.1	4.77	4.75	4.78	4.77	4.80	4.74	4.74	4.77
0.5	4.10	4.08	4.10	4.10	4.10	4.07	4.07	4.09
1	4.08	4.05	4.08	4.08	4.07	4.04	4.05	4.06
5	4.08	4.05	4.08	4.08	4.07	4.04	4.05	4.06
10	4.09	4.06	4.08	4.08	4.08	4.04	4.05	4.06
20	4.10	4.07	4.10	4.10	4.09	4.05	4.06	4.07
50	4.14	4.11	4.13	4.14	4.12	4.07	4.08	4.10
100	4.21	4.18	4.20	4.21	4.16	4.12	4.13	4.15
200	4.35	4.31	4.33	4.35	4.23	4.18	4.19	4.21
400	4.61	4.55	4.58	4.60	4.39	4.32	4.32	4.36
600	4.66	4.61	4.63	4.65	4.57	4.47	4.48	4.54
800	4.74	4.64	4.67	4.74	4.72	4.62	4.63	4.70
1000	5.02	4.89	4.92	5.02	4.81	4.71	4.72	4.79
1200	5.19	5.09	5.11	5.18	4.88	4.76	4.77	4.84
1400	5.27	5.11	5.14	5.27	4.96	4.80	4.79	4.91
1600	5.47	5.28	5.32	5.47	5.07	4.87	4.87	5.04
1800	5.69	5.56	5.59	5.68	5.20	5.00	5.00	5.17
2000	5.83	5.67	5.69	5.82	5.31	5.16	5.17	5.29
2200	5.92	5.73	5.77	5.92	5.42	5.30	5.31	5.40
2400	6.03	5.95	5.97	6.02	5.54	5.40	5.41	5.51
2600	6.21	6.10	6.12	6.20	5.63	5.48	5.49	5.59
2800	6.30	6.20	6.23	6.29	5.69	5.56	5.57	5.64
3000	6.40	6.35	6.37	6.39	5.76	5.65	5.66	5.72
3200	6.57	6.43	6.45	6.57	5.90	5.72	5.73	5.87
3400	6.64	6.52	6.54	6.64	6.03	5.77	5.78	6.00
3600	6.85	6.56	6.59	6.85	6.05	5.83	5.84	6.01
3800	6.95	6.61	6.64	6.95	6.04	5.89	5.90	6.01
4000	6.97	6.71	6.75	6.97	6.16	5.89	5.90	6.15
4200	7.17	6.62	6.68	7.17	6.31	5.81	5.82	6.31
4400	7.17	6.75	6.79	7.18	6.33	5.79	5.80	6.33
4600	7.25	7.00	7.03	7.26	6.30	5.97	5.97	6.29
4800	7.28	6.84	6.91	7.29	6.46	6.25	6.26	6.41
5000	7.37	7.13	7.13	7.38	6.69	6.39	6.39	6.65
5200	7.91	7.62	7.62	7.94	6.67	6.30	6.30	6.66
5400	7.85	7.50	7.53	7.88	6.55	6.23	6.24	6.54
5600	8.07	7.80	7.78	8.11	6.84	6.50	6.52	6.77
5800	8.82	8.36	8.40	8.88	7.42	6.94	6.99	7.33
6000	8.71	8.28	8.33	8.72	7.71	7.19	7.24	7.66
6200	8.68	8.30	8.33	8.71	7.60	7.16	7.18	7.58
6400	8.93	8.55	8.63	8.93	7.45	7.02	7.06	7.40
6600	8.82	8.49	8.53	8.79	7.41	7.03	7.07	7.37
6800	8.71	8.44	8.44	8.72	7.36	7.09	7.10	7.36
7000	8.76	8.50	8.48	8.77	7.44	7.09	7.08	7.42
7200	8.91	8.61	8.58	8.92	7.67	7.14	7.16	7.63
7400	9.14	8.84	8.78	9.16	7.74	7.28	7.33	7.70
7600	9.91	9.33	9.17	9.97	7.83	7.45	7.49	7.78
7800	10.12	9.67	9.58	10.12	8.41	7.74	7.77	8.34
8000	10.22	9.90	9.73	10.26	9.16	8.25	8.30	9.11
8200	11.09	10.52	10.33	11.08	9.60	8.74	8.82	9.56
8400	11.50	10.93	10.86	11.35	9.75	9.00	9.11	9.65
8500	11.42	10.95	10.86	11.28	9.75	9.03	9.15	9.64

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J9	COM-J10	COM-J11	COM-J12	COM-J13	COM-J14	COM-J15	COM-J16
0.1	4.80	4.79	4.82	4.80	4.76	4.83	4.78	4.77
0.5	4.12	4.11	4.16	4.14	4.08	4.17	4.10	4.11
1	4.09	4.08	4.13	4.11	4.06	4.14	4.07	4.09
5	4.09	4.08	4.13	4.11	4.06	4.15	4.07	4.09
10	4.10	4.09	4.14	4.11	4.06	4.15	4.08	4.09
20	4.11	4.10	4.14	4.12	4.08	4.16	4.09	4.10
50	4.13	4.12	4.17	4.15	4.11	4.20	4.13	4.14
100	4.18	4.17	4.21	4.20	4.19	4.28	4.19	4.21
200	4.25	4.23	4.28	4.28	4.32	4.41	4.32	4.35
400	4.41	4.37	4.42	4.43	4.56	4.64	4.55	4.59
600	4.58	4.52	4.58	4.61	4.60	4.68	4.59	4.63
800	4.73	4.67	4.73	4.76	4.70	4.75	4.65	4.73
1000	4.83	4.76	4.82	4.85	4.99	5.03	4.93	5.04
1200	4.89	4.81	4.86	4.91	5.17	5.23	5.14	5.21
1400	4.96	4.84	4.88	4.98	5.22	5.23	5.13	5.26
1600	5.07	4.90	4.95	5.08	5.40	5.36	5.26	5.44
1800	5.21	5.03	5.08	5.22	5.61	5.63	5.54	5.65
2000	5.33	5.19	5.26	5.35	5.75	5.75	5.65	5.79
2200	5.43	5.34	5.42	5.46	5.86	5.83	5.73	5.90
2400	5.54	5.45	5.52	5.57	5.96	6.06	5.96	6.01
2600	5.62	5.52	5.59	5.65	6.14	6.21	6.11	6.19
2800	5.68	5.61	5.68	5.71	6.24	6.31	6.22	6.29
3000	5.78	5.71	5.77	5.81	6.35	6.45	6.35	6.39
3200	5.95	5.78	5.83	5.98	6.53	6.55	6.45	6.57
3400	6.08	5.82	5.87	6.12	6.62	6.63	6.54	6.66
3600	6.09	5.87	5.93	6.13	6.86	6.68	6.60	6.90
3800	6.08	5.92	5.98	6.12	6.97	6.78	6.69	7.02
4000	6.20	5.93	5.95	6.23	6.98	6.88	6.80	7.01
4200	6.35	5.87	5.87	6.38	7.18	6.77	6.72	7.22
4400	6.37	5.86	5.87	6.42	7.21	6.91	6.84	7.25
4600	6.36	6.02	6.08	6.42	7.29	7.15	7.09	7.32
4800	6.51	6.28	6.37	6.56	7.33	6.99	6.96	7.36
5000	6.70	6.42	6.46	6.75	7.43	7.34	7.23	7.48
5200	6.67	6.34	6.34	6.73	8.01	7.86	7.77	8.07
5400	6.57	6.27	6.31	6.64	7.96	7.71	7.66	8.01
5600	6.87	6.51	6.65	6.95	8.11	7.99	7.87	8.15
5800	7.46	6.96	7.13	7.50	8.86	8.52	8.45	8.87
6000	7.75	7.26	7.34	7.79	8.77	8.44	8.41	8.79
6200	7.65	7.25	7.26	7.71	8.78	8.51	8.45	8.77
6400	7.49	7.09	7.14	7.55	9.00	8.71	8.71	9.01
6600	7.43	7.09	7.14	7.50	8.90	8.65	8.63	8.94
6800	7.39	7.16	7.13	7.51	8.83	8.63	8.59	8.88
7000	7.51	7.19	7.13	7.65	8.89	8.69	8.63	8.94
7200	7.76	7.25	7.25	7.87	9.04	8.81	8.75	9.07
7400	7.80	7.39	7.40	7.92	9.25	9.01	8.92	9.27
7600	7.85	7.55	7.50	7.99	9.96	9.44	9.30	9.97
7800	8.39	7.81	7.73	8.49	10.14	9.78	9.70	10.17
8000	9.08	8.26	8.23	9.17	10.33	10.03	9.88	10.36
8200	9.50	8.76	8.78	9.65	11.17	10.63	10.46	11.17
8400	9.67	9.05	9.08	9.84	11.54	11.03	10.93	11.49
8500	9.69	9.10	9.13	9.87	11.49	11.06	10.95	11.44

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)





# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	2.03	2.01	2.00	2.02	2.01	2.04	2.01	2.01	2.02
0.5	1.30	1.30	1.29	1.30	1.29	1.30	1.29	1.29	1.29
1	1.26	1.26	1.25	1.26	1.26	1.26	1.25	1.25	1.25
5	1.24	1.24	1.24	1.24	1.24	1.24	1.24	1.24	1.24
10	1.24	1.25	1.24	1.24	1.24	1.24	1.24	1.24	1.24
20	1.24	1.25	1.24	1.25	1.25	1.25	1.24	1.24	1.24
50	1.25	1.25	1.24	1.25	1.25	1.25	1.24	1.25	1.25
100	1.25	1.25	1.24	1.25	1.25	1.26	1.26	1.25	1.26
200	1.19	1.20	1.20	1.20	1.20	1.26	1.25	1.25	1.25
400	1.02	1.03	1.04	1.04	1.04	1.25	1.23	1.23	1.23
600	1.20	1.17	1.16	1.16	1.16	1.18	1.18	1.18	1.17
800	1.29	1.28	1.29	1.30	1.28	1.07	1.10	1.09	1.08
1000	1.18	1.14	1.19	1.20	1.16	1.05	1.02	1.02	1.03
1200	1.10	1.06	1.05	1.06	1.04	1.15	1.15	1.14	1.12
1400	1.21	1.14	1.25	1.26	1.16	1.17	1.26	1.24	1.16
1600	1.17	1.20	1.23	1.24	1.20	1.15	1.29	1.27	1.17
1800	1.05	1.23	1.08	1.07	1.21	1.20	1.24	1.23	1.21
2000	1.04	1.08	1.09	1.09	1.08	1.27	1.14	1.14	1.26
2200	1.07	1.22	1.09	1.11	1.22	1.26	1.06	1.08	1.25
2400	1.01	1.31	1.15	1.12	1.31	1.19	1.06	1.06	1.19
2600	1.18	1.18	1.14	1.11	1.19	1.17	1.05	1.04	1.15
2800	1.28	1.18	1.13	1.10	1.19	1.18	1.08	1.08	1.17
3000	1.13	1.14	1.23	1.20	1.15	1.14	1.16	1.15	1.13
3200	1.41	1.03	1.22	1.20	1.04	1.03	1.21	1.20	1.03
3400	1.55	1.01	1.26	1.24	1.01	1.10	1.18	1.18	1.07
3600	1.27	1.14	1.31	1.32	1.13	1.14	1.14	1.14	1.10
3800	1.48	1.21	1.19	1.22	1.22	1.07	1.25	1.25	1.03
4000	1.57	1.16	1.28	1.30	1.16	1.18	1.41	1.41	1.17
4200	1.35	1.40	1.36	1.44	1.41	1.39	1.49	1.50	1.38
4400	1.41	1.39	1.15	1.21	1.43	1.50	1.41	1.42	1.50
4600	1.32	1.14	1.12	1.17	1.18	1.39	1.19	1.19	1.42
4800	1.33	1.37	1.28	1.37	1.41	1.14	1.04	1.04	1.17
5000	1.18	1.31	1.22	1.21	1.32	1.10	1.24	1.25	1.10
5200	1.19	1.04	1.07	1.11	1.05	1.28	1.35	1.35	1.28
5400	1.31	1.23	1.20	1.28	1.26	1.27	1.30	1.30	1.31
5600	1.12	1.10	1.24	1.14	1.06	1.10	1.14	1.12	1.14
5800	1.56	1.25	1.15	1.18	1.34	1.19	1.16	1.17	1.18
6000	1.57	1.28	1.15	1.22	1.31	1.36	1.29	1.31	1.35
6200	1.40	1.13	1.09	1.02	1.19	1.34	1.29	1.28	1.35
6400	1.60	1.38	1.14	1.26	1.42	1.21	1.16	1.15	1.21
6600	1.55	1.30	1.17	1.24	1.28	1.21	1.15	1.17	1.21
6800	1.42	1.20	1.12	1.16	1.17	1.24	1.24	1.24	1.26
7000	1.25	1.19	1.19	1.18	1.13	1.17	1.23	1.19	1.18
7200	1.20	1.12	1.19	1.12	1.06	1.07	1.13	1.07	1.06
7400	1.48	1.20	1.35	1.23	1.16	1.03	1.05	1.03	1.03
7600	1.63	1.13	1.49	1.27	1.17	1.16	1.20	1.14	1.14
7800	1.40	1.09	1.28	1.11	1.06	1.22	1.39	1.33	1.21
8000	1.57	1.14	1.48	1.26	1.10	1.11	1.49	1.50	1.16
8200	1.75	1.16	1.62	1.43	1.12	1.20	1.42	1.47	1.17
8400	1.44	1.54	1.32	1.22	1.41	1.46	1.25	1.31	1.34
8500	1.24	1.60	1.31	1.16	1.47	1.55	1.19	1.24	1.42

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	2.03	2.02	2.01	2.01	2.01	2.00	2.02	2.00
0.5	1.30	1.30	1.30	1.30	1.29	1.30	1.30	1.29
1	1.26	1.26	1.27	1.26	1.25	1.27	1.26	1.26
5	1.25	1.24	1.25	1.25	1.24	1.25	1.24	1.24
10	1.25	1.24	1.25	1.25	1.24	1.25	1.24	1.24
20	1.25	1.24	1.26	1.25	1.24	1.26	1.24	1.25
50	1.26	1.25	1.26	1.26	1.25	1.26	1.25	1.25
100	1.27	1.26	1.27	1.27	1.25	1.26	1.25	1.25
200	1.27	1.26	1.27	1.27	1.21	1.21	1.20	1.20
400	1.25	1.24	1.24	1.25	1.05	1.04	1.04	1.05
600	1.18	1.18	1.17	1.17	1.18	1.18	1.16	1.17
800	1.06	1.09	1.07	1.06	1.30	1.32	1.30	1.30
1000	1.06	1.03	1.05	1.06	1.15	1.18	1.19	1.16
1200	1.15	1.16	1.18	1.16	1.09	1.10	1.06	1.08
1400	1.16	1.27	1.26	1.17	1.18	1.31	1.28	1.19
1600	1.16	1.31	1.26	1.14	1.21	1.24	1.26	1.20
1800	1.23	1.25	1.19	1.21	1.23	1.05	1.08	1.22
2000	1.30	1.16	1.13	1.29	1.08	1.12	1.08	1.09
2200	1.29	1.09	1.13	1.29	1.23	1.04	1.10	1.23
2400	1.21	1.07	1.13	1.22	1.29	1.16	1.14	1.32
2600	1.17	1.07	1.12	1.18	1.16	1.19	1.13	1.19
2800	1.17	1.11	1.16	1.18	1.15	1.18	1.11	1.18
3000	1.12	1.18	1.22	1.12	1.11	1.27	1.20	1.13
3200	1.03	1.22	1.24	1.02	1.03	1.26	1.20	1.05
3400	1.08	1.19	1.20	1.10	1.02	1.31	1.25	1.02
3600	1.11	1.13	1.16	1.12	1.14	1.32	1.30	1.16
3800	1.05	1.21	1.26	1.06	1.19	1.19	1.19	1.23
4000	1.18	1.36	1.41	1.18	1.12	1.30	1.29	1.15
4200	1.38	1.47	1.49	1.38	1.36	1.36	1.40	1.38
4400	1.50	1.45	1.40	1.50	1.37	1.13	1.19	1.38
4600	1.43	1.27	1.19	1.43	1.15	1.15	1.18	1.15
4800	1.18	1.05	1.03	1.20	1.38	1.28	1.35	1.36
5000	1.06	1.14	1.21	1.03	1.31	1.18	1.18	1.31
5200	1.23	1.29	1.30	1.19	1.05	1.10	1.12	1.04
5400	1.26	1.33	1.25	1.24	1.25	1.21	1.29	1.22
5600	1.11	1.22	1.12	1.17	1.09	1.21	1.14	1.14
5800	1.19	1.14	1.19	1.18	1.24	1.14	1.17	1.20
6000	1.34	1.19	1.29	1.28	1.23	1.15	1.20	1.21
6200	1.32	1.20	1.25	1.28	1.13	1.08	1.02	1.08
6400	1.19	1.11	1.12	1.17	1.32	1.12	1.25	1.29
6600	1.18	1.06	1.14	1.15	1.20	1.16	1.21	1.24
6800	1.22	1.14	1.20	1.23	1.13	1.11	1.15	1.17
7000	1.18	1.15	1.18	1.26	1.12	1.19	1.18	1.19
7200	1.11	1.11	1.11	1.18	1.08	1.20	1.13	1.15
7400	1.03	1.05	1.03	1.11	1.18	1.36	1.23	1.24
7600	1.18	1.08	1.18	1.25	1.14	1.46	1.23	1.15
7800	1.24	1.29	1.41	1.29	1.08	1.28	1.07	1.11
8000	1.11	1.49	1.53	1.11	1.18	1.57	1.31	1.21
8200	1.17	1.51	1.42	1.15	1.10	1.62	1.40	1.10
8400	1.43	1.39	1.24	1.42	1.45	1.34	1.18	1.45
8500	1.52	1.32	1.21	1.52	1.50	1.40	1.18	1.53

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	2.02	1.49	1.58	1.57	1.54	1.59	1.56	1.55	1.60
0.5	1.29	1.19	1.31	1.27	1.25	1.29	1.28	1.27	1.31
1	1.25	1.18	1.30	1.26	1.23	1.27	1.27	1.26	1.30
5	1.24	1.17	1.29	1.25	1.23	1.27	1.26	1.25	1.30
10	1.23	1.17	1.29	1.25	1.23	1.27	1.26	1.25	1.29
20	1.23	1.17	1.29	1.25	1.23	1.27	1.26	1.25	1.29
50	1.23	1.16	1.28	1.24	1.22	1.26	1.26	1.25	1.29
100	1.22	1.16	1.27	1.24	1.21	1.25	1.25	1.24	1.27
200	1.21	1.15	1.27	1.23	1.20	1.24	1.24	1.23	1.27
400	1.21	1.15	1.27	1.23	1.21	1.25	1.24	1.23	1.27
600	1.20	1.15	1.26	1.23	1.21	1.24	1.24	1.23	1.27
800	1.20	1.14	1.25	1.22	1.20	1.23	1.24	1.23	1.27
1000	1.19	1.14	1.24	1.21	1.20	1.23	1.23	1.22	1.26
1200	1.18	1.13	1.23	1.20	1.19	1.21	1.23	1.21	1.25
1400	1.18	1.12	1.21	1.19	1.18	1.20	1.22	1.21	1.24
1600	1.17	1.11	1.20	1.18	1.17	1.19	1.21	1.20	1.23
1800	1.15	1.11	1.18	1.16	1.16	1.17	1.20	1.19	1.22
2000	1.14	1.10	1.17	1.15	1.15	1.16	1.19	1.18	1.20
2200	1.13	1.09	1.15	1.14	1.13	1.15	1.18	1.17	1.19
2400	1.12	1.08	1.14	1.13	1.12	1.13	1.16	1.16	1.17
2600	1.11	1.08	1.14	1.12	1.11	1.12	1.15	1.15	1.16
2800	1.09	1.07	1.13	1.11	1.10	1.11	1.14	1.15	1.15
3000	1.07	1.06	1.12	1.10	1.08	1.10	1.13	1.14	1.14
3200	1.06	1.05	1.12	1.09	1.07	1.09	1.12	1.13	1.13
3400	1.05	1.05	1.12	1.09	1.07	1.08	1.11	1.12	1.12
3600	1.05	1.05	1.12	1.08	1.06	1.07	1.10	1.11	1.12
3800	1.05	1.04	1.13	1.07	1.05	1.06	1.09	1.10	1.11
4000	1.06	1.03	1.14	1.07	1.04	1.05	1.09	1.09	1.11
4200	1.08	1.03	1.14	1.07	1.04	1.05	1.09	1.08	1.10
4400	1.08	1.03	1.15	1.07	1.03	1.06	1.08	1.07	1.10
4600	1.11	1.04	1.16	1.07	1.02	1.06	1.07	1.06	1.09
4800	1.13	1.04	1.17	1.07	1.02	1.06	1.07	1.06	1.09
5000	1.15	1.05	1.17	1.06	1.01	1.06	1.07	1.05	1.08
5200	1.17	1.04	1.18	1.06	1.01	1.06	1.07	1.04	1.08
5400	1.19	1.06	1.16	1.06	1.01	1.05	1.05	1.04	1.07
5600	1.20	1.05	1.18	1.05	1.01	1.06	1.07	1.04	1.08
5800	1.23	1.07	1.16	1.06	1.02	1.05	1.05	1.04	1.07
6000	1.24	1.06	1.16	1.05	1.03	1.06	1.06	1.04	1.08
6200	1.27	1.06	1.17	1.06	1.04	1.07	1.07	1.06	1.09
6400	1.26	1.07	1.17	1.06	1.06	1.08	1.08	1.07	1.10
6600	1.26	1.07	1.18	1.08	1.08	1.09	1.10	1.10	1.12
6800	1.23	1.09	1.20	1.10	1.10	1.12	1.12	1.13	1.14
7000	1.24	1.12	1.21	1.12	1.12	1.13	1.14	1.16	1.15
7200	1.23	1.15	1.23	1.14	1.14	1.15	1.17	1.19	1.16
7400	1.22	1.18	1.25	1.17	1.17	1.18	1.19	1.23	1.18
7600	1.19	1.22	1.26	1.19	1.20	1.20	1.22	1.26	1.20
7800	1.17	1.27	1.29	1.23	1.23	1.23	1.24	1.30	1.22
8000	1.15	1.32	1.31	1.26	1.27	1.26	1.27	1.34	1.24
8200	1.15	1.36	1.33	1.28	1.30	1.29	1.29	1.37	1.26
8400	1.16	1.41	1.35	1.31	1.34	1.32	1.31	1.40	1.28
8500	1.16	1.42	1.36	1.32	1.35	1.33	1.32	1.41	1.29

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	1.56	1.58	1.53	1.50	1.57	1.49	1.55	1.53
0.5	1.25	1.28	1.24	1.20	1.29	1.19	1.26	1.25
1	1.24	1.26	1.23	1.18	1.27	1.18	1.25	1.24
5	1.23	1.26	1.22	1.18	1.27	1.17	1.25	1.24
10	1.23	1.26	1.22	1.18	1.27	1.17	1.25	1.24
20	1.23	1.26	1.22	1.17	1.27	1.17	1.25	1.24
50	1.23	1.25	1.22	1.17	1.27	1.17	1.24	1.23
100	1.22	1.24	1.21	1.16	1.25	1.16	1.23	1.22
200	1.21	1.23	1.20	1.15	1.24	1.15	1.22	1.21
400	1.21	1.24	1.20	1.16	1.25	1.15	1.23	1.22
600	1.21	1.23	1.19	1.15	1.24	1.15	1.22	1.21
800	1.20	1.23	1.19	1.15	1.23	1.14	1.22	1.21
1000	1.19	1.22	1.18	1.14	1.22	1.13	1.21	1.20
1200	1.18	1.21	1.17	1.14	1.21	1.13	1.20	1.20
1400	1.17	1.20	1.16	1.13	1.20	1.11	1.19	1.19
1600	1.15	1.19	1.14	1.12	1.18	1.11	1.17	1.17
1800	1.14	1.18	1.13	1.11	1.16	1.09	1.16	1.16
2000	1.13	1.17	1.12	1.10	1.15	1.08	1.15	1.15
2200	1.12	1.15	1.11	1.09	1.14	1.07	1.14	1.13
2400	1.11	1.14	1.10	1.09	1.13	1.06	1.13	1.12
2600	1.10	1.13	1.10	1.07	1.13	1.04	1.12	1.10
2800	1.09	1.12	1.10	1.07	1.12	1.03	1.11	1.09
3000	1.09	1.11	1.10	1.06	1.12	1.02	1.10	1.08
3200	1.09	1.11	1.10	1.05	1.11	1.01	1.10	1.07
3400	1.08	1.10	1.09	1.05	1.11	1.01	1.09	1.06
3600	1.07	1.10	1.08	1.04	1.10	1.02	1.08	1.06
3800	1.06	1.09	1.07	1.04	1.09	1.02	1.07	1.05
4000	1.06	1.09	1.07	1.04	1.08	1.03	1.07	1.05
4200	1.06	1.09	1.07	1.04	1.08	1.04	1.08	1.05
4400	1.05	1.09	1.06	1.04	1.08	1.05	1.08	1.06
4600	1.05	1.08	1.05	1.04	1.07	1.06	1.08	1.07
4800	1.05	1.09	1.05	1.05	1.07	1.08	1.08	1.07
5000	1.04	1.08	1.05	1.05	1.06	1.09	1.08	1.08
5200	1.04	1.08	1.04	1.06	1.07	1.11	1.08	1.09
5400	1.04	1.07	1.04	1.05	1.06	1.11	1.08	1.08
5600	1.04	1.08	1.04	1.06	1.07	1.13	1.08	1.09
5800	1.04	1.07	1.05	1.06	1.07	1.13	1.07	1.08
6000	1.04	1.08	1.05	1.07	1.08	1.15	1.07	1.09
6200	1.06	1.09	1.07	1.09	1.10	1.17	1.07	1.10
6400	1.07	1.10	1.09	1.10	1.11	1.19	1.06	1.10
6600	1.09	1.12	1.10	1.12	1.13	1.21	1.08	1.12
6800	1.11	1.15	1.13	1.14	1.15	1.23	1.10	1.13
7000	1.13	1.17	1.16	1.17	1.17	1.26	1.12	1.15
7200	1.16	1.19	1.19	1.20	1.20	1.29	1.14	1.18
7400	1.19	1.22	1.22	1.23	1.22	1.32	1.16	1.20
7600	1.21	1.25	1.25	1.27	1.25	1.35	1.18	1.23
7800	1.25	1.28	1.29	1.30	1.28	1.39	1.22	1.26
8000	1.28	1.31	1.33	1.34	1.32	1.42	1.25	1.29
8200	1.31	1.34	1.35	1.37	1.33	1.45	1.27	1.33
8400	1.34	1.37	1.38	1.40	1.35	1.47	1.30	1.36
8500	1.34	1.38	1.38	1.41	1.35	1.48	1.31	1.37

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION COM to terminated port								
	(dB)								
	COM-J1 @J16 Active	COM-J2 @J1 Active	COM-J4 @J3 Active	COM-J5 @J6 Active	COM-J7 @J6 Active	COM-J8 @J7 Active	COM-J10 @J9 Active	COM-J13 @J12 Active	COM-J15 @J14 Active
0.1	104.83	95.37	95.76	103.09	103.09	97.51	96.60	94.48	97.87
0.5	97.59	96.10	94.36	99.98	99.98	93.23	97.03	94.26	110.62
1	96.63	103.45	107.04	98.61	98.61	96.46	96.81	99.91	101.40
5	94.48	104.63	93.99	103.55	103.55	93.52	98.77	93.11	97.30
10	119.55	105.16	101.04	103.87	103.87	106.23	107.36	100.58	100.02
20	124.71	104.47	95.69	101.88	101.88	99.89	100.20	105.46	96.81
50	119.45	104.28	93.55	95.40	95.40	98.18	98.60	99.02	95.56
100	113.20	106.78	90.06	95.03	95.03	95.26	94.32	99.43	98.33
200	110.74	105.97	88.93	92.98	92.98	94.74	94.62	98.72	95.42
400	112.10	116.98	89.41	94.05	94.05	94.36	92.84	94.91	93.27
600	119.67	117.17	89.86	93.72	93.72	94.58	90.90	94.98	92.35
800	111.45	123.27	89.61	95.34	95.34	96.13	89.69	94.00	92.84
1000	106.78	110.96	90.15	95.52	95.52	97.60	90.21	95.07	91.89
1200	115.99	130.35	90.95	96.73	96.73	104.33	90.07	95.74	92.03
1400	114.24	113.69	90.77	97.62	97.62	104.23	89.75	93.48	92.68
1600	109.29	102.43	91.24	98.11	98.11	107.08	90.14	95.89	92.11
1800	116.97	110.55	91.89	99.90	99.90	118.60	89.78	94.90	91.69
2000	124.15	116.13	93.87	101.63	101.63	126.55	89.79	97.09	91.13
2200	105.27	112.93	92.35	102.14	102.14	126.83	88.36	96.56	91.03
2400	109.09	109.55	92.11	98.51	98.51	107.98	88.54	96.33	90.93
2600	111.61	100.38	93.13	113.05	113.05	106.00	88.33	98.55	90.75
2800	115.51	100.49	92.05	100.47	100.47	97.49	86.20	97.25	90.07
3000	107.67	102.48	92.47	103.09	103.09	98.49	86.41	97.71	89.58
3200	113.65	97.79	89.90	100.89	100.89	92.44	86.86	94.23	89.33
3400	116.97	98.46	89.97	113.17	113.17	91.25	87.02	96.06	90.13
3600	118.25	98.94	87.94	105.01	105.01	89.95	86.11	94.15	88.41
3800	118.51	97.02	87.02	106.64	106.64	88.78	85.15	95.23	89.15
4000	115.29	95.03	86.74	110.38	110.38	88.72	84.49	95.00	89.62
4200	109.93	95.56	87.06	106.33	106.33	88.49	83.82	94.11	88.67
4400	110.48	92.46	85.73	101.86	101.86	87.18	83.54	94.14	88.47
4600	110.48	91.95	85.49	102.32	102.32	86.11	83.81	96.57	88.64
4800	109.64	90.79	84.80	97.50	97.50	84.85	83.21	95.42	88.77
5000	112.27	90.30	84.28	97.57	97.57	84.02	83.63	99.51	87.23
5200	112.74	89.66	84.89	97.43	97.43	83.36	84.85	96.57	87.55
5400	105.64	89.72	84.83	98.01	98.01	83.10	86.84	94.96	86.12
5600	117.77	89.34	84.35	97.93	97.93	82.77	88.96	96.03	85.54
5800	112.84	89.58	84.82	94.67	94.67	82.37	92.77	100.10	85.45
6000	112.77	88.39	83.87	98.12	98.12	82.42	95.22	101.92	84.21
6200	106.07	87.71	83.80	94.64	94.64	82.19	96.02	99.99	83.89
6400	108.43	87.07	82.69	95.34	95.34	81.41	91.79	98.30	83.27
6600	117.09	85.68	81.92	92.11	92.11	80.50	87.40	98.67	82.39
6800	107.54	84.37	81.43	91.30	91.30	79.79	83.19	94.56	81.67
7000	103.33	83.86	80.59	89.45	89.45	78.78	80.90	94.27	80.58
7200	105.41	81.40	79.19	87.12	87.12	77.60	78.60	93.40	80.15
7400	102.11	80.10	77.77	84.28	84.28	76.25	76.54	91.97	79.87
7600	99.04	79.45	76.39	82.39	82.39	74.68	75.36	94.16	80.50
7800	98.23	78.40	74.50	81.46	81.46	73.18	74.15	91.30	80.09
8000	98.08	76.93	72.65	79.93	79.93	71.74	74.06	91.42	80.65
8200	96.88	77.03	71.05	78.57	78.57	70.34	73.52	89.17	81.30
8400	93.44	75.48	69.70	78.50	78.50	69.05	72.54	89.42	82.16
8500	96.44	74.29	68.90	77.49	77.49	68.25	72.23	88.94	82.07

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION between adjacent ports								
	(dB)								
	J1-J2 @J1 Active	J3-J4 @J3 Active	J5-J6 @J5 Active	J6-J7 @J6 Active	J8-J9 @J8 Active	J10-J11 @J10 Active	J12-J13 @J12 Active	J14-J15 @J14 Active	J15-J16 @J15 Active
0.1	94.45	95.05	106.40	101.09	96.07	98.05	101.50	91.04	97.50
0.5	92.72	97.79	94.25	98.05	99.08	97.90	101.20	97.29	95.77
1	99.75	100.38	100.24	94.18	104.09	93.25	101.78	94.11	100.24
5	93.38	94.07	96.38	95.36	109.12	90.44	91.93	98.35	96.91
10	101.85	96.96	96.62	98.61	98.03	98.18	102.00	97.88	93.95
20	98.27	93.92	93.44	95.54	95.47	96.14	97.57	97.28	93.23
50	103.78	89.64	90.36	91.54	92.11	95.82	96.17	94.73	93.33
100	105.06	87.22	88.84	90.18	89.84	94.15	94.61	92.48	92.16
200	102.16	85.69	88.09	88.97	87.94	91.67	93.88	92.23	91.96
400	109.90	85.07	87.61	88.31	86.12	90.82	90.62	90.06	91.58
600	110.02	85.92	88.09	89.08	85.53	89.66	89.96	89.47	91.02
800	113.15	84.20	88.58	90.91	86.50	90.36	89.99	87.66	89.22
1000	132.54	84.43	91.05	92.09	87.02	90.12	89.94	87.00	88.14
1200	108.42	84.07	89.55	93.13	86.24	89.99	89.16	87.94	88.74
1400	105.16	84.04	90.56	93.02	86.47	89.81	89.74	86.67	87.11
1600	101.94	83.97	90.07	92.91	87.43	88.99	90.24	86.35	87.98
1800	104.91	85.88	91.33	93.31	87.39	89.72	91.48	86.39	88.80
2000	104.24	87.16	90.79	94.42	86.55	89.92	91.05	85.59	88.92
2200	102.48	88.82	91.52	93.66	86.00	89.46	89.33	85.57	89.94
2400	97.70	89.56	92.99	93.15	86.02	89.64	89.29	85.63	89.22
2600	98.02	88.05	95.18	92.69	86.62	88.36	90.02	85.00	86.68
2800	97.44	86.34	98.65	92.50	86.08	88.95	89.60	84.68	85.61
3000	96.70	84.73	107.03	92.69	86.38	88.08	90.22	84.19	83.30
3200	95.67	84.30	106.41	93.63	87.06	88.25	90.33	84.22	82.70
3400	93.71	83.13	97.75	96.31	86.46	88.67	89.16	84.24	81.47
3600	94.03	82.80	94.57	100.64	85.55	90.28	88.76	83.54	81.23
3800	94.54	83.55	91.75	103.02	85.94	92.26	89.72	83.19	81.81
4000	93.71	84.16	91.22	100.21	84.97	93.25	89.07	81.49	81.58
4200	92.92	84.31	88.09	97.26	85.59	97.42	88.35	80.63	81.22
4400	92.53	85.34	87.82	95.13	85.65	105.26	87.17	79.70	83.39
4600	94.16	85.12	87.07	90.98	86.39	95.89	89.17	78.28	82.77
4800	90.09	83.81	88.54	88.79	86.64	92.23	89.12	78.05	81.97
5000	88.81	85.74	89.77	87.79	86.29	90.02	89.23	77.23	82.88
5200	90.49	83.01	89.49	86.21	85.09	87.82	90.12	76.13	80.53
5400	89.23	83.59	88.14	85.62	85.51	86.91	91.59	76.77	80.22
5600	87.17	86.72	89.53	84.73	87.26	85.00	91.00	75.79	81.51
5800	88.09	84.17	91.49	84.41	86.97	83.33	89.33	75.85	80.24
6000	91.09	85.29	90.80	84.49	87.21	83.18	92.07	76.76	81.22
6200	87.47	89.99	91.22	84.95	88.34	82.46	92.45	76.19	83.02
6400	86.89	85.26	89.07	84.13	89.01	82.10	91.90	77.20	82.31
6600	86.51	85.85	86.11	83.56	88.93	81.47	89.51	78.60	82.62
6800	87.47	83.20	84.64	82.73	90.04	81.19	89.86	78.66	81.65
7000	87.12	81.03	82.93	81.59	88.26	80.67	88.06	79.48	79.76
7200	84.41	79.04	83.96	80.96	87.11	80.23	87.79	79.01	77.80
7400	82.19	77.13	83.51	79.32	88.08	79.28	86.77	77.72	76.05
7600	82.23	77.76	81.14	77.13	87.32	77.41	86.68	74.75	75.83
7800	79.61	74.83	79.94	74.64	85.76	75.72	85.51	73.91	73.77
8000	75.87	73.61	79.73	72.83	90.26	74.14	85.05	71.23	72.52
8200	74.12	77.97	80.81	71.40	88.00	72.99	84.85	68.98	74.82
8400	73.72	77.89	82.42	70.35	84.66	71.70	83.71	67.59	74.72
8500	74.76	75.39	81.85	69.77	83.68	71.09	83.16	66.85	73.86

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J1	COM-J2	COM-J3	COM-J4	COM-J5	COM-J6	COM-J7	COM-J8
0.1	4.83	4.80	4.84	4.82	4.85	4.80	4.79	4.82
0.5	4.17	4.14	4.17	4.17	4.18	4.14	4.13	4.15
1	4.15	4.12	4.15	4.15	4.16	4.12	4.11	4.13
5	4.16	4.12	4.15	4.15	4.16	4.12	4.11	4.13
10	4.16	4.13	4.16	4.16	4.16	4.12	4.12	4.13
20	4.17	4.14	4.17	4.17	4.17	4.13	4.12	4.14
50	4.21	4.17	4.21	4.20	4.20	4.15	4.15	4.17
100	4.28	4.24	4.27	4.28	4.24	4.19	4.19	4.21
200	4.44	4.39	4.42	4.44	4.32	4.27	4.26	4.29
400	4.71	4.65	4.68	4.70	4.51	4.43	4.41	4.46
600	4.76	4.70	4.73	4.75	4.70	4.59	4.58	4.65
800	4.86	4.75	4.78	4.86	4.84	4.74	4.73	4.80
1000	5.14	5.01	5.05	5.14	4.94	4.84	4.82	4.89
1200	5.32	5.21	5.24	5.30	5.01	4.89	4.87	4.95
1400	5.40	5.23	5.27	5.39	5.10	4.93	4.90	5.03
1600	5.61	5.41	5.45	5.60	5.22	5.01	4.98	5.15
1800	5.83	5.70	5.74	5.81	5.34	5.15	5.12	5.29
2000	5.97	5.80	5.83	5.96	5.46	5.31	5.29	5.42
2200	6.07	5.87	5.92	6.05	5.58	5.46	5.44	5.53
2400	6.18	6.10	6.13	6.17	5.70	5.57	5.54	5.64
2600	6.36	6.25	6.28	6.34	5.80	5.64	5.62	5.72
2800	6.45	6.35	6.39	6.44	5.86	5.73	5.71	5.78
3000	6.55	6.49	6.52	6.55	5.93	5.82	5.79	5.86
3200	6.73	6.58	6.61	6.72	6.08	5.89	5.87	6.02
3400	6.82	6.68	6.71	6.82	6.21	5.95	5.92	6.15
3600	7.05	6.71	6.76	7.04	6.23	6.01	5.99	6.17
3800	7.14	6.78	6.84	7.13	6.23	6.07	6.06	6.19
4000	7.17	6.87	6.93	7.16	6.34	6.06	6.04	6.32
4200	7.37	6.80	6.87	7.36	6.49	5.98	5.97	6.48
4400	7.36	6.95	7.00	7.38	6.51	5.97	5.95	6.50
4600	7.45	7.19	7.24	7.47	6.49	6.17	6.14	6.47
4800	7.46	7.03	7.11	7.49	6.68	6.46	6.43	6.61
5000	7.58	7.35	7.36	7.61	6.90	6.59	6.55	6.84
5200	8.15	7.84	7.86	8.19	6.86	6.49	6.45	6.84
5400	8.05	7.72	7.75	8.11	6.77	6.46	6.41	6.73
5600	8.37	8.06	8.06	8.39	7.10	6.75	6.74	7.00
5800	9.07	8.60	8.67	9.14	7.68	7.19	7.21	7.58
6000	8.91	8.49	8.55	8.94	7.92	7.40	7.41	7.85
6200	8.93	8.54	8.60	8.96	7.82	7.35	7.35	7.73
6400	9.12	8.77	8.86	9.16	7.70	7.27	7.26	7.60
6600	9.06	8.73	8.78	9.05	7.69	7.31	7.28	7.60
6800	9.00	8.72	8.74	9.01	7.67	7.38	7.32	7.61
7000	9.10	8.80	8.79	9.10	7.78	7.40	7.34	7.71
7200	9.25	8.92	8.94	9.25	8.01	7.48	7.46	7.93
7400	9.53	9.17	9.15	9.54	8.09	7.62	7.63	8.00
7600	10.25	9.64	9.54	10.31	8.18	7.77	7.79	8.11
7800	10.44	9.97	9.92	10.44	8.70	8.06	8.06	8.66
8000	10.60	10.22	10.08	10.62	9.45	8.57	8.55	9.39
8200	11.48	10.85	10.70	11.43	9.97	9.11	9.10	9.87
8400	11.95	11.26	11.25	11.74	10.15	9.40	9.44	10.02
8500	11.88	11.30	11.26	11.70	10.15	9.45	9.50	10.04

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J9	COM-J10	COM-J11	COM-J12	COM-J13	COM-J14	COM-J15	COM-J16
0.1	4.85	4.85	4.86	4.84	4.81	4.88	4.84	4.83
0.5	4.18	4.18	4.21	4.19	4.15	4.24	4.18	4.19
1	4.16	4.15	4.19	4.17	4.12	4.21	4.16	4.17
5	4.16	4.15	4.19	4.17	4.13	4.22	4.16	4.17
10	4.16	4.16	4.19	4.18	4.13	4.22	4.17	4.18
20	4.17	4.17	4.20	4.19	4.15	4.23	4.18	4.19
50	4.20	4.19	4.23	4.21	4.18	4.27	4.21	4.22
100	4.24	4.23	4.27	4.26	4.25	4.34	4.28	4.30
200	4.32	4.31	4.34	4.34	4.41	4.49	4.42	4.45
400	4.50	4.46	4.50	4.52	4.65	4.74	4.67	4.70
600	4.69	4.63	4.67	4.70	4.70	4.77	4.70	4.74
800	4.84	4.77	4.82	4.85	4.81	4.86	4.77	4.86
1000	4.93	4.87	4.92	4.95	5.11	5.15	5.07	5.17
1200	5.00	4.92	4.96	5.01	5.29	5.34	5.27	5.34
1400	5.07	4.95	4.99	5.08	5.34	5.35	5.26	5.39
1600	5.19	5.02	5.05	5.19	5.52	5.49	5.41	5.57
1800	5.33	5.15	5.19	5.32	5.74	5.76	5.69	5.79
2000	5.45	5.33	5.38	5.46	5.88	5.88	5.80	5.93
2200	5.56	5.48	5.54	5.58	5.98	5.96	5.88	6.03
2400	5.67	5.59	5.64	5.69	6.10	6.19	6.11	6.16
2600	5.76	5.66	5.72	5.77	6.28	6.35	6.27	6.34
2800	5.82	5.75	5.81	5.84	6.38	6.45	6.38	6.44
3000	5.92	5.84	5.91	5.94	6.50	6.58	6.51	6.54
3200	6.09	5.92	5.96	6.11	6.67	6.68	6.61	6.71
3400	6.22	5.97	6.00	6.25	6.77	6.78	6.71	6.82
3600	6.24	6.02	6.07	6.26	7.02	6.82	6.77	7.07
3800	6.25	6.08	6.12	6.26	7.12	6.92	6.87	7.18
4000	6.37	6.08	6.07	6.37	7.14	7.01	6.97	7.18
4200	6.51	6.03	5.97	6.52	7.34	6.90	6.88	7.39
4400	6.52	6.03	5.99	6.57	7.36	7.08	7.03	7.41
4600	6.51	6.20	6.24	6.58	7.46	7.31	7.27	7.49
4800	6.68	6.47	6.54	6.73	7.48	7.15	7.13	7.52
5000	6.88	6.60	6.61	6.92	7.63	7.54	7.45	7.67
5200	6.82	6.52	6.46	6.89	8.22	8.05	7.98	8.28
5400	6.74	6.46	6.48	6.81	8.13	7.89	7.85	8.20
5600	7.11	6.74	6.88	7.16	8.35	8.22	8.13	8.39
5800	7.70	7.20	7.34	7.73	9.05	8.72	8.69	9.09
6000	7.92	7.45	7.49	7.97	8.94	8.63	8.62	8.97
6200	7.80	7.40	7.39	7.86	9.00	8.72	8.69	8.99
6400	7.67	7.29	7.32	7.73	9.19	8.91	8.91	9.20
6600	7.63	7.32	7.32	7.71	9.12	8.88	8.85	9.14
6800	7.63	7.40	7.32	7.74	9.08	8.88	8.83	9.11
7000	7.79	7.44	7.37	7.92	9.17	8.96	8.90	9.21
7200	8.04	7.54	7.53	8.14	9.33	9.10	9.07	9.35
7400	8.09	7.70	7.69	8.20	9.58	9.32	9.29	9.60
7600	8.18	7.86	7.82	8.32	10.29	9.77	9.70	10.29
7800	8.68	8.12	8.10	8.84	10.48	10.12	10.06	10.48
8000	9.35	8.59	8.61	9.50	10.70	10.38	10.26	10.69
8200	9.81	9.10	9.12	9.97	11.54	10.98	10.87	11.52
8400	10.01	9.40	9.42	10.18	11.89	11.38	11.35	11.86
8500	10.04	9.47	9.48	10.22	11.86	11.43	11.39	11.83

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)





# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	2.04	2.02	2.01	2.03	2.01	2.04	2.01	2.01	2.03
0.5	1.31	1.31	1.30	1.31	1.30	1.31	1.30	1.30	1.30
1	1.27	1.27	1.26	1.27	1.27	1.27	1.26	1.26	1.26
5	1.25	1.26	1.25	1.26	1.25	1.26	1.25	1.25	1.25
10	1.25	1.26	1.25	1.26	1.25	1.26	1.25	1.25	1.25
20	1.25	1.26	1.25	1.26	1.26	1.26	1.25	1.25	1.25
50	1.25	1.26	1.25	1.26	1.26	1.26	1.25	1.25	1.25
100	1.25	1.25	1.25	1.25	1.25	1.27	1.26	1.26	1.26
200	1.19	1.21	1.20	1.21	1.21	1.27	1.26	1.26	1.26
400	1.02	1.03	1.04	1.04	1.03	1.25	1.24	1.24	1.24
600	1.21	1.19	1.17	1.17	1.18	1.18	1.18	1.18	1.17
800	1.31	1.28	1.30	1.31	1.28	1.06	1.08	1.08	1.06
1000	1.18	1.12	1.18	1.19	1.15	1.06	1.04	1.03	1.04
1200	1.11	1.08	1.06	1.06	1.05	1.15	1.16	1.15	1.12
1400	1.21	1.12	1.25	1.26	1.15	1.16	1.26	1.24	1.15
1600	1.16	1.20	1.23	1.24	1.21	1.14	1.29	1.27	1.16
1800	1.04	1.26	1.07	1.07	1.22	1.21	1.23	1.22	1.22
2000	1.04	1.10	1.09	1.10	1.08	1.28	1.13	1.14	1.27
2200	1.06	1.26	1.08	1.10	1.23	1.27	1.06	1.08	1.26
2400	1.02	1.33	1.14	1.12	1.32	1.20	1.07	1.07	1.19
2600	1.20	1.19	1.15	1.12	1.19	1.18	1.06	1.06	1.16
2800	1.28	1.19	1.15	1.11	1.19	1.19	1.09	1.09	1.17
3000	1.12	1.12	1.25	1.21	1.14	1.14	1.17	1.17	1.13
3200	1.42	1.04	1.24	1.22	1.04	1.04	1.21	1.21	1.03
3400	1.57	1.04	1.28	1.26	1.01	1.11	1.18	1.19	1.06
3600	1.29	1.18	1.30	1.32	1.14	1.14	1.15	1.16	1.09
3800	1.52	1.23	1.18	1.22	1.21	1.07	1.25	1.26	1.04
4000	1.58	1.19	1.27	1.31	1.16	1.18	1.42	1.41	1.17
4200	1.37	1.41	1.36	1.44	1.41	1.41	1.51	1.50	1.38
4400	1.43	1.36	1.15	1.22	1.44	1.52	1.42	1.40	1.51
4600	1.31	1.12	1.13	1.19	1.19	1.39	1.18	1.18	1.44
4800	1.35	1.35	1.30	1.39	1.44	1.12	1.07	1.06	1.18
5000	1.14	1.26	1.21	1.19	1.31	1.13	1.27	1.25	1.12
5200	1.23	1.06	1.08	1.12	1.08	1.29	1.36	1.36	1.31
5400	1.30	1.18	1.21	1.27	1.26	1.24	1.28	1.27	1.31
5600	1.17	1.14	1.23	1.12	1.06	1.08	1.10	1.12	1.10
5800	1.56	1.23	1.15	1.19	1.35	1.21	1.18	1.18	1.20
6000	1.48	1.18	1.13	1.19	1.27	1.34	1.27	1.27	1.34
6200	1.36	1.08	1.08	1.05	1.21	1.29	1.25	1.22	1.32
6400	1.52	1.27	1.12	1.23	1.39	1.17	1.14	1.11	1.19
6600	1.49	1.26	1.16	1.20	1.25	1.19	1.15	1.15	1.21
6800	1.41	1.22	1.13	1.15	1.17	1.22	1.22	1.21	1.23
7000	1.24	1.25	1.20	1.16	1.11	1.17	1.19	1.17	1.15
7200	1.24	1.21	1.19	1.12	1.07	1.08	1.10	1.07	1.06
7400	1.51	1.29	1.34	1.23	1.17	1.05	1.05	1.04	1.02
7600	1.56	1.12	1.45	1.26	1.16	1.17	1.18	1.16	1.15
7800	1.34	1.18	1.27	1.09	1.04	1.19	1.37	1.33	1.23
8000	1.50	1.22	1.48	1.25	1.11	1.09	1.49	1.45	1.15
8200	1.63	1.27	1.59	1.38	1.11	1.20	1.43	1.42	1.13
8400	1.35	1.67	1.32	1.18	1.42	1.43	1.25	1.27	1.34
8500	1.18	1.71	1.33	1.13	1.47	1.51	1.19	1.21	1.43

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	2.04	2.03	2.01	2.01	2.02	2.01	2.02	2.00
0.5	1.31	1.31	1.31	1.31	1.30	1.32	1.31	1.31
1	1.27	1.27	1.28	1.27	1.26	1.28	1.27	1.27
5	1.26	1.25	1.26	1.26	1.25	1.27	1.26	1.26
10	1.26	1.25	1.26	1.26	1.25	1.27	1.26	1.26
20	1.26	1.26	1.27	1.26	1.25	1.27	1.26	1.26
50	1.26	1.26	1.27	1.26	1.25	1.27	1.26	1.26
100	1.27	1.26	1.27	1.27	1.25	1.26	1.25	1.26
200	1.28	1.27	1.27	1.27	1.22	1.22	1.21	1.21
400	1.26	1.25	1.25	1.25	1.05	1.04	1.04	1.04
600	1.17	1.18	1.18	1.17	1.19	1.20	1.18	1.19
800	1.05	1.08	1.07	1.04	1.30	1.33	1.31	1.29
1000	1.07	1.05	1.07	1.07	1.14	1.17	1.18	1.14
1200	1.15	1.17	1.19	1.15	1.09	1.10	1.07	1.08
1400	1.15	1.27	1.27	1.16	1.18	1.31	1.28	1.18
1600	1.15	1.30	1.25	1.14	1.21	1.23	1.26	1.20
1800	1.24	1.25	1.17	1.21	1.24	1.05	1.08	1.23
2000	1.32	1.15	1.12	1.30	1.09	1.12	1.08	1.09
2200	1.30	1.09	1.14	1.30	1.25	1.04	1.09	1.24
2400	1.23	1.08	1.16	1.23	1.32	1.16	1.14	1.34
2600	1.19	1.08	1.15	1.19	1.18	1.20	1.15	1.20
2800	1.18	1.12	1.20	1.18	1.17	1.19	1.13	1.19
3000	1.11	1.19	1.27	1.12	1.11	1.28	1.22	1.13
3200	1.02	1.22	1.28	1.01	1.02	1.28	1.22	1.06
3400	1.10	1.18	1.22	1.09	1.03	1.33	1.28	1.03
3600	1.12	1.13	1.19	1.12	1.17	1.33	1.31	1.17
3800	1.07	1.22	1.28	1.06	1.20	1.20	1.19	1.23
4000	1.20	1.37	1.40	1.17	1.14	1.31	1.30	1.16
4200	1.40	1.48	1.44	1.38	1.37	1.36	1.39	1.39
4400	1.50	1.46	1.33	1.51	1.35	1.12	1.16	1.39
4600	1.40	1.28	1.15	1.45	1.13	1.16	1.17	1.15
4800	1.16	1.05	1.07	1.21	1.38	1.28	1.34	1.38
5000	1.07	1.17	1.18	1.05	1.29	1.18	1.16	1.31
5200	1.23	1.32	1.24	1.22	1.06	1.10	1.13	1.04
5400	1.23	1.32	1.21	1.24	1.22	1.21	1.25	1.22
5600	1.13	1.18	1.19	1.14	1.10	1.20	1.14	1.13
5800	1.21	1.14	1.21	1.20	1.22	1.12	1.16	1.20
6000	1.30	1.19	1.21	1.28	1.18	1.14	1.15	1.18
6200	1.25	1.18	1.13	1.25	1.12	1.08	1.06	1.08
6400	1.14	1.06	1.05	1.13	1.28	1.11	1.18	1.26
6600	1.16	1.08	1.05	1.14	1.19	1.15	1.15	1.22
6800	1.22	1.13	1.12	1.21	1.14	1.13	1.11	1.18
7000	1.21	1.11	1.20	1.24	1.14	1.20	1.15	1.20
7200	1.12	1.10	1.19	1.18	1.11	1.19	1.12	1.16
7400	1.09	1.06	1.12	1.12	1.19	1.36	1.26	1.25
7600	1.22	1.06	1.28	1.27	1.11	1.42	1.27	1.13
7800	1.22	1.29	1.54	1.31	1.10	1.27	1.13	1.12
8000	1.06	1.50	1.63	1.13	1.16	1.55	1.35	1.20
8200	1.20	1.53	1.48	1.15	1.11	1.58	1.39	1.10
8400	1.44	1.40	1.31	1.43	1.42	1.34	1.16	1.43
8500	1.52	1.33	1.31	1.52	1.46	1.41	1.19	1.50

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	2.01	1.48	1.56	1.55	1.52	1.57	1.53	1.53	1.58
0.5	1.26	1.16	1.27	1.23	1.21	1.25	1.24	1.24	1.28
1	1.22	1.14	1.26	1.22	1.20	1.23	1.23	1.22	1.26
5	1.20	1.14	1.25	1.22	1.20	1.23	1.23	1.22	1.26
10	1.20	1.14	1.25	1.22	1.20	1.23	1.22	1.22	1.26
20	1.20	1.14	1.25	1.22	1.20	1.23	1.22	1.22	1.26
50	1.20	1.13	1.25	1.21	1.19	1.23	1.22	1.22	1.26
100	1.19	1.13	1.25	1.21	1.19	1.23	1.22	1.22	1.25
200	1.19	1.13	1.24	1.21	1.19	1.22	1.22	1.21	1.25
400	1.18	1.12	1.24	1.20	1.18	1.21	1.21	1.21	1.24
600	1.17	1.12	1.22	1.19	1.17	1.21	1.20	1.20	1.23
800	1.17	1.11	1.21	1.18	1.17	1.20	1.20	1.19	1.23
1000	1.16	1.11	1.21	1.18	1.16	1.19	1.19	1.19	1.22
1200	1.15	1.10	1.20	1.17	1.16	1.18	1.19	1.18	1.21
1400	1.14	1.10	1.18	1.16	1.15	1.17	1.18	1.18	1.20
1600	1.13	1.09	1.17	1.15	1.14	1.16	1.18	1.17	1.19
1800	1.12	1.09	1.16	1.14	1.13	1.15	1.17	1.16	1.19
2000	1.12	1.08	1.14	1.13	1.12	1.13	1.16	1.15	1.17
2200	1.11	1.07	1.12	1.12	1.11	1.12	1.15	1.14	1.16
2400	1.10	1.07	1.11	1.10	1.10	1.11	1.14	1.13	1.14
2600	1.09	1.06	1.10	1.09	1.09	1.10	1.13	1.13	1.13
2800	1.09	1.06	1.09	1.08	1.08	1.08	1.12	1.12	1.12
3000	1.09	1.05	1.08	1.08	1.07	1.07	1.11	1.11	1.11
3200	1.08	1.04	1.09	1.07	1.06	1.06	1.10	1.10	1.11
3400	1.08	1.04	1.09	1.06	1.06	1.05	1.10	1.09	1.11
3600	1.09	1.03	1.10	1.06	1.05	1.04	1.09	1.08	1.10
3800	1.10	1.02	1.11	1.05	1.05	1.04	1.08	1.08	1.09
4000	1.11	1.02	1.11	1.05	1.05	1.03	1.08	1.07	1.08
4200	1.12	1.02	1.12	1.05	1.04	1.03	1.08	1.07	1.08
4400	1.13	1.02	1.13	1.05	1.04	1.03	1.07	1.06	1.07
4600	1.14	1.03	1.13	1.05	1.04	1.03	1.06	1.06	1.06
4800	1.15	1.03	1.13	1.04	1.03	1.02	1.06	1.05	1.05
5000	1.17	1.04	1.14	1.04	1.02	1.02	1.05	1.05	1.05
5200	1.18	1.05	1.15	1.04	1.02	1.02	1.04	1.04	1.05
5400	1.20	1.06	1.15	1.04	1.02	1.03	1.04	1.04	1.04
5600	1.20	1.07	1.16	1.04	1.01	1.03	1.04	1.03	1.05
5800	1.21	1.10	1.15	1.05	1.02	1.04	1.03	1.05	1.06
6000	1.20	1.11	1.17	1.05	1.01	1.05	1.05	1.05	1.06
6200	1.20	1.12	1.17	1.06	1.03	1.07	1.06	1.07	1.08
6400	1.20	1.15	1.18	1.07	1.05	1.08	1.08	1.09	1.10
6600	1.20	1.16	1.18	1.08	1.06	1.09	1.10	1.10	1.12
6800	1.19	1.19	1.19	1.10	1.09	1.11	1.12	1.12	1.13
7000	1.18	1.21	1.21	1.11	1.11	1.13	1.14	1.14	1.15
7200	1.17	1.25	1.23	1.14	1.14	1.15	1.17	1.17	1.17
7400	1.16	1.28	1.25	1.16	1.18	1.17	1.20	1.20	1.19
7600	1.14	1.32	1.28	1.18	1.21	1.19	1.23	1.23	1.22
7800	1.13	1.35	1.30	1.21	1.25	1.22	1.26	1.27	1.24
8000	1.12	1.39	1.34	1.24	1.30	1.26	1.30	1.31	1.27
8200	1.12	1.43	1.36	1.27	1.33	1.28	1.32	1.34	1.29
8400	1.12	1.47	1.38	1.29	1.36	1.31	1.34	1.38	1.30
8500	1.13	1.49	1.39	1.30	1.38	1.31	1.34	1.39	1.31

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	1.54	1.56	1.51	1.48	1.55	1.47	1.53	1.50
0.5	1.22	1.24	1.21	1.17	1.25	1.16	1.22	1.22
1	1.21	1.23	1.19	1.15	1.24	1.14	1.21	1.20
5	1.20	1.23	1.19	1.15	1.23	1.14	1.21	1.20
10	1.20	1.23	1.19	1.15	1.23	1.14	1.21	1.20
20	1.20	1.23	1.19	1.15	1.23	1.14	1.21	1.20
50	1.20	1.22	1.19	1.15	1.23	1.14	1.21	1.20
100	1.20	1.22	1.19	1.14	1.23	1.13	1.20	1.19
200	1.19	1.22	1.18	1.14	1.22	1.13	1.20	1.19
400	1.19	1.21	1.17	1.14	1.22	1.12	1.19	1.19
600	1.18	1.20	1.17	1.13	1.21	1.12	1.18	1.18
800	1.17	1.19	1.15	1.12	1.20	1.11	1.18	1.17
1000	1.16	1.19	1.15	1.12	1.19	1.11	1.17	1.17
1200	1.15	1.18	1.13	1.11	1.18	1.10	1.16	1.16
1400	1.14	1.17	1.12	1.11	1.17	1.10	1.15	1.15
1600	1.12	1.16	1.11	1.10	1.15	1.10	1.14	1.14
1800	1.11	1.15	1.10	1.10	1.14	1.09	1.13	1.13
2000	1.10	1.14	1.08	1.09	1.13	1.09	1.12	1.12
2200	1.09	1.13	1.07	1.09	1.11	1.08	1.10	1.11
2400	1.08	1.12	1.06	1.08	1.10	1.07	1.09	1.10
2600	1.07	1.11	1.05	1.07	1.09	1.07	1.08	1.09
2800	1.06	1.10	1.04	1.06	1.08	1.06	1.07	1.07
3000	1.05	1.09	1.04	1.06	1.07	1.05	1.07	1.06
3200	1.05	1.09	1.04	1.05	1.07	1.04	1.06	1.05
3400	1.04	1.09	1.04	1.05	1.06	1.03	1.05	1.04
3600	1.04	1.09	1.04	1.04	1.06	1.02	1.05	1.03
3800	1.04	1.08	1.05	1.05	1.06	1.01	1.05	1.02
4000	1.04	1.08	1.05	1.05	1.06	1.01	1.05	1.02
4200	1.04	1.08	1.05	1.05	1.06	1.02	1.06	1.03
4400	1.04	1.08	1.06	1.06	1.06	1.03	1.06	1.04
4600	1.04	1.07	1.06	1.06	1.06	1.05	1.06	1.04
4800	1.03	1.07	1.06	1.06	1.06	1.06	1.06	1.05
5000	1.04	1.06	1.07	1.05	1.06	1.08	1.07	1.05
5200	1.04	1.05	1.07	1.05	1.06	1.10	1.07	1.06
5400	1.04	1.04	1.08	1.05	1.07	1.11	1.08	1.06
5600	1.05	1.05	1.10	1.05	1.06	1.13	1.07	1.07
5800	1.06	1.05	1.12	1.05	1.08	1.14	1.09	1.07
6000	1.06	1.06	1.12	1.07	1.08	1.17	1.09	1.09
6200	1.09	1.08	1.15	1.08	1.10	1.18	1.10	1.10
6400	1.10	1.11	1.17	1.10	1.11	1.20	1.12	1.11
6600	1.11	1.13	1.18	1.13	1.12	1.22	1.12	1.13
6800	1.13	1.16	1.21	1.15	1.14	1.24	1.14	1.14
7000	1.14	1.18	1.23	1.18	1.15	1.26	1.15	1.15
7200	1.17	1.22	1.26	1.22	1.18	1.29	1.17	1.17
7400	1.19	1.25	1.29	1.26	1.20	1.32	1.19	1.20
7600	1.21	1.28	1.32	1.30	1.23	1.35	1.21	1.23
7800	1.25	1.32	1.35	1.34	1.26	1.39	1.23	1.27
8000	1.28	1.36	1.39	1.39	1.30	1.43	1.26	1.31
8200	1.31	1.38	1.42	1.42	1.32	1.46	1.27	1.34
8400	1.33	1.40	1.45	1.44	1.35	1.50	1.29	1.37
8500	1.34	1.41	1.46	1.45	1.36	1.51	1.29	1.38

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/VCLStore/terms.jsp](http://www.minicircuits.com/VCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION COM to terminated port								
	(dB)								
	COM-J1 @J16 Active	COM-J2 @J1 Active	COM-J4 @J3 Active	COM-J5 @J6 Active	COM-J7 @J6 Active	COM-J8 @J7 Active	COM-J10 @J9 Active	COM-J13 @J12 Active	COM-J15 @J14 Active
0.1	95.55	95.25	97.00	105.90	105.90	110.23	109.91	98.47	103.68
0.5	97.04	95.42	108.17	96.94	96.94	100.28	98.84	99.41	96.84
1	105.57	104.30	105.42	96.88	96.88	92.32	95.85	94.22	97.49
5	115.48	94.81	99.45	97.30	97.30	97.06	96.41	104.52	91.22
10	115.11	111.26	104.12	103.03	103.03	107.81	106.63	103.22	100.03
20	124.43	102.85	97.40	98.15	98.15	103.42	103.54	100.91	99.94
50	121.65	101.82	94.58	97.53	97.53	99.65	99.12	100.05	99.38
100	137.11	102.43	92.82	94.79	94.79	96.98	100.45	99.73	97.96
200	127.40	110.59	92.83	94.87	94.87	96.77	96.43	99.33	97.41
400	110.21	109.99	92.39	95.20	95.20	97.97	98.44	95.89	96.38
600	115.07	111.44	93.05	95.13	95.13	98.11	95.71	95.44	94.40
800	122.92	114.31	93.65	95.52	95.52	99.21	95.97	96.92	93.27
1000	121.43	115.16	92.51	93.79	93.79	98.94	95.78	94.72	93.17
1200	114.32	113.55	92.41	95.27	95.27	101.19	99.52	95.15	92.68
1400	114.48	110.32	94.36	95.68	95.68	116.66	100.43	96.39	92.77
1600	114.96	109.31	93.16	97.26	97.26	134.00	97.25	94.96	92.08
1800	112.39	112.39	94.22	98.29	98.29	115.30	97.74	94.83	91.55
2000	114.13	115.91	93.98	98.48	98.48	119.93	101.75	94.62	91.97
2200	110.52	109.60	92.27	97.22	97.22	112.64	96.75	95.60	90.82
2400	117.81	100.96	92.75	97.66	97.66	104.03	95.19	93.84	91.19
2600	112.90	103.39	92.09	100.22	100.22	98.61	94.40	94.31	89.44
2800	107.64	102.48	90.32	98.80	98.80	96.72	96.24	94.08	91.24
3000	117.01	100.80	90.78	98.90	98.90	96.00	94.46	94.51	89.73
3200	119.59	103.72	89.20	101.91	101.91	92.13	95.65	92.62	89.30
3400	108.34	96.99	88.75	101.36	101.36	90.66	92.75	91.55	89.41
3600	105.04	98.07	87.37	105.71	105.71	90.87	92.05	91.47	88.48
3800	109.38	96.59	86.29	101.79	101.79	90.27	91.26	92.03	89.14
4000	116.08	93.92	87.30	106.90	106.90	89.55	89.74	92.39	89.11
4200	110.68	93.26	85.98	102.44	102.44	88.22	89.15	91.05	89.24
4400	105.82	93.38	85.23	99.60	99.60	86.86	87.75	90.85	88.95
4600	114.57	93.20	85.25	97.84	97.84	85.94	88.13	92.49	89.14
4800	106.86	90.21	85.13	96.14	96.14	84.79	87.48	92.63	87.29
5000	122.69	89.96	84.91	100.03	100.03	83.71	88.32	94.33	87.37
5200	108.74	90.24	84.81	95.21	95.21	83.33	87.03	93.82	89.07
5400	109.70	89.70	85.02	94.84	94.84	82.17	88.49	94.04	88.09
5600	113.79	89.11	85.24	95.82	95.82	82.65	90.77	94.82	86.86
5800	106.22	89.46	85.16	93.43	93.43	82.40	91.11	94.70	86.44
6000	122.78	89.45	84.12	94.10	94.10	82.52	93.62	95.11	85.35
6200	110.82	87.89	83.85	92.61	92.61	82.18	94.26	97.08	85.02
6400	115.24	87.59	83.11	91.51	91.51	81.52	90.49	96.42	83.99
6600	106.79	85.81	82.28	90.61	90.61	80.58	89.27	95.78	82.83
6800	109.19	84.32	81.31	89.41	89.41	79.68	84.84	94.19	82.71
7000	101.43	82.69	79.91	88.34	88.34	78.27	82.12	93.95	81.68
7200	102.78	81.34	78.86	85.66	85.66	76.97	80.39	93.13	80.95
7400	105.13	79.88	77.42	83.59	83.59	75.73	78.24	91.46	81.00
7600	105.01	79.44	75.88	81.57	81.57	74.05	76.71	90.72	81.79
7800	99.55	78.10	74.50	80.94	80.94	72.76	75.73	89.52	80.98
8000	107.64	77.01	72.45	79.73	79.73	71.37	75.16	89.35	82.14
8200	97.40	76.50	70.99	79.01	79.01	70.21	74.30	88.21	83.67
8400	95.47	75.40	69.82	77.86	77.86	68.93	73.53	86.90	84.11
8500	95.32	74.28	68.99	76.90	76.90	68.35	72.99	87.03	83.65

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION between adjacent ports								
	(dB)								
	J1-J2 @J1 Active	J3-J4 @J3 Active	J5-J6 @J5 Active	J6-J7 @J6 Active	J8-J9 @J8 Active	J10-J11 @J10 Active	J12-J13 @J12 Active	J14-J15 @J14 Active	J15-J16 @J15 Active
0.1	114.95	99.41	109.29	105.32	100.21	92.71	93.52	96.58	94.54
0.5	98.54	101.37	93.16	95.87	103.60	98.52	98.38	94.80	102.35
1	96.87	107.96	95.83	97.58	95.60	98.79	93.94	96.18	97.42
5	99.40	96.34	96.22	100.94	101.96	93.02	101.98	98.13	97.89
10	102.42	96.72	99.52	98.51	100.07	105.59	99.93	95.96	99.04
20	98.11	93.63	94.39	96.13	96.65	98.84	98.15	97.07	95.40
50	99.86	91.12	92.10	92.64	94.95	96.44	99.16	94.26	97.08
100	99.00	89.22	90.43	90.71	93.46	96.76	96.13	94.07	96.24
200	104.63	87.90	89.88	90.89	92.47	96.11	95.34	94.41	95.37
400	110.80	87.96	88.66	89.04	90.79	93.75	92.02	90.68	94.01
600	104.00	88.10	90.25	90.74	89.88	94.22	90.59	90.16	94.92
800	106.00	87.21	91.72	90.37	91.64	95.50	91.47	88.42	92.95
1000	108.84	86.28	91.61	92.27	90.98	96.09	90.47	88.20	92.60
1200	105.23	86.02	90.92	91.46	89.51	96.42	89.61	88.09	92.31
1400	105.66	85.65	91.52	91.06	90.48	95.62	89.64	86.14	91.74
1600	102.91	86.39	91.59	91.76	91.55	94.84	90.50	86.32	94.00
1800	103.13	87.84	92.40	93.23	91.22	94.31	89.94	86.46	94.90
2000	102.68	88.45	91.84	92.14	89.32	98.05	88.74	85.14	98.56
2200	99.44	88.63	92.11	91.48	88.54	94.42	87.85	84.95	103.22
2400	101.36	90.07	93.89	90.83	87.74	93.92	87.91	84.89	101.54
2600	100.01	88.00	94.76	91.42	89.52	93.05	86.87	83.80	93.88
2800	101.56	86.10	97.00	90.64	88.73	91.36	87.27	84.06	92.46
3000	99.13	84.38	104.86	90.66	88.14	92.94	87.08	83.69	89.39
3200	95.38	82.90	104.37	91.30	88.84	93.59	87.54	82.99	87.91
3400	95.91	82.40	96.52	93.07	88.31	93.35	86.53	82.77	86.75
3600	93.78	81.96	94.39	97.51	87.00	96.22	86.36	82.44	86.94
3800	93.82	82.67	91.02	101.85	86.74	96.55	85.91	82.66	88.63
4000	91.81	82.48	89.03	110.65	86.29	98.45	85.58	81.39	89.61
4200	91.90	82.59	87.70	100.40	84.71	98.84	83.86	80.89	89.27
4400	92.51	84.07	86.64	93.20	85.23	95.24	85.28	80.42	93.95
4600	92.18	83.81	87.08	90.46	86.63	93.08	86.29	79.03	92.34
4800	90.54	82.42	88.14	88.19	86.86	91.43	86.67	78.77	89.20
5000	89.76	84.04	88.99	87.24	85.89	90.01	85.61	77.46	94.87
5200	90.68	81.94	89.58	85.40	85.49	88.35	86.19	76.59	86.96
5400	90.88	82.38	88.59	84.30	86.83	86.89	88.04	77.10	87.73
5600	87.76	84.71	90.30	83.31	87.04	85.33	87.36	76.15	93.81
5800	88.85	82.99	91.20	82.98	85.19	84.25	86.67	76.14	88.42
6000	91.75	84.88	91.36	83.14	85.73	84.26	87.74	76.97	92.95
6200	88.19	89.27	92.57	83.71	85.80	83.95	89.33	76.49	92.73
6400	86.60	86.27	89.50	83.11	86.23	83.31	89.57	77.40	88.79
6600	87.75	86.46	86.82	82.62	85.51	82.42	88.20	78.52	89.42
6800	85.47	84.19	84.58	82.19	86.10	81.58	88.05	79.33	84.31
7000	84.45	81.91	83.67	81.58	84.67	80.69	86.61	80.05	82.45
7200	83.10	78.92	83.58	81.22	83.27	79.94	84.70	80.64	80.04
7400	80.75	77.23	82.74	79.34	83.73	78.46	85.11	80.48	79.04
7600	80.84	77.74	80.49	77.04	82.85	76.87	83.31	76.89	79.49
7800	79.87	74.60	79.24	74.63	82.62	74.86	82.51	75.67	76.31
8000	76.31	73.84	79.26	72.69	83.79	73.33	82.98	72.39	76.27
8200	75.73	78.46	81.42	71.51	83.56	72.13	82.80	70.11	80.66
8400	76.98	78.14	81.71	70.14	81.26	70.92	81.29	68.51	79.80
8500	76.53	75.23	81.24	69.50	80.49	70.32	81.78	67.70	77.24

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J1	COM-J2	COM-J3	COM-J4	COM-J5	COM-J6	COM-J7	COM-J8
0.1	4.89	4.86	4.90	4.89	4.92	4.86	4.85	4.89
0.5	4.26	4.23	4.26	4.25	4.26	4.22	4.21	4.23
1	4.24	4.20	4.23	4.23	4.24	4.20	4.19	4.21
5	4.24	4.21	4.24	4.24	4.24	4.20	4.19	4.21
10	4.25	4.21	4.24	4.24	4.25	4.20	4.19	4.22
20	4.26	4.23	4.26	4.26	4.26	4.21	4.20	4.23
50	4.29	4.26	4.29	4.29	4.28	4.23	4.23	4.25
100	4.37	4.33	4.36	4.36	4.32	4.27	4.26	4.29
200	4.54	4.49	4.52	4.53	4.41	4.35	4.34	4.37
400	4.82	4.75	4.79	4.81	4.61	4.52	4.51	4.56
600	4.86	4.80	4.82	4.85	4.80	4.69	4.68	4.75
800	4.97	4.86	4.88	4.97	4.95	4.85	4.83	4.91
1000	5.25	5.12	5.16	5.25	5.04	4.94	4.92	5.00
1200	5.42	5.32	5.34	5.42	5.11	4.99	4.97	5.06
1400	5.50	5.34	5.37	5.50	5.20	5.02	5.00	5.14
1600	5.71	5.51	5.56	5.71	5.32	5.10	5.07	5.26
1800	5.93	5.81	5.84	5.92	5.44	5.25	5.22	5.40
2000	6.07	5.91	5.93	6.06	5.56	5.41	5.39	5.51
2200	6.16	5.98	6.02	6.15	5.68	5.55	5.54	5.62
2400	6.27	6.20	6.23	6.26	5.80	5.65	5.64	5.74
2600	6.45	6.35	6.37	6.44	5.88	5.73	5.71	5.82
2800	6.54	6.46	6.48	6.53	5.94	5.82	5.80	5.88
3000	6.65	6.59	6.61	6.65	6.02	5.90	5.88	5.96
3200	6.81	6.67	6.70	6.81	6.17	5.97	5.95	6.12
3400	6.91	6.76	6.79	6.91	6.29	6.03	6.00	6.24
3600	7.14	6.81	6.84	7.14	6.31	6.10	6.07	6.26
3800	7.24	6.90	6.94	7.24	6.33	6.16	6.14	6.29
4000	7.27	6.98	7.02	7.28	6.46	6.14	6.12	6.43
4200	7.47	6.90	6.97	7.47	6.60	6.07	6.06	6.58
4400	7.48	7.08	7.12	7.50	6.62	6.09	6.06	6.60
4600	7.57	7.30	7.34	7.59	6.62	6.30	6.26	6.58
4800	7.58	7.16	7.22	7.60	6.81	6.58	6.54	6.74
5000	7.71	7.49	7.49	7.76	7.02	6.70	6.66	6.95
5200	8.29	7.97	8.00	8.33	6.98	6.60	6.56	6.94
5400	8.18	7.84	7.88	8.23	6.88	6.56	6.52	6.84
5600	8.51	8.22	8.22	8.55	7.24	6.88	6.87	7.14
5800	9.24	8.78	8.83	9.33	7.85	7.37	7.35	7.75
6000	9.06	8.66	8.70	9.11	8.08	7.58	7.55	8.03
6200	9.08	8.72	8.75	9.16	7.94	7.50	7.47	7.90
6400	9.25	8.93	8.99	9.32	7.81	7.40	7.38	7.76
6600	9.18	8.86	8.91	9.19	7.79	7.42	7.42	7.74
6800	9.14	8.85	8.89	9.14	7.79	7.46	7.46	7.73
7000	9.26	8.95	8.96	9.27	7.94	7.50	7.49	7.87
7200	9.44	9.13	9.13	9.45	8.19	7.64	7.64	8.13
7400	9.78	9.44	9.37	9.80	8.28	7.82	7.83	8.22
7600	10.51	9.95	9.81	10.59	8.44	8.01	8.02	8.39
7800	10.68	10.24	10.17	10.70	9.01	8.34	8.34	8.95
8000	10.85	10.48	10.35	10.90	9.75	8.86	8.85	9.69
8200	11.75	11.16	10.99	11.76	10.26	9.40	9.40	10.21
8400	12.20	11.62	11.54	12.14	10.44	9.73	9.73	10.41
8500	12.15	11.66	11.57	12.10	10.45	9.79	9.80	10.42

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	INSERTION LOSS							
	(dB)							
	COM-J9	COM-J10	COM-J11	COM-J12	COM-J13	COM-J14	COM-J15	COM-J16
0.1	4.92	4.91	4.92	4.91	4.85	4.94	4.89	4.89
0.5	4.26	4.25	4.29	4.27	4.21	4.31	4.25	4.26
1	4.24	4.23	4.27	4.24	4.19	4.29	4.22	4.24
5	4.24	4.23	4.27	4.25	4.20	4.29	4.23	4.24
10	4.24	4.23	4.27	4.25	4.20	4.30	4.23	4.25
20	4.25	4.24	4.28	4.26	4.21	4.31	4.25	4.26
50	4.28	4.26	4.30	4.28	4.25	4.34	4.28	4.30
100	4.32	4.30	4.34	4.33	4.32	4.41	4.34	4.37
200	4.40	4.38	4.41	4.41	4.48	4.58	4.50	4.54
400	4.60	4.55	4.59	4.61	4.74	4.83	4.75	4.80
600	4.79	4.73	4.76	4.80	4.78	4.86	4.78	4.83
800	4.94	4.88	4.91	4.95	4.90	4.96	4.86	4.96
1000	5.03	4.97	5.01	5.04	5.20	5.26	5.16	5.27
1200	5.10	5.02	5.05	5.11	5.38	5.44	5.36	5.44
1400	5.17	5.04	5.07	5.18	5.43	5.45	5.35	5.49
1600	5.29	5.11	5.14	5.28	5.61	5.60	5.49	5.67
1800	5.42	5.25	5.28	5.41	5.83	5.87	5.78	5.89
2000	5.54	5.43	5.47	5.54	5.97	5.98	5.88	6.03
2200	5.65	5.58	5.63	5.66	6.06	6.07	5.97	6.13
2400	5.76	5.68	5.72	5.77	6.18	6.30	6.20	6.25
2600	5.84	5.76	5.80	5.85	6.36	6.45	6.35	6.43
2800	5.90	5.85	5.89	5.92	6.46	6.55	6.46	6.53
3000	6.01	5.94	5.98	6.02	6.58	6.69	6.59	6.65
3200	6.18	6.01	6.03	6.20	6.75	6.79	6.69	6.81
3400	6.30	6.05	6.08	6.33	6.86	6.88	6.78	6.92
3600	6.31	6.11	6.14	6.34	7.10	6.92	6.84	7.17
3800	6.34	6.17	6.19	6.36	7.20	7.03	6.95	7.27
4000	6.45	6.17	6.15	6.47	7.22	7.11	7.04	7.28
4200	6.59	6.12	6.07	6.61	7.42	7.00	6.96	7.48
4400	6.62	6.14	6.10	6.65	7.45	7.21	7.13	7.53
4600	6.63	6.33	6.34	6.68	7.56	7.43	7.36	7.61
4800	6.81	6.59	6.63	6.84	7.58	7.26	7.22	7.63
5000	6.99	6.72	6.70	7.01	7.75	7.69	7.57	7.81
5200	6.94	6.62	6.56	6.98	8.34	8.18	8.09	8.41
5400	6.85	6.57	6.56	6.91	8.24	8.02	7.95	8.32
5600	7.23	6.86	6.98	7.28	8.48	8.37	8.25	8.53
5800	7.84	7.37	7.46	7.89	9.19	8.86	8.81	9.23
6000	8.07	7.63	7.61	8.14	9.06	8.78	8.74	9.11
6200	7.92	7.55	7.50	8.00	9.13	8.89	8.82	9.15
6400	7.78	7.43	7.41	7.85	9.32	9.07	9.04	9.36
6600	7.74	7.45	7.42	7.81	9.26	9.04	8.99	9.31
6800	7.75	7.52	7.42	7.84	9.23	9.06	8.99	9.29
7000	7.94	7.57	7.47	8.05	9.34	9.15	9.07	9.41
7200	8.20	7.72	7.66	8.31	9.51	9.31	9.24	9.56
7400	8.26	7.91	7.82	8.39	9.80	9.55	9.49	9.84
7600	8.39	8.09	7.96	8.56	10.51	10.02	9.93	10.55
7800	8.91	8.37	8.24	9.07	10.71	10.38	10.31	10.75
8000	9.57	8.84	8.74	9.70	10.96	10.67	10.55	11.00
8200	10.05	9.40	9.29	10.25	11.81	11.28	11.16	11.84
8400	10.26	9.75	9.61	10.54	12.18	11.69	11.65	12.20
8500	10.29	9.82	9.68	10.58	12.14	11.74	11.68	12.17

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)





# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	2.03	2.01	2.00	2.02	2.01	2.04	2.00	2.01	2.02
0.5	1.32	1.32	1.31	1.32	1.32	1.32	1.31	1.31	1.31
1	1.28	1.28	1.28	1.28	1.28	1.28	1.28	1.28	1.28
5	1.27	1.27	1.26	1.27	1.27	1.27	1.26	1.26	1.26
10	1.27	1.27	1.26	1.27	1.27	1.27	1.26	1.26	1.27
20	1.27	1.27	1.27	1.27	1.27	1.27	1.27	1.26	1.27
50	1.27	1.27	1.26	1.27	1.27	1.27	1.27	1.27	1.27
100	1.25	1.26	1.26	1.26	1.26	1.28	1.27	1.27	1.27
200	1.20	1.21	1.21	1.21	1.21	1.28	1.27	1.27	1.27
400	1.03	1.03	1.04	1.03	1.03	1.26	1.25	1.25	1.24
600	1.22	1.20	1.18	1.19	1.19	1.17	1.19	1.18	1.17
800	1.31	1.27	1.31	1.31	1.28	1.05	1.08	1.08	1.06
1000	1.18	1.12	1.18	1.19	1.14	1.07	1.05	1.04	1.05
1200	1.12	1.08	1.07	1.07	1.05	1.15	1.17	1.16	1.12
1400	1.20	1.12	1.25	1.26	1.14	1.15	1.26	1.24	1.14
1600	1.15	1.21	1.22	1.23	1.21	1.15	1.29	1.27	1.16
1800	1.03	1.25	1.08	1.07	1.23	1.22	1.23	1.22	1.23
2000	1.04	1.10	1.09	1.10	1.08	1.29	1.12	1.13	1.28
2200	1.06	1.25	1.08	1.10	1.24	1.27	1.06	1.08	1.26
2400	1.03	1.33	1.14	1.12	1.32	1.21	1.07	1.07	1.19
2600	1.21	1.19	1.14	1.12	1.20	1.19	1.06	1.06	1.18
2800	1.27	1.20	1.15	1.12	1.21	1.20	1.10	1.10	1.18
3000	1.12	1.13	1.24	1.21	1.15	1.14	1.18	1.17	1.13
3200	1.41	1.04	1.24	1.22	1.05	1.05	1.22	1.21	1.02
3400	1.56	1.03	1.29	1.28	1.01	1.12	1.19	1.18	1.07
3600	1.30	1.17	1.29	1.32	1.15	1.13	1.16	1.16	1.09
3800	1.53	1.21	1.18	1.22	1.21	1.07	1.27	1.27	1.04
4000	1.61	1.18	1.28	1.32	1.17	1.19	1.41	1.42	1.18
4200	1.40	1.41	1.35	1.44	1.41	1.40	1.49	1.50	1.37
4400	1.45	1.38	1.16	1.22	1.43	1.51	1.41	1.41	1.49
4600	1.34	1.15	1.12	1.20	1.19	1.40	1.20	1.19	1.43
4800	1.37	1.39	1.32	1.40	1.44	1.14	1.06	1.07	1.19
5000	1.14	1.29	1.21	1.19	1.34	1.14	1.28	1.27	1.13
5200	1.25	1.06	1.07	1.14	1.09	1.31	1.39	1.37	1.33
5400	1.30	1.21	1.22	1.27	1.27	1.25	1.28	1.27	1.32
5600	1.19	1.10	1.20	1.12	1.04	1.08	1.09	1.11	1.09
5800	1.58	1.26	1.16	1.20	1.37	1.23	1.21	1.20	1.22
6000	1.48	1.20	1.13	1.18	1.28	1.35	1.30	1.29	1.36
6200	1.35	1.12	1.08	1.07	1.23	1.28	1.25	1.22	1.31
6400	1.49	1.29	1.12	1.22	1.37	1.15	1.12	1.09	1.17
6600	1.45	1.24	1.12	1.18	1.21	1.19	1.15	1.15	1.19
6800	1.38	1.20	1.10	1.13	1.14	1.21	1.20	1.19	1.20
7000	1.23	1.21	1.18	1.15	1.10	1.17	1.17	1.15	1.15
7200	1.26	1.19	1.18	1.11	1.09	1.08	1.10	1.07	1.08
7400	1.57	1.28	1.36	1.24	1.21	1.07	1.05	1.02	1.05
7600	1.59	1.12	1.47	1.27	1.16	1.19	1.20	1.16	1.19
7800	1.34	1.15	1.30	1.11	1.05	1.20	1.40	1.34	1.24
8000	1.50	1.19	1.50	1.27	1.13	1.08	1.51	1.46	1.13
8200	1.58	1.23	1.59	1.39	1.11	1.20	1.44	1.43	1.13
8400	1.27	1.59	1.31	1.18	1.42	1.42	1.26	1.28	1.33
8500	1.11	1.63	1.31	1.14	1.46	1.49	1.19	1.21	1.41

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Active Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	2.03	2.03	2.01	2.01	2.01	2.00	2.01	1.99
0.5	1.32	1.32	1.32	1.32	1.31	1.33	1.32	1.32
1	1.29	1.28	1.29	1.29	1.28	1.29	1.28	1.28
5	1.27	1.27	1.28	1.27	1.26	1.28	1.27	1.27
10	1.27	1.27	1.28	1.27	1.27	1.28	1.27	1.27
20	1.27	1.27	1.28	1.27	1.27	1.28	1.27	1.27
50	1.28	1.27	1.28	1.28	1.27	1.28	1.27	1.27
100	1.28	1.27	1.28	1.28	1.26	1.27	1.26	1.26
200	1.29	1.28	1.28	1.28	1.22	1.22	1.21	1.22
400	1.26	1.25	1.25	1.25	1.05	1.05	1.04	1.04
600	1.17	1.18	1.17	1.17	1.21	1.21	1.19	1.20
800	1.04	1.08	1.06	1.04	1.30	1.34	1.31	1.29
1000	1.08	1.06	1.08	1.08	1.13	1.17	1.18	1.14
1200	1.15	1.18	1.20	1.16	1.10	1.12	1.08	1.09
1400	1.14	1.28	1.26	1.15	1.17	1.31	1.28	1.17
1600	1.15	1.30	1.25	1.14	1.21	1.22	1.25	1.21
1800	1.25	1.24	1.17	1.22	1.24	1.05	1.07	1.23
2000	1.32	1.14	1.12	1.30	1.09	1.12	1.08	1.09
2200	1.30	1.09	1.14	1.30	1.25	1.03	1.08	1.24
2400	1.23	1.08	1.14	1.23	1.32	1.16	1.14	1.33
2600	1.20	1.07	1.14	1.20	1.18	1.20	1.15	1.20
2800	1.19	1.12	1.19	1.19	1.17	1.19	1.14	1.20
3000	1.12	1.20	1.25	1.12	1.11	1.28	1.22	1.14
3200	1.01	1.23	1.27	1.01	1.03	1.28	1.23	1.06
3400	1.09	1.19	1.21	1.10	1.03	1.34	1.28	1.03
3600	1.10	1.14	1.18	1.11	1.17	1.34	1.31	1.17
3800	1.06	1.23	1.28	1.07	1.20	1.21	1.19	1.23
4000	1.19	1.37	1.41	1.19	1.14	1.32	1.30	1.16
4200	1.39	1.47	1.47	1.37	1.38	1.36	1.40	1.39
4400	1.52	1.45	1.37	1.49	1.36	1.12	1.17	1.39
4600	1.44	1.29	1.17	1.45	1.15	1.17	1.19	1.16
4800	1.18	1.07	1.04	1.23	1.39	1.28	1.34	1.39
5000	1.09	1.18	1.21	1.06	1.29	1.16	1.15	1.31
5200	1.27	1.34	1.29	1.24	1.07	1.10	1.14	1.04
5400	1.24	1.33	1.21	1.25	1.23	1.21	1.24	1.23
5600	1.09	1.17	1.14	1.12	1.10	1.20	1.13	1.13
5800	1.22	1.15	1.22	1.22	1.23	1.12	1.16	1.20
6000	1.33	1.21	1.25	1.30	1.18	1.13	1.14	1.17
6200	1.26	1.18	1.17	1.25	1.13	1.08	1.06	1.08
6400	1.13	1.05	1.04	1.11	1.27	1.11	1.17	1.26
6600	1.15	1.09	1.08	1.11	1.18	1.15	1.14	1.21
6800	1.19	1.12	1.13	1.18	1.14	1.13	1.10	1.18
7000	1.20	1.10	1.18	1.25	1.14	1.20	1.15	1.20
7200	1.12	1.11	1.16	1.20	1.11	1.20	1.12	1.17
7400	1.09	1.08	1.10	1.16	1.21	1.36	1.26	1.27
7600	1.22	1.08	1.26	1.30	1.12	1.43	1.28	1.15
7800	1.23	1.31	1.50	1.33	1.10	1.28	1.13	1.14
8000	1.07	1.51	1.58	1.14	1.16	1.56	1.35	1.21
8200	1.18	1.54	1.44	1.15	1.11	1.59	1.39	1.11
8400	1.43	1.40	1.26	1.42	1.41	1.35	1.17	1.44
8500	1.50	1.33	1.25	1.52	1.45	1.42	1.19	1.50

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports								
	(:1)								
	COM	J1	J2	J3	J4	J5	J6	J7	J8
0.1	1.96	1.46	1.53	1.52	1.49	1.54	1.50	1.50	1.55
0.5	1.23	1.13	1.23	1.20	1.18	1.21	1.20	1.20	1.24
1	1.18	1.11	1.22	1.18	1.17	1.20	1.19	1.19	1.22
5	1.17	1.10	1.22	1.18	1.16	1.19	1.19	1.18	1.22
10	1.17	1.10	1.22	1.18	1.16	1.19	1.19	1.18	1.22
20	1.16	1.10	1.22	1.18	1.16	1.19	1.18	1.18	1.22
50	1.16	1.10	1.22	1.18	1.16	1.19	1.19	1.18	1.22
100	1.16	1.10	1.22	1.18	1.16	1.19	1.18	1.18	1.22
200	1.16	1.10	1.22	1.18	1.16	1.19	1.18	1.18	1.22
400	1.15	1.09	1.20	1.17	1.15	1.18	1.18	1.17	1.21
600	1.14	1.09	1.19	1.16	1.14	1.17	1.17	1.16	1.20
800	1.14	1.08	1.18	1.15	1.14	1.16	1.16	1.16	1.19
1000	1.13	1.08	1.17	1.14	1.13	1.15	1.16	1.15	1.19
1200	1.12	1.08	1.16	1.13	1.12	1.14	1.15	1.15	1.18
1400	1.11	1.08	1.15	1.13	1.12	1.14	1.15	1.14	1.17
1600	1.10	1.08	1.14	1.12	1.11	1.13	1.14	1.14	1.16
1800	1.10	1.08	1.13	1.11	1.11	1.12	1.14	1.13	1.15
2000	1.10	1.08	1.11	1.10	1.10	1.11	1.14	1.13	1.14
2200	1.09	1.08	1.10	1.10	1.10	1.10	1.13	1.12	1.13
2400	1.09	1.08	1.09	1.09	1.09	1.09	1.12	1.12	1.12
2600	1.09	1.08	1.08	1.08	1.08	1.08	1.12	1.11	1.11
2800	1.09	1.08	1.07	1.07	1.08	1.07	1.11	1.11	1.10
3000	1.09	1.08	1.06	1.07	1.07	1.07	1.10	1.10	1.09
3200	1.10	1.08	1.06	1.06	1.06	1.05	1.09	1.09	1.08
3400	1.11	1.07	1.07	1.05	1.05	1.04	1.08	1.09	1.07
3600	1.12	1.07	1.08	1.05	1.05	1.04	1.08	1.08	1.07
3800	1.14	1.07	1.08	1.05	1.05	1.03	1.07	1.08	1.07
4000	1.15	1.06	1.09	1.05	1.05	1.03	1.08	1.08	1.06
4200	1.16	1.06	1.10	1.05	1.06	1.03	1.08	1.08	1.07
4400	1.17	1.06	1.10	1.04	1.06	1.02	1.09	1.07	1.06
4600	1.18	1.06	1.11	1.04	1.06	1.02	1.08	1.07	1.06
4800	1.19	1.06	1.11	1.04	1.07	1.02	1.09	1.06	1.05
5000	1.20	1.06	1.10	1.04	1.07	1.02	1.08	1.06	1.03
5200	1.20	1.06	1.11	1.03	1.06	1.01	1.06	1.04	1.02
5400	1.20	1.06	1.11	1.04	1.05	1.01	1.05	1.04	1.01
5600	1.20	1.06	1.11	1.02	1.05	1.01	1.04	1.02	1.01
5800	1.20	1.08	1.12	1.05	1.04	1.03	1.02	1.04	1.04
6000	1.19	1.08	1.14	1.04	1.02	1.03	1.03	1.03	1.05
6200	1.18	1.09	1.15	1.05	1.03	1.06	1.04	1.06	1.07
6400	1.18	1.12	1.18	1.08	1.05	1.08	1.08	1.09	1.10
6600	1.17	1.14	1.20	1.08	1.08	1.09	1.11	1.10	1.13
6800	1.17	1.17	1.22	1.11	1.11	1.12	1.14	1.14	1.14
7000	1.17	1.20	1.24	1.13	1.13	1.13	1.16	1.16	1.16
7200	1.14	1.24	1.26	1.15	1.17	1.16	1.19	1.19	1.18
7400	1.13	1.27	1.29	1.18	1.21	1.19	1.23	1.22	1.21
7600	1.12	1.31	1.32	1.20	1.25	1.21	1.25	1.26	1.23
7800	1.11	1.35	1.35	1.23	1.29	1.24	1.29	1.29	1.26
8000	1.11	1.39	1.37	1.26	1.33	1.27	1.31	1.33	1.28
8200	1.11	1.43	1.39	1.29	1.37	1.30	1.34	1.36	1.31
8400	1.12	1.47	1.40	1.31	1.39	1.32	1.35	1.39	1.32
8500	1.12	1.49	1.40	1.32	1.40	1.33	1.36	1.40	1.32

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	VSWR, Terminated Ports							
	(:1)							
	J9	J10	J11	J12	J13	J14	J15	J16
0.1	1.52	1.53	1.49	1.46	1.52	1.45	1.50	1.48
0.5	1.19	1.21	1.18	1.14	1.22	1.13	1.19	1.19
1	1.17	1.20	1.16	1.12	1.20	1.11	1.18	1.17
5	1.16	1.19	1.16	1.12	1.20	1.11	1.17	1.17
10	1.16	1.19	1.16	1.12	1.20	1.11	1.17	1.17
20	1.16	1.19	1.16	1.12	1.20	1.11	1.17	1.17
50	1.16	1.19	1.16	1.12	1.20	1.10	1.17	1.17
100	1.17	1.19	1.16	1.12	1.20	1.11	1.17	1.17
200	1.16	1.19	1.16	1.12	1.20	1.11	1.17	1.17
400	1.15	1.18	1.15	1.11	1.18	1.10	1.16	1.15
600	1.14	1.17	1.14	1.10	1.18	1.09	1.15	1.15
800	1.13	1.16	1.13	1.10	1.17	1.09	1.15	1.14
1000	1.13	1.16	1.12	1.10	1.16	1.09	1.14	1.14
1200	1.12	1.15	1.11	1.09	1.15	1.09	1.13	1.13
1400	1.11	1.14	1.10	1.09	1.14	1.09	1.12	1.12
1600	1.10	1.13	1.09	1.09	1.13	1.09	1.11	1.12
1800	1.09	1.12	1.08	1.09	1.12	1.09	1.11	1.11
2000	1.08	1.12	1.07	1.08	1.10	1.09	1.10	1.11
2200	1.08	1.11	1.07	1.08	1.10	1.09	1.09	1.10
2400	1.07	1.10	1.06	1.08	1.08	1.09	1.08	1.09
2600	1.07	1.09	1.05	1.08	1.07	1.09	1.07	1.08
2800	1.06	1.09	1.05	1.08	1.06	1.08	1.06	1.07
3000	1.05	1.08	1.05	1.07	1.05	1.08	1.05	1.06
3200	1.05	1.07	1.04	1.07	1.05	1.07	1.05	1.05
3400	1.04	1.07	1.04	1.06	1.04	1.06	1.04	1.04
3600	1.04	1.07	1.04	1.05	1.04	1.05	1.04	1.03
3800	1.04	1.07	1.04	1.05	1.04	1.04	1.04	1.03
4000	1.04	1.07	1.04	1.06	1.04	1.02	1.04	1.02
4200	1.05	1.08	1.05	1.07	1.04	1.02	1.05	1.03
4400	1.04	1.08	1.04	1.08	1.04	1.02	1.04	1.03
4600	1.04	1.08	1.04	1.08	1.04	1.03	1.05	1.03
4800	1.04	1.09	1.03	1.10	1.04	1.05	1.05	1.03
5000	1.04	1.07	1.04	1.09	1.04	1.06	1.05	1.03
5200	1.03	1.06	1.03	1.08	1.03	1.09	1.05	1.05
5400	1.02	1.04	1.04	1.07	1.05	1.10	1.06	1.04
5600	1.01	1.03	1.03	1.06	1.05	1.13	1.06	1.06
5800	1.03	1.02	1.07	1.04	1.07	1.14	1.09	1.07
6000	1.03	1.04	1.07	1.05	1.07	1.17	1.09	1.08
6200	1.06	1.07	1.10	1.06	1.09	1.19	1.10	1.10
6400	1.09	1.11	1.13	1.10	1.10	1.21	1.12	1.11
6600	1.10	1.14	1.15	1.14	1.12	1.24	1.13	1.13
6800	1.13	1.17	1.19	1.17	1.15	1.26	1.15	1.15
7000	1.15	1.20	1.21	1.21	1.17	1.29	1.17	1.18
7200	1.18	1.23	1.24	1.25	1.20	1.32	1.19	1.20
7400	1.21	1.27	1.28	1.30	1.23	1.35	1.21	1.23
7600	1.24	1.30	1.31	1.34	1.25	1.39	1.23	1.26
7800	1.27	1.34	1.35	1.39	1.29	1.43	1.25	1.30
8000	1.31	1.38	1.38	1.42	1.32	1.46	1.27	1.33
8200	1.33	1.41	1.41	1.46	1.35	1.50	1.29	1.36
8400	1.36	1.42	1.42	1.46	1.37	1.53	1.31	1.39
8500	1.37	1.42	1.43	1.47	1.38	1.54	1.31	1.40

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION COM to terminated port								
	(dB)								
	COM-J1 @J16 Active	COM-J2 @J1 Active	COM-J4 @J3 Active	COM-J5 @J6 Active	COM-J7 @J6 Active	COM-J8 @J7 Active	COM-J10 @J9 Active	COM-J13 @J12 Active	COM-J15 @J14 Active
0.1	102.34	100.44	96.93	93.25	93.25	94.84	107.28	98.64	94.80
0.5	103.20	97.10	94.72	101.72	101.72	106.14	93.76	101.81	100.85
1	98.27	98.46	91.39	95.36	95.36	93.25	97.93	91.35	97.97
5	95.56	105.26	95.87	99.55	99.55	102.91	98.22	116.91	102.31
10	108.28	109.56	102.85	112.07	112.07	105.68	101.80	105.94	103.06
20	115.34	102.98	100.21	102.66	102.66	107.56	100.96	101.78	99.39
50	111.18	104.81	96.97	102.89	102.89	100.57	97.31	101.54	100.19
100	105.31	104.03	94.32	100.91	100.91	102.69	100.40	100.93	101.33
200	132.22	111.49	97.47	101.55	101.55	102.16	95.75	99.54	98.17
400	112.38	110.41	97.97	104.42	104.42	108.62	97.40	98.61	98.99
600	119.97	113.18	100.31	109.62	109.62	108.75	95.59	96.67	102.17
800	109.29	111.36	102.63	104.61	104.61	108.37	95.36	96.73	102.36
1000	111.87	114.94	102.24	113.68	113.68	109.90	95.81	97.86	100.69
1200	111.37	117.78	103.14	114.07	114.07	112.24	97.25	99.16	100.37
1400	116.57	114.66	110.64	109.97	109.97	113.22	99.31	98.62	98.37
1600	119.52	107.68	106.07	106.83	106.83	105.98	97.32	97.26	97.40
1800	109.89	110.96	105.62	110.44	110.44	106.82	100.39	98.93	102.30
2000	106.80	122.87	103.84	112.13	112.13	99.90	98.67	97.93	100.38
2200	116.49	108.72	100.88	105.87	105.87	100.91	98.93	98.72	102.16
2400	110.59	106.71	99.59	104.54	104.54	101.45	98.75	96.70	100.64
2600	126.85	100.80	95.68	109.15	109.15	97.12	99.87	96.80	101.30
2800	108.89	99.93	94.63	105.93	105.93	95.21	97.42	97.65	101.57
3000	113.00	101.16	94.41	112.88	112.88	93.61	95.92	97.50	105.31
3200	117.58	97.46	93.74	111.75	111.75	92.47	93.64	97.63	103.63
3400	104.93	98.74	91.20	106.97	106.97	91.71	92.82	95.63	106.36
3600	107.28	96.80	90.24	123.61	123.61	89.95	92.03	96.39	102.91
3800	114.25	100.04	89.04	114.37	114.37	89.01	90.90	94.43	106.87
4000	110.02	95.46	89.00	108.94	108.94	87.34	90.59	96.32	107.44
4200	110.66	95.18	88.40	102.85	102.85	86.93	89.80	97.82	103.31
4400	105.90	93.61	86.88	101.91	101.91	85.77	89.86	96.21	109.22
4600	113.45	90.50	86.08	106.69	106.69	85.13	89.43	95.25	104.42
4800	109.06	89.13	85.42	101.66	101.66	84.57	88.54	98.21	103.71
5000	113.72	90.57	85.67	99.86	99.86	83.95	89.21	95.52	99.68
5200	119.89	89.64	85.37	98.39	98.39	83.80	88.68	99.14	99.39
5400	108.83	89.46	84.12	101.08	101.08	82.93	90.26	96.55	97.20
5600	129.88	88.31	83.86	97.47	97.47	83.09	90.64	97.20	96.66
5800	107.30	88.76	83.54	95.70	95.70	82.46	91.38	100.56	97.12
6000	123.69	88.18	82.78	99.80	99.80	82.21	92.87	98.50	95.39
6200	110.38	87.46	81.93	97.36	97.36	81.33	90.48	99.20	92.34
6400	113.06	86.28	81.27	96.15	96.15	80.46	88.87	96.55	93.15
6600	117.95	84.93	79.89	92.00	92.00	79.42	86.06	99.06	91.85
6800	106.34	83.84	79.15	90.00	90.00	78.85	83.11	96.11	90.92
7000	111.13	82.05	77.97	87.76	87.76	77.74	81.14	95.61	89.34
7200	104.15	80.47	77.13	86.16	86.16	76.53	79.46	93.66	88.58
7400	104.90	80.12	75.81	84.50	84.50	75.27	77.77	91.81	87.48
7600	101.05	78.67	74.50	82.27	82.27	73.95	76.55	90.59	85.99
7800	101.32	78.32	73.09	80.91	80.91	72.85	76.05	90.05	85.19
8000	100.08	76.70	71.74	80.23	80.23	71.37	75.55	90.99	84.23
8200	94.00	76.20	70.43	78.57	78.57	70.26	74.69	90.07	83.05
8400	96.16	75.10	69.40	77.97	77.97	68.80	74.06	89.21	81.71
8500	93.83	74.49	68.54	77.49	77.49	68.24	73.17	87.69	81.09

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State USB RF SP16T Switch

# USB-1SP16T-83H

## Typical Performance Data

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm

FREQUENCY (MHz)	ISOLATION between adjacent ports								
	(dB)								
	J1-J2 @J1 Active	J3-J4 @J3 Active	J5-J6 @J5 Active	J6-J7 @J6 Active	J8-J9 @J8 Active	J10-J11 @J10 Active	J12-J13 @J12 Active	J14-J15 @J14 Active	J15-J16 @J15 Active
0.1	127.16	98.88	117.95	108.32	97.72	101.79	98.22	103.70	98.35
0.5	118.20	108.83	94.15	97.19	107.76	97.11	95.90	90.79	91.91
1	89.21	97.26	99.21	96.83	102.95	101.00	98.85	106.38	99.90
5	96.32	101.88	103.02	95.51	93.01	98.71	97.02	95.76	92.95
10	104.36	100.44	101.14	99.09	102.90	97.08	101.04	100.48	96.91
20	105.60	96.01	98.02	100.04	98.26	99.07	99.05	95.51	97.02
50	98.89	94.60	96.88	97.96	94.09	95.85	96.18	95.90	96.10
100	102.36	92.64	97.09	96.92	93.99	96.99	95.96	97.36	97.65
200	104.22	92.42	96.90	97.92	92.65	94.72	97.25	95.27	97.45
400	111.59	94.29	97.15	101.22	91.45	94.43	92.40	96.13	97.72
600	108.23	95.34	96.65	100.90	91.20	93.88	91.52	98.29	101.20
800	109.53	94.13	101.84	102.95	92.45	96.02	92.40	95.18	99.22
1000	119.06	95.01	102.83	104.84	92.92	96.62	91.79	95.76	97.93
1200	114.76	94.41	100.40	118.42	93.35	94.98	90.98	95.20	96.34
1400	108.11	93.98	100.88	104.64	92.05	95.45	91.95	96.47	95.19
1600	104.14	94.32	100.90	111.11	93.94	95.19	91.96	95.17	95.74
1800	102.89	97.09	98.82	106.39	93.99	98.14	93.30	94.07	97.35
2000	106.04	98.34	100.18	108.69	93.73	95.24	90.81	95.84	101.82
2200	101.50	102.16	97.22	101.77	94.26	95.19	90.65	94.14	111.42
2400	100.76	107.30	100.83	100.27	92.31	94.35	89.75	92.86	106.44
2600	99.60	100.41	100.90	102.06	93.51	93.20	91.26	92.70	99.01
2800	102.26	97.43	101.14	100.44	92.48	93.27	91.99	93.42	95.50
3000	98.42	93.13	101.45	97.32	94.95	91.98	92.51	92.91	91.49
3200	94.43	93.05	103.58	97.08	92.31	90.98	90.40	94.04	90.49
3400	93.49	93.66	96.35	97.38	90.81	92.97	91.33	97.12	90.20
3600	94.55	92.36	95.54	98.10	92.67	93.86	90.19	100.31	89.04
3800	94.38	94.70	95.05	96.59	92.46	93.91	90.25	116.03	90.91
4000	92.05	96.12	92.48	95.45	91.90	96.94	89.14	100.86	92.11
4200	91.95	95.19	91.17	93.08	91.26	98.83	88.93	93.84	92.31
4400	91.97	102.31	89.65	92.70	90.93	95.17	88.71	90.82	99.24
4600	93.84	98.95	90.08	91.05	93.73	93.24	90.87	88.55	97.15
4800	90.78	95.75	90.04	89.62	93.11	91.50	91.76	87.99	92.60
5000	89.13	107.50	92.45	89.70	92.13	90.94	90.80	85.10	101.33
5200	91.04	95.12	90.34	87.88	91.10	88.11	91.12	85.28	91.86
5400	89.65	92.74	88.22	86.28	92.06	86.15	92.03	84.96	90.37
5600	88.06	100.66	87.18	86.38	92.91	84.74	89.37	84.13	101.61
5800	87.51	99.87	86.96	85.35	93.27	84.01	89.51	83.69	93.57
6000	91.51	99.71	87.63	85.37	92.55	83.64	90.66	84.22	96.54
6200	86.39	91.06	88.49	84.57	93.31	83.55	90.63	84.08	99.99
6400	85.97	89.50	86.38	83.98	92.94	81.87	89.88	84.25	92.92
6600	86.12	89.07	85.54	82.11	91.20	81.36	89.76	84.86	94.32
6800	85.18	85.27	84.20	81.05	91.79	80.63	88.99	85.23	87.64
7000	84.18	83.69	84.36	79.73	93.39	80.07	86.95	84.08	84.78
7200	82.52	81.23	84.02	78.51	89.44	79.31	86.26	83.59	81.81
7400	80.36	80.84	83.22	77.39	90.39	78.35	86.04	81.43	80.63
7600	80.31	83.19	81.38	75.65	88.37	76.66	85.08	79.02	81.65
7800	78.79	78.09	80.00	73.64	89.37	74.70	85.35	78.00	77.84
8000	75.76	75.72	80.21	71.99	90.32	73.08	84.21	74.86	76.01
8200	75.72	78.64	81.02	71.13	91.93	72.21	84.71	72.81	79.45
8400	76.86	78.11	81.23	70.24	87.78	70.72	82.80	71.29	78.47
8500	75.29	74.72	81.65	69.46	86.80	70.23	83.01	70.93	76.44

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




# Solid State USB RF SP16T Switch

# USB-1SP16T-83H


## Typical Performance Curves

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm


Insertion Loss (ports J1-J8)




Insertion Loss (ports J9-J16)



Isolation COM to Terminated port



Isolation



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




# Solid State USB RF SP16T Switch

# USB-1SP16T-83H


## Typical Performance Curves

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm


VSWR, Internally Terminated Ports




VSWR, Internally Terminated Ports



VSWR, Active Ports



VSWR, Active Ports



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MGStore/terms.jsp](http://www.minicircuits.com/MGStore/terms.jsp)

REV. OR

USB-1SP16T-83H

180228

Page 2 of 6






# Solid State USB RF SP16T Switch

# USB-1SP16T-83H


## Typical Performance Curves

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm


Insertion Loss (ports J1-J8)




Insertion Loss (ports J9-J16)



Isolation COM to Terminated port



Isolation



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




# Solid State USB RF SP16T Switch

# USB-1SP16T-83H


## Typical Performance Curves

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm


VSWR, Internally Terminated Ports




VSWR, Internally Terminated Ports



VSWR, Active Ports



VSWR, Active Ports



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MGStore/terms.jsp](http://www.minicircuits.com/MGStore/terms.jsp)




# Solid State USB RF SP16T Switch

# USB-1SP16T-83H


## Typical Performance Curves

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm


Insertion Loss (ports J1-J8)




Insertion Loss (ports J9-J16)



Isolation COM to Terminated port



Isolation



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCStore/terms.jsp](http://www.minicircuits.com/MCStore/terms.jsp)




# Solid State USB RF SP16T Switch

# USB-1SP16T-83H


## Typical Performance Curves

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm


VSWR, Internally Terminated Ports




VSWR, Internally Terminated Ports



VSWR, Active Ports



VSWR, Active Ports



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCStore/terms.jsp](http://www.minicircuits.com/MCStore/terms.jsp)




# Case Style

# RB

## Outline Dimensions

### RB2574-2



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
RB2574-2	10.98 (278.9)	2.50 (63.5)	.60 (15.2)	.69 (17.5)	.640 (16.26)	.278 (7.06)	.10 (2.54)	10.780 (273.81)	1.500 (38.10)	.50 (12.7)	.106 (2.69)	5.49 (139.45)	.73 (18.5)

CASE#	P	WT. GRAMS
RB2574-2	2.25 (57.15)	650

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

### Notes:

1. Case material: Aluminum alloy.
2. Case finish for RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Environmental Specifications **ENV55T2**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-10° to 60° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 85° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3