

# SPDT RF Switch

## VSW2-33-10W+

### The Big Deal

- High Input Power, 10W (cold switching)
- Very low insertion loss, 0.5 dB typ. at 1GHz
- Positive Control Voltage, 0/3V or 0/5V
- Small Size: 2mm x 3mm x 1mm



CASE STYLE: JZ1436

### Product Overview

VSW2-33-10W+ is a PHEMT high power reflective SPDT switch operates with positive control voltage while consuming, 20 $\mu$ A typical. Compared to competitive models, it operates over a wide frequency range, 50-3000 MHz and control voltages up to +5V. It is packaged in a tiny 2mm x 3mm x 1mm package and is rated MSL1 and class 1A for HBM.

Feature	Advantages
Broadband: 50-3000 MHz	Covers a range of wireless applications such as Cellular, PCS, LTE, WiMAX, Avionics, Broadcast, CATV, GPS, Radar etc.
High Input Power: 10W (cold switching) at +5V control	Suitable for Transmit/receive switching
Low Insertion Loss: 0.5 dB typ. at 1 GHz	Premium high power is transmitted with minimal loss and temperature rise of the DUT. In receive path results in minimal increase of system noise figure.
Positive control Voltage: 0/3V or 0/5V	No external components are required for change of operating voltage from 3 to 5V
Good Isolation: 26 dB to 1 GHz and 18 dB to 3 GHz	Minimizes filtering requirement.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# SPDT RF Switch

50Ω 50-3000 MHz

Reflective RF Switch 10W  
Positive Control Voltage; +3V to +5V

## Product Features

- High Power, 10 W (cold switching)
- Good Isolation, 26 dB typ. at 1 GHz
- Low insertion loss, 0.5 dB typ. at 1 GHz
- High IP3, 56 dBm typ. at 1 GHz
- Small size, 3mm x 2mm x 0.89 mm
- Aqueous washable

## Typical Applications

- Automated switching networks
- Cellular/ PCS
- ISM, WCDMA, WiMAX, LTE, TD-SCDMA



Generic photo used for illustration purposes only

## VSW2-33-10W+

CASE STYLE: JZ1436


**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## General Description

VSW2-33-10W+ is a high power reflective SPDT switch operates with positive control voltage while consuming, 20μA typical. It has been designed for very wideband operation of 50-3000 MHz for 50Ω systems. It is packaged in a tiny 2mm x 3mm x 1mm package and is rated MSL1 and class 1A for HBM.

## Simplified Schematic and Pad Description



Function	Pad Number	Description
RF COM	5	RF Common/ SUM Port, requires DC block (see Fig. 2)
RF1	1	RF Out #1/In Port #1, requires DC block (see Fig. 2)
RF2	3	RF Out #2/In Port #2, requires DC block (see Fig. 2)
Control #1 ( $V_{CTL1}$ )	6	Control IN #1
Control #2 ( $V_{CTL2}$ )	4	Control IN #2
GND	2	RF DC Ground

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



RF Electrical Specifications<sup>(1)</sup>, 50 - 3000 MHz, T<sub>AMB</sub>=25°C, V<sub>CTL</sub>= +3V to +5V

Parameter	Condition (MHz)	Min.	Typ.	Max.	Units	
Frequency Range		50		3000	MHz	
Insertion Loss <sup>(2)</sup>	50	—	0.4	—	dB	
	500	—	0.4	0.6		
	1000	—	0.5	0.7		
	2000	—	0.6	0.8		
	3000	—	0.6	0.8		
Isolation (From RF COM to RF1/RF2 and RF1 to RF2 ports)	50	—	42	—	dB	
	500	28	31	—		
	1000	23	26	—		
	2000	17	22	—		
	3000	15	18	—		
Return Loss (ON STATE)	50	—	24	—	dB	
	500	—	27	—		
	1000	—	21	—		
	2000	—	17	—		
	3000	—	19	—		
Input IP3	100	—	55	—	dBm	
	500	—	56	—		
	1000	—	56	—		
	2000	—	55	—		
	3000	—	53	—		
Operating Power <sup>(4,5)</sup> (cold switching)	V <sub>CTL</sub> =3V	50	—	—	7	W
		1000	—	—	7	
		2000	—	—	7	
		3000	—	—	7	
	V <sub>CTL</sub> =5V	50	—	—	10	
		1000	—	—	10	
		2000	—	—	9	
		3000	—	—	7	

DC Electrical Specifications

Parameter	Min.	Typ.	Max.	Units
Control Voltage Low (V <sub>CTL</sub> )	0	—	0.2	V
Control Voltage High (V <sub>CTL</sub> )	2.8	—	5.2	V
Control Current at (V <sub>CTL</sub> )= 3V (V <sub>CTL</sub> )= 5V	—	—	—	μA
	—	20	—	
	—	42	—	

Notes:

1. Tested on Mini-Circuits' test board TB-530+, (see Characterization Test Circuit, Fig.1).
2. Insertion loss values are deembedded from test board loss.
3. Do not exceed RF input power as shown in Absolute Maximum Rating table.
4. Derate linearly to 3W at 85°C ground lead temperature.
5. Compression 0.1 dB typ. over 1000-3000 MHz and 0.5dB typical at 50 MHz at max. operating power.

Switching Specifications

Parameter	Control Voltage (V)	Min.	Typ.	Max.	Units
Rise/Fall Time (10 to 90% or 90 to 10% RF)	0/3		433		nSec
	0/5		150		
Switching Time, 50% CTRL to 90/10% RF	0/3		550		nSec
	0/5		306		
Video Feedthrough, (control 0 to 3V, freq.=500 KHz)	0/3		20		mV <sub>p,p</sub>
	0/5		28		

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



**Absolute Maximum Ratings<sup>(4)</sup>**

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-65°C to 150°C
Control Voltage	10V
RF input power	22W, 50-2000 MHz 17W, 2000-3000 MHz

4. Operation of this device above any of these conditions may cause permanent damage.

**Truth Table** (State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	N/A	N/A
High	High	N/A	N/A

ON- low insertion loss state    OFF- Isolation State

**Characterization Test Circuit**




Figure 1: Block Diagram Of Test Circuit Used For Characterization.  
(DUT soldered on Mini-Circuit's TB-530+, Cblock=1000pF)

**Test Equipment:**

**For Insertion loss, Isolation, Return loss and DC current:**

Agilent's N5230A Network Analyzer , E3631A power supply.

**For Switching Time and DC Current:**

Agilent's 54832B oscilloscope, 81110A pulse generator and E3631A power supply.

**For Input IP3:**

Agilent's E8257D signal generators, E4418B power meter, N9020A Signal analyzer and E3631A power supply.

**For Compression:**

LZY-1+/LZY-2+/ZHL-900A-10W/ZHL-16W-43+ amplifier as driver amplifier at RF Common.  
Agilent's N5230A Network Analyzer, E3631A power supply

**Conditions:**

Control= 0 and 3V/5V

**For Insertion loss, isolation and return loss:** Pin=0 dBm

**For Input IP3:** Pin=+5dBm/tone.


**For Switching time:** RF frequency: 500 MHz at 0 dBm, Control Frequency: 100 KHz and 0 and +3/5V

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Product Marking



**Additional Detailed Technical Information**

Additional information is available on our web site. To access this information enter the model number on our web site home page.

**Performance data, graphs**

**Case Style: JZ1436**

Plastic, finish: matte tin

**Tape & Reel: F93**

**Suggested Layout for PCB Design: PL-324**

**Evaluation Board: TB-530+**

**Environmental Ratings: ENV57**

**Recommended Application Circuit**




Fig. 2: Evaluation board includes case, connectors and components soldered to PCB.

Frequency (MHz)	Cblock (Suggested value)
50-3000	1000 pF

Cblock should be free of resonance over frequency of operation.

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



**ESD Rating**


Human Body Model (HBM): Class 1A (250 to < 500V) in accordance with JESD22-A114

Machine Model (MM): Class A (Passes 150V) in accordance with JESD22-A115

**MSL Rating**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

**MSL Test Flow Chart**



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Typical Performance Data

RF FREQ (MHz)	INSERTION LOSS @ Vctl=+3V OVER TEMPERATURE						RF FREQ (MHz)	ISOLATION @ Vctl=+3V OVER TEMPERATURE											
	RF COM-RF1 (dB)			RF COM-RF2 (dB)				RF COM-RF1 (dB)			RF COM-RF2 (dB)			RF1-RF2 (dB)			RF1-RF2 (dB)		
														ON1			ON2		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C		-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
5.0	0.28	0.32	0.35	0.27	0.31	0.34	5.0	49.67	50.02	50.18	49.67	50.05	50.18	50.04	50.34	50.57	49.91	50.40	50.64
7.0	0.29	0.33	0.37	0.28	0.32	0.36	7.0	48.42	48.89	49.16	48.52	49.05	49.18	48.91	49.49	49.71	48.83	49.39	49.71
10.0	0.30	0.34	0.38	0.29	0.33	0.37	10.0	46.29	47.19	47.65	46.33	47.13	47.62	46.83	47.61	48.16	46.70	47.69	48.22
50.0	0.30	0.35	0.39	0.30	0.35	0.40	50.0	41.27	42.16	42.73	41.36	42.19	42.78	41.79	42.71	43.36	41.68	42.65	43.32
100.0	0.30	0.36	0.40	0.30	0.36	0.40	100.0	39.03	39.83	40.35	39.09	39.84	40.38	39.49	40.33	40.93	39.44	40.29	40.90
200.0	0.30	0.36	0.41	0.30	0.36	0.41	200.0	36.43	37.11	37.42	36.54	37.12	37.44	36.90	37.58	37.93	36.77	37.52	37.91
300.0	0.30	0.37	0.42	0.29	0.36	0.42	300.0	34.60	35.07	35.17	34.62	35.05	35.13	35.01	35.47	35.64	34.90	35.44	35.63
400.0	0.30	0.37	0.43	0.29	0.37	0.43	400.0	33.00	33.33	33.30	32.97	33.27	33.24	33.37	33.68	33.73	33.28	33.67	33.70
500.0	0.30	0.38	0.45	0.29	0.38	0.44	500.0	31.64	31.81	31.74	31.61	31.76	31.68	31.95	32.16	32.14	31.92	32.13	32.10
600.0	0.32	0.40	0.47	0.29	0.38	0.45	600.0	30.47	30.50	30.42	30.41	30.44	30.34	30.69	30.81	30.76	30.73	30.80	30.76
700.0	0.30	0.40	0.48	0.29	0.39	0.47	700.0	29.33	29.34	29.22	29.28	29.29	29.16	29.56	29.65	29.58	29.60	29.66	29.60
800.0	0.30	0.41	0.48	0.29	0.40	0.47	800.0	28.29	28.35	28.21	28.23	28.28	28.14	28.55	28.65	28.55	28.55	28.66	28.58
900.0	0.34	0.43	0.50	0.32	0.42	0.49	900.0	27.44	27.48	27.34	27.38	27.42	27.27	27.73	27.79	27.69	27.71	27.81	27.71
1000.0	0.33	0.44	0.52	0.31	0.43	0.51	1000.0	26.66	26.67	26.54	26.60	26.61	26.49	26.93	26.99	26.90	26.98	27.03	26.95
1100.0	0.34	0.45	0.54	0.32	0.44	0.53	1100.0	25.95	25.94	25.83	25.87	25.87	25.76	26.19	26.25	26.17	26.27	26.36	26.26
1200.0	0.34	0.46	0.55	0.33	0.45	0.54	1200.0	25.22	25.23	25.11	25.22	25.27	25.12	25.55	25.64	25.53	25.61	25.66	25.56
1300.0	0.35	0.47	0.57	0.33	0.46	0.56	1300.0	24.74	24.71	24.60	24.71	24.70	24.58	25.02	25.07	25.00	25.08	25.11	25.04
1400.0	0.36	0.49	0.58	0.34	0.48	0.57	1400.0	24.23	24.19	24.08	24.19	24.17	24.05	24.48	24.55	24.47	24.59	24.60	24.54
1500.0	0.37	0.50	0.60	0.36	0.49	0.58	1500.0	23.71	23.71	23.60	23.67	23.69	23.57	24.01	24.09	24.00	24.09	24.13	24.05
1600.0	0.38	0.52	0.62	0.36	0.50	0.60	1600.0	23.24	23.28	23.15	23.17	23.25	23.08	23.56	23.65	23.53	23.60	23.69	23.61
1700.0	0.39	0.52	0.63	0.36	0.51	0.61	1700.0	22.83	22.86	22.73	22.78	22.83	22.69	23.22	23.27	23.17	23.21	23.29	23.20
1800.0	0.40	0.53	0.64	0.36	0.52	0.62	1800.0	22.51	22.49	22.36	22.44	22.45	22.31	22.86	22.90	22.79	22.92	22.93	22.84
1900.0	0.39	0.54	0.65	0.37	0.52	0.63	1900.0	22.13	22.10	21.98	22.09	22.09	21.95	22.48	22.54	22.44	22.54	22.55	22.47
2000.0	0.39	0.54	0.66	0.37	0.53	0.64	2000.0	21.78	21.76	21.63	21.74	21.75	21.59	22.16	22.21	22.11	22.20	22.23	22.13
2100.0	0.40	0.55	0.67	0.38	0.54	0.65	2100.0	21.45	21.44	21.31	21.39	21.41	21.26	21.82	21.87	21.77	21.89	21.93	21.82
2200.0	0.40	0.56	0.68	0.39	0.55	0.67	2200.0	21.14	21.15	21.00	21.07	21.10	20.95	21.54	21.59	21.48	21.59	21.64	21.52
2300.0	0.41	0.57	0.69	0.39	0.56	0.68	2300.0	20.81	20.84	20.67	20.77	20.82	20.64	21.26	21.31	21.18	21.27	21.33	21.20
2400.0	0.40	0.56	0.69	0.39	0.56	0.68	2400.0	20.49	20.51	20.35	20.45	20.49	20.31	20.93	20.98	20.86	20.97	21.04	20.91
2500.0	0.41	0.56	0.70	0.39	0.56	0.69	2500.0	20.25	20.21	20.05	20.20	20.20	20.02	20.65	20.69	20.59	20.74	20.76	20.65
3000.0	0.41	0.58	0.73	0.39	0.58	0.73	3000.0	18.80	18.81	18.64	18.76	18.79	18.62	19.36	19.38	19.24	19.34	19.40	19.28
3500.0	0.43	0.62	0.78	0.40	0.60	0.76	3500.0	17.16	17.15	17.03	17.11	17.14	17.00	17.68	17.71	17.61	17.77	17.79	17.70
4000.0	0.48	0.67	0.84	0.44	0.65	0.82	4000.0	15.68	15.65	15.56	15.58	15.59	15.49	15.93	16.04	15.97	16.10	16.14	16.09
4500.0	0.57	0.75	0.94	0.51	0.73	0.91	4500.0	14.19	14.20	14.16	14.11	14.15	14.10	14.32	14.48	14.44	14.50	14.59	14.57
5000.0	0.70	0.88	1.09	0.63	0.85	1.04	5000.0	13.15	13.20	13.18	13.05	13.13	13.10	13.27	13.34	13.33	13.46	13.49	13.49
5500.0	0.87	1.07	1.30	0.83	1.05	1.27	5500.0	12.58	12.64	12.60	12.46	12.56	12.52	12.62	12.67	12.64	12.84	12.86	12.82
6000.0	1.03	1.26	1.51	1.02	1.28	1.51	6000.0	12.31	12.34	12.36	12.21	12.29	12.30	12.33	12.36	12.39	12.48	12.50	12.53
6500.0	1.15	1.40	1.68	1.10	1.40	1.67	6500.0	12.13	12.18	12.23	12.01	12.12	12.16	12.16	12.23	12.25	12.19	12.23	12.27
7000.0	1.18	1.43	1.74	1.14	1.44	1.72	7000.0	11.78	11.89	11.96	11.64	11.82	11.88	11.89	12.09	12.16	11.82	12.02	12.11
7500.0	1.26	1.48	1.76	1.16	1.42	1.71	7500.0	11.37	11.50	11.62	11.19	11.39	11.49	11.42	11.70	11.89	11.35	11.61	11.80
8000.0	1.33	1.53	1.84	1.22	1.45	1.74	8000.0	10.98	11.05	11.18	10.77	10.93	11.02	11.02	11.16	11.26	10.99	11.12	11.26

**Truth Table** (State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended

ON- low insertion loss state OFF- Isolation State

## Typical Performance Data

RF FREQ (MHz)	RETURN LOSS @ Vctl=+3V OVER TEMPERATURE (dB)											
	RF COM			RF COM			RF1			RF2		
	ON1			ON2			ON1			ON2		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
5.0	5.5	5.6	5.6	5.6	5.6	5.6	5.5	5.6	5.6	5.6	5.6	5.6
7.0	7.8	7.8	7.9	7.8	7.9	7.9	7.8	7.8	7.9	7.8	7.9	7.9
10.0	10.5	10.6	10.6	10.5	10.6	10.6	10.5	10.6	10.6	10.5	10.6	10.6
50.0	23.0	23.3	23.3	23.1	23.3	23.3	23.0	23.3	23.2	23.1	23.3	23.3
100.0	27.1	27.0	26.9	27.2	27.1	27.0	27.2	27.1	26.4	27.4	27.1	26.7
200.0	30.7	28.0	27.5	30.0	28.3	27.4	30.1	28.3	27.3	29.5	28.2	27.3
300.0	29.3	27.2	25.9	29.2	27.7	26.1	30.9	27.7	27.4	28.8	27.5	26.7
400.0	26.6	26.3	24.8	28.1	26.7	25.4	28.1	26.6	26.1	27.8	26.5	25.5
500.0	25.1	25.3	24.0	26.7	25.6	24.7	25.4	25.7	24.3	26.7	25.6	24.3
600.0	24.4	23.8	22.8	25.3	24.4	23.5	24.1	24.2	23.0	25.4	24.5	23.5
700.0	24.6	22.9	22.1	24.4	23.3	22.4	24.7	23.3	22.6	24.7	23.7	23.0
800.0	23.0	21.6	20.9	23.1	22.0	21.1	23.8	22.2	21.5	23.7	22.7	21.9
900.0	20.8	20.4	19.8	21.3	20.7	20.1	21.7	21.1	20.5	22.0	21.6	20.9
1000.0	20.0	19.7	19.3	20.6	20.0	19.5	20.8	20.5	20.0	21.4	21.0	20.4
1100.0	19.5	19.1	18.8	19.9	19.4	19.0	20.2	20.0	19.6	20.7	20.3	20.0
1200.0	18.7	18.6	18.3	19.1	18.8	18.5	19.5	19.5	19.2	19.9	19.7	19.5
1300.0	18.3	18.2	17.9	18.7	18.4	18.1	19.1	19.2	18.9	19.5	19.3	19.1
1400.0	18.2	17.8	17.7	18.2	18.0	17.8	19.0	18.8	18.7	19.0	18.9	18.8
1500.0	18.0	17.5	17.5	17.7	17.6	17.5	19.0	18.5	18.5	18.5	18.6	18.5
1600.0	17.4	17.2	17.1	17.5	17.3	17.3	18.4	18.2	18.3	18.3	18.4	18.4
1700.0	16.7	17.0	17.0	17.2	17.2	17.2	17.6	18.1	18.1	18.1	18.3	18.4
1800.0	16.7	16.9	16.9	17.2	17.1	17.1	17.4	17.9	18.0	18.1	18.3	18.3
1900.0	16.9	16.9	16.9	17.2	17.1	17.1	17.7	18.0	18.2	18.1	18.3	18.4
2000.0	17.0	17.0	17.1	17.2	17.1	17.2	17.9	18.1	18.3	18.1	18.3	18.5
2100.0	17.2	17.1	17.1	17.3	17.2	17.3	18.1	18.2	18.4	18.3	18.5	18.7
2200.0	17.2	17.1	17.2	17.3	17.3	17.3	18.2	18.4	18.6	18.2	18.5	18.8
2300.0	17.4	17.4	17.5	17.4	17.4	17.5	18.5	18.7	19.2	18.5	18.8	19.2
2400.0	17.6	17.8	17.8	17.9	17.9	17.9	18.7	19.3	19.5	19.0	19.4	19.7
2500.0	17.9	18.4	18.2	18.4	18.4	18.3	19.0	19.9	20.0	19.6	20.1	20.5
3000.0	22.0	22.0	21.6	23.1	22.3	21.9	24.6	25.7	25.8	26.3	26.4	26.6
3500.0	30.1	28.5	26.8	28.9	27.4	26.1	34.2	38.5	38.0	31.3	34.3	36.5
4000.0	33.6	33.2	29.8	36.2	33.0	29.6	40.0	37.6	38.6	32.5	34.2	35.1
4500.0	21.9	23.0	22.3	23.6	23.5	22.8	26.6	27.4	27.0	27.2	27.1	27.1
5000.0	16.1	16.6	16.4	16.5	16.6	16.4	18.0	18.9	18.8	17.9	18.4	18.2
5500.0	13.1	13.1	12.9	12.7	12.9	12.7	14.9	15.0	15.0	14.0	14.5	14.4
6000.0	11.6	11.3	11.2	10.9	10.8	10.8	13.5	13.2	13.2	11.9	12.1	12.1
6500.0	10.7	10.4	10.2	10.2	10.1	9.9	12.3	12.2	12.1	11.6	11.6	11.5
7000.0	10.8	10.5	10.4	10.5	10.3	10.4	12.5	12.3	12.3	11.9	11.8	11.9
7500.0	10.8	11.0	11.3	10.9	11.3	11.5	13.0	13.1	13.5	13.0	13.3	13.6
8000.0	11.5	11.9	12.2	11.6	12.3	12.6	13.8	14.1	14.7	13.6	14.6	15.2

**Truth Table** (State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended

ON- low insertion loss state OFF- Isolation State



## Typical Performance Data

RF FREQ (MHz)	INSERTION LOSS @ Vctl=+5V OVER TEMPERATURE						RF FREQ (MHz)	ISOLATION @ Vctl=+5V OVER TEMPERATURE											
	RF COM-RF1 (dB)			RF COM-RF2 (dB)				RF COM-RF1 (dB)			RF COM-RF2 (dB)			RF1-RF2 (dB)			RF1-RF2 (dB)		
														ON1			ON2		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C		-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
5.0	0.32	0.35	0.38	0.25	0.28	0.31	5.0	49.48	49.30	48.97	49.32	49.30	49.08	51.20	51.22	51.12	51.11	51.13	50.82
7.0	0.31	0.35	0.38	0.27	0.30	0.34	7.0	47.71	47.97	48.01	47.65	48.00	48.03	48.85	49.27	49.42	48.86	49.20	49.36
10.0	0.30	0.34	0.38	0.28	0.32	0.36	10.0	46.24	46.73	47.02	46.20	46.69	47.18	47.11	47.60	48.01	47.04	47.65	48.03
50.0	0.30	0.35	0.39	0.30	0.35	0.39	50.0	40.82	41.57	42.17	40.85	41.60	42.25	41.26	42.11	42.82	41.26	42.09	42.76
100.0	0.30	0.35	0.39	0.30	0.35	0.40	100.0	38.48	39.21	39.81	38.52	39.23	39.86	38.93	39.71	40.39	38.88	39.70	40.34
200.0	0.29	0.35	0.40	0.30	0.36	0.40	200.0	36.06	36.64	36.99	36.09	36.65	37.06	36.50	37.12	37.58	36.46	37.10	37.52
300.0	0.29	0.35	0.41	0.30	0.36	0.41	300.0	34.25	34.64	34.80	34.29	34.68	34.90	34.66	35.13	35.41	34.63	35.09	35.31
400.0	0.29	0.36	0.42	0.29	0.36	0.42	400.0	32.65	32.90	32.94	32.67	32.94	33.05	33.07	33.38	33.55	33.05	33.35	33.43
500.0	0.29	0.36	0.43	0.29	0.36	0.43	500.0	31.25	31.40	31.35	31.27	31.44	31.48	31.66	31.86	31.94	31.65	31.84	31.83
600.0	0.30	0.37	0.44	0.29	0.37	0.43	600.0	29.99	30.06	29.96	30.00	30.11	30.09	30.40	30.53	30.56	30.40	30.52	30.47
700.0	0.28	0.37	0.45	0.29	0.37	0.45	700.0	28.85	28.87	28.73	28.87	28.92	28.88	29.25	29.35	29.36	29.26	29.34	29.26
800.0	0.29	0.38	0.45	0.30	0.39	0.45	800.0	27.77	27.80	27.66	27.80	27.86	27.80	28.22	28.31	28.31	28.24	28.30	28.21
900.0	0.32	0.40	0.47	0.31	0.39	0.46	900.0	26.93	26.94	26.79	26.94	26.98	26.93	27.35	27.43	27.41	27.37	27.42	27.31
1000.0	0.30	0.40	0.48	0.30	0.40	0.48	1000.0	26.12	26.12	25.97	26.14	26.17	26.11	26.53	26.60	26.59	26.56	26.59	26.49
1100.0	0.30	0.41	0.49	0.30	0.41	0.49	1100.0	25.38	25.37	25.21	25.40	25.42	25.35	25.78	25.83	25.81	25.81	25.82	25.70
1200.0	0.31	0.42	0.51	0.31	0.42	0.51	1200.0	24.65	24.65	24.49	24.68	24.71	24.64	25.07	25.14	25.12	25.10	25.13	25.01
1300.0	0.31	0.43	0.52	0.32	0.43	0.52	1300.0	24.01	24.02	23.87	24.04	24.09	24.03	24.45	24.53	24.52	24.47	24.51	24.41
1400.0	0.33	0.44	0.53	0.33	0.45	0.53	1400.0	23.46	23.46	23.32	23.49	23.53	23.47	23.92	23.99	23.97	23.94	23.97	23.86
1500.0	0.34	0.45	0.55	0.34	0.46	0.55	1500.0	22.99	22.97	22.81	23.02	23.04	22.97	23.44	23.50	23.47	23.47	23.49	23.36
1600.0	0.35	0.47	0.56	0.35	0.47	0.56	1600.0	22.51	22.49	22.32	22.53	22.55	22.47	22.99	23.04	23.01	23.01	23.03	22.91
1700.0	0.35	0.48	0.58	0.35	0.48	0.58	1700.0	22.03	22.02	21.85	22.05	22.08	22.01	22.50	22.57	22.54	22.52	22.56	22.45
1800.0	0.36	0.49	0.59	0.36	0.49	0.59	1800.0	21.60	21.58	21.42	21.62	21.65	21.58	22.08	22.15	22.12	22.11	22.15	22.03
1900.0	0.36	0.50	0.60	0.37	0.50	0.61	1900.0	21.23	21.21	21.03	21.25	21.27	21.19	21.74	21.78	21.76	21.75	21.77	21.64
2000.0	0.36	0.50	0.61	0.37	0.51	0.62	2000.0	20.85	20.83	20.65	20.88	20.90	20.81	21.38	21.42	21.38	21.39	21.39	21.26
2100.0	0.37	0.51	0.62	0.37	0.52	0.63	2100.0	20.46	20.44	20.26	20.49	20.52	20.43	21.00	21.05	21.01	21.00	21.02	20.90
2200.0	0.37	0.52	0.63	0.38	0.52	0.64	2200.0	20.10	20.08	19.90	20.12	20.15	20.06	20.64	20.70	20.66	20.64	20.67	20.54
2300.0	0.38	0.53	0.64	0.39	0.54	0.65	2300.0	19.75	19.74	19.55	19.79	19.81	19.71	20.31	20.36	20.30	20.32	20.32	20.17
2400.0	0.38	0.54	0.66	0.39	0.54	0.67	2400.0	19.45	19.45	19.25	19.48	19.53	19.42	20.01	20.05	19.99	20.02	20.02	19.86
2500.0	0.39	0.54	0.67	0.40	0.55	0.68	2500.0	19.18	19.17	18.98	19.22	19.25	19.13	19.71	19.77	19.71	19.71	19.73	19.59
3000.0	0.40	0.58	0.72	0.42	0.60	0.74	3000.0	17.67	17.64	17.45	17.71	17.72	17.62	18.26	18.29	18.22	18.25	18.25	18.10
3500.0	0.45	0.64	0.80	0.47	0.66	0.81	3500.0	16.03	16.03	15.89	16.08	16.13	16.09	16.63	16.73	16.75	16.54	16.61	16.53
4000.0	0.53	0.73	0.90	0.54	0.75	0.92	4000.0	14.57	14.64	14.53	14.59	14.71	14.70	15.08	15.25	15.31	15.01	15.10	15.05
4500.0	0.65	0.86	1.04	0.65	0.87	1.05	4500.0	13.30	13.39	13.32	13.36	13.50	13.49	13.85	13.98	13.98	13.78	13.84	13.77
5000.0	0.83	1.06	1.25	0.82	1.05	1.24	5000.0	12.44	12.54	12.47	12.48	12.63	12.65	12.81	12.93	13.00	12.84	12.91	12.85
5500.0	1.02	1.29	1.50	1.01	1.28	1.50	5500.0	11.96	12.09	12.02	12.01	12.18	12.20	12.38	12.49	12.52	12.37	12.46	12.45
6000.0	1.19	1.49	1.72	1.18	1.48	1.72	6000.0	11.61	11.74	11.68	11.66	11.83	11.85	12.14	12.30	12.34	12.14	12.29	12.29
6500.0	1.29	1.58	1.82	1.24	1.55	1.82	6500.0	11.27	11.41	11.37	11.31	11.49	11.54	11.82	12.04	12.16	11.85	12.04	12.11
7000.0	1.37	1.69	1.94	1.31	1.64	1.91	7000.0	10.80	10.98	11.00	10.85	11.07	11.16	11.44	11.74	11.89	11.59	11.85	11.92
7500.0	1.42	1.75	2.02	1.40	1.75	2.04	7500.0	10.26	10.53	10.62	10.32	10.61	10.78	11.00	11.19	11.36	11.28	11.40	11.47
8000.0	1.48	1.81	2.11	1.56	1.88	2.19	8000.0	10.07	10.32	10.48	10.15	10.43	10.66	10.68	10.93	11.15	10.94	11.16	11.28

**Truth Table** (State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended

ON- low insertion loss state OFF- Isolation State

## Typical Performance Data

RF FREQ (MHz)	RETURN LOSS @ Vctl=+5V OVER TEMPERATURE (dB)											
	RF COM			RF COM			RF1			RF2		
	ON1			ON2			ON1			ON2		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
5.0	5.5	5.5	5.5	5.6	5.7	5.7	5.5	5.5	5.5	5.7	5.7	5.7
7.0	7.7	7.8	7.8	7.9	8.0	8.0	7.7	7.8	7.8	7.9	8.0	8.0
10.0	10.4	10.5	10.5	10.6	10.7	10.7	10.4	10.5	10.5	10.7	10.7	10.8
50.0	23.3	23.5	23.6	23.6	23.8	23.8	23.4	23.6	23.5	23.7	23.8	23.8
100.0	27.8	27.8	27.6	28.2	28.2	27.9	28.2	27.8	27.2	28.6	28.2	27.5
200.0	31.5	29.7	28.4	32.1	30.1	28.7	32.0	30.0	28.5	32.6	30.5	29.1
300.0	32.0	29.6	27.8	33.0	30.1	27.9	32.1	30.3	28.9	33.0	31.1	29.6
400.0	30.8	29.2	27.8	31.6	29.8	28.1	32.0	30.0	28.3	33.3	31.0	29.2
500.0	30.6	29.1	27.9	30.9	29.2	27.9	31.5	29.2	27.3	32.9	30.4	28.3
600.0	29.5	28.0	26.7	30.3	28.4	26.8	29.4	27.9	26.5	31.3	29.5	27.9
700.0	29.4	27.8	26.4	29.7	27.8	26.1	28.6	27.2	26.0	30.2	28.5	27.1
800.0	28.0	26.3	25.1	27.8	26.0	24.7	27.4	25.7	24.5	28.4	26.4	25.1
900.0	25.5	24.6	23.8	25.7	24.5	23.6	25.4	24.4	23.5	26.0	24.9	23.9
1000.0	24.9	24.3	23.6	24.9	24.2	23.4	24.8	24.1	23.5	25.2	24.5	23.7
1100.0	24.5	23.8	23.3	24.4	23.7	23.1	24.6	23.7	23.1	24.8	23.9	23.3
1200.0	23.9	23.0	22.4	23.8	22.9	22.1	24.2	23.3	22.6	24.3	23.5	22.8
1300.0	22.8	22.2	21.8	22.7	22.1	21.5	23.3	22.8	22.3	23.3	22.9	22.4
1400.0	21.7	21.5	21.3	21.6	21.3	21.1	22.5	22.2	21.9	22.5	22.2	21.9
1500.0	21.2	21.0	20.7	20.9	20.7	20.5	22.1	21.8	21.5	21.9	21.7	21.5
1600.0	21.0	20.7	20.5	20.8	20.5	20.2	22.1	21.7	21.4	21.6	21.5	21.4
1700.0	20.6	20.4	20.3	20.4	20.1	19.9	21.7	21.5	21.3	21.2	21.1	21.0
1800.0	19.9	20.0	20.1	19.6	19.6	19.5	20.9	21.0	21.0	20.4	20.5	20.5
1900.0	19.6	19.8	19.9	19.2	19.3	19.3	20.6	20.7	20.9	20.0	20.1	20.2
2000.0	19.8	19.8	19.9	19.3	19.3	19.4	20.8	20.8	20.9	20.1	20.1	20.3
2100.0	19.9	19.9	19.9	19.5	19.4	19.4	20.9	20.9	21.0	20.2	20.2	20.4
2200.0	19.8	20.0	20.1	19.6	19.7	19.7	20.7	21.0	21.2	20.2	20.4	20.6
2300.0	19.6	19.9	20.2	19.4	19.6	19.8	20.6	20.9	21.2	20.2	20.4	20.7
2400.0	19.9	20.0	20.1	19.6	19.7	19.7	20.9	21.0	21.2	20.4	20.5	20.7
2500.0	20.3	20.3	20.3	20.0	20.0	20.0	21.4	21.5	21.7	20.8	21.0	21.2
3000.0	23.0	22.8	22.6	21.8	21.6	21.3	26.2	25.8	25.5	23.9	23.7	23.4
3500.0	23.7	23.9	23.2	22.6	22.5	21.8	27.8	27.7	27.2	25.9	25.3	24.5
4000.0	20.7	20.7	20.4	20.4	20.3	19.9	24.2	24.4	23.9	24.5	24.2	23.6
4500.0	16.0	16.2	16.2	16.2	16.5	16.5	18.1	18.5	18.4	18.9	19.3	19.3
5000.0	12.6	12.7	12.5	13.0	13.1	12.9	14.1	14.2	14.2	14.6	14.9	15.0
5500.0	10.5	10.5	10.4	10.7	10.7	10.6	11.9	11.9	11.9	12.1	12.3	12.3
6000.0	9.3	9.3	9.4	9.5	9.5	9.5	10.6	10.6	10.7	10.9	11.0	11.1
6500.0	9.1	9.3	9.4	9.4	9.6	9.5	10.4	10.7	10.9	10.9	11.2	11.3
7000.0	9.0	9.3	9.5	9.4	9.6	9.7	10.5	10.8	11.1	11.0	11.2	11.4
7500.0	9.4	9.6	9.8	9.5	9.6	9.7	10.9	11.3	11.6	11.0	11.3	11.6
8000.0	9.5	9.6	9.6	9.1	9.3	9.3	11.3	11.6	11.8	10.5	10.9	11.2

**Truth Table** (State of control voltage selects the desired switch state)







State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended

ON- low insertion loss state OFF- Isolation State

## Typical Performance Data

RF FREQ (MHz)	INPUT IP3	
	Vctl=+3V (dBm)	Vctl =+5V (dBm)
	RF COM-RF1	RF COM-RF1
100.0	59.54	60.57
300.0	57.79	58.53
500.0	56.49	57.90
700.0	57.57	60.31
900.0	56.93	62.42
1000.0	59.52	59.07
1200.0	58.70	59.40
1400.0	57.70	58.88
1600.0	55.80	56.80
1800.0	55.24	57.85
2000.0	56.81	58.06
2250.0	59.39	59.21
2500.0	55.98	58.40
2750.0	58.24	57.03
3000.0	54.39	57.43
3250.0	54.20	56.44
3500.0	53.27	54.28
3750.0	53.06	54.66
4000.0	55.09	55.02

## Typical Performance Curves




**Truth Table** (State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended


ON- low insertion loss state OFF- Isolation State

## Typical Performance Curves


Insertion Loss @ Vctl=+3V over Temperature  
RF COM-RF1 & RF COM-RF2




Isolation @ Vctl=+3V over Temperature  
RF COM-RF1 & RF COM-RF2




Isolation @ Vctl=+3V over Temperature,  
RF1-RF2



Return Loss @ Vctl=+3V over Temperature  
RF COM



Return Loss @ Vctl=+3V over Temperature  
RF1(ON1) & RF2 (ON2)




Truth Table (State of control voltage selects the desired switch state)

State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended


ON- low insertion loss state OFF- Isolation State

## Typical Performance Curves


Insertion Loss @ Vctl=+5V over Temperature  
RF COM-RF1 & RF COM-RF2




Isolation @ Vctl=+5V over Temperature  
RF COM-RF1 & RF COM-RF2




Isolation @ Vctl=+5V over Temperature,  
RF1-RF2



Return Loss @ Vctl=+5V over Temperature  
RF COM



Return Loss @ Vctl=+5V over Temperature  
RF1(ON1) & RF2 (ON2)




Truth Table (State of control voltage selects the desired switch state)


State of Control Voltage		RF Common to	
V <sub>CTL1</sub>	V <sub>CTL2</sub>	RF1	RF2
Low	High	OFF	ON
High	Low	ON	OFF
Low	Low	Not recommended	Not recommended
High	High	Not recommended	Not recommended

ON- low insertion loss state OFF- Isolation State

### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
JZ1436	.118 (3.00)	.079 (2.00)	.035 (.89)	.048 (1.22)	.024 (.61)	.033 (.84)	.024 (.61)	.015 (.38)	.013 (.33)	.037 (.94)	.104 (2.64)	.144 (3.66)	.048 (1.22)

CASE#	P	Q	R	S	T	WT, GRAM
JZ1436	.014 (.36)	.024 (.61)	.033 (.84)	.009 (.23)	.005 (.125)	.015

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Matte Tin plate.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F93



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel See note
12	4	7	20
			50
			100
			200
			500
		1000	
		13	3000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified




THIRD ANGLE PROJECTION



REVISIONS

REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M125849	NEW RELEASE	01/05/10	MMG	RD


SUGGESTED MOUNTING CONFIGURATION FOR JZ1436 CASE STYLE, "06SW01" PIN CODE



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" ± .001"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	MMG 12/23/09
	CHECKED	AV 01/04/10
	APPROVED	RD 01/05/10



Mini-Circuits®



13 Neptune Avenue  
Brooklyn NY 11235

PL, 06SW01, JZ1436, TB-530+

Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-324	OR
FILE:	98PL324	SCALE:	10:1
		SHEET:	1 OF 1

# Evaluation Board and Circuit




COMPONENT	VALUE/PART NUMBER
DUT	Mini-Circuits VSW2-33-10W+
C1 - C5	0.001 uF

Schematic Diagram

## Notes:

- 50 Ohm SMA Female connectors.
- PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.010 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Temperature Cycling	-65° to 150°C, 500 cycles	JESD22-A104, condition C
Autoclave	121°C, 100% RH, 30 PSIA, 96 hours, unbiased	JESD22-A102
High Temp Storage	150°C 1008 hours	JESD22-A103
Solderability	Per Reference Spec	JESD22-B102
Resistance to Solvent	Per Reference Spec	MIL-STD-202, Method 215J
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	JESD22-A113