

SPDT RF Switch

50Ω 500-6000 MHz

Absorptive RF Switch with internal driver.
Single Supply Voltage, +3V to +5V

Product Features

- High Isolation, 65 dB typ. at 1 GHz
- Low insertion loss, 1.0 dB typ. at 1 GHz
- High IP3, 50 dBm typ. at 1 GHz
- Fast switching, Rise/fall time, 23 ns typ.
- Low current consumption, 12 μA typ.

Typical Applications

- Automated switching networks
- Cellular/ PCS
- ISM, WCDMA, WiMAX, LTE



VSWA2-63DR+

CASE STYLE: DG1235-1


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

General Description

VSWA2-63DR+ is a high isolation absorptive SPDT switch with integral CMOS driver, operates with single positive supply voltage while consuming, 12μA typical. It has been designed for very wideband operation of 500-6000 MHz for 50Ω systems and yet is usable in 75Ω systems with degraded return loss. This switch is usable over an extended frequencies from 300 kHz to 500 MHz with reflective switch performance. It is packaged in a tiny 4mm x 4mm x 0.9mm package and is rated MSL1 and class 1A ESD.

Simplified Schematic and Pad Description



| Function | Pad Number | Description |
|----------|--|--|
| RF COM | 3 | RF Common/ SUM Port, requires DC block (see Fig. 2) |
| RF1 | 12 | RF Out #1/In Port #1, requires DC block (see Fig. 2) |
| RF2 | 9 | RF Out #1/In Port #2, requires DC block (see Fig. 2) |
| Control | 2 | CMOS Control IN |
| VDD | 1 | Supply Voltage |
| GND | 4,5,6,7,8,10,11 13,14,15,16, paddle | RF Ground |

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



RF Electrical Specifications⁽¹⁾, 500 - 6000 MHz, T_{AMB}=25°C, V_{DD}= +3V to +5V

| Parameter | Condition (MHz) | Min. | Typ. | Max. | Units |
|---|-----------------------------|--------------|------|------|-------|
| Frequency Range | | 500 | | 6000 | MHz |
| Insertion Loss ⁽²⁾ | 0.3 to 500 | | 0.7 | | dB |
| | 500 to 2000 | | 0.7 | 1.3 | |
| | 2000 to 3000 | | 0.8 | 1.5 | |
| | 3000 to 4000 | | 0.9 | 1.5 | |
| | 4000 to 6000 | | 1.0 | 1.9 | |
| Isolation between Common port and RF1/RF2 Ports | 0.3 to 500 | — | 73 | | dB |
| | 500 to 2000 | 56 | 66 | | |
| | 2000 to 3000 | 50 | 64 | | |
| | 3000 to 4000 | 45 | 58 | | |
| | 4000 to 6000 | 38 | 54 | | |
| Isolation between RF1 and RF2 ports | 0.3 to 500 | | 74 | | dB |
| | 500 to 1000 | 50 | 60 | | |
| | 1000 to 2000 | 45 | 56 | | |
| | 2000 to 3000 | 40 | 52 | | |
| | 3000 to 4000 | 38 | 50 | | |
| Return Loss (ON STATE) | 0.3 to 500 | | 24 | | dB |
| | 500 to 2000 | | 23 | | |
| | 2000 to 3000 | | 23 | | |
| | 3000 to 4000 | | 22 | | |
| | 4000 to 6000 | | 20 | | |
| Return Loss @ RF1/RF2 ports (OFF STATE) | 500 to 2000 | | 23 | | dB |
| | 2000 to 3000 | | 33 | | |
| | 3000 to 4000 | | 23 | | |
| | 4000 to 6000 | | 24 | | |
| Input IP3 | V _{DD} =3V | 500 to 2000 | | 46 | dBm |
| | | 2000 to 6000 | | 40 | |
| | V _{DD} =5V | 500 to 2000 | | 50 | |
| | | 2000 to 6000 | | 44 | |
| Input Compression ⁽³⁾ | 1dB, V _{DD} =3V | 500 to 2000 | | 24 | dBm |
| | | 2000 to 6000 | | 22 | |
| | 0.2 dB, V _{DD} =5V | 500 to 2000 | | 30 | |
| | | 2000 to 6000 | | 27 | |

DC Electrical Specifications

| Parameter | Min. | Typ. | Max. | Units |
|--|--------------------|------|-----------------|-------|
| VDD, Supply Voltage | 3 | | 5 | V |
| Supply Current (V _{DD} = 5V) ⁽⁴⁾ | | 50 | | μA |
| Control Voltage Low | 0 | | 0.5 | V |
| Control Voltage High ⁽⁵⁾ | 2.7 ⁽⁶⁾ | | V _{DD} | V |
| Control Current | | 5 | | μA |

Notes:

- Tested on Mini-Circuit's test board TB-407+, using Agilent's N5230A network analyzer (see Characterization Test Circuit, Fig.1).
- Insertion loss values are deembedded from test board loss.
- Do not exceed RF input power as shown in Absolute Maximum Rating table.
- Supply current increases with switching repetition rate. See graph.
- CMOS interface. Latch up condition may occur when logic high signal is applied prior to power supply.
- 3.5V for V_{DD}=4 to 5V

Switching Specifications

| Parameter | Min. | Typ. | Max. | Units |
|--|------|------|------|-------------------|
| Rise/Fall Time (10 to 90% or 90 to 10% RF) | | 23 | | nSec |
| Switching Time, 50% CTRL to 90/10% RF | | 35 | | nSec |
| Video Feedthrough, (control 0 to 3V, freq.=500 KHz, V _{DD} =5V) | | 25 | | mV _{P-P} |

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Absolute Maximum Ratings⁽⁶⁾

| Parameter | Ratings |
|----------------------------------|---------------------------------|
| Operating Temperature | -40°C to +85°C |
| Storage Temperature | -65°C to 150°C |
| V _{DD} , Supply Voltage | 2.7 to 5.5V |
| Voltage Control | -0.2V Min. V _{DD} Max. |
| RF input power | 1Watt |
| Dissipated Power at 25°C | 350mW |

6. Operation of this device above any of these conditions may cause permanent damage.

Truth Table (State of control voltage selects the desired switch state)

| State of Control Voltage | RF Common to | |
|--------------------------|--------------|-----|
| | RF1 | RF2 |
| Low | ON | OFF |
| High | OFF | ON |

ON- low insertion loss state OFF- Isolation State

Characterization Test Circuit




Figure 1: Block Diagram Of Test Circuit Used For Characterization. (DUT soldered on Mini-Circuit's TB-407+)

Test Equipment:

For Insertion loss, Isolation, Return loss and DC current:

Agilent's N5230A Network Analyzer , E3631A power supply. Cblock: Internal to network Analyzer.

For Switching Time and DC Current:

Agilent's 54832B oscilloscope, 81110A pulse generator and E3631 A power supply. Cblock: Mini-Circuits BLK-18-S+

For Input IP3:

Mini-Circuits DC blocks: BLK-18-S+ on all ports, Agilent's E8257D signal generators, 437B power meter, N9020A Signal analyzer and E3631 A power supply.

For Compression:

Mini-Circuits DC blocks: BLK-18-S+ on all ports. ZVE-8G and ZHL-42W amplifier as driver amplifier at RF Common. Agilent's N5230A Network Analyzer, E3631A power supply

Conditions:

V_{DD} = +3 and +5V, Control= 0 and 3V.

For Insertion loss, isolation and return loss: Pin=0 dBm

For Input IP3: Pin=-5dBm/tone.

For Switching time: RF frequency: 500 MHz at 0 dBm, Control Frequency: 500 KHz and 0 and +3V.

Notes


A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Product Marking



Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

Performance data, graphs

Case Style: DG1235-1

Plastic, finish: Nickel Palladium Gold

Tape & Reel: F87

Standard quantities available on reel: 7" reels with 20, 50, 100, 200, 500 devices
13" reels with 3K devices

Suggested Layout for PCB Design: PL-278

Evaluation Board: TB-486+

Environmental Ratings: ENV41

Recommended Application Circuit




Fig. 2: Evaluation board includes case, connectors and components soldered to PCB.

| Frequency (MHz) | Cblock (Suggested value) |
|-----------------|--------------------------|
| 0.3-500 | 0.1µF |
| 500-6000 | 47pF |

Cblock should be free of resonance over frequency of operation.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



ESD Rating


Human Body Model (HBM): Class 1A (250 to < 500V) in accordance with JESD22-A114

Machine Model (MM): Class A (Passes 50V) in accordance with JESD22-A115

MSL Rating

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL Test Flow Chart



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



RF Switch SPDT

VSWA2-63DR+

Typical Performance Data

| RF FREQ (MHz) | INSERTION LOSS | | | | RF FREQ (MHz) | ISOLATION | | | | | | | |
|------------------|-----------------|------------|-----------------|------------|------------------|-----------------|------------|-----------------|------------|-----------------------|------------------------|-----------------------|------------------------|
| | VDD=+3V (dB) | | VDD=+5V (dB) | | | VDD=+3V (dB) | | VDD=+5V (dB) | | VDD=+3V (dB) | | VDD=+5V (dB) | |
| | RF COM-RF1 | RF COM-RF2 | RF COM-RF1 | RF COM-RF2 | | RF COM-RF1 | RF COM-RF2 | RF COM-RF1 | RF COM-RF2 | RF1-RF2 State LOW* | RF1-RF2 State HIGH* | RF1-RF2 State LOW* | RF1-RF2 State HIGH* |
| 0.3 | 0.87 | 0.88 | 0.86 | 0.86 | 0.3 | 88.66 | 99.00 | 89.65 | 89.93 | 103.84 | 93.40 | 87.91 | 92.90 |
| 0.5 | 0.90 | 0.90 | 0.90 | 0.89 | 0.5 | 96.22 | 97.27 | 93.19 | 92.84 | 94.19 | 89.91 | 92.70 | 86.59 |
| 1.0 | 0.90 | 0.89 | 0.91 | 0.89 | 1.0 | 108.36 | 100.23 | 98.89 | 101.81 | 101.08 | 110.13 | 95.93 | 106.23 |
| 5.0 | 0.89 | 0.86 | 0.91 | 0.86 | 5.0 | 86.99 | 79.30 | 90.21 | 81.62 | 80.92 | 87.16 | 83.46 | 88.15 |
| 10.0 | 0.88 | 0.83 | 0.90 | 0.84 | 10.0 | 82.21 | 73.18 | 84.33 | 74.69 | 74.47 | 82.88 | 75.65 | 85.82 |
| 50.0 | 0.91 | 0.83 | 0.92 | 0.84 | 50.0 | 74.88 | 60.17 | 75.61 | 61.25 | 61.49 | 74.64 | 62.50 | 75.83 |
| 100.0 | 0.91 | 0.83 | 0.93 | 0.85 | 100.0 | 70.60 | 58.46 | 71.24 | 58.97 | 59.93 | 69.51 | 60.39 | 70.28 |
| 200.0 | 0.92 | 0.84 | 0.94 | 0.86 | 200.0 | 69.14 | 59.86 | 69.61 | 60.18 | 61.63 | 66.17 | 61.75 | 66.61 |
| 300.0 | 0.93 | 0.85 | 0.94 | 0.87 | 300.0 | 68.79 | 61.18 | 69.09 | 61.47 | 62.09 | 63.81 | 62.14 | 64.38 |
| 400.0 | 0.93 | 0.86 | 0.95 | 0.88 | 400.0 | 68.93 | 61.94 | 69.07 | 62.21 | 61.21 | 62.00 | 61.20 | 62.48 |
| 500.0 | 0.94 | 0.87 | 0.96 | 0.89 | 500.0 | 69.44 | 62.60 | 69.48 | 62.81 | 59.82 | 60.36 | 59.89 | 60.85 |
| 600.0 | 0.95 | 0.88 | 0.97 | 0.91 | 600.0 | 69.16 | 62.64 | 69.18 | 62.84 | 58.35 | 58.85 | 58.40 | 59.34 |
| 700.0 | 0.96 | 0.89 | 0.98 | 0.92 | 700.0 | 69.23 | 62.78 | 69.06 | 62.91 | 57.16 | 57.70 | 57.24 | 58.12 |
| 800.0 | 0.96 | 0.90 | 0.98 | 0.92 | 800.0 | 69.67 | 62.66 | 69.06 | 62.76 | 56.08 | 56.66 | 56.15 | 57.07 |
| 900.0 | 0.96 | 0.90 | 0.97 | 0.91 | 900.0 | 70.09 | 62.68 | 69.45 | 62.77 | 55.08 | 55.67 | 55.16 | 56.05 |
| 1000.0 | 0.97 | 0.91 | 0.98 | 0.92 | 1000.0 | 70.44 | 62.61 | 69.72 | 62.69 | 54.22 | 54.80 | 54.29 | 55.21 |
| 1200.0 | 0.99 | 0.94 | 1.01 | 0.96 | 1200.0 | 71.00 | 62.29 | 69.15 | 62.03 | 52.79 | 53.28 | 52.85 | 53.71 |
| 1500.0 | 1.03 | 0.99 | 1.05 | 1.02 | 1500.0 | 73.24 | 62.11 | 70.68 | 61.73 | 50.86 | 51.27 | 51.00 | 51.59 |
| 1700.0 | 1.05 | 1.00 | 1.07 | 1.03 | 1700.0 | 78.96 | 62.42 | 73.04 | 61.84 | 49.74 | 50.06 | 49.83 | 50.38 |
| 2000.0 | 1.09 | 1.04 | 1.13 | 1.08 | 2000.0 | 74.87 | 64.61 | 79.90 | 64.20 | 48.13 | 48.67 | 48.15 | 48.72 |
| 2200.0 | 1.13 | 1.07 | 1.16 | 1.10 | 2200.0 | 70.18 | 64.16 | 69.96 | 63.52 | 47.40 | 47.86 | 47.46 | 48.01 |
| 2500.0 | 1.16 | 1.10 | 1.20 | 1.14 | 2500.0 | 64.32 | 60.98 | 63.58 | 60.17 | 46.47 | 46.77 | 46.54 | 46.90 |
| 2700.0 | 1.18 | 1.12 | 1.22 | 1.17 | 2700.0 | 61.66 | 58.96 | 61.22 | 58.56 | 45.85 | 45.98 | 45.84 | 46.07 |
| 3000.0 | 1.22 | 1.16 | 1.28 | 1.21 | 3000.0 | 61.35 | 57.26 | 62.47 | 56.94 | 44.76 | 44.60 | 44.70 | 44.45 |
| 3200.0 | 1.21 | 1.14 | 1.25 | 1.18 | 3200.0 | 58.20 | 55.31 | 57.60 | 55.00 | 44.21 | 44.21 | 44.21 | 44.12 |
| 3500.0 | 1.21 | 1.14 | 1.25 | 1.19 | 3500.0 | 56.58 | 53.41 | 56.54 | 52.90 | 43.31 | 43.24 | 43.28 | 43.09 |
| 3700.0 | 1.21 | 1.14 | 1.25 | 1.18 | 3700.0 | 54.63 | 52.04 | 53.88 | 51.48 | 42.83 | 42.71 | 42.79 | 42.56 |
| 4000.0 | 1.25 | 1.16 | 1.30 | 1.21 | 4000.0 | 52.54 | 50.50 | 51.81 | 50.15 | 42.07 | 41.90 | 41.96 | 41.66 |
| 4200.0 | 1.26 | 1.17 | 1.31 | 1.22 | 4200.0 | 50.91 | 49.70 | 50.22 | 49.14 | 41.79 | 41.38 | 41.70 | 41.11 |
| 4500.0 | 1.33 | 1.24 | 1.37 | 1.27 | 4500.0 | 50.59 | 48.83 | 49.74 | 48.14 | 41.31 | 40.61 | 41.15 | 40.25 |
| 4700.0 | 1.35 | 1.25 | 1.38 | 1.28 | 4700.0 | 49.47 | 48.11 | 48.91 | 47.37 | 41.17 | 40.24 | 40.93 | 39.89 |
| 5000.0 | 1.43 | 1.33 | 1.43 | 1.33 | 5000.0 | 49.00 | 46.66 | 47.58 | 46.01 | 40.83 | 39.64 | 40.52 | 39.21 |
| 5200.0 | 1.47 | 1.36 | 1.46 | 1.36 | 5200.0 | 49.58 | 45.75 | 48.16 | 45.32 | 40.59 | 39.47 | 40.29 | 38.96 |
| 5500.0 | 1.45 | 1.37 | 1.43 | 1.35 | 5500.0 | 50.57 | 44.72 | 48.55 | 44.04 | 40.05 | 39.43 | 39.79 | 38.81 |
| 5700.0 | 1.45 | 1.38 | 1.41 | 1.35 | 5700.0 | 50.68 | 44.07 | 48.40 | 43.28 | 39.59 | 39.35 | 39.34 | 38.70 |
| 6000.0 | 1.44 | 1.40 | 1.39 | 1.36 | 6000.0 | 51.38 | 44.33 | 48.09 | 43.04 | 38.96 | 39.22 | 38.72 | 38.55 |

***Note**

| State of Control Voltage | RF Common to | |
|--------------------------|--------------|-----|
| | RF1 | RF2 |
| LOW | ON | OFF |
| HIGH | OFF | ON |

ON - Low insertion loss state
OFF - Isolation state



RF Switch SPDT

VSWA2-63DR+

Typical Performance Data

| RF FREQ (MHz) | VSWR (:1) | | | | | | | | RF FREQ (MHz) | VSWR (:1) | | | |
|------------------|----------------------|-----------------------|-------------------|--------------------|----------------------|-----------------------|-------------------|--------------------|------------------|--------------------|-------------------|--------------------|-------------------|
| | VDD=+3V | | | | VDD=+5V | | | | | VDD=+3V | | VDD=+5V | |
| | RF COM State LOW* | RF COM State HIGH* | RF1 State LOW* | RF2 State HIGH* | RF COM State LOW* | RF COM State HIGH* | RF1 State LOW* | RF2 State HIGH* | | RF1 State HIGH* | RF2 State LOW* | RF1 State HIGH* | RF2 State LOW* |
| 0.3 | 1.20 | 1.20 | 1.20 | 1.20 | 1.21 | 1.21 | 1.21 | 1.21 | 500.0 | 1.84 | 1.87 | 1.86 | 1.89 |
| 0.5 | 1.20 | 1.20 | 1.20 | 1.20 | 1.21 | 1.21 | 1.21 | 1.21 | 600.0 | 1.80 | 1.83 | 1.82 | 1.85 |
| 1.0 | 1.20 | 1.20 | 1.20 | 1.20 | 1.20 | 1.20 | 1.20 | 1.20 | 700.0 | 1.78 | 1.80 | 1.80 | 1.83 |
| 5.0 | 1.19 | 1.18 | 1.19 | 1.18 | 1.19 | 1.18 | 1.19 | 1.18 | 800.0 | 1.77 | 1.80 | 1.79 | 1.82 |
| 10.0 | 1.17 | 1.18 | 1.17 | 1.18 | 1.18 | 1.18 | 1.18 | 1.18 | 900.0 | 1.77 | 1.79 | 1.79 | 1.82 |
| 50.0 | 1.16 | 1.18 | 1.16 | 1.18 | 1.16 | 1.18 | 1.16 | 1.18 | 1000.0 | 1.77 | 1.80 | 1.79 | 1.83 |
| 100.0 | 1.16 | 1.18 | 1.16 | 1.18 | 1.16 | 1.19 | 1.16 | 1.19 | 1200.0 | 1.78 | 1.80 | 1.80 | 1.83 |
| 200.0 | 1.16 | 1.19 | 1.16 | 1.18 | 1.17 | 1.19 | 1.17 | 1.19 | 1500.0 | 1.80 | 1.83 | 1.83 | 1.86 |
| 300.0 | 1.16 | 1.19 | 1.16 | 1.18 | 1.17 | 1.19 | 1.16 | 1.19 | 1700.0 | 1.82 | 1.85 | 1.85 | 1.89 |
| 400.0 | 1.17 | 1.19 | 1.16 | 1.18 | 1.18 | 1.20 | 1.16 | 1.19 | 2000.0 | 1.84 | 1.88 | 1.87 | 1.92 |
| 500.0 | 1.17 | 1.20 | 1.16 | 1.18 | 1.18 | 1.20 | 1.16 | 1.19 | 2200.0 | 1.85 | 1.89 | 1.89 | 1.93 |
| 600.0 | 1.18 | 1.20 | 1.16 | 1.18 | 1.19 | 1.21 | 1.16 | 1.18 | 2500.0 | 1.86 | 1.89 | 1.90 | 1.93 |
| 700.0 | 1.19 | 1.21 | 1.15 | 1.18 | 1.19 | 1.21 | 1.16 | 1.18 | 2700.0 | 1.85 | 1.88 | 1.89 | 1.92 |
| 800.0 | 1.19 | 1.21 | 1.15 | 1.17 | 1.19 | 1.21 | 1.16 | 1.18 | 3000.0 | 1.82 | 1.84 | 1.86 | 1.89 |
| 900.0 | 1.19 | 1.21 | 1.15 | 1.17 | 1.19 | 1.21 | 1.15 | 1.17 | 3200.0 | 1.78 | 1.80 | 1.83 | 1.85 |
| 1000.0 | 1.19 | 1.21 | 1.15 | 1.17 | 1.20 | 1.22 | 1.15 | 1.17 | 3500.0 | 1.71 | 1.73 | 1.75 | 1.78 |
| 1200.0 | 1.19 | 1.21 | 1.14 | 1.16 | 1.19 | 1.21 | 1.15 | 1.16 | 3700.0 | 1.65 | 1.67 | 1.70 | 1.72 |
| 1500.0 | 1.19 | 1.21 | 1.16 | 1.17 | 1.20 | 1.21 | 1.17 | 1.18 | 4000.0 | 1.56 | 1.58 | 1.61 | 1.63 |
| 1700.0 | 1.21 | 1.21 | 1.20 | 1.21 | 1.22 | 1.22 | 1.21 | 1.22 | 4200.0 | 1.50 | 1.51 | 1.54 | 1.56 |
| 2000.0 | 1.25 | 1.25 | 1.28 | 1.29 | 1.28 | 1.27 | 1.30 | 1.31 | 4500.0 | 1.41 | 1.41 | 1.45 | 1.46 |
| 2200.0 | 1.30 | 1.30 | 1.36 | 1.36 | 1.32 | 1.32 | 1.38 | 1.39 | 4700.0 | 1.35 | 1.35 | 1.39 | 1.40 |
| 2500.0 | 1.36 | 1.36 | 1.46 | 1.47 | 1.39 | 1.38 | 1.49 | 1.50 | 5000.0 | 1.26 | 1.27 | 1.30 | 1.32 |
| 2700.0 | 1.40 | 1.39 | 1.52 | 1.52 | 1.43 | 1.42 | 1.55 | 1.56 | 5200.0 | 1.22 | 1.24 | 1.25 | 1.28 |
| 3000.0 | 1.42 | 1.41 | 1.55 | 1.55 | 1.47 | 1.45 | 1.59 | 1.59 | 5500.0 | 1.16 | 1.19 | 1.20 | 1.24 |
| 3200.0 | 1.40 | 1.38 | 1.55 | 1.54 | 1.44 | 1.42 | 1.59 | 1.59 | 5700.0 | 1.13 | 1.17 | 1.17 | 1.22 |
| 3500.0 | 1.36 | 1.35 | 1.49 | 1.49 | 1.41 | 1.39 | 1.53 | 1.54 | 6000.0 | 1.10 | 1.17 | 1.14 | 1.22 |
| 3700.0 | 1.33 | 1.32 | 1.43 | 1.43 | 1.38 | 1.36 | 1.48 | 1.48 | | | | | |
| 4000.0 | 1.34 | 1.33 | 1.37 | 1.35 | 1.38 | 1.36 | 1.41 | 1.40 | | | | | |
| 4200.0 | 1.37 | 1.36 | 1.35 | 1.32 | 1.40 | 1.38 | 1.39 | 1.36 | | | | | |
| 4500.0 | 1.44 | 1.43 | 1.35 | 1.30 | 1.45 | 1.43 | 1.37 | 1.32 | | | | | |
| 4700.0 | 1.48 | 1.47 | 1.36 | 1.31 | 1.50 | 1.47 | 1.38 | 1.32 | | | | | |
| 5000.0 | 1.50 | 1.48 | 1.39 | 1.32 | 1.50 | 1.47 | 1.39 | 1.32 | | | | | |
| 5200.0 | 1.52 | 1.49 | 1.40 | 1.32 | 1.52 | 1.48 | 1.40 | 1.32 | | | | | |
| 5500.0 | 1.53 | 1.51 | 1.39 | 1.32 | 1.52 | 1.49 | 1.39 | 1.31 | | | | | |
| 5700.0 | 1.52 | 1.50 | 1.37 | 1.29 | 1.50 | 1.48 | 1.36 | 1.29 | | | | | |
| 6000.0 | 1.48 | 1.48 | 1.32 | 1.27 | 1.44 | 1.44 | 1.31 | 1.27 | | | | | |

***Note**

| State of Control Voltage | RF Common to | |
|--------------------------|--------------|-----|
| | RF1 | RF2 |
| LOW | ON | OFF |
| HIGH | OFF | ON |

ON - Low insertion loss state
OFF - Isolation state

RF Switch SPDT

VSWA2-63DR+

Typical Performance Data

| RF FREQ (MHz) | INPUT IP3 | | | | DC Current vs Repetition Rate | | | RF FREQ (MHz) | INPUT 1dB COMPRESSION | |
|------------------|------------------|------------|-------------------|------------|-------------------------------|---------|---------|------------------|--------------------------|-------------------|
| | VDD=+3V (dBm) | | VDD =+5V (dBm) | | IDD (micro A) | | | | VDD=+3V (dBm) | VDD =+5V (dBm) |
| | RF COM-RF1 | RF COM-RF2 | RF COM-RF1 | RF COM-RF2 | Typ. | | | | Pin | Pin |
| | | | | | Rep Rate (MHz) | VDD=+3V | VDD=+5V | | | |
| 500.0 | 48.68 | 48.14 | 52.14 | 51.26 | 0.0005 | 0.8 | 6.4 | 500.0 | 24.52 | 30.90 |
| 700.0 | 47.74 | 47.96 | 50.23 | 50.23 | 1.0 | 62.5 | 93.8 | 600.0 | 23.99 | 30.51 |
| 900.0 | 46.29 | 45.98 | 50.14 | 49.78 | 2.0 | 121.3 | 176.0 | 700.0 | 24.29 | 30.86 |
| 1000.0 | 46.09 | 45.75 | 50.44 | 50.05 | 3.0 | 175.3 | 252.5 | 800.0 | 23.99 | 30.59 |
| 1250.0 | 45.26 | 45.10 | 49.31 | 49.06 | 4.0 | 233.5 | 334.0 | 900.0 | 23.84 | 30.39 |
| 1500.0 | 45.12 | 44.89 | 49.65 | 49.35 | 5.0 | 282.5 | 409.3 | 1000.0 | 23.86 | 30.51 |
| 1750.0 | 44.62 | 44.46 | 49.20 | 48.88 | 6.0 | 319.0 | 462.0 | 1100.0 | 23.86 | 30.53 |
| 2000.0 | 43.65 | 43.55 | 47.62 | 47.78 | 7.0 | 386.5 | 559.5 | 1200.0 | 23.77 | 30.58 |
| 2500.0 | 42.40 | 42.22 | 46.94 | 47.01 | 8.0 | 432.8 | 614.8 | 1300.0 | 24.58 | 30.95 |
| 3000.0 | 40.70 | 40.68 | 45.78 | 45.68 | 9.0 | 491.0 | 729.5 | 1400.0 | 24.46 | 30.75 |
| 3500.0 | 38.61 | 38.61 | 43.12 | 43.33 | 10.0 | 540.5 | 776.8 | 1500.0 | 24.36 | 30.92 |
| 4000.0 | 38.09 | 38.20 | 42.75 | 43.01 | | | | 1600.0 | 24.41 | 31.02 |
| 4500.0 | 35.62 | 35.98 | 40.94 | 41.53 | | | | 1700.0 | 24.56 | 31.37 |
| 5000.0 | 36.21 | 36.61 | 40.71 | 41.32 | | | | 1800.0 | 24.27 | 31.07 |
| 5500.0 | 33.90 | 34.19 | 38.28 | 38.96 | | | | 1900.0 | 24.17 | 30.97 |
| 6000.0 | 34.14 | 34.38 | 39.72 | 40.31 | | | | 2000.0 | 24.70 | 31.29 |
| | | | | | | | | 2250.0 | 23.80 | 29.86 |
| | | | | | | | | 2500.0 | 23.65 | 29.78 |
| | | | | | | | | 2750.0 | 23.42 | 29.71 |
| | | | | | | | | 3000.0 | 22.64 | 29.22 |
| | | | | | | | | 3250.0 | 21.99 | 28.40 |
| | | | | | | | | 3500.0 | 22.15 | 28.31 |
| | | | | | | | | 3750.0 | 22.26 | 28.17 |
| | | | | | | | | 4000.0 | 22.00 | 27.80 |
| | | | | | | | | 4250.0 | 21.09 | 27.36 |
| | | | | | | | | 4500.0 | 19.90 | 26.68 |
| | | | | | | | | 4750.0 | 20.31 | 26.60 |
| | | | | | | | | 5000.0 | 20.84 | 26.87 |
| | | | | | | | | 5250.0 | 21.02 | 26.80 |
| | | | | | | | | 5500.0 | 20.85 | 26.92 |
| | | | | | | | | 5750.0 | 21.15 | 27.43 |
| | | | | | | | | 6000.0 | 21.01 | 27.32 |

Typical Performance Data

| RF FREQ (MHz) | INSERTION LOSS @ VDD=+5V OVER TEMPERATURE | | | | | | RF FREQ (MHz) | ISOLATION @ VDD=+5V OVER TEMPERATURE | | | | | | | | | | | |
|------------------|---|-------|--------|--------------------|-------|--------|------------------|--------------------------------------|--------|--------|--------------------|-------|--------|-----------------------|--------|--------|-----------------------|--------|--------|
| | RF COM-RF1 (dB) | | | RF COM-RF2 (dB) | | | | RF COM-RF1 (dB) | | | RF COM-RF2 (dB) | | | RF1-RF2 (ON1) (dB) | | | RF1-RF2 (ON2) (dB) | | |
| | | | | | | | | | | | | | | State LOW* | | | State HIGH* | | |
| | -55°C | +25°C | +100°C | -55°C | +25°C | +100°C | | -55°C | +25°C | +100°C | -55°C | +25°C | +100°C | -55°C | +25°C | +100°C | -55°C | +25°C | +100°C |
| 0.3 | 0.56 | 0.75 | 0.83 | 0.55 | 0.73 | 0.81 | 0.3 | 114.38 | 103.15 | 115.23 | 99.44 | 89.97 | 100.82 | 101.92 | 95.87 | 91.16 | 106.53 | 114.92 | 93.32 |
| 0.5 | 0.56 | 0.75 | 0.83 | 0.56 | 0.72 | 0.81 | 0.5 | 111.04 | 109.99 | 102.14 | 105.42 | 96.46 | 97.30 | 108.02 | 100.24 | 92.77 | 102.89 | 102.75 | 109.94 |
| 1.0 | 0.57 | 0.76 | 0.84 | 0.57 | 0.73 | 0.82 | 1.0 | 105.33 | 101.91 | 101.32 | 103.86 | 98.76 | 92.11 | 107.16 | 96.99 | 92.04 | 108.97 | 103.86 | 104.47 |
| 5.0 | 0.59 | 0.77 | 0.85 | 0.56 | 0.71 | 0.80 | 5.0 | 88.99 | 90.50 | 90.90 | 83.47 | 82.25 | 81.01 | 83.35 | 83.21 | 81.69 | 88.63 | 89.64 | 91.09 |
| 10.0 | 0.61 | 0.77 | 0.85 | 0.57 | 0.71 | 0.79 | 10.0 | 79.77 | 81.92 | 83.52 | 74.96 | 74.34 | 74.02 | 75.07 | 75.63 | 74.96 | 80.09 | 82.34 | 83.26 |
| 50.0 | 0.67 | 0.80 | 0.85 | 0.57 | 0.71 | 0.79 | 50.0 | 77.90 | 77.19 | 76.54 | 61.43 | 60.87 | 60.74 | 62.44 | 62.27 | 62.27 | 78.26 | 77.34 | 76.93 |
| 100.0 | 0.67 | 0.80 | 0.86 | 0.57 | 0.72 | 0.80 | 100.0 | 71.75 | 71.84 | 71.72 | 57.72 | 58.23 | 58.85 | 58.78 | 59.65 | 60.42 | 70.77 | 71.40 | 71.31 |
| 200.0 | 0.69 | 0.82 | 0.88 | 0.58 | 0.74 | 0.82 | 200.0 | 70.32 | 70.24 | 70.21 | 58.19 | 59.36 | 60.30 | 59.73 | 61.12 | 62.24 | 67.86 | 68.07 | 68.32 |
| 300.0 | 0.69 | 0.83 | 0.90 | 0.59 | 0.76 | 0.85 | 300.0 | 69.36 | 70.06 | 69.70 | 59.62 | 60.78 | 61.82 | 61.22 | 62.35 | 63.25 | 65.62 | 66.14 | 66.40 |
| 400.0 | 0.69 | 0.84 | 0.92 | 0.59 | 0.77 | 0.87 | 400.0 | 69.64 | 69.97 | 70.02 | 60.53 | 61.73 | 62.39 | 61.91 | 62.72 | 63.19 | 64.32 | 64.58 | 64.70 |
| 500.0 | 0.69 | 0.85 | 0.93 | 0.60 | 0.78 | 0.89 | 500.0 | 68.84 | 69.64 | 69.93 | 61.19 | 62.22 | 62.84 | 61.54 | 61.89 | 61.95 | 63.29 | 63.06 | 63.19 |
| 600.0 | 0.69 | 0.85 | 0.94 | 0.60 | 0.79 | 0.90 | 600.0 | 70.18 | 70.53 | 70.18 | 62.22 | 63.03 | 63.61 | 60.83 | 60.98 | 60.75 | 61.44 | 61.72 | 61.67 |
| 700.0 | 0.69 | 0.86 | 0.96 | 0.61 | 0.81 | 0.92 | 700.0 | 70.83 | 70.93 | 71.18 | 62.91 | 63.47 | 63.43 | 60.05 | 59.97 | 59.93 | 60.26 | 60.53 | 60.61 |
| 800.0 | 0.69 | 0.87 | 0.97 | 0.62 | 0.82 | 0.94 | 800.0 | 69.27 | 70.40 | 69.80 | 64.34 | 64.27 | 64.08 | 59.12 | 59.14 | 58.75 | 59.65 | 59.57 | 59.58 |
| 900.0 | 0.69 | 0.89 | 0.99 | 0.62 | 0.83 | 0.95 | 900.0 | 71.95 | 72.66 | 71.72 | 64.31 | 64.12 | 63.50 | 58.18 | 58.06 | 57.87 | 58.27 | 58.56 | 58.65 |
| 1000.0 | 0.70 | 0.90 | 1.00 | 0.63 | 0.85 | 0.97 | 1000.0 | 71.58 | 74.07 | 71.80 | 65.13 | 63.73 | 63.63 | 57.15 | 57.35 | 56.97 | 57.48 | 57.50 | 57.79 |
| 1200.0 | 0.71 | 0.92 | 1.03 | 0.65 | 0.88 | 1.01 | 1200.0 | 74.51 | 75.55 | 74.72 | 66.25 | 64.39 | 62.97 | 55.80 | 55.66 | 55.71 | 55.81 | 56.05 | 56.20 |
| 1500.0 | 0.73 | 0.97 | 1.09 | 0.68 | 0.93 | 1.07 | 1500.0 | 74.28 | 80.61 | 76.49 | 67.00 | 64.35 | 62.77 | 53.98 | 54.04 | 53.97 | 53.68 | 54.03 | 54.07 |
| 1700.0 | 0.75 | 0.99 | 1.13 | 0.71 | 0.96 | 1.11 | 1700.0 | 68.23 | 75.16 | 80.20 | 68.73 | 65.33 | 62.72 | 52.65 | 52.81 | 53.04 | 52.13 | 52.61 | 52.82 |
| 2000.0 | 0.77 | 1.03 | 1.17 | 0.73 | 1.00 | 1.16 | 2000.0 | 67.45 | 73.04 | 76.95 | 67.74 | 65.42 | 63.97 | 51.09 | 51.37 | 51.43 | 50.97 | 51.18 | 51.49 |
| 2200.0 | 0.81 | 1.08 | 1.20 | 0.76 | 1.04 | 1.17 | 2200.0 | 62.91 | 68.48 | 70.37 | 64.88 | 64.98 | 61.66 | 50.51 | 50.68 | 51.16 | 49.72 | 50.34 | 50.23 |
| 2500.0 | 0.84 | 1.13 | 1.25 | 0.79 | 1.09 | 1.22 | 2500.0 | 60.94 | 63.49 | 64.71 | 62.89 | 62.33 | 63.91 | 49.02 | 49.71 | 49.62 | 49.46 | 49.54 | 49.90 |
| 2700.0 | 0.89 | 1.18 | 1.29 | 0.86 | 1.13 | 1.27 | 2700.0 | 57.46 | 61.67 | 66.90 | 60.17 | 61.63 | 61.46 | 48.67 | 48.94 | 49.09 | 48.99 | 48.63 | 49.14 |
| 3000.0 | 0.96 | 1.22 | 1.36 | 0.92 | 1.18 | 1.34 | 3000.0 | 57.98 | 59.31 | 62.38 | 56.63 | 59.26 | 58.88 | 48.05 | 48.27 | 48.68 | 47.08 | 47.63 | 47.93 |
| 3200.0 | 0.93 | 1.22 | 1.36 | 0.88 | 1.17 | 1.33 | 3200.0 | 56.21 | 57.76 | 59.54 | 55.71 | 58.34 | 58.40 | 47.22 | 47.60 | 47.78 | 46.36 | 47.13 | 46.83 |
| 3500.0 | 0.94 | 1.23 | 1.37 | 0.91 | 1.20 | 1.36 | 3500.0 | 56.90 | 56.26 | 59.15 | 52.68 | 56.69 | 56.29 | 46.14 | 46.44 | 47.07 | 45.10 | 45.80 | 45.53 |
| 3700.0 | 0.93 | 1.22 | 1.38 | 0.88 | 1.19 | 1.36 | 3700.0 | 52.49 | 55.21 | 54.36 | 54.74 | 54.40 | 60.01 | 45.26 | 46.13 | 46.29 | 44.67 | 45.49 | 45.16 |
| 4000.0 | 0.93 | 1.22 | 1.40 | 0.90 | 1.21 | 1.40 | 4000.0 | 53.45 | 54.51 | 55.04 | 51.21 | 53.61 | 55.24 | 45.41 | 45.35 | 45.62 | 44.41 | 44.66 | 45.05 |
| 4200.0 | 0.88 | 1.23 | 1.42 | 0.87 | 1.21 | 1.41 | 4200.0 | 51.70 | 53.41 | 51.92 | 51.71 | 53.35 | 61.44 | 44.48 | 45.04 | 45.05 | 43.79 | 44.01 | 44.02 |
| 4500.0 | 0.92 | 1.27 | 1.45 | 0.90 | 1.24 | 1.44 | 4500.0 | 53.18 | 51.76 | 54.38 | 50.33 | 52.90 | 52.46 | 43.85 | 44.52 | 44.54 | 43.56 | 43.63 | 43.95 |
| 4700.0 | 0.94 | 1.33 | 1.52 | 0.91 | 1.30 | 1.49 | 4700.0 | 50.63 | 49.95 | 52.40 | 49.10 | 52.02 | 54.83 | 43.61 | 44.28 | 44.75 | 42.92 | 43.05 | 42.76 |
| 5000.0 | 1.08 | 1.45 | 1.66 | 1.03 | 1.42 | 1.63 | 5000.0 | 46.65 | 50.23 | 48.38 | 52.01 | 52.20 | 52.22 | 43.62 | 44.18 | 44.66 | 42.16 | 42.41 | 42.65 |
| 5200.0 | 1.09 | 1.50 | 1.73 | 1.10 | 1.49 | 1.72 | 5200.0 | 48.86 | 50.35 | 50.09 | 48.78 | 51.42 | 51.17 | 43.68 | 43.73 | 44.18 | 42.16 | 42.04 | 41.91 |
| 5500.0 | 1.13 | 1.55 | 1.77 | 1.15 | 1.54 | 1.77 | 5500.0 | 50.24 | 50.56 | 52.69 | 50.01 | 50.55 | 50.21 | 43.61 | 43.51 | 43.94 | 41.52 | 41.72 | 41.52 |
| 5700.0 | 1.07 | 1.51 | 1.77 | 1.11 | 1.51 | 1.80 | 5700.0 | 49.56 | 50.77 | 50.84 | 47.72 | 49.74 | 51.45 | 43.46 | 43.03 | 43.38 | 41.56 | 41.28 | 41.24 |
| 6000.0 | 1.03 | 1.47 | 1.74 | 1.10 | 1.50 | 1.82 | 6000.0 | 48.67 | 50.89 | 51.40 | 46.62 | 49.04 | 50.54 | 42.79 | 42.21 | 42.31 | 41.12 | 40.77 | 41.00 |

***Note**

| State of Control Voltage | RF Common to | |
|--------------------------|--------------|-----|
| | RF1 | RF2 |
| LOW | ON | OFF |
| HIGH | OFF | ON |

ON - Low insertion loss state
OFF - Isolation state

RF Switch SPDT

VSWA2-63DR+

Typical Performance Data









| RF FREQ (MHz) | VSWR @ VDD=+5V OVER TEMPERATURE (:1) | | | | | | | | | | | | RF FREQ (MHz) | VSWR @ VDD=+5V OVER TEMPERATURE (:1) | | | | | |
|------------------|--------------------------------------|-------|--------|-------------|-------|--------|------------|-------|--------|-------------|-------|--------|------------------|--------------------------------------|-------|--------|------------|-------|--------|
| | RF COM | | | RF COM | | | RF1 | | | RF2 | | | | RF1 | | | RF2 | | |
| | State LOW* | | | State HIGH* | | | State LOW* | | | State HIGH* | | | | State HIGH* | | | State LOW* | | |
| | -55°C | +25°C | +100°C | -55°C | +25°C | +100°C | -55°C | +25°C | +100°C | -55°C | +25°C | +100°C | | -55°C | +25°C | +100°C | -55°C | +25°C | +100°C |
| 0.3 | 1.13 | 1.17 | 1.20 | 1.14 | 1.17 | 1.19 | 1.13 | 1.17 | 1.20 | 1.14 | 1.17 | 1.19 | 500.0 | 1.59 | 1.70 | 1.84 | 1.57 | 1.69 | 1.83 |
| 0.5 | 1.13 | 1.18 | 1.20 | 1.13 | 1.17 | 1.19 | 1.14 | 1.18 | 1.20 | 1.13 | 1.17 | 1.19 | 600.0 | 1.51 | 1.65 | 1.79 | 1.49 | 1.63 | 1.78 |
| 1.0 | 1.14 | 1.18 | 1.20 | 1.13 | 1.17 | 1.19 | 1.14 | 1.18 | 1.21 | 1.13 | 1.17 | 1.19 | 700.0 | 1.46 | 1.61 | 1.76 | 1.44 | 1.59 | 1.75 |
| 5.0 | 1.13 | 1.18 | 1.20 | 1.13 | 1.16 | 1.19 | 1.14 | 1.18 | 1.20 | 1.13 | 1.16 | 1.19 | 800.0 | 1.42 | 1.59 | 1.75 | 1.41 | 1.57 | 1.73 |
| 10.0 | 1.14 | 1.17 | 1.19 | 1.15 | 1.18 | 1.20 | 1.14 | 1.18 | 1.20 | 1.14 | 1.18 | 1.20 | 900.0 | 1.40 | 1.57 | 1.74 | 1.38 | 1.55 | 1.71 |
| 50.0 | 1.11 | 1.14 | 1.17 | 1.13 | 1.16 | 1.19 | 1.11 | 1.15 | 1.17 | 1.13 | 1.16 | 1.19 | 1000.0 | 1.39 | 1.57 | 1.74 | 1.36 | 1.54 | 1.71 |
| 100.0 | 1.10 | 1.14 | 1.17 | 1.13 | 1.16 | 1.19 | 1.11 | 1.14 | 1.16 | 1.13 | 1.16 | 1.18 | 1200.0 | 1.37 | 1.56 | 1.73 | 1.34 | 1.53 | 1.70 |
| 200.0 | 1.10 | 1.13 | 1.16 | 1.12 | 1.16 | 1.18 | 1.10 | 1.13 | 1.16 | 1.12 | 1.15 | 1.17 | 1500.0 | 1.36 | 1.56 | 1.74 | 1.34 | 1.53 | 1.71 |
| 300.0 | 1.10 | 1.14 | 1.16 | 1.13 | 1.16 | 1.18 | 1.09 | 1.13 | 1.15 | 1.11 | 1.14 | 1.17 | 1700.0 | 1.37 | 1.57 | 1.75 | 1.33 | 1.54 | 1.71 |
| 400.0 | 1.11 | 1.15 | 1.17 | 1.13 | 1.17 | 1.19 | 1.09 | 1.12 | 1.15 | 1.11 | 1.14 | 1.16 | 2000.0 | 1.38 | 1.59 | 1.76 | 1.35 | 1.55 | 1.71 |
| 500.0 | 1.12 | 1.16 | 1.19 | 1.14 | 1.18 | 1.21 | 1.08 | 1.12 | 1.14 | 1.10 | 1.13 | 1.16 | 2200.0 | 1.39 | 1.59 | 1.76 | 1.37 | 1.56 | 1.73 |
| 600.0 | 1.13 | 1.17 | 1.21 | 1.16 | 1.19 | 1.23 | 1.08 | 1.12 | 1.14 | 1.09 | 1.13 | 1.15 | 2500.0 | 1.42 | 1.61 | 1.76 | 1.38 | 1.57 | 1.73 |
| 700.0 | 1.14 | 1.18 | 1.22 | 1.17 | 1.21 | 1.24 | 1.08 | 1.11 | 1.14 | 1.09 | 1.12 | 1.14 | 2700.0 | 1.42 | 1.61 | 1.76 | 1.41 | 1.58 | 1.73 |
| 800.0 | 1.16 | 1.20 | 1.23 | 1.18 | 1.22 | 1.25 | 1.07 | 1.10 | 1.13 | 1.08 | 1.11 | 1.13 | 3000.0 | 1.43 | 1.60 | 1.72 | 1.42 | 1.58 | 1.70 |
| 900.0 | 1.17 | 1.21 | 1.24 | 1.20 | 1.24 | 1.27 | 1.06 | 1.09 | 1.12 | 1.07 | 1.10 | 1.12 | 3200.0 | 1.45 | 1.60 | 1.71 | 1.42 | 1.57 | 1.70 |
| 1000.0 | 1.18 | 1.23 | 1.26 | 1.22 | 1.26 | 1.29 | 1.06 | 1.09 | 1.11 | 1.06 | 1.09 | 1.11 | 3500.0 | 1.44 | 1.56 | 1.65 | 1.42 | 1.54 | 1.63 |
| 1200.0 | 1.21 | 1.25 | 1.28 | 1.25 | 1.29 | 1.31 | 1.03 | 1.06 | 1.09 | 1.03 | 1.06 | 1.08 | 3700.0 | 1.46 | 1.55 | 1.63 | 1.43 | 1.52 | 1.60 |
| 1500.0 | 1.25 | 1.30 | 1.32 | 1.29 | 1.33 | 1.35 | 1.04 | 1.05 | 1.08 | 1.03 | 1.04 | 1.07 | 4000.0 | 1.45 | 1.49 | 1.55 | 1.42 | 1.48 | 1.53 |
| 1700.0 | 1.27 | 1.31 | 1.33 | 1.31 | 1.35 | 1.37 | 1.10 | 1.10 | 1.11 | 1.09 | 1.08 | 1.09 | 4200.0 | 1.45 | 1.47 | 1.51 | 1.41 | 1.44 | 1.47 |
| 2000.0 | 1.33 | 1.36 | 1.38 | 1.35 | 1.38 | 1.40 | 1.22 | 1.21 | 1.22 | 1.20 | 1.19 | 1.19 | 4500.0 | 1.45 | 1.42 | 1.43 | 1.42 | 1.39 | 1.40 |
| 2200.0 | 1.40 | 1.41 | 1.43 | 1.40 | 1.42 | 1.43 | 1.29 | 1.29 | 1.29 | 1.26 | 1.26 | 1.26 | 4700.0 | 1.44 | 1.38 | 1.38 | 1.39 | 1.36 | 1.34 |
| 2500.0 | 1.48 | 1.48 | 1.48 | 1.46 | 1.47 | 1.47 | 1.43 | 1.42 | 1.41 | 1.39 | 1.39 | 1.38 | 5000.0 | 1.45 | 1.35 | 1.33 | 1.40 | 1.31 | 1.27 |
| 2700.0 | 1.55 | 1.53 | 1.51 | 1.54 | 1.51 | 1.50 | 1.52 | 1.50 | 1.48 | 1.50 | 1.47 | 1.46 | 5200.0 | 1.42 | 1.31 | 1.26 | 1.41 | 1.28 | 1.23 |
| 3000.0 | 1.58 | 1.54 | 1.50 | 1.57 | 1.52 | 1.49 | 1.60 | 1.58 | 1.54 | 1.59 | 1.56 | 1.53 | 5500.0 | 1.44 | 1.29 | 1.23 | 1.40 | 1.24 | 1.18 |
| 3200.0 | 1.57 | 1.52 | 1.47 | 1.54 | 1.49 | 1.46 | 1.64 | 1.61 | 1.58 | 1.61 | 1.59 | 1.57 | 5700.0 | 1.42 | 1.25 | 1.17 | 1.40 | 1.23 | 1.15 |
| 3500.0 | 1.49 | 1.45 | 1.40 | 1.47 | 1.44 | 1.40 | 1.55 | 1.54 | 1.50 | 1.53 | 1.53 | 1.51 | 6000.0 | 1.42 | 1.23 | 1.14 | 1.38 | 1.20 | 1.10 |
| 3700.0 | 1.44 | 1.40 | 1.37 | 1.42 | 1.39 | 1.37 | 1.50 | 1.48 | 1.44 | 1.48 | 1.46 | 1.45 | | | | | | | |
| 4000.0 | 1.41 | 1.37 | 1.36 | 1.39 | 1.37 | 1.37 | 1.41 | 1.38 | 1.34 | 1.37 | 1.37 | 1.35 | | | | | | | |
| 4200.0 | 1.39 | 1.38 | 1.39 | 1.39 | 1.39 | 1.39 | 1.39 | 1.35 | 1.32 | 1.36 | 1.33 | 1.31 | | | | | | | |
| 4500.0 | 1.42 | 1.45 | 1.47 | 1.44 | 1.46 | 1.47 | 1.42 | 1.39 | 1.36 | 1.39 | 1.35 | 1.33 | | | | | | | |
| 4700.0 | 1.49 | 1.52 | 1.55 | 1.49 | 1.53 | 1.55 | 1.47 | 1.43 | 1.40 | 1.42 | 1.41 | 1.37 | | | | | | | |
| 5000.0 | 1.60 | 1.65 | 1.65 | 1.60 | 1.65 | 1.65 | 1.59 | 1.55 | 1.52 | 1.54 | 1.50 | 1.45 | | | | | | | |
| 5200.0 | 1.64 | 1.68 | 1.69 | 1.66 | 1.69 | 1.68 | 1.61 | 1.57 | 1.53 | 1.58 | 1.52 | 1.47 | | | | | | | |
| 5500.0 | 1.69 | 1.72 | 1.73 | 1.71 | 1.71 | 1.71 | 1.65 | 1.58 | 1.56 | 1.60 | 1.52 | 1.47 | | | | | | | |
| 5700.0 | 1.69 | 1.70 | 1.73 | 1.73 | 1.71 | 1.72 | 1.60 | 1.54 | 1.52 | 1.58 | 1.50 | 1.46 | | | | | | | |
| 6000.0 | 1.61 | 1.63 | 1.66 | 1.66 | 1.66 | 1.67 | 1.56 | 1.49 | 1.47 | 1.53 | 1.46 | 1.42 | | | | | | | |

***Note**

| State of Control Voltage | RF Common to | | |
|--------------------------|--------------|--|-----|
| | RF1 | | RF2 |
| LOW | ON | | OFF |
| HIGH | OFF | | ON |

ON - Low insertion loss state
OFF - Isolation state

Typical Performance Curves




***Note**

| State of Control Voltage | RF Common to | |
|--------------------------|--------------|-----|
| | RF1 | RF2 |
| LOW | ON | OFF |
| HIGH | OFF | ON |


ON - Low insertion loss state
 OFF - Isolation state

Typical Performance Curves


Insertion Loss @ VDD=+5V over Temperature
RF COM-RF1 & RF COM-RF2




Isolation @ VDD=+5V over Temperature
RF COM-RF1 & RF COM-RF2




Isolation @ VDD=+5V over Temperature,
RF1-RF2




VSWR @ VDD=+5V over Temperature
RF COM




VSWR @ VDD=+5V over Temperature
RF1(State LOW*) & RF2 (State HIGH*)



VSWR @ VDD=+5V over Temperature
RF1 (State HIGH*) & RF2 (State LOW*)



DC Current vs Repetition Rate




*Note


| State of Control Voltage | RF Common to | |
|--------------------------|--------------|-----|
| | RF1 | RF2 |
| LOW | ON | OFF |
| HIGH | OFF | ON |

ON - Low insertion loss state
OFF - Isolation state

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE # | A | B | C | D | E | F | G | H | J | K |
|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| DG1235-1 | .157 (4.00) | .157 (4.00) | .035 (0.90) | .008 (0.20) | .106 (2.70) | .106 (2.70) | .012 (0.30) | .019 (0.48) | .016 (0.40) | .026 (0.65) |


| CASE # | L | M | N | P | Q | R | S | T | WT. GRAM |
|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| DG1235-1 | .185 (4.70) | .185 (4.70) | .085 (2.16) | .014 (0.36) | .031 (0.79) | .085 (2.16) | .013 (0.33) | .019 (0.48) | .04 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: NiPdAu. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|---------|-------------------------------|----------|-----|------|
| OR | M116142 | NEW RELEASE | 04/08/09 | MMG | RD |
| A | M124875 | MODIFIED LAYOUT, CHANGED "TB" | 10/30/09 | AV | RD |
| B | M153891 | MODIFIED LAYOUT TO DG1235-1 | 01/22/16 | ITG | RD |

SUGGESTED MOUNTING CONFIGURATION FOR
DG1235-1 CASE STYLE, "16SW02" PIN CODE



NOTES:

1. TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $.010" \pm .001"$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | | DATE |
|--|----------|-----|----------|
| DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ± | DRAWN | MMG | 04/08/09 |
| | CHECKED | IL | 04/08/09 |
| | APPROVED | RD | 04/08/09 |



Mini-Circuits®



13 Neptune Avenue
Brooklyn NY 11235

PL, 16SW02, DG1235-1, TB-486+

| | | | |
|------------------|---------------------|--------------------------|-----------|
| SIZE A | CODE IDENT 15542 | DRAWING NO: 98-PL-278 | REV: B |
| FILE: 98PL278 | SCALE: 10:1 | SHEET: 1 OF 1 | |

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


Evaluation Board and Circuit



NOTES:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent, Dielectric Constant=3.5, Thickness=.010 inch.

Schematic Diagram

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|-------------------------------|--|-----------------------------|
| Operating Temperature | -40° to 85° C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -65° to 150° C Ambient Environment | Individual Model Data Sheet |
| Temperature Cycling | -65° to 150°C, 500 cycles | JESD22-A104, condition C |
| Autoclave | 121°C, 100% RH, 30 PSIA, 96 hours, unbiased | JESD22-A102 |
| High Temp Storage | 150°C 1008 hours | JESD22-A103 |
| Solderability | Per Reference Spec | JESD22-B102 |
| Resistance to Solvent | Per Reference Spec | MIL-STD-202, Method 215J |
| Moisture Sensitivity: Level 1 | Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak | JESD22-A113 |